

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333531

Luminaire Tested: **S125RDIP-S610D590U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333531
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4499.9 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53								
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45								
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38								
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32								
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28								
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24								
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22								
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19								
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17								
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16								
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.1
10°-20°	264.3	5.9
20°-30°	383.3	8.5
30°-40°	436.9	9.7
40°-50°	425.9	9.5
50°-60°	358.5	8.0
60°-70°	251.3	5.6
70°-80°	129.2	2.9
80°-90°	34.2	0.8
90°-100°	205.1	4.6
100°-110°	440.9	9.8
110°-120°	413.8	9.2
120°-130°	335.3	7.5
130°-140°	269.1	6.0
140°-150°	203.1	4.5
150°-160°	142.9	3.2
160°-170°	84.3	1.9
170°-180°	27.4	0.6
0°-30°	742.3	16.5
0°-40°	1179.2	26.2
0°-60°	1963.5	43.6
0°-90°	2378.1	52.8
90°-120°	1059.7	23.5
90°-150°	1867.2	41.5
90°-180°	2122.0	47.2
0°-180°	4499.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	1	5	9	12	13	3
95°	19	56	505	229	134	20
105°	64	90	414	814	756	68
115°	115	139	332	716	842	113
125°	160	187	318	569	663	142
135°	187	225	316	477	551	145
145°	218	250	317	395	435	137
155°	249	268	309	349	364	114
165°	272	279	297	315	319	76
175°	282	282	285	288	287	27
180°	283	283	283	283	283	



TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.3	12.5	11.8	11.1	10.8	10.8	10.9	10.8	10.9	11.1
90°	0.6	1.1	2.3	3.4	4.6	5.7	6.3	7.4	8.0	9.1	9.7
92.5°	7.0	8.4	13.2	20.3	30.1	46.8	77.9	130.2	186.9	183.9	148.9
95°	18.8	19.4	24.0	30.2	42.8	68.5	129.5	255.0	412.4	505.4	494.6
97.5°	31.3	31.9	35.1	41.4	52.7	71.2	111.6	203.5	368.3	539.7	625.8
100°	39.9	41.1	43.4	49.6	60.5	77.6	110.7	184.8	328.6	515.1	657.7
102.5°	49.5	50.2	52.0	58.8	68.7	85.3	114.8	177.1	298.4	471.7	638.5
105°	64.5	64.5	67.3	73.0	82.1	98.1	123.2	174.0	269.2	413.6	577.3
107.5°	79.1	80.2	82.9	87.6	97.1	111.5	135.8	179.2	256.9	373.5	514.8
110°	89.6	90.7	93.0	98.1	106.7	121.5	144.9	184.2	253.3	354.8	479.2



TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	100.1	101.2	103.0	108.2	116.7	131.1	153.6	190.6	253.3	343.9	452.7
115°	115.2	116.4	118.1	123.2	131.8	146.0	167.1	200.2	255.0	332.0	423.8
117.5°	128.9	130.6	132.5	137.6	147.3	161.1	181.1	211.2	258.7	326.2	406.6
120°	138.0	139.8	142.0	147.2	156.9	171.1	191.1	218.5	262.4	323.4	397.0
122.5°	147.6	148.9	150.7	155.8	166.5	180.7	200.7	226.7	265.6	321.2	388.8
125°	159.7	160.9	163.7	168.8	179.7	194.5	213.3	237.9	271.0	318.3	377.6
127.5°	169.2	170.9	174.6	181.1	192.6	207.4	225.5	248.1	277.0	316.9	367.4
130°	175.1	176.8	181.4	188.8	200.8	215.6	233.3	255.0	280.7	316.0	360.5
132.5°	179.7	181.9	187.3	195.7	208.1	222.9	240.6	260.9	284.8	316.0	355.0
135°	187.1	189.4	196.2	205.4	217.3	232.7	250.4	269.2	290.3	316.0	348.5
137.5°	196.5	198.2	204.6	213.7	225.4	241.3	257.4	275.4	295.5	316.7	342.7
140°	201.9	203.6	210.5	219.6	230.5	245.9	262.4	279.5	297.8	317.2	340.0
142.5°	208.3	209.6	216.0	225.1	235.5	250.0	265.6	281.8	299.1	317.6	337.7
145°	217.9	219.0	224.7	232.7	243.0	256.1	271.0	285.2	300.6	317.2	334.3
147.5°	227.9	228.6	233.5	240.9	249.8	261.4	274.4	287.3	301.2	315.7	330.7
150°	233.9	235.0	239.0	246.4	254.4	264.1	276.7	288.6	301.2	314.3	328.0
152.5°	240.3	240.9	244.5	251.0	258.5	267.3	278.9	289.5	300.7	312.5	324.8
155°	248.7	248.7	252.1	257.8	263.5	271.5	281.2	290.3	299.5	309.2	319.4
157.5°	256.2	256.1	258.9	263.8	268.8	274.8	283.2	290.9	298.0	305.7	314.4
160°	261.3	260.7	263.0	267.0	271.5	276.7	284.1	290.9	296.6	303.5	310.3
162.5°	265.4	264.8	267.1	270.6	274.3	278.5	285.0	290.5	295.3	300.7	306.7
165°	271.5	270.4	272.1	274.9	277.2	280.7	285.2	289.8	293.2	296.6	301.2
167.5°	275.6	275.1	276.1	277.7	279.3	281.4	285.2	288.4	290.0	292.6	295.8
170°	278.4	277.8	278.4	279.5	280.7	282.4	285.2	287.5	288.6	290.3	292.6
172.5°	280.2	279.2	279.7	280.9	281.6	282.4	284.8	286.6	286.8	287.6	289.4
175°	282.4	281.2	281.8	282.4	282.4	282.4	284.1	285.2	284.6	284.6	285.2
177.5°	283.4	282.5	282.5	282.9	282.5	282.5	283.4	283.8	282.9	282.9	283.4
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	11.2	11.3	11.4	11.6	11.4	11.3	11.3	11.1
90°	10.3	10.8	11.4	12.5	12.5	12.5	13.1	13.1
92.5°	101.1	73.4	55.2	46.8	39.5	38.1	37.3	36.4
95°	410.1	323.4	253.3	205.4	164.9	147.7	143.2	134.1
97.5°	610.8	550.0	481.7	415.0	379.8	347.8	331.3	324.0
100°	701.6	673.7	614.9	555.6	516.2	475.2	454.1	444.9
102.5°	732.2	749.4	721.2	681.1	639.0	609.8	586.9	580.0
105°	714.2	792.3	817.4	811.1	792.9	774.1	762.7	755.8
107.5°	649.8	754.1	818.6	848.3	857.6	857.5	853.7	849.1
110°	602.4	710.8	791.2	839.7	865.3	876.2	880.2	880.2



TEST NUMBER: P333531

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	565.0	667.9	749.2	806.4	843.9	862.5	872.4	876.5
115°	517.9	606.4	684.5	746.7	791.2	818.6	834.5	842.0
117.5°	487.6	563.8	631.1	688.2	732.7	761.0	776.8	781.4
120°	471.2	539.6	602.4	652.6	694.8	722.2	737.6	742.1
122.5°	458.9	522.3	578.2	625.2	662.8	687.9	703.3	707.4
125°	440.9	499.1	548.8	589.8	621.8	645.2	657.7	663.4
127.5°	422.7	477.0	523.3	561.8	590.7	611.4	623.2	625.8
130°	411.3	461.5	506.0	543.0	571.6	590.4	601.8	605.2
132.5°	399.9	446.9	487.3	523.0	551.5	570.3	580.8	584.7
135°	385.0	424.4	460.9	493.4	518.5	537.3	547.6	551.0
137.5°	372.5	404.3	434.7	462.3	484.7	501.9	511.3	515.1
140°	365.6	392.5	418.7	442.7	463.8	478.6	487.1	490.0
142.5°	359.7	382.4	405.0	425.8	443.7	456.2	464.3	466.7
145°	352.0	369.6	387.3	402.7	416.4	426.1	432.4	434.7
147.5°	344.7	359.0	372.6	384.2	395.1	402.8	406.5	407.5
150°	340.5	353.1	363.9	374.2	382.8	389.6	391.9	392.5
152.5°	336.0	347.2	357.1	365.1	372.3	377.7	380.0	380.6
155°	329.1	338.3	346.2	352.5	358.2	362.2	363.9	364.5
157.5°	322.3	329.8	336.0	340.9	345.3	348.6	350.2	350.1
160°	317.7	323.4	329.1	333.1	337.1	340.0	341.1	340.5
162.5°	312.7	318.0	322.7	326.3	329.4	331.8	332.0	331.9
165°	305.7	309.7	313.2	316.0	318.3	319.4	319.4	319.4
167.5°	299.1	301.8	304.4	306.4	307.6	308.6	308.1	308.0
170°	295.5	297.2	298.9	300.0	301.2	301.8	301.8	301.2
172.5°	291.4	293.1	294.3	295.0	295.3	296.3	295.4	294.8
175°	286.9	286.9	288.1	288.1	288.1	288.6	287.5	286.9
177.5°	283.8	284.3	284.3	284.3	283.8	284.3	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9

(END OF REPORT)