

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331322-927

Luminaire Tested: **SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331322-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4751.7 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331322-927  
CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	19	17	14
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	13
9	49	37	30	25	45	34	28	24	29	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.3	1.5
10°-20°	213.1	4.5
20°-30°	309.3	6.5
30°-40°	326.4	6.9
40°-50°	289.0	6.1
50°-60°	230.6	4.9
60°-70°	156.8	3.3
70°-80°	80.4	1.7
80°-90°	23.7	0.5
90°-100°	69.1	1.5
100°-110°	214.6	4.5
110°-120°	366.8	7.7
120°-130°	482.4	10.2
130°-140°	541.4	11.4
140°-150°	530.9	11.2
150°-160°	445.3	9.4
160°-170°	295.3	6.2
170°-180°	103.2	2.2
0°-30°	595.8	12.5
0°-40°	922.2	19.4
0°-60°	1441.8	30.3
0°-90°	1702.7	35.8
90°-120°	650.5	13.7
90°-150°	2205.2	46.4
90°-180°	3049.0	64.2
0°-180°	4751.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	31	1	31	1	31	14
95°	57	48	57	48	57	64
105°	204	198	204	198	204	215
115°	368	368	368	368	368	363
125°	537	536	537	536	537	479
135°	701	693	701	693	701	540
145°	850	841	850	841	850	531
155°	969	962	969	962	969	446
165°	1047	1046	1047	1046	1047	295
175°	1085	1089	1085	1089	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	12.4	12.4	12.6	12.3	12.3	12.5	12.6	12.4	12.8	13.1	12.4
90°	31.3	31.1	30.9	30.7	30.5	30.6	31.0	31.4	31.8	32.2	27.7
92.5°	29.8	29.8	29.7	29.7	29.6	29.6	29.5	29.4	29.3	29.2	28.2
95°	57.0	57.4	57.9	58.3	58.7	58.9	58.9	58.9	58.9	58.9	58.5
97.5°	98.9	98.9	98.9	98.9	99.0	99.0	99.0	99.0	99.0	99.0	98.2
100°	126.0	126.3	126.5	126.7	126.9	127.0	127.0	127.0	127.0	127.0	126.4
102.5°	157.0	157.2	157.4	157.6	157.8	157.8	157.6	157.5	157.3	157.2	156.4
105°	204.3	204.3	204.3	204.3	204.3	204.1	203.7	203.3	202.9	202.4	202.0
107.5°	248.8	249.8	250.7	251.7	252.5	252.9	252.8	252.6	252.5	252.3	252.3
110°	283.4	284.0	284.6	285.3	285.9	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.6	317.0	317.4	317.9	318.4	318.9	319.3	319.8	320.3	320.8	320.9
115°	368.0	368.7	369.3	369.9	370.5	370.9	371.1	371.4	371.5	371.8	372.2
117.5°	417.2	417.8	418.4	419.1	419.7	420.3	420.7	421.2	421.7	422.2	423.3
120°	451.8	452.4	453.0	453.7	454.2	454.6	454.6	454.6	454.6	454.6	456.2
122.5°	485.7	486.2	486.6	487.0	487.5	487.9	488.5	488.9	489.4	489.9	491.1
125°	537.4	537.6	537.8	538.0	538.2	538.6	539.2	539.9	540.4	541.1	541.7
127.5°	584.5	585.2	585.8	586.5	587.1	587.8	588.5	589.3	590.0	590.7	591.5
130°	618.4	619.2	620.0	620.8	621.6	622.3	622.7	623.1	623.4	623.9	624.3
132.5°	650.8	651.4	652.0	652.8	653.4	654.2	655.1	655.9	656.9	657.7	657.7
135°	701.2	701.8	702.4	703.0	703.6	704.0	704.3	704.5	704.6	704.9	704.5
137.5°	746.8	747.7	748.5	749.2	750.1	750.6	750.8	750.9	751.1	751.2	750.7
140°	778.5	779.3	780.1	780.9	781.7	782.1	782.1	782.1	782.1	782.1	781.2
142.5°	807.2	808.0	808.8	809.6	810.5	810.8	810.6	810.5	810.3	810.2	809.5
145°	850.2	851.0	851.9	852.7	853.5	853.8	853.7	853.4	853.2	853.0	851.8
147.5°	888.7	889.5	890.3	891.0	891.8	892.0	891.5	891.1	890.7	890.2	889.4
150°	913.8	914.3	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8	912.9
152.5°	937.3	938.1	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3	936.4
155°	968.9	969.6	970.2	970.8	971.4	971.2	970.2	969.2	968.1	967.1	966.5
157.5°	996.2	997.2	998.1	999.1	1000.1	999.9	998.5	997.1	995.8	994.3	994.0
160°	1013.1	1013.9	1014.8	1015.6	1016.4	1016.2	1014.9	1013.8	1012.5	1011.3	1011.1
162.5°	1027.9	1028.8	1029.8	1030.8	1031.7	1031.6	1030.2	1028.8	1027.4	1026.0	1025.8
165°	1047.2	1048.2	1049.2	1050.3	1051.2	1051.1	1049.6	1048.2	1046.8	1045.4	1045.4
167.5°	1063.0	1064.1	1065.1	1066.2	1067.2	1067.1	1065.6	1064.2	1062.8	1061.4	1061.4
170°	1071.1	1072.3	1073.6	1074.8	1076.0	1075.9	1074.4	1073.0	1071.6	1070.2	1070.4
172.5°	1077.7	1079.0	1080.1	1081.4	1082.6	1082.5	1081.1	1079.7	1078.2	1076.8	1077.0
175°	1084.9	1086.2	1087.3	1088.6	1089.8	1089.7	1088.3	1086.9	1085.4	1083.9	1084.4
177.5°	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2	1088.5
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	11.7	10.9	10.0	9.7	8.6	8.0	6.6	5.4	5.6	5.9	5.9
90°	23.2	18.7	14.2	10.8	8.3	5.9	3.4	1.0	3.4	5.9	8.3
92.5°	27.2	26.1	25.0	23.6	21.8	20.0	18.1	16.4	18.1	20.0	21.8
95°	58.1	57.7	57.3	56.0	53.9	52.0	49.9	47.8	49.9	52.0	53.9
97.5°	97.4	96.6	95.9	94.6	92.8	91.0	89.2	87.5	89.2	91.0	92.8
100°	125.7	125.2	124.5	123.4	121.8	120.2	118.5	116.8	118.5	120.2	121.8
102.5°	155.6	154.9	154.1	153.0	151.7	150.4	149.1	147.8	149.1	150.4	151.7
105°	201.6	201.2	200.8	200.3	199.7	199.1	198.4	197.8	198.4	199.1	199.7
107.5°	252.3	252.3	252.3	251.8	251.0	250.1	249.1	248.3	249.1	250.1	251.0
110°	286.2	286.2	286.2	285.6	284.3	283.1	281.9	280.7	281.9	283.1	284.3





TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	321.1	321.2	321.5	320.9	319.6	318.5	317.2	316.0	317.2	318.5	319.6
115°	372.6	373.0	373.4	373.0	371.8	370.5	369.3	368.0	369.3	370.5	371.8
117.5°	424.5	425.6	426.7	426.5	424.8	423.3	421.6	419.9	421.6	423.3	424.8
120°	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	456.2	457.9	459.5
122.5°	492.2	493.4	494.5	494.1	492.1	490.1	488.2	486.2	488.2	490.1	492.1
125°	542.3	542.9	543.5	542.9	541.1	539.2	537.4	535.5	537.4	539.2	541.1
127.5°	592.2	592.9	593.7	592.9	590.6	588.3	585.9	583.6	585.9	588.3	590.6
130°	624.7	625.1	625.5	624.4	621.7	619.1	616.4	613.8	616.4	619.1	621.7
132.5°	657.6	657.5	657.4	656.3	654.1	652.0	649.8	647.6	649.8	652.0	654.1
135°	704.0	703.6	703.2	701.9	699.7	697.4	695.1	692.9	695.1	697.4	699.7
137.5°	750.2	749.6	749.1	747.9	746.1	744.3	742.4	740.5	742.4	744.3	746.1
140°	780.1	779.1	778.1	776.7	774.8	772.9	771.1	769.3	771.1	772.9	774.8
142.5°	808.7	808.0	807.3	806.0	804.2	802.4	800.6	798.8	800.6	802.4	804.2
145°	850.6	849.3	848.1	846.8	845.3	843.9	842.5	841.1	842.5	843.9	845.3
147.5°	888.6	887.7	886.9	885.7	883.9	882.2	880.5	878.8	880.5	882.2	883.9
150°	912.1	911.3	910.5	909.4	908.2	907.0	905.8	904.5	905.8	907.0	908.2
152.5°	935.3	934.4	933.3	932.2	931.1	929.8	928.6	927.3	928.6	929.8	931.1
155°	965.9	965.3	964.6	964.1	963.5	962.8	962.2	961.6	962.2	962.8	963.5
157.5°	993.6	993.2	992.8	992.5	992.0	991.7	991.3	990.9	991.3	991.7	992.0
160°	1010.9	1010.7	1010.4	1010.2	1009.7	1009.3	1008.9	1008.5	1008.9	1009.3	1009.7
162.5°	1025.6	1025.4	1025.2	1025.1	1024.9	1024.8	1024.8	1024.7	1024.8	1024.8	1024.9
165°	1045.4	1045.4	1045.4	1045.4	1045.6	1045.8	1046.1	1046.2	1046.1	1045.8	1045.6
167.5°	1061.4	1061.4	1061.5	1061.8	1062.5	1063.0	1063.7	1064.3	1063.7	1063.0	1062.5
170°	1070.6	1070.8	1071.0	1071.4	1072.0	1072.6	1073.2	1073.9	1073.2	1072.6	1072.0
172.5°	1077.2	1077.4	1077.6	1078.0	1078.6	1079.3	1079.9	1080.5	1079.9	1079.3	1078.6
175°	1084.8	1085.2	1085.6	1086.2	1086.7	1087.3	1088.0	1088.6	1088.0	1087.3	1086.7
177.5°	1088.9	1089.2	1089.5	1090.0	1090.4	1090.9	1091.4	1091.9	1091.4	1090.9	1090.4
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	6.2	6.7	7.3	8.2	8.9	9.5	9.2	9.1	9.0	8.5	8.5
90°	10.8	14.2	18.7	23.2	27.7	32.2	31.8	31.4	31.0	30.6	30.5
92.5°	23.6	25.0	26.1	27.2	28.2	29.2	29.3	29.4	29.5	29.6	29.6
95°	56.0	57.3	57.7	58.1	58.5	58.9	58.9	58.9	58.9	58.9	58.7
97.5°	94.6	95.9	96.6	97.4	98.2	99.0	99.0	99.0	99.0	99.0	99.0
100°	123.4	124.5	125.2	125.7	126.4	127.0	127.0	127.0	127.0	127.0	126.9
102.5°	153.0	154.1	154.9	155.6	156.4	157.2	157.3	157.5	157.6	157.8	157.8
105°	200.3	200.8	201.2	201.6	202.0	202.4	202.9	203.3	203.7	204.1	204.3
107.5°	251.8	252.3	252.3	252.3	252.3	252.3	252.5	252.6	252.8	252.9	252.5
110°	285.6	286.2	286.2	286.2	286.2	286.2	286.2	286.2	286.2	286.2	285.9



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	320.9	321.5	321.2	321.1	320.9	320.8	320.3	319.8	319.3	318.9	318.4
115°	373.0	373.4	373.0	372.6	372.2	371.8	371.5	371.4	371.1	370.9	370.5
117.5°	426.5	426.7	425.6	424.5	423.3	422.2	421.7	421.2	420.7	420.3	419.7
120°	461.1	461.1	459.5	457.9	456.2	454.6	454.6	454.6	454.6	454.6	454.2
122.5°	494.1	494.5	493.4	492.2	491.1	489.9	489.4	488.9	488.5	487.9	487.5
125°	542.9	543.5	542.9	542.3	541.7	541.1	540.4	539.9	539.2	538.6	538.2
127.5°	592.9	593.7	592.9	592.2	591.5	590.7	590.0	589.3	588.5	587.8	587.1
130°	624.4	625.5	625.1	624.7	624.3	623.9	623.4	623.1	622.7	622.3	621.6
132.5°	656.3	657.4	657.5	657.6	657.7	657.7	656.9	655.9	655.1	654.2	653.4
135°	701.9	703.2	703.6	704.0	704.5	704.9	704.6	704.5	704.3	704.0	703.6
137.5°	747.9	749.1	749.6	750.2	750.7	751.2	751.1	750.9	750.8	750.6	750.1
140°	776.7	778.1	779.1	780.1	781.2	782.1	782.1	782.1	782.1	782.1	781.7
142.5°	806.0	807.3	808.0	808.7	809.5	810.2	810.3	810.5	810.6	810.8	810.5
145°	846.8	848.1	849.3	850.6	851.8	853.0	853.2	853.4	853.7	853.8	853.5
147.5°	885.7	886.9	887.7	888.6	889.4	890.2	890.7	891.1	891.5	892.0	891.8
150°	909.4	910.5	911.3	912.1	912.9	913.8	914.3	915.0	915.6	916.2	916.2
152.5°	932.2	933.3	934.4	935.3	936.4	937.3	938.1	938.9	939.6	940.4	940.4
155°	964.1	964.6	965.3	965.9	966.5	967.1	968.1	969.2	970.2	971.2	971.4
157.5°	992.5	992.8	993.2	993.6	994.0	994.3	995.8	997.1	998.5	999.9	1000.1
160°	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5	1013.8	1014.9	1016.2	1016.4
162.5°	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4	1028.8	1030.2	1031.6	1031.7
165°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8	1048.2	1049.6	1051.1	1051.2
167.5°	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8	1064.2	1065.6	1067.1	1067.2
170°	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6	1073.0	1074.4	1075.9	1076.0
172.5°	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2	1079.7	1081.1	1082.5	1082.6
175°	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4	1086.9	1088.3	1089.7	1089.8
177.5°	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	8.5	8.3	8.3	8.2	8.3	8.3	8.5	8.5	8.5	9.0	9.1
90°	30.7	30.9	31.1	31.3	31.1	30.9	30.7	30.5	30.6	31.0	31.4
92.5°	29.7	29.7	29.8	29.8	29.8	29.7	29.7	29.6	29.6	29.5	29.4
95°	58.3	57.9	57.4	57.0	57.4	57.9	58.3	58.7	58.9	58.9	58.9
97.5°	98.9	98.9	98.9	98.9	98.9	98.9	98.9	99.0	99.0	99.0	99.0
100°	126.7	126.5	126.3	126.0	126.3	126.5	126.7	126.9	127.0	127.0	127.0
102.5°	157.6	157.4	157.2	157.0	157.2	157.4	157.6	157.8	157.8	157.6	157.5
105°	204.3	204.3	204.3	204.3	204.3	204.3	204.3	204.3	204.1	203.7	203.3
107.5°	251.7	250.7	249.8	248.8	249.8	250.7	251.7	252.5	252.9	252.8	252.6
110°	285.3	284.6	284.0	283.4	284.0	284.6	285.3	285.9	286.2	286.2	286.2



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	317.9	317.4	317.0	316.6	317.0	317.4	317.9	318.4	318.9	319.3	319.8
115°	369.9	369.3	368.7	368.0	368.7	369.3	369.9	370.5	370.9	371.1	371.4
117.5°	419.1	418.4	417.8	417.2	417.8	418.4	419.1	419.7	420.3	420.7	421.2
120°	453.7	453.0	452.4	451.8	452.4	453.0	453.7	454.2	454.6	454.6	454.6
122.5°	487.0	486.6	486.2	485.7	486.2	486.6	487.0	487.5	487.9	488.5	488.9
125°	538.0	537.8	537.6	537.4	537.6	537.8	538.0	538.2	538.6	539.2	539.9
127.5°	586.5	585.8	585.2	584.5	585.2	585.8	586.5	587.1	587.8	588.5	589.3
130°	620.8	620.0	619.2	618.4	619.2	620.0	620.8	621.6	622.3	622.7	623.1
132.5°	652.8	652.0	651.4	650.8	651.4	652.0	652.8	653.4	654.2	655.1	655.9
135°	703.0	702.4	701.8	701.2	701.8	702.4	703.0	703.6	704.0	704.3	704.5
137.5°	749.2	748.5	747.7	746.8	747.7	748.5	749.2	750.1	750.6	750.8	750.9
140°	780.9	780.1	779.3	778.5	779.3	780.1	780.9	781.7	782.1	782.1	782.1
142.5°	809.6	808.8	808.0	807.2	808.0	808.8	809.6	810.5	810.8	810.6	810.5
145°	852.7	851.9	851.0	850.2	851.0	851.9	852.7	853.5	853.8	853.7	853.4
147.5°	891.0	890.3	889.5	888.7	889.5	890.3	891.0	891.8	892.0	891.5	891.1
150°	915.6	915.0	914.3	913.8	914.3	915.0	915.6	916.2	916.2	915.6	915.0
152.5°	939.6	938.9	938.1	937.3	938.1	938.9	939.6	940.4	940.4	939.6	938.9
155°	970.8	970.2	969.6	968.9	969.6	970.2	970.8	971.4	971.2	970.2	969.2
157.5°	999.1	998.1	997.2	996.2	997.2	998.1	999.1	1000.1	999.9	998.5	997.1
160°	1015.6	1014.8	1013.9	1013.1	1013.9	1014.8	1015.6	1016.4	1016.2	1014.9	1013.8
162.5°	1030.8	1029.8	1028.8	1027.9	1028.8	1029.8	1030.8	1031.7	1031.6	1030.2	1028.8
165°	1050.3	1049.2	1048.2	1047.2	1048.2	1049.2	1050.3	1051.2	1051.1	1049.6	1048.2
167.5°	1066.2	1065.1	1064.1	1063.0	1064.1	1065.1	1066.2	1067.2	1067.1	1065.6	1064.2
170°	1074.8	1073.6	1072.3	1071.1	1072.3	1073.6	1074.8	1076.0	1075.9	1074.4	1073.0
172.5°	1081.4	1080.1	1079.0	1077.7	1079.0	1080.1	1081.4	1082.6	1082.5	1081.1	1079.7
175°	1088.6	1087.3	1086.2	1084.9	1086.2	1087.3	1088.6	1089.8	1089.7	1088.3	1086.9
177.5°	1091.2	1090.2	1089.2	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	9.2	9.5	8.9	8.2	7.3	6.7	6.2	5.9	5.9	5.6	5.4
90°	31.8	32.2	27.7	23.2	18.7	14.2	10.8	8.3	5.9	3.4	1.0
92.5°	29.3	29.2	28.2	27.2	26.1	25.0	23.6	21.8	20.0	18.1	16.4
95°	58.9	58.9	58.5	58.1	57.7	57.3	56.0	53.9	52.0	49.9	47.8
97.5°	99.0	99.0	98.2	97.4	96.6	95.9	94.6	92.8	91.0	89.2	87.5
100°	127.0	127.0	126.4	125.7	125.2	124.5	123.4	121.8	120.2	118.5	116.8
102.5°	157.3	157.2	156.4	155.6	154.9	154.1	153.0	151.7	150.4	149.1	147.8
105°	202.9	202.4	202.0	201.6	201.2	200.8	200.3	199.7	199.1	198.4	197.8
107.5°	252.5	252.3	252.3	252.3	252.3	252.3	251.8	251.0	250.1	249.1	248.3
110°	286.2	286.2	286.2	286.2	286.2	286.2	285.6	284.3	283.1	281.9	280.7



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	320.3	320.8	320.9	321.1	321.2	321.5	320.9	319.6	318.5	317.2	316.0
115°	371.5	371.8	372.2	372.6	373.0	373.4	373.0	371.8	370.5	369.3	368.0
117.5°	421.7	422.2	423.3	424.5	425.6	426.7	426.5	424.8	423.3	421.6	419.9
120°	454.6	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6
122.5°	489.4	489.9	491.1	492.2	493.4	494.5	494.1	492.1	490.1	488.2	486.2
125°	540.4	541.1	541.7	542.3	542.9	543.5	542.9	541.1	539.2	537.4	535.5
127.5°	590.0	590.7	591.5	592.2	592.9	593.7	592.9	590.6	588.3	585.9	583.6
130°	623.4	623.9	624.3	624.7	625.1	625.5	624.4	621.7	619.1	616.4	613.8
132.5°	656.9	657.7	657.7	657.6	657.5	657.4	656.3	654.1	652.0	649.8	647.6
135°	704.6	704.9	704.5	704.0	703.6	703.2	701.9	699.7	697.4	695.1	692.9
137.5°	751.1	751.2	750.7	750.2	749.6	749.1	747.9	746.1	744.3	742.4	740.5
140°	782.1	782.1	781.2	780.1	779.1	778.1	776.7	774.8	772.9	771.1	769.3
142.5°	810.3	810.2	809.5	808.7	808.0	807.3	806.0	804.2	802.4	800.6	798.8
145°	853.2	853.0	851.8	850.6	849.3	848.1	846.8	845.3	843.9	842.5	841.1
147.5°	890.7	890.2	889.4	888.6	887.7	886.9	885.7	883.9	882.2	880.5	878.8
150°	914.3	913.8	912.9	912.1	911.3	910.5	909.4	908.2	907.0	905.8	904.5
152.5°	938.1	937.3	936.4	935.3	934.4	933.3	932.2	931.1	929.8	928.6	927.3
155°	968.1	967.1	966.5	965.9	965.3	964.6	964.1	963.5	962.8	962.2	961.6
157.5°	995.8	994.3	994.0	993.6	993.2	992.8	992.5	992.0	991.7	991.3	990.9
160°	1012.5	1011.3	1011.1	1010.9	1010.7	1010.4	1010.2	1009.7	1009.3	1008.9	1008.5
162.5°	1027.4	1026.0	1025.8	1025.6	1025.4	1025.2	1025.1	1024.9	1024.8	1024.8	1024.7
165°	1046.8	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.6	1045.8	1046.1	1046.2
167.5°	1062.8	1061.4	1061.4	1061.4	1061.4	1061.5	1061.8	1062.5	1063.0	1063.7	1064.3
170°	1071.6	1070.2	1070.4	1070.6	1070.8	1071.0	1071.4	1072.0	1072.6	1073.2	1073.9
172.5°	1078.2	1076.8	1077.0	1077.2	1077.4	1077.6	1078.0	1078.6	1079.3	1079.9	1080.5
175°	1085.4	1083.9	1084.4	1084.8	1085.2	1085.6	1086.2	1086.7	1087.3	1088.0	1088.6
177.5°	1089.2	1088.2	1088.5	1088.9	1089.2	1089.5	1090.0	1090.4	1090.9	1091.4	1091.9
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.6	8.0	8.6	9.7	10.0	10.9	11.7	12.4	13.1	12.8	12.4
90°	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8	31.4
92.5°	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3	29.4
95°	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9	58.9
97.5°	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0	99.0
100°	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0	127.0
102.5°	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3	157.5
105°	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9	203.3
107.5°	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5	252.6
110°	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2	286.2





TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3	319.8
115°	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5	371.4
117.5°	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7	421.2
120°	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6	454.6
122.5°	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4	488.9
125°	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4	539.9
127.5°	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0	589.3
130°	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4	623.1
132.5°	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9	655.9
135°	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6	704.5
137.5°	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1	750.9
140°	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1	782.1
142.5°	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3	810.5
145°	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2	853.4
147.5°	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7	891.1
150°	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3	915.0
152.5°	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1	938.9
155°	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1	969.2
157.5°	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8	997.1
160°	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5	1013.8
162.5°	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4	1028.8
165°	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8	1048.2
167.5°	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8	1064.2
170°	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6	1073.0
172.5°	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2	1079.7
175°	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4	1086.9
177.5°	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2	1090.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	12.6	12.5	12.3	12.3	12.6	12.4	12.4
90°	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	285.9	285.3	284.6	284.0	283.4



TEST NUMBER: P331322-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)