

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333534

Luminaire Tested: **S125RDIP-S610D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333534  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D810U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5307.9 lumens  
Efficiency: N/A  
Efficacy: 138.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	28				
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	25				
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	22				
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5977	5977	5977	5977
5°	6876	5984	5285	5984
10°	7887	5954	4663	5954
15°	8519	5893	4145	5893
20°	9394	5822	3827	5822
25°	10871	5728	3552	5728
30°	11830	5629	3371	5629
35°	9979	5513	3205	5513
40°	6969	5306	3062	5306
45°	5170	5027	2922	5027
50°	4122	4736	2801	4736
55°	3498	4376	2694	4376
60°	3023	4053	2523	4053
65°	2694	3704	2172	3704
70°	2368	3393	1979	3393
75°	2049	2939	1859	2939
80°	1555	2473	1555	2473
85°	1297	1941	1467	1941



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	1.7
10°-20°	260.1	4.9
20°-30°	412.3	7.8
30°-40°	497.2	9.4
40°-50°	444.0	8.4
50°-60°	340.5	6.4
60°-70°	221.3	4.2
70°-80°	107.6	2.0
80°-90°	27.8	0.5
90°-100°	281.1	5.3
100°-110°	604.3	11.4
110°-120°	567.1	10.7
120°-130°	459.6	8.7
130°-140°	368.8	6.9
140°-150°	278.3	5.2
150°-160°	195.9	3.7
160°-170°	115.5	2.2
170°-180°	37.6	0.7
0°-30°	761.1	14.3
0°-40°	1258.3	23.7
0°-60°	2042.9	38.5
0°-90°	2399.6	45.2
90°-120°	1452.5	27.4
90°-150°	2559.3	48.2
90°-180°	2908.0	54.8
0°-180°	5307.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1061	923	815	923	1061	106
15°	1274	881	620	881	1274	365
25°	1526	804	498	804	1526	700
35°	1266	699	406	699	1266	765
45°	566	550	320	550	566	452
55°	311	389	239	389	311	282
65°	176	242	142	242	176	175
75°	82	118	74	118	82	87
85°	18	26	20	26	18	21
90°	18	1	18	1	18	13
95°	184	26	184	26	184	260
105°	1036	88	1036	88	1036	1030
115°	1154	158	1154	158	1154	1128
125°	909	219	909	219	909	823
135°	755	256	755	256	755	585
145°	596	299	596	299	596	379
155°	500	341	500	341	500	233
165°	438	372	438	372	438	125
175°	393	387	393	387	393	38
180°	388	388	388	388	388	



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	973.4	972.8	974.0	970.6	971.0	965.8	965.8	961.8	956.7	952.7	950.9
5°	1060.6	1061.4	1059.8	1054.1	1050.3	1044.6	1038.2	1026.8	1017.3	1008.2	1001.0
7.5°	1150.4	1150.9	1145.9	1144.2	1134.6	1127.6	1113.3	1097.8	1084.0	1066.5	1053.2
10°	1202.7	1202.3	1197.0	1192.8	1184.4	1173.8	1159.7	1141.5	1124.4	1105.4	1087.2
12.5°	1233.1	1232.1	1230.4	1225.3	1217.6	1208.1	1196.2	1178.3	1157.2	1136.4	1115.2
15°	1274.1	1271.4	1266.5	1260.0	1249.0	1238.0	1224.7	1208.8	1188.6	1165.1	1145.3
17.5°	1324.8	1324.9	1317.3	1308.4	1293.4	1273.9	1253.4	1227.7	1200.3	1174.4	1153.4
20°	1366.8	1365.6	1358.0	1340.6	1323.5	1299.2	1275.6	1244.1	1210.7	1176.8	1150.6
22.5°	1426.9	1424.0	1416.1	1393.1	1366.6	1335.3	1299.3	1260.8	1220.4	1182.0	1147.6
25°	1525.6	1523.3	1507.7	1481.1	1443.9	1395.6	1348.5	1295.7	1237.6	1187.1	1145.3
27.5°	1593.0	1590.5	1579.0	1556.9	1522.5	1471.8	1408.0	1337.5	1264.9	1195.4	1135.1
30°	1586.3	1592.0	1590.5	1580.3	1554.4	1508.8	1450.0	1370.6	1284.3	1202.7	1130.9
32.5°	1490.9	1496.0	1509.4	1529.5	1531.0	1512.8	1468.8	1395.5	1306.2	1213.3	1127.5
35°	1265.7	1272.6	1298.4	1339.0	1392.2	1436.7	1445.8	1406.3	1326.1	1226.2	1122.5
37.5°	973.1	1010.5	1032.2	1075.0	1155.3	1237.1	1315.7	1344.7	1310.6	1220.9	1114.4
40°	826.6	835.7	874.5	922.7	990.3	1075.4	1187.5	1268.4	1271.0	1208.8	1101.6
42.5°	707.5	719.0	745.6	784.1	842.0	927.1	1042.8	1149.6	1199.0	1175.3	1084.9
45°	566.0	574.7	594.1	623.7	668.2	738.5	838.0	961.5	1059.5	1097.8	1040.1
47.5°	465.0	469.7	486.5	509.1	542.0	593.2	670.2	777.4	895.0	977.4	969.3
50°	410.3	415.6	428.5	445.6	473.3	516.6	578.2	667.4	788.6	889.3	909.4
52.5°	367.7	372.1	380.2	396.4	419.2	452.5	502.2	583.0	692.0	799.0	845.6
55°	310.7	313.8	320.2	329.3	347.6	371.5	414.4	470.3	558.4	666.3	734.7
57.5°	263.8	265.3	269.4	277.8	290.4	307.9	338.9	386.3	449.5	546.6	622.1
60°	234.0	235.5	240.8	246.5	256.4	272.4	296.7	329.7	390.5	470.7	547.0
62.5°	210.3	211.2	213.5	219.2	227.8	240.2	259.3	286.3	334.6	405.0	477.1
65°	176.3	176.6	177.4	182.0	187.3	196.4	208.9	227.9	264.4	317.6	381.4
67.5°	143.6	144.1	146.8	148.4	153.9	158.7	166.1	180.6	206.3	242.1	291.7
70°	125.4	125.0	127.6	129.5	131.4	137.1	142.1	153.8	169.8	197.2	238.6
72.5°	108.3	107.4	108.5	109.2	111.7	115.6	120.5	127.7	140.0	158.9	190.5
75°	82.1	82.4	82.4	83.2	85.1	86.6	88.1	91.9	98.8	111.3	128.4
77.5°	57.6	57.0	58.6	58.8	59.9	61.6	62.9	64.4	67.2	72.4	81.2
80°	41.8	41.8	42.2	43.3	42.9	43.7	45.6	47.1	50.5	53.6	56.6
82.5°	32.1	31.8	32.1	32.4	32.3	33.0	33.7	34.0	35.3	36.8	39.0
85°	17.5	17.5	17.9	17.9	18.2	18.2	18.6	18.6	18.6	19.0	19.4
87.5°	10.3	10.0	9.5	9.5	9.8	10.1	9.7	9.2	9.0	8.9	8.9
90°	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1	13.3	12.5	10.9
92.5°	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6	204.1	252.1	256.1
95°	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2	677.9	692.8	565.3
97.5°	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3	857.7	739.8	504.8
100°	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7	901.5	706.1	450.4
102.5°	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6	875.3	646.6	409.1
105°	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9	791.3	566.9	369.1
107.5°	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7	705.6	512.0	352.2
110°	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7	656.8	486.3	347.2



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4	620.5	471.3	347.2
115°	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0	580.9	455.1	349.5
117.5°	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4	557.3	447.1	354.7
120°	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8	544.2	443.3	359.7
122.5°	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0	532.9	440.2	364.0
125°	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4	517.6	436.3	371.4
127.5°	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4	503.5	434.4	379.7
130°	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7	494.2	433.2	384.7
132.5°	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1	486.7	433.2	390.3
135°	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8	477.7	433.2	398.0
137.5°	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6	469.8	434.1	405.0
140°	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2	466.0	434.7	408.1
142.5°	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1	462.9	435.4	410.0
145°	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4	458.2	434.7	412.1
147.5°	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4	453.3	432.7	412.8
150°	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8	449.6	430.8	412.8
152.5°	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5	445.2	428.3	412.2
155°	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2	437.9	423.8	410.5
157.5°	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8	431.0	419.1	408.5
160°	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5	425.4	416.0	406.6
162.5°	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6	420.3	412.2	404.7
165°	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1	412.8	406.6	401.9
167.5°	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0	405.5	401.1	397.5
170°	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0	401.1	398.0	395.6
172.5°	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4	396.7	394.2	393.1
175°	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3	390.9	390.2	390.2
177.5°	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1	388.4	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	950.9	948.8	944.8	941.2	936.6	932.7	929.9	926.6	922.3	917.2	912.9
5°	993.0	984.6	973.6	964.1	952.0	942.5	932.6	923.1	913.6	901.4	890.8
7.5°	1039.6	1022.4	1005.6	984.5	965.3	948.2	931.8	915.2	898.9	881.7	865.0
10°	1068.2	1047.3	1024.1	997.5	973.2	950.1	928.8	907.9	885.9	866.5	845.6
12.5°	1094.9	1068.0	1041.5	1007.9	978.7	950.4	923.3	897.3	873.7	848.6	826.1
15°	1119.1	1092.5	1062.9	1021.9	981.2	947.0	915.1	881.3	852.1	823.9	798.9
17.5°	1128.4	1100.6	1066.1	1026.7	982.3	939.3	898.2	861.1	826.7	793.9	765.7
20°	1124.8	1097.8	1062.5	1024.9	977.4	932.6	888.1	847.1	808.7	774.2	744.2
22.5°	1116.0	1088.1	1054.0	1014.3	969.2	921.6	874.2	830.4	790.2	754.4	721.7
25°	1102.8	1064.8	1029.8	991.1	948.2	901.1	852.1	803.8	760.9	724.4	688.7
27.5°	1089.0	1041.6	997.2	958.6	913.3	871.3	824.0	774.6	729.4	692.3	655.7
30°	1076.6	1023.4	974.4	930.7	887.8	847.9	803.0	754.8	708.5	670.1	632.9
32.5°	1061.1	1004.5	950.7	900.3	858.9	819.3	778.7	732.6	687.5	647.9	610.1
35°	1041.6	969.4	910.9	857.4	811.4	773.0	736.6	699.3	654.1	613.1	576.3
37.5°	1016.1	934.2	866.5	808.1	759.7	721.1	692.4	658.3	617.1	577.8	543.6
40°	1000.6	908.7	834.6	776.8	725.9	685.3	658.3	629.4	591.8	555.0	520.8
42.5°	979.9	885.3	802.4	742.2	691.0	651.9	624.6	599.4	567.8	533.1	496.5
45°	939.4	839.9	752.9	688.3	636.7	598.3	572.8	550.4	526.5	494.6	462.7
47.5°	886.7	792.6	701.5	631.0	580.4	544.8	520.1	502.4	485.3	458.2	427.2
50°	844.5	753.7	664.8	596.4	542.5	508.6	485.5	471.4	455.8	431.2	405.3
52.5°	794.6	713.6	626.5	556.6	505.7	474.0	451.7	437.7	424.8	404.7	380.1
55°	716.1	645.0	565.2	501.8	455.1	423.2	401.9	388.6	381.0	363.9	344.5
57.5°	625.4	574.5	504.2	443.0	401.7	370.1	354.6	343.3	334.7	322.6	308.9
60°	562.2	526.5	463.4	405.3	367.3	337.3	323.3	313.8	305.8	295.5	284.9
62.5°	498.1	472.1	417.3	367.3	332.4	307.2	294.1	285.5	276.3	269.4	259.1
65°	412.2	389.0	351.0	311.9	279.6	259.5	250.0	242.4	236.7	229.1	221.8
67.5°	320.6	311.2	285.0	258.0	234.8	216.9	208.7	203.4	196.5	192.0	187.0
70°	264.4	259.8	241.2	223.4	201.7	189.6	182.0	179.7	171.3	166.8	163.3
72.5°	214.6	212.4	201.7	189.3	174.1	163.4	156.4	153.8	148.5	144.9	142.7
75°	147.0	147.8	145.9	137.9	132.2	125.4	119.3	117.8	114.0	110.9	109.0
77.5°	93.0	96.9	97.0	96.6	94.4	90.2	87.7	86.5	82.8	81.7	81.2
80°	63.8	68.0	71.8	71.4	70.7	69.5	67.6	66.5	64.6	63.4	62.7
82.5°	42.5	46.4	49.6	51.7	51.5	50.4	49.1	48.5	48.2	47.3	47.2
85°	20.1	20.9	22.0	24.7	26.6	27.0	26.6	26.2	25.1	25.5	25.8
87.5°	9.0	8.7	8.9	8.5	7.9	9.1	9.7	9.9	9.4	9.1	8.8
90°	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5	11.6	18.1	27.8
95°	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8	26.6	32.8	41.4
97.5°	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8	43.8	48.2	56.8
100°	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7	56.3	59.4	68.0
102.5°	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9	68.8	71.3	80.5
105°	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4	88.4	92.3	100.1
107.5°	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4	109.9	113.7	120.1
110°	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8	124.3	127.4	134.5





TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1	138.7	141.2	148.2
115°	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9	159.5	161.9	168.9
117.5°	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7	179.1	181.6	188.6
120°	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2	191.6	194.7	201.7
122.5°	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4	204.1	206.6	213.6
125°	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9	220.5	224.4	231.4
127.5°	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9	234.3	239.3	248.2
130°	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0	242.4	248.6	258.8
132.5°	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3	249.3	256.8	268.2
135°	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5	259.6	269.0	281.5
137.5°	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3	271.6	280.4	292.9
140°	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8	279.1	288.5	301.0
142.5°	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5	287.3	296.0	308.5
145°	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7	300.2	308.1	319.0
147.5°	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4	313.4	320.1	330.3
150°	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6	322.1	327.6	337.8
152.5°	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3	330.3	335.1	344.0
155°	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9	340.9	345.6	353.4
157.5°	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2	351.1	354.8	361.5
160°	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1	357.3	360.5	365.9
162.5°	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7	363.0	366.1	370.9
165°	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2	370.6	373.0	376.9
167.5°	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8	377.0	378.4	380.6
170°	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6	380.8	381.6	383.1
172.5°	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1	382.7	383.4	385.0
175°	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0	385.5	386.3	387.0
177.5°	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4	387.2	387.2	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	909.9	905.6	902.6	896.5	892.2	890.4	887.1	886.2	889.5	887.1	886.8
5°	882.8	871.8	863.1	854.3	844.8	838.8	829.6	828.1	825.8	822.4	821.7
7.5°	850.4	836.0	824.8	810.3	797.8	787.7	776.3	770.9	767.9	763.5	757.6
10°	828.5	811.4	796.2	781.8	766.2	753.7	742.3	733.5	727.8	722.5	720.2
12.5°	806.9	789.5	770.1	752.6	735.2	721.1	708.5	702.8	696.5	690.3	685.0
15°	773.4	750.2	729.0	708.8	694.0	678.8	666.7	658.3	648.8	646.2	635.9
17.5°	737.9	715.1	690.2	669.0	651.9	635.1	621.8	612.3	605.1	595.3	590.6
20°	715.7	688.7	664.4	645.0	626.0	606.3	592.6	584.6	577.8	569.8	566.0
22.5°	692.0	665.6	640.7	618.0	598.7	579.2	569.5	561.2	553.5	546.1	541.1
25°	657.2	630.6	604.4	580.8	560.7	546.6	535.2	525.7	521.6	514.3	509.0
27.5°	622.8	594.5	567.3	543.8	528.0	514.1	504.8	497.3	489.7	483.4	478.8
30°	600.6	571.7	542.1	523.5	506.7	493.5	483.2	476.0	470.3	464.6	461.2
32.5°	578.4	548.6	522.3	502.2	486.4	474.9	464.4	457.4	451.4	445.1	441.1
35°	542.8	512.4	491.2	471.4	455.8	445.2	438.0	428.1	423.2	418.6	414.4
37.5°	509.8	481.5	458.5	441.2	427.7	417.1	407.8	402.4	396.4	392.3	388.8
40°	485.5	459.6	438.8	420.5	410.6	398.9	390.1	383.3	378.7	373.4	369.6
42.5°	463.6	439.6	419.3	402.9	390.6	380.6	372.2	365.4	359.6	355.8	352.6
45°	432.7	408.7	389.0	373.8	362.4	352.9	344.2	340.7	333.1	328.6	327.1
47.5°	400.7	379.3	360.2	346.2	334.5	325.5	317.3	310.4	306.2	301.7	299.3
50°	379.1	358.6	340.7	327.1	315.7	305.8	298.2	293.6	287.9	283.8	280.7
52.5°	357.5	338.5	320.7	307.6	297.7	287.9	279.4	274.8	269.4	266.7	264.6
55°	326.7	306.6	291.4	278.4	268.2	259.1	251.1	246.5	243.1	240.5	239.7
57.5°	291.7	275.8	261.7	250.0	239.4	230.8	223.8	219.5	216.5	216.1	213.8
60°	268.9	254.5	241.6	229.1	219.9	212.0	205.9	201.0	197.9	197.5	196.8
62.5°	246.2	232.3	220.3	209.3	201.1	193.4	187.7	182.1	180.3	178.4	176.7
65°	212.3	199.8	189.9	181.2	172.5	166.0	160.3	156.9	152.7	150.4	146.3
67.5°	179.1	169.4	159.9	152.6	145.7	139.6	134.9	129.8	127.0	125.1	122.1
70°	157.3	149.7	140.2	132.2	126.9	121.9	118.1	112.4	110.5	109.0	107.5
72.5°	136.6	129.9	121.9	115.5	110.2	105.5	101.1	98.5	96.6	95.0	94.1
75°	107.5	101.0	94.2	89.6	85.9	82.1	79.8	77.9	77.1	76.7	75.2
77.5°	78.9	75.5	70.0	66.4	63.9	62.4	60.3	59.3	59.3	57.6	57.1
80°	60.4	58.5	53.9	52.4	50.5	49.0	47.9	46.0	44.1	43.3	42.2
82.5°	44.9	43.0	41.2	38.7	37.2	36.2	35.1	34.4	34.6	33.6	33.0
85°	23.9	22.0	21.3	20.9	20.1	20.9	20.5	20.1	19.8	19.4	19.8
87.5°	8.8	9.2	9.0	9.9	9.2	9.8	10.0	9.8	10.0	10.1	10.1
90°	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1	14.9	15.6	17.2
92.5°	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6	100.6	75.7	64.1
95°	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2	443.3	347.2	281.5
97.5°	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3	753.9	660.2	568.9
100°	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7	923.4	842.9	761.6
102.5°	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6	1027.3	988.6	933.6
105°	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9	1086.1	1120.5	1111.9
107.5°	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7	1033.7	1122.0	1162.8
110°	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7	974.2	1084.5	1150.9



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4	915.4	1026.9	1105.3
115°	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0	831.2	938.3	1023.5
117.5°	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4	772.8	865.1	943.3
120°	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8	739.7	825.7	894.5
122.5°	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0	715.9	792.5	857.0
125°	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4	684.2	752.2	808.5
127.5°	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4	653.8	717.3	770.0
130°	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7	632.6	693.5	744.4
132.5°	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1	612.5	667.9	716.8
135°	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8	581.7	631.8	676.3
137.5°	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6	554.2	595.8	633.6
140°	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2	537.9	573.9	606.7
142.5°	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1	524.2	555.1	583.6
145°	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4	506.7	530.9	552.0
147.5°	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4	492.1	510.7	526.7
150°	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8	484.0	498.8	512.9
152.5°	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5	475.9	489.5	500.4
155°	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2	463.7	474.6	483.2
157.5°	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8	452.1	460.5	467.3
160°	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5	443.3	451.2	456.6
162.5°	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6	435.8	442.4	447.2
165°	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1	424.6	429.3	433.2
167.5°	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0	413.6	417.2	420.0
170°	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0	407.4	409.7	411.3
172.5°	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4	401.7	403.5	404.4
175°	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3	393.3	394.9	394.9
177.5°	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1	389.7	389.7	389.7
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	886.5	883.1	882.2	883.4	882.2	883.1	886.5	886.8	887.1	889.5	886.2
5°	817.9	814.1	816.0	815.2	816.0	814.1	817.9	821.7	822.4	825.8	828.1
7.5°	757.5	752.8	747.8	749.4	747.8	752.8	757.5	757.6	763.5	767.9	770.9
10°	715.3	711.5	709.2	711.1	709.2	711.5	715.3	720.2	722.5	727.8	733.5
12.5°	679.7	677.5	675.5	674.7	675.5	677.5	679.7	685.0	690.3	696.5	702.8
15°	631.3	626.8	624.9	620.0	624.9	626.8	631.3	635.9	646.2	648.8	658.3
17.5°	586.7	585.2	580.3	578.2	580.3	585.2	586.7	590.6	595.3	605.1	612.3
20°	560.3	558.8	553.9	556.9	553.9	558.8	560.3	566.0	569.8	577.8	584.6
22.5°	538.4	535.1	533.5	532.6	533.5	535.1	538.4	541.1	546.1	553.5	561.2
25°	507.5	502.6	500.7	498.4	500.7	502.6	507.5	509.0	514.3	521.6	525.7
27.5°	476.7	474.0	471.5	470.9	471.5	474.0	476.7	478.8	483.4	489.7	497.3
30°	456.6	453.9	452.0	452.0	452.0	453.9	456.6	461.2	464.6	470.3	476.0
32.5°	438.7	436.6	434.7	434.4	434.7	436.6	438.7	441.1	445.1	451.4	457.4
35°	412.5	409.5	408.7	406.5	408.7	409.5	412.5	414.4	418.6	423.2	428.1
37.5°	385.4	382.9	382.8	382.6	382.8	382.9	385.4	388.8	392.3	396.4	402.4
40°	368.1	366.2	365.8	363.2	365.8	366.2	368.1	369.6	373.4	378.7	383.3
42.5°	349.6	348.6	347.3	346.1	347.3	348.6	349.6	352.6	355.8	359.6	365.4
45°	324.4	321.8	321.8	319.9	321.8	321.8	324.4	327.1	328.6	333.1	340.7
47.5°	298.4	296.4	296.6	294.6	296.6	296.4	298.4	299.3	301.7	306.2	310.4
50°	281.1	280.0	279.6	278.8	279.6	280.0	281.1	280.7	283.8	287.9	293.6
52.5°	263.8	263.3	264.7	263.0	264.7	263.3	263.8	264.6	266.7	269.4	274.8
55°	240.5	239.3	241.6	239.3	241.6	239.3	240.5	239.7	240.5	243.1	246.5
57.5°	213.6	212.6	214.6	213.5	214.6	212.6	213.6	213.8	216.1	216.5	219.5
60°	196.0	193.7	194.9	195.3	194.9	193.7	196.0	196.8	197.5	197.9	201.0
62.5°	175.0	173.7	174.5	172.8	174.5	173.7	175.0	176.7	178.4	180.3	182.1
65°	145.5	144.4	142.8	142.1	142.8	144.4	145.5	146.3	150.4	152.7	156.9
67.5°	122.2	119.5	119.4	120.0	119.4	119.5	122.2	122.1	125.1	127.0	129.8
70°	105.2	105.2	104.8	104.8	104.8	105.2	105.2	107.5	109.0	110.5	112.4
72.5°	93.4	93.1	92.4	92.1	92.4	93.1	93.4	94.1	95.0	96.6	98.5
75°	75.2	75.6	74.8	74.5	74.8	75.6	75.2	75.2	76.7	77.1	77.9
77.5°	55.5	53.9	54.8	53.9	54.8	53.9	55.5	57.1	57.6	59.3	59.3
80°	42.2	41.8	42.9	41.8	42.9	41.8	42.2	42.2	43.3	44.1	46.0
82.5°	33.4	33.0	33.5	32.7	33.5	33.0	33.4	33.0	33.6	34.6	34.4
85°	20.1	19.8	19.4	19.8	19.4	19.8	20.1	19.8	19.4	19.8	20.1
87.5°	10.4	10.1	10.3	10.3	10.3	10.1	10.4	10.1	10.1	10.0	9.8
90°	17.2	17.2	18.0	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1
92.5°	54.1	52.2	51.1	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6
95°	226.0	202.5	196.3	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2
97.5°	520.6	476.8	454.1	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3
100°	707.6	651.3	622.4	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7
102.5°	875.9	835.8	804.4	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6
105°	1086.8	1061.0	1045.4	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9
107.5°	1175.5	1175.3	1170.2	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7
110°	1186.1	1201.0	1206.5	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1156.7	1182.2	1195.8	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4
115°	1084.5	1122.0	1143.9	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0
117.5°	1004.3	1043.0	1064.8	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4
120°	952.3	989.9	1011.0	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8
122.5°	908.6	943.0	964.1	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0
125°	852.3	884.3	901.5	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4
127.5°	809.7	838.0	854.3	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4
130°	783.5	809.3	824.9	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7
132.5°	755.9	781.7	796.1	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1
135°	710.7	736.5	750.6	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8
137.5°	664.5	687.9	700.9	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6
140°	635.7	656.0	667.7	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2
142.5°	608.2	625.4	636.5	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1
145°	570.8	584.1	592.7	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4
147.5°	541.5	552.2	557.2	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4
150°	524.7	534.0	537.2	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8
152.5°	510.3	517.8	520.9	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5
155°	491.0	496.5	498.8	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2
157.5°	473.4	477.9	480.1	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8
160°	462.1	466.0	467.6	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5
162.5°	451.5	454.7	455.1	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6
165°	436.3	437.9	437.9	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1
167.5°	421.6	423.0	422.4	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0
170°	412.8	413.6	413.6	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0
172.5°	404.7	406.1	404.9	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4
175°	394.9	395.6	394.1	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3
177.5°	389.1	389.7	387.8	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	887.1	890.4	892.2	896.5	902.6	905.6	909.9	912.9	917.2	922.3	926.6
5°	829.6	838.8	844.8	854.3	863.1	871.8	882.8	890.8	901.4	913.6	923.1
7.5°	776.3	787.7	797.8	810.3	824.8	836.0	850.4	865.0	881.7	898.9	915.2
10°	742.3	753.7	766.2	781.8	796.2	811.4	828.5	845.6	866.5	885.9	907.9
12.5°	708.5	721.1	735.2	752.6	770.1	789.5	806.9	826.1	848.6	873.7	897.3
15°	666.7	678.8	694.0	708.8	729.0	750.2	773.4	798.9	823.9	852.1	881.3
17.5°	621.8	635.1	651.9	669.0	690.2	715.1	737.9	765.7	793.9	826.7	861.1
20°	592.6	606.3	626.0	645.0	664.4	688.7	715.7	744.2	774.2	808.7	847.1
22.5°	569.5	579.2	598.7	618.0	640.7	665.6	692.0	721.7	754.4	790.2	830.4
25°	535.2	546.6	560.7	580.8	604.4	630.6	657.2	688.7	724.4	760.9	803.8
27.5°	504.8	514.1	528.0	543.8	567.3	594.5	622.8	655.7	692.3	729.4	774.6
30°	483.2	493.5	506.7	523.5	542.1	571.7	600.6	632.9	670.1	708.5	754.8
32.5°	464.4	474.9	486.4	502.2	522.3	548.6	578.4	610.1	647.9	687.5	732.6
35°	438.0	445.2	455.8	471.4	491.2	512.4	542.8	576.3	613.1	654.1	699.3
37.5°	407.8	417.1	427.7	441.2	458.5	481.5	509.8	543.6	577.8	617.1	658.3
40°	390.1	398.9	410.6	420.5	438.8	459.6	485.5	520.8	555.0	591.8	629.4
42.5°	372.2	380.6	390.6	402.9	419.3	439.6	463.6	496.5	533.1	567.8	599.4
45°	344.2	352.9	362.4	373.8	389.0	408.7	432.7	462.7	494.6	526.5	550.4
47.5°	317.3	325.5	334.5	346.2	360.2	379.3	400.7	427.2	458.2	485.3	502.4
50°	298.2	305.8	315.7	327.1	340.7	358.6	379.1	405.3	431.2	455.8	471.4
52.5°	279.4	287.9	297.7	307.6	320.7	338.5	357.5	380.1	404.7	424.8	437.7
55°	251.1	259.1	268.2	278.4	291.4	306.6	326.7	344.5	363.9	381.0	388.6
57.5°	223.8	230.8	239.4	250.0	261.7	275.8	291.7	308.9	322.6	334.7	343.3
60°	205.9	212.0	219.9	229.1	241.6	254.5	268.9	284.9	295.5	305.8	313.8
62.5°	187.7	193.4	201.1	209.3	220.3	232.3	246.2	259.1	269.4	276.3	285.5
65°	160.3	166.0	172.5	181.2	189.9	199.8	212.3	221.8	229.1	236.7	242.4
67.5°	134.9	139.6	145.7	152.6	159.9	169.4	179.1	187.0	192.0	196.5	203.4
70°	118.1	121.9	126.9	132.2	140.2	149.7	157.3	163.3	166.8	171.3	179.7
72.5°	101.1	105.5	110.2	115.5	121.9	129.9	136.6	142.7	144.9	148.5	153.8
75°	79.8	82.1	85.9	89.6	94.2	101.0	107.5	109.0	110.9	114.0	117.8
77.5°	60.3	62.4	63.9	66.4	70.0	75.5	78.9	81.2	81.7	82.8	86.5
80°	47.9	49.0	50.5	52.4	53.9	58.5	60.4	62.7	63.4	64.6	66.5
82.5°	35.1	36.2	37.2	38.7	41.2	43.0	44.9	47.2	47.3	48.2	48.5
85°	20.5	20.9	20.1	20.9	21.3	22.0	23.9	25.8	25.5	25.1	26.2
87.5°	10.0	9.8	9.2	9.9	9.0	9.2	8.8	8.8	9.1	9.4	9.9
90°	13.3	12.5	10.9	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8
92.5°	204.1	252.1	256.1	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5
95°	677.9	692.8	565.3	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8
97.5°	857.7	739.8	504.8	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8
100°	901.5	706.1	450.4	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7
102.5°	875.3	646.6	409.1	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9
105°	791.3	566.9	369.1	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4
107.5°	705.6	512.0	352.2	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4
110°	656.8	486.3	347.2	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	620.5	471.3	347.2	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1
115°	580.9	455.1	349.5	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9
117.5°	557.3	447.1	354.7	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7
120°	544.2	443.3	359.7	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2
122.5°	532.9	440.2	364.0	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4
125°	517.6	436.3	371.4	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9
127.5°	503.5	434.4	379.7	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9
130°	494.2	433.2	384.7	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0
132.5°	486.7	433.2	390.3	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3
135°	477.7	433.2	398.0	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5
137.5°	469.8	434.1	405.0	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3
140°	466.0	434.7	408.1	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8
142.5°	462.9	435.4	410.0	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5
145°	458.2	434.7	412.1	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7
147.5°	453.3	432.7	412.8	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4
150°	449.6	430.8	412.8	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6
152.5°	445.2	428.3	412.2	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3
155°	437.9	423.8	410.5	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9
157.5°	431.0	419.1	408.5	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2
160°	425.4	416.0	406.6	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1
162.5°	420.3	412.2	404.7	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7
165°	412.8	406.6	401.9	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2
167.5°	405.5	401.1	397.5	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8
170°	401.1	398.0	395.6	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6
172.5°	396.7	394.2	393.1	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1
175°	390.9	390.2	390.2	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0
177.5°	388.4	387.8	387.8	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	929.9	932.7	936.6	941.2	944.8	948.8	950.9	950.9	952.7	956.7	961.8
5°	932.6	942.5	952.0	964.1	973.6	984.6	993.0	1001.0	1008.2	1017.3	1026.8
7.5°	931.8	948.2	965.3	984.5	1005.6	1022.4	1039.6	1053.2	1066.5	1084.0	1097.8
10°	928.8	950.1	973.2	997.5	1024.1	1047.3	1068.2	1087.2	1105.4	1124.4	1141.5
12.5°	923.3	950.4	978.7	1007.9	1041.5	1068.0	1094.9	1115.2	1136.4	1157.2	1178.3
15°	915.1	947.0	981.2	1021.9	1062.9	1092.5	1119.1	1145.3	1165.1	1188.6	1208.8
17.5°	898.2	939.3	982.3	1026.7	1066.1	1100.6	1128.4	1153.4	1174.4	1200.3	1227.7
20°	888.1	932.6	977.4	1024.9	1062.5	1097.8	1124.8	1150.6	1176.8	1210.7	1244.1
22.5°	874.2	921.6	969.2	1014.3	1054.0	1088.1	1116.0	1147.6	1182.0	1220.4	1260.8
25°	852.1	901.1	948.2	991.1	1029.8	1064.8	1102.8	1145.3	1187.1	1237.6	1295.7
27.5°	824.0	871.3	913.3	958.6	997.2	1041.6	1089.0	1135.1	1195.4	1264.9	1337.5
30°	803.0	847.9	887.8	930.7	974.4	1023.4	1076.6	1130.9	1202.7	1284.3	1370.6
32.5°	778.7	819.3	858.9	900.3	950.7	1004.5	1061.1	1127.5	1213.3	1306.2	1395.5
35°	736.6	773.0	811.4	857.4	910.9	969.4	1041.6	1122.5	1226.2	1326.1	1406.3
37.5°	692.4	721.1	759.7	808.1	866.5	934.2	1016.1	1114.4	1220.9	1310.6	1344.7
40°	658.3	685.3	725.9	776.8	834.6	908.7	1000.6	1101.6	1208.8	1271.0	1268.4
42.5°	624.6	651.9	691.0	742.2	802.4	885.3	979.9	1084.9	1175.3	1199.0	1149.6
45°	572.8	598.3	636.7	688.3	752.9	839.9	939.4	1040.1	1097.8	1059.5	961.5
47.5°	520.1	544.8	580.4	631.0	701.5	792.6	886.7	969.3	977.4	895.0	777.4
50°	485.5	508.6	542.5	596.4	664.8	753.7	844.5	909.4	889.3	788.6	667.4
52.5°	451.7	474.0	505.7	556.6	626.5	713.6	794.6	845.6	799.0	692.0	583.0
55°	401.9	423.2	455.1	501.8	565.2	645.0	716.1	734.7	666.3	558.4	470.3
57.5°	354.6	370.1	401.7	443.0	504.2	574.5	625.4	622.1	546.6	449.5	386.3
60°	323.3	337.3	367.3	405.3	463.4	526.5	562.2	547.0	470.7	390.5	329.7
62.5°	294.1	307.2	332.4	367.3	417.3	472.1	498.1	477.1	405.0	334.6	286.3
65°	250.0	259.5	279.6	311.9	351.0	389.0	412.2	381.4	317.6	264.4	227.9
67.5°	208.7	216.9	234.8	258.0	285.0	311.2	320.6	291.7	242.1	206.3	180.6
70°	182.0	189.6	201.7	223.4	241.2	259.8	264.4	238.6	197.2	169.8	153.8
72.5°	156.4	163.4	174.1	189.3	201.7	212.4	214.6	190.5	158.9	140.0	127.7
75°	119.3	125.4	132.2	137.9	145.9	147.8	147.0	128.4	111.3	98.8	91.9
77.5°	87.7	90.2	94.4	96.6	97.0	96.9	93.0	81.2	72.4	67.2	64.4
80°	67.6	69.5	70.7	71.4	71.8	68.0	63.8	56.6	53.6	50.5	47.1
82.5°	49.1	50.4	51.5	51.7	49.6	46.4	42.5	39.0	36.8	35.3	34.0
85°	26.6	27.0	26.6	24.7	22.0	20.9	20.1	19.4	19.0	18.6	18.6
87.5°	9.7	9.1	7.9	8.5	8.9	8.7	9.0	8.9	8.9	9.0	9.2
90°	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1
92.5°	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6
95°	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2
97.5°	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3
100°	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7
102.5°	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6
105°	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9
107.5°	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7
110°	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7





TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4
115°	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0
117.5°	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4
120°	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8
122.5°	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0
125°	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4
127.5°	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4
130°	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7
132.5°	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1
135°	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8
137.5°	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6
140°	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2
142.5°	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1
145°	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4
147.5°	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4
150°	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8
152.5°	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5
155°	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2
157.5°	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8
160°	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5
162.5°	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6
165°	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1
167.5°	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0
170°	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0
172.5°	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4
175°	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3
177.5°	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	965.8	965.8	971.0	970.6	974.0	972.8	973.4
5°	1038.2	1044.6	1050.3	1054.1	1059.8	1061.4	1060.6
7.5°	1113.3	1127.6	1134.6	1144.2	1145.9	1150.9	1150.4
10°	1159.7	1173.8	1184.4	1192.8	1197.0	1202.3	1202.7
12.5°	1196.2	1208.1	1217.6	1225.3	1230.4	1232.1	1233.1
15°	1224.7	1238.0	1249.0	1260.0	1266.5	1271.4	1274.1
17.5°	1253.4	1273.9	1293.4	1308.4	1317.3	1324.9	1324.8
20°	1275.6	1299.2	1323.5	1340.6	1358.0	1365.6	1366.8
22.5°	1299.3	1335.3	1366.6	1393.1	1416.1	1424.0	1426.9
25°	1348.5	1395.6	1443.9	1481.1	1507.7	1523.3	1525.6
27.5°	1408.0	1471.8	1522.5	1556.9	1579.0	1590.5	1593.0
30°	1450.0	1508.8	1554.4	1580.3	1590.5	1592.0	1586.3
32.5°	1468.8	1512.8	1531.0	1529.5	1509.4	1496.0	1490.9
35°	1445.8	1436.7	1392.2	1339.0	1298.4	1272.6	1265.7
37.5°	1315.7	1237.1	1155.3	1075.0	1032.2	1010.5	973.1
40°	1187.5	1075.4	990.3	922.7	874.5	835.7	826.6
42.5°	1042.8	927.1	842.0	784.1	745.6	719.0	707.5
45°	838.0	738.5	668.2	623.7	594.1	574.7	566.0
47.5°	670.2	593.2	542.0	509.1	486.5	469.7	465.0
50°	578.2	516.6	473.3	445.6	428.5	415.6	410.3
52.5°	502.2	452.5	419.2	396.4	380.2	372.1	367.7
55°	414.4	371.5	347.6	329.3	320.2	313.8	310.7
57.5°	338.9	307.9	290.4	277.8	269.4	265.3	263.8
60°	296.7	272.4	256.4	246.5	240.8	235.5	234.0
62.5°	259.3	240.2	227.8	219.2	213.5	211.2	210.3
65°	208.9	196.4	187.3	182.0	177.4	176.6	176.3
67.5°	166.1	158.7	153.9	148.4	146.8	144.1	143.6
70°	142.1	137.1	131.4	129.5	127.6	125.0	125.4
72.5°	120.5	115.6	111.7	109.2	108.5	107.4	108.3
75°	88.1	86.6	85.1	83.2	82.4	82.4	82.1
77.5°	62.9	61.6	59.9	58.8	58.6	57.0	57.6
80°	45.6	43.7	42.9	43.3	42.2	41.8	41.8
82.5°	33.7	33.0	32.3	32.4	32.1	31.8	32.1
85°	18.6	18.2	18.2	17.9	17.9	17.5	17.5
87.5°	9.7	10.1	9.8	9.5	9.5	10.0	10.3
90°	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333534

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)