

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331329-927

Luminaire Tested: **SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331329-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4899.6 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331329-927
CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331329-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9935	9935	9935
5°	9972	9828	9887
10°	9914	9729	9778
15°	9790	9603	9593
20°	9617	9414	9402
25°	9444	9180	9180
30°	9221	8968	8889
35°	9014	8712	8584
40°	8753	8456	8292
45°	8499	8200	7996
50°	8219	7935	7654
55°	7927	7626	7344
60°	7601	7259	6991
65°	7255	6896	6575
70°	6812	6453	6146
75°	6201	5939	5795
80°	5504	5337	5058
85°	4483	4279	3835



TEST NUMBER: P331329-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	1.2
10°-20°	162.8	3.3
20°-30°	239.3	4.9
30°-40°	278.0	5.7
40°-50°	277.7	5.7
50°-60°	242.1	4.9
60°-70°	179.0	3.7
70°-80°	101.4	2.1
80°-90°	31.6	0.6
90°-100°	191.3	3.9
100°-110°	649.3	13.3
110°-120°	689.8	14.1
120°-130°	567.8	11.6
130°-140°	456.0	9.3
140°-150°	344.6	7.0
150°-160°	242.2	4.9
160°-170°	142.6	2.9
170°-180°	46.4	0.9
0°-30°	459.9	9.4
0°-40°	737.9	15.1
0°-60°	1257.7	25.7
0°-90°	1569.7	32.0
90°-120°	1530.4	31.2
90°-150°	2898.8	59.2
90°-180°	3330.0	68.0
0°-180°	4899.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	615	613	606	611	610	58
15°	586	582	574	577	574	165
25°	530	525	515	516	515	244
35°	457	451	442	438	436	285
45°	372	368	359	353	350	287
55°	282	278	271	264	261	252
65°	190	186	180	175	172	188
75°	99	98	95	92	93	106
85°	24	24	23	21	21	28
90°	1	12	31	30	30	3
95°	32	79	361	136	105	34
105°	112	169	682	1219	1037	119
115°	198	250	570	1177	1365	196
125°	276	327	548	954	1107	245
135°	324	386	542	802	918	250
145°	370	425	539	670	732	232
155°	421	454	524	592	616	193
165°	458	472	502	532	540	129
175°	478	478	482	488	487	45
180°	479	479	479	479	479	



TEST NUMBER: P331329-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	618.1	617.6	617.1	616.6	616.0	615.2	614.0	612.9	611.7	610.5	611.6
5°	615.3	614.7	614.3	613.7	613.2	612.2	610.8	609.3	607.8	606.4	607.4
7.5°	609.8	609.0	608.2	607.4	606.6	605.5	604.0	602.5	601.0	599.5	600.6
10°	604.7	603.7	602.8	601.9	600.9	599.7	598.1	596.6	595.0	593.4	594.5
12.5°	597.5	596.8	595.9	595.1	594.3	593.1	591.5	589.9	588.4	586.8	587.5
15°	585.7	584.9	584.2	583.4	582.6	581.3	579.6	577.9	576.2	574.5	575.0
17.5°	570.5	569.8	569.0	568.2	567.4	566.2	564.4	562.7	560.9	559.2	559.8
20°	559.7	558.9	558.1	557.3	556.5	555.2	553.3	551.5	549.7	547.9	548.3
22.5°	548.8	547.7	546.6	545.5	544.4	543.0	541.2	539.5	537.7	536.0	536.1
25°	530.1	529.0	528.0	527.0	525.9	524.3	522.0	519.8	517.5	515.3	515.6
27.5°	508.8	507.9	506.9	506.0	505.0	503.7	501.9	500.1	498.4	496.6	496.2
30°	494.6	493.5	492.5	491.5	490.4	488.9	486.9	485.0	483.0	481.0	480.6
32.5°	479.4	478.6	477.8	476.9	476.1	474.6	472.5	470.5	468.4	466.4	465.6
35°	457.3	456.0	454.7	453.4	452.1	450.4	448.3	446.2	444.0	442.0	441.2
37.5°	432.4	431.2	430.1	428.9	427.7	426.1	424.0	421.9	419.8	417.7	416.7
40°	415.3	414.2	413.2	412.2	411.1	409.6	407.4	405.4	403.2	401.2	400.0
42.5°	398.8	397.7	396.6	395.6	394.6	393.0	390.9	388.8	386.7	384.5	383.3
45°	372.2	371.2	370.3	369.4	368.4	367.0	365.0	363.1	361.1	359.1	357.7
47.5°	345.6	344.8	343.9	343.0	342.1	340.7	338.7	336.6	334.5	332.5	331.0
50°	327.2	326.5	325.8	325.2	324.6	323.3	321.5	319.6	317.7	315.9	314.1
52.5°	309.2	308.3	307.4	306.6	305.7	304.4	302.7	301.0	299.2	297.5	296.0
55°	281.6	280.8	280.0	279.2	278.5	277.3	275.7	274.1	272.5	270.9	269.4
57.5°	253.9	253.3	252.6	252.1	251.4	250.3	248.5	246.8	245.0	243.3	241.7
60°	235.4	235.0	234.4	233.9	233.4	232.2	230.4	228.5	226.6	224.8	223.4
62.5°	217.5	216.7	215.8	214.9	214.1	213.0	211.6	210.2	208.7	207.3	206.0
65°	189.9	189.1	188.3	187.5	186.8	185.7	184.4	183.1	181.7	180.5	179.3
67.5°	161.8	161.2	160.6	159.9	159.3	158.4	157.2	156.1	154.9	153.7	152.8
70°	144.3	143.9	143.3	142.8	142.3	141.4	140.2	139.0	137.8	136.7	135.8
72.5°	126.4	125.9	125.3	124.8	124.3	123.7	122.9	122.1	121.4	120.6	119.6
75°	99.4	99.1	98.9	98.6	98.3	97.9	97.2	96.6	95.9	95.2	94.4
77.5°	75.3	74.8	74.4	73.9	73.4	73.1	72.9	72.6	72.3	72.1	71.7
80°	59.2	59.0	58.9	58.8	58.6	58.5	58.1	57.9	57.7	57.4	57.0
82.5°	44.0	44.0	44.0	44.0	43.9	43.8	43.6	43.5	43.3	43.2	42.7
85°	24.2	24.2	24.0	23.8	23.8	23.6	23.4	23.4	23.2	23.1	22.7
87.5°	8.7	9.0	9.6	9.7	9.9	10.2	10.9	12.0	12.9	12.9	12.4
90°	1.0	3.6	7.4	9.2	11.0	13.8	18.4	24.9	30.3	31.3	30.3
92.5°	11.2	16.2	22.8	26.9	33.1	41.7	62.6	91.8	118.0	119.6	101.1
95°	32.2	35.9	45.1	53.4	68.1	90.2	132.5	212.5	319.3	360.8	315.7
97.5°	52.4	57.4	67.2	79.7	96.6	121.7	174.8	286.4	463.8	615.8	646.0
100°	70.8	73.6	81.9	96.6	115.0	140.8	189.6	301.8	500.6	727.0	859.5
102.5°	87.8	89.8	98.1	112.8	132.0	157.7	202.8	302.6	486.6	730.7	939.1
105°	112.3	116.0	122.4	136.2	156.5	182.2	225.5	307.4	459.2	681.9	926.7
107.5°	138.8	141.7	148.0	160.7	180.8	206.7	248.7	320.0	445.6	629.6	845.9
110°	156.5	160.1	165.6	177.6	196.9	223.6	264.1	330.3	442.7	604.6	795.1



TEST NUMBER: P331329-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.6	176.3	182.6	193.8	212.4	239.8	278.8	341.4	443.4	588.4	759.8
115°	197.9	202.5	207.9	219.0	237.4	262.3	301.8	358.0	447.3	570.5	716.0
117.5°	224.0	227.7	233.2	243.0	260.6	286.4	323.0	375.7	453.8	561.9	688.3
120°	240.2	243.8	249.4	257.7	276.1	301.8	337.7	387.5	458.3	556.7	673.6
122.5°	255.6	258.6	264.1	273.1	291.5	318.1	351.7	397.8	463.4	553.8	661.1
125°	276.1	278.8	284.4	295.4	313.8	339.6	372.7	414.2	471.2	548.5	643.3
127.5°	292.2	296.0	303.7	315.8	333.5	360.0	392.2	429.4	479.1	545.3	626.7
130°	301.8	305.5	314.7	327.6	346.0	371.8	404.0	438.9	485.0	543.8	615.7
132.5°	310.7	315.1	325.0	338.7	357.8	383.6	414.3	448.5	490.8	543.1	606.8
135°	323.9	327.6	338.7	352.4	373.6	399.4	428.8	461.1	497.9	542.0	594.5
137.5°	336.4	340.9	351.9	366.6	387.6	411.5	440.6	470.6	504.1	541.9	585.8
140°	346.0	349.7	360.8	375.5	395.7	419.6	447.3	475.8	507.1	541.1	580.7
142.5°	355.6	358.5	368.8	383.6	403.1	425.6	452.4	480.2	509.3	541.1	575.5
145°	369.9	373.6	382.9	396.6	415.0	435.3	460.1	485.9	511.7	539.2	568.7
147.5°	385.4	388.2	397.0	409.7	425.0	443.0	466.4	489.0	512.4	536.0	561.7
150°	395.7	398.5	405.8	417.8	431.6	448.1	469.4	490.5	511.7	533.8	555.8
152.5°	406.0	407.3	414.6	425.2	438.2	453.3	472.3	491.2	510.2	530.0	550.6
155°	420.6	421.4	427.0	437.1	447.3	461.1	476.7	492.3	507.9	523.6	541.1
157.5°	432.7	433.6	438.1	446.9	455.0	466.6	479.8	492.3	503.7	517.0	532.1
160°	440.8	441.7	445.4	452.7	460.1	470.2	481.3	492.3	501.5	512.6	525.5
162.5°	448.9	448.4	452.0	457.9	464.5	472.5	482.0	491.6	499.3	508.9	519.6
165°	458.3	457.4	459.2	464.7	469.4	474.8	483.2	489.6	495.1	501.5	509.8
167.5°	466.0	464.9	466.6	470.1	473.4	476.9	482.9	488.3	490.8	495.1	500.3
170°	471.2	469.4	470.2	473.0	474.8	477.6	482.2	486.8	488.6	491.4	495.1
172.5°	474.1	473.0	472.5	475.2	476.3	478.3	481.5	484.6	485.7	487.0	490.0
175°	477.6	476.7	475.8	477.6	477.6	478.6	480.4	482.2	481.3	482.2	483.2
177.5°	479.3	477.8	477.1	478.6	478.6	478.6	479.3	480.8	479.3	478.6	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331329-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	612.7	613.7	614.7	615.2	615.0	614.7	614.6	614.3
5°	608.6	609.6	610.6	611.0	610.8	610.5	610.2	610.0
7.5°	601.7	602.7	603.8	604.1	603.9	603.6	603.2	603.0
10°	595.5	596.6	597.6	597.9	597.5	597.1	596.8	596.4
12.5°	588.3	589.0	589.7	589.9	589.6	589.4	589.1	588.7
15°	575.5	576.1	576.6	576.5	575.8	575.2	574.6	573.9
17.5°	560.4	561.0	561.7	561.6	560.9	560.4	559.8	559.1
20°	548.7	549.1	549.5	549.4	548.8	548.3	547.8	547.2
22.5°	536.1	536.2	536.3	536.2	535.9	535.6	535.3	535.0
25°	515.9	516.1	516.3	516.3	516.1	515.9	515.6	515.3
27.5°	495.8	495.4	495.0	494.6	493.9	493.3	492.7	492.0
30°	480.2	479.8	479.4	479.0	478.4	477.9	477.4	476.8
32.5°	464.9	464.2	463.5	462.9	462.3	461.8	461.3	460.7
35°	440.4	439.6	438.8	438.1	437.4	436.7	436.1	435.5
37.5°	415.7	414.8	413.8	413.0	412.3	411.7	411.1	410.5
40°	398.8	397.6	396.4	395.5	395.0	394.5	394.0	393.4
42.5°	382.0	380.7	379.4	378.4	377.6	376.9	376.2	375.4
45°	356.2	354.8	353.3	352.4	351.8	351.3	350.8	350.2
47.5°	329.5	327.9	326.4	325.3	324.5	323.8	323.0	322.2
50°	312.3	310.4	308.6	307.3	306.7	306.0	305.3	304.7
52.5°	294.5	292.9	291.4	290.2	289.3	288.4	287.6	286.7
55°	267.8	266.3	264.7	263.6	262.8	262.2	261.6	260.9
57.5°	240.2	238.6	237.1	236.1	235.5	235.0	234.6	234.0
60°	221.9	220.5	219.0	218.1	217.7	217.3	216.9	216.5
62.5°	204.6	203.3	201.9	201.1	200.5	200.0	199.6	199.0
65°	178.1	176.9	175.7	174.8	174.1	173.5	172.9	172.1
67.5°	151.9	150.9	150.0	149.3	148.8	148.2	147.7	147.2
70°	134.8	133.9	133.0	132.3	131.7	131.2	130.7	130.2
72.5°	118.7	117.8	116.9	116.2	115.8	115.3	114.9	114.5
75°	93.6	92.9	92.1	91.8	92.1	92.4	92.6	92.9
77.5°	71.3	70.9	70.5	70.1	69.7	69.4	69.0	68.6
80°	56.6	56.2	55.8	55.5	55.2	55.0	54.7	54.4
82.5°	42.2	41.7	41.2	40.9	40.9	40.8	40.7	40.7
85°	22.3	21.9	21.5	21.2	21.1	21.0	20.8	20.7
87.5°	11.9	11.2	11.2	11.2	11.1	11.0	10.9	10.8
90°	29.5	27.6	29.5	30.3	30.3	30.3	30.3	30.3
92.5°	80.2	68.8	61.1	55.4	54.7	51.7	52.4	51.0
95°	241.1	185.0	146.3	126.0	114.1	106.8	104.0	104.9
97.5°	562.6	460.3	360.8	294.3	250.3	227.7	214.2	206.5
100°	840.2	726.1	600.0	488.6	412.3	372.7	346.0	329.5
102.5°	1022.1	996.2	904.0	786.1	703.1	635.6	602.2	579.8
105°	1118.1	1222.1	1234.1	1203.7	1146.6	1089.6	1050.0	1037.1
107.5°	1048.9	1205.5	1301.2	1345.8	1353.0	1349.8	1341.9	1324.8
110°	989.3	1154.0	1271.8	1347.3	1386.8	1404.3	1412.6	1411.7



TEST NUMBER: P331329-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	934.8	1092.9	1218.8	1305.3	1360.3	1389.6	1405.3	1410.2
115°	867.8	1009.6	1130.0	1224.9	1290.2	1332.5	1356.5	1364.8
117.5°	817.4	941.8	1051.1	1140.0	1206.7	1251.3	1276.6	1283.6
120°	792.3	906.4	1004.0	1087.7	1152.1	1195.4	1222.1	1231.3
122.5°	772.5	877.0	969.4	1045.0	1102.8	1145.3	1169.1	1176.8
125°	743.5	838.4	919.3	988.3	1041.7	1076.7	1099.7	1107.1
127.5°	715.0	800.8	877.2	940.9	987.5	1020.2	1040.1	1046.0
130°	696.6	775.8	848.5	909.2	954.3	985.6	1004.0	1011.4
132.5°	679.0	752.3	819.0	876.1	920.4	951.7	968.7	975.3
135°	654.3	715.0	775.8	827.3	866.9	897.2	913.8	917.5
137.5°	634.6	685.4	733.6	778.6	814.6	840.7	855.3	860.8
140°	622.1	666.3	708.6	749.1	778.6	802.5	816.3	821.8
142.5°	611.8	649.4	685.8	719.6	747.6	769.4	781.6	782.8
145°	597.2	627.6	656.2	682.9	704.9	720.6	729.8	732.5
147.5°	586.1	610.0	632.2	651.7	669.9	682.5	688.7	690.4
150°	577.9	598.2	617.5	634.1	647.8	658.9	664.4	665.4
152.5°	569.8	588.6	605.0	619.3	630.2	639.8	643.8	644.0
155°	558.6	573.3	587.1	597.2	607.4	613.8	617.5	615.7
157.5°	545.5	557.9	569.4	577.3	584.6	589.9	591.5	591.5
160°	537.4	547.6	557.7	564.1	570.5	575.1	576.1	576.1
162.5°	529.3	538.0	546.6	551.6	558.0	561.2	562.1	561.3
165°	517.2	523.6	530.0	533.8	537.4	541.1	541.1	540.2
167.5°	505.6	510.6	515.0	518.3	519.9	522.0	521.8	520.7
170°	499.7	502.5	506.1	507.9	508.9	511.7	510.7	508.9
172.5°	493.1	495.1	498.0	499.2	500.1	501.4	500.4	499.3
175°	485.9	486.8	487.7	488.6	488.6	489.6	488.6	486.8
177.5°	480.8	480.8	481.5	481.5	481.5	481.5	480.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)