

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333536

Luminaire Tested: **S125RDIP-S610D810U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333536
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D810U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5182.6 lumens
Efficiency: N/A
Efficacy: 135.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	47	46	45	39				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	39	38	33				
3	81	72	64	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28				
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	14				
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.8
10°-20°	264.3	5.1
20°-30°	383.3	7.4
30°-40°	436.9	8.4
40°-50°	425.9	8.2
50°-60°	358.5	6.9
60°-70°	251.3	4.8
70°-80°	129.2	2.5
80°-90°	34.8	0.7
90°-100°	67.3	1.3
100°-110°	198.7	3.8
110°-120°	336.6	6.5
120°-130°	443.0	8.5
130°-140°	496.4	9.6
140°-150°	486.5	9.4
150°-160°	408.6	7.9
160°-170°	271.6	5.2
170°-180°	95.1	1.8
0°-30°	742.3	14.3
0°-40°	1179.2	22.8
0°-60°	1963.5	37.9
0°-90°	2378.7	45.9
90°-120°	602.7	11.6
90°-150°	2028.6	39.1
90°-180°	2804.0	54.1
0°-180°	5182.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	1	7	12	16	19	5
95°	51	53	60	66	67	54
105°	178	182	187	191	194	190
115°	337	340	342	341	340	333
125°	492	496	497	496	495	440
135°	640	644	645	645	642	493
145°	775	778	780	780	778	484
155°	887	887	888	890	887	408
165°	964	963	963	966	962	272
175°	1002	1000	999	1003	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.5	12.8	12.1	11.5	11.2	11.3	11.4	11.5	11.6	11.8
90°	0.8	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4
92.5°	18.9	19.9	20.9	21.8	22.8	24.0	25.5	27.0	28.5	30.0	31.2
95°	50.8	51.2	51.5	51.9	52.2	53.3	55.0	56.7	58.5	60.2	61.4
97.5°	84.5	84.6	84.7	84.9	85.0	86.3	88.7	91.1	93.5	95.9	97.0
100°	109.5	109.5	109.5	109.5	109.5	110.6	112.9	115.1	117.4	119.6	121.2
102.5°	136.4	137.1	137.8	138.5	139.2	140.1	141.2	142.4	143.5	144.7	146.4
105°	178.3	179.2	180.0	180.9	181.8	182.7	183.8	184.8	185.8	186.9	187.9
107.5°	224.6	225.4	226.3	227.2	228.1	228.9	229.7	230.5	231.3	232.1	232.6
110°	256.5	257.4	258.2	259.1	260.0	260.7	261.2	261.7	262.2	262.7	263.3



TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	289.0	289.5	289.9	290.4	290.8	291.4	292.0	292.7	293.4	294.0	294.3
115°	337.0	337.7	338.4	339.1	339.8	340.3	340.7	341.0	341.4	341.7	341.5
117.5°	385.2	385.5	385.8	386.1	386.4	386.8	387.1	387.4	387.7	388.0	388.1
120°	415.2	416.1	417.0	417.8	418.7	419.2	419.4	419.6	419.7	419.9	419.9
122.5°	447.7	448.1	448.4	448.7	449.0	449.4	449.8	450.3	450.7	451.2	451.0
125°	491.8	492.9	493.9	495.0	496.0	496.6	496.8	497.0	497.1	497.3	497.0
127.5°	538.8	539.4	539.9	540.5	541.1	541.5	541.7	541.9	542.2	542.4	542.2
130°	566.9	567.8	568.7	569.5	570.4	571.0	571.3	571.7	572.0	572.4	572.2
132.5°	595.1	596.5	597.9	599.3	600.8	601.4	601.4	601.3	601.2	601.2	601.0
135°	639.6	640.7	641.7	642.8	643.8	644.4	644.6	644.8	644.9	645.1	645.1
137.5°	681.6	682.6	683.6	684.6	685.6	686.3	686.7	687.0	687.4	687.8	688.0
140°	708.5	709.3	710.2	711.1	711.9	712.6	713.1	713.7	714.2	714.7	715.1
142.5°	735.4	736.1	736.8	737.5	738.3	739.0	739.6	740.3	740.9	741.6	741.8
145°	774.9	775.6	776.3	777.0	777.7	778.3	778.8	779.3	779.9	780.4	780.4
147.5°	811.5	811.9	812.3	812.7	813.0	813.4	813.9	814.3	814.7	815.1	815.5
150°	835.9	835.7	835.6	835.4	835.2	835.5	836.2	836.9	837.6	838.3	838.3
152.5°	855.9	856.2	856.4	856.7	856.9	857.2	857.4	857.7	858.0	858.3	858.7
155°	886.7	886.7	886.7	886.7	886.7	886.8	887.0	887.2	887.3	887.5	888.2
157.5°	914.3	913.9	913.5	913.1	912.7	912.6	912.8	913.0	913.1	913.3	914.0
160°	930.5	930.0	929.5	929.0	928.4	928.3	928.4	928.6	928.8	929.0	929.7
162.5°	944.9	944.5	944.1	943.8	943.4	943.2	943.2	943.3	943.3	943.4	944.2
165°	964.2	963.8	963.5	963.1	962.8	962.7	962.8	963.0	963.2	963.4	964.1
167.5°	980.4	979.7	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	978.3
170°	989.2	988.5	987.8	987.1	986.4	986.0	986.0	986.0	986.0	986.0	987.1
172.5°	995.4	994.7	994.0	993.3	992.6	992.3	992.3	992.3	992.3	992.3	993.3
175°	1002.5	1001.8	1001.1	1000.4	999.7	999.3	999.3	999.3	999.3	999.3	1000.4
177.5°	1006.1	1005.5	1005.0	1004.4	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	12.0	12.1	12.3	12.4	12.4	12.3	12.3	12.3
90°	14.2	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	32.3	33.5	34.6	35.4	35.8	36.1	36.5	36.9
95°	62.6	63.9	65.1	65.9	66.2	66.6	66.9	67.2
97.5°	98.2	99.3	100.5	101.1	101.3	101.5	101.8	102.0
100°	122.8	124.3	125.9	126.9	127.2	127.5	127.9	128.2
102.5°	148.1	149.8	151.5	152.6	153.1	153.5	154.0	154.5
105°	189.0	190.0	191.1	191.8	192.4	192.9	193.4	193.9
107.5°	233.1	233.6	234.2	234.4	234.4	234.3	234.3	234.3
110°	263.8	264.3	264.8	265.0	264.8	264.6	264.5	264.3



TEST NUMBER: P333536

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.5	294.7	295.0	295.0	294.6	294.3	294.0	293.7
115°	341.4	341.2	341.0	340.8	340.7	340.5	340.3	340.2
117.5°	388.3	388.4	388.6	388.3	387.6	386.9	386.2	385.5
120°	419.9	419.9	419.9	419.6	418.9	418.2	417.5	416.8
122.5°	450.9	450.8	450.6	450.3	449.7	449.2	448.6	448.1
125°	496.6	496.3	495.9	495.7	495.5	495.3	495.2	495.0
127.5°	542.0	541.8	541.7	541.4	541.1	540.7	540.4	540.0
130°	572.0	571.9	571.7	571.4	571.1	570.7	570.4	570.0
132.5°	600.8	600.6	600.5	600.1	599.7	599.2	598.7	598.2
135°	645.1	645.1	645.1	644.8	644.1	643.4	642.7	642.0
137.5°	688.2	688.4	688.6	688.3	687.4	686.6	685.7	684.8
140°	715.4	715.7	716.1	715.8	715.0	714.1	713.2	712.4
142.5°	742.0	742.2	742.4	742.1	741.2	740.4	739.5	738.6
145°	780.4	780.4	780.4	780.1	779.6	779.1	778.6	778.0
147.5°	815.9	816.4	816.8	816.4	815.2	814.0	812.9	811.7
150°	838.3	838.3	838.3	838.1	837.7	837.4	837.0	836.7
152.5°	859.1	859.5	859.9	859.8	859.2	858.6	858.0	857.3
155°	888.9	889.6	890.3	890.2	889.3	888.5	887.6	886.7
157.5°	914.7	915.4	916.1	915.9	914.7	913.6	912.4	911.3
160°	930.4	931.0	931.7	931.7	930.8	929.9	929.0	928.2
162.5°	945.0	945.9	946.7	946.6	945.6	944.6	943.6	942.6
165°	964.8	965.5	966.1	966.0	964.9	963.9	962.8	961.8
167.5°	979.4	980.4	981.5	981.4	980.4	979.3	978.2	977.1
170°	988.1	989.2	990.2	990.1	988.9	987.7	986.5	985.3
172.5°	994.4	995.4	996.5	996.5	995.4	994.3	993.2	992.1
175°	1001.4	1002.5	1003.5	1003.4	1002.2	1001.0	999.8	998.6
177.5°	1004.6	1005.4	1006.3	1006.2	1005.2	1004.3	1003.3	1002.3
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8

(END OF REPORT)