

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331295-927

Luminaire Tested: **SA2XXDIP-C485D530U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331295-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3197.3 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46				46
2	91	83	77	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39				39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34				34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29				29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	32	29	26				26
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26	23				23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21				21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19				19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17				17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15				15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	2.3
10°-20°	213.1	6.7
20°-30°	309.3	9.7
30°-40°	326.4	10.2
40°-50°	289.0	9.0
50°-60°	230.6	7.2
60°-70°	156.8	4.9
70°-80°	80.4	2.5
80°-90°	21.5	0.7
90°-100°	33.9	1.1
100°-110°	105.4	3.3
110°-120°	180.1	5.6
120°-130°	236.8	7.4
130°-140°	265.8	8.3
140°-150°	260.6	8.2
150°-160°	218.6	6.8
160°-170°	145.0	4.5
170°-180°	50.7	1.6
0°-30°	595.8	18.6
0°-40°	922.2	28.8
0°-60°	1441.8	45.1
0°-90°	1700.5	53.2
90°-120°	319.4	10.0
90°-150°	1082.6	33.9
90°-180°	1497.0	46.8
0°-180°	3197.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	15	0	15	0	15	7
95°	28	24	28	24	28	31
105°	100	97	100	97	100	105
115°	181	181	181	181	181	178
125°	264	263	264	263	264	235
135°	344	340	344	340	344	265
145°	417	413	417	413	417	261
155°	476	472	476	472	476	219
165°	514	514	514	514	514	145
175°	533	534	533	534	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	9.2	9.2	9.4	9.2	9.1	9.4	9.4	9.3	9.5	9.8	9.6
90°	15.4	15.3	15.1	15.1	15.0	15.0	15.2	15.4	15.6	15.8	13.6
92.5°	14.7	14.7	14.6	14.6	14.6	14.5	14.5	14.4	14.4	14.3	13.9
95°	28.0	28.2	28.4	28.6	28.8	28.9	28.9	28.9	28.9	28.9	28.7
97.5°	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.2
100°	61.9	62.0	62.1	62.2	62.3	62.3	62.3	62.3	62.3	62.3	62.0
102.5°	77.1	77.2	77.2	77.4	77.5	77.5	77.4	77.3	77.2	77.2	76.8
105°	100.3	100.3	100.3	100.3	100.3	100.2	100.0	99.8	99.6	99.4	99.2
107.5°	122.2	122.6	123.1	123.5	124.0	124.2	124.1	124.1	124.0	123.9	123.9
110°	139.1	139.4	139.7	140.1	140.4	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.4	155.6	155.8	156.1	156.3	156.5	156.8	157.0	157.2	157.5	157.6
115°	180.7	181.0	181.3	181.6	181.9	182.1	182.2	182.3	182.4	182.5	182.7
117.5°	204.8	205.1	205.4	205.7	206.0	206.3	206.5	206.8	207.0	207.2	207.8
120°	221.8	222.1	222.4	222.7	223.0	223.2	223.2	223.2	223.2	223.2	223.9
122.5°	238.4	238.7	238.8	239.1	239.3	239.6	239.8	240.0	240.3	240.5	241.1
125°	263.8	263.9	264.0	264.1	264.2	264.4	264.7	265.0	265.3	265.6	265.9
127.5°	286.9	287.2	287.6	287.9	288.2	288.6	288.9	289.3	289.6	290.0	290.4
130°	303.6	304.0	304.4	304.8	305.1	305.5	305.7	305.9	306.1	306.3	306.5
132.5°	319.5	319.8	320.1	320.4	320.8	321.2	321.5	322.0	322.5	322.9	322.9
135°	344.2	344.5	344.8	345.2	345.4	345.6	345.7	345.9	345.9	346.0	345.9
137.5°	366.6	367.0	367.4	367.8	368.2	368.4	368.5	368.6	368.7	368.8	368.5
140°	382.1	382.5	382.9	383.3	383.8	384.0	384.0	384.0	384.0	384.0	383.5
142.5°	396.2	396.6	397.0	397.4	397.8	398.0	397.9	397.8	397.8	397.7	397.4
145°	417.4	417.8	418.2	418.6	419.0	419.1	419.1	419.0	418.8	418.7	418.2
147.5°	436.3	436.7	437.0	437.4	437.8	437.9	437.7	437.4	437.2	437.0	436.6
150°	448.6	448.9	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6	448.1
152.5°	460.2	460.5	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2	459.6
155°	475.7	475.9	476.3	476.6	476.9	476.8	476.3	475.8	475.3	474.8	474.4
157.5°	489.0	489.6	490.0	490.5	491.0	490.9	490.2	489.5	488.9	488.1	488.0
160°	497.3	497.7	498.2	498.6	499.0	498.8	498.3	497.6	497.1	496.5	496.4
162.5°	504.6	505.1	505.6	506.0	506.5	506.4	505.7	505.0	504.4	503.7	503.6
165°	514.0	514.6	515.1	515.6	516.1	515.9	515.3	514.6	513.9	513.2	513.2
167.5°	521.8	522.4	522.9	523.4	523.9	523.9	523.2	522.4	521.7	521.0	521.0
170°	525.9	526.4	527.0	527.6	528.2	528.1	527.5	526.8	526.1	525.4	525.5
172.5°	529.1	529.7	530.3	530.9	531.5	531.4	530.8	530.0	529.3	528.6	528.7
175°	532.6	533.2	533.8	534.4	535.0	535.0	534.2	533.5	532.8	532.1	532.3
177.5°	534.2	534.7	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2	534.4
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	9.3	9.0	8.5	8.6	7.7	7.4	6.3	5.3	5.3	5.3	5.1
90°	11.4	9.2	7.0	5.3	4.0	2.9	1.7	0.5	1.7	2.9	4.0
92.5°	13.3	12.8	12.3	11.6	10.7	9.8	9.0	8.1	9.0	9.8	10.7
95°	28.5	28.3	28.1	27.5	26.5	25.5	24.5	23.5	24.5	25.5	26.5
97.5°	47.8	47.5	47.1	46.4	45.6	44.7	43.8	42.9	43.8	44.7	45.6
100°	61.7	61.5	61.2	60.6	59.8	58.9	58.1	57.4	58.1	58.9	59.8
102.5°	76.4	76.0	75.7	75.1	74.5	73.8	73.2	72.6	73.2	73.8	74.5
105°	98.9	98.8	98.5	98.3	98.0	97.8	97.4	97.1	97.4	97.8	98.0
107.5°	123.9	123.9	123.9	123.7	123.2	122.8	122.3	121.9	122.3	122.8	123.2
110°	140.5	140.5	140.5	140.2	139.6	138.9	138.4	137.8	138.4	138.9	139.6



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	157.6	157.7	157.8	157.6	156.9	156.3	155.7	155.1	155.7	156.3	156.9
115°	182.9	183.1	183.3	183.1	182.5	181.9	181.3	180.7	181.3	181.9	182.5
117.5°	208.3	209.0	209.5	209.4	208.6	207.8	207.0	206.2	207.0	207.8	208.6
120°	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.9	224.7	225.5
122.5°	241.6	242.2	242.7	242.6	241.6	240.7	239.6	238.7	239.6	240.7	241.6
125°	266.3	266.5	266.8	266.5	265.6	264.7	263.8	262.9	263.8	264.7	265.6
127.5°	290.7	291.1	291.4	291.0	289.9	288.8	287.6	286.5	287.6	288.8	289.9
130°	306.7	306.9	307.0	306.5	305.2	303.9	302.6	301.3	302.6	303.9	305.2
132.5°	322.8	322.8	322.7	322.2	321.2	320.0	319.0	317.9	319.0	320.0	321.2
135°	345.6	345.4	345.2	344.6	343.5	342.4	341.3	340.2	341.3	342.4	343.5
137.5°	368.3	368.0	367.7	367.2	366.3	365.4	364.5	363.5	364.5	365.4	366.3
140°	382.9	382.5	382.0	381.3	380.3	379.5	378.6	377.6	378.6	379.5	380.3
142.5°	397.0	396.7	396.3	395.7	394.8	394.0	393.0	392.1	393.0	394.0	394.8
145°	417.6	416.9	416.4	415.7	415.0	414.3	413.6	412.9	413.6	414.3	415.0
147.5°	436.2	435.8	435.4	434.7	434.0	433.1	432.2	431.4	432.2	433.1	434.0
150°	447.7	447.3	446.9	446.5	445.8	445.3	444.7	444.1	444.7	445.3	445.8
152.5°	459.1	458.7	458.2	457.6	457.1	456.5	455.9	455.3	455.9	456.5	457.1
155°	474.2	473.9	473.6	473.2	472.9	472.7	472.4	472.1	472.4	472.7	472.9
157.5°	487.8	487.6	487.4	487.3	487.0	486.8	486.6	486.4	486.6	486.8	487.0
160°	496.2	496.1	496.1	495.9	495.7	495.5	495.3	495.1	495.3	495.5	495.7
162.5°	503.5	503.4	503.3	503.2	503.2	503.1	503.1	503.0	503.1	503.1	503.2
165°	513.2	513.2	513.2	513.3	513.3	513.4	513.5	513.7	513.5	513.4	513.3
167.5°	521.1	521.1	521.1	521.3	521.6	521.9	522.2	522.4	522.2	521.9	521.6
170°	525.5	525.7	525.8	526.0	526.2	526.6	526.9	527.2	526.9	526.6	526.2
172.5°	528.9	528.9	529.0	529.3	529.5	529.8	530.1	530.4	530.1	529.8	529.5
175°	532.6	532.7	533.0	533.2	533.5	533.8	534.1	534.4	534.1	533.8	533.5
177.5°	534.6	534.7	534.9	535.0	535.3	535.5	535.8	536.1	535.8	535.5	535.3
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	5.1	5.1	5.4	5.9	6.0	6.3	5.9	5.9	5.9	5.4	5.4
90°	5.3	7.0	9.2	11.4	13.6	15.8	15.6	15.4	15.2	15.0	15.0
92.5°	11.6	12.3	12.8	13.3	13.9	14.3	14.4	14.4	14.5	14.5	14.6
95°	27.5	28.1	28.3	28.5	28.7	28.9	28.9	28.9	28.9	28.9	28.8
97.5°	46.4	47.1	47.5	47.8	48.2	48.6	48.6	48.6	48.6	48.6	48.6
100°	60.6	61.2	61.5	61.7	62.0	62.3	62.3	62.3	62.3	62.3	62.3
102.5°	75.1	75.7	76.0	76.4	76.8	77.2	77.2	77.3	77.4	77.5	77.5
105°	98.3	98.5	98.8	98.9	99.2	99.4	99.6	99.8	100.0	100.2	100.3
107.5°	123.7	123.9	123.9	123.9	123.9	123.9	124.0	124.1	124.1	124.2	124.0
110°	140.2	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.4



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	157.6	157.8	157.7	157.6	157.6	157.5	157.2	157.0	156.8	156.5	156.3
115°	183.1	183.3	183.1	182.9	182.7	182.5	182.4	182.3	182.2	182.1	181.9
117.5°	209.4	209.5	209.0	208.3	207.8	207.2	207.0	206.8	206.5	206.3	206.0
120°	226.4	226.4	225.5	224.7	223.9	223.2	223.2	223.2	223.2	223.2	223.0
122.5°	242.6	242.7	242.2	241.6	241.1	240.5	240.3	240.0	239.8	239.6	239.3
125°	266.5	266.8	266.5	266.3	265.9	265.6	265.3	265.0	264.7	264.4	264.2
127.5°	291.0	291.4	291.1	290.7	290.4	290.0	289.6	289.3	288.9	288.6	288.2
130°	306.5	307.0	306.9	306.7	306.5	306.3	306.1	305.9	305.7	305.5	305.1
132.5°	322.2	322.7	322.8	322.8	322.9	322.9	322.5	322.0	321.5	321.2	320.8
135°	344.6	345.2	345.4	345.6	345.9	346.0	345.9	345.9	345.7	345.6	345.4
137.5°	367.2	367.7	368.0	368.3	368.5	368.8	368.7	368.6	368.5	368.4	368.2
140°	381.3	382.0	382.5	382.9	383.5	384.0	384.0	384.0	384.0	384.0	383.8
142.5°	395.7	396.3	396.7	397.0	397.4	397.7	397.8	397.8	397.9	398.0	397.8
145°	415.7	416.4	416.9	417.6	418.2	418.7	418.8	419.0	419.1	419.1	419.0
147.5°	434.7	435.4	435.8	436.2	436.6	437.0	437.2	437.4	437.7	437.9	437.8
150°	446.5	446.9	447.3	447.7	448.1	448.6	448.9	449.2	449.5	449.8	449.8
152.5°	457.6	458.2	458.7	459.1	459.6	460.2	460.5	460.9	461.3	461.7	461.7
155°	473.2	473.6	473.9	474.2	474.4	474.8	475.3	475.8	476.3	476.8	476.9
157.5°	487.3	487.4	487.6	487.8	488.0	488.1	488.9	489.5	490.2	490.9	491.0
160°	495.9	496.1	496.1	496.2	496.4	496.5	497.1	497.6	498.3	498.8	499.0
162.5°	503.2	503.3	503.4	503.5	503.6	503.7	504.4	505.0	505.7	506.4	506.5
165°	513.3	513.2	513.2	513.2	513.2	513.2	513.9	514.6	515.3	515.9	516.1
167.5°	521.3	521.1	521.1	521.1	521.0	521.0	521.7	522.4	523.2	523.9	523.9
170°	526.0	525.8	525.7	525.5	525.5	525.4	526.1	526.8	527.5	528.1	528.2
172.5°	529.3	529.0	528.9	528.9	528.7	528.6	529.3	530.0	530.8	531.4	531.5
175°	533.2	533.0	532.7	532.6	532.3	532.1	532.8	533.5	534.2	535.0	535.0
177.5°	535.0	534.9	534.7	534.6	534.4	534.2	534.7	535.2	535.7	536.1	536.1
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	5.4	5.1	5.1	5.0	5.1	5.1	5.4	5.4	5.4	5.9	5.9
90°	15.1	15.1	15.3	15.4	15.3	15.1	15.1	15.0	15.0	15.2	15.4
92.5°	14.6	14.6	14.7	14.7	14.7	14.6	14.6	14.6	14.5	14.5	14.4
95°	28.6	28.4	28.2	28.0	28.2	28.4	28.6	28.8	28.9	28.9	28.9
97.5°	48.6	48.6	48.6	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6
100°	62.2	62.1	62.0	61.9	62.0	62.1	62.2	62.3	62.3	62.3	62.3
102.5°	77.4	77.2	77.2	77.1	77.2	77.2	77.4	77.5	77.5	77.4	77.3
105°	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.2	100.0	99.8
107.5°	123.5	123.1	122.6	122.2	122.6	123.1	123.5	124.0	124.2	124.1	124.1
110°	140.1	139.7	139.4	139.1	139.4	139.7	140.1	140.4	140.5	140.5	140.5



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	156.1	155.8	155.6	155.4	155.6	155.8	156.1	156.3	156.5	156.8	157.0
115°	181.6	181.3	181.0	180.7	181.0	181.3	181.6	181.9	182.1	182.2	182.3
117.5°	205.7	205.4	205.1	204.8	205.1	205.4	205.7	206.0	206.3	206.5	206.8
120°	222.7	222.4	222.1	221.8	222.1	222.4	222.7	223.0	223.2	223.2	223.2
122.5°	239.1	238.8	238.7	238.4	238.7	238.8	239.1	239.3	239.6	239.8	240.0
125°	264.1	264.0	263.9	263.8	263.9	264.0	264.1	264.2	264.4	264.7	265.0
127.5°	287.9	287.6	287.2	286.9	287.2	287.6	287.9	288.2	288.6	288.9	289.3
130°	304.8	304.4	304.0	303.6	304.0	304.4	304.8	305.1	305.5	305.7	305.9
132.5°	320.4	320.1	319.8	319.5	319.8	320.1	320.4	320.8	321.2	321.5	322.0
135°	345.2	344.8	344.5	344.2	344.5	344.8	345.2	345.4	345.6	345.7	345.9
137.5°	367.8	367.4	367.0	366.6	367.0	367.4	367.8	368.2	368.4	368.5	368.6
140°	383.3	382.9	382.5	382.1	382.5	382.9	383.3	383.8	384.0	384.0	384.0
142.5°	397.4	397.0	396.6	396.2	396.6	397.0	397.4	397.8	398.0	397.9	397.8
145°	418.6	418.2	417.8	417.4	417.8	418.2	418.6	419.0	419.1	419.1	419.0
147.5°	437.4	437.0	436.7	436.3	436.7	437.0	437.4	437.8	437.9	437.7	437.4
150°	449.5	449.2	448.9	448.6	448.9	449.2	449.5	449.8	449.8	449.5	449.2
152.5°	461.3	460.9	460.5	460.2	460.5	460.9	461.3	461.7	461.7	461.3	460.9
155°	476.6	476.3	475.9	475.7	475.9	476.3	476.6	476.9	476.8	476.3	475.8
157.5°	490.5	490.0	489.6	489.0	489.6	490.0	490.5	491.0	490.9	490.2	489.5
160°	498.6	498.2	497.7	497.3	497.7	498.2	498.6	499.0	498.8	498.3	497.6
162.5°	506.0	505.6	505.1	504.6	505.1	505.6	506.0	506.5	506.4	505.7	505.0
165°	515.6	515.1	514.6	514.0	514.6	515.1	515.6	516.1	515.9	515.3	514.6
167.5°	523.4	522.9	522.4	521.8	522.4	522.9	523.4	523.9	523.9	523.2	522.4
170°	527.6	527.0	526.4	525.9	526.4	527.0	527.6	528.2	528.1	527.5	526.8
172.5°	530.9	530.3	529.7	529.1	529.7	530.3	530.9	531.5	531.4	530.8	530.0
175°	534.4	533.8	533.2	532.6	533.2	533.8	534.4	535.0	535.0	534.2	533.5
177.5°	535.7	535.2	534.7	534.2	534.7	535.2	535.7	536.1	536.1	535.7	535.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	5.9	6.3	6.0	5.9	5.4	5.1	5.1	5.1	5.3	5.3	5.3
90°	15.6	15.8	13.6	11.4	9.2	7.0	5.3	4.0	2.9	1.7	0.5
92.5°	14.4	14.3	13.9	13.3	12.8	12.3	11.6	10.7	9.8	9.0	8.1
95°	28.9	28.9	28.7	28.5	28.3	28.1	27.5	26.5	25.5	24.5	23.5
97.5°	48.6	48.6	48.2	47.8	47.5	47.1	46.4	45.6	44.7	43.8	42.9
100°	62.3	62.3	62.0	61.7	61.5	61.2	60.6	59.8	58.9	58.1	57.4
102.5°	77.2	77.2	76.8	76.4	76.0	75.7	75.1	74.5	73.8	73.2	72.6
105°	99.6	99.4	99.2	98.9	98.8	98.5	98.3	98.0	97.8	97.4	97.1
107.5°	124.0	123.9	123.9	123.9	123.9	123.9	123.7	123.2	122.8	122.3	121.9
110°	140.5	140.5	140.5	140.5	140.5	140.5	140.2	139.6	138.9	138.4	137.8



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	157.2	157.5	157.6	157.6	157.7	157.8	157.6	156.9	156.3	155.7	155.1
115°	182.4	182.5	182.7	182.9	183.1	183.3	183.1	182.5	181.9	181.3	180.7
117.5°	207.0	207.2	207.8	208.3	209.0	209.5	209.4	208.6	207.8	207.0	206.2
120°	223.2	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2
122.5°	240.3	240.5	241.1	241.6	242.2	242.7	242.6	241.6	240.7	239.6	238.7
125°	265.3	265.6	265.9	266.3	266.5	266.8	266.5	265.6	264.7	263.8	262.9
127.5°	289.6	290.0	290.4	290.7	291.1	291.4	291.0	289.9	288.8	287.6	286.5
130°	306.1	306.3	306.5	306.7	306.9	307.0	306.5	305.2	303.9	302.6	301.3
132.5°	322.5	322.9	322.9	322.8	322.8	322.7	322.2	321.2	320.0	319.0	317.9
135°	345.9	346.0	345.9	345.6	345.4	345.2	344.6	343.5	342.4	341.3	340.2
137.5°	368.7	368.8	368.5	368.3	368.0	367.7	367.2	366.3	365.4	364.5	363.5
140°	384.0	384.0	383.5	382.9	382.5	382.0	381.3	380.3	379.5	378.6	377.6
142.5°	397.8	397.7	397.4	397.0	396.7	396.3	395.7	394.8	394.0	393.0	392.1
145°	418.8	418.7	418.2	417.6	416.9	416.4	415.7	415.0	414.3	413.6	412.9
147.5°	437.2	437.0	436.6	436.2	435.8	435.4	434.7	434.0	433.1	432.2	431.4
150°	448.9	448.6	448.1	447.7	447.3	446.9	446.5	445.8	445.3	444.7	444.1
152.5°	460.5	460.2	459.6	459.1	458.7	458.2	457.6	457.1	456.5	455.9	455.3
155°	475.3	474.8	474.4	474.2	473.9	473.6	473.2	472.9	472.7	472.4	472.1
157.5°	488.9	488.1	488.0	487.8	487.6	487.4	487.3	487.0	486.8	486.6	486.4
160°	497.1	496.5	496.4	496.2	496.1	496.1	495.9	495.7	495.5	495.3	495.1
162.5°	504.4	503.7	503.6	503.5	503.4	503.3	503.2	503.2	503.1	503.1	503.0
165°	513.9	513.2	513.2	513.2	513.2	513.2	513.3	513.3	513.4	513.5	513.7
167.5°	521.7	521.0	521.0	521.1	521.1	521.1	521.3	521.6	521.9	522.2	522.4
170°	526.1	525.4	525.5	525.5	525.7	525.8	526.0	526.2	526.6	526.9	527.2
172.5°	529.3	528.6	528.7	528.9	528.9	529.0	529.3	529.5	529.8	530.1	530.4
175°	532.8	532.1	532.3	532.6	532.7	533.0	533.2	533.5	533.8	534.1	534.4
177.5°	534.7	534.2	534.4	534.6	534.7	534.9	535.0	535.3	535.5	535.8	536.1
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.3	7.4	7.7	8.6	8.5	9.0	9.3	9.6	9.8	9.5	9.3
90°	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6	15.4
92.5°	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4	14.4
95°	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9	28.9
97.5°	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6	48.6
100°	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3	62.3
102.5°	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2	77.3
105°	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6	99.8
107.5°	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0	124.1
110°	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2	157.0
115°	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4	182.3
117.5°	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0	206.8
120°	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2	223.2
122.5°	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3	240.0
125°	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3	265.0
127.5°	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6	289.3
130°	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1	305.9
132.5°	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5	322.0
135°	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9	345.9
137.5°	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7	368.6
140°	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0	384.0
142.5°	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8	397.8
145°	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8	419.0
147.5°	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2	437.4
150°	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9	449.2
152.5°	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5	460.9
155°	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3	475.8
157.5°	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9	489.5
160°	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1	497.6
162.5°	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4	505.0
165°	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9	514.6
167.5°	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7	522.4
170°	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1	526.8
172.5°	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3	530.0
175°	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8	533.5
177.5°	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7	535.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	9.4	9.4	9.1	9.2	9.4	9.2	9.2
90°	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.4	140.1	139.7	139.4	139.1



TEST NUMBER: P331295-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)