

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333578

Luminaire Tested: **S125RDIP-S850D1205U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333578
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1205U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7418.5 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8881	8881	8881
5°	8901	8800	8854
10°	8834	8718	8718
15°	8729	8541	8471
20°	8594	8294	8194
25°	8437	8052	7874
30°	8240	7768	7520
35°	8041	7476	7123
40°	7854	7171	6734
45°	7626	6830	6308
50°	7398	6459	5865
55°	7133	6104	5391
60°	6868	5674	4883
65°	6554	5174	4300
70°	6197	4549	3707
75°	5702	3835	3084
80°	5021	3013	2589
85°	4231	2460	2312



TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	1.7
10°-20°	361.3	4.9
20°-30°	524.0	7.1
30°-40°	597.2	8.0
40°-50°	582.1	7.8
50°-60°	490.0	6.6
60°-70°	343.5	4.6
70°-80°	176.6	2.4
80°-90°	47.9	0.6
90°-100°	100.0	1.3
100°-110°	295.3	4.0
110°-120°	500.2	6.7
120°-130°	658.3	8.9
130°-140°	737.7	9.9
140°-150°	723.0	9.7
150°-160°	607.3	8.2
160°-170°	403.7	5.4
170°-180°	141.3	1.9
0°-30°	1014.6	13.7
0°-40°	1611.8	21.7
0°-60°	2683.9	36.2
0°-90°	3251.8	43.8
90°-120°	895.6	12.1
90°-150°	3014.6	40.6
90°-180°	4167.0	56.2
0°-180°	7418.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1373	1368	1357	1367	1366	130
15°	1306	1298	1277	1276	1267	368
25°	1184	1167	1130	1117	1105	545
35°	1020	994	948	919	904	638
45°	835	803	748	708	691	644
55°	634	599	542	497	479	566
65°	429	392	339	298	281	425
75°	228	197	154	132	124	242
85°	57	39	33	32	31	64
90°	1	10	19	24	28	7
95°	76	78	90	97	100	81
105°	265	271	278	284	288	283
115°	501	505	508	507	506	495
125°	731	738	739	737	736	654
135°	951	957	959	958	954	732
145°	1152	1156	1160	1160	1156	720
155°	1318	1318	1319	1323	1318	607
165°	1433	1431	1432	1436	1429	404
175°	1490	1485	1485	1491	1484	141
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1377.5	1377.0	1376.4	1375.9	1375.3	1374.1	1372.3	1370.4	1368.6	1366.7	1368.6
5°	1373.0	1372.1	1371.1	1370.2	1369.3	1367.6	1365.0	1362.5	1359.9	1357.4	1359.7
7.5°	1359.5	1358.6	1357.7	1356.8	1356.0	1354.0	1351.0	1347.9	1344.9	1341.8	1343.4
10°	1347.0	1346.3	1345.6	1344.9	1344.2	1342.3	1339.1	1335.8	1332.6	1329.4	1330.0
12.5°	1332.9	1332.0	1331.1	1330.3	1329.4	1326.8	1322.4	1318.1	1313.8	1309.4	1309.9
15°	1305.5	1304.1	1302.7	1301.3	1299.9	1296.8	1292.0	1287.1	1282.3	1277.4	1277.2
17.5°	1274.5	1272.4	1270.3	1268.2	1266.0	1261.9	1255.8	1249.7	1243.6	1237.5	1236.4
20°	1250.4	1248.1	1245.8	1243.5	1241.2	1236.3	1229.0	1221.6	1214.2	1206.8	1205.7
22.5°	1223.8	1221.5	1219.2	1216.9	1214.6	1209.6	1201.8	1194.1	1186.3	1178.6	1176.3
25°	1184.0	1180.5	1177.0	1173.6	1170.1	1164.1	1155.6	1147.0	1138.5	1130.0	1127.0
27.5°	1138.3	1134.1	1129.9	1125.7	1121.5	1114.8	1105.7	1096.5	1087.4	1078.2	1074.0
30°	1105.0	1100.6	1096.3	1091.9	1087.5	1080.4	1070.8	1061.1	1051.4	1041.7	1036.4
32.5°	1072.6	1067.5	1062.4	1057.3	1052.1	1044.6	1034.8	1024.9	1015.0	1005.1	999.3
35°	1019.9	1014.3	1008.8	1003.2	997.7	989.7	979.4	969.0	958.6	948.2	941.5
37.5°	968.1	961.4	954.7	947.9	941.2	932.5	921.8	911.0	900.3	889.6	881.6
40°	931.6	924.7	917.7	910.8	903.9	894.9	883.8	872.7	861.7	850.6	841.8
42.5°	893.4	886.3	879.2	872.0	864.9	855.7	844.2	832.8	821.3	809.9	801.5
45°	835.0	828.3	821.6	814.9	808.2	798.5	785.8	773.2	760.5	747.8	738.5
47.5°	774.6	767.5	760.4	753.4	746.3	736.4	723.6	710.8	698.0	685.2	675.7
50°	736.3	728.7	721.1	713.5	705.9	695.5	682.3	669.2	656.0	642.9	633.2
52.5°	694.8	687.0	679.2	671.4	663.6	653.5	641.1	628.7	616.2	603.8	593.4
55°	633.5	626.1	618.8	611.4	604.0	593.8	580.9	568.0	555.1	542.1	531.7
57.5°	571.6	563.7	555.8	547.9	540.1	529.9	517.4	504.9	492.5	480.0	469.9
60°	531.7	523.7	515.6	507.5	499.4	489.2	476.7	464.2	451.8	439.3	429.2
62.5°	489.4	481.7	474.0	466.2	458.5	448.4	435.7	423.1	410.4	397.8	388.4
65°	428.9	421.1	413.2	405.4	397.5	387.5	375.3	363.0	350.8	338.6	329.3
67.5°	368.9	361.0	353.2	345.4	337.5	327.7	316.0	304.3	292.6	280.8	272.4
70°	328.2	320.3	312.5	304.6	296.8	287.1	275.6	264.0	252.5	240.9	233.8
72.5°	288.3	280.6	273.0	265.3	257.7	248.4	237.6	226.8	216.0	205.2	198.6
75°	228.5	221.6	214.6	207.7	200.8	192.5	182.8	173.1	163.4	153.7	148.6
77.5°	169.1	163.5	158.0	152.5	146.9	140.3	132.5	124.8	117.0	109.3	105.7
80°	135.0	129.5	123.9	118.4	112.9	106.9	100.4	93.9	87.5	81.0	78.9
82.5°	101.8	96.8	91.8	86.8	81.8	77.1	72.7	68.3	63.8	59.4	58.4
85°	57.1	53.0	48.8	44.7	40.5	37.8	36.7	35.5	34.4	33.2	33.0
87.5°	19.3	18.5	17.6	16.7	15.8	15.5	15.7	15.8	16.0	16.2	16.4
90°	1.2	3.2	5.3	7.4	9.4	11.4	13.2	15.0	16.8	18.6	19.9
92.5°	28.1	29.6	31.0	32.5	33.9	35.7	38.0	40.2	42.4	44.6	46.3
95°	75.5	76.0	76.6	77.1	77.6	79.1	81.7	84.3	86.9	89.5	91.3
97.5°	125.5	125.7	125.9	126.1	126.3	128.2	131.8	135.3	138.9	142.5	144.2
100°	162.7	162.7	162.7	162.7	162.7	164.4	167.7	171.1	174.4	177.8	180.1
102.5°	202.7	203.7	204.7	205.8	206.8	208.2	209.9	211.6	213.3	215.0	217.5
105°	264.9	266.2	267.5	268.8	270.1	271.5	273.1	274.6	276.2	277.7	279.3
107.5°	333.7	335.0	336.3	337.6	338.9	340.1	341.3	342.5	343.7	344.9	345.7
110°	381.2	382.4	383.7	385.0	386.3	387.3	388.1	388.9	389.7	390.4	391.2



TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	429.5	430.2	430.8	431.5	432.2	433.0	434.0	435.0	435.9	436.9	437.3
115°	500.8	501.9	502.9	503.9	505.0	505.7	506.3	506.8	507.3	507.8	507.6
117.5°	572.4	572.9	573.4	573.8	574.3	574.7	575.2	575.7	576.1	576.6	576.8
120°	617.0	618.3	619.6	620.9	622.2	623.0	623.2	623.5	623.8	624.0	624.0
122.5°	665.4	665.9	666.3	666.8	667.2	667.8	668.5	669.2	669.8	670.5	670.3
125°	730.9	732.5	734.0	735.6	737.1	738.0	738.3	738.5	738.8	739.1	738.5
127.5°	800.7	801.5	802.4	803.3	804.2	804.8	805.1	805.4	805.7	806.0	805.7
130°	842.5	843.8	845.1	846.4	847.6	848.6	849.1	849.6	850.1	850.6	850.4
132.5°	884.3	886.4	888.6	890.7	892.8	893.8	893.7	893.6	893.5	893.4	893.1
135°	950.6	952.1	953.7	955.2	956.8	957.7	957.9	958.2	958.4	958.7	958.7
137.5°	1012.8	1014.3	1015.8	1017.3	1018.8	1019.9	1020.4	1021.0	1021.6	1022.1	1022.4
140°	1052.8	1054.1	1055.4	1056.7	1058.0	1059.0	1059.8	1060.6	1061.3	1062.1	1062.6
142.5°	1092.8	1093.9	1095.0	1096.0	1097.1	1098.2	1099.1	1100.1	1101.1	1102.1	1102.4
145°	1151.6	1152.6	1153.7	1154.7	1155.7	1156.6	1157.4	1158.2	1158.9	1159.7	1159.7
147.5°	1206.0	1206.5	1207.1	1207.7	1208.2	1208.8	1209.5	1210.1	1210.7	1211.3	1211.9
150°	1242.2	1242.0	1241.7	1241.5	1241.2	1241.6	1242.6	1243.6	1244.7	1245.7	1245.7
152.5°	1272.0	1272.3	1272.7	1273.1	1273.4	1273.8	1274.2	1274.6	1275.1	1275.5	1276.1
155°	1317.8	1317.8	1317.8	1317.8	1317.8	1317.9	1318.2	1318.4	1318.7	1318.9	1320.0
157.5°	1358.7	1358.1	1357.5	1357.0	1356.4	1356.2	1356.5	1356.8	1357.0	1357.3	1358.3
160°	1382.8	1382.1	1381.3	1380.5	1379.7	1379.5	1379.7	1380.0	1380.3	1380.5	1381.5
162.5°	1404.2	1403.7	1403.1	1402.5	1401.9	1401.7	1401.7	1401.8	1401.8	1401.9	1403.1
165°	1432.8	1432.3	1431.8	1431.3	1430.7	1430.6	1430.9	1431.1	1431.4	1431.6	1432.7
167.5°	1457.0	1455.9	1454.9	1453.9	1452.8	1452.3	1452.3	1452.3	1452.3	1452.3	1453.9
170°	1470.0	1469.0	1467.9	1466.9	1465.9	1465.3	1465.3	1465.3	1465.3	1465.3	1466.9
172.5°	1479.3	1478.3	1477.2	1476.2	1475.2	1474.6	1474.6	1474.6	1474.6	1474.6	1476.2
175°	1489.7	1488.7	1487.7	1486.6	1485.6	1485.1	1485.1	1485.1	1485.1	1485.1	1486.6
177.5°	1495.1	1494.3	1493.4	1492.6	1491.8	1491.3	1491.1	1490.9	1490.6	1490.4	1491.7
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2



TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1370.4	1372.3	1374.1	1375.0	1374.8	1374.6	1374.4	1374.2
5°	1362.0	1364.3	1366.6	1367.6	1367.1	1366.6	1366.2	1365.7
7.5°	1345.1	1346.7	1348.3	1348.8	1348.3	1347.8	1347.3	1346.8
10°	1330.7	1331.4	1332.1	1332.1	1331.4	1330.7	1330.0	1329.4
12.5°	1310.4	1310.9	1311.4	1311.2	1310.1	1309.0	1308.0	1306.9
15°	1277.0	1276.7	1276.5	1275.4	1273.3	1271.2	1269.1	1267.0
17.5°	1235.2	1234.1	1232.9	1231.5	1229.8	1228.1	1226.4	1224.7
20°	1204.5	1203.3	1202.2	1200.6	1198.5	1196.4	1194.3	1192.3
22.5°	1174.0	1171.8	1169.5	1167.5	1165.8	1164.1	1162.4	1160.7
25°	1124.0	1121.0	1118.0	1115.2	1112.6	1110.1	1107.6	1105.0
27.5°	1069.8	1065.6	1061.4	1058.1	1055.7	1053.2	1050.8	1048.3
30°	1031.1	1025.8	1020.4	1016.8	1014.7	1012.6	1010.5	1008.4
32.5°	993.4	987.5	981.7	977.4	974.8	972.2	969.5	966.9
35°	934.8	928.1	921.4	916.5	913.2	910.0	906.8	903.5
37.5°	873.6	865.5	857.5	851.9	848.8	845.6	842.5	839.4
40°	833.0	824.3	815.5	809.7	807.0	804.2	801.4	798.7
42.5°	793.1	784.7	776.3	770.0	766.0	761.9	757.8	753.8
45°	729.3	720.1	710.8	704.5	701.0	697.6	694.1	690.6
47.5°	666.2	656.7	647.2	640.5	636.7	632.9	629.0	625.2
50°	623.5	613.8	604.1	597.5	594.1	590.6	587.1	583.7
52.5°	583.0	572.5	562.1	555.1	551.7	548.2	544.8	541.3
55°	521.4	511.0	500.6	493.5	489.9	486.2	482.5	478.8
57.5°	459.7	449.6	439.4	432.7	429.4	426.1	422.9	419.6
60°	419.0	408.8	398.7	391.9	388.4	385.0	381.5	378.0
62.5°	378.9	369.5	360.1	353.7	350.2	346.7	343.3	339.8
65°	320.1	310.9	301.6	295.3	291.8	288.4	284.9	281.4
67.5°	263.9	255.5	247.0	241.4	238.7	235.9	233.1	230.4
70°	226.6	219.5	212.3	207.4	204.6	201.8	199.1	196.3
72.5°	192.0	185.4	178.8	174.6	172.7	170.9	169.1	167.2
75°	143.6	138.5	133.4	130.1	128.4	126.8	125.2	123.6
77.5°	102.1	98.6	95.0	92.7	91.5	90.3	89.1	87.9
80°	76.9	74.8	72.7	71.4	71.0	70.5	70.0	69.6
82.5°	57.5	56.5	55.5	54.9	54.6	54.4	54.1	53.8
85°	32.8	32.5	32.3	32.1	31.8	31.6	31.4	31.2
87.5°	16.7	17.0	17.2	17.3	17.3	17.3	17.2	17.2
90°	21.2	22.5	23.8	24.8	25.6	26.3	27.1	27.9
92.5°	48.0	49.7	51.4	52.6	53.1	53.7	54.3	54.8
95°	93.1	94.9	96.7	97.9	98.4	98.9	99.4	99.9
97.5°	145.9	147.6	149.3	150.3	150.6	150.9	151.2	151.5
100°	182.4	184.8	187.1	188.5	189.0	189.5	190.1	190.6
102.5°	220.0	222.6	225.1	226.7	227.5	228.2	228.9	229.6
105°	280.8	282.4	283.9	285.1	285.9	286.6	287.4	288.2
107.5°	346.4	347.2	348.0	348.4	348.3	348.3	348.2	348.1
110°	392.0	392.8	393.5	393.8	393.5	393.3	393.0	392.8



TEST NUMBER: P333578

CATALOG NUMBER: S125RDIP-S850D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	437.7	438.0	438.4	438.3	437.9	437.4	436.9	436.5
115°	507.3	507.0	506.8	506.5	506.3	506.0	505.7	505.5
117.5°	577.0	577.2	577.4	577.0	576.0	575.0	573.9	572.9
120°	624.0	624.0	624.0	623.5	622.5	621.4	620.4	619.4
122.5°	670.1	669.9	669.7	669.2	668.3	667.5	666.7	665.9
125°	738.0	737.5	737.0	736.6	736.4	736.1	735.8	735.6
127.5°	805.5	805.2	805.0	804.6	804.1	803.5	803.0	802.5
130°	850.1	849.8	849.6	849.2	848.7	848.2	847.6	847.1
132.5°	892.9	892.6	892.3	891.9	891.1	890.4	889.7	889.0
135°	958.7	958.7	958.7	958.2	957.1	956.1	955.1	954.0
137.5°	1022.8	1023.1	1023.4	1022.9	1021.6	1020.3	1019.0	1017.7
140°	1063.1	1063.7	1064.2	1063.8	1062.5	1061.2	1059.9	1058.6
142.5°	1102.7	1103.0	1103.3	1102.8	1101.5	1100.3	1099.0	1097.7
145°	1159.7	1159.7	1159.7	1159.3	1158.6	1157.8	1157.0	1156.2
147.5°	1212.6	1213.2	1213.8	1213.2	1211.5	1209.7	1208.0	1206.2
150°	1245.7	1245.7	1245.7	1245.5	1244.9	1244.4	1243.9	1243.4
152.5°	1276.7	1277.3	1277.9	1277.8	1276.9	1275.9	1275.0	1274.1
155°	1321.0	1322.0	1323.1	1322.9	1321.6	1320.3	1319.1	1317.8
157.5°	1359.3	1360.4	1361.4	1361.1	1359.4	1357.7	1356.0	1354.3
160°	1382.6	1383.6	1384.6	1384.5	1383.2	1381.9	1380.6	1379.4
162.5°	1404.4	1405.6	1406.9	1406.7	1405.2	1403.7	1402.2	1400.7
165°	1433.7	1434.7	1435.8	1435.5	1434.0	1432.4	1430.9	1429.3
167.5°	1455.4	1457.0	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1468.4	1470.0	1471.5	1471.4	1469.6	1467.8	1466.0	1464.2
172.5°	1477.7	1479.3	1480.8	1480.8	1479.2	1477.6	1476.0	1474.4
175°	1488.2	1489.7	1491.3	1491.2	1489.4	1487.6	1485.7	1483.9
177.5°	1492.9	1494.2	1495.4	1495.3	1493.9	1492.4	1491.0	1489.5
180°	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2	1493.2

(END OF REPORT)