

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331303-927

Luminaire Tested: **SA2XXDIP-C485D725U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331303-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D725U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3995.3 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43				
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	44	43	42	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31				
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	27				
4	74	64	56	50	67	59	52	47	49	44	40	40	37	34	32	29	27	24				
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24	21				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	21	18				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17				
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17	15				
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14				
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.3	1.8
10°-20°	213.1	5.3
20°-30°	309.3	7.7
30°-40°	326.4	8.2
40°-50°	289.0	7.2
50°-60°	230.6	5.8
60°-70°	156.8	3.9
70°-80°	80.4	2.0
80°-90°	21.3	0.5
90°-100°	26.1	0.7
100°-110°	95.8	2.4
110°-120°	256.1	6.4
120°-130°	422.7	10.6
130°-140°	449.6	11.3
140°-150°	417.8	10.5
150°-160°	335.9	8.4
160°-170°	216.5	5.4
170°-180°	74.5	1.9
0°-30°	595.8	14.9
0°-40°	922.2	23.1
0°-60°	1441.8	36.1
0°-90°	1700.3	42.6
90°-120°	378.0	9.5
90°-150°	1668.1	41.8
90°-180°	2295.0	57.4
0°-180°	3995.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	15	1	15	1	15	8
95°	24	37	24	37	24	23
105°	43	172	43	172	43	45
115°	46	326	46	326	46	116
125°	484	461	484	461	484	419
135°	589	570	589	570	589	454
145°	672	661	672	661	672	420
155°	729	728	729	728	729	336
165°	766	767	766	767	766	216
175°	780	785	780	785	780	74
180°	783	783	783	783	783	



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	9.2	9.2	9.3	9.0	9.0	9.2	9.0	8.6	8.8	8.9	9.0
90°	15.3	15.1	14.8	14.6	14.3	13.9	13.2	12.6	12.0	11.3	10.3
92.5°	15.3	15.1	15.0	14.8	14.7	14.4	14.1	13.8	13.5	13.2	12.7
95°	24.4	24.5	24.6	24.7	24.9	24.6	24.0	23.4	22.7	22.1	21.2
97.5°	32.6	32.4	32.2	32.1	31.9	31.6	31.1	30.6	30.1	29.5	27.6
100°	37.9	37.7	37.5	37.2	37.0	36.4	35.3	34.3	33.3	32.3	30.2
102.5°	40.7	40.3	40.0	39.6	39.3	38.4	37.2	35.8	34.5	33.2	31.1
105°	43.1	42.5	42.1	41.6	41.0	40.1	38.7	37.3	36.0	34.5	32.9
107.5°	44.3	43.8	43.3	42.8	42.3	42.8	44.1	45.6	47.0	48.4	49.6
110°	44.8	44.3	43.7	43.3	42.8	48.8	61.4	74.0	86.6	99.2	135.5



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.2	44.8	44.4	44.0	43.6	66.4	112.3	158.3	204.2	250.1	259.1
115°	46.5	55.5	64.6	73.7	82.7	116.5	174.8	233.1	291.4	349.7	346.5
117.5°	189.7	219.5	249.3	279.1	308.9	330.8	344.9	359.1	373.2	387.3	385.1
120°	345.7	362.7	379.7	396.6	413.7	421.4	419.9	418.4	416.8	415.3	413.1
122.5°	431.3	434.7	437.9	441.2	444.6	445.8	444.8	443.9	443.0	442.1	439.7
125°	484.5	484.1	483.8	483.4	483.0	482.4	481.5	480.6	479.7	478.9	476.4
127.5°	518.1	518.0	517.9	517.8	517.8	517.1	515.8	514.5	513.3	511.9	510.2
130°	538.9	539.0	539.2	539.3	539.4	538.8	537.4	536.0	534.6	533.2	531.9
132.5°	559.3	559.4	559.6	559.7	559.8	559.3	558.1	556.9	555.7	554.5	553.2
135°	588.7	589.0	589.3	589.5	589.8	589.3	588.0	586.8	585.5	584.2	583.1
137.5°	615.6	616.1	616.5	617.0	617.3	617.0	615.7	614.5	613.2	612.0	610.7
140°	632.4	633.0	633.7	634.3	634.9	634.7	633.5	632.4	631.3	630.2	628.8
142.5°	648.7	649.4	650.0	650.6	651.3	651.0	650.0	649.0	647.9	646.9	645.3
145°	671.5	672.2	672.8	673.4	674.0	673.9	673.0	672.2	671.3	670.3	668.2
147.5°	691.6	692.1	692.6	693.2	693.7	693.6	693.0	692.3	691.7	691.0	688.9
150°	703.8	704.4	705.0	705.7	706.3	706.2	705.5	704.7	704.0	703.2	701.2
152.5°	714.2	715.1	715.9	716.8	717.6	717.6	716.8	716.1	715.3	714.5	712.6
155°	728.7	729.8	730.8	731.7	732.8	732.9	732.1	731.4	730.6	729.8	728.3
157.5°	742.0	743.0	743.9	745.0	745.9	746.0	745.1	744.3	743.5	742.6	741.5
160°	749.7	750.6	751.5	752.3	753.2	753.3	752.6	751.8	751.1	750.3	749.5
162.5°	756.1	757.2	758.2	759.3	760.4	760.5	759.6	758.8	758.0	757.1	756.5
165°	765.6	766.4	767.3	768.3	769.1	769.1	768.3	767.3	766.4	765.6	765.2
167.5°	771.6	772.7	773.9	775.0	776.1	776.3	775.4	774.5	773.6	772.7	772.4
170°	775.2	776.3	777.4	778.6	779.7	779.9	779.0	778.1	777.2	776.3	776.1
172.5°	777.9	779.0	780.2	781.3	782.4	782.6	781.7	780.9	780.0	779.0	778.8
175°	780.3	781.6	782.8	784.1	785.4	785.5	784.7	783.8	782.9	782.0	781.7
177.5°	781.8	782.7	783.6	784.5	785.4	785.5	784.8	784.1	783.4	782.7	782.6
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	9.0	8.8	8.6	8.8	7.8	7.5	6.3	5.3	5.4	5.4	5.2
90°	9.3	8.3	7.3	6.1	4.8	3.3	2.0	0.6	2.0	3.3	4.8
92.5°	12.1	11.6	11.2	10.9	11.1	11.2	11.3	11.4	11.3	11.2	11.1
95°	20.4	19.5	18.5	20.2	24.4	28.5	32.7	36.8	32.7	28.5	24.4
97.5°	25.5	23.4	21.4	26.2	37.9	49.7	61.4	73.1	61.4	49.7	37.9
100°	28.0	25.9	23.8	31.3	48.6	65.8	83.0	100.3	83.0	65.8	48.6
102.5°	69.0	86.9	104.8	115.6	119.3	122.9	126.6	130.2	126.6	122.9	119.3
105°	103.3	137.7	172.1	187.4	183.6	179.8	176.0	172.3	176.0	179.8	183.6
107.5°	130.9	172.1	213.3	232.4	229.3	226.3	223.2	220.2	223.2	226.3	229.3
110°	172.0	208.3	244.7	261.6	259.0	256.4	253.7	251.0	253.7	256.4	259.0





TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	268.1	277.1	286.1	289.4	287.1	284.7	282.4	280.0	282.4	284.7	287.1
115°	343.3	340.2	337.1	334.4	332.2	330.1	328.0	325.8	328.0	330.1	332.2
117.5°	382.9	380.8	378.6	376.3	373.9	371.5	369.2	366.8	369.2	371.5	373.9
120°	410.8	408.6	406.3	404.3	402.3	400.4	398.5	396.6	398.5	400.4	402.3
122.5°	437.2	434.7	432.2	430.0	428.0	426.0	424.1	422.1	424.1	426.0	428.0
125°	474.0	471.7	469.3	467.2	465.6	464.0	462.3	460.7	462.3	464.0	465.6
127.5°	508.3	506.6	504.8	503.0	501.1	499.4	497.6	495.7	497.6	499.4	501.1
130°	530.4	529.1	527.7	526.0	523.9	522.0	520.0	517.9	520.0	522.0	523.9
132.5°	551.8	550.4	549.0	547.5	545.7	544.1	542.3	540.6	542.3	544.1	545.7
135°	581.9	580.8	579.7	578.1	576.2	574.1	572.1	570.1	572.1	574.1	576.2
137.5°	609.4	608.2	606.9	605.5	604.1	602.7	601.3	599.9	601.3	602.7	604.1
140°	627.4	626.0	624.6	623.4	622.4	621.4	620.4	619.4	620.4	621.4	622.4
142.5°	643.7	642.1	640.6	639.3	638.4	637.5	636.6	635.7	636.6	637.5	638.4
145°	666.1	663.9	661.8	660.8	660.9	661.1	661.2	661.3	661.2	661.1	660.9
147.5°	686.7	684.7	682.5	681.8	682.2	682.7	683.2	683.7	683.2	682.7	682.2
150°	699.2	697.2	695.2	694.6	695.5	696.4	697.3	698.2	697.3	696.4	695.5
152.5°	710.7	708.8	706.9	706.5	707.4	708.4	709.4	710.3	709.4	708.4	707.4
155°	726.8	725.3	723.8	723.7	724.8	725.9	727.1	728.2	727.1	725.9	724.8
157.5°	740.5	739.4	738.3	738.3	739.3	740.2	741.2	742.1	741.2	740.2	739.3
160°	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	749.5	748.8	748.0
162.5°	755.7	755.1	754.5	754.5	755.3	756.1	756.8	757.6	756.8	756.1	755.3
165°	764.9	764.5	764.1	764.2	765.0	765.8	766.5	767.3	766.5	765.8	765.0
167.5°	772.0	771.7	771.3	771.5	772.3	773.0	773.8	774.5	773.8	773.0	772.3
170°	775.9	775.6	775.3	775.6	776.3	777.1	777.8	778.6	777.8	777.1	776.3
172.5°	778.6	778.3	778.1	778.3	779.0	779.8	780.5	781.3	780.5	779.8	779.0
175°	781.5	781.3	781.0	781.3	782.2	783.1	783.9	784.8	783.9	783.1	782.2
177.5°	782.5	782.4	782.3	782.6	783.3	784.0	784.7	785.4	784.7	784.0	783.3
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	5.2	5.2	5.2	5.4	5.4	5.3	5.2	5.4	5.5	5.1	5.2
90°	6.1	7.3	8.3	9.3	10.3	11.3	12.0	12.6	13.2	13.9	14.3
92.5°	10.9	11.2	11.6	12.1	12.7	13.2	13.5	13.8	14.1	14.4	14.7
95°	20.2	18.5	19.5	20.4	21.2	22.1	22.7	23.4	24.0	24.6	24.9
97.5°	26.2	21.4	23.4	25.5	27.6	29.5	30.1	30.6	31.1	31.6	31.9
100°	31.3	23.8	25.9	28.0	30.2	32.3	33.3	34.3	35.3	36.4	37.0
102.5°	115.6	104.8	86.9	69.0	51.1	33.2	34.5	35.8	37.2	38.4	39.3
105°	187.4	172.1	137.7	103.3	68.9	34.5	36.0	37.3	38.7	40.1	41.0
107.5°	232.4	213.3	172.1	130.9	89.6	48.4	47.0	45.6	44.1	42.8	42.3
110°	261.6	244.7	208.3	172.0	135.5	99.2	86.6	74.0	61.4	48.8	42.8



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.4	286.1	277.1	268.1	259.1	250.1	204.2	158.3	112.3	66.4	43.6
115°	334.4	337.1	340.2	343.3	346.5	349.7	291.4	233.1	174.8	116.5	82.7
117.5°	376.3	378.6	380.8	382.9	385.1	387.3	373.2	359.1	344.9	330.8	308.9
120°	404.3	406.3	408.6	410.8	413.1	415.3	416.8	418.4	419.9	421.4	413.7
122.5°	430.0	432.2	434.7	437.2	439.7	442.1	443.0	443.9	444.8	445.8	444.6
125°	467.2	469.3	471.7	474.0	476.4	478.9	479.7	480.6	481.5	482.4	483.0
127.5°	503.0	504.8	506.6	508.3	510.2	511.9	513.3	514.5	515.8	517.1	517.8
130°	526.0	527.7	529.1	530.4	531.9	533.2	534.6	536.0	537.4	538.8	539.4
132.5°	547.5	549.0	550.4	551.8	553.2	554.5	555.7	556.9	558.1	559.3	559.8
135°	578.1	579.7	580.8	581.9	583.1	584.2	585.5	586.8	588.0	589.3	589.8
137.5°	605.5	606.9	608.2	609.4	610.7	612.0	613.2	614.5	615.7	617.0	617.3
140°	623.4	624.6	626.0	627.4	628.8	630.2	631.3	632.4	633.5	634.7	634.9
142.5°	639.3	640.6	642.1	643.7	645.3	646.9	647.9	649.0	650.0	651.0	651.3
145°	660.8	661.8	663.9	666.1	668.2	670.3	671.3	672.2	673.0	673.9	674.0
147.5°	681.8	682.5	684.7	686.7	688.9	691.0	691.7	692.3	693.0	693.6	693.7
150°	694.6	695.2	697.2	699.2	701.2	703.2	704.0	704.7	705.5	706.2	706.3
152.5°	706.5	706.9	708.8	710.7	712.6	714.5	715.3	716.1	716.8	717.6	717.6
155°	723.7	723.8	725.3	726.8	728.3	729.8	730.6	731.4	732.1	732.9	732.8
157.5°	738.3	738.3	739.4	740.5	741.5	742.6	743.5	744.3	745.1	746.0	745.9
160°	747.3	747.3	748.0	748.8	749.5	750.3	751.1	751.8	752.6	753.3	753.2
162.5°	754.5	754.5	755.1	755.7	756.5	757.1	758.0	758.8	759.6	760.5	760.4
165°	764.2	764.1	764.5	764.9	765.2	765.6	766.4	767.3	768.3	769.1	769.1
167.5°	771.5	771.3	771.7	772.0	772.4	772.7	773.6	774.5	775.4	776.3	776.1
170°	775.6	775.3	775.6	775.9	776.1	776.3	777.2	778.1	779.0	779.9	779.7
172.5°	778.3	778.1	778.3	778.6	778.8	779.0	780.0	780.9	781.7	782.6	782.4
175°	781.3	781.0	781.3	781.5	781.7	782.0	782.9	783.8	784.7	785.5	785.4
177.5°	782.6	782.3	782.4	782.5	782.6	782.7	783.4	784.1	784.8	785.5	785.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	5.3	5.1	5.1	5.0	5.1	5.1	5.3	5.2	5.1	5.5	5.4
90°	14.6	14.8	15.1	15.3	15.1	14.8	14.6	14.3	13.9	13.2	12.6
92.5°	14.8	15.0	15.1	15.3	15.1	15.0	14.8	14.7	14.4	14.1	13.8
95°	24.7	24.6	24.5	24.4	24.5	24.6	24.7	24.9	24.6	24.0	23.4
97.5°	32.1	32.2	32.4	32.6	32.4	32.2	32.1	31.9	31.6	31.1	30.6
100°	37.2	37.5	37.7	37.9	37.7	37.5	37.2	37.0	36.4	35.3	34.3
102.5°	39.6	40.0	40.3	40.7	40.3	40.0	39.6	39.3	38.4	37.2	35.8
105°	41.6	42.1	42.5	43.1	42.5	42.1	41.6	41.0	40.1	38.7	37.3
107.5°	42.8	43.3	43.8	44.3	43.8	43.3	42.8	42.3	42.8	44.1	45.6
110°	43.3	43.7	44.3	44.8	44.3	43.7	43.3	42.8	48.8	61.4	74.0



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.0	44.4	44.8	45.2	44.8	44.4	44.0	43.6	66.4	112.3	158.3
115°	73.7	64.6	55.5	46.5	55.5	64.6	73.7	82.7	116.5	174.8	233.1
117.5°	279.1	249.3	219.5	189.7	219.5	249.3	279.1	308.9	330.8	344.9	359.1
120°	396.6	379.7	362.7	345.7	362.7	379.7	396.6	413.7	421.4	419.9	418.4
122.5°	441.2	437.9	434.7	431.3	434.7	437.9	441.2	444.6	445.8	444.8	443.9
125°	483.4	483.8	484.1	484.5	484.1	483.8	483.4	483.0	482.4	481.5	480.6
127.5°	517.8	517.9	518.0	518.1	518.0	517.9	517.8	517.8	517.1	515.8	514.5
130°	539.3	539.2	539.0	538.9	539.0	539.2	539.3	539.4	538.8	537.4	536.0
132.5°	559.7	559.6	559.4	559.3	559.4	559.6	559.7	559.8	559.3	558.1	556.9
135°	589.5	589.3	589.0	588.7	589.0	589.3	589.5	589.8	589.3	588.0	586.8
137.5°	617.0	616.5	616.1	615.6	616.1	616.5	617.0	617.3	617.0	615.7	614.5
140°	634.3	633.7	633.0	632.4	633.0	633.7	634.3	634.9	634.7	633.5	632.4
142.5°	650.6	650.0	649.4	648.7	649.4	650.0	650.6	651.3	651.0	650.0	649.0
145°	673.4	672.8	672.2	671.5	672.2	672.8	673.4	674.0	673.9	673.0	672.2
147.5°	693.2	692.6	692.1	691.6	692.1	692.6	693.2	693.7	693.6	693.0	692.3
150°	705.7	705.0	704.4	703.8	704.4	705.0	705.7	706.3	706.2	705.5	704.7
152.5°	716.8	715.9	715.1	714.2	715.1	715.9	716.8	717.6	717.6	716.8	716.1
155°	731.7	730.8	729.8	728.7	729.8	730.8	731.7	732.8	732.9	732.1	731.4
157.5°	745.0	743.9	743.0	742.0	743.0	743.9	745.0	745.9	746.0	745.1	744.3
160°	752.3	751.5	750.6	749.7	750.6	751.5	752.3	753.2	753.3	752.6	751.8
162.5°	759.3	758.2	757.2	756.1	757.2	758.2	759.3	760.4	760.5	759.6	758.8
165°	768.3	767.3	766.4	765.6	766.4	767.3	768.3	769.1	769.1	768.3	767.3
167.5°	775.0	773.9	772.7	771.6	772.7	773.9	775.0	776.1	776.3	775.4	774.5
170°	778.6	777.4	776.3	775.2	776.3	777.4	778.6	779.7	779.9	779.0	778.1
172.5°	781.3	780.2	779.0	777.9	779.0	780.2	781.3	782.4	782.6	781.7	780.9
175°	784.1	782.8	781.6	780.3	781.6	782.8	784.1	785.4	785.5	784.7	783.8
177.5°	784.5	783.6	782.7	781.8	782.7	783.6	784.5	785.4	785.5	784.8	784.1
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	5.2	5.3	5.4	5.4	5.2	5.2	5.2	5.2	5.4	5.4	5.3
90°	12.0	11.3	10.3	9.3	8.3	7.3	6.1	4.8	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.1	11.6	11.2	10.9	11.1	11.2	11.3	11.4
95°	22.7	22.1	21.2	20.4	19.5	18.5	20.2	24.4	28.5	32.7	36.8
97.5°	30.1	29.5	27.6	25.5	23.4	21.4	26.2	37.9	49.7	61.4	73.1
100°	33.3	32.3	30.2	28.0	25.9	23.8	31.3	48.6	65.8	83.0	100.3
102.5°	34.5	33.2	51.1	69.0	86.9	104.8	115.6	119.3	122.9	126.6	130.2
105°	36.0	34.5	68.9	103.3	137.7	172.1	187.4	183.6	179.8	176.0	172.3
107.5°	47.0	48.4	89.6	130.9	172.1	213.3	232.4	229.3	226.3	223.2	220.2
110°	86.6	99.2	135.5	172.0	208.3	244.7	261.6	259.0	256.4	253.7	251.0



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	204.2	250.1	259.1	268.1	277.1	286.1	289.4	287.1	284.7	282.4	280.0
115°	291.4	349.7	346.5	343.3	340.2	337.1	334.4	332.2	330.1	328.0	325.8
117.5°	373.2	387.3	385.1	382.9	380.8	378.6	376.3	373.9	371.5	369.2	366.8
120°	416.8	415.3	413.1	410.8	408.6	406.3	404.3	402.3	400.4	398.5	396.6
122.5°	443.0	442.1	439.7	437.2	434.7	432.2	430.0	428.0	426.0	424.1	422.1
125°	479.7	478.9	476.4	474.0	471.7	469.3	467.2	465.6	464.0	462.3	460.7
127.5°	513.3	511.9	510.2	508.3	506.6	504.8	503.0	501.1	499.4	497.6	495.7
130°	534.6	533.2	531.9	530.4	529.1	527.7	526.0	523.9	522.0	520.0	517.9
132.5°	555.7	554.5	553.2	551.8	550.4	549.0	547.5	545.7	544.1	542.3	540.6
135°	585.5	584.2	583.1	581.9	580.8	579.7	578.1	576.2	574.1	572.1	570.1
137.5°	613.2	612.0	610.7	609.4	608.2	606.9	605.5	604.1	602.7	601.3	599.9
140°	631.3	630.2	628.8	627.4	626.0	624.6	623.4	622.4	621.4	620.4	619.4
142.5°	647.9	646.9	645.3	643.7	642.1	640.6	639.3	638.4	637.5	636.6	635.7
145°	671.3	670.3	668.2	666.1	663.9	661.8	660.8	660.9	661.1	661.2	661.3
147.5°	691.7	691.0	688.9	686.7	684.7	682.5	681.8	682.2	682.7	683.2	683.7
150°	704.0	703.2	701.2	699.2	697.2	695.2	694.6	695.5	696.4	697.3	698.2
152.5°	715.3	714.5	712.6	710.7	708.8	706.9	706.5	707.4	708.4	709.4	710.3
155°	730.6	729.8	728.3	726.8	725.3	723.8	723.7	724.8	725.9	727.1	728.2
157.5°	743.5	742.6	741.5	740.5	739.4	738.3	738.3	739.3	740.2	741.2	742.1
160°	751.1	750.3	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3
162.5°	758.0	757.1	756.5	755.7	755.1	754.5	754.5	755.3	756.1	756.8	757.6
165°	766.4	765.6	765.2	764.9	764.5	764.1	764.2	765.0	765.8	766.5	767.3
167.5°	773.6	772.7	772.4	772.0	771.7	771.3	771.5	772.3	773.0	773.8	774.5
170°	777.2	776.3	776.1	775.9	775.6	775.3	775.6	776.3	777.1	777.8	778.6
172.5°	780.0	779.0	778.8	778.6	778.3	778.1	778.3	779.0	779.8	780.5	781.3
175°	782.9	782.0	781.7	781.5	781.3	781.0	781.3	782.2	783.1	783.9	784.8
177.5°	783.4	782.7	782.6	782.5	782.4	782.3	782.6	783.3	784.0	784.7	785.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.3	7.5	7.8	8.8	8.6	8.8	9.0	9.0	8.9	8.8	8.6
90°	2.0	3.3	4.8	6.1	7.3	8.3	9.3	10.3	11.3	12.0	12.6
92.5°	11.3	11.2	11.1	10.9	11.2	11.6	12.1	12.7	13.2	13.5	13.8
95°	32.7	28.5	24.4	20.2	18.5	19.5	20.4	21.2	22.1	22.7	23.4
97.5°	61.4	49.7	37.9	26.2	21.4	23.4	25.5	27.6	29.5	30.1	30.6
100°	83.0	65.8	48.6	31.3	23.8	25.9	28.0	30.2	32.3	33.3	34.3
102.5°	126.6	122.9	119.3	115.6	104.8	86.9	69.0	51.1	33.2	34.5	35.8
105°	176.0	179.8	183.6	187.4	172.1	137.7	103.3	68.9	34.5	36.0	37.3
107.5°	223.2	226.3	229.3	232.4	213.3	172.1	130.9	89.6	48.4	47.0	45.6
110°	253.7	256.4	259.0	261.6	244.7	208.3	172.0	135.5	99.2	86.6	74.0





TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	282.4	284.7	287.1	289.4	286.1	277.1	268.1	259.1	250.1	204.2	158.3
115°	328.0	330.1	332.2	334.4	337.1	340.2	343.3	346.5	349.7	291.4	233.1
117.5°	369.2	371.5	373.9	376.3	378.6	380.8	382.9	385.1	387.3	373.2	359.1
120°	398.5	400.4	402.3	404.3	406.3	408.6	410.8	413.1	415.3	416.8	418.4
122.5°	424.1	426.0	428.0	430.0	432.2	434.7	437.2	439.7	442.1	443.0	443.9
125°	462.3	464.0	465.6	467.2	469.3	471.7	474.0	476.4	478.9	479.7	480.6
127.5°	497.6	499.4	501.1	503.0	504.8	506.6	508.3	510.2	511.9	513.3	514.5
130°	520.0	522.0	523.9	526.0	527.7	529.1	530.4	531.9	533.2	534.6	536.0
132.5°	542.3	544.1	545.7	547.5	549.0	550.4	551.8	553.2	554.5	555.7	556.9
135°	572.1	574.1	576.2	578.1	579.7	580.8	581.9	583.1	584.2	585.5	586.8
137.5°	601.3	602.7	604.1	605.5	606.9	608.2	609.4	610.7	612.0	613.2	614.5
140°	620.4	621.4	622.4	623.4	624.6	626.0	627.4	628.8	630.2	631.3	632.4
142.5°	636.6	637.5	638.4	639.3	640.6	642.1	643.7	645.3	646.9	647.9	649.0
145°	661.2	661.1	660.9	660.8	661.8	663.9	666.1	668.2	670.3	671.3	672.2
147.5°	683.2	682.7	682.2	681.8	682.5	684.7	686.7	688.9	691.0	691.7	692.3
150°	697.3	696.4	695.5	694.6	695.2	697.2	699.2	701.2	703.2	704.0	704.7
152.5°	709.4	708.4	707.4	706.5	706.9	708.8	710.7	712.6	714.5	715.3	716.1
155°	727.1	725.9	724.8	723.7	723.8	725.3	726.8	728.3	729.8	730.6	731.4
157.5°	741.2	740.2	739.3	738.3	738.3	739.4	740.5	741.5	742.6	743.5	744.3
160°	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	751.1	751.8
162.5°	756.8	756.1	755.3	754.5	754.5	755.1	755.7	756.5	757.1	758.0	758.8
165°	766.5	765.8	765.0	764.2	764.1	764.5	764.9	765.2	765.6	766.4	767.3
167.5°	773.8	773.0	772.3	771.5	771.3	771.7	772.0	772.4	772.7	773.6	774.5
170°	777.8	777.1	776.3	775.6	775.3	775.6	775.9	776.1	776.3	777.2	778.1
172.5°	780.5	779.8	779.0	778.3	778.1	778.3	778.6	778.8	779.0	780.0	780.9
175°	783.9	783.1	782.2	781.3	781.0	781.3	781.5	781.7	782.0	782.9	783.8
177.5°	784.7	784.0	783.3	782.6	782.3	782.4	782.5	782.6	782.7	783.4	784.1
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	9.0	9.2	9.0	9.0	9.3	9.2	9.2
90°	13.2	13.9	14.3	14.6	14.8	15.1	15.3
92.5°	14.1	14.4	14.7	14.8	15.0	15.1	15.3
95°	24.0	24.6	24.9	24.7	24.6	24.5	24.4
97.5°	31.1	31.6	31.9	32.1	32.2	32.4	32.6
100°	35.3	36.4	37.0	37.2	37.5	37.7	37.9
102.5°	37.2	38.4	39.3	39.6	40.0	40.3	40.7
105°	38.7	40.1	41.0	41.6	42.1	42.5	43.1
107.5°	44.1	42.8	42.3	42.8	43.3	43.8	44.3
110°	61.4	48.8	42.8	43.3	43.7	44.3	44.8



TEST NUMBER: P331303-927

CATALOG NUMBER: SA2XXDIP-C485D725U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	112.3	66.4	43.6	44.0	44.4	44.8	45.2
115°	174.8	116.5	82.7	73.7	64.6	55.5	46.5
117.5°	344.9	330.8	308.9	279.1	249.3	219.5	189.7
120°	419.9	421.4	413.7	396.6	379.7	362.7	345.7
122.5°	444.8	445.8	444.6	441.2	437.9	434.7	431.3
125°	481.5	482.4	483.0	483.4	483.8	484.1	484.5
127.5°	515.8	517.1	517.8	517.8	517.9	518.0	518.1
130°	537.4	538.8	539.4	539.3	539.2	539.0	538.9
132.5°	558.1	559.3	559.8	559.7	559.6	559.4	559.3
135°	588.0	589.3	589.8	589.5	589.3	589.0	588.7
137.5°	615.7	617.0	617.3	617.0	616.5	616.1	615.6
140°	633.5	634.7	634.9	634.3	633.7	633.0	632.4
142.5°	650.0	651.0	651.3	650.6	650.0	649.4	648.7
145°	673.0	673.9	674.0	673.4	672.8	672.2	671.5
147.5°	693.0	693.6	693.7	693.2	692.6	692.1	691.6
150°	705.5	706.2	706.3	705.7	705.0	704.4	703.8
152.5°	716.8	717.6	717.6	716.8	715.9	715.1	714.2
155°	732.1	732.9	732.8	731.7	730.8	729.8	728.7
157.5°	745.1	746.0	745.9	745.0	743.9	743.0	742.0
160°	752.6	753.3	753.2	752.3	751.5	750.6	749.7
162.5°	759.6	760.5	760.4	759.3	758.2	757.2	756.1
165°	768.3	769.1	769.1	768.3	767.3	766.4	765.6
167.5°	775.4	776.3	776.1	775.0	773.9	772.7	771.6
170°	779.0	779.9	779.7	778.6	777.4	776.3	775.2
172.5°	781.7	782.6	782.4	781.3	780.2	779.0	777.9
175°	784.7	785.5	785.4	784.1	782.8	781.6	780.3
177.5°	784.8	785.5	785.4	784.5	783.6	782.7	781.8
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2

(END OF REPORT)