

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333552

Luminaire Tested: **S125RDIP-S850D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333552  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D365U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4592.7 lumens  
Efficiency: N/A  
Efficacy: 131.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	76	76	76	71		
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	65	65	65	65	65	65	65	61		
2	94	87	81	76	89	83	77	73	75	71	67	67	64	61	61	58	56	56	56	56	56	56	56	52		
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	51	48	48	48	48	48	48	48	45		
4	79	69	61	55	75	65	58	53	59	54	49	54	49	45	49	45	42	42	42	42	42	42	42	39		
5	73	61	53	47	69	59	51	46	53	47	43	49	44	40	44	40	37	37	37	37	37	37	37	34		
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	33	33	33	33	33	33	33	30		
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	37	32	29	29	29	29	29	29	29	27		
8	58	46	38	32	55	44	37	32	40	34	30	37	32	28	34	29	26	26	26	26	26	26	26	24		
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24	24	24	24	24	24	24	22		
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	25	21	21	21	21	21	21	21	20		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	2.6
10°-20°	355.5	7.7
20°-30°	563.6	12.3
30°-40°	679.7	14.8
40°-50°	607.0	13.2
50°-60°	465.5	10.1
60°-70°	302.5	6.6
70°-80°	147.1	3.2
80°-90°	36.1	0.8
90°-100°	127.1	2.8
100°-110°	273.1	5.9
110°-120°	256.3	5.6
120°-130°	207.7	4.5
130°-140°	166.7	3.6
140°-150°	125.8	2.7
150°-160°	88.6	1.9
160°-170°	52.2	1.1
170°-180°	17.0	0.4
0°-30°	1040.4	22.7
0°-40°	1720.1	37.5
0°-60°	2792.5	60.8
0°-90°	3278.1	71.4
90°-120°	656.5	14.3
90°-150°	1156.8	25.2
90°-180°	1315.0	28.6
0°-180°	4592.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	8	0	8	0	8	7
95°	83	12	83	12	83	118
105°	468	40	468	40	468	465
115°	522	71	522	71	522	510
125°	411	99	411	99	411	372
135°	341	116	341	116	341	265
145°	269	135	269	135	269	171
155°	226	154	226	154	226	105
165°	198	168	198	168	198	57
175°	178	175	178	175	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	10.8	10.3	9.9	9.9	10.3	11.0	10.5	10.0	9.9	9.9	10.1
90°	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4	6.0	5.7	4.9
92.5°	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6	92.2	113.9	115.8
95°	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1	306.4	313.1	255.5
97.5°	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4	387.7	334.4	228.2
100°	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7	407.5	319.1	203.6
102.5°	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6	395.6	292.3	184.9
105°	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5	357.7	256.2	166.8
107.5°	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6	318.9	231.4	159.2
110°	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2	296.9	219.8	156.9



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0	280.5	213.0	156.9
115°	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9	262.6	205.7	158.0
117.5°	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1	251.9	202.1	160.3
120°	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9	246.0	200.4	162.6
122.5°	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3	240.9	199.0	164.5
125°	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2	234.0	197.2	167.9
127.5°	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9	227.6	196.4	171.6
130°	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8	223.4	195.8	173.9
132.5°	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7	220.0	195.8	176.4
135°	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6	215.9	195.8	179.9
137.5°	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8	212.3	196.2	183.1
140°	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5	210.6	196.5	184.5
142.5°	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9	209.2	196.8	185.3
145°	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1	207.1	196.5	186.2
147.5°	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5	204.9	195.6	186.6
150°	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0	203.2	194.7	186.6
152.5°	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2	201.2	193.6	186.3
155°	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9	197.9	191.6	185.5
157.5°	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7	194.8	189.4	184.6
160°	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9	192.3	188.0	183.8
162.5°	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7	190.0	186.3	182.9
165°	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4	186.6	183.8	181.7
167.5°	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3	183.3	181.3	179.7
170°	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1	181.3	179.9	178.8
172.5°	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5	179.3	178.2	177.7
175°	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8	176.7	176.4	176.4
177.5°	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9	175.6	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	10.5	10.3	10.7	10.5	10.0	11.9	13.0	13.4	12.6	11.9	11.2
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3	5.2	8.2	12.6
95°	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7	12.0	14.8	18.7
97.5°	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4	19.8	21.8	25.7
100°	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7	25.4	26.9	30.7
102.5°	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7	31.1	32.2	36.4
105°	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9	39.9	41.7	45.2
107.5°	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0	49.7	51.4	54.3
110°	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5	56.2	57.6	60.8





TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0	62.7	63.8	67.0
115°	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4	72.1	73.2	76.3
117.5°	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9	80.9	82.1	85.2
120°	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5	86.6	88.0	91.2
122.5°	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5	92.2	93.4	96.6
125°	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0	99.7	101.4	104.6
127.5°	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8	105.9	108.1	112.2
130°	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5	109.6	112.4	117.0
132.5°	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3	112.7	116.1	121.2
135°	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9	117.3	121.6	127.2
137.5°	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7	122.8	126.7	132.4
140°	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1	126.2	130.4	136.1
142.5°	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1	129.8	133.8	139.5
145°	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0	135.7	139.2	144.2
147.5°	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2	141.6	144.7	149.3
150°	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9	145.6	148.1	152.7
152.5°	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9	149.3	151.5	155.5
155°	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1	154.1	156.2	159.7
157.5°	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8	158.7	160.4	163.4
160°	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9	161.5	162.9	165.4
162.5°	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4	164.1	165.5	167.7
165°	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2	167.5	168.6	170.3
167.5°	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8	170.4	171.1	172.0
170°	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5	172.1	172.5	173.2
172.5°	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6	173.0	173.3	174.0
175°	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9	174.2	174.6	174.9
177.5°	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.0	175.0	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	11.0	11.1	10.7	11.7	10.5	11.1	11.2	10.8	10.9	11.0	10.7
90°	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4	6.7	7.1	7.8
92.5°	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6	45.4	34.2	29.0
95°	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1	200.4	156.9	127.2
97.5°	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4	340.8	298.4	257.1
100°	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7	417.4	381.0	344.2
102.5°	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6	464.3	446.9	422.0
105°	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5	490.9	506.4	502.6
107.5°	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6	467.2	507.1	525.6
110°	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2	440.4	490.2	520.2



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0	413.8	464.2	499.6
115°	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9	375.7	424.1	462.6
117.5°	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1	349.3	391.0	426.4
120°	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9	334.3	373.2	404.3
122.5°	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3	323.6	358.2	387.3
125°	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2	309.2	340.0	365.4
127.5°	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9	295.5	324.2	348.0
130°	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8	285.9	313.5	336.5
132.5°	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7	276.9	301.9	324.0
135°	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6	262.9	285.6	305.7
137.5°	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8	250.5	269.3	286.4
140°	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5	243.1	259.4	274.2
142.5°	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9	236.9	250.9	263.8
145°	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1	229.0	240.0	249.5
147.5°	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5	222.4	230.9	238.1
150°	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0	218.8	225.5	231.8
152.5°	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2	215.1	221.2	226.2
155°	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9	209.6	214.5	218.4
157.5°	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7	204.3	208.2	211.2
160°	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9	200.4	203.9	206.4
162.5°	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7	197.0	200.0	202.2
165°	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4	191.9	194.0	195.8
167.5°	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3	187.0	188.6	189.9
170°	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1	184.1	185.2	185.9
172.5°	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5	181.6	182.4	182.8
175°	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8	177.8	178.5	178.5
177.5°	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9	176.1	176.1	176.1
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	11.1	10.7	10.8	10.8	10.8	10.7	11.1	10.7	11.0	10.9	10.8
90°	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4
92.5°	24.5	23.6	23.1	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6
95°	102.1	91.5	88.7	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1
97.5°	235.3	215.5	205.3	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4
100°	319.8	294.4	281.3	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7
102.5°	395.9	377.8	363.6	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6
105°	491.2	479.6	472.5	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5
107.5°	531.3	531.3	528.9	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6
110°	536.1	542.8	545.3	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.8	534.4	540.5	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0
115°	490.2	507.1	517.0	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9
117.5°	453.9	471.5	481.3	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1
120°	430.5	447.4	457.0	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9
122.5°	410.7	426.2	435.8	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3
125°	385.2	399.7	407.5	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2
127.5°	366.0	378.8	386.1	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9
130°	354.1	365.8	372.9	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8
132.5°	341.7	353.3	359.8	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7
135°	321.3	332.9	339.3	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6
137.5°	300.3	310.9	316.8	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8
140°	287.3	296.5	301.8	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5
142.5°	274.9	282.7	287.7	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9
145°	258.0	264.0	267.9	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1
147.5°	244.8	249.6	251.8	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5
150°	237.1	241.4	242.8	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0
152.5°	230.6	234.0	235.4	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2
155°	221.9	224.4	225.5	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9
157.5°	214.0	216.0	217.0	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7
160°	208.9	210.6	211.3	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9
162.5°	204.1	205.5	205.7	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7
165°	197.2	197.9	197.9	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4
167.5°	190.6	191.2	190.9	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3
170°	186.6	187.0	187.0	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1
172.5°	182.9	183.6	183.0	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5
175°	178.5	178.8	178.1	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8
177.5°	175.9	176.1	175.3	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	11.2	11.1	10.5	11.7	10.7	11.1	11.0	11.2	11.9	12.6	13.4
90°	6.0	5.7	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	92.2	113.9	115.8	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3
95°	306.4	313.1	255.5	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7
97.5°	387.7	334.4	228.2	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4
100°	407.5	319.1	203.6	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7
102.5°	395.6	292.3	184.9	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7
105°	357.7	256.2	166.8	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9
107.5°	318.9	231.4	159.2	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0
110°	296.9	219.8	156.9	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.5	213.0	156.9	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0
115°	262.6	205.7	158.0	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4
117.5°	251.9	202.1	160.3	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9
120°	246.0	200.4	162.6	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5
122.5°	240.9	199.0	164.5	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5
125°	234.0	197.2	167.9	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0
127.5°	227.6	196.4	171.6	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8
130°	223.4	195.8	173.9	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5
132.5°	220.0	195.8	176.4	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3
135°	215.9	195.8	179.9	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9
137.5°	212.3	196.2	183.1	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7
140°	210.6	196.5	184.5	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1
142.5°	209.2	196.8	185.3	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1
145°	207.1	196.5	186.2	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0
147.5°	204.9	195.6	186.6	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2
150°	203.2	194.7	186.6	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9
152.5°	201.2	193.6	186.3	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9
155°	197.9	191.6	185.5	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1
157.5°	194.8	189.4	184.6	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8
160°	192.3	188.0	183.8	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9
162.5°	190.0	186.3	182.9	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4
165°	186.6	183.8	181.7	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2
167.5°	183.3	181.3	179.7	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8
170°	181.3	179.9	178.8	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5
172.5°	179.3	178.2	177.7	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6
175°	176.7	176.4	176.4	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9
177.5°	175.6	175.3	175.3	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.0	11.9	10.0	10.5	10.7	10.3	10.5	10.1	9.9	9.9	10.0
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4
92.5°	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6
95°	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1
97.5°	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4
100°	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7
102.5°	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6
105°	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5
107.5°	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6
110°	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2





TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0
115°	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9
117.5°	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1
120°	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9
122.5°	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3
125°	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2
127.5°	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9
130°	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8
132.5°	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7
135°	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6
137.5°	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8
140°	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5
142.5°	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9
145°	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1
147.5°	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5
150°	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0
152.5°	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2
155°	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9
157.5°	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7
160°	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9
162.5°	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7
165°	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4
167.5°	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3
170°	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1
172.5°	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5
175°	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8
177.5°	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	10.5	11.0	10.3	9.9	9.9	10.3	10.8
90°	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333552

CATALOG NUMBER: S125RDIP-S850D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)