

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331313-927

Luminaire Tested: **SA2XXDIP-C485D925U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331313-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4321.6 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331313-927
CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	42	41	40	34				
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29				
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25				
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	28	26	22				
5	67	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19				
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20	17				
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15				
8	53	42	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16	14				
9	50	38	31	26	45	35	29	24	29	24	21	24	21	18	19	17	15	13				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.7
10°-20°	213.1	4.9
20°-30°	309.3	7.2
30°-40°	326.4	7.6
40°-50°	289.0	6.7
50°-60°	230.6	5.3
60°-70°	156.8	3.6
70°-80°	80.4	1.9
80°-90°	23.1	0.5
90°-100°	59.4	1.4
100°-110°	184.4	4.3
110°-120°	315.1	7.3
120°-130°	414.4	9.6
130°-140°	465.2	10.8
140°-150°	456.1	10.6
150°-160°	382.5	8.9
160°-170°	253.7	5.9
170°-180°	88.7	2.1
0°-30°	595.8	13.8
0°-40°	922.2	21.3
0°-60°	1441.8	33.4
0°-90°	1702.1	39.4
90°-120°	558.9	12.9
90°-150°	1894.5	43.8
90°-180°	2620.0	60.6
0°-180°	4321.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	27	1	27	1	27	12
95°	49	41	49	41	49	55
105°	176	170	176	170	176	185
115°	316	316	316	316	316	312
125°	462	460	462	460	462	412
135°	602	595	602	595	602	464
145°	730	722	730	722	730	456
155°	832	826	832	826	832	383
165°	900	899	900	899	900	254
175°	932	935	932	935	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	11.6	11.5	11.7	11.4	11.4	11.6	11.7	11.6	11.9	12.2	11.6
90°	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9	27.3	27.6	23.8
92.5°	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3	25.2	25.1	24.2
95°	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6	50.6	50.6	50.2
97.5°	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1	85.1	85.1	84.4
100°	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1	109.1	109.1	108.6
102.5°	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3	135.1	135.1	134.4
105°	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6	174.3	173.9	173.6
107.5°	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1	216.9	216.7	216.7
110°	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7	275.2	275.6	275.8
115°	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0	319.2	319.4	319.7
117.5°	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9	362.3	362.7	363.7
120°	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5	390.5	390.5	392.0
122.5°	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0	420.5	420.9	421.9
125°	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8	464.3	464.9	465.4
127.5°	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3	506.9	507.6	508.2
130°	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3	535.7	536.0	536.4
132.5°	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6	564.4	565.1	565.0
135°	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2	605.4	605.5	605.2
137.5°	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2	645.3	645.4	645.0
140°	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0	672.0	672.0	671.1
142.5°	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3	696.2	696.0	695.4
145°	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2	733.0	732.8	731.8
147.5°	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6	765.2	764.8	764.1
150°	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1	784.3
152.5°	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3	804.4
155°	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7	831.8	830.8	830.4
157.5°	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7	855.5	854.3	854.0
160°	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9	869.9	868.8	868.6
162.5°	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8	882.6	881.5	881.3
165°	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6	899.3	898.1	898.1
167.5°	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3	913.1	911.8	911.9
170°	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9	920.7	919.4	919.6
172.5°	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6	926.4	925.1	925.3
175°	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7	932.5	931.3	931.6
177.5°	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9	935.2
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	11.1	10.3	9.5	9.4	8.3	7.8	6.5	5.4	5.5	5.7	5.7
90°	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1	15.6	17.2	18.7
95°	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1	42.9	44.6	46.3
97.5°	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1	76.7	78.2	79.8
100°	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4	101.8	103.2	104.6
102.5°	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0	128.1	129.2	130.3
105°	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0	170.5	171.0	171.6
107.5°	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3	214.0	214.8	215.6
110°	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1	242.2	243.2	244.3



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5	272.5	273.6	274.6
115°	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2	317.3	318.3	319.4
117.5°	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8	362.2	363.6	365.0
120°	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	392.0	393.3	394.7
122.5°	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7	419.4	421.1	422.8
125°	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1	461.7	463.3	464.9
127.5°	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4	503.4	505.4	507.4
130°	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3	529.6	531.9	534.2
132.5°	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4	558.3	560.2	562.0
135°	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3	597.2	599.1	601.1
137.5°	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3	637.8	639.4	641.0
140°	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9	662.5	664.1	665.7
142.5°	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2	687.8	689.4	690.9
145°	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5	723.8	725.0	726.3
147.5°	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9	756.5	758.0	759.4
150°	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1	778.2	779.2	780.3
152.5°	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7	797.8	798.8	799.9
155°	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2	826.6	827.2	827.8
157.5°	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3	851.6	852.0	852.3
160°	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5	866.8	867.1	867.5
162.5°	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4	880.4	880.5	880.6
165°	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9	898.7	898.5	898.3
167.5°	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3	913.9	913.3	912.8
170°	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6	922.0	921.5	921.0
172.5°	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3	927.7	927.2	926.7
175°	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3	934.7	934.1	933.7
177.5°	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1	937.6	937.2	936.8
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	5.9	6.3	6.7	7.5	8.1	8.6	8.3	8.2	8.2	7.6	7.6
90°	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9	26.6	26.3	26.1
92.5°	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3	25.3	25.4	25.5
95°	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6	50.6	50.6	50.4
97.5°	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1	85.1	85.1	85.1
100°	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1	109.1	109.1	109.0
102.5°	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3	135.5	135.6	135.5
105°	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6	175.0	175.3	175.5
107.5°	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1	217.2	217.3	217.0
110°	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.6



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7	274.3	273.9	273.5
115°	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0	318.9	318.7	318.3
117.5°	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9	361.5	361.0	360.5
120°	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5	390.5	390.5	390.3
122.5°	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0	419.6	419.2	418.8
125°	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8	463.3	462.7	462.4
127.5°	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3	505.6	505.0	504.4
130°	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3	535.0	534.6	534.1
132.5°	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6	562.8	562.0	561.3
135°	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2	605.1	604.8	604.5
137.5°	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2	645.0	644.8	644.4
140°	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0	672.0	672.0	671.6
142.5°	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3	696.4	696.6	696.3
145°	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2	733.4	733.6	733.3
147.5°	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6	766.0	766.4	766.2
150°	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1	786.6	787.1	787.1
152.5°	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6	807.2	807.9	807.9
155°	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7	833.5	834.4	834.6
157.5°	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7	857.9	859.0	859.2
160°	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9	872.0	873.1	873.2
162.5°	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8	885.0	886.2	886.5
165°	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6	901.7	903.0	903.2
167.5°	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3	915.5	916.7	916.9
170°	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9	923.1	924.3	924.4
172.5°	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6	928.8	930.0	930.1
175°	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7	934.9	936.2	936.3
177.5°	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6	937.5	938.3	938.3
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	7.6	7.4	7.4	7.3	7.4	7.4	7.6	7.6	7.6	8.2	8.2
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9
92.5°	25.5	25.5	25.6	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3
95°	50.1	49.7	49.4	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6
97.5°	85.0	85.0	84.9	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1
100°	108.8	108.7	108.4	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1
102.5°	135.4	135.2	135.1	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3
105°	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6
107.5°	216.2	215.4	214.6	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1
110°	245.1	244.5	244.0	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.1	272.7	272.4	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7
115°	317.8	317.3	316.7	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0
117.5°	360.0	359.5	358.9	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9
120°	389.8	389.2	388.7	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5
122.5°	418.4	418.0	417.6	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0
125°	462.2	462.0	461.8	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8
127.5°	503.8	503.3	502.7	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3
130°	533.4	532.7	532.0	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3
132.5°	560.8	560.2	559.7	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6
135°	604.0	603.5	602.9	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2
137.5°	643.7	643.0	642.3	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2
140°	670.9	670.2	669.6	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0
142.5°	695.6	694.9	694.2	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3
145°	732.6	731.9	731.2	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2
147.5°	765.6	764.9	764.2	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6
150°	786.6	786.1	785.5	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1
152.5°	807.2	806.6	806.0	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6
155°	834.0	833.5	833.0	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7
157.5°	858.4	857.5	856.7	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7
160°	872.5	871.8	871.1	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9
162.5°	885.6	884.7	883.9	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8
165°	902.3	901.4	900.6	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6
167.5°	916.0	915.0	914.2	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3
170°	923.4	922.3	921.2	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9
172.5°	929.1	928.0	926.9	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6
175°	935.3	934.1	933.1	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7
177.5°	937.5	936.6	935.7	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	8.3	8.6	8.1	7.5	6.7	6.3	5.9	5.7	5.7	5.5	5.4
90°	27.3	27.6	23.8	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.2	25.1	24.2	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1
95°	50.6	50.6	50.2	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1
97.5°	85.1	85.1	84.4	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1
100°	109.1	109.1	108.6	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4
102.5°	135.1	135.1	134.4	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0
105°	174.3	173.9	173.6	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0
107.5°	216.9	216.7	216.7	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3
110°	245.9	245.9	245.9	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.2	275.6	275.8	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5
115°	319.2	319.4	319.7	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2
117.5°	362.3	362.7	363.7	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8
120°	390.5	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5
122.5°	420.5	420.9	421.9	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7
125°	464.3	464.9	465.4	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1
127.5°	506.9	507.6	508.2	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4
130°	535.7	536.0	536.4	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3
132.5°	564.4	565.1	565.0	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4
135°	605.4	605.5	605.2	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3
137.5°	645.3	645.4	645.0	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3
140°	672.0	672.0	671.1	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9
142.5°	696.2	696.0	695.4	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2
145°	733.0	732.8	731.8	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5
147.5°	765.2	764.8	764.1	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9
150°	785.5	785.1	784.3	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1
152.5°	806.0	805.3	804.4	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7
155°	831.8	830.8	830.4	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2
157.5°	855.5	854.3	854.0	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3
160°	869.9	868.8	868.6	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5
162.5°	882.6	881.5	881.3	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4
165°	899.3	898.1	898.1	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9
167.5°	913.1	911.8	911.9	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3
170°	920.7	919.4	919.6	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6
172.5°	926.4	925.1	925.3	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3
175°	932.5	931.3	931.6	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3
177.5°	935.7	934.9	935.2	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.5	7.8	8.3	9.4	9.5	10.3	11.1	11.6	12.2	11.9	11.6
90°	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9
92.5°	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3
95°	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6
97.5°	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1
100°	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1
102.5°	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3
105°	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6
107.5°	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1
110°	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7
115°	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0
117.5°	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9
120°	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5
122.5°	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0
125°	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8
127.5°	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3
130°	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3
132.5°	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6
135°	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2
137.5°	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2
140°	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0
142.5°	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3
145°	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2
147.5°	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6
150°	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1
152.5°	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6
155°	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7
157.5°	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7
160°	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9
162.5°	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8
165°	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6
167.5°	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3
170°	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9
172.5°	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6
175°	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7
177.5°	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	11.7	11.6	11.4	11.4	11.7	11.5	11.6
90°	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.6	245.1	244.5	244.0	243.5



TEST NUMBER: P331313-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)