

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331367-927

Luminaire Tested: **SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331367-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5374.8 lumens  
Efficiency: N/A  
Efficacy: 94.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331367-927  
CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	51	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	39	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.2	1.9
10°-20°	291.3	5.4
20°-30°	422.8	7.9
30°-40°	446.2	8.3
40°-50°	395.0	7.3
50°-60°	315.3	5.9
60°-70°	214.3	4.0
70°-80°	109.9	2.0
80°-90°	30.8	0.6
90°-100°	69.1	1.3
100°-110°	214.6	4.0
110°-120°	366.8	6.8
120°-130°	482.4	9.0
130°-140°	541.4	10.1
140°-150°	530.9	9.9
150°-160°	445.3	8.3
160°-170°	295.3	5.5
170°-180°	103.2	1.9
0°-30°	814.3	15.2
0°-40°	1260.5	23.5
0°-60°	1970.8	36.7
0°-90°	2325.8	43.3
90°-120°	650.5	12.1
90°-150°	2205.2	41.0
90°-180°	3049.0	56.7
0°-180°	5374.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	25
90°	31	1	31	1	31	15
95°	57	48	57	48	57	64
105°	204	198	204	198	204	215
115°	368	368	368	368	368	363
125°	537	536	537	536	537	479
135°	701	693	701	693	701	540
145°	850	841	850	841	850	531
155°	969	962	969	962	969	446
165°	1047	1046	1047	1046	1047	295
175°	1085	1089	1085	1089	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	14.7	14.7	14.9	14.6	14.5	14.8	14.9	14.7	15.1	15.5	14.9
90°	31.3	31.1	30.9	30.7	30.5	30.6	31.0	31.4	31.8	32.2	27.7
92.5°	29.8	29.8	29.7	29.7	29.6	29.6	29.5	29.4	29.3	29.2	28.2
95°	57.0	57.4	57.9	58.3	58.7	58.9	58.9	58.9	58.9	58.9	58.5
97.5°	98.9	98.9	98.9	98.9	99.0	99.0	99.0	99.0	99.0	99.0	98.2
100°	126.0	126.3	126.5	126.7	126.9	127.0	127.0	127.0	127.0	127.0	126.4
102.5°	157.0	157.2	157.4	157.6	157.8	157.8	157.6	157.5	157.3	157.2	156.4
105°	204.3	204.3	204.3	204.3	204.3	204.1	203.7	203.3	202.9	202.4	202.0
107.5°	248.8	249.8	250.7	251.7	252.5	252.9	252.8	252.6	252.5	252.3	252.3
110°	283.4	284.0	284.6	285.3	285.9	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.6	317.0	317.4	317.9	318.4	318.9	319.3	319.8	320.3	320.8	320.9
115°	368.0	368.7	369.3	369.9	370.5	370.9	371.1	371.4	371.5	371.8	372.2
117.5°	417.2	417.8	418.4	419.1	419.7	420.3	420.7	421.2	421.7	422.2	423.3
120°	451.8	452.4	453.0	453.7	454.2	454.6	454.6	454.6	454.6	454.6	456.2
122.5°	485.7	486.2	486.6	487.0	487.5	487.9	488.5	488.9	489.4	489.9	491.1
125°	537.4	537.6	537.8	538.0	538.2	538.6	539.2	539.9	540.4	541.1	541.7
127.5°	584.5	585.2	585.8	586.5	587.1	587.8	588.5	589.3	590.0	590.7	591.5
130°	618.4	619.2	620.0	620.8	621.6	622.3	622.7	623.1	623.4	623.9	624.3
132.5°	650.8	651.4	652.0	652.8	653.4	654.2	655.1	655.9	656.9	657.7	657.7
135°	701.2	701.8	702.4	703.0	703.6	704.0	704.3	704.5	704.6	704.9	704.5
137.5°	746.8	747.7	748.5	749.2	750.1	750.6	750.8	750.9	751.1	751.2	750.7
140°	778.5	779.3	780.1	780.9	781.7	782.1	782.1	782.1	782.1	782.1	781.2
142.5°	807.2	808.0	808.8	809.6	810.5	810.8	810.6	810.5	810.3	810.2	809.5
145°	850.2	851.0	851.9	852.7	853.5	853.8	853.7	853.4	853.2	853.0	851.8
147.5°	888.7	889.5	890.3	891.0	891.8	892.0	891.5	891.1	890.7	890.2	889.4
150°	913.8	914.3	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8	912.9
152.5°	937.3	938.1	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3	936.4
155°	968.9	969.6	970.2	970.8	971.4	971.2	970.2	969.2	968.1	967.1	966.5
157.5°	996.2	997.2	998.1	999.1	1000.1	999.9	998.5	997.1	995.8	994.3	994.0
160°	1013.1	1013.9	1014.8	1015.6	1016.4	1016.2	1014.9	1013.8	1012.5	1011.3	1011.1
162.5°	1027.9	1028.8	1029.8	1030.8	1031.7	1031.6	1030.2	1028.8	1027.4	1026.0	1025.8
165°	1047.2	1048.2	1049.2	1050.3	1051.2	1051.1	1049.6	1048.2	1046.8	1045.4	1045.4
167.5°	1063.0	1064.1	1065.1	1066.2	1067.2	1067.1	1065.6	1064.2	1062.8	1061.4	1061.4
170°	1071.1	1072.3	1073.6	1074.8	1076.0	1075.9	1074.4	1073.0	1071.6	1070.2	1070.4
172.5°	1077.7	1079.0	1080.1	1081.4	1082.6	1082.5	1081.1	1079.7	1078.2	1076.8	1077.0
175°	1084.9	1086.2	1087.3	1088.6	1089.8	1089.7	1088.3	1086.9	1085.4	1083.9	1084.4
177.5°	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2	1088.5
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	14.3	13.5	12.5	12.5	11.0	10.5	8.8	7.3	7.4	7.6	7.4
90°	23.2	18.7	14.2	10.8	8.3	5.9	3.4	1.0	3.4	5.9	8.3
92.5°	27.2	26.1	25.0	23.6	21.8	20.0	18.1	16.4	18.1	20.0	21.8
95°	58.1	57.7	57.3	56.0	53.9	52.0	49.9	47.8	49.9	52.0	53.9
97.5°	97.4	96.6	95.9	94.6	92.8	91.0	89.2	87.5	89.2	91.0	92.8
100°	125.7	125.2	124.5	123.4	121.8	120.2	118.5	116.8	118.5	120.2	121.8
102.5°	155.6	154.9	154.1	153.0	151.7	150.4	149.1	147.8	149.1	150.4	151.7
105°	201.6	201.2	200.8	200.3	199.7	199.1	198.4	197.8	198.4	199.1	199.7
107.5°	252.3	252.3	252.3	251.8	251.0	250.1	249.1	248.3	249.1	250.1	251.0
110°	286.2	286.2	286.2	285.6	284.3	283.1	281.9	280.7	281.9	283.1	284.3





TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	321.1	321.2	321.5	320.9	319.6	318.5	317.2	316.0	317.2	318.5	319.6
115°	372.6	373.0	373.4	373.0	371.8	370.5	369.3	368.0	369.3	370.5	371.8
117.5°	424.5	425.6	426.7	426.5	424.8	423.3	421.6	419.9	421.6	423.3	424.8
120°	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	456.2	457.9	459.5
122.5°	492.2	493.4	494.5	494.1	492.1	490.1	488.2	486.2	488.2	490.1	492.1
125°	542.3	542.9	543.5	542.9	541.1	539.2	537.4	535.5	537.4	539.2	541.1
127.5°	592.2	592.9	593.7	592.9	590.6	588.3	585.9	583.6	585.9	588.3	590.6
130°	624.7	625.1	625.5	624.4	621.7	619.1	616.4	613.8	616.4	619.1	621.7
132.5°	657.6	657.5	657.4	656.3	654.1	652.0	649.8	647.6	649.8	652.0	654.1
135°	704.0	703.6	703.2	701.9	699.7	697.4	695.1	692.9	695.1	697.4	699.7
137.5°	750.2	749.6	749.1	747.9	746.1	744.3	742.4	740.5	742.4	744.3	746.1
140°	780.1	779.1	778.1	776.7	774.8	772.9	771.1	769.3	771.1	772.9	774.8
142.5°	808.7	808.0	807.3	806.0	804.2	802.4	800.6	798.8	800.6	802.4	804.2
145°	850.6	849.3	848.1	846.8	845.3	843.9	842.5	841.1	842.5	843.9	845.3
147.5°	888.6	887.7	886.9	885.7	883.9	882.2	880.5	878.8	880.5	882.2	883.9
150°	912.1	911.3	910.5	909.4	908.2	907.0	905.8	904.5	905.8	907.0	908.2
152.5°	935.3	934.4	933.3	932.2	931.1	929.8	928.6	927.3	928.6	929.8	931.1
155°	965.9	965.3	964.6	964.1	963.5	962.8	962.2	961.6	962.2	962.8	963.5
157.5°	993.6	993.2	992.8	992.5	992.0	991.7	991.3	990.9	991.3	991.7	992.0
160°	1010.9	1010.7	1010.4	1010.2	1009.7	1009.3	1008.9	1008.5	1008.9	1009.3	1009.7
162.5°	1025.6	1025.4	1025.2	1025.1	1024.9	1024.8	1024.8	1024.7	1024.8	1024.8	1024.9
165°	1045.4	1045.4	1045.4	1045.4	1045.6	1045.8	1046.1	1046.2	1046.1	1045.8	1045.6
167.5°	1061.4	1061.4	1061.5	1061.8	1062.5	1063.0	1063.7	1064.3	1063.7	1063.0	1062.5
170°	1070.6	1070.8	1071.0	1071.4	1072.0	1072.6	1073.2	1073.9	1073.2	1072.6	1072.0
172.5°	1077.2	1077.4	1077.6	1078.0	1078.6	1079.3	1079.9	1080.5	1079.9	1079.3	1078.6
175°	1084.8	1085.2	1085.6	1086.2	1086.7	1087.3	1088.0	1088.6	1088.0	1087.3	1086.7
177.5°	1088.9	1089.2	1089.5	1090.0	1090.4	1090.9	1091.4	1091.9	1091.4	1090.9	1090.4
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	7.7	8.0	8.6	9.5	10.1	10.6	10.2	10.1	10.1	9.3	9.3
90°	10.8	14.2	18.7	23.2	27.7	32.2	31.8	31.4	31.0	30.6	30.5
92.5°	23.6	25.0	26.1	27.2	28.2	29.2	29.3	29.4	29.5	29.6	29.6
95°	56.0	57.3	57.7	58.1	58.5	58.9	58.9	58.9	58.9	58.9	58.7
97.5°	94.6	95.9	96.6	97.4	98.2	99.0	99.0	99.0	99.0	99.0	99.0
100°	123.4	124.5	125.2	125.7	126.4	127.0	127.0	127.0	127.0	127.0	126.9
102.5°	153.0	154.1	154.9	155.6	156.4	157.2	157.3	157.5	157.6	157.8	157.8
105°	200.3	200.8	201.2	201.6	202.0	202.4	202.9	203.3	203.7	204.1	204.3
107.5°	251.8	252.3	252.3	252.3	252.3	252.3	252.5	252.6	252.8	252.9	252.5
110°	285.6	286.2	286.2	286.2	286.2	286.2	286.2	286.2	286.2	286.2	285.9



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	320.9	321.5	321.2	321.1	320.9	320.8	320.3	319.8	319.3	318.9	318.4
115°	373.0	373.4	373.0	372.6	372.2	371.8	371.5	371.4	371.1	370.9	370.5
117.5°	426.5	426.7	425.6	424.5	423.3	422.2	421.7	421.2	420.7	420.3	419.7
120°	461.1	461.1	459.5	457.9	456.2	454.6	454.6	454.6	454.6	454.6	454.2
122.5°	494.1	494.5	493.4	492.2	491.1	489.9	489.4	488.9	488.5	487.9	487.5
125°	542.9	543.5	542.9	542.3	541.7	541.1	540.4	539.9	539.2	538.6	538.2
127.5°	592.9	593.7	592.9	592.2	591.5	590.7	590.0	589.3	588.5	587.8	587.1
130°	624.4	625.5	625.1	624.7	624.3	623.9	623.4	623.1	622.7	622.3	621.6
132.5°	656.3	657.4	657.5	657.6	657.7	657.7	656.9	655.9	655.1	654.2	653.4
135°	701.9	703.2	703.6	704.0	704.5	704.9	704.6	704.5	704.3	704.0	703.6
137.5°	747.9	749.1	749.6	750.2	750.7	751.2	751.1	750.9	750.8	750.6	750.1
140°	776.7	778.1	779.1	780.1	781.2	782.1	782.1	782.1	782.1	782.1	781.7
142.5°	806.0	807.3	808.0	808.7	809.5	810.2	810.3	810.5	810.6	810.8	810.5
145°	846.8	848.1	849.3	850.6	851.8	853.0	853.2	853.4	853.7	853.8	853.5
147.5°	885.7	886.9	887.7	888.6	889.4	890.2	890.7	891.1	891.5	892.0	891.8
150°	909.4	910.5	911.3	912.1	912.9	913.8	914.3	915.0	915.6	916.2	916.2
152.5°	932.2	933.3	934.4	935.3	936.4	937.3	938.1	938.9	939.6	940.4	940.4
155°	964.1	964.6	965.3	965.9	966.5	967.1	968.1	969.2	970.2	971.2	971.4
157.5°	992.5	992.8	993.2	993.6	994.0	994.3	995.8	997.1	998.5	999.9	1000.1
160°	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5	1013.8	1014.9	1016.2	1016.4
162.5°	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4	1028.8	1030.2	1031.6	1031.7
165°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8	1048.2	1049.6	1051.1	1051.2
167.5°	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8	1064.2	1065.6	1067.1	1067.2
170°	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6	1073.0	1074.4	1075.9	1076.0
172.5°	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2	1079.7	1081.1	1082.5	1082.6
175°	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4	1086.9	1088.3	1089.7	1089.8
177.5°	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	9.3	9.1	9.1	8.9	9.1	9.1	9.3	9.3	9.3	10.1	10.1
90°	30.7	30.9	31.1	31.3	31.1	30.9	30.7	30.5	30.6	31.0	31.4
92.5°	29.7	29.7	29.8	29.8	29.8	29.7	29.7	29.6	29.6	29.5	29.4
95°	58.3	57.9	57.4	57.0	57.4	57.9	58.3	58.7	58.9	58.9	58.9
97.5°	98.9	98.9	98.9	98.9	98.9	98.9	98.9	99.0	99.0	99.0	99.0
100°	126.7	126.5	126.3	126.0	126.3	126.5	126.7	126.9	127.0	127.0	127.0
102.5°	157.6	157.4	157.2	157.0	157.2	157.4	157.6	157.8	157.8	157.6	157.5
105°	204.3	204.3	204.3	204.3	204.3	204.3	204.3	204.3	204.1	203.7	203.3
107.5°	251.7	250.7	249.8	248.8	249.8	250.7	251.7	252.5	252.9	252.8	252.6
110°	285.3	284.6	284.0	283.4	284.0	284.6	285.3	285.9	286.2	286.2	286.2



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	317.9	317.4	317.0	316.6	317.0	317.4	317.9	318.4	318.9	319.3	319.8
115°	369.9	369.3	368.7	368.0	368.7	369.3	369.9	370.5	370.9	371.1	371.4
117.5°	419.1	418.4	417.8	417.2	417.8	418.4	419.1	419.7	420.3	420.7	421.2
120°	453.7	453.0	452.4	451.8	452.4	453.0	453.7	454.2	454.6	454.6	454.6
122.5°	487.0	486.6	486.2	485.7	486.2	486.6	487.0	487.5	487.9	488.5	488.9
125°	538.0	537.8	537.6	537.4	537.6	537.8	538.0	538.2	538.6	539.2	539.9
127.5°	586.5	585.8	585.2	584.5	585.2	585.8	586.5	587.1	587.8	588.5	589.3
130°	620.8	620.0	619.2	618.4	619.2	620.0	620.8	621.6	622.3	622.7	623.1
132.5°	652.8	652.0	651.4	650.8	651.4	652.0	652.8	653.4	654.2	655.1	655.9
135°	703.0	702.4	701.8	701.2	701.8	702.4	703.0	703.6	704.0	704.3	704.5
137.5°	749.2	748.5	747.7	746.8	747.7	748.5	749.2	750.1	750.6	750.8	750.9
140°	780.9	780.1	779.3	778.5	779.3	780.1	780.9	781.7	782.1	782.1	782.1
142.5°	809.6	808.8	808.0	807.2	808.0	808.8	809.6	810.5	810.8	810.6	810.5
145°	852.7	851.9	851.0	850.2	851.0	851.9	852.7	853.5	853.8	853.7	853.4
147.5°	891.0	890.3	889.5	888.7	889.5	890.3	891.0	891.8	892.0	891.5	891.1
150°	915.6	915.0	914.3	913.8	914.3	915.0	915.6	916.2	916.2	915.6	915.0
152.5°	939.6	938.9	938.1	937.3	938.1	938.9	939.6	940.4	940.4	939.6	938.9
155°	970.8	970.2	969.6	968.9	969.6	970.2	970.8	971.4	971.2	970.2	969.2
157.5°	999.1	998.1	997.2	996.2	997.2	998.1	999.1	1000.1	999.9	998.5	997.1
160°	1015.6	1014.8	1013.9	1013.1	1013.9	1014.8	1015.6	1016.4	1016.2	1014.9	1013.8
162.5°	1030.8	1029.8	1028.8	1027.9	1028.8	1029.8	1030.8	1031.7	1031.6	1030.2	1028.8
165°	1050.3	1049.2	1048.2	1047.2	1048.2	1049.2	1050.3	1051.2	1051.1	1049.6	1048.2
167.5°	1066.2	1065.1	1064.1	1063.0	1064.1	1065.1	1066.2	1067.2	1067.1	1065.6	1064.2
170°	1074.8	1073.6	1072.3	1071.1	1072.3	1073.6	1074.8	1076.0	1075.9	1074.4	1073.0
172.5°	1081.4	1080.1	1079.0	1077.7	1079.0	1080.1	1081.4	1082.6	1082.5	1081.1	1079.7
175°	1088.6	1087.3	1086.2	1084.9	1086.2	1087.3	1088.6	1089.8	1089.7	1088.3	1086.9
177.5°	1091.2	1090.2	1089.2	1088.2	1089.2	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	10.2	10.6	10.1	9.5	8.6	8.0	7.7	7.4	7.6	7.4	7.3
90°	31.8	32.2	27.7	23.2	18.7	14.2	10.8	8.3	5.9	3.4	1.0
92.5°	29.3	29.2	28.2	27.2	26.1	25.0	23.6	21.8	20.0	18.1	16.4
95°	58.9	58.9	58.5	58.1	57.7	57.3	56.0	53.9	52.0	49.9	47.8
97.5°	99.0	99.0	98.2	97.4	96.6	95.9	94.6	92.8	91.0	89.2	87.5
100°	127.0	127.0	126.4	125.7	125.2	124.5	123.4	121.8	120.2	118.5	116.8
102.5°	157.3	157.2	156.4	155.6	154.9	154.1	153.0	151.7	150.4	149.1	147.8
105°	202.9	202.4	202.0	201.6	201.2	200.8	200.3	199.7	199.1	198.4	197.8
107.5°	252.5	252.3	252.3	252.3	252.3	252.3	251.8	251.0	250.1	249.1	248.3
110°	286.2	286.2	286.2	286.2	286.2	286.2	285.6	284.3	283.1	281.9	280.7



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	320.3	320.8	320.9	321.1	321.2	321.5	320.9	319.6	318.5	317.2	316.0
115°	371.5	371.8	372.2	372.6	373.0	373.4	373.0	371.8	370.5	369.3	368.0
117.5°	421.7	422.2	423.3	424.5	425.6	426.7	426.5	424.8	423.3	421.6	419.9
120°	454.6	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6
122.5°	489.4	489.9	491.1	492.2	493.4	494.5	494.1	492.1	490.1	488.2	486.2
125°	540.4	541.1	541.7	542.3	542.9	543.5	542.9	541.1	539.2	537.4	535.5
127.5°	590.0	590.7	591.5	592.2	592.9	593.7	592.9	590.6	588.3	585.9	583.6
130°	623.4	623.9	624.3	624.7	625.1	625.5	624.4	621.7	619.1	616.4	613.8
132.5°	656.9	657.7	657.7	657.6	657.5	657.4	656.3	654.1	652.0	649.8	647.6
135°	704.6	704.9	704.5	704.0	703.6	703.2	701.9	699.7	697.4	695.1	692.9
137.5°	751.1	751.2	750.7	750.2	749.6	749.1	747.9	746.1	744.3	742.4	740.5
140°	782.1	782.1	781.2	780.1	779.1	778.1	776.7	774.8	772.9	771.1	769.3
142.5°	810.3	810.2	809.5	808.7	808.0	807.3	806.0	804.2	802.4	800.6	798.8
145°	853.2	853.0	851.8	850.6	849.3	848.1	846.8	845.3	843.9	842.5	841.1
147.5°	890.7	890.2	889.4	888.6	887.7	886.9	885.7	883.9	882.2	880.5	878.8
150°	914.3	913.8	912.9	912.1	911.3	910.5	909.4	908.2	907.0	905.8	904.5
152.5°	938.1	937.3	936.4	935.3	934.4	933.3	932.2	931.1	929.8	928.6	927.3
155°	968.1	967.1	966.5	965.9	965.3	964.6	964.1	963.5	962.8	962.2	961.6
157.5°	995.8	994.3	994.0	993.6	993.2	992.8	992.5	992.0	991.7	991.3	990.9
160°	1012.5	1011.3	1011.1	1010.9	1010.7	1010.4	1010.2	1009.7	1009.3	1008.9	1008.5
162.5°	1027.4	1026.0	1025.8	1025.6	1025.4	1025.2	1025.1	1024.9	1024.8	1024.8	1024.7
165°	1046.8	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.6	1045.8	1046.1	1046.2
167.5°	1062.8	1061.4	1061.4	1061.4	1061.4	1061.5	1061.8	1062.5	1063.0	1063.7	1064.3
170°	1071.6	1070.2	1070.4	1070.6	1070.8	1071.0	1071.4	1072.0	1072.6	1073.2	1073.9
172.5°	1078.2	1076.8	1077.0	1077.2	1077.4	1077.6	1078.0	1078.6	1079.3	1079.9	1080.5
175°	1085.4	1083.9	1084.4	1084.8	1085.2	1085.6	1086.2	1086.7	1087.3	1088.0	1088.6
177.5°	1089.2	1088.2	1088.5	1088.9	1089.2	1089.5	1090.0	1090.4	1090.9	1091.4	1091.9
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.8	10.5	11.0	12.5	12.5	13.5	14.3	14.9	15.5	15.1	14.7
90°	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8	31.4
92.5°	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3	29.4
95°	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9	58.9
97.5°	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0	99.0
100°	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0	127.0
102.5°	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3	157.5
105°	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9	203.3
107.5°	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5	252.6
110°	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2	286.2





TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3	319.8
115°	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5	371.4
117.5°	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7	421.2
120°	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6	454.6
122.5°	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4	488.9
125°	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4	539.9
127.5°	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0	589.3
130°	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4	623.1
132.5°	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9	655.9
135°	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6	704.5
137.5°	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1	750.9
140°	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1	782.1
142.5°	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3	810.5
145°	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2	853.4
147.5°	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7	891.1
150°	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3	915.0
152.5°	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1	938.9
155°	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1	969.2
157.5°	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8	997.1
160°	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5	1013.8
162.5°	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4	1028.8
165°	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8	1048.2
167.5°	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8	1064.2
170°	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6	1073.0
172.5°	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2	1079.7
175°	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4	1086.9
177.5°	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2	1090.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	14.9	14.8	14.5	14.6	14.9	14.7	14.7
90°	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	285.9	285.3	284.6	284.0	283.4



TEST NUMBER: P331367-927

CATALOG NUMBER: SA2XXDIP-C675D1080U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)