

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333267-935

Luminaire Tested: **S125DIP-S1090D590U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333267-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5651.2 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		72	72	72	68
1	102	97	93	90	96	92	88	85	82	79	77		72	70	69		64	62	61	57
2	93	85	78	73	87	80	75	70	72	67	63		64	60	57		56	54	51	48
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		50	46	44	40
4	77	66	58	52	73	63	55	50	56	50	45		50	45	41		44	41	38	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	36	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9489	9489	9489
5°	9510	9419	9479
10°	9452	9353	9406
15°	9349	9240	9279
20°	9203	9082	9099
25°	9045	8896	8888
30°	8850	8694	8651
35°	8642	8476	8358
40°	8427	8241	8123
45°	8195	8026	7867
50°	7941	7766	7533
55°	7696	7473	7264
60°	7401	7177	6921
65°	7051	6820	6589
70°	6717	6409	6190
75°	6119	5916	5712
80°	5449	5359	5229
85°	4735	4824	4565



TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.5	2.5
10°-20°	391.3	6.9
20°-30°	577.8	10.2
30°-40°	674.2	11.9
40°-50°	677.1	12.0
50°-60°	594.4	10.5
60°-70°	442.9	7.8
70°-80°	253.2	4.5
80°-90°	75.0	1.3
90°-100°	176.6	3.1
100°-110°	379.6	6.7
110°-120°	356.2	6.3
120°-130°	288.7	5.1
130°-140°	231.7	4.1
140°-150°	174.8	3.1
150°-160°	123.1	2.2
160°-170°	72.5	1.3
170°-180°	23.6	0.4
0°-30°	1107.6	19.6
0°-40°	1781.8	31.5
0°-60°	3053.3	54.0
0°-90°	3824.4	67.7
90°-120°	912.4	16.1
90°-150°	1607.6	28.4
90°-180°	1827.0	32.3
0°-180°	5651.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1469	1469	1469	1469	1469	
5°	1467	1464	1453	1463	1462	139
15°	1398	1394	1382	1388	1388	394
25°	1269	1263	1248	1250	1247	584
35°	1096	1091	1075	1069	1060	685
45°	897	892	879	865	861	691
55°	684	679	664	653	645	610
65°	461	458	446	436	431	458
75°	245	243	237	234	229	261
85°	64	65	65	64	62	71
90°	0	4	8	10	11	4
95°	16	48	435	197	116	17
105°	56	78	356	701	651	59
115°	99	120	286	616	725	98
125°	138	161	274	490	571	122
135°	161	194	272	411	474	125
145°	188	215	273	340	374	118
155°	214	230	266	301	314	99
165°	234	240	255	271	275	66
175°	243	243	245	248	247	23
180°	244	244	244	244	244	



TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1472.9	1472.3	1471.6	1471.0	1470.4	1469.0	1467.0	1464.9	1462.8	1460.8	1462.8
5°	1466.9	1466.4	1465.9	1465.3	1464.8	1463.3	1460.7	1458.1	1455.5	1452.9	1455.3
7.5°	1453.4	1452.9	1452.3	1451.8	1451.3	1449.6	1446.7	1443.9	1441.1	1438.2	1440.5
10°	1441.3	1440.8	1440.3	1439.8	1439.2	1437.5	1434.7	1431.8	1429.0	1426.2	1428.2
12.5°	1426.4	1425.5	1424.5	1423.6	1422.7	1420.9	1418.2	1415.7	1413.0	1410.3	1412.0
15°	1398.3	1397.5	1396.7	1395.9	1395.2	1393.4	1390.5	1387.7	1384.8	1382.0	1383.3
17.5°	1366.0	1364.9	1363.7	1362.5	1361.4	1359.3	1356.4	1353.5	1350.6	1347.6	1349.2
20°	1339.0	1338.5	1338.0	1337.5	1337.0	1335.0	1331.6	1328.3	1324.9	1321.5	1323.4
22.5°	1312.0	1311.1	1310.2	1309.2	1308.3	1306.2	1303.1	1299.9	1296.8	1293.7	1294.9
25°	1269.3	1268.0	1266.7	1265.4	1264.1	1261.8	1258.4	1255.1	1251.7	1248.4	1248.9
27.5°	1219.3	1218.5	1217.7	1216.9	1216.2	1214.1	1210.6	1207.1	1203.7	1200.2	1200.3
30°	1186.7	1185.9	1185.2	1184.4	1183.6	1181.3	1177.4	1173.5	1169.7	1165.8	1165.3
32.5°	1151.4	1150.2	1149.0	1147.8	1146.7	1144.4	1140.8	1137.4	1133.9	1130.5	1129.5
35°	1096.1	1095.0	1094.0	1093.0	1091.9	1089.6	1086.0	1082.4	1078.7	1075.1	1073.8
37.5°	1038.6	1037.3	1036.0	1034.7	1033.5	1031.1	1027.7	1024.3	1020.9	1017.5	1015.5
40°	999.6	998.3	997.0	995.7	994.5	992.0	988.3	984.7	981.1	977.5	975.2
42.5°	957.8	956.7	955.6	954.5	953.4	951.1	947.4	943.8	940.2	936.6	934.4
45°	897.3	896.3	895.3	894.2	893.2	891.1	888.0	884.9	881.8	878.7	875.6
47.5°	832.2	832.2	832.3	832.4	832.4	830.6	826.9	823.1	819.4	815.7	812.5
50°	790.4	789.6	788.8	788.1	787.3	785.3	782.2	779.1	776.0	772.9	769.6
52.5°	747.6	747.0	746.5	745.9	745.4	743.4	740.1	736.8	733.5	730.1	727.2
55°	683.5	682.7	681.9	681.1	680.4	678.1	674.5	670.9	667.3	663.7	661.3
57.5°	615.8	615.4	615.0	614.6	614.2	612.4	609.3	606.3	603.3	600.2	597.2
60°	573.0	572.0	570.9	569.9	568.9	567.0	564.1	561.3	558.4	555.6	553.0
62.5°	528.4	527.5	526.8	525.9	525.1	523.5	521.0	518.6	516.2	513.8	510.9
65°	461.4	460.9	460.4	459.9	459.3	457.7	454.9	452.0	449.2	446.3	444.0
67.5°	396.6	395.5	394.4	393.3	392.3	390.6	388.5	386.4	384.3	382.2	380.2
70°	355.7	354.4	353.1	351.8	350.5	348.7	346.4	344.1	341.7	339.4	337.9
72.5°	311.1	310.1	309.3	308.4	307.5	306.3	304.9	303.3	301.9	300.3	298.6
75°	245.2	244.7	244.2	243.7	243.1	242.3	241.0	239.7	238.4	237.1	236.3
77.5°	184.6	184.3	184.2	184.0	183.7	183.3	182.5	181.8	181.2	180.4	179.9
80°	146.5	146.5	146.5	146.5	146.5	146.2	145.7	145.2	144.6	144.1	143.9
82.5°	113.0	112.5	112.2	111.8	111.3	111.1	111.0	110.9	110.7	110.6	110.2
85°	63.9	64.1	64.4	64.7	64.9	65.1	65.1	65.1	65.1	65.1	64.8
87.5°	25.2	25.3	25.5	25.7	25.9	26.0	25.9	25.8	25.7	25.7	25.8
90°	0.5	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4
92.5°	6.0	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2
95°	16.2	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9
97.5°	26.9	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8
100°	34.4	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3
102.5°	42.6	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7
105°	55.5	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1
107.5°	68.1	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2
110°	77.1	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6



TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	86.2	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8
115°	99.2	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9
117.5°	111.0	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1
120°	118.8	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8
122.5°	127.1	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8
125°	137.5	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1
127.5°	145.7	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3
130°	150.8	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4
132.5°	154.7	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7
135°	161.1	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1
137.5°	169.2	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1
140°	173.8	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7
142.5°	179.3	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8
145°	187.6	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8
147.5°	196.2	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7
150°	201.4	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4
152.5°	206.9	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7
155°	214.1	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0
157.5°	220.6	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7
160°	225.0	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2
162.5°	228.5	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1
165°	233.8	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3
167.5°	237.3	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7
170°	239.7	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9
172.5°	241.3	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2
175°	243.1	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6
177.5°	244.0	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1464.9	1467.0	1469.0	1470.0	1469.8	1469.6	1469.4	1469.2
5°	1457.6	1459.9	1462.2	1463.3	1463.0	1462.8	1462.5	1462.2
7.5°	1442.8	1445.1	1447.3	1448.4	1448.1	1447.9	1447.6	1447.3
10°	1430.3	1432.4	1434.4	1435.4	1435.1	1434.9	1434.6	1434.3
12.5°	1413.7	1415.3	1416.9	1417.8	1417.7	1417.6	1417.6	1417.6
15°	1384.6	1385.9	1387.2	1387.8	1387.8	1387.8	1387.8	1387.8
17.5°	1350.8	1352.4	1354.0	1354.2	1352.9	1351.6	1350.3	1349.0
20°	1325.2	1327.0	1328.8	1329.0	1327.7	1326.5	1325.2	1323.9
22.5°	1296.1	1297.3	1298.4	1298.6	1297.7	1296.8	1296.0	1295.0
25°	1249.4	1249.9	1250.4	1250.3	1249.5	1248.7	1247.9	1247.2
27.5°	1200.4	1200.5	1200.7	1200.3	1199.5	1198.8	1198.0	1197.2
30°	1164.8	1164.2	1163.7	1163.1	1162.4	1161.6	1160.8	1160.0
32.5°	1128.6	1127.7	1126.8	1125.6	1124.2	1122.8	1121.4	1120.0
35°	1072.5	1071.3	1070.0	1068.3	1066.3	1064.2	1062.1	1060.1
37.5°	1013.7	1011.8	1009.9	1008.3	1007.1	1005.9	1004.7	1003.6
40°	972.8	970.5	968.2	966.6	965.9	965.1	964.3	963.5
42.5°	932.4	930.2	928.2	926.4	925.3	924.1	922.9	921.7
45°	872.5	869.4	866.3	864.4	863.6	862.8	862.0	861.3
47.5°	809.4	806.2	803.1	800.6	798.8	797.0	795.2	793.4
50°	766.2	762.8	759.5	756.9	755.1	753.3	751.5	749.7
52.5°	724.3	721.3	718.4	715.9	713.9	711.9	709.9	707.8
55°	659.0	656.7	654.4	652.3	650.5	648.7	646.9	645.1
57.5°	594.3	591.2	588.2	586.3	585.3	584.3	583.3	582.3
60°	550.4	547.9	545.3	543.0	541.2	539.4	537.6	535.8
62.5°	508.2	505.4	502.6	500.5	499.1	497.7	496.3	494.9
65°	441.7	439.4	437.0	435.3	434.3	433.3	432.2	431.2
67.5°	378.2	376.3	374.3	373.0	372.4	371.8	371.2	370.6
70°	336.3	334.8	333.2	331.9	330.9	329.8	328.8	327.8
72.5°	296.9	295.1	293.3	292.0	290.9	289.9	288.9	287.8
75°	235.6	234.8	234.0	233.1	232.0	231.0	230.0	228.9
77.5°	179.4	179.0	178.6	178.0	177.2	176.5	175.7	175.0
80°	143.6	143.4	143.1	142.7	142.2	141.6	141.1	140.6
82.5°	109.7	109.3	108.8	108.5	108.4	108.3	108.2	108.1
85°	64.6	64.3	64.1	63.6	63.1	62.6	62.1	61.6
87.5°	25.9	26.0	26.2	26.1	25.7	25.3	25.0	24.5
90°	8.9	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	87.0	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	353.1	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	525.9	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	604.1	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	630.4	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	614.9	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	559.5	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	518.7	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333267-935

CATALOG NUMBER: S125DIP-S1090D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	486.5	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	445.9	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	419.8	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	405.7	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	395.1	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	379.6	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	363.9	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	354.1	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	344.3	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	331.5	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	320.7	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	314.8	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	309.7	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	303.1	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	296.8	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	293.2	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	289.3	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	283.4	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	277.5	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	273.5	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	269.2	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	263.2	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	257.5	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	254.4	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	250.9	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.4	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)