

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333270-935

Luminaire Tested: **S125DIP-S1090D810U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333270-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D810U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6369.4 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	43	36	30	52	41	34	29	37	31	27	32	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	35	28	23	31	25	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8843	8843	8843	8843
5°	10240	8873	7769	8873
10°	11913	8826	6807	8826
15°	13188	8762	6279	8762
20°	14762	8659	5856	8659
25°	17293	8543	5648	8543
30°	18678	8429	5469	8429
35°	15358	8215	5351	8215
40°	10916	7917	5223	7917
45°	8386	7516	5149	7516
50°	7159	7018	5138	7018
55°	6373	6531	5183	6531
60°	5749	5997	5315	5997
65°	5310	5462	5453	5462
70°	4828	4906	5531	4906
75°	4262	4319	5480	4319
80°	3585	3522	5013	3522
85°	2838	2542	4046	2542



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.8	2.1
10°-20°	392.4	6.2
20°-30°	637.2	10.0
30°-40°	777.3	12.2
40°-50°	707.1	11.1
50°-60°	563.2	8.8
60°-70°	392.3	6.2
70°-80°	209.2	3.3
80°-90°	54.7	0.9
90°-100°	242.0	3.8
100°-110°	520.3	8.2
110°-120°	488.3	7.7
120°-130°	395.7	6.2
130°-140°	317.6	5.0
140°-150°	239.7	3.8
150°-160°	168.7	2.6
160°-170°	99.4	1.6
170°-180°	32.3	0.5
0°-30°	1161.5	18.2
0°-40°	1938.8	30.4
0°-60°	3209.2	50.4
0°-90°	3865.3	60.7
90°-120°	1250.6	19.6
90°-150°	2203.6	34.6
90°-180°	2504.0	39.3
0°-180°	6369.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1580	1369	1198	1369	1580	159
15°	1972	1310	939	1310	1972	565
25°	2427	1199	793	1199	2427	1108
35°	1948	1042	679	1042	1948	1192
45°	918	823	564	823	918	735
55°	566	580	460	580	566	510
65°	348	357	357	357	348	345
75°	171	173	220	173	171	184
85°	38	34	55	34	38	45
90°	16	1	16	1	16	12
95°	158	22	158	22	158	224
105°	892	76	892	76	892	887
115°	994	136	994	136	994	971
125°	783	188	783	188	783	708
135°	650	221	650	221	650	504
145°	513	257	513	257	513	326
155°	430	294	430	294	430	201
165°	377	320	377	320	377	108
175°	339	333	339	333	339	33
180°	334	334	334	334	334	



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1448.2	1446.3	1444.5	1440.7	1443.6	1435.6	1431.9	1425.4	1417.5	1414.7	1411.4
5°	1579.5	1582.4	1585.4	1573.1	1574.3	1566.2	1547.6	1532.4	1520.3	1504.5	1493.5
7.5°	1737.6	1730.7	1730.2	1722.3	1708.7	1697.7	1678.2	1653.3	1629.3	1601.8	1579.2
10°	1816.6	1817.2	1812.0	1802.7	1788.1	1777.7	1752.1	1727.7	1698.1	1663.2	1638.2
12.5°	1876.1	1878.5	1872.0	1859.4	1852.3	1828.9	1808.9	1779.8	1744.6	1716.7	1678.7
15°	1972.4	1966.0	1961.4	1945.6	1933.5	1909.0	1877.1	1846.8	1808.4	1773.1	1737.6
17.5°	2065.1	2070.2	2061.5	2047.2	2009.3	1980.8	1937.9	1896.6	1848.8	1801.3	1758.9
20°	2147.9	2152.5	2139.2	2114.2	2068.8	2040.4	1984.0	1930.5	1875.3	1814.3	1767.8
22.5°	2251.1	2247.4	2229.3	2191.3	2152.1	2099.4	2038.4	1973.3	1904.1	1835.2	1773.4
25°	2426.8	2402.4	2391.3	2344.3	2292.6	2215.3	2131.6	2036.3	1950.3	1859.1	1780.0
27.5°	2524.2	2516.5	2504.2	2471.4	2417.1	2334.4	2235.8	2119.6	1998.3	1883.1	1779.7
30°	2504.6	2505.9	2507.0	2496.6	2461.7	2399.5	2301.3	2176.3	2032.2	1902.6	1782.9
32.5°	2331.8	2352.9	2373.1	2397.0	2406.8	2394.9	2333.4	2220.5	2072.2	1924.9	1781.1
35°	1947.9	1954.4	2020.0	2085.1	2173.4	2242.0	2287.9	2237.9	2113.0	1943.9	1778.8
37.5°	1518.9	1550.2	1595.7	1669.2	1796.7	1910.9	2057.7	2125.2	2084.9	1950.1	1774.8
40°	1294.8	1323.8	1353.5	1428.4	1535.9	1674.2	1841.0	1983.4	2016.5	1930.5	1760.8
42.5°	1121.8	1144.9	1177.8	1234.1	1324.0	1446.5	1605.8	1791.8	1906.3	1873.8	1731.6
45°	918.2	932.7	958.3	1003.1	1068.2	1164.0	1304.7	1508.0	1685.3	1744.0	1662.1
47.5°	785.9	785.8	805.7	836.6	883.6	965.0	1069.0	1228.4	1417.7	1557.8	1551.3
50°	712.5	709.6	725.2	752.0	789.2	843.3	942.6	1069.9	1251.7	1410.4	1454.6
52.5°	649.3	649.6	659.3	679.0	710.2	756.3	830.5	945.3	1100.7	1263.5	1346.7
55°	566.0	563.7	574.7	588.1	610.8	641.0	694.5	782.2	908.3	1068.7	1176.8
57.5°	489.7	496.2	500.6	509.9	528.7	549.0	594.0	658.4	758.5	896.1	1010.4
60°	445.1	451.5	455.0	464.3	479.4	496.9	531.8	584.0	668.3	786.9	900.2
62.5°	405.2	410.2	411.3	419.7	432.0	449.0	476.4	520.4	586.9	690.6	801.6
65°	347.5	347.5	349.8	358.5	364.4	379.4	400.4	432.4	485.9	566.6	661.3
67.5°	292.0	294.7	294.2	298.0	303.3	315.1	330.1	356.5	396.1	455.0	530.8
70°	255.7	258.0	257.4	260.4	266.1	273.7	285.9	310.9	339.4	389.9	455.0
72.5°	223.2	224.1	222.6	226.4	229.9	236.5	250.1	263.5	290.1	332.8	386.2
75°	170.8	172.0	173.1	175.5	179.0	182.4	189.4	202.9	220.2	252.2	286.5
77.5°	128.1	125.9	128.6	128.3	130.3	132.9	139.1	146.2	160.5	180.7	207.2
80°	96.4	97.0	97.0	97.6	100.6	102.3	107.5	112.7	123.8	138.9	157.5
82.5°	70.4	72.0	71.0	72.1	74.5	75.8	78.7	83.0	89.4	101.3	114.7
85°	38.3	35.5	36.6	37.8	37.8	38.3	40.6	42.4	45.9	50.5	55.8
87.5°	14.3	15.2	15.5	15.5	16.0	15.7	17.4	17.3	18.6	19.8	21.4
90°	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1	11.5	10.8	9.4
92.5°	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3	175.7	217.1	220.5
95°	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1	583.7	596.5	486.7
97.5°	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9	738.5	637.0	434.6
100°	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0	776.2	608.0	387.8
102.5°	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1	753.6	556.7	352.2
105°	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8	681.3	488.1	317.8
107.5°	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9	607.5	440.8	303.2
110°	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9	565.5	418.7	298.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8	534.3	405.8	298.9
115°	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3	500.2	391.8	300.9
117.5°	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5	479.8	385.0	305.4
120°	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0	468.6	381.7	309.7
122.5°	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6	458.8	379.0	313.4
125°	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4	445.7	375.7	319.8
127.5°	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9	433.5	374.0	326.9
130°	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3	425.5	373.0	331.2
132.5°	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9	419.0	373.0	336.0
135°	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4	411.3	373.0	342.7
137.5°	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6	404.5	373.8	348.7
140°	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5	401.2	374.3	351.4
142.5°	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6	398.6	374.9	353.0
145°	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3	394.5	374.3	354.8
147.5°	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7	390.3	372.6	355.4
150°	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9	387.1	370.9	355.4
152.5°	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5	383.3	368.8	354.9
155°	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5	377.0	364.9	353.4
157.5°	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4	371.1	360.8	351.7
160°	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0	366.3	358.2	350.1
162.5°	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0	361.9	354.9	348.4
165°	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8	355.4	350.1	346.0
167.5°	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0	349.1	345.3	342.2
170°	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7	345.3	342.7	340.6
172.5°	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9	341.6	339.4	338.5
175°	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6	336.6	336.0	336.0
177.5°	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0	334.4	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1408.7	1405.4	1401.7	1395.2	1387.2	1383.1	1376.6	1372.4	1364.0	1357.0	1349.6
5°	1480.1	1465.1	1451.1	1433.0	1413.3	1400.5	1385.4	1368.6	1351.2	1333.1	1313.4
7.5°	1554.2	1527.4	1498.4	1467.1	1436.6	1408.4	1381.6	1355.2	1330.6	1300.8	1275.6
10°	1604.0	1570.2	1534.2	1491.8	1450.5	1414.5	1377.9	1345.9	1313.4	1278.5	1247.7
12.5°	1653.6	1608.8	1557.9	1511.3	1461.6	1418.2	1375.1	1334.3	1293.4	1254.8	1218.8
15°	1688.8	1649.2	1602.1	1535.9	1480.1	1420.3	1363.3	1310.4	1261.0	1218.1	1172.8
17.5°	1711.9	1661.0	1610.4	1546.9	1473.8	1406.8	1342.3	1281.8	1226.1	1171.6	1127.8
20°	1716.1	1663.8	1610.9	1548.7	1473.8	1397.1	1332.6	1259.9	1200.1	1143.7	1090.2
22.5°	1714.7	1655.4	1597.8	1533.9	1460.8	1390.1	1312.1	1238.0	1173.1	1117.7	1061.9
25°	1701.6	1638.2	1566.2	1501.7	1429.6	1354.6	1275.6	1198.9	1132.6	1069.3	1014.1
27.5°	1690.7	1608.4	1526.9	1451.6	1382.1	1313.4	1237.7	1159.2	1085.6	1021.5	969.5
30°	1677.1	1587.1	1495.2	1416.8	1345.3	1278.5	1207.0	1130.3	1053.6	990.8	935.0
32.5°	1665.1	1560.1	1463.2	1377.8	1302.1	1237.1	1171.2	1098.2	1022.9	959.2	903.4
35°	1641.7	1520.3	1409.3	1312.8	1232.0	1165.2	1110.0	1042.0	972.8	911.2	857.7
37.5°	1612.1	1467.9	1348.8	1247.7	1159.2	1088.7	1037.3	985.2	918.8	859.4	811.1
40°	1588.8	1430.7	1304.7	1201.2	1109.4	1036.1	988.5	939.1	883.9	828.7	777.6
42.5°	1559.5	1397.3	1260.0	1148.7	1057.7	986.4	936.4	894.5	845.8	794.3	746.8
45°	1505.7	1336.6	1187.8	1068.2	976.3	905.9	854.3	822.9	786.3	737.4	697.3
47.5°	1426.6	1263.7	1109.8	986.3	891.6	826.4	777.9	747.8	722.0	685.7	649.4
50°	1356.3	1209.4	1053.6	931.0	836.3	770.6	725.8	698.5	676.4	648.5	617.8
52.5°	1277.8	1141.0	998.2	877.0	783.3	718.5	674.7	650.7	632.2	612.3	581.9
55°	1153.0	1036.7	904.2	789.2	702.6	639.2	600.9	580.0	564.9	549.7	531.2
57.5°	1015.5	924.5	807.2	702.0	622.2	564.6	528.8	508.5	496.7	489.0	478.0
60°	918.8	840.9	739.8	643.9	566.0	514.9	480.0	464.3	454.4	448.1	439.9
62.5°	829.1	765.1	671.4	583.9	515.8	467.4	436.4	421.1	411.6	408.5	401.8
65°	696.8	647.4	570.1	497.5	439.4	398.0	372.0	357.4	351.5	348.1	348.7
67.5°	566.5	536.4	474.3	412.3	366.0	331.4	310.5	299.3	296.4	291.7	291.6
70°	487.0	464.3	412.0	358.0	316.7	290.0	271.4	259.8	256.8	254.5	254.0
72.5°	416.8	396.9	351.5	308.2	271.1	247.7	232.3	225.3	220.6	219.2	219.1
75°	313.2	302.2	266.1	231.9	206.3	190.0	179.6	173.1	169.7	169.1	169.7
77.5°	222.7	213.0	190.1	165.8	149.7	137.4	128.5	126.3	122.3	122.5	121.9
80°	167.4	161.0	146.5	127.3	113.9	103.4	98.8	94.7	93.6	91.8	93.6
82.5°	121.3	114.5	104.6	92.4	81.4	75.1	70.4	69.1	68.4	67.7	68.0
85°	59.8	60.4	54.6	45.3	40.6	37.2	34.3	34.3	33.7	33.1	33.7
87.5°	22.2	21.0	19.0	17.3	14.7	13.1	12.4	12.7	11.5	11.2	12.0
90°	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7	1.4	2.7	4.0
92.5°	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2	10.0	15.6	23.9
95°	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2	22.9	28.2	35.6
97.5°	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9	37.7	41.5	48.9
100°	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1	48.5	51.1	58.5
102.5°	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5	59.2	61.4	69.3
105°	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1	76.1	79.5	86.2
107.5°	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3	94.6	97.9	103.4
110°	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7	107.0	109.7	115.8





TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0	119.4	121.6	127.6
115°	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0	137.3	139.4	145.4
117.5°	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1	154.2	156.4	162.4
120°	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9	165.0	167.6	173.7
122.5°	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3	175.7	177.9	183.9
125°	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5	189.9	193.2	199.2
127.5°	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7	201.7	206.0	213.7
130°	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6	208.7	214.0	222.8
132.5°	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1	214.6	221.1	230.9
135°	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8	223.5	231.6	242.4
137.5°	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9	233.8	241.4	252.2
140°	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3	240.3	248.4	259.2
142.5°	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8	247.4	254.9	265.6
145°	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2	258.5	265.3	274.7
147.5°	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0	269.8	275.6	284.4
150°	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0	277.3	282.1	290.8
152.5°	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5	284.4	288.5	296.2
155°	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5	293.5	297.6	304.3
157.5°	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4	302.3	305.5	311.3
160°	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3	307.6	310.4	315.0
162.5°	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1	312.5	315.2	319.3
165°	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5	319.1	321.2	324.5
167.5°	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3	324.6	325.8	327.7
170°	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6	327.9	328.6	329.8
172.5°	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7	329.5	330.1	331.5
175°	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2	331.9	332.6	333.2
177.5°	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4	333.4	333.4	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1345.4	1340.3	1336.1	1326.8	1321.7	1314.7	1309.2	1315.2	1308.7	1311.5	1307.3
5°	1303.5	1287.2	1275.6	1258.7	1244.2	1230.8	1221.0	1219.2	1214.5	1212.2	1205.2
7.5°	1253.0	1232.7	1212.7	1190.6	1172.0	1153.1	1141.0	1131.0	1124.4	1115.7	1109.7
10°	1223.3	1195.9	1172.8	1146.0	1122.7	1102.4	1086.2	1078.0	1070.5	1059.4	1055.3
12.5°	1186.5	1158.3	1130.0	1101.4	1079.0	1056.4	1042.4	1030.1	1024.8	1012.4	1011.2
15°	1142.5	1100.1	1072.2	1043.1	1012.4	993.8	982.1	968.7	962.9	954.2	947.8
17.5°	1089.9	1052.1	1017.2	987.1	960.7	945.0	930.7	921.4	911.5	905.8	895.3
20°	1051.9	1015.8	980.9	949.0	928.7	910.6	899.0	890.3	879.9	876.9	866.5
22.5°	1019.8	980.0	946.6	919.7	897.5	877.2	864.6	858.7	851.4	842.5	840.4
25°	967.6	926.3	897.9	871.2	851.4	832.8	824.1	816.5	809.5	803.1	800.8
27.5°	922.5	885.6	851.8	827.7	810.5	793.5	785.8	776.6	771.5	766.4	760.1
30°	890.9	853.1	823.5	800.2	781.6	766.5	758.4	752.0	747.3	742.7	739.2
32.5°	858.3	823.4	794.6	771.9	753.3	741.8	734.7	730.1	725.0	719.5	715.1
35°	815.4	777.0	749.1	729.4	714.8	706.1	697.9	693.9	688.0	688.0	683.4
37.5°	766.9	733.7	709.1	691.1	678.0	670.3	661.4	658.7	655.0	652.5	650.8
40°	738.0	707.2	684.0	666.0	652.0	645.7	638.7	634.0	631.7	628.8	627.6
42.5°	708.3	678.9	656.6	640.0	627.8	622.4	615.9	612.6	608.0	604.2	603.5
45°	663.1	634.6	614.2	600.9	590.4	584.0	580.0	573.0	570.7	566.0	565.4
47.5°	620.2	592.9	572.9	562.0	552.8	547.5	541.1	534.2	531.5	529.2	528.9
50°	588.1	563.1	544.5	534.1	525.4	517.8	511.4	506.8	505.0	505.0	506.2
52.5°	555.6	534.3	518.5	505.7	497.5	489.4	483.5	480.7	478.0	480.9	482.9
55°	507.9	486.4	474.8	462.6	454.4	445.1	442.2	441.1	439.4	444.0	446.3
57.5°	457.4	442.4	428.8	416.6	409.3	404.0	400.0	399.3	402.6	404.8	412.3
60°	425.4	407.9	395.7	386.4	377.7	374.3	373.1	372.0	374.3	380.6	390.5
62.5°	390.0	375.9	362.7	355.8	349.4	343.5	343.4	344.1	348.7	356.0	365.8
65°	338.2	326.0	317.3	309.2	303.9	300.4	301.6	303.9	309.2	319.0	330.1
67.5°	285.6	277.2	269.4	262.8	257.8	257.8	259.0	262.4	268.6	280.0	290.1
70°	251.7	242.4	235.9	233.1	228.9	226.6	230.1	235.9	241.2	251.7	260.4
72.5°	217.7	209.8	204.8	202.9	201.0	199.2	200.4	206.6	213.7	224.2	234.3
75°	167.4	164.5	161.0	158.7	156.9	158.1	159.2	165.1	170.8	181.9	193.6
77.5°	122.2	119.2	117.0	116.5	115.5	116.1	119.3	123.6	129.3	137.4	146.2
80°	92.4	91.3	90.1	89.5	89.5	90.1	94.7	97.6	102.9	110.4	117.4
82.5°	67.3	66.6	66.4	66.2	66.7	66.8	69.7	73.4	77.7	83.4	89.5
85°	35.5	34.3	36.0	36.6	35.5	37.2	38.3	40.6	42.4	45.3	48.2
87.5°	12.7	13.9	13.6	14.3	14.5	15.7	15.3	17.3	18.3	19.5	19.2
90°	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1	12.8	13.4	14.8
92.5°	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3	86.6	65.2	55.2
95°	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1	381.7	298.9	242.4
97.5°	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9	649.1	568.4	489.8
100°	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0	795.0	725.7	655.7
102.5°	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1	884.5	851.2	803.8
105°	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8	935.1	964.8	957.3
107.5°	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9	890.0	966.0	1001.2
110°	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9	838.8	933.8	990.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8	788.2	884.2	951.7
115°	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3	715.7	807.9	881.2
117.5°	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5	665.4	744.9	812.2
120°	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0	636.9	710.9	770.2
122.5°	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6	616.4	682.3	737.9
125°	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4	589.1	647.6	696.1
127.5°	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9	562.9	617.6	663.0
130°	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3	544.7	597.1	640.9
132.5°	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9	527.4	575.1	617.2
135°	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4	500.8	544.0	582.3
137.5°	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6	477.2	513.0	545.5
140°	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5	463.1	494.1	522.4
142.5°	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6	451.3	477.9	502.5
145°	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3	436.3	457.1	475.3
147.5°	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7	423.7	439.7	453.5
150°	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9	416.7	429.5	441.6
152.5°	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5	409.7	421.5	430.8
155°	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5	399.2	408.6	416.0
157.5°	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4	389.3	396.5	402.3
160°	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0	381.7	388.5	393.1
162.5°	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0	375.2	380.9	385.0
165°	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8	365.6	369.6	373.0
167.5°	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0	356.1	359.2	361.6
170°	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7	350.8	352.8	354.1
172.5°	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9	345.9	347.4	348.2
175°	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6	338.6	340.0	340.0
177.5°	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0	335.5	335.5	335.5
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1304.5	1307.8	1305.0	1308.7	1305.0	1307.8	1304.5	1307.3	1311.5	1308.7	1315.2
5°	1202.4	1197.1	1200.6	1198.3	1200.6	1197.1	1202.4	1205.2	1212.2	1214.5	1219.2
7.5°	1108.0	1103.0	1097.3	1094.6	1097.3	1103.0	1108.0	1109.7	1115.7	1124.4	1131.0
10°	1049.0	1042.6	1042.0	1037.9	1042.0	1042.6	1049.0	1055.3	1059.4	1070.5	1078.0
12.5°	1005.7	999.8	993.2	991.4	993.2	999.8	1005.7	1011.2	1012.4	1024.8	1030.1
15°	944.3	939.7	935.6	939.1	935.6	939.7	944.3	947.8	954.2	962.9	968.7
17.5°	893.3	889.5	888.8	884.5	888.8	889.5	893.3	895.3	905.8	911.5	921.4
20°	861.3	858.3	859.5	852.0	859.5	858.3	861.3	866.5	876.9	879.9	890.3
22.5°	835.7	830.0	829.3	827.8	829.3	830.0	835.7	840.4	842.5	851.4	858.7
25°	795.6	792.6	789.8	792.6	789.8	792.6	795.6	800.8	803.1	809.5	816.5
27.5°	760.6	757.1	756.3	756.6	756.3	757.1	760.6	760.1	766.4	771.5	776.6
30°	739.2	733.4	734.0	733.4	734.0	733.4	739.2	739.2	742.7	747.3	752.0
32.5°	715.9	712.0	711.2	710.2	711.2	712.0	715.9	715.1	719.5	725.0	730.1
35°	681.7	681.7	678.7	678.7	678.7	681.7	681.7	683.4	688.0	688.0	693.9
37.5°	649.5	648.8	647.1	647.4	647.1	648.8	649.5	650.8	652.5	655.0	658.7
40°	625.3	624.7	622.9	619.5	622.9	624.7	625.3	627.6	628.8	631.7	634.0
42.5°	602.0	600.1	599.3	598.1	599.3	600.1	602.0	603.5	604.2	608.0	612.6
45°	565.4	565.4	564.3	563.7	564.3	565.4	565.4	565.4	566.0	570.7	573.0
47.5°	529.9	530.9	533.1	532.8	533.1	530.9	529.9	528.9	529.2	531.5	534.2
50°	508.5	509.1	510.8	511.4	510.8	509.1	508.5	506.2	505.0	505.0	506.8
52.5°	484.7	488.2	490.3	490.0	490.3	488.2	484.7	482.9	480.9	478.0	480.7
55°	451.5	455.6	459.7	460.3	459.7	455.6	451.5	446.3	444.0	439.4	441.1
57.5°	418.6	424.3	428.6	430.1	428.6	424.3	418.6	412.3	404.8	402.6	399.3
60°	396.3	403.9	409.1	411.5	409.1	403.9	396.3	390.5	380.6	374.3	372.0
62.5°	375.0	383.4	388.7	389.1	388.7	383.4	375.0	365.8	356.0	348.7	344.1
65°	339.9	348.7	353.4	356.8	353.4	348.7	339.9	330.1	319.0	309.2	303.9
67.5°	302.3	311.0	316.2	318.9	316.2	311.0	302.3	290.1	280.0	268.6	262.4
70°	274.9	283.6	290.6	292.9	290.6	283.6	274.9	260.4	251.7	241.2	235.9
72.5°	247.9	255.7	261.3	264.1	261.3	255.7	247.9	234.3	224.2	213.7	206.6
75°	201.0	211.5	216.8	219.6	216.8	211.5	201.0	193.6	181.9	170.8	165.1
77.5°	155.1	164.5	167.7	169.2	167.7	164.5	155.1	146.2	137.4	129.3	123.6
80°	124.3	130.2	134.2	134.8	134.2	130.2	124.3	117.4	110.4	102.9	97.6
82.5°	95.6	100.4	101.7	103.2	101.7	100.4	95.6	89.5	83.4	77.7	73.4
85°	52.3	54.6	55.2	54.6	55.2	54.6	52.3	48.2	45.3	42.4	40.6
87.5°	20.1	19.7	19.8	20.8	19.8	19.7	20.1	19.2	19.5	18.3	17.3
90°	14.8	14.8	15.5	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1
92.5°	46.6	44.9	44.0	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3
95°	194.6	174.4	169.0	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1
97.5°	448.2	410.5	391.0	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9
100°	609.2	560.8	535.9	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0
102.5°	754.1	719.6	692.6	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1
105°	935.7	913.5	900.1	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8
107.5°	1012.1	1011.9	1007.5	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9
110°	1021.2	1034.1	1038.8	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	995.9	1017.9	1029.6	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8
115°	933.8	966.0	984.9	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3
117.5°	864.7	898.0	916.8	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5
120°	819.9	852.3	870.5	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0
122.5°	782.3	811.9	830.1	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6
125°	733.8	761.4	776.2	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4
127.5°	697.2	721.5	735.6	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9
130°	674.6	696.8	710.2	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3
132.5°	650.8	673.0	685.4	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9
135°	611.9	634.1	646.3	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4
137.5°	572.1	592.3	603.5	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6
140°	547.3	564.8	574.9	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5
142.5°	523.7	538.5	548.0	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6
145°	491.5	502.9	510.3	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3
147.5°	466.2	475.4	479.7	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7
150°	451.8	459.8	462.5	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9
152.5°	439.4	445.8	448.5	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5
155°	422.8	427.5	429.5	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5
157.5°	407.6	411.5	413.4	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4
160°	397.9	401.2	402.6	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0
162.5°	388.7	391.5	391.8	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0
165°	375.7	377.0	377.0	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8
167.5°	363.0	364.2	363.7	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0
170°	355.4	356.1	356.1	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7
172.5°	348.4	349.7	348.6	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9
175°	340.0	340.6	339.3	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6
177.5°	335.0	335.5	333.9	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1309.2	1314.7	1321.7	1326.8	1336.1	1340.3	1345.4	1349.6	1357.0	1364.0	1372.4
5°	1221.0	1230.8	1244.2	1258.7	1275.6	1287.2	1303.5	1313.4	1333.1	1351.2	1368.6
7.5°	1141.0	1153.1	1172.0	1190.6	1212.7	1232.7	1253.0	1275.6	1300.8	1330.6	1355.2
10°	1086.2	1102.4	1122.7	1146.0	1172.8	1195.9	1223.3	1247.7	1278.5	1313.4	1345.9
12.5°	1042.4	1056.4	1079.0	1101.4	1130.0	1158.3	1186.5	1218.8	1254.8	1293.4	1334.3
15°	982.1	993.8	1012.4	1043.1	1072.2	1100.1	1142.5	1172.8	1218.1	1261.0	1310.4
17.5°	930.7	945.0	960.7	987.1	1017.2	1052.1	1089.9	1127.8	1171.6	1226.1	1281.8
20°	899.0	910.6	928.7	949.0	980.9	1015.8	1051.9	1090.2	1143.7	1200.1	1259.9
22.5°	864.6	877.2	897.5	919.7	946.6	980.0	1019.8	1061.9	1117.7	1173.1	1238.0
25°	824.1	832.8	851.4	871.2	897.9	926.3	967.6	1014.1	1069.3	1132.6	1198.9
27.5°	785.8	793.5	810.5	827.7	851.8	885.6	922.5	969.5	1021.5	1085.6	1159.2
30°	758.4	766.5	781.6	800.2	823.5	853.1	890.9	935.0	990.8	1053.6	1130.3
32.5°	734.7	741.8	753.3	771.9	794.6	823.4	858.3	903.4	959.2	1022.9	1098.2
35°	697.9	706.1	714.8	729.4	749.1	777.0	815.4	857.7	911.2	972.8	1042.0
37.5°	661.4	670.3	678.0	691.1	709.1	733.7	766.9	811.1	859.4	918.8	985.2
40°	638.7	645.7	652.0	666.0	684.0	707.2	738.0	777.6	828.7	883.9	939.1
42.5°	615.9	622.4	627.8	640.0	656.6	678.9	708.3	746.8	794.3	845.8	894.5
45°	580.0	584.0	590.4	600.9	614.2	634.6	663.1	697.3	737.4	786.3	822.9
47.5°	541.1	547.5	552.8	562.0	572.9	592.9	620.2	649.4	685.7	722.0	747.8
50°	511.4	517.8	525.4	534.1	544.5	563.1	588.1	617.8	648.5	676.4	698.5
52.5°	483.5	489.4	497.5	505.7	518.5	534.3	555.6	581.9	612.3	632.2	650.7
55°	442.2	445.1	454.4	462.6	474.8	486.4	507.9	531.2	549.7	564.9	580.0
57.5°	400.0	404.0	409.3	416.6	428.8	442.4	457.4	478.0	489.0	496.7	508.5
60°	373.1	374.3	377.7	386.4	395.7	407.9	425.4	439.9	448.1	454.4	464.3
62.5°	343.4	343.5	349.4	355.8	362.7	375.9	390.0	401.8	408.5	411.6	421.1
65°	301.6	300.4	303.9	309.2	317.3	326.0	338.2	348.7	348.1	351.5	357.4
67.5°	259.0	257.8	257.8	262.8	269.4	277.2	285.6	291.6	291.7	296.4	299.3
70°	230.1	226.6	228.9	233.1	235.9	242.4	251.7	254.0	254.5	256.8	259.8
72.5°	200.4	199.2	201.0	202.9	204.8	209.8	217.7	219.1	219.2	220.6	225.3
75°	159.2	158.1	156.9	158.7	161.0	164.5	167.4	169.7	169.1	169.7	173.1
77.5°	119.3	116.1	115.5	116.5	117.0	119.2	122.2	121.9	122.5	122.3	126.3
80°	94.7	90.1	89.5	89.5	90.1	91.3	92.4	93.6	91.8	93.6	94.7
82.5°	69.7	66.8	66.7	66.2	66.4	66.6	67.3	68.0	67.7	68.4	69.1
85°	38.3	37.2	35.5	36.6	36.0	34.3	35.5	33.7	33.1	33.7	34.3
87.5°	15.3	15.7	14.5	14.3	13.6	13.9	12.7	12.0	11.2	11.5	12.7
90°	11.5	10.8	9.4	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7
92.5°	175.7	217.1	220.5	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2
95°	583.7	596.5	486.7	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2
97.5°	738.5	637.0	434.6	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9
100°	776.2	608.0	387.8	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1
102.5°	753.6	556.7	352.2	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5
105°	681.3	488.1	317.8	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1
107.5°	607.5	440.8	303.2	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3
110°	565.5	418.7	298.9	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.3	405.8	298.9	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0
115°	500.2	391.8	300.9	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0
117.5°	479.8	385.0	305.4	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1
120°	468.6	381.7	309.7	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9
122.5°	458.8	379.0	313.4	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3
125°	445.7	375.7	319.8	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5
127.5°	433.5	374.0	326.9	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7
130°	425.5	373.0	331.2	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6
132.5°	419.0	373.0	336.0	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1
135°	411.3	373.0	342.7	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8
137.5°	404.5	373.8	348.7	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9
140°	401.2	374.3	351.4	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3
142.5°	398.6	374.9	353.0	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8
145°	394.5	374.3	354.8	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2
147.5°	390.3	372.6	355.4	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0
150°	387.1	370.9	355.4	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0
152.5°	383.3	368.8	354.9	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5
155°	377.0	364.9	353.4	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5
157.5°	371.1	360.8	351.7	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4
160°	366.3	358.2	350.1	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3
162.5°	361.9	354.9	348.4	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1
165°	355.4	350.1	346.0	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5
167.5°	349.1	345.3	342.2	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3
170°	345.3	342.7	340.6	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6
172.5°	341.6	339.4	338.5	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7
175°	336.6	336.0	336.0	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2
177.5°	334.4	333.9	333.9	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1376.6	1383.1	1387.2	1395.2	1401.7	1405.4	1408.7	1411.4	1414.7	1417.5	1425.4
5°	1385.4	1400.5	1413.3	1433.0	1451.1	1465.1	1480.1	1493.5	1504.5	1520.3	1532.4
7.5°	1381.6	1408.4	1436.6	1467.1	1498.4	1527.4	1554.2	1579.2	1601.8	1629.3	1653.3
10°	1377.9	1414.5	1450.5	1491.8	1534.2	1570.2	1604.0	1638.2	1663.2	1698.1	1727.7
12.5°	1375.1	1418.2	1461.6	1511.3	1557.9	1608.8	1653.6	1678.7	1716.7	1744.6	1779.8
15°	1363.3	1420.3	1480.1	1535.9	1602.1	1649.2	1688.8	1737.6	1773.1	1808.4	1846.8
17.5°	1342.3	1406.8	1473.8	1546.9	1610.4	1661.0	1711.9	1758.9	1801.3	1848.8	1896.6
20°	1332.6	1397.1	1473.8	1548.7	1610.9	1663.8	1716.1	1767.8	1814.3	1875.3	1930.5
22.5°	1312.1	1390.1	1460.8	1533.9	1597.8	1655.4	1714.7	1773.4	1835.2	1904.1	1973.3
25°	1275.6	1354.6	1429.6	1501.7	1566.2	1638.2	1701.6	1780.0	1859.1	1950.3	2036.3
27.5°	1237.7	1313.4	1382.1	1451.6	1526.9	1608.4	1690.7	1779.7	1883.1	1998.3	2119.6
30°	1207.0	1278.5	1345.3	1416.8	1495.2	1587.1	1677.1	1782.9	1902.6	2032.2	2176.3
32.5°	1171.2	1237.1	1302.1	1377.8	1463.2	1560.1	1665.1	1781.1	1924.9	2072.2	2220.5
35°	1110.0	1165.2	1232.0	1312.8	1409.3	1520.3	1641.7	1778.8	1943.9	2113.0	2237.9
37.5°	1037.3	1088.7	1159.2	1247.7	1348.8	1467.9	1612.1	1774.8	1950.1	2084.9	2125.2
40°	988.5	1036.1	1109.4	1201.2	1304.7	1430.7	1588.8	1760.8	1930.5	2016.5	1983.4
42.5°	936.4	986.4	1057.7	1148.7	1260.0	1397.3	1559.5	1731.6	1873.8	1906.3	1791.8
45°	854.3	905.9	976.3	1068.2	1187.8	1336.6	1505.7	1662.1	1744.0	1685.3	1508.0
47.5°	777.9	826.4	891.6	986.3	1109.8	1263.7	1426.6	1551.3	1557.8	1417.7	1228.4
50°	725.8	770.6	836.3	931.0	1053.6	1209.4	1356.3	1454.6	1410.4	1251.7	1069.9
52.5°	674.7	718.5	783.3	877.0	998.2	1141.0	1277.8	1346.7	1263.5	1100.7	945.3
55°	600.9	639.2	702.6	789.2	904.2	1036.7	1153.0	1176.8	1068.7	908.3	782.2
57.5°	528.8	564.6	622.2	702.0	807.2	924.5	1015.5	1010.4	896.1	758.5	658.4
60°	480.0	514.9	566.0	643.9	739.8	840.9	918.8	900.2	786.9	668.3	584.0
62.5°	436.4	467.4	515.8	583.9	671.4	765.1	829.1	801.6	690.6	586.9	520.4
65°	372.0	398.0	439.4	497.5	570.1	647.4	696.8	661.3	566.6	485.9	432.4
67.5°	310.5	331.4	366.0	412.3	474.3	536.4	566.5	530.8	455.0	396.1	356.5
70°	271.4	290.0	316.7	358.0	412.0	464.3	487.0	455.0	389.9	339.4	310.9
72.5°	232.3	247.7	271.1	308.2	351.5	396.9	416.8	386.2	332.8	290.1	263.5
75°	179.6	190.0	206.3	231.9	266.1	302.2	313.2	286.5	252.2	220.2	202.9
77.5°	128.5	137.4	149.7	165.8	190.1	213.0	222.7	207.2	180.7	160.5	146.2
80°	98.8	103.4	113.9	127.3	146.5	161.0	167.4	157.5	138.9	123.8	112.7
82.5°	70.4	75.1	81.4	92.4	104.6	114.5	121.3	114.7	101.3	89.4	83.0
85°	34.3	37.2	40.6	45.3	54.6	60.4	59.8	55.8	50.5	45.9	42.4
87.5°	12.4	13.1	14.7	17.3	19.0	21.0	22.2	21.4	19.8	18.6	17.3
90°	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1
92.5°	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3
95°	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1
97.5°	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9
100°	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0
102.5°	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1
105°	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8
107.5°	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9
110°	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9





TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8
115°	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3
117.5°	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5
120°	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0
122.5°	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6
125°	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4
127.5°	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9
130°	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3
132.5°	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9
135°	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4
137.5°	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6
140°	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5
142.5°	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6
145°	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3
147.5°	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7
150°	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9
152.5°	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5
155°	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5
157.5°	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4
160°	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0
162.5°	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0
165°	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8
167.5°	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0
170°	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7
172.5°	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9
175°	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6
177.5°	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1431.9	1435.6	1443.6	1440.7	1444.5	1446.3	1448.2
5°	1547.6	1566.2	1574.3	1573.1	1585.4	1582.4	1579.5
7.5°	1678.2	1697.7	1708.7	1722.3	1730.2	1730.7	1737.6
10°	1752.1	1777.7	1788.1	1802.7	1812.0	1817.2	1816.6
12.5°	1808.9	1828.9	1852.3	1859.4	1872.0	1878.5	1876.1
15°	1877.1	1909.0	1933.5	1945.6	1961.4	1966.0	1972.4
17.5°	1937.9	1980.8	2009.3	2047.2	2061.5	2070.2	2065.1
20°	1984.0	2040.4	2068.8	2114.2	2139.2	2152.5	2147.9
22.5°	2038.4	2099.4	2152.1	2191.3	2229.3	2247.4	2251.1
25°	2131.6	2215.3	2292.6	2344.3	2391.3	2402.4	2426.8
27.5°	2235.8	2334.4	2417.1	2471.4	2504.2	2516.5	2524.2
30°	2301.3	2399.5	2461.7	2496.6	2507.0	2505.9	2504.6
32.5°	2333.4	2394.9	2406.8	2397.0	2373.1	2352.9	2331.8
35°	2287.9	2242.0	2173.4	2085.1	2020.0	1954.4	1947.9
37.5°	2057.7	1910.9	1796.7	1669.2	1595.7	1550.2	1518.9
40°	1841.0	1674.2	1535.9	1428.4	1353.5	1323.8	1294.8
42.5°	1605.8	1446.5	1324.0	1234.1	1177.8	1144.9	1121.8
45°	1304.7	1164.0	1068.2	1003.1	958.3	932.7	918.2
47.5°	1069.0	965.0	883.6	836.6	805.7	785.8	785.9
50°	942.6	843.3	789.2	752.0	725.2	709.6	712.5
52.5°	830.5	756.3	710.2	679.0	659.3	649.6	649.3
55°	694.5	641.0	610.8	588.1	574.7	563.7	566.0
57.5°	594.0	549.0	528.7	509.9	500.6	496.2	489.7
60°	531.8	496.9	479.4	464.3	455.0	451.5	445.1
62.5°	476.4	449.0	432.0	419.7	411.3	410.2	405.2
65°	400.4	379.4	364.4	358.5	349.8	347.5	347.5
67.5°	330.1	315.1	303.3	298.0	294.2	294.7	292.0
70°	285.9	273.7	266.1	260.4	257.4	258.0	255.7
72.5°	250.1	236.5	229.9	226.4	222.6	224.1	223.2
75°	189.4	182.4	179.0	175.5	173.1	172.0	170.8
77.5°	139.1	132.9	130.3	128.3	128.6	125.9	128.1
80°	107.5	102.3	100.6	97.6	97.0	97.0	96.4
82.5°	78.7	75.8	74.5	72.1	71.0	72.0	70.4
85°	40.6	38.3	37.8	37.8	36.6	35.5	38.3
87.5°	17.4	15.7	16.0	15.5	15.5	15.2	14.3
90°	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333270-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)