

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331340-927

Luminaire Tested: **SA2XXDIP-C675D530U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331340-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3820.4 lumens  
Efficiency: N/A  
Efficacy: 94.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331340-927  
CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	59	58	57	57	57	57	52	
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	49	45	
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42	42	42	42	39	
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	37	37	37	34	
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	33	33	33	30	
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	29	29	29	26	
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	26	26	26	24	
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	24	24	24	21	
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	21	21	21	19	
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	20	20	20	18	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.2	2.6
10°-20°	291.3	7.6
20°-30°	422.8	11.1
30°-40°	446.2	11.7
40°-50°	395.0	10.3
50°-60°	315.3	8.3
60°-70°	214.3	5.6
70°-80°	109.9	2.9
80°-90°	28.6	0.7
90°-100°	33.9	0.9
100°-110°	105.4	2.8
110°-120°	180.1	4.7
120°-130°	236.8	6.2
130°-140°	265.8	7.0
140°-150°	260.6	6.8
150°-160°	218.6	5.7
160°-170°	145.0	3.8
170°-180°	50.7	1.3
0°-30°	814.3	21.3
0°-40°	1260.5	33.0
0°-60°	1970.8	51.6
0°-90°	2323.6	60.8
90°-120°	319.4	8.4
90°-150°	1082.6	28.3
90°-180°	1497.0	39.2
0°-180°	3820.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	24
90°	15	0	15	0	15	8
95°	28	24	28	24	28	31
105°	100	97	100	97	100	105
115°	181	181	181	181	181	178
125°	264	263	264	263	264	235
135°	344	340	344	340	344	265
145°	417	413	417	413	417	261
155°	476	472	476	472	476	219
165°	514	514	514	514	514	145
175°	533	534	533	534	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	11.5	11.5	11.8	11.4	11.4	11.7	11.8	11.5	11.9	12.2	12.1
90°	15.4	15.3	15.1	15.1	15.0	15.0	15.2	15.4	15.6	15.8	13.6
92.5°	14.7	14.7	14.6	14.6	14.6	14.5	14.5	14.4	14.4	14.3	13.9
95°	28.0	28.2	28.4	28.6	28.8	28.9	28.9	28.9	28.9	28.9	28.7
97.5°	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.2
100°	61.9	62.0	62.1	62.2	62.3	62.3	62.3	62.3	62.3	62.3	62.0
102.5°	77.1	77.2	77.2	77.4	77.5	77.5	77.4	77.3	77.2	77.2	76.8
105°	100.3	100.3	100.3	100.3	100.3	100.2	100.0	99.8	99.6	99.4	99.2
107.5°	122.2	122.6	123.1	123.5	124.0	124.2	124.1	124.1	124.0	123.9	123.9
110°	139.1	139.4	139.7	140.1	140.4	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.4	155.6	155.8	156.1	156.3	156.5	156.8	157.0	157.2	157.5	157.6
115°	180.7	181.0	181.3	181.6	181.9	182.1	182.2	182.3	182.4	182.5	182.7
117.5°	204.8	205.1	205.4	205.7	206.0	206.3	206.5	206.8	207.0	207.2	207.8
120°	221.8	222.1	222.4	222.7	223.0	223.2	223.2	223.2	223.2	223.2	223.9
122.5°	238.4	238.7	238.8	239.1	239.3	239.6	239.8	240.0	240.3	240.5	241.1
125°	263.8	263.9	264.0	264.1	264.2	264.4	264.7	265.0	265.3	265.6	265.9
127.5°	286.9	287.2	287.6	287.9	288.2	288.6	288.9	289.3	289.6	290.0	290.4
130°	303.6	304.0	304.4	304.8	305.1	305.5	305.7	305.9	306.1	306.3	306.5
132.5°	319.5	319.8	320.1	320.4	320.8	321.2	321.5	322.0	322.5	322.9	322.9
135°	344.2	344.5	344.8	345.2	345.4	345.6	345.7	345.9	345.9	346.0	345.9
137.5°	366.6	367.0	367.4	367.8	368.2	368.4	368.5	368.6	368.7	368.8	368.5
140°	382.1	382.5	382.9	383.3	383.8	384.0	384.0	384.0	384.0	384.0	383.5
142.5°	396.2	396.6	397.0	397.4	397.8	398.0	397.9	397.8	397.8	397.7	397.4
145°	417.4	417.8	418.2	418.6	419.0	419.1	419.1	419.0	418.8	418.7	418.2
147.5°	436.3	436.7	437.0	437.4	437.8	437.9	437.7	437.4	437.2	437.0	436.6
150°	448.6	448.9	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6	448.1
152.5°	460.2	460.5	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2	459.6
155°	475.7	475.9	476.3	476.6	476.9	476.8	476.3	475.8	475.3	474.8	474.4
157.5°	489.0	489.6	490.0	490.5	491.0	490.9	490.2	489.5	488.9	488.1	488.0
160°	497.3	497.7	498.2	498.6	499.0	498.8	498.3	497.6	497.1	496.5	496.4
162.5°	504.6	505.1	505.6	506.0	506.5	506.4	505.7	505.0	504.4	503.7	503.6
165°	514.0	514.6	515.1	515.6	516.1	515.9	515.3	514.6	513.9	513.2	513.2
167.5°	521.8	522.4	522.9	523.4	523.9	523.9	523.2	522.4	521.7	521.0	521.0
170°	525.9	526.4	527.0	527.6	528.2	528.1	527.5	526.8	526.1	525.4	525.5
172.5°	529.1	529.7	530.3	530.9	531.5	531.4	530.8	530.0	529.3	528.6	528.7
175°	532.6	533.2	533.8	534.4	535.0	535.0	534.2	533.5	532.8	532.1	532.3
177.5°	534.2	534.7	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2	534.4
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	12.0	11.6	11.1	11.4	10.2	10.0	8.4	7.2	7.1	7.1	6.7
90°	11.4	9.2	7.0	5.3	4.0	2.9	1.7	0.5	1.7	2.9	4.0
92.5°	13.3	12.8	12.3	11.6	10.7	9.8	9.0	8.1	9.0	9.8	10.7
95°	28.5	28.3	28.1	27.5	26.5	25.5	24.5	23.5	24.5	25.5	26.5
97.5°	47.8	47.5	47.1	46.4	45.6	44.7	43.8	42.9	43.8	44.7	45.6
100°	61.7	61.5	61.2	60.6	59.8	58.9	58.1	57.4	58.1	58.9	59.8
102.5°	76.4	76.0	75.7	75.1	74.5	73.8	73.2	72.6	73.2	73.8	74.5
105°	98.9	98.8	98.5	98.3	98.0	97.8	97.4	97.1	97.4	97.8	98.0
107.5°	123.9	123.9	123.9	123.7	123.2	122.8	122.3	121.9	122.3	122.8	123.2
110°	140.5	140.5	140.5	140.2	139.6	138.9	138.4	137.8	138.4	138.9	139.6





TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	157.6	157.7	157.8	157.6	156.9	156.3	155.7	155.1	155.7	156.3	156.9
115°	182.9	183.1	183.3	183.1	182.5	181.9	181.3	180.7	181.3	181.9	182.5
117.5°	208.3	209.0	209.5	209.4	208.6	207.8	207.0	206.2	207.0	207.8	208.6
120°	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.9	224.7	225.5
122.5°	241.6	242.2	242.7	242.6	241.6	240.7	239.6	238.7	239.6	240.7	241.6
125°	266.3	266.5	266.8	266.5	265.6	264.7	263.8	262.9	263.8	264.7	265.6
127.5°	290.7	291.1	291.4	291.0	289.9	288.8	287.6	286.5	287.6	288.8	289.9
130°	306.7	306.9	307.0	306.5	305.2	303.9	302.6	301.3	302.6	303.9	305.2
132.5°	322.8	322.8	322.7	322.2	321.2	320.0	319.0	317.9	319.0	320.0	321.2
135°	345.6	345.4	345.2	344.6	343.5	342.4	341.3	340.2	341.3	342.4	343.5
137.5°	368.3	368.0	367.7	367.2	366.3	365.4	364.5	363.5	364.5	365.4	366.3
140°	382.9	382.5	382.0	381.3	380.3	379.5	378.6	377.6	378.6	379.5	380.3
142.5°	397.0	396.7	396.3	395.7	394.8	394.0	393.0	392.1	393.0	394.0	394.8
145°	417.6	416.9	416.4	415.7	415.0	414.3	413.6	412.9	413.6	414.3	415.0
147.5°	436.2	435.8	435.4	434.7	434.0	433.1	432.2	431.4	432.2	433.1	434.0
150°	447.7	447.3	446.9	446.5	445.8	445.3	444.7	444.1	444.7	445.3	445.8
152.5°	459.1	458.7	458.2	457.6	457.1	456.5	455.9	455.3	455.9	456.5	457.1
155°	474.2	473.9	473.6	473.2	472.9	472.7	472.4	472.1	472.4	472.7	472.9
157.5°	487.8	487.6	487.4	487.3	487.0	486.8	486.6	486.4	486.6	486.8	487.0
160°	496.2	496.1	496.1	495.9	495.7	495.5	495.3	495.1	495.3	495.5	495.7
162.5°	503.5	503.4	503.3	503.2	503.2	503.1	503.1	503.0	503.1	503.1	503.2
165°	513.2	513.2	513.2	513.3	513.3	513.4	513.5	513.7	513.5	513.4	513.3
167.5°	521.1	521.1	521.1	521.3	521.6	521.9	522.2	522.4	522.2	521.9	521.6
170°	525.5	525.7	525.8	526.0	526.2	526.6	526.9	527.2	526.9	526.6	526.2
172.5°	528.9	528.9	529.0	529.3	529.5	529.8	530.1	530.4	530.1	529.8	529.5
175°	532.6	532.7	533.0	533.2	533.5	533.8	534.1	534.4	534.1	533.8	533.5
177.5°	534.6	534.7	534.9	535.0	535.3	535.5	535.8	536.1	535.8	535.5	535.3
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	6.6	6.6	6.7	7.1	7.3	7.4	7.0	7.0	6.9	6.3	6.3
90°	5.3	7.0	9.2	11.4	13.6	15.8	15.6	15.4	15.2	15.0	15.0
92.5°	11.6	12.3	12.8	13.3	13.9	14.3	14.4	14.4	14.5	14.5	14.6
95°	27.5	28.1	28.3	28.5	28.7	28.9	28.9	28.9	28.9	28.9	28.8
97.5°	46.4	47.1	47.5	47.8	48.2	48.6	48.6	48.6	48.6	48.6	48.6
100°	60.6	61.2	61.5	61.7	62.0	62.3	62.3	62.3	62.3	62.3	62.3
102.5°	75.1	75.7	76.0	76.4	76.8	77.2	77.2	77.3	77.4	77.5	77.5
105°	98.3	98.5	98.8	98.9	99.2	99.4	99.6	99.8	100.0	100.2	100.3
107.5°	123.7	123.9	123.9	123.9	123.9	123.9	124.0	124.1	124.1	124.2	124.0
110°	140.2	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.5	140.4



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	157.6	157.8	157.7	157.6	157.6	157.5	157.2	157.0	156.8	156.5	156.3
115°	183.1	183.3	183.1	182.9	182.7	182.5	182.4	182.3	182.2	182.1	181.9
117.5°	209.4	209.5	209.0	208.3	207.8	207.2	207.0	206.8	206.5	206.3	206.0
120°	226.4	226.4	225.5	224.7	223.9	223.2	223.2	223.2	223.2	223.2	223.0
122.5°	242.6	242.7	242.2	241.6	241.1	240.5	240.3	240.0	239.8	239.6	239.3
125°	266.5	266.8	266.5	266.3	265.9	265.6	265.3	265.0	264.7	264.4	264.2
127.5°	291.0	291.4	291.1	290.7	290.4	290.0	289.6	289.3	288.9	288.6	288.2
130°	306.5	307.0	306.9	306.7	306.5	306.3	306.1	305.9	305.7	305.5	305.1
132.5°	322.2	322.7	322.8	322.8	322.9	322.9	322.5	322.0	321.5	321.2	320.8
135°	344.6	345.2	345.4	345.6	345.9	346.0	345.9	345.9	345.7	345.6	345.4
137.5°	367.2	367.7	368.0	368.3	368.5	368.8	368.7	368.6	368.5	368.4	368.2
140°	381.3	382.0	382.5	382.9	383.5	384.0	384.0	384.0	384.0	384.0	383.8
142.5°	395.7	396.3	396.7	397.0	397.4	397.7	397.8	397.8	397.9	398.0	397.8
145°	415.7	416.4	416.9	417.6	418.2	418.7	418.8	419.0	419.1	419.1	419.0
147.5°	434.7	435.4	435.8	436.2	436.6	437.0	437.2	437.4	437.7	437.9	437.8
150°	446.5	446.9	447.3	447.7	448.1	448.6	448.9	449.2	449.5	449.8	449.8
152.5°	457.6	458.2	458.7	459.1	459.6	460.2	460.5	460.9	461.3	461.7	461.7
155°	473.2	473.6	473.9	474.2	474.4	474.8	475.3	475.8	476.3	476.8	476.9
157.5°	487.3	487.4	487.6	487.8	488.0	488.1	488.9	489.5	490.2	490.9	491.0
160°	495.9	496.1	496.1	496.2	496.4	496.5	497.1	497.6	498.3	498.8	499.0
162.5°	503.2	503.3	503.4	503.5	503.6	503.7	504.4	505.0	505.7	506.4	506.5
165°	513.3	513.2	513.2	513.2	513.2	513.2	513.9	514.6	515.3	515.9	516.1
167.5°	521.3	521.1	521.1	521.1	521.0	521.0	521.7	522.4	523.2	523.9	523.9
170°	526.0	525.8	525.7	525.5	525.5	525.4	526.1	526.8	527.5	528.1	528.2
172.5°	529.3	529.0	528.9	528.9	528.7	528.6	529.3	530.0	530.8	531.4	531.5
175°	533.2	533.0	532.7	532.6	532.3	532.1	532.8	533.5	534.2	535.0	535.0
177.5°	535.0	534.9	534.7	534.6	534.4	534.2	534.7	535.2	535.7	536.1	536.1
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	6.3	5.9	5.9	5.6	5.9	5.9	6.3	6.3	6.3	6.9	7.0
90°	15.1	15.1	15.3	15.4	15.3	15.1	15.1	15.0	15.0	15.2	15.4
92.5°	14.6	14.6	14.7	14.7	14.7	14.6	14.6	14.6	14.5	14.5	14.4
95°	28.6	28.4	28.2	28.0	28.2	28.4	28.6	28.8	28.9	28.9	28.9
97.5°	48.6	48.6	48.6	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6
100°	62.2	62.1	62.0	61.9	62.0	62.1	62.2	62.3	62.3	62.3	62.3
102.5°	77.4	77.2	77.2	77.1	77.2	77.2	77.4	77.5	77.5	77.4	77.3
105°	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.2	100.0	99.8
107.5°	123.5	123.1	122.6	122.2	122.6	123.1	123.5	124.0	124.2	124.1	124.1
110°	140.1	139.7	139.4	139.1	139.4	139.7	140.1	140.4	140.5	140.5	140.5



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	156.1	155.8	155.6	155.4	155.6	155.8	156.1	156.3	156.5	156.8	157.0
115°	181.6	181.3	181.0	180.7	181.0	181.3	181.6	181.9	182.1	182.2	182.3
117.5°	205.7	205.4	205.1	204.8	205.1	205.4	205.7	206.0	206.3	206.5	206.8
120°	222.7	222.4	222.1	221.8	222.1	222.4	222.7	223.0	223.2	223.2	223.2
122.5°	239.1	238.8	238.7	238.4	238.7	238.8	239.1	239.3	239.6	239.8	240.0
125°	264.1	264.0	263.9	263.8	263.9	264.0	264.1	264.2	264.4	264.7	265.0
127.5°	287.9	287.6	287.2	286.9	287.2	287.6	287.9	288.2	288.6	288.9	289.3
130°	304.8	304.4	304.0	303.6	304.0	304.4	304.8	305.1	305.5	305.7	305.9
132.5°	320.4	320.1	319.8	319.5	319.8	320.1	320.4	320.8	321.2	321.5	322.0
135°	345.2	344.8	344.5	344.2	344.5	344.8	345.2	345.4	345.6	345.7	345.9
137.5°	367.8	367.4	367.0	366.6	367.0	367.4	367.8	368.2	368.4	368.5	368.6
140°	383.3	382.9	382.5	382.1	382.5	382.9	383.3	383.8	384.0	384.0	384.0
142.5°	397.4	397.0	396.6	396.2	396.6	397.0	397.4	397.8	398.0	397.9	397.8
145°	418.6	418.2	417.8	417.4	417.8	418.2	418.6	419.0	419.1	419.1	419.0
147.5°	437.4	437.0	436.7	436.3	436.7	437.0	437.4	437.8	437.9	437.7	437.4
150°	449.5	449.2	448.9	448.6	448.9	449.2	449.5	449.8	449.8	449.5	449.2
152.5°	461.3	460.9	460.5	460.2	460.5	460.9	461.3	461.7	461.7	461.3	460.9
155°	476.6	476.3	475.9	475.7	475.9	476.3	476.6	476.9	476.8	476.3	475.8
157.5°	490.5	490.0	489.6	489.0	489.6	490.0	490.5	491.0	490.9	490.2	489.5
160°	498.6	498.2	497.7	497.3	497.7	498.2	498.6	499.0	498.8	498.3	497.6
162.5°	506.0	505.6	505.1	504.6	505.1	505.6	506.0	506.5	506.4	505.7	505.0
165°	515.6	515.1	514.6	514.0	514.6	515.1	515.6	516.1	515.9	515.3	514.6
167.5°	523.4	522.9	522.4	521.8	522.4	522.9	523.4	523.9	523.9	523.2	522.4
170°	527.6	527.0	526.4	525.9	526.4	527.0	527.6	528.2	528.1	527.5	526.8
172.5°	530.9	530.3	529.7	529.1	529.7	530.3	530.9	531.5	531.4	530.8	530.0
175°	534.4	533.8	533.2	532.6	533.2	533.8	534.4	535.0	535.0	534.2	533.5
177.5°	535.7	535.2	534.7	534.2	534.7	535.2	535.7	536.1	536.1	535.7	535.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	7.0	7.4	7.3	7.1	6.7	6.6	6.6	6.7	7.1	7.1	7.2
90°	15.6	15.8	13.6	11.4	9.2	7.0	5.3	4.0	2.9	1.7	0.5
92.5°	14.4	14.3	13.9	13.3	12.8	12.3	11.6	10.7	9.8	9.0	8.1
95°	28.9	28.9	28.7	28.5	28.3	28.1	27.5	26.5	25.5	24.5	23.5
97.5°	48.6	48.6	48.2	47.8	47.5	47.1	46.4	45.6	44.7	43.8	42.9
100°	62.3	62.3	62.0	61.7	61.5	61.2	60.6	59.8	58.9	58.1	57.4
102.5°	77.2	77.2	76.8	76.4	76.0	75.7	75.1	74.5	73.8	73.2	72.6
105°	99.6	99.4	99.2	98.9	98.8	98.5	98.3	98.0	97.8	97.4	97.1
107.5°	124.0	123.9	123.9	123.9	123.9	123.9	123.7	123.2	122.8	122.3	121.9
110°	140.5	140.5	140.5	140.5	140.5	140.5	140.2	139.6	138.9	138.4	137.8



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	157.2	157.5	157.6	157.6	157.7	157.8	157.6	156.9	156.3	155.7	155.1
115°	182.4	182.5	182.7	182.9	183.1	183.3	183.1	182.5	181.9	181.3	180.7
117.5°	207.0	207.2	207.8	208.3	209.0	209.5	209.4	208.6	207.8	207.0	206.2
120°	223.2	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2
122.5°	240.3	240.5	241.1	241.6	242.2	242.7	242.6	241.6	240.7	239.6	238.7
125°	265.3	265.6	265.9	266.3	266.5	266.8	266.5	265.6	264.7	263.8	262.9
127.5°	289.6	290.0	290.4	290.7	291.1	291.4	291.0	289.9	288.8	287.6	286.5
130°	306.1	306.3	306.5	306.7	306.9	307.0	306.5	305.2	303.9	302.6	301.3
132.5°	322.5	322.9	322.9	322.8	322.8	322.7	322.2	321.2	320.0	319.0	317.9
135°	345.9	346.0	345.9	345.6	345.4	345.2	344.6	343.5	342.4	341.3	340.2
137.5°	368.7	368.8	368.5	368.3	368.0	367.7	367.2	366.3	365.4	364.5	363.5
140°	384.0	384.0	383.5	382.9	382.5	382.0	381.3	380.3	379.5	378.6	377.6
142.5°	397.8	397.7	397.4	397.0	396.7	396.3	395.7	394.8	394.0	393.0	392.1
145°	418.8	418.7	418.2	417.6	416.9	416.4	415.7	415.0	414.3	413.6	412.9
147.5°	437.2	437.0	436.6	436.2	435.8	435.4	434.7	434.0	433.1	432.2	431.4
150°	448.9	448.6	448.1	447.7	447.3	446.9	446.5	445.8	445.3	444.7	444.1
152.5°	460.5	460.2	459.6	459.1	458.7	458.2	457.6	457.1	456.5	455.9	455.3
155°	475.3	474.8	474.4	474.2	473.9	473.6	473.2	472.9	472.7	472.4	472.1
157.5°	488.9	488.1	488.0	487.8	487.6	487.4	487.3	487.0	486.8	486.6	486.4
160°	497.1	496.5	496.4	496.2	496.1	496.1	495.9	495.7	495.5	495.3	495.1
162.5°	504.4	503.7	503.6	503.5	503.4	503.3	503.2	503.2	503.1	503.1	503.0
165°	513.9	513.2	513.2	513.2	513.2	513.2	513.3	513.3	513.4	513.5	513.7
167.5°	521.7	521.0	521.0	521.1	521.1	521.1	521.3	521.6	521.9	522.2	522.4
170°	526.1	525.4	525.5	525.5	525.7	525.8	526.0	526.2	526.6	526.9	527.2
172.5°	529.3	528.6	528.7	528.9	528.9	529.0	529.3	529.5	529.8	530.1	530.4
175°	532.8	532.1	532.3	532.6	532.7	533.0	533.2	533.5	533.8	534.1	534.4
177.5°	534.7	534.2	534.4	534.6	534.7	534.9	535.0	535.3	535.5	535.8	536.1
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.4	10.0	10.2	11.4	11.1	11.6	12.0	12.1	12.2	11.9	11.5
90°	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6	15.4
92.5°	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4	14.4
95°	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9	28.9
97.5°	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6	48.6
100°	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3	62.3
102.5°	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2	77.3
105°	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6	99.8
107.5°	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0	124.1
110°	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5	140.5





TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2	157.0
115°	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4	182.3
117.5°	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0	206.8
120°	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2	223.2
122.5°	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3	240.0
125°	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3	265.0
127.5°	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6	289.3
130°	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1	305.9
132.5°	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5	322.0
135°	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9	345.9
137.5°	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7	368.6
140°	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0	384.0
142.5°	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8	397.8
145°	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8	419.0
147.5°	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2	437.4
150°	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9	449.2
152.5°	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5	460.9
155°	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3	475.8
157.5°	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9	489.5
160°	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1	497.6
162.5°	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4	505.0
165°	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9	514.6
167.5°	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7	522.4
170°	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1	526.8
172.5°	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3	530.0
175°	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8	533.5
177.5°	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7	535.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	11.8	11.7	11.4	11.4	11.8	11.5	11.5
90°	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.4	140.1	139.7	139.4	139.1



TEST NUMBER: P331340-927

CATALOG NUMBER: SA2XXDIP-C675D530U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)