

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333276-935

Luminaire Tested: **S125DIP-S1090D810U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333276-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D810U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6328.9 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		66	66	66	60
1	100	96	92	88	93	90	86	83	78	76	73		68	66	64		58	57	55	51
2	91	83	77	72	85	78	73	68	68	64	61		59	56	53		51	49	47	42
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43		47	42	39		40	37	34	31
5	70	58	50	43	65	55	47	41	48	42	37		42	37	34		36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33		38	33	29		33	29	26	23
7	60	47	39	33	56	44	37	32	39	33	29		35	30	26		30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26		32	27	23		28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23		29	24	21		26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21		27	22	19		24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9489	9489	9489
5°	9510	9419	9479
10°	9452	9353	9406
15°	9349	9240	9279
20°	9203	9082	9099
25°	9045	8896	8888
30°	8850	8694	8651
35°	8642	8476	8358
40°	8427	8241	8123
45°	8195	8026	7867
50°	7941	7766	7533
55°	7696	7473	7264
60°	7401	7177	6921
65°	7051	6820	6589
70°	6717	6409	6190
75°	6119	5916	5712
80°	5449	5359	5229
85°	4735	4824	4565



TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.5	2.2
10°-20°	391.3	6.2
20°-30°	577.8	9.1
30°-40°	674.2	10.7
40°-50°	677.1	10.7
50°-60°	594.4	9.4
60°-70°	442.9	7.0
70°-80°	253.2	4.0
80°-90°	75.5	1.2
90°-100°	242.0	3.8
100°-110°	520.3	8.2
110°-120°	488.3	7.7
120°-130°	395.7	6.3
130°-140°	317.6	5.0
140°-150°	239.7	3.8
150°-160°	168.7	2.7
160°-170°	99.4	1.6
170°-180°	32.3	0.5
0°-30°	1107.6	17.5
0°-40°	1781.8	28.2
0°-60°	3053.3	48.2
0°-90°	3824.9	60.4
90°-120°	1250.6	19.8
90°-150°	2203.6	34.8
90°-180°	2504.0	39.6
0°-180°	6328.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1469	1469	1469	1469	1469	
5°	1467	1464	1453	1463	1462	139
15°	1398	1394	1382	1388	1388	394
25°	1269	1263	1248	1250	1247	584
35°	1096	1091	1075	1069	1060	685
45°	897	892	879	865	861	691
55°	684	679	664	653	645	610
65°	461	458	446	436	431	458
75°	245	243	237	234	229	261
85°	64	65	65	64	62	71
90°	1	6	11	14	16	5
95°	22	66	596	271	158	24
105°	76	106	488	961	892	80
115°	136	164	392	845	994	134
125°	188	221	376	672	783	167
135°	221	266	373	563	650	171
145°	257	295	374	466	513	161
155°	294	316	365	412	430	135
165°	320	329	350	371	377	90
175°	333	333	336	340	339	32
180°	334	334	334	334	334	



TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1472.9	1472.3	1471.6	1471.0	1470.4	1469.0	1467.0	1464.9	1462.8	1460.8	1462.8
5°	1466.9	1466.4	1465.9	1465.3	1464.8	1463.3	1460.7	1458.1	1455.5	1452.9	1455.3
7.5°	1453.4	1452.9	1452.3	1451.8	1451.3	1449.6	1446.7	1443.9	1441.1	1438.2	1440.5
10°	1441.3	1440.8	1440.3	1439.8	1439.2	1437.5	1434.7	1431.8	1429.0	1426.2	1428.2
12.5°	1426.4	1425.5	1424.5	1423.6	1422.7	1420.9	1418.2	1415.7	1413.0	1410.3	1412.0
15°	1398.3	1397.5	1396.7	1395.9	1395.2	1393.4	1390.5	1387.7	1384.8	1382.0	1383.3
17.5°	1366.0	1364.9	1363.7	1362.5	1361.4	1359.3	1356.4	1353.5	1350.6	1347.6	1349.2
20°	1339.0	1338.5	1338.0	1337.5	1337.0	1335.0	1331.6	1328.3	1324.9	1321.5	1323.4
22.5°	1312.0	1311.1	1310.2	1309.2	1308.3	1306.2	1303.1	1299.9	1296.8	1293.7	1294.9
25°	1269.3	1268.0	1266.7	1265.4	1264.1	1261.8	1258.4	1255.1	1251.7	1248.4	1248.9
27.5°	1219.3	1218.5	1217.7	1216.9	1216.2	1214.1	1210.6	1207.1	1203.7	1200.2	1200.3
30°	1186.7	1185.9	1185.2	1184.4	1183.6	1181.3	1177.4	1173.5	1169.7	1165.8	1165.3
32.5°	1151.4	1150.2	1149.0	1147.8	1146.7	1144.4	1140.8	1137.4	1133.9	1130.5	1129.5
35°	1096.1	1095.0	1094.0	1093.0	1091.9	1089.6	1086.0	1082.4	1078.7	1075.1	1073.8
37.5°	1038.6	1037.3	1036.0	1034.7	1033.5	1031.1	1027.7	1024.3	1020.9	1017.5	1015.5
40°	999.6	998.3	997.0	995.7	994.5	992.0	988.3	984.7	981.1	977.5	975.2
42.5°	957.8	956.7	955.6	954.5	953.4	951.1	947.4	943.8	940.2	936.6	934.4
45°	897.3	896.3	895.3	894.2	893.2	891.1	888.0	884.9	881.8	878.7	875.6
47.5°	832.2	832.2	832.3	832.4	832.4	830.6	826.9	823.1	819.4	815.7	812.5
50°	790.4	789.6	788.8	788.1	787.3	785.3	782.2	779.1	776.0	772.9	769.6
52.5°	747.6	747.0	746.5	745.9	745.4	743.4	740.1	736.8	733.5	730.1	727.2
55°	683.5	682.7	681.9	681.1	680.4	678.1	674.5	670.9	667.3	663.7	661.3
57.5°	615.8	615.4	615.0	614.6	614.2	612.4	609.3	606.3	603.3	600.2	597.2
60°	573.0	572.0	570.9	569.9	568.9	567.0	564.1	561.3	558.4	555.6	553.0
62.5°	528.4	527.5	526.8	525.9	525.1	523.5	521.0	518.6	516.2	513.8	510.9
65°	461.4	460.9	460.4	459.9	459.3	457.7	454.9	452.0	449.2	446.3	444.0
67.5°	396.6	395.5	394.4	393.3	392.3	390.6	388.5	386.4	384.3	382.2	380.2
70°	355.7	354.4	353.1	351.8	350.5	348.7	346.4	344.1	341.7	339.4	337.9
72.5°	311.1	310.1	309.3	308.4	307.5	306.3	304.9	303.3	301.9	300.3	298.6
75°	245.2	244.7	244.2	243.7	243.1	242.3	241.0	239.7	238.4	237.1	236.3
77.5°	184.6	184.3	184.2	184.0	183.7	183.3	182.5	181.8	181.2	180.4	179.9
80°	146.5	146.5	146.5	146.5	146.5	146.2	145.7	145.2	144.6	144.1	143.9
82.5°	113.0	112.5	112.2	111.8	111.3	111.1	111.0	110.9	110.7	110.6	110.2
85°	63.9	64.1	64.4	64.7	64.9	65.1	65.1	65.1	65.1	65.1	64.8
87.5°	25.2	25.4	25.7	25.9	26.2	26.3	26.3	26.3	26.3	26.3	26.4
90°	0.7	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5
92.5°	8.2	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7
95°	22.2	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7
97.5°	36.9	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5
100°	47.1	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2
102.5°	58.5	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6
105°	76.1	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3
107.5°	93.3	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5
110°	105.7	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5



TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	118.0	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3
115°	136.0	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2
117.5°	152.1	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8
120°	162.9	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6
122.5°	174.3	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8
125°	188.5	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7
127.5°	199.7	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5
130°	206.6	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5
132.5°	212.1	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0
135°	220.8	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3
137.5°	231.9	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5
140°	238.3	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2
142.5°	245.8	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6
145°	257.2	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5
147.5°	269.0	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3
150°	276.0	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1
152.5°	283.5	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3
155°	293.5	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0
157.5°	302.4	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1
160°	308.3	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3
162.5°	313.1	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9
165°	320.5	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4
167.5°	325.3	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1
170°	328.6	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3
172.5°	330.7	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6
175°	333.2	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6
177.5°	334.4	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1464.9	1467.0	1469.0	1470.0	1469.8	1469.6	1469.4	1469.2
5°	1457.6	1459.9	1462.2	1463.3	1463.0	1462.8	1462.5	1462.2
7.5°	1442.8	1445.1	1447.3	1448.4	1448.1	1447.9	1447.6	1447.3
10°	1430.3	1432.4	1434.4	1435.4	1435.1	1434.9	1434.6	1434.3
12.5°	1413.7	1415.3	1416.9	1417.8	1417.7	1417.6	1417.6	1417.6
15°	1384.6	1385.9	1387.2	1387.8	1387.8	1387.8	1387.8	1387.8
17.5°	1350.8	1352.4	1354.0	1354.2	1352.9	1351.6	1350.3	1349.0
20°	1325.2	1327.0	1328.8	1329.0	1327.7	1326.5	1325.2	1323.9
22.5°	1296.1	1297.3	1298.4	1298.6	1297.7	1296.8	1296.0	1295.0
25°	1249.4	1249.9	1250.4	1250.3	1249.5	1248.7	1247.9	1247.2
27.5°	1200.4	1200.5	1200.7	1200.3	1199.5	1198.8	1198.0	1197.2
30°	1164.8	1164.2	1163.7	1163.1	1162.4	1161.6	1160.8	1160.0
32.5°	1128.6	1127.7	1126.8	1125.6	1124.2	1122.8	1121.4	1120.0
35°	1072.5	1071.3	1070.0	1068.3	1066.3	1064.2	1062.1	1060.1
37.5°	1013.7	1011.8	1009.9	1008.3	1007.1	1005.9	1004.7	1003.6
40°	972.8	970.5	968.2	966.6	965.9	965.1	964.3	963.5
42.5°	932.4	930.2	928.2	926.4	925.3	924.1	922.9	921.7
45°	872.5	869.4	866.3	864.4	863.6	862.8	862.0	861.3
47.5°	809.4	806.2	803.1	800.6	798.8	797.0	795.2	793.4
50°	766.2	762.8	759.5	756.9	755.1	753.3	751.5	749.7
52.5°	724.3	721.3	718.4	715.9	713.9	711.9	709.9	707.8
55°	659.0	656.7	654.4	652.3	650.5	648.7	646.9	645.1
57.5°	594.3	591.2	588.2	586.3	585.3	584.3	583.3	582.3
60°	550.4	547.9	545.3	543.0	541.2	539.4	537.6	535.8
62.5°	508.2	505.4	502.6	500.5	499.1	497.7	496.3	494.9
65°	441.7	439.4	437.0	435.3	434.3	433.3	432.2	431.2
67.5°	378.2	376.3	374.3	373.0	372.4	371.8	371.2	370.6
70°	336.3	334.8	333.2	331.9	330.9	329.8	328.8	327.8
72.5°	296.9	295.1	293.3	292.0	290.9	289.9	288.9	287.8
75°	235.6	234.8	234.0	233.1	232.0	231.0	230.0	228.9
77.5°	179.4	179.0	178.6	178.0	177.2	176.5	175.7	175.0
80°	143.6	143.4	143.1	142.7	142.2	141.6	141.1	140.6
82.5°	109.7	109.3	108.8	108.5	108.4	108.3	108.2	108.1
85°	64.6	64.3	64.1	63.6	63.1	62.6	62.1	61.6
87.5°	26.6	26.8	26.9	26.9	26.5	26.1	25.8	25.4
90°	12.1	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	119.3	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	484.1	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	720.9	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	828.0	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	864.1	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	842.8	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	766.9	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	710.9	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333276-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	666.8	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	611.3	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	575.5	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	556.0	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	541.6	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	520.4	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	498.9	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	485.3	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	471.9	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	454.4	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	439.6	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	431.5	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	424.6	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	415.3	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	406.7	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	401.9	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	396.5	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	388.5	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	380.4	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	375.0	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	369.0	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	360.8	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	353.0	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	348.7	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	343.9	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.0	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)