

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333323-935

Luminaire Tested: **S125DIP-S1270D1035U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333323-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1035U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7546.7 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	83	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	76	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	50	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	32	40	34	30	35	30	27	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	30	26	33	28	24	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	2.0
10°-20°	453.2	6.0
20°-30°	736.0	9.8
30°-40°	897.7	11.9
40°-50°	816.7	10.8
50°-60°	650.5	8.6
60°-70°	453.1	6.0
70°-80°	241.6	3.2
80°-90°	63.4	0.8
90°-100°	74.0	1.0
100°-110°	218.5	2.9
110°-120°	370.0	4.9
120°-130°	487.0	6.5
130°-140°	545.7	7.2
140°-150°	534.8	7.1
150°-160°	449.2	6.0
160°-170°	298.6	4.0
170°-180°	104.5	1.4
0°-30°	1341.4	17.8
0°-40°	2239.2	29.7
0°-60°	3706.4	49.1
0°-90°	4464.5	59.2
90°-120°	662.5	8.8
90°-150°	2229.9	29.5
90°-180°	3082.0	40.8
0°-180°	7546.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	52
90°	21	1	21	1	21	14
95°	74	56	74	56	74	75
105°	213	196	213	196	213	226
115°	374	370	374	370	374	370
125°	544	541	544	541	544	486
135°	706	703	706	703	706	544
145°	855	852	855	852	855	534
155°	975	975	975	975	975	449
165°	1057	1060	1057	1060	1057	298
175°	1098	1102	1098	1102	1098	104
180°	1105	1105	1105	1105	1105	



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	17.0	18.0	18.4	18.3	18.7	18.5	20.5	20.3	21.7	23.2	25.1
90°	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7	14.7	13.8	12.4
92.5°	40.6	40.1	39.7	39.3	38.9	38.1	36.8	35.6	34.3	33.0	31.3
95°	74.0	73.5	73.2	72.8	72.4	71.5	70.2	68.9	67.5	66.2	64.3
97.5°	112.1	111.8	111.7	111.4	111.2	110.5	109.2	107.9	106.7	105.4	102.7
100°	140.9	140.6	140.2	139.8	139.5	138.4	136.6	134.9	133.2	131.5	129.1
102.5°	169.9	169.4	168.8	168.2	167.7	166.5	164.6	162.7	160.9	159.0	157.7
105°	213.2	212.6	212.1	211.5	210.9	210.0	208.9	207.8	206.6	205.4	204.3
107.5°	257.5	257.6	257.6	257.6	257.7	257.4	256.8	256.2	255.7	255.1	254.3
110°	290.5	290.8	290.9	291.1	291.3	291.1	290.5	290.0	289.4	288.8	288.3



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	322.9	323.2	323.6	323.9	324.3	324.3	324.0	323.7	323.5	323.2	322.4
115°	373.9	374.1	374.3	374.4	374.7	374.9	375.1	375.2	375.5	375.7	375.2
117.5°	423.8	424.6	425.3	426.0	426.8	427.1	427.0	426.8	426.7	426.5	426.2
120°	458.1	458.9	459.7	460.5	461.2	461.6	461.6	461.6	461.6	461.6	461.4
122.5°	492.6	493.2	493.8	494.4	495.0	495.3	495.5	495.7	495.8	495.9	495.5
125°	544.2	544.3	544.5	544.7	544.8	545.2	545.5	546.0	546.3	546.7	546.5
127.5°	593.7	594.0	594.3	594.8	595.1	595.5	595.6	595.8	596.0	596.2	596.0
130°	626.6	627.0	627.4	627.8	628.2	628.4	628.6	628.8	629.0	629.2	628.8
132.5°	657.5	658.1	658.7	659.2	659.7	660.0	660.3	660.5	660.6	660.8	660.9
135°	705.7	706.5	707.2	708.0	708.8	709.1	709.1	709.1	709.1	709.1	708.9
137.5°	752.9	753.8	754.8	755.7	756.6	757.0	756.7	756.6	756.3	756.0	755.7
140°	783.1	784.0	785.0	785.9	786.9	787.2	786.8	786.4	786.0	785.7	785.1
142.5°	811.9	813.0	813.9	814.9	815.8	816.1	815.9	815.7	815.5	815.2	814.5
145°	855.3	855.8	856.4	857.0	857.6	857.9	857.9	857.9	857.9	857.9	857.3
147.5°	892.3	893.5	894.8	896.1	897.4	897.9	897.4	896.9	896.5	896.0	895.5
150°	919.7	920.2	920.5	920.9	921.3	921.4	921.4	921.4	921.4	921.4	920.7
152.5°	942.5	943.1	943.8	944.5	945.2	945.3	944.9	944.4	943.9	943.5	943.1
155°	974.7	975.7	976.6	977.7	978.6	978.7	977.9	977.1	976.4	975.6	975.4
157.5°	1001.8	1003.0	1004.3	1005.6	1006.8	1007.0	1006.3	1005.5	1004.8	1004.0	1003.8
160°	1020.3	1021.3	1022.3	1023.2	1024.2	1024.2	1023.5	1022.7	1021.9	1021.1	1021.0
162.5°	1036.1	1037.2	1038.4	1039.5	1040.6	1040.7	1039.7	1038.8	1037.9	1037.0	1037.0
165°	1057.3	1058.4	1059.5	1060.8	1061.9	1062.0	1061.3	1060.5	1059.8	1059.0	1058.8
167.5°	1074.1	1075.3	1076.5	1077.7	1078.8	1078.9	1077.7	1076.6	1075.5	1074.3	1074.3
170°	1083.1	1084.4	1085.7	1087.1	1088.4	1088.5	1087.4	1086.2	1085.1	1083.9	1083.9
172.5°	1090.6	1091.8	1093.0	1094.2	1095.4	1095.4	1094.2	1093.1	1091.9	1090.8	1090.8
175°	1097.7	1099.0	1100.4	1101.7	1103.0	1103.1	1102.0	1100.9	1099.7	1098.5	1098.5
177.5°	1101.8	1102.9	1104.0	1105.0	1106.1	1106.1	1105.3	1104.3	1103.5	1102.5	1102.7
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	25.8	24.5	22.0	20.1	17.2	15.2	14.5	14.6	13.3	13.2	13.9
90°	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9	2.4	3.9	5.4
92.5°	29.7	28.1	26.4	25.1	24.0	22.9	21.9	20.8	21.9	22.9	24.0
95°	62.3	60.4	58.5	57.4	57.0	56.7	56.2	55.9	56.2	56.7	57.0
97.5°	100.1	97.5	94.9	93.4	93.3	93.2	93.0	92.8	93.0	93.2	93.3
100°	126.6	124.1	121.6	120.4	120.4	120.4	120.4	120.4	120.4	120.4	120.4
102.5°	156.5	155.2	153.9	153.0	152.2	151.4	150.7	149.9	150.7	151.4	152.2
105°	203.1	202.0	200.9	199.8	198.9	197.9	196.9	196.0	196.9	197.9	198.9
107.5°	253.4	252.4	251.6	250.7	249.8	248.7	247.8	246.8	247.8	248.7	249.8
110°	287.7	287.1	286.5	285.8	284.8	283.9	282.9	282.0	282.9	283.9	284.8



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	321.8	321.1	320.3	319.7	319.2	318.7	318.2	317.7	318.2	318.7	319.2
115°	374.9	374.4	374.1	373.5	372.8	372.0	371.3	370.5	371.3	372.0	372.8
117.5°	425.9	425.5	425.2	424.8	424.5	424.1	423.8	423.4	423.8	424.1	424.5
120°	461.2	461.0	460.8	460.3	459.3	458.3	457.4	456.4	457.4	458.3	459.3
122.5°	495.0	494.5	494.0	493.6	493.3	492.9	492.6	492.2	492.6	492.9	493.3
125°	546.3	546.1	546.0	545.3	544.2	542.9	541.8	540.7	541.8	542.9	544.2
127.5°	595.7	595.6	595.3	594.9	594.2	593.6	592.9	592.3	592.9	593.6	594.2
130°	628.4	628.1	627.7	627.0	626.0	625.1	624.1	623.2	624.1	625.1	626.0
132.5°	661.0	661.1	661.2	660.4	658.8	657.3	655.7	654.1	655.7	657.3	658.8
135°	708.8	708.6	708.4	707.7	706.5	705.4	704.3	703.2	704.3	705.4	706.5
137.5°	755.3	754.8	754.4	753.6	752.5	751.4	750.3	749.2	750.3	751.4	752.5
140°	784.5	783.9	783.3	782.6	781.6	780.7	779.7	778.8	779.7	780.7	781.6
142.5°	813.8	813.0	812.4	811.6	810.7	809.9	809.2	808.3	809.2	809.9	810.7
145°	856.7	856.2	855.6	854.9	854.1	853.3	852.6	851.9	852.6	853.3	854.1
147.5°	895.1	894.7	894.2	893.7	893.4	892.9	892.5	892.1	892.5	892.9	893.4
150°	920.0	919.2	918.4	918.2	918.3	918.5	918.7	918.9	918.7	918.5	918.3
152.5°	942.9	942.5	942.3	941.9	941.7	941.4	941.2	940.9	941.2	941.4	941.7
155°	975.3	975.1	974.8	974.7	974.7	974.7	974.7	974.7	974.7	974.7	974.7
157.5°	1003.6	1003.4	1003.2	1003.3	1003.8	1004.2	1004.6	1005.0	1004.6	1004.2	1003.8
160°	1020.8	1020.6	1020.5	1020.6	1021.1	1021.7	1022.4	1022.9	1022.4	1021.7	1021.1
162.5°	1036.9	1036.9	1036.8	1037.1	1037.4	1037.8	1038.3	1038.7	1038.3	1037.8	1037.4
165°	1058.6	1058.4	1058.3	1058.3	1058.7	1059.1	1059.5	1059.9	1059.5	1059.1	1058.7
167.5°	1074.3	1074.3	1074.3	1074.7	1075.5	1076.2	1076.9	1077.7	1076.9	1076.2	1075.5
170°	1083.9	1083.9	1083.9	1084.3	1085.1	1085.8	1086.6	1087.4	1086.6	1085.8	1085.1
172.5°	1090.8	1090.8	1090.8	1091.2	1091.9	1092.7	1093.5	1094.2	1093.5	1092.7	1091.9
175°	1098.5	1098.5	1098.5	1098.9	1099.7	1100.4	1101.2	1102.0	1101.2	1100.4	1099.7
177.5°	1102.8	1102.9	1103.1	1103.5	1104.1	1104.7	1105.4	1106.0	1105.4	1104.7	1104.1
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	14.8	16.2	15.9	16.7	17.0	18.3	18.0	20.3	21.6	22.8	22.5
90°	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7	16.6	17.6	18.3
92.5°	25.1	26.4	28.1	29.7	31.3	33.0	34.3	35.6	36.8	38.1	38.9
95°	57.4	58.5	60.4	62.3	64.3	66.2	67.5	68.9	70.2	71.5	72.4
97.5°	93.4	94.9	97.5	100.1	102.7	105.4	106.7	107.9	109.2	110.5	111.2
100°	120.4	121.6	124.1	126.6	129.1	131.5	133.2	134.9	136.6	138.4	139.5
102.5°	153.0	153.9	155.2	156.5	157.7	159.0	160.9	162.7	164.6	166.5	167.7
105°	199.8	200.9	202.0	203.1	204.3	205.4	206.6	207.8	208.9	210.0	210.9
107.5°	250.7	251.6	252.4	253.4	254.3	255.1	255.7	256.2	256.8	257.4	257.7
110°	285.8	286.5	287.1	287.7	288.3	288.8	289.4	290.0	290.5	291.1	291.3



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	319.7	320.3	321.1	321.8	322.4	323.2	323.5	323.7	324.0	324.3	324.3
115°	373.5	374.1	374.4	374.9	375.2	375.7	375.5	375.2	375.1	374.9	374.7
117.5°	424.8	425.2	425.5	425.9	426.2	426.5	426.7	426.8	427.0	427.1	426.8
120°	460.3	460.8	461.0	461.2	461.4	461.6	461.6	461.6	461.6	461.6	461.2
122.5°	493.6	494.0	494.5	495.0	495.5	495.9	495.8	495.7	495.5	495.3	495.0
125°	545.3	546.0	546.1	546.3	546.5	546.7	546.3	546.0	545.5	545.2	544.8
127.5°	594.9	595.3	595.6	595.7	596.0	596.2	596.0	595.8	595.6	595.5	595.1
130°	627.0	627.7	628.1	628.4	628.8	629.2	629.0	628.8	628.6	628.4	628.2
132.5°	660.4	661.2	661.1	661.0	660.9	660.8	660.6	660.5	660.3	660.0	659.7
135°	707.7	708.4	708.6	708.8	708.9	709.1	709.1	709.1	709.1	709.1	708.8
137.5°	753.6	754.4	754.8	755.3	755.7	756.0	756.3	756.6	756.7	757.0	756.6
140°	782.6	783.3	783.9	784.5	785.1	785.7	786.0	786.4	786.8	787.2	786.9
142.5°	811.6	812.4	813.0	813.8	814.5	815.2	815.5	815.7	815.9	816.1	815.8
145°	854.9	855.6	856.2	856.7	857.3	857.9	857.9	857.9	857.9	857.9	857.6
147.5°	893.7	894.2	894.7	895.1	895.5	896.0	896.5	896.9	897.4	897.9	897.4
150°	918.2	918.4	919.2	920.0	920.7	921.4	921.4	921.4	921.4	921.4	921.3
152.5°	941.9	942.3	942.5	942.9	943.1	943.5	943.9	944.4	944.9	945.3	945.2
155°	974.7	974.8	975.1	975.3	975.4	975.6	976.4	977.1	977.9	978.7	978.6
157.5°	1003.3	1003.2	1003.4	1003.6	1003.8	1004.0	1004.8	1005.5	1006.3	1007.0	1006.8
160°	1020.6	1020.5	1020.6	1020.8	1021.0	1021.1	1021.9	1022.7	1023.5	1024.2	1024.2
162.5°	1037.1	1036.8	1036.9	1036.9	1037.0	1037.0	1037.9	1038.8	1039.7	1040.7	1040.6
165°	1058.3	1058.3	1058.4	1058.6	1058.8	1059.0	1059.8	1060.5	1061.3	1062.0	1061.9
167.5°	1074.7	1074.3	1074.3	1074.3	1074.3	1074.3	1075.5	1076.6	1077.7	1078.9	1078.8
170°	1084.3	1083.9	1083.9	1083.9	1083.9	1083.9	1085.1	1086.2	1087.4	1088.5	1088.4
172.5°	1091.2	1090.8	1090.8	1090.8	1090.8	1090.8	1091.9	1093.1	1094.2	1095.4	1095.4
175°	1098.9	1098.5	1098.5	1098.5	1098.5	1098.5	1099.7	1100.9	1102.0	1103.1	1103.0
177.5°	1103.5	1103.1	1102.9	1102.8	1102.7	1102.5	1103.5	1104.3	1105.3	1106.1	1106.1
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	23.7	23.2	23.3	24.5	23.3	23.2	23.7	22.5	22.8	21.6	20.3
90°	18.9	19.5	20.1	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7
92.5°	39.3	39.7	40.1	40.6	40.1	39.7	39.3	38.9	38.1	36.8	35.6
95°	72.8	73.2	73.5	74.0	73.5	73.2	72.8	72.4	71.5	70.2	68.9
97.5°	111.4	111.7	111.8	112.1	111.8	111.7	111.4	111.2	110.5	109.2	107.9
100°	139.8	140.2	140.6	140.9	140.6	140.2	139.8	139.5	138.4	136.6	134.9
102.5°	168.2	168.8	169.4	169.9	169.4	168.8	168.2	167.7	166.5	164.6	162.7
105°	211.5	212.1	212.6	213.2	212.6	212.1	211.5	210.9	210.0	208.9	207.8
107.5°	257.6	257.6	257.6	257.5	257.6	257.6	257.6	257.7	257.4	256.8	256.2
110°	291.1	290.9	290.8	290.5	290.8	290.9	291.1	291.3	291.1	290.5	290.0



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	323.9	323.6	323.2	322.9	323.2	323.6	323.9	324.3	324.3	324.0	323.7
115°	374.4	374.3	374.1	373.9	374.1	374.3	374.4	374.7	374.9	375.1	375.2
117.5°	426.0	425.3	424.6	423.8	424.6	425.3	426.0	426.8	427.1	427.0	426.8
120°	460.5	459.7	458.9	458.1	458.9	459.7	460.5	461.2	461.6	461.6	461.6
122.5°	494.4	493.8	493.2	492.6	493.2	493.8	494.4	495.0	495.3	495.5	495.7
125°	544.7	544.5	544.3	544.2	544.3	544.5	544.7	544.8	545.2	545.5	546.0
127.5°	594.8	594.3	594.0	593.7	594.0	594.3	594.8	595.1	595.5	595.6	595.8
130°	627.8	627.4	627.0	626.6	627.0	627.4	627.8	628.2	628.4	628.6	628.8
132.5°	659.2	658.7	658.1	657.5	658.1	658.7	659.2	659.7	660.0	660.3	660.5
135°	708.0	707.2	706.5	705.7	706.5	707.2	708.0	708.8	709.1	709.1	709.1
137.5°	755.7	754.8	753.8	752.9	753.8	754.8	755.7	756.6	757.0	756.7	756.6
140°	785.9	785.0	784.0	783.1	784.0	785.0	785.9	786.9	787.2	786.8	786.4
142.5°	814.9	813.9	813.0	811.9	813.0	813.9	814.9	815.8	816.1	815.9	815.7
145°	857.0	856.4	855.8	855.3	855.8	856.4	857.0	857.6	857.9	857.9	857.9
147.5°	896.1	894.8	893.5	892.3	893.5	894.8	896.1	897.4	897.9	897.4	896.9
150°	920.9	920.5	920.2	919.7	920.2	920.5	920.9	921.3	921.4	921.4	921.4
152.5°	944.5	943.8	943.1	942.5	943.1	943.8	944.5	945.2	945.3	944.9	944.4
155°	977.7	976.6	975.7	974.7	975.7	976.6	977.7	978.6	978.7	977.9	977.1
157.5°	1005.6	1004.3	1003.0	1001.8	1003.0	1004.3	1005.6	1006.8	1007.0	1006.3	1005.5
160°	1023.2	1022.3	1021.3	1020.3	1021.3	1022.3	1023.2	1024.2	1024.2	1023.5	1022.7
162.5°	1039.5	1038.4	1037.2	1036.1	1037.2	1038.4	1039.5	1040.6	1040.7	1039.7	1038.8
165°	1060.8	1059.5	1058.4	1057.3	1058.4	1059.5	1060.8	1061.9	1062.0	1061.3	1060.5
167.5°	1077.7	1076.5	1075.3	1074.1	1075.3	1076.5	1077.7	1078.8	1078.9	1077.7	1076.6
170°	1087.1	1085.7	1084.4	1083.1	1084.4	1085.7	1087.1	1088.4	1088.5	1087.4	1086.2
172.5°	1094.2	1093.0	1091.8	1090.6	1091.8	1093.0	1094.2	1095.4	1095.4	1094.2	1093.1
175°	1101.7	1100.4	1099.0	1097.7	1099.0	1100.4	1101.7	1103.0	1103.1	1102.0	1100.9
177.5°	1105.0	1104.0	1102.9	1101.8	1102.9	1104.0	1105.0	1106.1	1106.1	1105.3	1104.3
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	18.0	18.3	17.0	16.7	15.9	16.2	14.8	13.9	13.2	13.3	14.6
90°	14.7	13.8	12.4	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9
92.5°	34.3	33.0	31.3	29.7	28.1	26.4	25.1	24.0	22.9	21.9	20.8
95°	67.5	66.2	64.3	62.3	60.4	58.5	57.4	57.0	56.7	56.2	55.9
97.5°	106.7	105.4	102.7	100.1	97.5	94.9	93.4	93.3	93.2	93.0	92.8
100°	133.2	131.5	129.1	126.6	124.1	121.6	120.4	120.4	120.4	120.4	120.4
102.5°	160.9	159.0	157.7	156.5	155.2	153.9	153.0	152.2	151.4	150.7	149.9
105°	206.6	205.4	204.3	203.1	202.0	200.9	199.8	198.9	197.9	196.9	196.0
107.5°	255.7	255.1	254.3	253.4	252.4	251.6	250.7	249.8	248.7	247.8	246.8
110°	289.4	288.8	288.3	287.7	287.1	286.5	285.8	284.8	283.9	282.9	282.0



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	323.5	323.2	322.4	321.8	321.1	320.3	319.7	319.2	318.7	318.2	317.7
115°	375.5	375.7	375.2	374.9	374.4	374.1	373.5	372.8	372.0	371.3	370.5
117.5°	426.7	426.5	426.2	425.9	425.5	425.2	424.8	424.5	424.1	423.8	423.4
120°	461.6	461.6	461.4	461.2	461.0	460.8	460.3	459.3	458.3	457.4	456.4
122.5°	495.8	495.9	495.5	495.0	494.5	494.0	493.6	493.3	492.9	492.6	492.2
125°	546.3	546.7	546.5	546.3	546.1	546.0	545.3	544.2	542.9	541.8	540.7
127.5°	596.0	596.2	596.0	595.7	595.6	595.3	594.9	594.2	593.6	592.9	592.3
130°	629.0	629.2	628.8	628.4	628.1	627.7	627.0	626.0	625.1	624.1	623.2
132.5°	660.6	660.8	660.9	661.0	661.1	661.2	660.4	658.8	657.3	655.7	654.1
135°	709.1	709.1	708.9	708.8	708.6	708.4	707.7	706.5	705.4	704.3	703.2
137.5°	756.3	756.0	755.7	755.3	754.8	754.4	753.6	752.5	751.4	750.3	749.2
140°	786.0	785.7	785.1	784.5	783.9	783.3	782.6	781.6	780.7	779.7	778.8
142.5°	815.5	815.2	814.5	813.8	813.0	812.4	811.6	810.7	809.9	809.2	808.3
145°	857.9	857.9	857.3	856.7	856.2	855.6	854.9	854.1	853.3	852.6	851.9
147.5°	896.5	896.0	895.5	895.1	894.7	894.2	893.7	893.4	892.9	892.5	892.1
150°	921.4	921.4	920.7	920.0	919.2	918.4	918.2	918.3	918.5	918.7	918.9
152.5°	943.9	943.5	943.1	942.9	942.5	942.3	941.9	941.7	941.4	941.2	940.9
155°	976.4	975.6	975.4	975.3	975.1	974.8	974.7	974.7	974.7	974.7	974.7
157.5°	1004.8	1004.0	1003.8	1003.6	1003.4	1003.2	1003.3	1003.8	1004.2	1004.6	1005.0
160°	1021.9	1021.1	1021.0	1020.8	1020.6	1020.5	1020.6	1021.1	1021.7	1022.4	1022.9
162.5°	1037.9	1037.0	1037.0	1036.9	1036.9	1036.8	1037.1	1037.4	1037.8	1038.3	1038.7
165°	1059.8	1059.0	1058.8	1058.6	1058.4	1058.3	1058.3	1058.7	1059.1	1059.5	1059.9
167.5°	1075.5	1074.3	1074.3	1074.3	1074.3	1074.3	1074.7	1075.5	1076.2	1076.9	1077.7
170°	1085.1	1083.9	1083.9	1083.9	1083.9	1083.9	1084.3	1085.1	1085.8	1086.6	1087.4
172.5°	1091.9	1090.8	1090.8	1090.8	1090.8	1090.8	1091.2	1091.9	1092.7	1093.5	1094.2
175°	1099.7	1098.5	1098.5	1098.5	1098.5	1098.5	1098.9	1099.7	1100.4	1101.2	1102.0
177.5°	1103.5	1102.5	1102.7	1102.8	1102.9	1103.1	1103.5	1104.1	1104.7	1105.4	1106.0
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.5	15.2	17.2	20.1	22.0	24.5	25.8	25.1	23.2	21.7	20.3
90°	2.4	3.9	5.4	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7
92.5°	21.9	22.9	24.0	25.1	26.4	28.1	29.7	31.3	33.0	34.3	35.6
95°	56.2	56.7	57.0	57.4	58.5	60.4	62.3	64.3	66.2	67.5	68.9
97.5°	93.0	93.2	93.3	93.4	94.9	97.5	100.1	102.7	105.4	106.7	107.9
100°	120.4	120.4	120.4	120.4	121.6	124.1	126.6	129.1	131.5	133.2	134.9
102.5°	150.7	151.4	152.2	153.0	153.9	155.2	156.5	157.7	159.0	160.9	162.7
105°	196.9	197.9	198.9	199.8	200.9	202.0	203.1	204.3	205.4	206.6	207.8
107.5°	247.8	248.7	249.8	250.7	251.6	252.4	253.4	254.3	255.1	255.7	256.2
110°	282.9	283.9	284.8	285.8	286.5	287.1	287.7	288.3	288.8	289.4	290.0



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.2	318.7	319.2	319.7	320.3	321.1	321.8	322.4	323.2	323.5	323.7
115°	371.3	372.0	372.8	373.5	374.1	374.4	374.9	375.2	375.7	375.5	375.2
117.5°	423.8	424.1	424.5	424.8	425.2	425.5	425.9	426.2	426.5	426.7	426.8
120°	457.4	458.3	459.3	460.3	460.8	461.0	461.2	461.4	461.6	461.6	461.6
122.5°	492.6	492.9	493.3	493.6	494.0	494.5	495.0	495.5	495.9	495.8	495.7
125°	541.8	542.9	544.2	545.3	546.0	546.1	546.3	546.5	546.7	546.3	546.0
127.5°	592.9	593.6	594.2	594.9	595.3	595.6	595.7	596.0	596.2	596.0	595.8
130°	624.1	625.1	626.0	627.0	627.7	628.1	628.4	628.8	629.2	629.0	628.8
132.5°	655.7	657.3	658.8	660.4	661.2	661.1	661.0	660.9	660.8	660.6	660.5
135°	704.3	705.4	706.5	707.7	708.4	708.6	708.8	708.9	709.1	709.1	709.1
137.5°	750.3	751.4	752.5	753.6	754.4	754.8	755.3	755.7	756.0	756.3	756.6
140°	779.7	780.7	781.6	782.6	783.3	783.9	784.5	785.1	785.7	786.0	786.4
142.5°	809.2	809.9	810.7	811.6	812.4	813.0	813.8	814.5	815.2	815.5	815.7
145°	852.6	853.3	854.1	854.9	855.6	856.2	856.7	857.3	857.9	857.9	857.9
147.5°	892.5	892.9	893.4	893.7	894.2	894.7	895.1	895.5	896.0	896.5	896.9
150°	918.7	918.5	918.3	918.2	918.4	919.2	920.0	920.7	921.4	921.4	921.4
152.5°	941.2	941.4	941.7	941.9	942.3	942.5	942.9	943.1	943.5	943.9	944.4
155°	974.7	974.7	974.7	974.7	974.8	975.1	975.3	975.4	975.6	976.4	977.1
157.5°	1004.6	1004.2	1003.8	1003.3	1003.2	1003.4	1003.6	1003.8	1004.0	1004.8	1005.5
160°	1022.4	1021.7	1021.1	1020.6	1020.5	1020.6	1020.8	1021.0	1021.1	1021.9	1022.7
162.5°	1038.3	1037.8	1037.4	1037.1	1036.8	1036.9	1036.9	1037.0	1037.0	1037.9	1038.8
165°	1059.5	1059.1	1058.7	1058.3	1058.3	1058.4	1058.6	1058.8	1059.0	1059.8	1060.5
167.5°	1076.9	1076.2	1075.5	1074.7	1074.3	1074.3	1074.3	1074.3	1074.3	1075.5	1076.6
170°	1086.6	1085.8	1085.1	1084.3	1083.9	1083.9	1083.9	1083.9	1083.9	1085.1	1086.2
172.5°	1093.5	1092.7	1091.9	1091.2	1090.8	1090.8	1090.8	1090.8	1090.8	1091.9	1093.1
175°	1101.2	1100.4	1099.7	1098.9	1098.5	1098.5	1098.5	1098.5	1098.5	1099.7	1100.9
177.5°	1105.4	1104.7	1104.1	1103.5	1103.1	1102.9	1102.8	1102.7	1102.5	1103.5	1104.3
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	20.5	18.5	18.7	18.3	18.4	18.0	17.0
90°	16.6	17.6	18.3	18.9	19.5	20.1	20.7
92.5°	36.8	38.1	38.9	39.3	39.7	40.1	40.6
95°	70.2	71.5	72.4	72.8	73.2	73.5	74.0
97.5°	109.2	110.5	111.2	111.4	111.7	111.8	112.1
100°	136.6	138.4	139.5	139.8	140.2	140.6	140.9
102.5°	164.6	166.5	167.7	168.2	168.8	169.4	169.9
105°	208.9	210.0	210.9	211.5	212.1	212.6	213.2
107.5°	256.8	257.4	257.7	257.6	257.6	257.6	257.5
110°	290.5	291.1	291.3	291.1	290.9	290.8	290.5



TEST NUMBER: P333323-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	324.0	324.3	324.3	323.9	323.6	323.2	322.9
115°	375.1	374.9	374.7	374.4	374.3	374.1	373.9
117.5°	427.0	427.1	426.8	426.0	425.3	424.6	423.8
120°	461.6	461.6	461.2	460.5	459.7	458.9	458.1
122.5°	495.5	495.3	495.0	494.4	493.8	493.2	492.6
125°	545.5	545.2	544.8	544.7	544.5	544.3	544.2
127.5°	595.6	595.5	595.1	594.8	594.3	594.0	593.7
130°	628.6	628.4	628.2	627.8	627.4	627.0	626.6
132.5°	660.3	660.0	659.7	659.2	658.7	658.1	657.5
135°	709.1	709.1	708.8	708.0	707.2	706.5	705.7
137.5°	756.7	757.0	756.6	755.7	754.8	753.8	752.9
140°	786.8	787.2	786.9	785.9	785.0	784.0	783.1
142.5°	815.9	816.1	815.8	814.9	813.9	813.0	811.9
145°	857.9	857.9	857.6	857.0	856.4	855.8	855.3
147.5°	897.4	897.9	897.4	896.1	894.8	893.5	892.3
150°	921.4	921.4	921.3	920.9	920.5	920.2	919.7
152.5°	944.9	945.3	945.2	944.5	943.8	943.1	942.5
155°	977.9	978.7	978.6	977.7	976.6	975.7	974.7
157.5°	1006.3	1007.0	1006.8	1005.6	1004.3	1003.0	1001.8
160°	1023.5	1024.2	1024.2	1023.2	1022.3	1021.3	1020.3
162.5°	1039.7	1040.7	1040.6	1039.5	1038.4	1037.2	1036.1
165°	1061.3	1062.0	1061.9	1060.8	1059.5	1058.4	1057.3
167.5°	1077.7	1078.9	1078.8	1077.7	1076.5	1075.3	1074.1
170°	1087.4	1088.5	1088.4	1087.1	1085.7	1084.4	1083.1
172.5°	1094.2	1095.4	1095.4	1094.2	1093.0	1091.8	1090.6
175°	1102.0	1103.1	1103.0	1101.7	1100.4	1099.0	1097.7
177.5°	1105.3	1106.1	1106.1	1105.0	1104.0	1102.9	1101.8
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6

(END OF REPORT)