

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331359-927

Luminaire Tested: **SA2XXDIP-C675D925U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331359-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5186.0 lumens  
Efficiency: N/A  
Efficacy: 99.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331359-927  
CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	28
4	74	64	56	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	52	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	27	47	36	30	25	31	26	22	26	22	19	21	19	16	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.2	1.9
10°-20°	291.3	5.6
20°-30°	422.8	8.2
30°-40°	446.2	8.6
40°-50°	395.0	7.6
50°-60°	315.3	6.1
60°-70°	214.3	4.1
70°-80°	109.9	2.1
80°-90°	30.2	0.6
90°-100°	164.4	3.2
100°-110°	557.8	10.8
110°-120°	592.6	11.4
120°-130°	487.8	9.4
130°-140°	391.8	7.6
140°-150°	296.0	5.7
150°-160°	208.1	4.0
160°-170°	122.5	2.4
170°-180°	39.9	0.8
0°-30°	814.3	15.7
0°-40°	1260.5	24.3
0°-60°	1970.8	38.0
0°-90°	2325.1	44.8
90°-120°	1314.8	25.4
90°-150°	2490.5	48.0
90°-180°	2861.0	55.2
0°-180°	5186.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	25
90°	26	1	26	1	26	15
95°	90	28	90	28	90	117
105°	891	96	891	96	891	862
115°	1172	170	1172	170	1172	1148
125°	951	237	951	237	951	859
135°	788	278	788	278	788	612
145°	629	318	629	318	629	400
155°	529	361	529	361	529	247
165°	464	394	464	394	464	133
175°	418	410	418	410	418	41
180°	411	411	411	411	411	



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	13.6	13.6	13.9	13.6	13.6	13.8	13.5	13.5	13.9	14.4	14.6
90°	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3	26.1	26.9	26.1
92.5°	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9	86.8	102.7	101.3
95°	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2	271.2	309.9	274.3
97.5°	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4	555.0	529.1	398.5
100°	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8	738.5	624.6	430.1
102.5°	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1	806.8	627.7	418.1
105°	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6	796.1	585.8	394.5
107.5°	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2	726.7	541.0	382.8
110°	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9	683.1	519.4	380.3



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1	652.8	505.5	380.9
115°	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5	615.1	490.2	384.2
117.5°	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2	591.4	482.8	389.9
120°	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7	578.8	478.3	393.7
122.5°	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6	568.0	475.8	398.2
125°	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8	552.6	471.2	404.8
127.5°	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3	538.4	468.5	411.6
130°	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5	528.9	467.2	416.7
132.5°	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3	521.3	466.6	421.7
135°	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1	510.7	465.6	427.7
137.5°	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2	503.3	465.5	433.1
140°	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5	498.9	464.9	435.6
142.5°	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6	494.5	464.9	437.5
145°	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1	488.6	463.3	439.6
147.5°	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4	482.6	460.5	440.2
150°	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5	477.5	458.6	439.6
152.5°	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6	473.1	455.4	438.3
155°	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9	464.9	449.9	436.4
157.5°	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7	457.2	444.2	432.8
160°	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7	451.5	440.4	430.9
162.5°	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8	446.4	437.2	429.0
165°	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3	438.0	430.9	425.3
167.5°	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4	429.8	425.3	421.7
170°	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3	425.3	422.2	419.9
172.5°	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6	421.0	418.4	417.3
175°	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5	415.1	414.3	413.5
177.5°	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	13.9	12.8	12.0	12.3	10.9	10.6	8.7	7.3	7.4	7.8	7.4
90°	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8	3.2	6.3	7.9
92.5°	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7	13.9	19.6	23.1
95°	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6	30.8	38.7	45.9
97.5°	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1	49.4	57.8	68.4
100°	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8	63.2	70.3	83.0
102.5°	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4	77.2	84.3	97.0
105°	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5	99.7	105.1	117.0
107.5°	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2	121.8	127.1	138.1
110°	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4	137.6	142.3	152.6





TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3	151.5	156.9	166.5
115°	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0	174.0	178.7	188.1
117.5°	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4	195.6	200.3	208.7
120°	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4	209.5	214.3	221.3
122.5°	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7	222.1	226.9	234.6
125°	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2	239.6	244.3	253.8
127.5°	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1	254.3	260.9	271.3
130°	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4	262.4	270.4	281.5
132.5°	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9	270.7	279.2	291.0
135°	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3	281.5	291.0	302.8
137.5°	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1	292.9	302.3	315.0
140°	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3	300.5	309.9	322.6
142.5°	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5	308.0	316.9	329.5
145°	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8	321.0	328.9	340.8
147.5°	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1	333.5	341.0	352.0
150°	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0	342.3	348.6	358.9
152.5°	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8	349.9	356.2	365.3
155°	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3	362.1	366.9	375.6
157.5°	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8	372.6	376.4	383.9
160°	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7	379.5	382.6	389.0
162.5°	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6	385.2	388.3	393.4
165°	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7	392.9	394.5	399.3
167.5°	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4	399.4	400.8	403.9
170°	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8	403.2	404.0	406.4
172.5°	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3	406.4	405.9	408.3
175°	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4	409.6	408.8	410.4
177.5°	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8	410.5	409.9	411.1
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	7.4	7.5	8.0	9.1	9.7	9.6	9.1	9.0	8.6	8.3	8.5
90°	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3	23.7	25.3	26.1
92.5°	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9	59.2	52.5	47.6
95°	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2	158.9	125.7	108.3
97.5°	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4	395.5	309.9	252.9
100°	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8	623.8	515.5	419.9
102.5°	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1	856.0	776.7	675.3
105°	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6	1050.0	1060.3	1034.1
107.5°	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2	1035.7	1117.9	1156.2
110°	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9	991.4	1092.7	1157.5



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1	939.0	1047.1	1121.4
115°	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5	867.3	970.9	1052.3
117.5°	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2	809.1	903.0	979.5
120°	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7	778.8	862.5	934.5
122.5°	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6	753.4	832.8	897.9
125°	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8	720.3	789.8	849.1
127.5°	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3	688.0	753.6	808.3
130°	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5	666.5	729.0	781.2
132.5°	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3	646.3	703.6	752.7
135°	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1	614.3	666.5	710.7
137.5°	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2	588.8	630.3	668.8
140°	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5	572.4	608.8	643.6
142.5°	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6	557.9	589.1	618.3
145°	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1	539.2	563.7	586.6
147.5°	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4	524.0	543.1	559.9
150°	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5	513.9	530.5	544.7
152.5°	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6	505.6	519.8	532.1
155°	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9	492.6	504.4	513.1
157.5°	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7	479.3	489.3	496.1
160°	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7	470.4	479.1	484.7
162.5°	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8	462.2	469.6	473.9
165°	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3	449.9	455.4	458.6
167.5°	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4	438.6	442.4	445.3
170°	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3	431.7	434.8	436.4
172.5°	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6	425.3	427.9	428.8
175°	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5	418.3	419.1	419.9
177.5°	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0	413.0	413.7	413.7
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	8.5	8.2	8.2	7.8	8.2	8.2	8.5	8.5	8.3	8.6	9.0
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3
92.5°	47.0	44.4	45.1	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9
95°	98.1	91.7	89.4	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2
97.5°	215.1	195.6	184.0	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4
100°	354.2	320.2	297.3	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8
102.5°	604.0	546.0	517.4	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1
105°	985.1	936.1	902.1	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6
107.5°	1162.4	1159.7	1152.9	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2
110°	1191.4	1206.5	1213.6	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.7	1193.8	1207.3	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1
115°	1108.4	1144.8	1165.4	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5
117.5°	1036.6	1075.1	1096.8	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2
120°	989.8	1027.0	1050.0	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7
122.5°	947.5	984.0	1004.4	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6
125°	895.0	925.0	944.8	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8
127.5°	848.3	876.5	893.6	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3
130°	819.9	846.8	862.5	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5
132.5°	790.8	817.7	832.2	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3
135°	744.7	770.9	785.1	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1
137.5°	699.9	722.3	734.8	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2
140°	668.8	689.4	701.3	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5
142.5°	642.3	661.0	671.5	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6
145°	605.6	619.1	626.9	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1
147.5°	575.6	586.3	591.7	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4
150°	556.6	566.1	570.8	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5
152.5°	541.4	549.6	553.1	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6
155°	521.8	527.4	530.5	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9
157.5°	502.2	506.8	508.2	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7
160°	490.2	494.2	495.0	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7
162.5°	479.4	482.1	482.9	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8
165°	461.7	464.9	464.9	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3
167.5°	446.7	448.5	448.3	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4
170°	437.2	439.6	438.8	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3
172.5°	429.6	430.7	429.9	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6
175°	419.9	420.6	419.9	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5
177.5°	413.7	413.7	413.0	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	9.1	9.6	9.7	9.1	8.0	7.5	7.4	7.4	7.8	7.4	7.3
90°	26.1	26.9	26.1	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8
92.5°	86.8	102.7	101.3	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7
95°	271.2	309.9	274.3	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6
97.5°	555.0	529.1	398.5	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1
100°	738.5	624.6	430.1	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8
102.5°	806.8	627.7	418.1	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4
105°	796.1	585.8	394.5	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5
107.5°	726.7	541.0	382.8	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2
110°	683.1	519.4	380.3	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	652.8	505.5	380.9	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3
115°	615.1	490.2	384.2	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0
117.5°	591.4	482.8	389.9	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4
120°	578.8	478.3	393.7	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4
122.5°	568.0	475.8	398.2	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7
125°	552.6	471.2	404.8	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2
127.5°	538.4	468.5	411.6	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1
130°	528.9	467.2	416.7	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4
132.5°	521.3	466.6	421.7	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9
135°	510.7	465.6	427.7	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3
137.5°	503.3	465.5	433.1	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1
140°	498.9	464.9	435.6	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3
142.5°	494.5	464.9	437.5	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5
145°	488.6	463.3	439.6	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8
147.5°	482.6	460.5	440.2	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1
150°	477.5	458.6	439.6	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0
152.5°	473.1	455.4	438.3	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8
155°	464.9	449.9	436.4	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3
157.5°	457.2	444.2	432.8	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8
160°	451.5	440.4	430.9	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7
162.5°	446.4	437.2	429.0	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6
165°	438.0	430.9	425.3	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7
167.5°	429.8	425.3	421.7	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4
170°	425.3	422.2	419.9	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8
172.5°	421.0	418.4	417.3	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3
175°	415.1	414.3	413.5	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4
177.5°	411.8	411.1	411.8	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.7	10.6	10.9	12.3	12.0	12.8	13.9	14.6	14.4	13.9	13.5
90°	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3
92.5°	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9
95°	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2
97.5°	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4
100°	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8
102.5°	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1
105°	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6
107.5°	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2
110°	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9





TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1
115°	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5
117.5°	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2
120°	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7
122.5°	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6
125°	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8
127.5°	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3
130°	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5
132.5°	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3
135°	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1
137.5°	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2
140°	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5
142.5°	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6
145°	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1
147.5°	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4
150°	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5
152.5°	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6
155°	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9
157.5°	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7
160°	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7
162.5°	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8
165°	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3
167.5°	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4
170°	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3
172.5°	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6
175°	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5
177.5°	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	13.5	13.8	13.6	13.6	13.9	13.6	13.6
90°	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8



TEST NUMBER: P331359-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)