

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331363-927

Luminaire Tested: **SA2XXDIP-C675D925U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331363-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5072.4 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	73	65	58	53	53	49	45	43	40	37	34	32	30	25
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26	22
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	15
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.6
10°-20°	222.5	4.4
20°-30°	327.1	6.4
30°-40°	379.9	7.5
40°-50°	379.5	7.5
50°-60°	331.0	6.5
60°-70°	244.7	4.8
70°-80°	138.6	2.7
80°-90°	39.7	0.8
90°-100°	33.4	0.7
100°-110°	122.3	2.4
110°-120°	326.9	6.4
120°-130°	539.7	10.6
130°-140°	574.0	11.3
140°-150°	533.5	10.5
150°-160°	428.9	8.5
160°-170°	276.4	5.4
170°-180°	95.1	1.9
0°-30°	628.7	12.4
0°-40°	1008.6	19.9
0°-60°	1719.1	33.9
0°-90°	2142.2	42.2
90°-120°	482.6	9.5
90°-150°	2129.7	42.0
90°-180°	2930.0	57.8
0°-180°	5072.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	1	9	14	18	20	4
95°	47	25	28	32	31	58
105°	220	229	44	52	55	235
115°	416	429	446	127	59	409
125°	588	598	611	616	619	524
135°	728	739	746	753	752	562
145°	844	844	856	860	857	528
155°	930	924	932	936	930	428
165°	980	976	978	982	978	277
175°	1002	997	998	1003	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.8	11.9	11.9	12.0	12.0	12.0	12.0	12.0	12.0	12.0	11.6
90°	0.7	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3
92.5°	14.6	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2
95°	47.1	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0
97.5°	93.3	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4
100°	128.1	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5
102.5°	166.3	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0
105°	219.9	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9
107.5°	281.1	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0
110°	320.5	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5



TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.5	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7
115°	416.0	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9
117.5°	468.3	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4
120°	506.4	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3
122.5°	538.8	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6
125°	588.2	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5
127.5°	632.9	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2
130°	661.3	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5
132.5°	690.2	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6
135°	727.9	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5
137.5°	765.9	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9
140°	790.8	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0
142.5°	811.6	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3
145°	844.3	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0
147.5°	872.8	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0
150°	891.4	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8
152.5°	907.0	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3
155°	929.7	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8
157.5°	947.5	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2
160°	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9
162.5°	967.2	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7
165°	979.6	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6
167.5°	988.9	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7
170°	994.1	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3
172.5°	997.5	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8
175°	1002.0	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6
177.5°	1002.7	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	11.4	11.2	10.9	10.7	10.6	10.5	10.5	10.4
90°	16.1	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	17.6	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	29.8	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.1	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	43.8	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	45.7	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	47.7	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	58.1	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	94.4	78.3	62.3	54.6	55.2	55.8	56.5	57.2



TEST NUMBER: P331363-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.1	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	297.5	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	458.4	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	534.2	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	566.8	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	613.6	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	656.9	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	684.4	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	711.1	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	749.2	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	784.5	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	807.4	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	828.5	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	858.2	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	883.9	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	899.8	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	914.3	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	933.8	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	950.2	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	959.8	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	968.8	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	988.8	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	993.5	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	996.9	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1000.7	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1001.1	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)