

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333152-935

Luminaire Tested: **S125DIP-S375D1205U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333152-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1205U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4913.0 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	57	48	41	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	13	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	19	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	0.9
10°-20°	134.4	2.7
20°-30°	218.2	4.4
30°-40°	266.1	5.4
40°-50°	242.1	4.9
50°-60°	192.8	3.9
60°-70°	134.3	2.7
70°-80°	71.6	1.5
80°-90°	20.9	0.4
90°-100°	86.1	1.8
100°-110°	254.3	5.2
110°-120°	430.7	8.8
120°-130°	566.8	11.5
130°-140°	635.1	12.9
140°-150°	622.5	12.7
150°-160°	522.8	10.6
160°-170°	347.5	7.1
170°-180°	121.6	2.5
0°-30°	397.6	8.1
0°-40°	663.7	13.5
0°-60°	1098.7	22.4
0°-90°	1325.5	27.0
90°-120°	771.1	15.7
90°-150°	2595.6	52.8
90°-180°	3588.0	73.0
0°-180°	4913.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	16
90°	24	1	24	1	24	14
95°	86	65	86	65	86	88
105°	248	228	248	228	248	263
115°	435	431	435	431	435	430
125°	633	629	633	629	633	565
135°	821	818	821	818	821	634
145°	996	992	996	992	996	621
155°	1135	1135	1135	1135	1135	522
165°	1231	1234	1231	1234	1231	347
175°	1278	1283	1278	1283	1278	121
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	8.6	8.8	8.9	8.7	8.7	8.5	9.0	8.8	9.0	9.2	9.6
90°	24.0	23.3	22.6	22.0	21.4	20.5	19.4	18.3	17.1	16.0	14.5
92.5°	47.2	46.8	46.2	45.7	45.3	44.3	42.8	41.3	39.9	38.4	36.5
95°	86.0	85.6	85.2	84.7	84.3	83.3	81.7	80.2	78.6	77.1	74.8
97.5°	130.4	130.2	129.9	129.7	129.4	128.5	127.1	125.6	124.2	122.7	119.6
100°	164.1	163.7	163.2	162.7	162.3	161.1	159.1	157.0	155.1	153.1	150.2
102.5°	197.7	197.1	196.5	195.9	195.2	193.8	191.7	189.4	187.3	185.1	183.7
105°	248.1	247.5	246.8	246.2	245.5	244.4	243.1	241.8	240.5	239.1	237.8
107.5°	299.7	299.8	299.9	299.9	300.0	299.6	298.9	298.3	297.6	297.0	295.9
110°	338.2	338.4	338.6	338.8	339.1	338.8	338.2	337.5	336.8	336.1	335.5



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.8	376.2	376.6	377.0	377.4	377.5	377.1	376.9	376.5	376.2	375.3
115°	435.2	435.4	435.7	435.9	436.1	436.4	436.5	436.8	437.0	437.2	436.8
117.5°	493.3	494.1	495.1	495.9	496.8	497.1	497.0	496.8	496.6	496.5	496.0
120°	533.3	534.2	535.0	536.0	536.8	537.3	537.3	537.3	537.3	537.3	537.1
122.5°	573.3	574.0	574.7	575.4	576.2	576.6	576.8	577.0	577.1	577.3	576.7
125°	633.4	633.5	633.8	634.0	634.2	634.6	635.0	635.4	635.8	636.4	636.1
127.5°	691.0	691.4	691.8	692.3	692.8	693.1	693.3	693.5	693.7	694.0	693.7
130°	729.4	729.8	730.3	730.7	731.2	731.5	731.7	731.9	732.2	732.4	731.9
132.5°	765.4	766.0	766.6	767.2	767.9	768.3	768.5	768.8	769.0	769.2	769.3
135°	821.4	822.3	823.2	824.1	825.0	825.4	825.4	825.4	825.4	825.4	825.2
137.5°	876.2	877.4	878.5	879.6	880.7	881.1	880.9	880.6	880.3	880.0	879.6
140°	911.5	912.6	913.7	914.8	915.9	916.3	915.8	915.3	914.9	914.5	913.8
142.5°	945.1	946.2	947.4	948.4	949.5	949.9	949.7	949.4	949.2	948.9	948.0
145°	995.5	996.2	996.9	997.6	998.2	998.5	998.5	998.5	998.5	998.5	997.8
147.5°	1038.5	1040.1	1041.6	1043.1	1044.6	1045.1	1044.6	1044.0	1043.4	1042.9	1042.4
150°	1070.6	1071.0	1071.4	1071.9	1072.4	1072.5	1072.5	1072.5	1072.5	1072.5	1071.7
152.5°	1097.0	1097.8	1098.5	1099.4	1100.2	1100.3	1099.8	1099.2	1098.7	1098.2	1097.9
155°	1134.6	1135.7	1136.8	1137.9	1139.0	1139.2	1138.2	1137.4	1136.5	1135.6	1135.4
157.5°	1166.1	1167.5	1169.0	1170.4	1171.9	1172.2	1171.3	1170.4	1169.5	1168.6	1168.4
160°	1187.7	1188.7	1189.8	1190.9	1192.1	1192.1	1191.3	1190.4	1189.5	1188.6	1188.4
162.5°	1206.0	1207.3	1208.6	1209.9	1211.2	1211.3	1210.2	1209.2	1208.1	1207.0	1206.9
165°	1230.6	1232.0	1233.3	1234.7	1236.0	1236.2	1235.3	1234.4	1233.6	1232.6	1232.4
167.5°	1250.3	1251.6	1253.0	1254.4	1255.8	1255.8	1254.5	1253.1	1251.8	1250.4	1250.4
170°	1260.7	1262.2	1263.8	1265.3	1266.9	1267.0	1265.7	1264.3	1263.0	1261.6	1261.6
172.5°	1269.5	1270.8	1272.2	1273.6	1275.0	1275.0	1273.7	1272.3	1271.0	1269.6	1269.6
175°	1277.6	1279.2	1280.8	1282.4	1283.9	1284.0	1282.6	1281.3	1280.0	1278.7	1278.7
177.5°	1282.5	1283.8	1285.0	1286.2	1287.5	1287.5	1286.5	1285.4	1284.4	1283.2	1283.4
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	9.6	9.0	8.0	7.2	6.0	5.2	4.7	4.5	4.4	4.6	5.1
90°	12.9	11.4	9.8	8.1	6.4	4.6	2.8	1.0	2.8	4.6	6.4
92.5°	34.6	32.7	30.7	29.2	28.0	26.7	25.5	24.2	25.5	26.7	28.0
95°	72.6	70.3	68.1	66.8	66.4	66.0	65.4	65.0	65.4	66.0	66.4
97.5°	116.5	113.5	110.4	108.7	108.6	108.4	108.2	108.1	108.2	108.4	108.6
100°	147.3	144.4	141.5	140.1	140.1	140.1	140.1	140.1	140.1	140.1	140.1
102.5°	182.2	180.7	179.3	178.1	177.2	176.2	175.4	174.5	175.4	176.2	177.2
105°	236.4	235.1	233.8	232.6	231.4	230.3	229.2	228.1	229.2	230.3	231.4
107.5°	294.9	293.9	292.8	291.8	290.7	289.6	288.4	287.3	288.4	289.6	290.7
110°	334.8	334.2	333.5	332.6	331.5	330.4	329.2	328.2	329.2	330.4	331.5



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	374.5	373.7	372.8	372.1	371.5	370.9	370.4	369.8	370.4	370.9	371.5
115°	436.4	435.9	435.4	434.8	433.9	433.0	432.1	431.2	432.1	433.0	433.9
117.5°	495.7	495.2	494.8	494.5	494.0	493.7	493.3	492.8	493.3	493.7	494.0
120°	536.8	536.6	536.4	535.7	534.6	533.5	532.4	531.2	532.4	533.5	534.6
122.5°	576.2	575.6	575.0	574.5	574.1	573.7	573.3	572.9	573.3	573.7	574.1
125°	635.8	635.7	635.4	634.6	633.4	632.0	630.7	629.3	630.7	632.0	633.4
127.5°	693.4	693.2	692.9	692.4	691.6	690.9	690.1	689.4	690.1	690.9	691.6
130°	731.5	731.1	730.6	729.8	728.8	727.6	726.5	725.4	726.5	727.6	728.8
132.5°	769.4	769.5	769.6	768.7	766.9	765.1	763.2	761.4	763.2	765.1	766.9
135°	825.0	824.8	824.6	823.8	822.4	821.1	819.8	818.5	819.8	821.1	822.4
137.5°	879.1	878.6	878.1	877.2	875.9	874.6	873.3	872.0	873.3	874.6	875.9
140°	913.2	912.5	911.8	910.9	909.8	908.7	907.6	906.5	907.6	908.7	909.8
142.5°	947.2	946.3	945.6	944.6	943.7	942.8	941.8	940.9	941.8	942.8	943.7
145°	997.2	996.5	995.8	995.1	994.2	993.3	992.4	991.5	992.4	993.3	994.2
147.5°	1041.9	1041.4	1040.8	1040.3	1039.8	1039.3	1038.8	1038.4	1038.8	1039.3	1039.8
150°	1070.7	1069.9	1069.0	1068.7	1068.9	1069.1	1069.4	1069.5	1069.4	1069.1	1068.9
152.5°	1097.4	1097.1	1096.7	1096.4	1096.1	1095.8	1095.5	1095.2	1095.5	1095.8	1096.1
155°	1135.1	1135.0	1134.7	1134.6	1134.6	1134.6	1134.6	1134.6	1134.6	1134.6	1134.6
157.5°	1168.2	1167.9	1167.7	1167.9	1168.4	1168.8	1169.3	1169.8	1169.3	1168.8	1168.4
160°	1188.2	1187.9	1187.7	1187.9	1188.6	1189.3	1190.0	1190.6	1190.0	1189.3	1188.6
162.5°	1206.9	1206.9	1206.9	1207.0	1207.6	1208.1	1208.6	1209.0	1208.6	1208.1	1207.6
165°	1232.2	1232.0	1231.7	1231.8	1232.3	1232.8	1233.2	1233.6	1233.2	1232.8	1232.3
167.5°	1250.4	1250.4	1250.4	1250.9	1251.8	1252.7	1253.5	1254.5	1253.5	1252.7	1251.8
170°	1261.6	1261.6	1261.6	1262.1	1263.0	1263.9	1264.8	1265.7	1264.8	1263.9	1263.0
172.5°	1269.6	1269.6	1269.6	1270.1	1271.0	1271.9	1272.8	1273.7	1272.8	1271.9	1271.0
175°	1278.7	1278.7	1278.7	1279.1	1280.0	1280.9	1281.8	1282.6	1281.8	1280.9	1280.0
177.5°	1283.7	1283.8	1284.0	1284.4	1285.1	1285.8	1286.6	1287.3	1286.6	1285.8	1285.1
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	5.6	6.3	6.4	6.9	7.1	7.8	7.9	8.8	9.3	9.8	9.8
90°	8.1	9.8	11.4	12.9	14.5	16.0	17.1	18.3	19.4	20.5	21.4
92.5°	29.2	30.7	32.7	34.6	36.5	38.4	39.9	41.3	42.8	44.3	45.3
95°	66.8	68.1	70.3	72.6	74.8	77.1	78.6	80.2	81.7	83.3	84.3
97.5°	108.7	110.4	113.5	116.5	119.6	122.7	124.2	125.6	127.1	128.5	129.4
100°	140.1	141.5	144.4	147.3	150.2	153.1	155.1	157.0	159.1	161.1	162.3
102.5°	178.1	179.3	180.7	182.2	183.7	185.1	187.3	189.4	191.7	193.8	195.2
105°	232.6	233.8	235.1	236.4	237.8	239.1	240.5	241.8	243.1	244.4	245.5
107.5°	291.8	292.8	293.9	294.9	295.9	297.0	297.6	298.3	298.9	299.6	300.0
110°	332.6	333.5	334.2	334.8	335.5	336.1	336.8	337.5	338.2	338.8	339.1



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	372.1	372.8	373.7	374.5	375.3	376.2	376.5	376.9	377.1	377.5	377.4
115°	434.8	435.4	435.9	436.4	436.8	437.2	437.0	436.8	436.5	436.4	436.1
117.5°	494.5	494.8	495.2	495.7	496.0	496.5	496.6	496.8	497.0	497.1	496.8
120°	535.7	536.4	536.6	536.8	537.1	537.3	537.3	537.3	537.3	537.3	536.8
122.5°	574.5	575.0	575.6	576.2	576.7	577.3	577.1	577.0	576.8	576.6	576.2
125°	634.6	635.4	635.7	635.8	636.1	636.4	635.8	635.4	635.0	634.6	634.2
127.5°	692.4	692.9	693.2	693.4	693.7	694.0	693.7	693.5	693.3	693.1	692.8
130°	729.8	730.6	731.1	731.5	731.9	732.4	732.2	731.9	731.7	731.5	731.2
132.5°	768.7	769.6	769.5	769.4	769.3	769.2	769.0	768.8	768.5	768.3	767.9
135°	823.8	824.6	824.8	825.0	825.2	825.4	825.4	825.4	825.4	825.4	825.0
137.5°	877.2	878.1	878.6	879.1	879.6	880.0	880.3	880.6	880.9	881.1	880.7
140°	910.9	911.8	912.5	913.2	913.8	914.5	914.9	915.3	915.8	916.3	915.9
142.5°	944.6	945.6	946.3	947.2	948.0	948.9	949.2	949.4	949.7	949.9	949.5
145°	995.1	995.8	996.5	997.2	997.8	998.5	998.5	998.5	998.5	998.5	998.2
147.5°	1040.3	1040.8	1041.4	1041.9	1042.4	1042.9	1043.4	1044.0	1044.6	1045.1	1044.6
150°	1068.7	1069.0	1069.9	1070.7	1071.7	1072.5	1072.5	1072.5	1072.5	1072.5	1072.4
152.5°	1096.4	1096.7	1097.1	1097.4	1097.9	1098.2	1098.7	1099.2	1099.8	1100.3	1100.2
155°	1134.6	1134.7	1135.0	1135.1	1135.4	1135.6	1136.5	1137.4	1138.2	1139.2	1139.0
157.5°	1167.9	1167.7	1167.9	1168.2	1168.4	1168.6	1169.5	1170.4	1171.3	1172.2	1171.9
160°	1187.9	1187.7	1187.9	1188.2	1188.4	1188.6	1189.5	1190.4	1191.3	1192.1	1192.1
162.5°	1207.0	1206.9	1206.9	1206.9	1206.9	1207.0	1208.1	1209.2	1210.2	1211.3	1211.2
165°	1231.8	1231.7	1232.0	1232.2	1232.4	1232.6	1233.6	1234.4	1235.3	1236.2	1236.0
167.5°	1250.9	1250.4	1250.4	1250.4	1250.4	1250.4	1251.8	1253.1	1254.5	1255.8	1255.8
170°	1262.1	1261.6	1261.6	1261.6	1261.6	1261.6	1263.0	1264.3	1265.7	1267.0	1266.9
172.5°	1270.1	1269.6	1269.6	1269.6	1269.6	1269.6	1271.0	1272.3	1273.7	1275.0	1275.0
175°	1279.1	1278.7	1278.7	1278.7	1278.7	1278.7	1280.0	1281.3	1282.6	1284.0	1283.9
177.5°	1284.4	1284.0	1283.8	1283.7	1283.4	1283.2	1284.4	1285.4	1286.5	1287.5	1287.5
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	10.3	10.2	10.4	10.8	10.4	10.2	10.3	9.8	9.8	9.3	8.8
90°	22.0	22.6	23.3	24.0	23.3	22.6	22.0	21.4	20.5	19.4	18.3
92.5°	45.7	46.2	46.8	47.2	46.8	46.2	45.7	45.3	44.3	42.8	41.3
95°	84.7	85.2	85.6	86.0	85.6	85.2	84.7	84.3	83.3	81.7	80.2
97.5°	129.7	129.9	130.2	130.4	130.2	129.9	129.7	129.4	128.5	127.1	125.6
100°	162.7	163.2	163.7	164.1	163.7	163.2	162.7	162.3	161.1	159.1	157.0
102.5°	195.9	196.5	197.1	197.7	197.1	196.5	195.9	195.2	193.8	191.7	189.4
105°	246.2	246.8	247.5	248.1	247.5	246.8	246.2	245.5	244.4	243.1	241.8
107.5°	299.9	299.9	299.8	299.7	299.8	299.9	299.9	300.0	299.6	298.9	298.3
110°	338.8	338.6	338.4	338.2	338.4	338.6	338.8	339.1	338.8	338.2	337.5



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	377.0	376.6	376.2	375.8	376.2	376.6	377.0	377.4	377.5	377.1	376.9
115°	435.9	435.7	435.4	435.2	435.4	435.7	435.9	436.1	436.4	436.5	436.8
117.5°	495.9	495.1	494.1	493.3	494.1	495.1	495.9	496.8	497.1	497.0	496.8
120°	536.0	535.0	534.2	533.3	534.2	535.0	536.0	536.8	537.3	537.3	537.3
122.5°	575.4	574.7	574.0	573.3	574.0	574.7	575.4	576.2	576.6	576.8	577.0
125°	634.0	633.8	633.5	633.4	633.5	633.8	634.0	634.2	634.6	635.0	635.4
127.5°	692.3	691.8	691.4	691.0	691.4	691.8	692.3	692.8	693.1	693.3	693.5
130°	730.7	730.3	729.8	729.4	729.8	730.3	730.7	731.2	731.5	731.7	731.9
132.5°	767.2	766.6	766.0	765.4	766.0	766.6	767.2	767.9	768.3	768.5	768.8
135°	824.1	823.2	822.3	821.4	822.3	823.2	824.1	825.0	825.4	825.4	825.4
137.5°	879.6	878.5	877.4	876.2	877.4	878.5	879.6	880.7	881.1	880.9	880.6
140°	914.8	913.7	912.6	911.5	912.6	913.7	914.8	915.9	916.3	915.8	915.3
142.5°	948.4	947.4	946.2	945.1	946.2	947.4	948.4	949.5	949.9	949.7	949.4
145°	997.6	996.9	996.2	995.5	996.2	996.9	997.6	998.2	998.5	998.5	998.5
147.5°	1043.1	1041.6	1040.1	1038.5	1040.1	1041.6	1043.1	1044.6	1045.1	1044.6	1044.0
150°	1071.9	1071.4	1071.0	1070.6	1071.0	1071.4	1071.9	1072.4	1072.5	1072.5	1072.5
152.5°	1099.4	1098.5	1097.8	1097.0	1097.8	1098.5	1099.4	1100.2	1100.3	1099.8	1099.2
155°	1137.9	1136.8	1135.7	1134.6	1135.7	1136.8	1137.9	1139.0	1139.2	1138.2	1137.4
157.5°	1170.4	1169.0	1167.5	1166.1	1167.5	1169.0	1170.4	1171.9	1172.2	1171.3	1170.4
160°	1190.9	1189.8	1188.7	1187.7	1188.7	1189.8	1190.9	1192.1	1192.1	1191.3	1190.4
162.5°	1209.9	1208.6	1207.3	1206.0	1207.3	1208.6	1209.9	1211.2	1211.3	1210.2	1209.2
165°	1234.7	1233.3	1232.0	1230.6	1232.0	1233.3	1234.7	1236.0	1236.2	1235.3	1234.4
167.5°	1254.4	1253.0	1251.6	1250.3	1251.6	1253.0	1254.4	1255.8	1255.8	1254.5	1253.1
170°	1265.3	1263.8	1262.2	1260.7	1262.2	1263.8	1265.3	1266.9	1267.0	1265.7	1264.3
172.5°	1273.6	1272.2	1270.8	1269.5	1270.8	1272.2	1273.6	1275.0	1275.0	1273.7	1272.3
175°	1282.4	1280.8	1279.2	1277.6	1279.2	1280.8	1282.4	1283.9	1284.0	1282.6	1281.3
177.5°	1286.2	1285.0	1283.8	1282.5	1283.8	1285.0	1286.2	1287.5	1287.5	1286.5	1285.4
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	7.9	7.8	7.1	6.9	6.4	6.3	5.6	5.1	4.6	4.4	4.5
90°	17.1	16.0	14.5	12.9	11.4	9.8	8.1	6.4	4.6	2.8	1.0
92.5°	39.9	38.4	36.5	34.6	32.7	30.7	29.2	28.0	26.7	25.5	24.2
95°	78.6	77.1	74.8	72.6	70.3	68.1	66.8	66.4	66.0	65.4	65.0
97.5°	124.2	122.7	119.6	116.5	113.5	110.4	108.7	108.6	108.4	108.2	108.1
100°	155.1	153.1	150.2	147.3	144.4	141.5	140.1	140.1	140.1	140.1	140.1
102.5°	187.3	185.1	183.7	182.2	180.7	179.3	178.1	177.2	176.2	175.4	174.5
105°	240.5	239.1	237.8	236.4	235.1	233.8	232.6	231.4	230.3	229.2	228.1
107.5°	297.6	297.0	295.9	294.9	293.9	292.8	291.8	290.7	289.6	288.4	287.3
110°	336.8	336.1	335.5	334.8	334.2	333.5	332.6	331.5	330.4	329.2	328.2



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	376.5	376.2	375.3	374.5	373.7	372.8	372.1	371.5	370.9	370.4	369.8
115°	437.0	437.2	436.8	436.4	435.9	435.4	434.8	433.9	433.0	432.1	431.2
117.5°	496.6	496.5	496.0	495.7	495.2	494.8	494.5	494.0	493.7	493.3	492.8
120°	537.3	537.3	537.1	536.8	536.6	536.4	535.7	534.6	533.5	532.4	531.2
122.5°	577.1	577.3	576.7	576.2	575.6	575.0	574.5	574.1	573.7	573.3	572.9
125°	635.8	636.4	636.1	635.8	635.7	635.4	634.6	633.4	632.0	630.7	629.3
127.5°	693.7	694.0	693.7	693.4	693.2	692.9	692.4	691.6	690.9	690.1	689.4
130°	732.2	732.4	731.9	731.5	731.1	730.6	729.8	728.8	727.6	726.5	725.4
132.5°	769.0	769.2	769.3	769.4	769.5	769.6	768.7	766.9	765.1	763.2	761.4
135°	825.4	825.4	825.2	825.0	824.8	824.6	823.8	822.4	821.1	819.8	818.5
137.5°	880.3	880.0	879.6	879.1	878.6	878.1	877.2	875.9	874.6	873.3	872.0
140°	914.9	914.5	913.8	913.2	912.5	911.8	910.9	909.8	908.7	907.6	906.5
142.5°	949.2	948.9	948.0	947.2	946.3	945.6	944.6	943.7	942.8	941.8	940.9
145°	998.5	998.5	997.8	997.2	996.5	995.8	995.1	994.2	993.3	992.4	991.5
147.5°	1043.4	1042.9	1042.4	1041.9	1041.4	1040.8	1040.3	1039.8	1039.3	1038.8	1038.4
150°	1072.5	1072.5	1071.7	1070.7	1069.9	1069.0	1068.7	1068.9	1069.1	1069.4	1069.5
152.5°	1098.7	1098.2	1097.9	1097.4	1097.1	1096.7	1096.4	1096.1	1095.8	1095.5	1095.2
155°	1136.5	1135.6	1135.4	1135.1	1135.0	1134.7	1134.6	1134.6	1134.6	1134.6	1134.6
157.5°	1169.5	1168.6	1168.4	1168.2	1167.9	1167.7	1167.9	1168.4	1168.8	1169.3	1169.8
160°	1189.5	1188.6	1188.4	1188.2	1187.9	1187.7	1187.9	1188.6	1189.3	1190.0	1190.6
162.5°	1208.1	1207.0	1206.9	1206.9	1206.9	1206.9	1207.0	1207.6	1208.1	1208.6	1209.0
165°	1233.6	1232.6	1232.4	1232.2	1232.0	1231.7	1231.8	1232.3	1232.8	1233.2	1233.6
167.5°	1251.8	1250.4	1250.4	1250.4	1250.4	1250.4	1250.9	1251.8	1252.7	1253.5	1254.5
170°	1263.0	1261.6	1261.6	1261.6	1261.6	1261.6	1262.1	1263.0	1263.9	1264.8	1265.7
172.5°	1271.0	1269.6	1269.6	1269.6	1269.6	1269.6	1270.1	1271.0	1271.9	1272.8	1273.7
175°	1280.0	1278.7	1278.7	1278.7	1278.7	1278.7	1279.1	1280.0	1280.9	1281.8	1282.6
177.5°	1284.4	1283.2	1283.4	1283.7	1283.8	1284.0	1284.4	1285.1	1285.8	1286.6	1287.3
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.7	5.2	6.0	7.2	8.0	9.0	9.6	9.6	9.2	9.0	8.8
90°	2.8	4.6	6.4	8.1	9.8	11.4	12.9	14.5	16.0	17.1	18.3
92.5°	25.5	26.7	28.0	29.2	30.7	32.7	34.6	36.5	38.4	39.9	41.3
95°	65.4	66.0	66.4	66.8	68.1	70.3	72.6	74.8	77.1	78.6	80.2
97.5°	108.2	108.4	108.6	108.7	110.4	113.5	116.5	119.6	122.7	124.2	125.6
100°	140.1	140.1	140.1	140.1	141.5	144.4	147.3	150.2	153.1	155.1	157.0
102.5°	175.4	176.2	177.2	178.1	179.3	180.7	182.2	183.7	185.1	187.3	189.4
105°	229.2	230.3	231.4	232.6	233.8	235.1	236.4	237.8	239.1	240.5	241.8
107.5°	288.4	289.6	290.7	291.8	292.8	293.9	294.9	295.9	297.0	297.6	298.3
110°	329.2	330.4	331.5	332.6	333.5	334.2	334.8	335.5	336.1	336.8	337.5



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	370.4	370.9	371.5	372.1	372.8	373.7	374.5	375.3	376.2	376.5	376.9
115°	432.1	433.0	433.9	434.8	435.4	435.9	436.4	436.8	437.2	437.0	436.8
117.5°	493.3	493.7	494.0	494.5	494.8	495.2	495.7	496.0	496.5	496.6	496.8
120°	532.4	533.5	534.6	535.7	536.4	536.6	536.8	537.1	537.3	537.3	537.3
122.5°	573.3	573.7	574.1	574.5	575.0	575.6	576.2	576.7	577.3	577.1	577.0
125°	630.7	632.0	633.4	634.6	635.4	635.7	635.8	636.1	636.4	635.8	635.4
127.5°	690.1	690.9	691.6	692.4	692.9	693.2	693.4	693.7	694.0	693.7	693.5
130°	726.5	727.6	728.8	729.8	730.6	731.1	731.5	731.9	732.4	732.2	731.9
132.5°	763.2	765.1	766.9	768.7	769.6	769.5	769.4	769.3	769.2	769.0	768.8
135°	819.8	821.1	822.4	823.8	824.6	824.8	825.0	825.2	825.4	825.4	825.4
137.5°	873.3	874.6	875.9	877.2	878.1	878.6	879.1	879.6	880.0	880.3	880.6
140°	907.6	908.7	909.8	910.9	911.8	912.5	913.2	913.8	914.5	914.9	915.3
142.5°	941.8	942.8	943.7	944.6	945.6	946.3	947.2	948.0	948.9	949.2	949.4
145°	992.4	993.3	994.2	995.1	995.8	996.5	997.2	997.8	998.5	998.5	998.5
147.5°	1038.8	1039.3	1039.8	1040.3	1040.8	1041.4	1041.9	1042.4	1042.9	1043.4	1044.0
150°	1069.4	1069.1	1068.9	1068.7	1069.0	1069.9	1070.7	1071.7	1072.5	1072.5	1072.5
152.5°	1095.5	1095.8	1096.1	1096.4	1096.7	1097.1	1097.4	1097.9	1098.2	1098.7	1099.2
155°	1134.6	1134.6	1134.6	1134.6	1134.7	1135.0	1135.1	1135.4	1135.6	1136.5	1137.4
157.5°	1169.3	1168.8	1168.4	1167.9	1167.7	1167.9	1168.2	1168.4	1168.6	1169.5	1170.4
160°	1190.0	1189.3	1188.6	1187.9	1187.7	1187.9	1188.2	1188.4	1188.6	1189.5	1190.4
162.5°	1208.6	1208.1	1207.6	1207.0	1206.9	1206.9	1206.9	1206.9	1207.0	1208.1	1209.2
165°	1233.2	1232.8	1232.3	1231.8	1231.7	1232.0	1232.2	1232.4	1232.6	1233.6	1234.4
167.5°	1253.5	1252.7	1251.8	1250.9	1250.4	1250.4	1250.4	1250.4	1250.4	1251.8	1253.1
170°	1264.8	1263.9	1263.0	1262.1	1261.6	1261.6	1261.6	1261.6	1261.6	1263.0	1264.3
172.5°	1272.8	1271.9	1271.0	1270.1	1269.6	1269.6	1269.6	1269.6	1269.6	1271.0	1272.3
175°	1281.8	1280.9	1280.0	1279.1	1278.7	1278.7	1278.7	1278.7	1278.7	1280.0	1281.3
177.5°	1286.6	1285.8	1285.1	1284.4	1284.0	1283.8	1283.7	1283.4	1283.2	1284.4	1285.4
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	9.0	8.5	8.7	8.7	8.9	8.8	8.6
90°	19.4	20.5	21.4	22.0	22.6	23.3	24.0
92.5°	42.8	44.3	45.3	45.7	46.2	46.8	47.2
95°	81.7	83.3	84.3	84.7	85.2	85.6	86.0
97.5°	127.1	128.5	129.4	129.7	129.9	130.2	130.4
100°	159.1	161.1	162.3	162.7	163.2	163.7	164.1
102.5°	191.7	193.8	195.2	195.9	196.5	197.1	197.7
105°	243.1	244.4	245.5	246.2	246.8	247.5	248.1
107.5°	298.9	299.6	300.0	299.9	299.9	299.8	299.7
110°	338.2	338.8	339.1	338.8	338.6	338.4	338.2



TEST NUMBER: P333152-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	377.1	377.5	377.4	377.0	376.6	376.2	375.8
115°	436.5	436.4	436.1	435.9	435.7	435.4	435.2
117.5°	497.0	497.1	496.8	495.9	495.1	494.1	493.3
120°	537.3	537.3	536.8	536.0	535.0	534.2	533.3
122.5°	576.8	576.6	576.2	575.4	574.7	574.0	573.3
125°	635.0	634.6	634.2	634.0	633.8	633.5	633.4
127.5°	693.3	693.1	692.8	692.3	691.8	691.4	691.0
130°	731.7	731.5	731.2	730.7	730.3	729.8	729.4
132.5°	768.5	768.3	767.9	767.2	766.6	766.0	765.4
135°	825.4	825.4	825.0	824.1	823.2	822.3	821.4
137.5°	880.9	881.1	880.7	879.6	878.5	877.4	876.2
140°	915.8	916.3	915.9	914.8	913.7	912.6	911.5
142.5°	949.7	949.9	949.5	948.4	947.4	946.2	945.1
145°	998.5	998.5	998.2	997.6	996.9	996.2	995.5
147.5°	1044.6	1045.1	1044.6	1043.1	1041.6	1040.1	1038.5
150°	1072.5	1072.5	1072.4	1071.9	1071.4	1071.0	1070.6
152.5°	1099.8	1100.3	1100.2	1099.4	1098.5	1097.8	1097.0
155°	1138.2	1139.2	1139.0	1137.9	1136.8	1135.7	1134.6
157.5°	1171.3	1172.2	1171.9	1170.4	1169.0	1167.5	1166.1
160°	1191.3	1192.1	1192.1	1190.9	1189.8	1188.7	1187.7
162.5°	1210.2	1211.3	1211.2	1209.9	1208.6	1207.3	1206.0
165°	1235.3	1236.2	1236.0	1234.7	1233.3	1232.0	1230.6
167.5°	1254.5	1255.8	1255.8	1254.4	1253.0	1251.6	1250.3
170°	1265.7	1267.0	1266.9	1265.3	1263.8	1262.2	1260.7
172.5°	1273.7	1275.0	1275.0	1273.6	1272.2	1270.8	1269.5
175°	1282.6	1284.0	1283.9	1282.4	1280.8	1279.2	1277.6
177.5°	1286.5	1287.5	1287.5	1286.2	1285.0	1283.8	1282.5
180°	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6	1285.6

(END OF REPORT)