

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333123-935

Luminaire Tested: **S125DIP-S375D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333123-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U935-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2441.5 lumens  
Efficiency: N/A  
Efficacy: 120.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	38	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3249	3249	3249
5°	3255	3225	3245
10°	3236	3202	3220
15°	3201	3163	3177
20°	3151	3110	3115
25°	3096	3046	3043
30°	3030	2976	2961
35°	2958	2902	2861
40°	2885	2822	2780
45°	2806	2747	2693
50°	2719	2659	2579
55°	2634	2558	2486
60°	2533	2457	2370
65°	2415	2335	2257
70°	2298	2194	2119
75°	2094	2026	1956
80°	1863	1834	1789
85°	1623	1652	1564



TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	1.9
10°-20°	134.0	5.5
20°-30°	197.8	8.1
30°-40°	230.8	9.5
40°-50°	231.8	9.5
50°-60°	203.5	8.3
60°-70°	151.6	6.2
70°-80°	86.7	3.6
80°-90°	26.1	1.1
90°-100°	109.4	4.5
100°-110°	235.2	9.6
110°-120°	220.7	9.0
120°-130°	178.9	7.3
130°-140°	143.5	5.9
140°-150°	108.3	4.4
150°-160°	76.2	3.1
160°-170°	44.9	1.8
170°-180°	14.6	0.6
0°-30°	379.2	15.5
0°-40°	610.0	25.0
0°-60°	1045.3	42.8
0°-90°	1309.7	53.6
90°-120°	565.3	23.2
90°-150°	996.0	40.8
90°-180°	1132.0	46.4
0°-180°	2441.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	503	503	503	503	503	
5°	502	501	497	501	501	48
15°	479	477	473	475	475	135
25°	434	432	427	428	427	200
35°	375	373	368	366	363	235
45°	307	305	301	296	295	237
55°	234	232	227	224	221	209
65°	158	157	153	149	148	157
75°	84	83	81	80	78	89
85°	22	22	22	22	21	24
90°	0	3	5	6	7	2
95°	10	30	270	122	72	11
105°	34	48	221	434	403	36
115°	62	74	177	382	449	60
125°	85	100	170	304	354	76
135°	100	120	169	255	294	77
145°	116	133	169	211	232	73
155°	133	143	165	186	194	61
165°	145	149	158	168	170	41
175°	151	151	152	154	153	14
180°	151	151	151	151	151	



TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	504.2	504.0	503.9	503.6	503.4	502.9	502.2	501.5	500.8	500.1	500.8
5°	502.1	502.0	501.8	501.6	501.4	500.9	500.1	499.2	498.3	497.4	498.2
7.5°	497.6	497.4	497.2	497.1	496.9	496.3	495.3	494.3	493.4	492.4	493.2
10°	493.4	493.3	493.1	492.9	492.8	492.1	491.2	490.2	489.2	488.3	489.0
12.5°	488.4	488.0	487.7	487.4	487.1	486.5	485.5	484.7	483.7	482.8	483.4
15°	478.7	478.5	478.2	477.9	477.6	477.0	476.0	475.1	474.1	473.1	473.6
17.5°	467.6	467.3	466.8	466.5	466.1	465.4	464.3	463.4	462.4	461.3	461.9
20°	458.4	458.2	458.1	457.9	457.7	457.0	455.9	454.7	453.6	452.5	453.1
22.5°	449.2	448.8	448.5	448.2	447.9	447.2	446.1	445.1	443.9	442.9	443.3
25°	434.5	434.1	433.6	433.2	432.7	432.0	430.8	429.6	428.5	427.4	427.6
27.5°	417.4	417.2	416.9	416.6	416.4	415.6	414.5	413.3	412.1	410.9	411.0
30°	406.3	406.0	405.7	405.4	405.2	404.4	403.1	401.7	400.5	399.1	398.9
32.5°	394.2	393.7	393.4	393.0	392.5	391.8	390.5	389.3	388.2	387.0	386.7
35°	375.2	374.9	374.5	374.2	373.8	373.0	371.8	370.6	369.3	368.1	367.6
37.5°	355.6	355.2	354.7	354.2	353.8	353.0	351.8	350.7	349.5	348.4	347.7
40°	342.2	341.7	341.3	340.9	340.4	339.6	338.4	337.2	335.9	334.7	333.9
42.5°	327.9	327.5	327.2	326.7	326.4	325.6	324.3	323.1	321.8	320.6	319.9
45°	307.2	306.9	306.5	306.2	305.7	305.1	304.0	303.0	301.9	300.8	299.8
47.5°	284.9	284.9	284.9	285.0	285.0	284.4	283.1	281.8	280.5	279.2	278.2
50°	270.6	270.4	270.1	269.8	269.5	268.9	267.8	266.7	265.7	264.6	263.5
52.5°	256.0	255.7	255.5	255.4	255.2	254.5	253.4	252.3	251.1	249.9	249.0
55°	233.9	233.7	233.4	233.2	232.9	232.1	230.9	229.7	228.4	227.2	226.4
57.5°	210.9	210.7	210.5	210.4	210.3	209.7	208.6	207.6	206.6	205.5	204.5
60°	196.1	195.8	195.4	195.1	194.8	194.1	193.1	192.2	191.1	190.2	189.3
62.5°	180.9	180.6	180.3	180.0	179.8	179.2	178.4	177.5	176.7	175.9	175.0
65°	158.0	157.8	157.6	157.5	157.3	156.7	155.8	154.7	153.8	152.8	152.0
67.5°	135.8	135.4	135.0	134.7	134.3	133.7	133.0	132.2	131.6	130.9	130.2
70°	121.7	121.3	120.9	120.5	120.0	119.3	118.6	117.8	117.0	116.2	115.6
72.5°	106.5	106.2	105.9	105.6	105.3	104.9	104.4	103.8	103.3	102.8	102.2
75°	83.9	83.8	83.6	83.4	83.3	82.9	82.5	82.1	81.6	81.2	80.9
77.5°	63.2	63.1	63.0	62.9	62.9	62.8	62.5	62.3	62.0	61.7	61.6
80°	50.1	50.1	50.1	50.1	50.1	50.0	49.9	49.7	49.5	49.3	49.2
82.5°	38.7	38.6	38.4	38.2	38.1	38.1	38.0	38.0	37.9	37.9	37.7
85°	21.9	22.0	22.0	22.1	22.2	22.3	22.3	22.3	22.3	22.3	22.2
87.5°	8.7	8.7	8.9	9.0	9.0	9.1	9.1	9.2	9.2	9.2	9.3
90°	0.3	0.6	1.2	1.8	2.4	3.0	3.4	4.0	4.2	4.9	5.2
92.5°	3.7	4.5	7.1	10.8	16.1	25.0	41.6	69.4	99.7	98.1	79.4
95°	10.1	10.3	12.7	16.1	22.8	36.5	69.1	136.0	220.0	269.6	263.8
97.5°	16.7	17.0	18.8	22.1	28.2	38.0	59.5	108.6	196.5	287.9	333.8
100°	21.3	21.9	23.2	26.4	32.3	41.4	59.1	98.6	175.3	274.7	350.9
102.5°	26.4	26.8	27.7	31.3	36.7	45.5	61.2	94.5	159.2	251.7	340.6
105°	34.4	34.4	35.9	38.9	43.8	52.3	65.7	92.8	143.6	220.6	308.0
107.5°	42.2	42.8	44.3	46.8	51.8	59.5	72.4	95.6	137.1	199.2	274.6
110°	47.8	48.4	49.6	52.3	56.9	64.8	77.3	98.3	135.1	189.2	255.6



TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	53.4	54.0	54.9	57.7	62.3	69.9	81.9	101.7	135.1	183.4	241.5
115°	61.5	62.1	63.0	65.7	70.3	77.9	89.2	106.8	136.0	177.1	226.1
117.5°	68.8	69.7	70.7	73.4	78.6	85.9	96.6	112.6	138.0	174.0	216.9
120°	73.6	74.6	75.8	78.5	83.7	91.3	101.9	116.6	140.0	172.5	211.8
122.5°	78.8	79.4	80.4	83.2	88.8	96.4	107.0	120.9	141.6	171.3	207.4
125°	85.2	85.8	87.3	90.1	95.8	103.8	113.8	126.9	144.6	169.8	201.5
127.5°	90.2	91.2	93.1	96.6	102.7	110.6	120.3	132.3	147.7	169.1	196.0
130°	93.4	94.4	96.8	100.7	107.1	115.0	124.4	136.0	149.7	168.6	192.3
132.5°	95.8	97.0	100.0	104.4	111.0	118.9	128.4	139.2	151.9	168.6	189.4
135°	99.8	101.0	104.7	109.5	116.0	124.2	133.5	143.6	154.9	168.6	185.9
137.5°	104.8	105.7	109.1	114.0	120.3	128.7	137.3	146.9	157.6	168.9	182.8
140°	107.7	108.7	112.3	117.2	123.0	131.1	140.0	149.1	158.9	169.2	181.3
142.5°	111.2	111.8	115.2	120.1	125.6	133.4	141.6	150.3	159.5	169.4	180.1
145°	116.2	116.8	119.9	124.2	129.7	136.6	144.6	152.1	160.3	169.2	178.3
147.5°	121.6	121.9	124.6	128.5	133.3	139.4	146.4	153.3	160.7	168.4	176.4
150°	124.8	125.4	127.5	131.5	135.7	140.9	147.6	153.9	160.7	167.6	175.0
152.5°	128.2	128.5	130.4	133.9	137.9	142.6	148.8	154.5	160.4	166.7	173.2
155°	132.7	132.7	134.5	137.5	140.6	144.8	150.0	154.9	159.7	165.0	170.4
157.5°	136.7	136.6	138.1	140.7	143.4	146.6	151.0	155.2	158.9	163.1	167.7
160°	139.4	139.1	140.3	142.4	144.8	147.6	151.5	155.2	158.3	161.9	165.6
162.5°	141.5	141.3	142.5	144.4	146.3	148.5	152.1	155.0	157.5	160.4	163.6
165°	144.8	144.2	145.2	146.6	147.9	149.7	152.1	154.5	156.4	158.3	160.7
167.5°	147.1	146.7	147.3	148.1	149.0	150.2	152.1	153.9	154.7	156.1	157.8
170°	148.5	148.2	148.5	149.1	149.7	150.6	152.1	153.3	153.9	154.9	156.1
172.5°	149.5	149.0	149.2	149.8	150.2	150.6	151.9	152.9	153.0	153.4	154.4
175°	150.6	150.0	150.3	150.6	150.6	150.6	151.5	152.1	151.9	151.9	152.1
177.5°	151.2	150.7	150.7	150.9	150.7	150.7	151.2	151.4	150.9	150.9	151.2
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	501.5	502.2	502.9	503.3	503.2	503.1	503.1	503.0
5°	498.9	499.8	500.6	500.9	500.8	500.8	500.7	500.6
7.5°	494.0	494.7	495.5	495.8	495.8	495.7	495.6	495.5
10°	489.7	490.3	491.1	491.4	491.3	491.2	491.1	491.0
12.5°	484.0	484.6	485.1	485.3	485.3	485.3	485.3	485.3
15°	474.0	474.4	474.9	475.1	475.1	475.1	475.1	475.1
17.5°	462.4	463.0	463.6	463.6	463.1	462.7	462.3	461.8
20°	453.7	454.3	454.9	455.0	454.5	454.1	453.7	453.2
22.5°	443.7	444.1	444.5	444.5	444.3	443.9	443.7	443.3
25°	427.7	427.9	428.1	428.0	427.7	427.5	427.2	427.0
27.5°	411.0	411.0	411.0	411.0	410.6	410.4	410.1	409.8
30°	398.7	398.6	398.4	398.2	398.0	397.7	397.4	397.1
32.5°	386.4	386.1	385.7	385.4	384.9	384.4	383.9	383.4
35°	367.2	366.8	366.3	365.8	365.1	364.3	363.6	362.9
37.5°	347.1	346.4	345.7	345.2	344.7	344.4	344.0	343.5
40°	333.0	332.3	331.5	331.0	330.7	330.4	330.1	329.8
42.5°	319.2	318.5	317.7	317.2	316.8	316.3	316.0	315.6
45°	298.7	297.6	296.6	295.9	295.7	295.4	295.2	294.9
47.5°	277.1	276.0	274.9	274.1	273.5	272.9	272.2	271.6
50°	262.3	261.1	260.0	259.2	258.5	257.9	257.3	256.7
52.5°	248.0	246.9	245.9	245.1	244.4	243.7	243.1	242.4
55°	225.6	224.8	224.0	223.3	222.7	222.1	221.4	220.8
57.5°	203.5	202.4	201.4	200.7	200.4	200.0	199.7	199.3
60°	188.5	187.5	186.7	185.9	185.3	184.7	184.1	183.5
62.5°	174.0	173.0	172.0	171.3	170.9	170.4	169.9	169.4
65°	151.2	150.4	149.6	149.0	148.7	148.4	148.0	147.7
67.5°	129.5	128.8	128.1	127.7	127.5	127.3	127.1	126.8
70°	115.1	114.6	114.1	113.7	113.3	113.0	112.5	112.2
72.5°	101.6	101.0	100.4	100.0	99.6	99.3	98.8	98.5
75°	80.7	80.4	80.1	79.8	79.5	79.1	78.8	78.4
77.5°	61.5	61.3	61.1	61.0	60.7	60.4	60.2	59.9
80°	49.2	49.1	49.0	48.8	48.6	48.5	48.3	48.1
82.5°	37.5	37.4	37.3	37.1	37.1	37.1	37.0	37.0
85°	22.1	22.0	22.0	21.8	21.6	21.4	21.3	21.1
87.5°	9.4	9.5	9.5	9.6	9.4	9.3	9.2	9.0
90°	5.5	5.8	6.1	6.7	6.7	6.7	7.0	7.0
92.5°	53.9	39.1	29.4	25.0	21.1	20.3	19.9	19.4
95°	218.8	172.5	135.1	109.5	87.9	78.8	76.4	71.5
97.5°	325.8	293.4	256.9	221.4	202.6	185.5	176.8	172.8
100°	374.3	359.4	328.0	296.4	275.3	253.5	242.2	237.4
102.5°	390.5	399.8	384.8	363.3	340.9	325.3	313.1	309.4
105°	381.0	422.7	436.0	432.7	422.9	412.9	406.8	403.2
107.5°	346.6	402.3	436.6	452.5	457.4	457.4	455.4	453.0
110°	321.3	379.2	422.1	447.9	461.6	467.4	469.5	469.5





TEST NUMBER: P333123-935

CATALOG NUMBER: S125DIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.4	356.3	399.7	430.2	450.1	460.1	465.4	467.6
115°	276.3	323.5	365.2	398.3	422.1	436.6	445.1	449.1
117.5°	260.1	300.7	336.7	367.1	390.8	406.0	414.4	416.8
120°	251.3	287.8	321.3	348.1	370.7	385.2	393.5	395.9
122.5°	244.8	278.6	308.4	333.5	353.6	367.0	375.2	377.4
125°	235.2	266.2	292.7	314.6	331.7	344.1	350.9	353.9
127.5°	225.5	254.4	279.1	299.6	315.1	326.1	332.4	333.8
130°	219.4	246.2	269.9	289.7	304.9	315.0	321.1	322.9
132.5°	213.3	238.4	259.9	279.0	294.2	304.2	309.8	311.9
135°	205.4	226.4	245.9	263.2	276.6	286.6	292.1	293.9
137.5°	198.7	215.7	231.9	246.6	258.6	267.7	272.8	274.7
140°	195.0	209.3	223.3	236.1	247.4	255.3	259.8	261.4
142.5°	191.9	204.0	216.0	227.1	236.7	243.4	247.7	249.0
145°	187.8	197.2	206.6	214.8	222.1	227.3	230.7	231.9
147.5°	183.8	191.5	198.8	205.0	210.8	214.9	216.8	217.4
150°	181.7	188.4	194.2	199.6	204.1	207.8	209.1	209.3
152.5°	179.3	185.2	190.5	194.8	198.5	201.5	202.7	203.0
155°	175.6	180.5	184.7	188.0	191.1	193.2	194.2	194.4
157.5°	171.9	175.9	179.3	181.8	184.3	186.0	186.8	186.8
160°	169.5	172.5	175.6	177.7	179.9	181.3	181.9	181.7
162.5°	166.8	169.6	172.2	174.1	175.7	176.9	177.1	177.0
165°	163.1	165.2	167.0	168.6	169.8	170.4	170.4	170.4
167.5°	159.5	161.0	162.4	163.5	164.1	164.6	164.4	164.3
170°	157.6	158.5	159.5	160.1	160.7	161.0	161.0	160.7
172.5°	155.4	156.4	157.0	157.4	157.5	158.1	157.6	157.2
175°	153.1	153.1	153.7	153.7	153.7	153.9	153.3	153.1
177.5°	151.4	151.6	151.6	151.6	151.4	151.6	150.9	150.9
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9

(END OF REPORT)