

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331413-927

Luminaire Tested: **SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331413-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6351.8 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	98	94	90	86	90	86	83	80	73	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40				35	
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34				30	
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30				26	
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	32	29	26				23	
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24				21	
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				17	
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17				15	
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16				14	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22083	22083	22083	22083
5°	24759	22227	19697	22227
10°	28370	22046	17046	22046
15°	31385	21641	15059	21641
20°	30907	21206	13728	21206
25°	27868	20630	12886	20630
30°	23029	19708	12269	19708
35°	16783	18743	11832	18743
40°	13405	17606	11590	17606
45°	11714	16287	11259	16287
50°	11012	15013	11037	15013
55°	10151	13717	10742	13717
60°	9300	12339	10285	12339
65°	8474	11106	9838	11106
70°	7695	9904	9182	9904
75°	6818	8559	8135	8559
80°	5867	7085	6546	7085
85°	5261	5261	3890	5261



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.1
10°-20°	378.7	6.0
20°-30°	549.6	8.7
30°-40°	579.9	9.1
40°-50°	513.5	8.1
50°-60°	409.8	6.5
60°-70°	278.5	4.4
70°-80°	142.8	2.2
80°-90°	38.7	0.6
90°-100°	191.3	3.0
100°-110°	649.3	10.2
110°-120°	689.8	10.9
120°-130°	567.8	8.9
130°-140°	456.0	7.2
140°-150°	344.6	5.4
150°-160°	242.2	3.8
160°-170°	142.6	2.2
170°-180°	46.4	0.7
0°-30°	1058.5	16.7
0°-40°	1638.5	25.8
0°-60°	2561.8	40.3
0°-90°	3021.8	47.6
90°-120°	1530.4	24.1
90°-150°	2898.8	45.6
90°-180°	3330.0	52.4
0°-180°	6351.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1368	1368	1368	1368	1368	
5°	1528	1371	1215	1371	1528	153
15°	1878	1295	901	1295	1878	518
25°	1564	1158	723	1158	1564	707
35°	852	951	600	951	852	554
45°	513	713	493	713	513	403
55°	361	487	382	487	361	323
65°	222	291	258	291	222	221
75°	109	137	130	137	109	117
85°	28	28	21	28	28	32
90°	30	1	30	1	30	18
95°	105	32	105	32	105	136
105°	1037	112	1037	112	1037	1003
115°	1365	198	1365	198	1365	1336
125°	1107	276	1107	276	1107	1000
135°	918	324	918	324	918	713
145°	732	370	732	370	732	465
155°	616	421	616	421	616	287
165°	540	458	540	458	540	154
175°	487	478	487	478	487	47
180°	479	479	479	479	479	



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1430.8	1431.2	1432.1	1425.4	1424.5	1424.5	1418.6	1413.6	1407.7	1399.7	1400.6
5°	1527.6	1533.3	1535.4	1529.1	1519.6	1518.6	1509.7	1494.9	1481.3	1470.2	1462.4
7.5°	1643.0	1645.3	1640.1	1631.8	1624.8	1612.2	1595.5	1579.3	1556.5	1535.6	1520.0
10°	1730.4	1733.6	1724.7	1712.5	1702.6	1687.8	1663.7	1638.9	1609.0	1580.1	1557.0
12.5°	1796.9	1804.7	1793.2	1791.6	1774.5	1754.3	1725.5	1713.0	1670.9	1630.5	1605.8
15°	1877.6	1877.1	1878.2	1868.1	1855.5	1852.4	1821.9	1788.8	1729.4	1705.7	1664.8
17.5°	1854.3	1862.3	1866.0	1865.8	1865.5	1863.5	1853.8	1832.9	1803.1	1764.7	1717.4
20°	1798.8	1809.3	1810.8	1823.0	1829.8	1838.7	1842.4	1836.6	1818.2	1786.1	1745.2
22.5°	1713.0	1715.9	1720.9	1739.7	1754.5	1776.9	1788.6	1808.0	1800.9	1785.3	1751.0
25°	1564.3	1559.1	1577.5	1586.9	1621.1	1656.8	1682.6	1711.0	1736.2	1751.4	1741.5
27.5°	1385.8	1377.9	1405.5	1430.6	1458.3	1497.1	1537.2	1584.6	1624.1	1673.3	1690.3
30°	1235.2	1240.0	1266.3	1293.1	1335.1	1389.8	1435.0	1487.1	1543.3	1598.5	1636.9
32.5°	1072.9	1091.2	1107.8	1148.8	1185.9	1246.8	1313.0	1378.2	1448.3	1511.0	1570.4
35°	851.5	872.6	895.7	925.7	977.7	1038.2	1102.8	1190.6	1286.3	1372.0	1442.4
37.5°	716.8	713.4	726.7	748.3	790.4	839.2	913.7	1000.4	1113.0	1213.7	1313.0
40°	636.0	633.9	643.4	663.4	695.5	731.2	796.4	872.6	977.2	1100.2	1218.5
42.5°	580.5	581.8	587.0	601.1	623.1	652.5	701.3	766.2	862.0	977.8	1104.9
45°	513.0	516.7	522.5	529.3	541.9	566.1	593.4	639.7	715.4	812.1	937.2
47.5°	464.5	464.5	470.5	476.4	483.9	497.6	519.8	548.9	602.3	681.0	788.6
50°	438.4	434.7	438.9	443.6	451.5	461.0	475.7	503.0	538.8	602.4	692.3
52.5°	406.5	406.5	410.4	412.1	419.1	428.6	442.0	461.0	493.4	543.1	617.0
55°	360.6	363.2	365.4	368.4	374.8	381.6	392.1	404.7	430.0	467.3	522.0
57.5°	317.5	318.3	320.4	326.5	330.4	336.8	346.7	358.1	374.5	402.2	443.3
60°	288.0	288.0	292.2	294.9	300.2	306.4	314.3	325.3	340.1	362.7	395.9
62.5°	261.2	260.7	262.4	266.7	270.7	276.6	284.5	293.8	307.7	327.8	355.1
65°	221.8	220.8	223.9	225.0	229.2	235.0	241.3	251.3	262.3	277.0	301.2
67.5°	183.9	185.2	187.0	188.9	191.2	197.3	201.5	208.6	217.9	230.1	246.5
70°	163.0	163.0	163.0	164.5	167.7	170.9	175.1	180.9	189.7	200.3	215.0
72.5°	139.4	141.1	142.8	141.8	145.8	147.7	152.7	156.0	164.5	171.3	184.3
75°	109.3	109.3	109.3	111.9	113.5	115.1	118.3	121.4	125.6	134.0	140.9
77.5°	81.6	81.4	81.9	82.5	84.2	86.1	87.1	89.9	93.8	97.7	103.5
80°	63.1	64.2	64.6	65.7	65.7	66.8	67.3	71.0	73.6	76.2	79.9
82.5°	48.8	49.0	49.1	49.3	49.7	50.4	51.7	52.9	53.8	56.0	58.9
85°	28.4	27.9	27.9	28.9	28.4	28.4	29.5	30.5	30.5	31.0	32.6
87.5°	17.0	17.0	17.4	17.0	17.0	17.3	16.9	16.8	17.4	18.1	18.3
90°	30.3	30.3	30.3	30.3	30.3	29.5	27.6	29.5	30.3	31.3	30.3
92.5°	51.0	52.4	51.7	54.7	55.4	61.1	68.8	80.2	101.1	119.6	118.0
95°	104.9	104.0	106.8	114.1	126.0	146.3	185.0	241.1	315.7	360.8	319.3
97.5°	206.5	214.2	227.7	250.3	294.3	360.8	460.3	562.6	646.0	615.8	463.8
100°	329.5	346.0	372.7	412.3	488.6	600.0	726.1	840.2	859.5	727.0	500.6
102.5°	579.8	602.2	635.6	703.1	786.1	904.0	996.2	1022.1	939.1	730.7	486.6
105°	1037.1	1050.0	1089.6	1146.6	1203.7	1234.1	1222.1	1118.1	926.7	681.9	459.2
107.5°	1324.8	1341.9	1349.8	1353.0	1345.8	1301.2	1205.5	1048.9	845.9	629.6	445.6
110°	1411.7	1412.6	1404.3	1386.8	1347.3	1271.8	1154.0	989.3	795.1	604.6	442.7



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1410.2	1405.3	1389.6	1360.3	1305.3	1218.8	1092.9	934.8	759.8	588.4	443.4
115°	1364.8	1356.5	1332.5	1290.2	1224.9	1130.0	1009.6	867.8	716.0	570.5	447.3
117.5°	1283.6	1276.6	1251.3	1206.7	1140.0	1051.1	941.8	817.4	688.3	561.9	453.8
120°	1231.3	1222.1	1195.4	1152.1	1087.7	1004.0	906.4	792.3	673.6	556.7	458.3
122.5°	1176.8	1169.1	1145.3	1102.8	1045.0	969.4	877.0	772.5	661.1	553.8	463.4
125°	1107.1	1099.7	1076.7	1041.7	988.3	919.3	838.4	743.5	643.3	548.5	471.2
127.5°	1046.0	1040.1	1020.2	987.5	940.9	877.2	800.8	715.0	626.7	545.3	479.1
130°	1011.4	1004.0	985.6	954.3	909.2	848.5	775.8	696.6	615.7	543.8	485.0
132.5°	975.3	968.7	951.7	920.4	876.1	819.0	752.3	679.0	606.8	543.1	490.8
135°	917.5	913.8	897.2	866.9	827.3	775.8	715.0	654.3	594.5	542.0	497.9
137.5°	860.8	855.3	840.7	814.6	778.6	733.6	685.4	634.6	585.8	541.9	504.1
140°	821.8	816.3	802.5	778.6	749.1	708.6	666.3	622.1	580.7	541.1	507.1
142.5°	782.8	781.6	769.4	747.6	719.6	685.8	649.4	611.8	575.5	541.1	509.3
145°	732.5	729.8	720.6	704.9	682.9	656.2	627.6	597.2	568.7	539.2	511.7
147.5°	690.4	688.7	682.5	669.9	651.7	632.2	610.0	586.1	561.7	536.0	512.4
150°	665.4	664.4	658.9	647.8	634.1	617.5	598.2	577.9	555.8	533.8	511.7
152.5°	644.0	643.8	639.8	630.2	619.3	605.0	588.6	569.8	550.6	530.0	510.2
155°	615.7	617.5	613.8	607.4	597.2	587.1	573.3	558.6	541.1	523.6	507.9
157.5°	591.5	591.5	589.9	584.6	577.3	569.4	557.9	545.5	532.1	517.0	503.7
160°	576.1	576.1	575.1	570.5	564.1	557.7	547.6	537.4	525.5	512.6	501.5
162.5°	561.3	562.1	561.2	558.0	551.6	546.6	538.0	529.3	519.6	508.9	499.3
165°	540.2	541.1	541.1	537.4	533.8	530.0	523.6	517.2	509.8	501.5	495.1
167.5°	520.7	521.8	522.0	519.9	518.3	515.0	510.6	505.6	500.3	495.1	490.8
170°	508.9	510.7	511.7	508.9	507.9	506.1	502.5	499.7	495.1	491.4	488.6
172.5°	499.3	500.4	501.4	500.1	499.2	498.0	495.1	493.1	490.0	487.0	485.7
175°	486.8	488.6	489.6	488.6	488.6	487.7	486.8	485.9	483.2	482.2	481.3
177.5°	479.3	480.8	481.5	481.5	481.5	481.5	480.8	480.8	479.3	478.6	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1403.5	1400.1	1398.0	1390.4	1383.7	1377.0	1374.9	1375.7	1366.5	1357.6	1353.8
5°	1458.2	1447.6	1437.7	1423.5	1406.7	1388.2	1378.8	1371.4	1353.0	1333.1	1321.5
7.5°	1507.1	1492.1	1472.9	1446.2	1421.7	1392.7	1374.4	1358.0	1331.2	1303.0	1285.7
10°	1537.0	1516.5	1491.8	1459.2	1429.3	1394.0	1369.3	1344.7	1313.0	1279.5	1258.4
12.5°	1562.7	1535.0	1510.7	1468.9	1433.5	1389.4	1360.1	1325.2	1292.0	1252.1	1231.5
15°	1623.7	1572.7	1526.5	1479.2	1435.5	1374.0	1341.5	1294.7	1251.0	1201.7	1178.0
17.5°	1671.0	1613.7	1540.8	1480.7	1429.7	1361.7	1313.8	1257.7	1206.2	1149.7	1117.5
20°	1697.9	1632.1	1553.8	1482.3	1421.3	1343.5	1291.5	1234.2	1173.8	1110.2	1075.5
22.5°	1713.8	1644.7	1567.3	1476.0	1404.5	1328.8	1263.4	1200.6	1139.3	1070.6	1034.3
25°	1718.9	1655.8	1573.8	1470.8	1383.5	1297.8	1219.0	1158.0	1083.9	1019.8	966.7
27.5°	1693.8	1648.6	1569.8	1460.9	1359.2	1259.0	1171.2	1102.1	1023.9	954.3	900.9
30°	1663.2	1636.9	1560.1	1450.8	1339.9	1232.2	1135.4	1057.1	979.3	908.9	854.2
32.5°	1615.7	1610.0	1542.5	1436.5	1319.3	1198.1	1098.0	1018.8	932.6	863.4	811.3
35°	1522.3	1547.5	1504.9	1404.5	1280.5	1149.6	1041.3	950.9	861.6	795.3	746.4
37.5°	1397.2	1459.8	1448.7	1357.7	1228.1	1096.9	977.3	882.8	797.6	730.8	682.8
40°	1311.0	1390.8	1402.4	1322.0	1191.1	1056.1	929.4	835.3	752.2	691.3	642.9
42.5°	1218.5	1311.8	1343.5	1279.1	1150.7	1013.1	886.5	789.0	706.8	647.5	604.6
45°	1063.4	1186.9	1244.2	1207.4	1083.4	942.5	812.1	713.3	638.7	583.0	549.9
47.5°	918.4	1053.4	1130.4	1117.5	1008.4	868.9	740.0	645.2	572.5	528.1	498.4
50°	815.8	954.6	1047.6	1051.9	954.6	816.3	687.1	597.7	530.9	489.4	465.2
52.5°	726.7	859.1	960.6	982.9	894.5	761.7	639.5	550.6	491.8	453.6	432.0
55°	610.3	722.2	834.7	875.8	804.8	678.6	565.6	487.3	432.1	405.8	386.9
57.5°	507.4	600.7	704.6	749.9	706.2	598.2	492.2	424.2	379.4	356.4	341.9
60°	453.1	526.7	619.2	673.4	635.5	539.3	446.8	382.1	345.4	324.9	311.2
62.5°	402.7	467.9	546.1	595.6	575.0	484.3	401.4	344.3	312.5	293.3	283.4
65°	332.2	383.7	444.2	489.9	476.3	407.3	339.6	290.7	265.5	250.2	242.3
67.5°	273.5	310.8	352.7	392.8	381.8	333.0	278.5	240.4	221.7	208.5	203.7
70°	236.5	264.9	302.2	334.3	325.3	285.4	242.3	209.8	193.5	182.4	177.7
72.5°	201.2	224.6	253.0	279.2	273.2	240.0	204.1	179.4	166.9	156.8	152.9
75°	151.9	169.8	187.1	204.5	202.9	177.1	156.1	137.2	127.2	119.3	117.7
77.5°	112.2	122.2	134.0	144.3	141.4	126.7	110.2	99.3	92.0	86.7	85.9
80°	85.7	91.5	99.9	107.3	103.5	97.3	84.1	76.2	71.0	65.7	63.6
82.5°	62.1	67.9	73.0	76.9	74.1	68.2	60.1	54.7	51.7	48.0	47.2
85°	32.6	35.7	37.9	38.9	37.9	34.1	30.5	28.4	25.7	24.2	23.7
87.5°	17.6	16.3	15.4	15.7	14.0	13.7	11.2	9.4	9.6	9.9	9.4
90°	24.9	18.4	13.8	11.0	9.2	7.4	3.6	1.0	3.6	7.4	9.2
92.5°	91.8	62.6	41.7	33.1	26.9	22.8	16.2	11.2	16.2	22.8	26.9
95°	212.5	132.5	90.2	68.1	53.4	45.1	35.9	32.2	35.9	45.1	53.4
97.5°	286.4	174.8	121.7	96.6	79.7	67.2	57.4	52.4	57.4	67.2	79.7
100°	301.8	189.6	140.8	115.0	96.6	81.9	73.6	70.8	73.6	81.9	96.6
102.5°	302.6	202.8	157.7	132.0	112.8	98.1	89.8	87.8	89.8	98.1	112.8
105°	307.4	225.5	182.2	156.5	136.2	122.4	116.0	112.3	116.0	122.4	136.2
107.5°	320.0	248.7	206.7	180.8	160.7	148.0	141.7	138.8	141.7	148.0	160.7
110°	330.3	264.1	223.6	196.9	177.6	165.6	160.1	156.5	160.1	165.6	177.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.4	278.8	239.8	212.4	193.8	182.6	176.3	172.6	176.3	182.6	193.8
115°	358.0	301.8	262.3	237.4	219.0	207.9	202.5	197.9	202.5	207.9	219.0
117.5°	375.7	323.0	286.4	260.6	243.0	233.2	227.7	224.0	227.7	233.2	243.0
120°	387.5	337.7	301.8	276.1	257.7	249.4	243.8	240.2	243.8	249.4	257.7
122.5°	397.8	351.7	318.1	291.5	273.1	264.1	258.6	255.6	258.6	264.1	273.1
125°	414.2	372.7	339.6	313.8	295.4	284.4	278.8	276.1	278.8	284.4	295.4
127.5°	429.4	392.2	360.0	333.5	315.8	303.7	296.0	292.2	296.0	303.7	315.8
130°	438.9	404.0	371.8	346.0	327.6	314.7	305.5	301.8	305.5	314.7	327.6
132.5°	448.5	414.3	383.6	357.8	338.7	325.0	315.1	310.7	315.1	325.0	338.7
135°	461.1	428.8	399.4	373.6	352.4	338.7	327.6	323.9	327.6	338.7	352.4
137.5°	470.6	440.6	411.5	387.6	366.6	351.9	340.9	336.4	340.9	351.9	366.6
140°	475.8	447.3	419.6	395.7	375.5	360.8	349.7	346.0	349.7	360.8	375.5
142.5°	480.2	452.4	425.6	403.1	383.6	368.8	358.5	355.6	358.5	368.8	383.6
145°	485.9	460.1	435.3	415.0	396.6	382.9	373.6	369.9	373.6	382.9	396.6
147.5°	489.0	466.4	443.0	425.0	409.7	397.0	388.2	385.4	388.2	397.0	409.7
150°	490.5	469.4	448.1	431.6	417.8	405.8	398.5	395.7	398.5	405.8	417.8
152.5°	491.2	472.3	453.3	438.2	425.2	414.6	407.3	406.0	407.3	414.6	425.2
155°	492.3	476.7	461.1	447.3	437.1	427.0	421.4	420.6	421.4	427.0	437.1
157.5°	492.3	479.8	466.6	455.0	446.9	438.1	433.6	432.7	433.6	438.1	446.9
160°	492.3	481.3	470.2	460.1	452.7	445.4	441.7	440.8	441.7	445.4	452.7
162.5°	491.6	482.0	472.5	464.5	457.9	452.0	448.4	448.9	448.4	452.0	457.9
165°	489.6	483.2	474.8	469.4	464.7	459.2	457.4	458.3	457.4	459.2	464.7
167.5°	488.3	482.9	476.9	473.4	470.1	466.6	464.9	466.0	464.9	466.6	470.1
170°	486.8	482.2	477.6	474.8	473.0	470.2	469.4	471.2	469.4	470.2	473.0
172.5°	484.6	481.5	478.3	476.3	475.2	472.5	473.0	474.1	473.0	472.5	475.2
175°	482.2	480.4	478.6	477.6	477.6	475.8	476.7	477.6	476.7	475.8	477.6
177.5°	480.8	479.3	478.6	478.6	478.6	477.1	477.8	479.3	477.8	477.1	478.6
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1349.6	1347.1	1338.3	1333.7	1326.1	1319.0	1314.3	1316.4	1318.1	1317.2	1316.1
5°	1311.0	1301.0	1285.7	1272.6	1263.1	1245.8	1238.4	1234.8	1231.6	1227.9	1224.2
7.5°	1265.0	1249.2	1227.2	1208.6	1190.9	1169.3	1157.1	1149.7	1142.2	1133.9	1126.5
10°	1232.2	1210.1	1186.9	1160.6	1139.6	1120.1	1102.8	1091.2	1080.8	1070.7	1063.4
12.5°	1197.6	1172.2	1143.6	1107.6	1084.5	1056.7	1054.0	1033.6	1017.2	1011.1	1002.4
15°	1142.8	1107.0	1070.7	1028.2	1009.8	984.5	968.8	953.0	938.8	928.8	926.2
17.5°	1080.5	1034.2	998.1	967.5	937.3	911.5	897.0	884.4	872.7	859.4	857.5
20°	1032.9	992.9	953.5	926.7	895.7	869.4	851.5	838.9	828.9	821.1	814.2
22.5°	987.9	944.2	908.1	878.8	848.2	827.0	812.9	800.7	792.3	783.6	777.2
25°	915.7	881.5	842.1	809.0	783.7	770.1	758.5	748.0	742.8	737.0	729.6
27.5°	852.5	814.5	777.7	752.0	729.8	717.7	709.6	702.3	697.4	694.0	689.8
30°	807.9	769.5	740.6	715.4	697.0	684.9	679.7	675.5	669.7	667.6	665.5
32.5°	765.0	730.5	705.8	683.9	666.3	658.5	653.6	649.8	645.3	643.2	639.0
35°	704.4	675.5	651.3	639.2	625.0	618.1	614.5	609.3	605.0	602.9	602.4
37.5°	647.3	622.2	606.3	590.7	584.7	580.5	575.5	571.9	570.6	570.3	569.8
40°	610.3	589.8	575.6	563.0	560.3	554.1	549.9	546.7	546.7	547.2	546.7
42.5°	576.6	558.3	545.7	534.8	531.7	528.0	523.8	523.6	524.4	526.2	524.4
45°	525.6	512.5	503.6	498.3	492.5	488.9	488.3	489.9	490.4	491.0	492.5
47.5°	478.8	470.0	461.9	456.1	453.6	453.0	452.3	455.1	457.6	458.6	461.0
50°	451.0	441.0	434.2	430.5	428.4	427.4	428.4	431.6	433.6	436.3	437.8
52.5°	419.9	412.8	408.1	405.3	404.4	405.0	405.3	408.8	412.3	413.1	413.9
55°	376.9	371.6	370.6	365.8	368.0	367.4	370.0	372.2	375.3	378.5	379.0
57.5°	334.0	329.8	326.9	327.4	328.0	330.3	332.6	336.2	339.6	342.9	343.3
60°	305.4	303.3	301.7	301.7	302.8	305.9	308.6	312.2	314.3	316.5	318.0
62.5°	279.3	277.3	275.7	276.5	279.2	281.1	284.2	286.1	288.3	290.3	291.1
65°	238.1	237.1	238.7	239.7	240.2	242.9	246.5	248.1	250.2	251.3	254.9
67.5°	200.2	200.3	200.2	201.6	204.7	205.3	208.8	212.5	212.9	214.9	217.3
70°	174.5	175.5	176.7	177.7	180.3	181.3	183.9	185.5	187.7	189.3	190.8
72.5°	151.0	151.1	152.3	152.0	154.2	156.5	158.8	160.3	162.4	164.5	166.0
75°	116.1	116.1	117.2	117.7	120.4	123.0	122.5	123.5	125.6	127.7	128.8
77.5°	84.8	83.7	84.8	85.4	86.2	88.4	88.8	90.3	92.7	92.0	93.2
80°	64.6	63.1	64.6	65.2	65.2	67.8	67.8	68.8	70.4	68.8	70.4
82.5°	46.2	45.4	46.6	46.7	47.5	47.6	48.5	48.6	50.2	49.5	50.2
85°	23.1	22.6	23.1	22.6	23.1	23.7	23.7	23.1	23.1	24.2	22.6
87.5°	9.3	9.5	10.0	11.2	12.0	11.7	11.1	10.9	10.5	10.1	10.3
90°	11.0	13.8	18.4	24.9	30.3	31.3	30.3	29.5	27.6	29.5	30.3
92.5°	33.1	41.7	62.6	91.8	118.0	119.6	101.1	80.2	68.8	61.1	55.4
95°	68.1	90.2	132.5	212.5	319.3	360.8	315.7	241.1	185.0	146.3	126.0
97.5°	96.6	121.7	174.8	286.4	463.8	615.8	646.0	562.6	460.3	360.8	294.3
100°	115.0	140.8	189.6	301.8	500.6	727.0	859.5	840.2	726.1	600.0	488.6
102.5°	132.0	157.7	202.8	302.6	486.6	730.7	939.1	1022.1	996.2	904.0	786.1
105°	156.5	182.2	225.5	307.4	459.2	681.9	926.7	1118.1	1222.1	1234.1	1203.7
107.5°	180.8	206.7	248.7	320.0	445.6	629.6	845.9	1048.9	1205.5	1301.2	1345.8
110°	196.9	223.6	264.1	330.3	442.7	604.6	795.1	989.3	1154.0	1271.8	1347.3



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.4	239.8	278.8	341.4	443.4	588.4	759.8	934.8	1092.9	1218.8	1305.3
115°	237.4	262.3	301.8	358.0	447.3	570.5	716.0	867.8	1009.6	1130.0	1224.9
117.5°	260.6	286.4	323.0	375.7	453.8	561.9	688.3	817.4	941.8	1051.1	1140.0
120°	276.1	301.8	337.7	387.5	458.3	556.7	673.6	792.3	906.4	1004.0	1087.7
122.5°	291.5	318.1	351.7	397.8	463.4	553.8	661.1	772.5	877.0	969.4	1045.0
125°	313.8	339.6	372.7	414.2	471.2	548.5	643.3	743.5	838.4	919.3	988.3
127.5°	333.5	360.0	392.2	429.4	479.1	545.3	626.7	715.0	800.8	877.2	940.9
130°	346.0	371.8	404.0	438.9	485.0	543.8	615.7	696.6	775.8	848.5	909.2
132.5°	357.8	383.6	414.3	448.5	490.8	543.1	606.8	679.0	752.3	819.0	876.1
135°	373.6	399.4	428.8	461.1	497.9	542.0	594.5	654.3	715.0	775.8	827.3
137.5°	387.6	411.5	440.6	470.6	504.1	541.9	585.8	634.6	685.4	733.6	778.6
140°	395.7	419.6	447.3	475.8	507.1	541.1	580.7	622.1	666.3	708.6	749.1
142.5°	403.1	425.6	452.4	480.2	509.3	541.1	575.5	611.8	649.4	685.8	719.6
145°	415.0	435.3	460.1	485.9	511.7	539.2	568.7	597.2	627.6	656.2	682.9
147.5°	425.0	443.0	466.4	489.0	512.4	536.0	561.7	586.1	610.0	632.2	651.7
150°	431.6	448.1	469.4	490.5	511.7	533.8	555.8	577.9	598.2	617.5	634.1
152.5°	438.2	453.3	472.3	491.2	510.2	530.0	550.6	569.8	588.6	605.0	619.3
155°	447.3	461.1	476.7	492.3	507.9	523.6	541.1	558.6	573.3	587.1	597.2
157.5°	455.0	466.6	479.8	492.3	503.7	517.0	532.1	545.5	557.9	569.4	577.3
160°	460.1	470.2	481.3	492.3	501.5	512.6	525.5	537.4	547.6	557.7	564.1
162.5°	464.5	472.5	482.0	491.6	499.3	508.9	519.6	529.3	538.0	546.6	551.6
165°	469.4	474.8	483.2	489.6	495.1	501.5	509.8	517.2	523.6	530.0	533.8
167.5°	473.4	476.9	482.9	488.3	490.8	495.1	500.3	505.6	510.6	515.0	518.3
170°	474.8	477.6	482.2	486.8	488.6	491.4	495.1	499.7	502.5	506.1	507.9
172.5°	476.3	478.3	481.5	484.6	485.7	487.0	490.0	493.1	495.1	498.0	499.2
175°	477.6	478.6	480.4	482.2	481.3	482.2	483.2	485.9	486.8	487.7	488.6
177.5°	478.6	478.6	479.3	480.8	479.3	478.6	479.3	480.8	480.8	481.5	481.5
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1311.8	1311.0	1311.0	1307.2	1311.0	1311.0	1311.8	1316.1	1317.2	1318.1	1316.4
5°	1216.9	1215.3	1212.7	1215.3	1212.7	1215.3	1216.9	1224.2	1227.9	1231.6	1234.8
7.5°	1123.0	1116.7	1115.7	1109.5	1115.7	1116.7	1123.0	1126.5	1133.9	1142.2	1149.7
10°	1054.5	1050.3	1049.7	1039.7	1049.7	1050.3	1054.5	1063.4	1070.7	1080.8	1091.2
12.5°	1002.3	992.2	994.2	988.4	994.2	992.2	1002.3	1002.4	1011.1	1017.2	1033.6
15°	912.0	912.0	909.9	900.9	909.9	912.0	912.0	926.2	928.8	938.8	953.0
17.5°	847.2	846.1	841.1	843.6	841.1	846.1	847.2	857.5	859.4	872.7	884.4
20°	808.4	805.3	799.0	799.0	799.0	805.3	808.4	814.2	821.1	828.9	838.9
22.5°	771.9	771.7	764.9	767.0	764.9	771.7	771.9	777.2	783.6	792.3	800.7
25°	729.0	724.8	721.8	723.3	721.8	724.8	729.0	729.6	737.0	742.8	748.0
27.5°	688.5	686.2	686.0	681.7	686.0	686.2	688.5	689.8	694.0	697.4	702.3
30°	665.0	659.7	660.8	658.1	660.8	659.7	665.0	665.5	667.6	669.7	675.5
32.5°	638.0	636.1	635.1	632.9	635.1	636.1	638.0	639.0	643.2	645.3	649.8
35°	601.3	601.9	599.2	600.3	599.2	601.9	601.3	602.4	602.9	605.0	609.3
37.5°	569.3	570.9	569.7	570.1	569.7	570.9	569.3	569.8	570.3	570.6	571.9
40°	548.3	548.3	548.3	549.9	548.3	548.3	548.3	546.7	547.2	546.7	546.7
42.5°	528.1	527.2	526.4	526.2	526.4	527.2	528.1	524.4	526.2	524.4	523.6
45°	493.6	495.2	495.7	493.1	495.7	495.2	493.6	492.5	491.0	490.4	489.9
47.5°	462.4	462.6	462.4	464.7	462.4	462.6	462.4	461.0	458.6	457.6	455.1
50°	440.5	439.4	440.5	439.4	440.5	439.4	440.5	437.8	436.3	433.6	431.6
52.5°	417.4	417.6	416.9	416.8	416.9	417.6	417.4	413.9	413.1	412.3	408.8
55°	381.1	382.1	381.6	381.6	381.6	382.1	381.1	379.0	378.5	375.3	372.2
57.5°	343.6	344.5	345.2	342.9	345.2	344.5	343.6	343.3	342.9	339.6	336.2
60°	317.5	320.1	319.6	318.5	319.6	320.1	317.5	318.0	316.5	314.3	312.2
62.5°	293.5	294.5	294.4	294.1	294.4	294.5	293.5	291.1	290.3	288.3	286.1
65°	256.5	257.5	256.0	257.5	256.0	257.5	256.5	254.9	251.3	250.2	248.1
67.5°	216.7	217.0	218.2	218.9	218.2	217.0	216.7	217.3	214.9	212.9	212.5
70°	191.9	191.3	192.9	194.5	192.9	191.3	191.9	190.8	189.3	187.7	185.5
72.5°	165.8	166.9	166.4	167.5	166.4	166.9	165.8	166.0	164.5	162.4	160.3
75°	127.7	129.3	128.8	130.4	128.8	129.3	127.7	128.8	127.7	125.6	123.5
77.5°	92.3	92.5	92.3	93.2	92.3	92.5	92.3	93.2	92.0	92.7	90.3
80°	70.4	69.4	68.4	70.4	68.4	69.4	70.4	70.4	68.8	70.4	68.8
82.5°	49.0	49.6	48.6	48.6	48.6	49.6	49.0	50.2	49.5	50.2	48.6
85°	22.6	22.1	21.0	21.0	21.0	22.1	22.6	22.6	24.2	23.1	23.1
87.5°	10.3	9.8	9.8	9.4	9.8	9.8	10.3	10.3	10.1	10.5	10.9
90°	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	29.5	27.6	29.5
92.5°	54.7	51.7	52.4	51.0	52.4	51.7	54.7	55.4	61.1	68.8	80.2
95°	114.1	106.8	104.0	104.9	104.0	106.8	114.1	126.0	146.3	185.0	241.1
97.5°	250.3	227.7	214.2	206.5	214.2	227.7	250.3	294.3	360.8	460.3	562.6
100°	412.3	372.7	346.0	329.5	346.0	372.7	412.3	488.6	600.0	726.1	840.2
102.5°	703.1	635.6	602.2	579.8	602.2	635.6	703.1	786.1	904.0	996.2	1022.1
105°	1146.6	1089.6	1050.0	1037.1	1050.0	1089.6	1146.6	1203.7	1234.1	1222.1	1118.1
107.5°	1353.0	1349.8	1341.9	1324.8	1341.9	1349.8	1353.0	1345.8	1301.2	1205.5	1048.9
110°	1386.8	1404.3	1412.6	1411.7	1412.6	1404.3	1386.8	1347.3	1271.8	1154.0	989.3



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1360.3	1389.6	1405.3	1410.2	1405.3	1389.6	1360.3	1305.3	1218.8	1092.9	934.8
115°	1290.2	1332.5	1356.5	1364.8	1356.5	1332.5	1290.2	1224.9	1130.0	1009.6	867.8
117.5°	1206.7	1251.3	1276.6	1283.6	1276.6	1251.3	1206.7	1140.0	1051.1	941.8	817.4
120°	1152.1	1195.4	1222.1	1231.3	1222.1	1195.4	1152.1	1087.7	1004.0	906.4	792.3
122.5°	1102.8	1145.3	1169.1	1176.8	1169.1	1145.3	1102.8	1045.0	969.4	877.0	772.5
125°	1041.7	1076.7	1099.7	1107.1	1099.7	1076.7	1041.7	988.3	919.3	838.4	743.5
127.5°	987.5	1020.2	1040.1	1046.0	1040.1	1020.2	987.5	940.9	877.2	800.8	715.0
130°	954.3	985.6	1004.0	1011.4	1004.0	985.6	954.3	909.2	848.5	775.8	696.6
132.5°	920.4	951.7	968.7	975.3	968.7	951.7	920.4	876.1	819.0	752.3	679.0
135°	866.9	897.2	913.8	917.5	913.8	897.2	866.9	827.3	775.8	715.0	654.3
137.5°	814.6	840.7	855.3	860.8	855.3	840.7	814.6	778.6	733.6	685.4	634.6
140°	778.6	802.5	816.3	821.8	816.3	802.5	778.6	749.1	708.6	666.3	622.1
142.5°	747.6	769.4	781.6	782.8	781.6	769.4	747.6	719.6	685.8	649.4	611.8
145°	704.9	720.6	729.8	732.5	729.8	720.6	704.9	682.9	656.2	627.6	597.2
147.5°	669.9	682.5	688.7	690.4	688.7	682.5	669.9	651.7	632.2	610.0	586.1
150°	647.8	658.9	664.4	665.4	664.4	658.9	647.8	634.1	617.5	598.2	577.9
152.5°	630.2	639.8	643.8	644.0	643.8	639.8	630.2	619.3	605.0	588.6	569.8
155°	607.4	613.8	617.5	615.7	617.5	613.8	607.4	597.2	587.1	573.3	558.6
157.5°	584.6	589.9	591.5	591.5	591.5	589.9	584.6	577.3	569.4	557.9	545.5
160°	570.5	575.1	576.1	576.1	576.1	575.1	570.5	564.1	557.7	547.6	537.4
162.5°	558.0	561.2	562.1	561.3	562.1	561.2	558.0	551.6	546.6	538.0	529.3
165°	537.4	541.1	541.1	540.2	541.1	541.1	537.4	533.8	530.0	523.6	517.2
167.5°	519.9	522.0	521.8	520.7	521.8	522.0	519.9	518.3	515.0	510.6	505.6
170°	508.9	511.7	510.7	508.9	510.7	511.7	508.9	507.9	506.1	502.5	499.7
172.5°	500.1	501.4	500.4	499.3	500.4	501.4	500.1	499.2	498.0	495.1	493.1
175°	488.6	489.6	488.6	486.8	488.6	489.6	488.6	488.6	487.7	486.8	485.9
177.5°	481.5	481.5	480.8	479.3	480.8	481.5	481.5	481.5	481.5	480.8	480.8
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1314.3	1319.0	1326.1	1333.7	1338.3	1347.1	1349.6	1353.8	1357.6	1366.5	1375.7
5°	1238.4	1245.8	1263.1	1272.6	1285.7	1301.0	1311.0	1321.5	1333.1	1353.0	1371.4
7.5°	1157.1	1169.3	1190.9	1208.6	1227.2	1249.2	1265.0	1285.7	1303.0	1331.2	1358.0
10°	1102.8	1120.1	1139.6	1160.6	1186.9	1210.1	1232.2	1258.4	1279.5	1313.0	1344.7
12.5°	1054.0	1056.7	1084.5	1107.6	1143.6	1172.2	1197.6	1231.5	1252.1	1292.0	1325.2
15°	968.8	984.5	1009.8	1028.2	1070.7	1107.0	1142.8	1178.0	1201.7	1251.0	1294.7
17.5°	897.0	911.5	937.3	967.5	998.1	1034.2	1080.5	1117.5	1149.7	1206.2	1257.7
20°	851.5	869.4	895.7	926.7	953.5	992.9	1032.9	1075.5	1110.2	1173.8	1234.2
22.5°	812.9	827.0	848.2	878.8	908.1	944.2	987.9	1034.3	1070.6	1139.3	1200.6
25°	758.5	770.1	783.7	809.0	842.1	881.5	915.7	966.7	1019.8	1083.9	1158.0
27.5°	709.6	717.7	729.8	752.0	777.7	814.5	852.5	900.9	954.3	1023.9	1102.1
30°	679.7	684.9	697.0	715.4	740.6	769.5	807.9	854.2	908.9	979.3	1057.1
32.5°	653.6	658.5	666.3	683.9	705.8	730.5	765.0	811.3	863.4	932.6	1018.8
35°	614.5	618.1	625.0	639.2	651.3	675.5	704.4	746.4	795.3	861.6	950.9
37.5°	575.5	580.5	584.7	590.7	606.3	622.2	647.3	682.8	730.8	797.6	882.8
40°	549.9	554.1	560.3	563.0	575.6	589.8	610.3	642.9	691.3	752.2	835.3
42.5°	523.8	528.0	531.7	534.8	545.7	558.3	576.6	604.6	647.5	706.8	789.0
45°	488.3	488.9	492.5	498.3	503.6	512.5	525.6	549.9	583.0	638.7	713.3
47.5°	452.3	453.0	453.6	456.1	461.9	470.0	478.8	498.4	528.1	572.5	645.2
50°	428.4	427.4	428.4	430.5	434.2	441.0	451.0	465.2	489.4	530.9	597.7
52.5°	405.3	405.0	404.4	405.3	408.1	412.8	419.9	432.0	453.6	491.8	550.6
55°	370.0	367.4	368.0	365.8	370.6	371.6	376.9	386.9	405.8	432.1	487.3
57.5°	332.6	330.3	328.0	327.4	326.9	329.8	334.0	341.9	356.4	379.4	424.2
60°	308.6	305.9	302.8	301.7	301.7	303.3	305.4	311.2	324.9	345.4	382.1
62.5°	284.2	281.1	279.2	276.5	275.7	277.3	279.3	283.4	293.3	312.5	344.3
65°	246.5	242.9	240.2	239.7	238.7	237.1	238.1	242.3	250.2	265.5	290.7
67.5°	208.8	205.3	204.7	201.6	200.2	200.3	200.2	203.7	208.5	221.7	240.4
70°	183.9	181.3	180.3	177.7	176.7	175.5	174.5	177.7	182.4	193.5	209.8
72.5°	158.8	156.5	154.2	152.0	152.3	151.1	151.0	152.9	156.8	166.9	179.4
75°	122.5	123.0	120.4	117.7	117.2	116.1	116.1	117.7	119.3	127.2	137.2
77.5°	88.8	88.4	86.2	85.4	84.8	83.7	84.8	85.9	86.7	92.0	99.3
80°	67.8	67.8	65.2	65.2	64.6	63.1	64.6	63.6	65.7	71.0	76.2
82.5°	48.5	47.6	47.5	46.7	46.6	45.4	46.2	47.2	48.0	51.7	54.7
85°	23.7	23.7	23.1	22.6	23.1	22.6	23.1	23.7	24.2	25.7	28.4
87.5°	11.1	11.7	12.0	11.2	10.0	9.5	9.3	9.4	9.9	9.6	9.4
90°	30.3	31.3	30.3	24.9	18.4	13.8	11.0	9.2	7.4	3.6	1.0
92.5°	101.1	119.6	118.0	91.8	62.6	41.7	33.1	26.9	22.8	16.2	11.2
95°	315.7	360.8	319.3	212.5	132.5	90.2	68.1	53.4	45.1	35.9	32.2
97.5°	646.0	615.8	463.8	286.4	174.8	121.7	96.6	79.7	67.2	57.4	52.4
100°	859.5	727.0	500.6	301.8	189.6	140.8	115.0	96.6	81.9	73.6	70.8
102.5°	939.1	730.7	486.6	302.6	202.8	157.7	132.0	112.8	98.1	89.8	87.8
105°	926.7	681.9	459.2	307.4	225.5	182.2	156.5	136.2	122.4	116.0	112.3
107.5°	845.9	629.6	445.6	320.0	248.7	206.7	180.8	160.7	148.0	141.7	138.8
110°	795.1	604.6	442.7	330.3	264.1	223.6	196.9	177.6	165.6	160.1	156.5



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	759.8	588.4	443.4	341.4	278.8	239.8	212.4	193.8	182.6	176.3	172.6
115°	716.0	570.5	447.3	358.0	301.8	262.3	237.4	219.0	207.9	202.5	197.9
117.5°	688.3	561.9	453.8	375.7	323.0	286.4	260.6	243.0	233.2	227.7	224.0
120°	673.6	556.7	458.3	387.5	337.7	301.8	276.1	257.7	249.4	243.8	240.2
122.5°	661.1	553.8	463.4	397.8	351.7	318.1	291.5	273.1	264.1	258.6	255.6
125°	643.3	548.5	471.2	414.2	372.7	339.6	313.8	295.4	284.4	278.8	276.1
127.5°	626.7	545.3	479.1	429.4	392.2	360.0	333.5	315.8	303.7	296.0	292.2
130°	615.7	543.8	485.0	438.9	404.0	371.8	346.0	327.6	314.7	305.5	301.8
132.5°	606.8	543.1	490.8	448.5	414.3	383.6	357.8	338.7	325.0	315.1	310.7
135°	594.5	542.0	497.9	461.1	428.8	399.4	373.6	352.4	338.7	327.6	323.9
137.5°	585.8	541.9	504.1	470.6	440.6	411.5	387.6	366.6	351.9	340.9	336.4
140°	580.7	541.1	507.1	475.8	447.3	419.6	395.7	375.5	360.8	349.7	346.0
142.5°	575.5	541.1	509.3	480.2	452.4	425.6	403.1	383.6	368.8	358.5	355.6
145°	568.7	539.2	511.7	485.9	460.1	435.3	415.0	396.6	382.9	373.6	369.9
147.5°	561.7	536.0	512.4	489.0	466.4	443.0	425.0	409.7	397.0	388.2	385.4
150°	555.8	533.8	511.7	490.5	469.4	448.1	431.6	417.8	405.8	398.5	395.7
152.5°	550.6	530.0	510.2	491.2	472.3	453.3	438.2	425.2	414.6	407.3	406.0
155°	541.1	523.6	507.9	492.3	476.7	461.1	447.3	437.1	427.0	421.4	420.6
157.5°	532.1	517.0	503.7	492.3	479.8	466.6	455.0	446.9	438.1	433.6	432.7
160°	525.5	512.6	501.5	492.3	481.3	470.2	460.1	452.7	445.4	441.7	440.8
162.5°	519.6	508.9	499.3	491.6	482.0	472.5	464.5	457.9	452.0	448.4	448.9
165°	509.8	501.5	495.1	489.6	483.2	474.8	469.4	464.7	459.2	457.4	458.3
167.5°	500.3	495.1	490.8	488.3	482.9	476.9	473.4	470.1	466.6	464.9	466.0
170°	495.1	491.4	488.6	486.8	482.2	477.6	474.8	473.0	470.2	469.4	471.2
172.5°	490.0	487.0	485.7	484.6	481.5	478.3	476.3	475.2	472.5	473.0	474.1
175°	483.2	482.2	481.3	482.2	480.4	478.6	477.6	477.6	475.8	476.7	477.6
177.5°	479.3	478.6	479.3	480.8	479.3	478.6	478.6	478.6	477.1	477.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1374.9	1377.0	1383.7	1390.4	1398.0	1400.1	1403.5	1400.6	1399.7	1407.7	1413.6
5°	1378.8	1388.2	1406.7	1423.5	1437.7	1447.6	1458.2	1462.4	1470.2	1481.3	1494.9
7.5°	1374.4	1392.7	1421.7	1446.2	1472.9	1492.1	1507.1	1520.0	1535.6	1556.5	1579.3
10°	1369.3	1394.0	1429.3	1459.2	1491.8	1516.5	1537.0	1557.0	1580.1	1609.0	1638.9
12.5°	1360.1	1389.4	1433.5	1468.9	1510.7	1535.0	1562.7	1605.8	1630.5	1670.9	1713.0
15°	1341.5	1374.0	1435.5	1479.2	1526.5	1572.7	1623.7	1664.8	1705.7	1729.4	1788.8
17.5°	1313.8	1361.7	1429.7	1480.7	1540.8	1613.7	1671.0	1717.4	1764.7	1803.1	1832.9
20°	1291.5	1343.5	1421.3	1482.3	1553.8	1632.1	1697.9	1745.2	1786.1	1818.2	1836.6
22.5°	1263.4	1328.8	1404.5	1476.0	1567.3	1644.7	1713.8	1751.0	1785.3	1800.9	1808.0
25°	1219.0	1297.8	1383.5	1470.8	1573.8	1655.8	1718.9	1741.5	1751.4	1736.2	1711.0
27.5°	1171.2	1259.0	1359.2	1460.9	1569.8	1648.6	1693.8	1690.3	1673.3	1624.1	1584.6
30°	1135.4	1232.2	1339.9	1450.8	1560.1	1636.9	1663.2	1636.9	1598.5	1543.3	1487.1
32.5°	1098.0	1198.1	1319.3	1436.5	1542.5	1610.0	1615.7	1570.4	1511.0	1448.3	1378.2
35°	1041.3	1149.6	1280.5	1404.5	1504.9	1547.5	1522.3	1442.4	1372.0	1286.3	1190.6
37.5°	977.3	1096.9	1228.1	1357.7	1448.7	1459.8	1397.2	1313.0	1213.7	1113.0	1000.4
40°	929.4	1056.1	1191.1	1322.0	1402.4	1390.8	1311.0	1218.5	1100.2	977.2	872.6
42.5°	886.5	1013.1	1150.7	1279.1	1343.5	1311.8	1218.5	1104.9	977.8	862.0	766.2
45°	812.1	942.5	1083.4	1207.4	1244.2	1186.9	1063.4	937.2	812.1	715.4	639.7
47.5°	740.0	868.9	1008.4	1117.5	1130.4	1053.4	918.4	788.6	681.0	602.3	548.9
50°	687.1	816.3	954.6	1051.9	1047.6	954.6	815.8	692.3	602.4	538.8	503.0
52.5°	639.5	761.7	894.5	982.9	960.6	859.1	726.7	617.0	543.1	493.4	461.0
55°	565.6	678.6	804.8	875.8	834.7	722.2	610.3	522.0	467.3	430.0	404.7
57.5°	492.2	598.2	706.2	749.9	704.6	600.7	507.4	443.3	402.2	374.5	358.1
60°	446.8	539.3	635.5	673.4	619.2	526.7	453.1	395.9	362.7	340.1	325.3
62.5°	401.4	484.3	575.0	595.6	546.1	467.9	402.7	355.1	327.8	307.7	293.8
65°	339.6	407.3	476.3	489.9	444.2	383.7	332.2	301.2	277.0	262.3	251.3
67.5°	278.5	333.0	381.8	392.8	352.7	310.8	273.5	246.5	230.1	217.9	208.6
70°	242.3	285.4	325.3	334.3	302.2	264.9	236.5	215.0	200.3	189.7	180.9
72.5°	204.1	240.0	273.2	279.2	253.0	224.6	201.2	184.3	171.3	164.5	156.0
75°	156.1	177.1	202.9	204.5	187.1	169.8	151.9	140.9	134.0	125.6	121.4
77.5°	110.2	126.7	141.4	144.3	134.0	122.2	112.2	103.5	97.7	93.8	89.9
80°	84.1	97.3	103.5	107.3	99.9	91.5	85.7	79.9	76.2	73.6	71.0
82.5°	60.1	68.2	74.1	76.9	73.0	67.9	62.1	58.9	56.0	53.8	52.9
85°	30.5	34.1	37.9	38.9	37.9	35.7	32.6	32.6	31.0	30.5	30.5
87.5°	11.2	13.7	14.0	15.7	15.4	16.3	17.6	18.3	18.1	17.4	16.8
90°	3.6	7.4	9.2	11.0	13.8	18.4	24.9	30.3	31.3	30.3	29.5
92.5°	16.2	22.8	26.9	33.1	41.7	62.6	91.8	118.0	119.6	101.1	80.2
95°	35.9	45.1	53.4	68.1	90.2	132.5	212.5	319.3	360.8	315.7	241.1
97.5°	57.4	67.2	79.7	96.6	121.7	174.8	286.4	463.8	615.8	646.0	562.6
100°	73.6	81.9	96.6	115.0	140.8	189.6	301.8	500.6	727.0	859.5	840.2
102.5°	89.8	98.1	112.8	132.0	157.7	202.8	302.6	486.6	730.7	939.1	1022.1
105°	116.0	122.4	136.2	156.5	182.2	225.5	307.4	459.2	681.9	926.7	1118.1
107.5°	141.7	148.0	160.7	180.8	206.7	248.7	320.0	445.6	629.6	845.9	1048.9
110°	160.1	165.6	177.6	196.9	223.6	264.1	330.3	442.7	604.6	795.1	989.3



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	176.3	182.6	193.8	212.4	239.8	278.8	341.4	443.4	588.4	759.8	934.8
115°	202.5	207.9	219.0	237.4	262.3	301.8	358.0	447.3	570.5	716.0	867.8
117.5°	227.7	233.2	243.0	260.6	286.4	323.0	375.7	453.8	561.9	688.3	817.4
120°	243.8	249.4	257.7	276.1	301.8	337.7	387.5	458.3	556.7	673.6	792.3
122.5°	258.6	264.1	273.1	291.5	318.1	351.7	397.8	463.4	553.8	661.1	772.5
125°	278.8	284.4	295.4	313.8	339.6	372.7	414.2	471.2	548.5	643.3	743.5
127.5°	296.0	303.7	315.8	333.5	360.0	392.2	429.4	479.1	545.3	626.7	715.0
130°	305.5	314.7	327.6	346.0	371.8	404.0	438.9	485.0	543.8	615.7	696.6
132.5°	315.1	325.0	338.7	357.8	383.6	414.3	448.5	490.8	543.1	606.8	679.0
135°	327.6	338.7	352.4	373.6	399.4	428.8	461.1	497.9	542.0	594.5	654.3
137.5°	340.9	351.9	366.6	387.6	411.5	440.6	470.6	504.1	541.9	585.8	634.6
140°	349.7	360.8	375.5	395.7	419.6	447.3	475.8	507.1	541.1	580.7	622.1
142.5°	358.5	368.8	383.6	403.1	425.6	452.4	480.2	509.3	541.1	575.5	611.8
145°	373.6	382.9	396.6	415.0	435.3	460.1	485.9	511.7	539.2	568.7	597.2
147.5°	388.2	397.0	409.7	425.0	443.0	466.4	489.0	512.4	536.0	561.7	586.1
150°	398.5	405.8	417.8	431.6	448.1	469.4	490.5	511.7	533.8	555.8	577.9
152.5°	407.3	414.6	425.2	438.2	453.3	472.3	491.2	510.2	530.0	550.6	569.8
155°	421.4	427.0	437.1	447.3	461.1	476.7	492.3	507.9	523.6	541.1	558.6
157.5°	433.6	438.1	446.9	455.0	466.6	479.8	492.3	503.7	517.0	532.1	545.5
160°	441.7	445.4	452.7	460.1	470.2	481.3	492.3	501.5	512.6	525.5	537.4
162.5°	448.4	452.0	457.9	464.5	472.5	482.0	491.6	499.3	508.9	519.6	529.3
165°	457.4	459.2	464.7	469.4	474.8	483.2	489.6	495.1	501.5	509.8	517.2
167.5°	464.9	466.6	470.1	473.4	476.9	482.9	488.3	490.8	495.1	500.3	505.6
170°	469.4	470.2	473.0	474.8	477.6	482.2	486.8	488.6	491.4	495.1	499.7
172.5°	473.0	472.5	475.2	476.3	478.3	481.5	484.6	485.7	487.0	490.0	493.1
175°	476.7	475.8	477.6	477.6	478.6	480.4	482.2	481.3	482.2	483.2	485.9
177.5°	477.8	477.1	478.6	478.6	478.6	479.3	480.8	479.3	478.6	479.3	480.8
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1418.6	1424.5	1424.5	1425.4	1432.1	1431.2	1430.8
5°	1509.7	1518.6	1519.6	1529.1	1535.4	1533.3	1527.6
7.5°	1595.5	1612.2	1624.8	1631.8	1640.1	1645.3	1643.0
10°	1663.7	1687.8	1702.6	1712.5	1724.7	1733.6	1730.4
12.5°	1725.5	1754.3	1774.5	1791.6	1793.2	1804.7	1796.9
15°	1821.9	1852.4	1855.5	1868.1	1878.2	1877.1	1877.6
17.5°	1853.8	1863.5	1865.5	1865.8	1866.0	1862.3	1854.3
20°	1842.4	1838.7	1829.8	1823.0	1810.8	1809.3	1798.8
22.5°	1788.6	1776.9	1754.5	1739.7	1720.9	1715.9	1713.0
25°	1682.6	1656.8	1621.1	1586.9	1577.5	1559.1	1564.3
27.5°	1537.2	1497.1	1458.3	1430.6	1405.5	1377.9	1385.8
30°	1435.0	1389.8	1335.1	1293.1	1266.3	1240.0	1235.2
32.5°	1313.0	1246.8	1185.9	1148.8	1107.8	1091.2	1072.9
35°	1102.8	1038.2	977.7	925.7	895.7	872.6	851.5
37.5°	913.7	839.2	790.4	748.3	726.7	713.4	716.8
40°	796.4	731.2	695.5	663.4	643.4	633.9	636.0
42.5°	701.3	652.5	623.1	601.1	587.0	581.8	580.5
45°	593.4	566.1	541.9	529.3	522.5	516.7	513.0
47.5°	519.8	497.6	483.9	476.4	470.5	464.5	464.5
50°	475.7	461.0	451.5	443.6	438.9	434.7	438.4
52.5°	442.0	428.6	419.1	412.1	410.4	406.5	406.5
55°	392.1	381.6	374.8	368.4	365.4	363.2	360.6
57.5°	346.7	336.8	330.4	326.5	320.4	318.3	317.5
60°	314.3	306.4	300.2	294.9	292.2	288.0	288.0
62.5°	284.5	276.6	270.7	266.7	262.4	260.7	261.2
65°	241.3	235.0	229.2	225.0	223.9	220.8	221.8
67.5°	201.5	197.3	191.2	188.9	187.0	185.2	183.9
70°	175.1	170.9	167.7	164.5	163.0	163.0	163.0
72.5°	152.7	147.7	145.8	141.8	142.8	141.1	139.4
75°	118.3	115.1	113.5	111.9	109.3	109.3	109.3
77.5°	87.1	86.1	84.2	82.5	81.9	81.4	81.6
80°	67.3	66.8	65.7	65.7	64.6	64.2	63.1
82.5°	51.7	50.4	49.7	49.3	49.1	49.0	48.8
85°	29.5	28.4	28.4	28.9	27.9	27.9	28.4
87.5°	16.9	17.3	17.0	17.0	17.4	17.0	17.0
90°	27.6	29.5	30.3	30.3	30.3	30.3	30.3
92.5°	68.8	61.1	55.4	54.7	51.7	52.4	51.0
95°	185.0	146.3	126.0	114.1	106.8	104.0	104.9
97.5°	460.3	360.8	294.3	250.3	227.7	214.2	206.5
100°	726.1	600.0	488.6	412.3	372.7	346.0	329.5
102.5°	996.2	904.0	786.1	703.1	635.6	602.2	579.8
105°	1222.1	1234.1	1203.7	1146.6	1089.6	1050.0	1037.1
107.5°	1205.5	1301.2	1345.8	1353.0	1349.8	1341.9	1324.8
110°	1154.0	1271.8	1347.3	1386.8	1404.3	1412.6	1411.7



TEST NUMBER: P331413-927

CATALOG NUMBER: SA2XXDIP-C865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1092.9	1218.8	1305.3	1360.3	1389.6	1405.3	1410.2
115°	1009.6	1130.0	1224.9	1290.2	1332.5	1356.5	1364.8
117.5°	941.8	1051.1	1140.0	1206.7	1251.3	1276.6	1283.6
120°	906.4	1004.0	1087.7	1152.1	1195.4	1222.1	1231.3
122.5°	877.0	969.4	1045.0	1102.8	1145.3	1169.1	1176.8
125°	838.4	919.3	988.3	1041.7	1076.7	1099.7	1107.1
127.5°	800.8	877.2	940.9	987.5	1020.2	1040.1	1046.0
130°	775.8	848.5	909.2	954.3	985.6	1004.0	1011.4
132.5°	752.3	819.0	876.1	920.4	951.7	968.7	975.3
135°	715.0	775.8	827.3	866.9	897.2	913.8	917.5
137.5°	685.4	733.6	778.6	814.6	840.7	855.3	860.8
140°	666.3	708.6	749.1	778.6	802.5	816.3	821.8
142.5°	649.4	685.8	719.6	747.6	769.4	781.6	782.8
145°	627.6	656.2	682.9	704.9	720.6	729.8	732.5
147.5°	610.0	632.2	651.7	669.9	682.5	688.7	690.4
150°	598.2	617.5	634.1	647.8	658.9	664.4	665.4
152.5°	588.6	605.0	619.3	630.2	639.8	643.8	644.0
155°	573.3	587.1	597.2	607.4	613.8	617.5	615.7
157.5°	557.9	569.4	577.3	584.6	589.9	591.5	591.5
160°	547.6	557.7	564.1	570.5	575.1	576.1	576.1
162.5°	538.0	546.6	551.6	558.0	561.2	562.1	561.3
165°	523.6	530.0	533.8	537.4	541.1	541.1	540.2
167.5°	510.6	515.0	518.3	519.9	522.0	521.8	520.7
170°	502.5	506.1	507.9	508.9	511.7	510.7	508.9
172.5°	495.1	498.0	499.2	500.1	501.4	500.4	499.3
175°	486.8	487.7	488.6	488.6	489.6	488.6	486.8
177.5°	480.8	481.5	481.5	481.5	481.5	480.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)