

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333140-935

Luminaire Tested: **S125DIP-S375D810U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333140-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D810U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3724.8 lumens  
Efficiency: N/A  
Efficacy: 119.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	78	75	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	39	36	34	29	27	26	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3249	3249	3249
5°	3255	3225	3245
10°	3236	3202	3220
15°	3201	3163	3177
20°	3151	3110	3115
25°	3096	3046	3043
30°	3030	2976	2961
35°	2958	2902	2861
40°	2885	2822	2780
45°	2806	2747	2693
50°	2719	2659	2579
55°	2634	2558	2486
60°	2533	2457	2370
65°	2415	2335	2257
70°	2298	2194	2119
75°	2094	2026	1956
80°	1863	1834	1789
85°	1623	1652	1564



TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	1.3
10°-20°	134.0	3.6
20°-30°	197.8	5.3
30°-40°	230.8	6.2
40°-50°	231.8	6.2
50°-60°	203.5	5.5
60°-70°	151.6	4.1
70°-80°	86.7	2.3
80°-90°	27.1	0.7
90°-100°	57.9	1.6
100°-110°	171.1	4.6
110°-120°	289.8	7.8
120°-130°	381.4	10.2
130°-140°	427.4	11.5
140°-150°	418.9	11.2
150°-160°	351.8	9.4
160°-170°	233.9	6.3
170°-180°	81.8	2.2
0°-30°	379.2	10.2
0°-40°	610.0	16.4
0°-60°	1045.3	28.1
0°-90°	1310.7	35.2
90°-120°	518.9	13.9
90°-150°	1746.6	46.9
90°-180°	2414.0	64.8
0°-180°	3724.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	503	503	503	503	503	
5°	502	501	497	501	501	48
15°	479	477	473	475	475	135
25°	434	432	427	428	427	200
35°	375	373	368	366	363	235
45°	307	305	301	296	295	237
55°	234	232	227	224	221	209
65°	158	157	153	149	148	157
75°	84	83	81	80	78	89
85°	22	22	22	22	21	24
90°	1	6	11	14	16	4
95°	44	45	52	56	58	47
105°	154	157	161	165	167	164
115°	290	293	294	294	293	287
125°	423	427	428	427	426	379
135°	551	555	555	555	553	424
145°	667	670	672	672	670	417
155°	763	763	764	766	763	351
165°	830	829	830	832	828	234
175°	863	861	860	864	860	82
180°	865	865	865	865	865	



TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	504.2	504.0	503.9	503.6	503.4	502.9	502.2	501.5	500.8	500.1	500.8
5°	502.1	502.0	501.8	501.6	501.4	500.9	500.1	499.2	498.3	497.4	498.2
7.5°	497.6	497.4	497.2	497.1	496.9	496.3	495.3	494.3	493.4	492.4	493.2
10°	493.4	493.3	493.1	492.9	492.8	492.1	491.2	490.2	489.2	488.3	489.0
12.5°	488.4	488.0	487.7	487.4	487.1	486.5	485.5	484.7	483.7	482.8	483.4
15°	478.7	478.5	478.2	477.9	477.6	477.0	476.0	475.1	474.1	473.1	473.6
17.5°	467.6	467.3	466.8	466.5	466.1	465.4	464.3	463.4	462.4	461.3	461.9
20°	458.4	458.2	458.1	457.9	457.7	457.0	455.9	454.7	453.6	452.5	453.1
22.5°	449.2	448.8	448.5	448.2	447.9	447.2	446.1	445.1	443.9	442.9	443.3
25°	434.5	434.1	433.6	433.2	432.7	432.0	430.8	429.6	428.5	427.4	427.6
27.5°	417.4	417.2	416.9	416.6	416.4	415.6	414.5	413.3	412.1	410.9	411.0
30°	406.3	406.0	405.7	405.4	405.2	404.4	403.1	401.7	400.5	399.1	398.9
32.5°	394.2	393.7	393.4	393.0	392.5	391.8	390.5	389.3	388.2	387.0	386.7
35°	375.2	374.9	374.5	374.2	373.8	373.0	371.8	370.6	369.3	368.1	367.6
37.5°	355.6	355.2	354.7	354.2	353.8	353.0	351.8	350.7	349.5	348.4	347.7
40°	342.2	341.7	341.3	340.9	340.4	339.6	338.4	337.2	335.9	334.7	333.9
42.5°	327.9	327.5	327.2	326.7	326.4	325.6	324.3	323.1	321.8	320.6	319.9
45°	307.2	306.9	306.5	306.2	305.7	305.1	304.0	303.0	301.9	300.8	299.8
47.5°	284.9	284.9	284.9	285.0	285.0	284.4	283.1	281.8	280.5	279.2	278.2
50°	270.6	270.4	270.1	269.8	269.5	268.9	267.8	266.7	265.7	264.6	263.5
52.5°	256.0	255.7	255.5	255.4	255.2	254.5	253.4	252.3	251.1	249.9	249.0
55°	233.9	233.7	233.4	233.2	232.9	232.1	230.9	229.7	228.4	227.2	226.4
57.5°	210.9	210.7	210.5	210.4	210.3	209.7	208.6	207.6	206.6	205.5	204.5
60°	196.1	195.8	195.4	195.1	194.8	194.1	193.1	192.2	191.1	190.2	189.3
62.5°	180.9	180.6	180.3	180.0	179.8	179.2	178.4	177.5	176.7	175.9	175.0
65°	158.0	157.8	157.6	157.5	157.3	156.7	155.8	154.7	153.8	152.8	152.0
67.5°	135.8	135.4	135.0	134.7	134.3	133.7	133.0	132.2	131.6	130.9	130.2
70°	121.7	121.3	120.9	120.5	120.0	119.3	118.6	117.8	117.0	116.2	115.6
72.5°	106.5	106.2	105.9	105.6	105.3	104.9	104.4	103.8	103.3	102.8	102.2
75°	83.9	83.8	83.6	83.4	83.3	82.9	82.5	82.1	81.6	81.2	80.9
77.5°	63.2	63.1	63.0	62.9	62.9	62.8	62.5	62.3	62.0	61.7	61.6
80°	50.1	50.1	50.1	50.1	50.1	50.0	49.9	49.7	49.5	49.3	49.2
82.5°	38.7	38.6	38.4	38.2	38.1	38.1	38.0	38.0	37.9	37.9	37.7
85°	21.9	22.0	22.0	22.1	22.2	22.3	22.3	22.3	22.3	22.3	22.2
87.5°	8.7	9.0	9.2	9.5	9.7	9.9	10.0	10.2	10.3	10.4	10.6
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	16.3	17.1	18.0	18.8	19.6	20.7	22.0	23.2	24.5	25.8	26.9
95°	43.7	44.1	44.3	44.7	44.9	45.9	47.4	48.8	50.4	51.8	52.9
97.5°	72.8	72.8	72.9	73.1	73.2	74.3	76.4	78.4	80.5	82.6	83.5
100°	94.3	94.3	94.3	94.3	94.3	95.2	97.2	99.1	101.1	103.0	104.4
102.5°	117.4	118.0	118.6	119.2	119.9	120.6	121.6	122.6	123.6	124.6	126.1
105°	153.5	154.3	155.0	155.8	156.5	157.3	158.3	159.1	160.0	160.9	161.8
107.5°	193.4	194.1	194.8	195.6	196.4	197.1	197.8	198.5	199.1	199.8	200.3
110°	220.8	221.6	222.3	223.1	223.9	224.5	224.9	225.3	225.8	226.2	226.7



TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	248.8	249.3	249.6	250.0	250.4	250.9	251.4	252.0	252.6	253.1	253.4
115°	290.2	290.8	291.4	292.0	292.6	293.0	293.3	293.6	293.9	294.2	294.0
117.5°	331.7	331.9	332.2	332.4	332.7	333.0	333.3	333.6	333.8	334.1	334.2
120°	357.5	358.3	359.0	359.7	360.5	360.9	361.1	361.3	361.4	361.5	361.5
122.5°	385.5	385.8	386.1	386.3	386.6	386.9	387.3	387.7	388.1	388.5	388.3
125°	423.4	424.4	425.2	426.2	427.1	427.6	427.7	427.9	428.0	428.2	427.9
127.5°	463.9	464.4	464.9	465.4	465.9	466.2	466.4	466.6	466.8	467.0	466.8
130°	488.1	488.9	489.7	490.3	491.1	491.6	491.9	492.2	492.5	492.8	492.7
132.5°	512.4	513.6	514.8	516.0	517.3	517.8	517.8	517.7	517.6	517.6	517.5
135°	550.7	551.6	552.5	553.5	554.3	554.8	555.0	555.2	555.3	555.4	555.4
137.5°	586.9	587.7	588.6	589.4	590.3	590.9	591.2	591.5	591.9	592.2	592.4
140°	610.0	610.7	611.5	612.3	612.9	613.5	614.0	614.5	614.9	615.4	615.7
142.5°	633.2	633.8	634.4	635.0	635.7	636.3	636.8	637.4	637.9	638.5	638.7
145°	667.2	667.8	668.4	669.0	669.6	670.1	670.5	671.0	671.5	671.9	671.9
147.5°	698.7	699.0	699.4	699.7	700.0	700.3	700.8	701.1	701.5	701.8	702.1
150°	719.7	719.5	719.5	719.3	719.1	719.4	720.0	720.6	721.2	721.8	721.8
152.5°	736.9	737.2	737.4	737.6	737.8	738.0	738.2	738.5	738.7	739.0	739.3
155°	763.4	763.4	763.4	763.4	763.4	763.5	763.7	763.9	764.0	764.1	764.7
157.5°	787.2	786.9	786.5	786.2	785.8	785.7	785.9	786.1	786.2	786.4	787.0
160°	801.2	800.7	800.3	799.9	799.4	799.3	799.4	799.5	799.7	799.9	800.5
162.5°	813.6	813.2	812.9	812.6	812.3	812.1	812.1	812.2	812.2	812.3	813.0
165°	830.2	829.8	829.6	829.2	829.0	828.9	829.0	829.1	829.3	829.5	830.1
167.5°	844.1	843.5	842.9	842.3	841.7	841.5	841.5	841.5	841.5	841.5	842.3
170°	851.7	851.1	850.5	849.9	849.3	848.9	848.9	848.9	848.9	848.9	849.9
172.5°	857.0	856.4	855.8	855.2	854.6	854.4	854.4	854.4	854.4	854.4	855.2
175°	863.2	862.5	861.9	861.3	860.7	860.4	860.4	860.4	860.4	860.4	861.3
177.5°	866.3	865.7	865.3	864.8	864.3	864.0	863.9	863.8	863.7	863.5	864.3
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	501.5	502.2	502.9	503.3	503.2	503.1	503.1	503.0
5°	498.9	499.8	500.6	500.9	500.8	500.8	500.7	500.6
7.5°	494.0	494.7	495.5	495.8	495.8	495.7	495.6	495.5
10°	489.7	490.3	491.1	491.4	491.3	491.2	491.1	491.0
12.5°	484.0	484.6	485.1	485.3	485.3	485.3	485.3	485.3
15°	474.0	474.4	474.9	475.1	475.1	475.1	475.1	475.1
17.5°	462.4	463.0	463.6	463.6	463.1	462.7	462.3	461.8
20°	453.7	454.3	454.9	455.0	454.5	454.1	453.7	453.2
22.5°	443.7	444.1	444.5	444.5	444.3	443.9	443.7	443.3
25°	427.7	427.9	428.1	428.0	427.7	427.5	427.2	427.0
27.5°	411.0	411.0	411.0	411.0	410.6	410.4	410.1	409.8
30°	398.7	398.6	398.4	398.2	398.0	397.7	397.4	397.1
32.5°	386.4	386.1	385.7	385.4	384.9	384.4	383.9	383.4
35°	367.2	366.8	366.3	365.8	365.1	364.3	363.6	362.9
37.5°	347.1	346.4	345.7	345.2	344.7	344.4	344.0	343.5
40°	333.0	332.3	331.5	331.0	330.7	330.4	330.1	329.8
42.5°	319.2	318.5	317.7	317.2	316.8	316.3	316.0	315.6
45°	298.7	297.6	296.6	295.9	295.7	295.4	295.2	294.9
47.5°	277.1	276.0	274.9	274.1	273.5	272.9	272.2	271.6
50°	262.3	261.1	260.0	259.2	258.5	257.9	257.3	256.7
52.5°	248.0	246.9	245.9	245.1	244.4	243.7	243.1	242.4
55°	225.6	224.8	224.0	223.3	222.7	222.1	221.4	220.8
57.5°	203.5	202.4	201.4	200.7	200.4	200.0	199.7	199.3
60°	188.5	187.5	186.7	185.9	185.3	184.7	184.1	183.5
62.5°	174.0	173.0	172.0	171.3	170.9	170.4	169.9	169.4
65°	151.2	150.4	149.6	149.0	148.7	148.4	148.0	147.7
67.5°	129.5	128.8	128.1	127.7	127.5	127.3	127.1	126.8
70°	115.1	114.6	114.1	113.7	113.3	113.0	112.5	112.2
72.5°	101.6	101.0	100.4	100.0	99.6	99.3	98.8	98.5
75°	80.7	80.4	80.1	79.8	79.5	79.1	78.8	78.4
77.5°	61.5	61.3	61.1	61.0	60.7	60.4	60.2	59.9
80°	49.2	49.1	49.0	48.8	48.6	48.5	48.3	48.1
82.5°	37.5	37.4	37.3	37.1	37.1	37.1	37.0	37.0
85°	22.1	22.0	22.0	21.8	21.6	21.4	21.3	21.1
87.5°	10.8	10.8	11.0	11.1	11.0	10.9	10.9	10.8
90°	12.2	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	27.8	28.8	29.8	30.5	30.8	31.1	31.4	31.8
95°	53.9	55.0	56.1	56.7	57.0	57.3	57.6	57.9
97.5°	84.6	85.5	86.5	87.0	87.2	87.4	87.6	87.8
100°	105.7	107.0	108.4	109.3	109.5	109.8	110.1	110.4
102.5°	127.5	129.0	130.4	131.4	131.8	132.2	132.6	133.0
105°	162.7	163.6	164.5	165.1	165.7	166.1	166.5	166.9
107.5°	200.7	201.1	201.6	201.8	201.8	201.7	201.7	201.7
110°	227.1	227.6	228.0	228.2	228.0	227.8	227.7	227.6





TEST NUMBER: P333140-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	253.6	253.7	254.0	254.0	253.7	253.4	253.1	252.9
115°	293.9	293.8	293.6	293.4	293.3	293.2	293.0	292.9
117.5°	334.3	334.4	334.6	334.3	333.7	333.1	332.5	331.9
120°	361.5	361.5	361.5	361.3	360.7	360.1	359.5	358.9
122.5°	388.2	388.1	388.0	387.7	387.2	386.8	386.2	385.8
125°	427.6	427.3	427.0	426.8	426.6	426.5	426.4	426.2
127.5°	466.7	466.5	466.4	466.1	465.9	465.5	465.3	464.9
130°	492.5	492.4	492.2	492.0	491.7	491.4	491.1	490.8
132.5°	517.3	517.1	517.0	516.7	516.3	515.9	515.5	515.1
135°	555.4	555.4	555.4	555.2	554.6	554.0	553.4	552.8
137.5°	592.5	592.7	592.9	592.6	591.9	591.2	590.4	589.6
140°	616.0	616.2	616.6	616.3	615.6	614.8	614.1	613.4
142.5°	638.9	639.0	639.2	638.9	638.2	637.5	636.7	635.9
145°	671.9	671.9	671.9	671.7	671.2	670.8	670.4	669.9
147.5°	702.5	702.9	703.3	702.9	701.9	700.9	699.9	698.9
150°	721.8	721.8	721.8	721.6	721.3	721.0	720.7	720.4
152.5°	739.7	740.0	740.4	740.3	739.8	739.3	738.7	738.1
155°	765.3	765.9	766.5	766.5	765.7	765.0	764.2	763.4
157.5°	787.6	788.2	788.8	788.6	787.6	786.6	785.6	784.6
160°	801.1	801.6	802.2	802.2	801.4	800.6	799.9	799.2
162.5°	813.6	814.4	815.1	815.0	814.2	813.3	812.4	811.6
165°	830.7	831.3	831.8	831.7	830.8	829.9	829.0	828.1
167.5°	843.3	844.1	845.1	845.0	844.1	843.2	842.2	841.3
170°	850.8	851.7	852.6	852.5	851.4	850.4	849.4	848.3
172.5°	856.2	857.0	858.0	858.0	857.0	856.1	855.1	854.2
175°	862.2	863.2	864.0	863.9	862.9	861.9	860.8	859.8
177.5°	865.0	865.6	866.4	866.3	865.5	864.7	863.8	863.0
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1

(END OF REPORT)