

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333141-935

Luminaire Tested: **S125DIP-S375D810U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333141-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3814.7 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	67	77	71	66	62	57	54	50	44	42	40	32	31	30	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25	20
4	71	61	53	47	64	55	49	43	45	40	36	35	31	29	26	23	22	17
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	17	15	12
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3249	3249	3249
5°	3255	3225	3245
10°	3236	3202	3220
15°	3201	3163	3177
20°	3151	3110	3115
25°	3096	3046	3043
30°	3030	2976	2961
35°	2958	2902	2861
40°	2885	2822	2780
45°	2806	2747	2693
50°	2719	2659	2579
55°	2634	2558	2486
60°	2533	2457	2370
65°	2415	2335	2257
70°	2298	2194	2119
75°	2094	2026	1956
80°	1863	1834	1789
85°	1623	1652	1564



TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.2
10°-20°	134.0	3.5
20°-30°	197.8	5.2
30°-40°	230.8	6.1
40°-50°	231.8	6.1
50°-60°	203.5	5.3
60°-70°	151.6	4.0
70°-80°	86.7	2.3
80°-90°	27.1	0.7
90°-100°	242.0	6.3
100°-110°	520.3	13.6
110°-120°	488.3	12.8
120°-130°	395.7	10.4
130°-140°	317.6	8.3
140°-150°	239.7	6.3
150°-160°	168.7	4.4
160°-170°	99.4	2.6
170°-180°	32.3	0.8
0°-30°	379.2	9.9
0°-40°	610.0	16.0
0°-60°	1045.3	27.4
0°-90°	1310.7	34.4
90°-120°	1250.6	32.8
90°-150°	2203.6	57.8
90°-180°	2504.0	65.6
0°-180°	3814.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	503	503	503	503	503	
5°	502	501	497	501	501	48
15°	479	477	473	475	475	135
25°	434	432	427	428	427	200
35°	375	373	368	366	363	235
45°	307	305	301	296	295	237
55°	234	232	227	224	221	209
65°	158	157	153	149	148	157
75°	84	83	81	80	78	89
85°	22	22	22	22	21	24
90°	1	6	11	14	16	3
95°	22	66	596	271	158	24
105°	76	106	488	961	892	80
115°	136	164	392	845	994	134
125°	188	221	376	672	783	167
135°	221	266	373	563	650	171
145°	257	295	374	466	513	161
155°	294	316	365	412	430	135
165°	320	329	350	371	377	90
175°	333	333	336	340	339	32
180°	334	334	334	334	334	



TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	504.2	504.0	503.9	503.6	503.4	502.9	502.2	501.5	500.8	500.1	500.8
5°	502.1	502.0	501.8	501.6	501.4	500.9	500.1	499.2	498.3	497.4	498.2
7.5°	497.6	497.4	497.2	497.1	496.9	496.3	495.3	494.3	493.4	492.4	493.2
10°	493.4	493.3	493.1	492.9	492.8	492.1	491.2	490.2	489.2	488.3	489.0
12.5°	488.4	488.0	487.7	487.4	487.1	486.5	485.5	484.7	483.7	482.8	483.4
15°	478.7	478.5	478.2	477.9	477.6	477.0	476.0	475.1	474.1	473.1	473.6
17.5°	467.6	467.3	466.8	466.5	466.1	465.4	464.3	463.4	462.4	461.3	461.9
20°	458.4	458.2	458.1	457.9	457.7	457.0	455.9	454.7	453.6	452.5	453.1
22.5°	449.2	448.8	448.5	448.2	447.9	447.2	446.1	445.1	443.9	442.9	443.3
25°	434.5	434.1	433.6	433.2	432.7	432.0	430.8	429.6	428.5	427.4	427.6
27.5°	417.4	417.2	416.9	416.6	416.4	415.6	414.5	413.3	412.1	410.9	411.0
30°	406.3	406.0	405.7	405.4	405.2	404.4	403.1	401.7	400.5	399.1	398.9
32.5°	394.2	393.7	393.4	393.0	392.5	391.8	390.5	389.3	388.2	387.0	386.7
35°	375.2	374.9	374.5	374.2	373.8	373.0	371.8	370.6	369.3	368.1	367.6
37.5°	355.6	355.2	354.7	354.2	353.8	353.0	351.8	350.7	349.5	348.4	347.7
40°	342.2	341.7	341.3	340.9	340.4	339.6	338.4	337.2	335.9	334.7	333.9
42.5°	327.9	327.5	327.2	326.7	326.4	325.6	324.3	323.1	321.8	320.6	319.9
45°	307.2	306.9	306.5	306.2	305.7	305.1	304.0	303.0	301.9	300.8	299.8
47.5°	284.9	284.9	284.9	285.0	285.0	284.4	283.1	281.8	280.5	279.2	278.2
50°	270.6	270.4	270.1	269.8	269.5	268.9	267.8	266.7	265.7	264.6	263.5
52.5°	256.0	255.7	255.5	255.4	255.2	254.5	253.4	252.3	251.1	249.9	249.0
55°	233.9	233.7	233.4	233.2	232.9	232.1	230.9	229.7	228.4	227.2	226.4
57.5°	210.9	210.7	210.5	210.4	210.3	209.7	208.6	207.6	206.6	205.5	204.5
60°	196.1	195.8	195.4	195.1	194.8	194.1	193.1	192.2	191.1	190.2	189.3
62.5°	180.9	180.6	180.3	180.0	179.8	179.2	178.4	177.5	176.7	175.9	175.0
65°	158.0	157.8	157.6	157.5	157.3	156.7	155.8	154.7	153.8	152.8	152.0
67.5°	135.8	135.4	135.0	134.7	134.3	133.7	133.0	132.2	131.6	130.9	130.2
70°	121.7	121.3	120.9	120.5	120.0	119.3	118.6	117.8	117.0	116.2	115.6
72.5°	106.5	106.2	105.9	105.6	105.3	104.9	104.4	103.8	103.3	102.8	102.2
75°	83.9	83.8	83.6	83.4	83.3	82.9	82.5	82.1	81.6	81.2	80.9
77.5°	63.2	63.1	63.0	62.9	62.9	62.8	62.5	62.3	62.0	61.7	61.6
80°	50.1	50.1	50.1	50.1	50.1	50.0	49.9	49.7	49.5	49.3	49.2
82.5°	38.7	38.6	38.4	38.2	38.1	38.1	38.0	38.0	37.9	37.9	37.7
85°	21.9	22.0	22.0	22.1	22.2	22.3	22.3	22.3	22.3	22.3	22.2
87.5°	8.7	8.9	9.1	9.4	9.6	9.9	10.0	10.2	10.2	10.4	10.6
90°	0.7	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5
92.5°	8.2	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7
95°	22.2	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7
97.5°	36.9	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5
100°	47.1	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2
102.5°	58.5	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6
105°	76.1	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3
107.5°	93.3	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5
110°	105.7	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5



TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	118.0	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3
115°	136.0	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2
117.5°	152.1	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8
120°	162.9	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6
122.5°	174.3	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8
125°	188.5	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7
127.5°	199.7	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5
130°	206.6	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5
132.5°	212.1	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0
135°	220.8	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3
137.5°	231.9	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5
140°	238.3	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2
142.5°	245.8	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6
145°	257.2	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5
147.5°	269.0	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3
150°	276.0	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1
152.5°	283.5	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3
155°	293.5	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0
157.5°	302.4	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1
160°	308.3	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3
162.5°	313.1	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9
165°	320.5	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4
167.5°	325.3	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1
170°	328.6	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3
172.5°	330.7	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6
175°	333.2	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6
177.5°	334.4	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	501.5	502.2	502.9	503.3	503.2	503.1	503.1	503.0
5°	498.9	499.8	500.6	500.9	500.8	500.8	500.7	500.6
7.5°	494.0	494.7	495.5	495.8	495.8	495.7	495.6	495.5
10°	489.7	490.3	491.1	491.4	491.3	491.2	491.1	491.0
12.5°	484.0	484.6	485.1	485.3	485.3	485.3	485.3	485.3
15°	474.0	474.4	474.9	475.1	475.1	475.1	475.1	475.1
17.5°	462.4	463.0	463.6	463.6	463.1	462.7	462.3	461.8
20°	453.7	454.3	454.9	455.0	454.5	454.1	453.7	453.2
22.5°	443.7	444.1	444.5	444.5	444.3	443.9	443.7	443.3
25°	427.7	427.9	428.1	428.0	427.7	427.5	427.2	427.0
27.5°	411.0	411.0	411.0	411.0	410.6	410.4	410.1	409.8
30°	398.7	398.6	398.4	398.2	398.0	397.7	397.4	397.1
32.5°	386.4	386.1	385.7	385.4	384.9	384.4	383.9	383.4
35°	367.2	366.8	366.3	365.8	365.1	364.3	363.6	362.9
37.5°	347.1	346.4	345.7	345.2	344.7	344.4	344.0	343.5
40°	333.0	332.3	331.5	331.0	330.7	330.4	330.1	329.8
42.5°	319.2	318.5	317.7	317.2	316.8	316.3	316.0	315.6
45°	298.7	297.6	296.6	295.9	295.7	295.4	295.2	294.9
47.5°	277.1	276.0	274.9	274.1	273.5	272.9	272.2	271.6
50°	262.3	261.1	260.0	259.2	258.5	257.9	257.3	256.7
52.5°	248.0	246.9	245.9	245.1	244.4	243.7	243.1	242.4
55°	225.6	224.8	224.0	223.3	222.7	222.1	221.4	220.8
57.5°	203.5	202.4	201.4	200.7	200.4	200.0	199.7	199.3
60°	188.5	187.5	186.7	185.9	185.3	184.7	184.1	183.5
62.5°	174.0	173.0	172.0	171.3	170.9	170.4	169.9	169.4
65°	151.2	150.4	149.6	149.0	148.7	148.4	148.0	147.7
67.5°	129.5	128.8	128.1	127.7	127.5	127.3	127.1	126.8
70°	115.1	114.6	114.1	113.7	113.3	113.0	112.5	112.2
72.5°	101.6	101.0	100.4	100.0	99.6	99.3	98.8	98.5
75°	80.7	80.4	80.1	79.8	79.5	79.1	78.8	78.4
77.5°	61.5	61.3	61.1	61.0	60.7	60.4	60.2	59.9
80°	49.2	49.1	49.0	48.8	48.6	48.5	48.3	48.1
82.5°	37.5	37.4	37.3	37.1	37.1	37.1	37.0	37.0
85°	22.1	22.0	22.0	21.8	21.6	21.4	21.3	21.1
87.5°	10.7	10.8	10.9	11.2	11.0	10.8	10.8	10.8
90°	12.1	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	119.3	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	484.1	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	720.9	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	828.0	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	864.1	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	842.8	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	766.9	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	710.9	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333141-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	666.8	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	611.3	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	575.5	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	556.0	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	541.6	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	520.4	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	498.9	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	485.3	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	471.9	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	454.4	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	439.6	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	431.5	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	424.6	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	415.3	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	406.7	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	401.9	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	396.5	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	388.5	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	380.4	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	375.0	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	369.0	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	360.8	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	353.0	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	348.7	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	343.9	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.0	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)