

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331382-927

Luminaire Tested: **SA2XXDIP-C865D330U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331382-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3710.0 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67	63
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56	53
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	38
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17651	17651	17651
5°	17718	17462	17566
10°	17613	17285	17372
15°	17396	17061	17043
20°	17086	16725	16706
25°	16778	16311	16311
30°	16384	15933	15795
35°	16015	15477	15248
40°	15553	15022	14733
45°	15098	14570	14209
50°	14601	14099	13599
55°	14083	13551	13050
60°	13511	12897	12426
65°	12894	12248	11687
70°	12109	11462	10914
75°	11017	10555	10293
80°	9772	9484	8991
85°	7984	7595	6817



TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.8	2.8
10°-20°	289.3	7.8
20°-30°	425.2	11.5
30°-40°	493.9	13.3
40°-50°	493.3	13.3
50°-60°	430.2	11.6
60°-70°	318.1	8.6
70°-80°	180.2	4.9
80°-90°	49.8	1.3
90°-100°	21.0	0.6
100°-110°	65.3	1.8
110°-120°	111.6	3.0
120°-130°	146.7	4.0
130°-140°	164.7	4.4
140°-150°	161.5	4.4
150°-160°	135.4	3.7
160°-170°	89.8	2.4
170°-180°	31.4	0.8
0°-30°	817.2	22.0
0°-40°	1311.1	35.3
0°-60°	2234.6	60.2
0°-90°	2782.6	75.0
90°-120°	197.9	5.3
90°-150°	670.7	18.1
90°-180°	927.0	25.0
0°-180°	3710.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1093	1093	1093	1093	1093	
5°	1093	1089	1077	1085	1084	104
15°	1041	1034	1021	1024	1020	293
25°	942	933	916	917	916	433
35°	812	802	785	779	774	507
45°	661	653	638	627	622	510
55°	500	494	481	469	464	447
65°	338	331	321	311	306	334
75°	177	174	169	163	165	189
85°	43	42	41	38	37	49
90°	0	4	10	9	10	3
95°	15	17	18	18	17	17
105°	60	61	62	62	62	64
115°	112	114	113	113	112	111
125°	163	165	164	164	163	146
135°	211	214	214	214	213	163
145°	256	258	259	260	259	160
155°	292	293	294	295	295	135
165°	318	318	318	320	318	90
175°	331	330	330	331	330	31
180°	332	332	332	332	332	



TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1098.3	1097.3	1096.4	1095.5	1094.6	1093.1	1091.0	1088.9	1086.9	1084.8	1086.7
5°	1093.2	1092.3	1091.4	1090.4	1089.5	1087.7	1085.2	1082.6	1080.1	1077.4	1079.3
7.5°	1083.5	1082.1	1080.7	1079.2	1077.8	1075.7	1073.1	1070.5	1067.9	1065.2	1067.1
10°	1074.3	1072.7	1071.0	1069.4	1067.8	1065.6	1062.7	1059.9	1057.2	1054.3	1056.2
12.5°	1061.7	1060.3	1058.8	1057.3	1055.9	1053.8	1051.0	1048.1	1045.4	1042.6	1043.9
15°	1040.7	1039.3	1037.8	1036.5	1035.1	1032.8	1029.8	1026.7	1023.7	1020.7	1021.6
17.5°	1013.8	1012.3	1011.0	1009.6	1008.1	1005.9	1002.8	999.7	996.6	993.6	994.7
20°	994.4	993.0	991.7	990.2	988.8	986.5	983.2	979.9	976.7	973.4	974.1
22.5°	975.1	973.1	971.1	969.2	967.3	964.7	961.6	958.5	955.5	952.4	952.5
25°	941.8	940.0	938.1	936.3	934.4	931.4	927.5	923.5	919.6	915.6	916.1
27.5°	904.0	902.4	900.6	899.0	897.3	894.8	891.8	888.6	885.5	882.3	881.7
30°	878.8	876.9	875.0	873.2	871.3	868.6	865.1	861.7	858.1	854.6	853.9
32.5°	851.9	850.4	848.9	847.4	845.9	843.3	839.6	835.9	832.3	828.5	827.3
35°	812.5	810.2	807.9	805.6	803.2	800.2	796.5	792.7	788.9	785.2	783.9
37.5°	768.2	766.1	764.1	762.0	760.0	757.1	753.4	749.6	745.8	742.1	740.4
40°	737.9	736.1	734.2	732.3	730.5	727.6	723.9	720.2	716.4	712.7	710.6
42.5°	708.5	706.6	704.7	702.9	701.0	698.2	694.5	690.8	687.0	683.3	681.0
45°	661.2	659.6	657.9	656.3	654.7	652.0	648.6	645.1	641.6	638.1	635.5
47.5°	614.1	612.6	611.0	609.5	607.9	605.3	601.7	598.0	594.4	590.7	588.0
50°	581.3	580.1	579.0	577.8	576.6	574.4	571.2	567.8	564.6	561.3	558.1
52.5°	549.4	547.8	546.3	544.7	543.2	540.9	537.8	534.7	531.6	528.5	525.9
55°	500.3	499.0	497.6	496.1	494.7	492.7	489.9	487.0	484.3	481.4	478.6
57.5°	451.1	450.0	448.9	447.8	446.7	444.6	441.5	438.4	435.3	432.2	429.5
60°	418.4	417.4	416.5	415.6	414.6	412.6	409.2	406.0	402.7	399.4	396.9
62.5°	386.4	384.9	383.4	381.9	380.4	378.4	375.9	373.4	370.8	368.4	366.0
65°	337.5	336.0	334.6	333.2	331.8	329.9	327.6	325.3	323.0	320.6	318.5
67.5°	287.6	286.5	285.3	284.2	283.1	281.5	279.4	277.3	275.2	273.1	271.5
70°	256.5	255.6	254.6	253.7	252.8	251.2	249.1	247.0	244.9	242.8	241.2
72.5°	224.5	223.6	222.7	221.7	220.8	219.7	218.3	217.0	215.6	214.2	212.6
75°	176.6	176.1	175.6	175.2	174.8	173.9	172.8	171.6	170.4	169.2	167.9
77.5°	133.7	132.9	132.1	131.3	130.6	129.9	129.4	129.0	128.5	128.0	127.3
80°	105.1	104.9	104.6	104.4	104.2	103.9	103.4	102.9	102.4	102.0	101.2
82.5°	78.2	78.2	78.1	78.0	78.0	77.9	77.6	77.3	77.0	76.8	75.8
85°	43.1	42.9	42.6	42.4	42.1	41.9	41.7	41.4	41.2	41.0	40.3
87.5°	15.2	15.0	14.7	14.5	14.3	14.1	14.0	13.9	13.9	13.7	13.2
90°	0.3	1.0	1.7	2.5	3.2	4.4	5.7	7.1	8.4	9.8	9.7
92.5°	5.0	5.5	6.1	6.7	7.2	7.6	7.9	8.2	8.6	8.9	9.0
95°	14.6	15.2	15.8	16.4	17.0	17.4	17.5	17.7	17.8	17.9	17.9
97.5°	26.6	27.2	27.6	28.2	28.8	29.2	29.4	29.6	29.9	30.1	30.1
100°	35.6	36.0	36.5	37.1	37.5	37.9	38.0	38.3	38.4	38.7	38.7
102.5°	44.9	45.3	45.7	46.1	46.5	46.9	47.1	47.3	47.5	47.8	47.8
105°	60.2	60.4	60.5	60.8	60.9	61.1	61.2	61.3	61.5	61.6	61.7
107.5°	75.5	75.8	76.0	76.4	76.6	76.8	76.8	76.8	76.8	76.8	76.8
110°	85.4	85.7	86.1	86.5	86.8	87.1	87.1	87.1	87.1	87.1	87.1



TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.1	96.5	96.9	97.2	97.6	97.8	97.7	97.7	97.6	97.6	97.4
115°	111.9	112.3	112.7	113.0	113.4	113.6	113.4	113.3	113.2	113.0	113.0
117.5°	127.7	128.3	128.7	129.2	129.8	129.8	129.4	129.1	128.7	128.4	128.3
120°	138.2	138.8	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2	138.2
122.5°	147.9	148.5	149.1	149.6	150.3	150.4	150.0	149.7	149.3	149.0	148.9
125°	162.9	163.4	164.0	164.5	165.1	165.3	165.1	164.9	164.8	164.5	164.4
127.5°	177.5	178.2	179.0	179.6	180.3	180.5	180.4	180.1	179.9	179.7	179.4
130°	186.7	187.5	188.3	189.1	189.9	190.3	190.1	190.0	189.9	189.7	189.6
132.5°	197.0	197.6	198.3	198.9	199.6	199.9	199.9	200.0	200.0	200.0	199.8
135°	210.7	211.4	212.1	212.8	213.5	213.9	214.0	214.1	214.3	214.4	214.3
137.5°	225.2	225.8	226.3	227.0	227.5	227.8	228.0	228.1	228.3	228.5	228.5
140°	234.0	234.6	235.1	235.7	236.2	236.6	236.9	237.3	237.6	237.9	237.9
142.5°	243.0	243.5	244.1	244.6	245.2	245.6	245.7	246.0	246.2	246.4	246.4
145°	255.8	256.3	256.7	257.1	257.5	257.9	258.3	258.7	259.0	259.4	259.5
147.5°	267.3	267.8	268.3	268.9	269.3	269.7	270.0	270.3	270.5	270.8	270.9
150°	275.1	275.5	275.8	276.2	276.6	276.9	277.2	277.4	277.7	277.9	278.1
152.5°	282.1	282.4	282.8	283.2	283.5	283.9	284.2	284.5	284.8	285.1	285.3
155°	292.5	292.6	292.9	293.0	293.2	293.4	293.6	293.7	294.0	294.1	294.5
157.5°	301.3	301.5	301.6	301.7	301.9	302.0	302.1	302.2	302.3	302.5	302.9
160°	306.7	306.9	307.0	307.1	307.2	307.4	307.4	307.4	307.5	307.6	307.9
162.5°	311.6	311.7	311.7	311.7	311.8	311.8	311.9	312.0	312.0	312.0	312.5
165°	318.2	318.1	318.1	318.1	318.0	317.9	317.9	317.9	317.9	317.9	318.4
167.5°	323.7	323.5	323.4	323.1	323.0	322.9	322.8	322.8	322.8	322.8	323.2
170°	326.6	326.5	326.2	326.1	325.9	325.7	325.7	325.6	325.6	325.5	325.9
172.5°	328.6	328.4	328.3	328.0	327.9	327.7	327.7	327.6	327.6	327.5	328.0
175°	331.1	330.9	330.7	330.5	330.3	330.2	330.1	329.9	329.8	329.7	330.1
177.5°	332.1	331.9	331.8	331.7	331.5	331.4	331.3	331.2	331.1	331.0	331.3
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1088.5	1090.4	1092.3	1093.1	1092.7	1092.3	1091.9	1091.5
5°	1081.2	1083.1	1085.0	1085.6	1085.2	1084.7	1084.3	1083.8
7.5°	1069.0	1070.9	1072.8	1073.4	1072.9	1072.4	1071.9	1071.3
10°	1058.0	1059.9	1061.8	1062.4	1061.7	1061.0	1060.3	1059.6
12.5°	1045.2	1046.5	1047.8	1048.2	1047.7	1047.2	1046.6	1046.2
15°	1022.5	1023.5	1024.5	1024.3	1023.2	1022.0	1020.8	1019.6
17.5°	995.7	996.8	997.9	997.8	996.7	995.6	994.5	993.4
20°	974.8	975.5	976.2	976.0	975.2	974.2	973.3	972.3
22.5°	952.7	952.8	952.9	952.8	952.1	951.6	951.0	950.5
25°	916.6	917.0	917.4	917.4	917.0	916.6	916.1	915.6
27.5°	881.0	880.3	879.6	878.7	877.5	876.4	875.3	874.2
30°	853.2	852.5	851.8	851.0	850.1	849.1	848.2	847.2
32.5°	826.0	824.7	823.5	822.4	821.5	820.5	819.6	818.6
35°	782.4	781.0	779.7	778.3	777.2	776.0	774.8	773.6
37.5°	738.7	737.0	735.2	733.8	732.7	731.6	730.5	729.3
40°	708.5	706.4	704.3	702.7	701.9	700.9	700.0	699.0
42.5°	678.7	676.4	674.1	672.3	671.0	669.7	668.4	667.1
45°	633.0	630.3	627.8	626.1	625.1	624.2	623.2	622.3
47.5°	585.3	582.7	580.0	577.9	576.6	575.2	573.9	572.5
50°	554.8	551.5	548.3	546.1	544.9	543.7	542.6	541.4
52.5°	523.1	520.4	517.7	515.6	514.0	512.5	511.0	509.4
55°	475.9	473.0	470.2	468.3	467.1	465.9	464.8	463.6
57.5°	426.7	424.0	421.2	419.4	418.5	417.6	416.8	415.8
60°	394.3	391.7	389.2	387.5	386.8	386.1	385.4	384.8
62.5°	363.5	361.2	358.8	357.2	356.2	355.4	354.5	353.6
65°	316.4	314.3	312.2	310.5	309.4	308.2	307.0	305.9
67.5°	269.8	268.2	266.6	265.3	264.4	263.4	262.4	261.5
70°	239.6	237.9	236.3	235.0	234.1	233.1	232.2	231.2
72.5°	211.0	209.3	207.7	206.5	205.7	205.0	204.2	203.5
75°	166.4	165.0	163.7	163.2	163.7	164.1	164.5	165.0
77.5°	126.7	126.0	125.2	124.5	123.9	123.3	122.6	121.9
80°	100.5	99.9	99.2	98.5	98.1	97.7	97.2	96.7
82.5°	74.9	74.1	73.2	72.7	72.6	72.5	72.4	72.3
85°	39.6	38.9	38.2	37.7	37.5	37.2	37.0	36.8
87.5°	12.6	12.0	11.4	11.0	10.9	10.7	10.5	10.3
90°	9.6	9.4	9.3	9.3	9.3	9.4	9.4	9.5
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
95°	17.9	17.9	17.9	17.8	17.7	17.6	17.5	17.3
97.5°	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.0
100°	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3
102.5°	47.9	47.9	48.0	48.0	47.9	47.8	47.8	47.8
105°	61.8	61.9	62.1	62.1	62.1	62.1	62.1	62.1
107.5°	76.8	76.9	76.9	76.8	76.5	76.3	76.0	75.7
110°	87.1	87.1	87.1	87.0	86.7	86.6	86.4	86.2





TEST NUMBER: P331382-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	97.3	97.1	97.0	96.8	96.7	96.6	96.4	96.3
115°	113.0	112.9	112.8	112.7	112.5	112.3	112.2	111.9
117.5°	128.1	127.9	127.8	127.6	127.5	127.3	127.1	126.9
120°	138.2	138.2	138.2	138.2	138.0	137.8	137.6	137.4
122.5°	148.7	148.5	148.4	148.3	148.1	148.0	147.8	147.7
125°	164.2	164.0	163.8	163.7	163.7	163.6	163.5	163.4
127.5°	179.3	179.0	178.8	178.6	178.4	178.2	178.0	177.8
130°	189.5	189.4	189.3	189.1	188.9	188.5	188.3	188.1
132.5°	199.5	199.2	199.0	198.8	198.5	198.4	198.1	198.0
135°	214.3	214.2	214.1	214.0	213.8	213.7	213.5	213.3
137.5°	228.4	228.3	228.3	228.1	227.9	227.7	227.4	227.1
140°	237.9	237.9	237.9	237.7	237.5	237.3	237.0	236.8
142.5°	246.5	246.5	246.6	246.5	246.3	246.0	245.7	245.5
145°	259.6	259.6	259.7	259.6	259.4	259.1	258.9	258.6
147.5°	271.0	271.2	271.3	271.2	271.0	270.8	270.5	270.3
150°	278.3	278.5	278.7	278.7	278.5	278.3	278.1	277.9
152.5°	285.6	285.8	286.1	286.1	285.8	285.6	285.3	285.1
155°	294.8	295.1	295.4	295.5	295.2	295.1	294.9	294.7
157.5°	303.2	303.7	304.1	304.2	303.9	303.6	303.3	303.0
160°	308.3	308.7	309.1	309.1	308.9	308.6	308.4	308.2
162.5°	312.9	313.3	313.8	313.8	313.5	313.2	312.9	312.6
165°	318.8	319.2	319.6	319.7	319.4	319.1	318.8	318.5
167.5°	323.7	324.1	324.6	324.6	324.3	323.9	323.6	323.3
170°	326.4	326.8	327.3	327.3	326.9	326.5	326.1	325.7
172.5°	328.4	328.8	329.2	329.3	328.9	328.5	328.2	327.8
175°	330.6	331.0	331.4	331.4	331.1	330.7	330.3	329.9
177.5°	331.6	331.8	332.2	332.2	331.8	331.6	331.3	331.0
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7

(END OF REPORT)