

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333188-935

Luminaire Tested: **S125DIP-S610D1035U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333188-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1035U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5259.1 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	32	30	25
4	73	63	55	49	66	57	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	28	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4977	4977	4977	4977
5°	5763	4994	4372	4994
10°	6705	4968	3831	4968
15°	7422	4931	3534	4931
20°	8308	4874	3296	4874
25°	9733	4809	3180	4809
30°	10513	4744	3078	4744
35°	8643	4623	3012	4623
40°	6144	4457	2939	4457
45°	4720	4230	2898	4230
50°	4029	3950	2892	3950
55°	3587	3675	2917	3675
60°	3237	3375	2992	3375
65°	2989	3073	3069	3073
70°	2717	2761	3114	2761
75°	2400	2433	3084	2433
80°	2020	1982	2823	1982
85°	1601	1430	2275	1430



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	1.4
10°-20°	220.9	4.2
20°-30°	358.6	6.8
30°-40°	437.5	8.3
40°-50°	398.0	7.6
50°-60°	317.0	6.0
60°-70°	220.8	4.2
70°-80°	117.7	2.2
80°-90°	32.1	0.6
90°-100°	74.0	1.4
100°-110°	218.5	4.2
110°-120°	370.0	7.0
120°-130°	487.0	9.3
130°-140°	545.7	10.4
140°-150°	534.8	10.2
150°-160°	449.2	8.5
160°-170°	298.6	5.7
170°-180°	104.5	2.0
0°-30°	653.7	12.4
0°-40°	1091.2	20.7
0°-60°	1806.2	34.3
0°-90°	2176.9	41.4
90°-120°	662.5	12.6
90°-150°	2229.9	42.4
90°-180°	3082.0	58.6
0°-180°	5259.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	771	771	771	771	771	
5°	889	770	674	770	889	90
15°	1110	738	529	738	1110	318
25°	1366	675	446	675	1366	624
35°	1096	586	382	586	1096	671
45°	517	463	317	463	517	414
55°	319	326	259	326	319	287
65°	196	201	201	201	196	194
75°	96	98	124	98	96	104
85°	22	19	31	19	22	25
90°	21	1	21	1	21	13
95°	74	56	74	56	74	75
105°	213	196	213	196	213	226
115°	374	370	374	370	374	370
125°	544	541	544	541	544	486
135°	706	703	706	703	706	544
145°	855	852	855	852	855	534
155°	975	975	975	975	975	449
165°	1057	1060	1057	1060	1057	298
175°	1098	1102	1098	1102	1098	104
180°	1105	1105	1105	1105	1105	



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	815.1	814.0	813.0	810.9	812.4	808.0	805.9	802.3	797.8	796.3	794.4
5°	889.0	890.6	892.3	885.4	886.1	881.5	871.0	862.5	855.7	846.8	840.6
7.5°	977.9	974.0	973.8	969.3	961.7	955.5	944.5	930.5	917.0	901.6	888.8
10°	1022.4	1022.8	1019.9	1014.6	1006.4	1000.5	986.1	972.4	955.7	936.1	922.0
12.5°	1055.9	1057.3	1053.6	1046.5	1042.5	1029.3	1018.0	1001.7	981.9	966.2	944.8
15°	1110.1	1106.5	1103.9	1095.0	1088.1	1074.4	1056.4	1039.4	1017.9	997.9	977.9
17.5°	1162.3	1165.2	1160.3	1152.2	1130.9	1114.8	1090.7	1067.5	1040.5	1013.8	990.0
20°	1208.8	1211.5	1203.9	1189.9	1164.4	1148.3	1116.6	1086.5	1055.5	1021.1	995.0
22.5°	1267.0	1264.9	1254.7	1233.3	1211.3	1181.6	1147.3	1110.6	1071.7	1032.9	998.1
25°	1365.9	1352.1	1345.9	1319.4	1290.3	1246.8	1199.7	1146.1	1097.7	1046.3	1001.9
27.5°	1420.6	1416.3	1409.5	1390.9	1360.4	1313.9	1258.4	1193.0	1124.6	1059.9	1001.6
30°	1409.7	1410.3	1411.0	1405.1	1385.5	1350.5	1295.2	1224.9	1143.8	1070.8	1003.5
32.5°	1312.3	1324.2	1335.7	1349.1	1354.6	1347.9	1313.3	1249.7	1166.3	1083.4	1002.4
35°	1096.3	1099.9	1137.0	1173.5	1223.2	1261.9	1287.7	1259.6	1189.2	1094.1	1001.2
37.5°	854.8	872.5	898.1	939.5	1011.2	1075.5	1158.1	1196.1	1173.4	1097.5	998.8
40°	728.8	745.1	761.7	803.9	864.4	942.3	1036.1	1116.3	1135.0	1086.5	991.0
42.5°	631.4	644.4	662.9	694.6	745.1	814.1	903.8	1008.5	1072.9	1054.6	974.6
45°	516.8	525.0	539.3	564.6	601.2	655.1	734.3	848.8	948.5	981.5	935.4
47.5°	442.3	442.3	453.5	470.9	497.3	543.1	601.7	691.4	797.9	876.8	873.1
50°	401.0	399.3	408.2	423.3	444.2	474.6	530.5	602.2	704.6	793.8	818.6
52.5°	365.4	365.6	371.0	382.1	399.7	425.7	467.4	532.0	619.5	711.1	757.9
55°	318.6	317.3	323.5	331.0	343.8	360.8	390.9	440.2	511.2	601.5	662.3
57.5°	275.7	279.2	281.7	287.0	297.6	308.9	334.3	370.6	426.9	504.4	568.7
60°	250.6	254.2	256.1	261.3	269.8	279.7	299.3	328.7	376.2	442.9	506.6
62.5°	228.0	230.8	231.5	236.2	243.1	252.7	268.1	292.8	330.4	388.7	451.2
65°	195.6	195.6	196.9	201.8	205.1	213.6	225.3	243.3	273.5	318.9	372.2
67.5°	164.3	165.9	165.6	167.7	170.7	177.4	185.8	200.6	222.9	256.1	298.8
70°	143.9	145.3	144.9	146.5	149.8	154.0	160.9	175.0	191.0	219.5	256.1
72.5°	125.6	126.1	125.3	127.4	129.4	133.1	140.8	148.3	163.2	187.3	217.4
75°	96.2	96.8	97.5	98.8	100.7	102.7	106.6	114.2	124.0	142.0	161.3
77.5°	72.1	70.9	72.4	72.2	73.4	74.8	78.3	82.3	90.3	101.7	116.7
80°	54.3	54.6	54.6	54.9	56.6	57.6	60.5	63.5	69.7	78.2	88.6
82.5°	39.6	40.5	40.0	40.6	41.9	42.6	44.3	46.7	50.3	57.0	64.6
85°	21.6	20.0	20.6	21.3	21.3	21.6	22.9	23.8	25.8	28.4	31.4
87.5°	10.4	10.8	10.9	10.8	11.0	10.8	11.7	11.5	12.1	12.7	13.4
90°	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7	14.7	13.8	12.4
92.5°	40.6	40.1	39.7	39.3	38.9	38.1	36.8	35.6	34.3	33.0	31.3
95°	74.0	73.5	73.2	72.8	72.4	71.5	70.2	68.9	67.5	66.2	64.3
97.5°	112.1	111.8	111.7	111.4	111.2	110.5	109.2	107.9	106.7	105.4	102.7
100°	140.9	140.6	140.2	139.8	139.5	138.4	136.6	134.9	133.2	131.5	129.1
102.5°	169.9	169.4	168.8	168.2	167.7	166.5	164.6	162.7	160.9	159.0	157.7
105°	213.2	212.6	212.1	211.5	210.9	210.0	208.9	207.8	206.6	205.4	204.3
107.5°	257.5	257.6	257.6	257.6	257.7	257.4	256.8	256.2	255.7	255.1	254.3
110°	290.5	290.8	290.9	291.1	291.3	291.1	290.5	290.0	289.4	288.8	288.3



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	322.9	323.2	323.6	323.9	324.3	324.3	324.0	323.7	323.5	323.2	322.4
115°	373.9	374.1	374.3	374.4	374.7	374.9	375.1	375.2	375.5	375.7	375.2
117.5°	423.8	424.6	425.3	426.0	426.8	427.1	427.0	426.8	426.7	426.5	426.2
120°	458.1	458.9	459.7	460.5	461.2	461.6	461.6	461.6	461.6	461.6	461.4
122.5°	492.6	493.2	493.8	494.4	495.0	495.3	495.5	495.7	495.8	495.9	495.5
125°	544.2	544.3	544.5	544.7	544.8	545.2	545.5	546.0	546.3	546.7	546.5
127.5°	593.7	594.0	594.3	594.8	595.1	595.5	595.6	595.8	596.0	596.2	596.0
130°	626.6	627.0	627.4	627.8	628.2	628.4	628.6	628.8	629.0	629.2	628.8
132.5°	657.5	658.1	658.7	659.2	659.7	660.0	660.3	660.5	660.6	660.8	660.9
135°	705.7	706.5	707.2	708.0	708.8	709.1	709.1	709.1	709.1	709.1	708.9
137.5°	752.9	753.8	754.8	755.7	756.6	757.0	756.7	756.6	756.3	756.0	755.7
140°	783.1	784.0	785.0	785.9	786.9	787.2	786.8	786.4	786.0	785.7	785.1
142.5°	811.9	813.0	813.9	814.9	815.8	816.1	815.9	815.7	815.5	815.2	814.5
145°	855.3	855.8	856.4	857.0	857.6	857.9	857.9	857.9	857.9	857.9	857.3
147.5°	892.3	893.5	894.8	896.1	897.4	897.9	897.4	896.9	896.5	896.0	895.5
150°	919.7	920.2	920.5	920.9	921.3	921.4	921.4	921.4	921.4	921.4	920.7
152.5°	942.5	943.1	943.8	944.5	945.2	945.3	944.9	944.4	943.9	943.5	943.1
155°	974.7	975.7	976.6	977.7	978.6	978.7	977.9	977.1	976.4	975.6	975.4
157.5°	1001.8	1003.0	1004.3	1005.6	1006.8	1007.0	1006.3	1005.5	1004.8	1004.0	1003.8
160°	1020.3	1021.3	1022.3	1023.2	1024.2	1024.2	1023.5	1022.7	1021.9	1021.1	1021.0
162.5°	1036.1	1037.2	1038.4	1039.5	1040.6	1040.7	1039.7	1038.8	1037.9	1037.0	1037.0
165°	1057.3	1058.4	1059.5	1060.8	1061.9	1062.0	1061.3	1060.5	1059.8	1059.0	1058.8
167.5°	1074.1	1075.3	1076.5	1077.7	1078.8	1078.9	1077.7	1076.6	1075.5	1074.3	1074.3
170°	1083.1	1084.4	1085.7	1087.1	1088.4	1088.5	1087.4	1086.2	1085.1	1083.9	1083.9
172.5°	1090.6	1091.8	1093.0	1094.2	1095.4	1095.4	1094.2	1093.1	1091.9	1090.8	1090.8
175°	1097.7	1099.0	1100.4	1101.7	1103.0	1103.1	1102.0	1100.9	1099.7	1098.5	1098.5
177.5°	1101.8	1102.9	1104.0	1105.0	1106.1	1106.1	1105.3	1104.3	1103.5	1102.5	1102.7
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	792.8	791.0	788.9	785.2	780.8	778.4	774.8	772.4	767.7	763.8	759.6
5°	833.0	824.6	816.7	806.6	795.5	788.2	779.7	770.3	760.4	750.3	739.2
7.5°	874.7	859.7	843.3	825.7	808.6	792.7	777.6	762.8	748.9	732.1	717.9
10°	902.8	883.7	863.5	839.6	816.4	796.1	775.5	757.5	739.2	719.5	702.2
12.5°	930.7	905.4	876.8	850.6	822.7	798.2	774.0	751.0	728.0	706.2	686.0
15°	950.5	928.2	901.7	864.4	833.0	799.4	767.3	737.5	709.7	685.5	660.0
17.5°	963.5	934.9	906.4	870.6	829.5	791.8	755.4	721.4	690.1	659.4	634.8
20°	965.9	936.4	906.6	871.7	829.5	786.3	750.0	709.1	675.4	643.7	613.5
22.5°	965.1	931.7	899.3	863.2	822.2	782.4	738.5	696.8	660.2	629.0	597.6
25°	957.7	922.0	881.5	845.2	804.6	762.4	717.9	674.8	637.5	601.8	570.8
27.5°	951.5	905.3	859.4	817.0	777.8	739.2	696.6	652.4	611.1	574.9	545.6
30°	943.9	893.2	841.5	797.4	757.2	719.5	679.3	636.2	593.0	557.7	526.2
32.5°	937.1	878.0	823.5	775.4	732.9	696.3	659.2	618.1	575.8	539.8	508.5
35°	924.0	855.7	793.2	738.8	693.4	655.8	624.7	586.4	547.5	512.8	482.8
37.5°	907.3	826.2	759.1	702.2	652.4	612.8	583.8	554.5	517.1	483.7	456.5
40°	894.2	805.3	734.3	676.1	624.4	583.2	556.4	528.6	497.5	466.4	437.6
42.5°	877.7	786.4	709.1	646.5	595.4	555.2	527.0	503.4	476.0	447.0	420.3
45°	847.5	752.3	668.6	601.2	549.5	509.9	480.8	463.1	442.6	415.1	392.5
47.5°	802.9	711.3	624.7	555.1	501.8	465.1	437.8	420.9	406.4	386.0	365.5
50°	763.4	680.6	593.0	524.0	470.6	433.7	408.5	393.1	380.7	365.0	347.7
52.5°	719.2	642.1	561.9	493.6	440.8	404.4	379.7	366.2	355.9	344.6	327.5
55°	648.9	583.5	508.9	444.2	395.5	359.8	338.2	326.4	317.9	309.4	298.9
57.5°	571.5	520.4	454.3	395.1	350.3	317.8	297.6	286.2	279.6	275.2	269.1
60°	517.1	473.3	416.4	362.4	318.6	289.8	270.2	261.3	255.8	252.2	247.6
62.5°	466.6	430.6	377.9	328.6	290.3	263.1	245.6	237.0	231.7	230.0	226.1
65°	392.2	364.4	320.9	280.0	247.3	224.0	209.3	201.1	197.9	195.9	196.2
67.5°	318.8	301.9	267.0	232.1	206.0	186.5	174.7	168.4	166.8	164.2	164.1
70°	274.1	261.3	231.9	201.5	178.2	163.2	152.7	146.2	144.6	143.3	142.9
72.5°	234.5	223.4	197.9	173.5	152.7	139.4	130.8	126.8	124.2	123.4	123.3
75°	176.3	170.0	149.8	130.5	116.1	106.9	101.1	97.5	95.5	95.1	95.5
77.5°	125.4	119.9	107.0	93.3	84.3	77.3	72.3	71.1	68.9	69.0	68.6
80°	94.2	90.6	82.4	71.6	64.1	58.2	55.6	53.3	52.7	51.7	52.7
82.5°	68.3	64.4	58.9	52.0	45.8	42.3	39.6	38.9	38.5	38.1	38.2
85°	33.7	34.0	30.7	25.5	22.9	20.9	19.3	19.3	18.9	18.7	18.9
87.5°	13.7	12.9	11.6	10.6	9.0	7.8	7.3	7.2	6.7	6.8	7.4
90°	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9	2.4	3.9	5.4
92.5°	29.7	28.1	26.4	25.1	24.0	22.9	21.9	20.8	21.9	22.9	24.0
95°	62.3	60.4	58.5	57.4	57.0	56.7	56.2	55.9	56.2	56.7	57.0
97.5°	100.1	97.5	94.9	93.4	93.3	93.2	93.0	92.8	93.0	93.2	93.3
100°	126.6	124.1	121.6	120.4	120.4	120.4	120.4	120.4	120.4	120.4	120.4
102.5°	156.5	155.2	153.9	153.0	152.2	151.4	150.7	149.9	150.7	151.4	152.2
105°	203.1	202.0	200.9	199.8	198.9	197.9	196.9	196.0	196.9	197.9	198.9
107.5°	253.4	252.4	251.6	250.7	249.8	248.7	247.8	246.8	247.8	248.7	249.8
110°	287.7	287.1	286.5	285.8	284.8	283.9	282.9	282.0	282.9	283.9	284.8



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	321.8	321.1	320.3	319.7	319.2	318.7	318.2	317.7	318.2	318.7	319.2
115°	374.9	374.4	374.1	373.5	372.8	372.0	371.3	370.5	371.3	372.0	372.8
117.5°	425.9	425.5	425.2	424.8	424.5	424.1	423.8	423.4	423.8	424.1	424.5
120°	461.2	461.0	460.8	460.3	459.3	458.3	457.4	456.4	457.4	458.3	459.3
122.5°	495.0	494.5	494.0	493.6	493.3	492.9	492.6	492.2	492.6	492.9	493.3
125°	546.3	546.1	546.0	545.3	544.2	542.9	541.8	540.7	541.8	542.9	544.2
127.5°	595.7	595.6	595.3	594.9	594.2	593.6	592.9	592.3	592.9	593.6	594.2
130°	628.4	628.1	627.7	627.0	626.0	625.1	624.1	623.2	624.1	625.1	626.0
132.5°	661.0	661.1	661.2	660.4	658.8	657.3	655.7	654.1	655.7	657.3	658.8
135°	708.8	708.6	708.4	707.7	706.5	705.4	704.3	703.2	704.3	705.4	706.5
137.5°	755.3	754.8	754.4	753.6	752.5	751.4	750.3	749.2	750.3	751.4	752.5
140°	784.5	783.9	783.3	782.6	781.6	780.7	779.7	778.8	779.7	780.7	781.6
142.5°	813.8	813.0	812.4	811.6	810.7	809.9	809.2	808.3	809.2	809.9	810.7
145°	856.7	856.2	855.6	854.9	854.1	853.3	852.6	851.9	852.6	853.3	854.1
147.5°	895.1	894.7	894.2	893.7	893.4	892.9	892.5	892.1	892.5	892.9	893.4
150°	920.0	919.2	918.4	918.2	918.3	918.5	918.7	918.9	918.7	918.5	918.3
152.5°	942.9	942.5	942.3	941.9	941.7	941.4	941.2	940.9	941.2	941.4	941.7
155°	975.3	975.1	974.8	974.7	974.7	974.7	974.7	974.7	974.7	974.7	974.7
157.5°	1003.6	1003.4	1003.2	1003.3	1003.8	1004.2	1004.6	1005.0	1004.6	1004.2	1003.8
160°	1020.8	1020.6	1020.5	1020.6	1021.1	1021.7	1022.4	1022.9	1022.4	1021.7	1021.1
162.5°	1036.9	1036.9	1036.8	1037.1	1037.4	1037.8	1038.3	1038.7	1038.3	1037.8	1037.4
165°	1058.6	1058.4	1058.3	1058.3	1058.7	1059.1	1059.5	1059.9	1059.5	1059.1	1058.7
167.5°	1074.3	1074.3	1074.3	1074.7	1075.5	1076.2	1076.9	1077.7	1076.9	1076.2	1075.5
170°	1083.9	1083.9	1083.9	1084.3	1085.1	1085.8	1086.6	1087.4	1086.6	1085.8	1085.1
172.5°	1090.8	1090.8	1090.8	1091.2	1091.9	1092.7	1093.5	1094.2	1093.5	1092.7	1091.9
175°	1098.5	1098.5	1098.5	1098.9	1099.7	1100.4	1101.2	1102.0	1101.2	1100.4	1099.7
177.5°	1102.8	1102.9	1103.1	1103.5	1104.1	1104.7	1105.4	1106.0	1105.4	1104.7	1104.1
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	757.2	754.3	752.0	746.7	743.9	739.9	736.8	740.2	736.6	738.1	735.8
5°	733.7	724.4	717.9	708.4	700.3	692.8	687.2	686.2	683.5	682.3	678.4
7.5°	705.2	693.8	682.5	670.1	659.6	649.0	642.1	636.5	632.8	627.9	624.6
10°	688.5	673.1	660.0	645.0	631.9	620.4	611.3	606.7	602.4	596.2	594.0
12.5°	667.8	651.9	635.9	619.8	607.3	594.5	586.7	579.8	576.9	569.8	569.1
15°	643.0	619.1	603.5	587.1	569.7	559.3	552.8	545.3	542.0	537.1	533.5
17.5°	613.5	592.1	572.5	555.6	540.7	531.9	523.7	518.6	513.0	509.8	503.9
20°	592.0	571.7	552.1	534.1	522.6	512.6	506.0	501.1	495.2	493.5	487.7
22.5°	573.9	551.6	532.7	517.6	505.1	493.7	486.6	483.3	479.2	474.2	473.0
25°	544.6	521.3	505.3	490.3	479.1	468.7	463.8	459.5	455.6	452.0	450.7
27.5°	519.2	498.4	479.4	465.8	456.2	446.6	442.3	437.1	434.2	431.4	427.8
30°	501.4	480.2	463.5	450.4	439.9	431.4	426.8	423.3	420.6	418.0	416.0
32.5°	483.1	463.4	447.2	434.5	424.0	417.6	413.5	411.0	408.0	404.9	402.4
35°	458.9	437.3	421.6	410.4	402.3	397.4	392.8	390.5	387.3	387.3	384.6
37.5°	431.6	412.9	399.1	388.9	381.6	377.2	372.3	370.7	368.6	367.2	366.4
40°	415.3	398.0	385.0	374.8	367.0	363.3	359.5	356.8	355.5	353.9	353.3
42.5°	398.6	382.1	369.5	360.2	353.4	350.3	346.6	344.8	342.2	340.0	339.7
45°	373.2	357.1	345.7	338.2	332.3	328.7	326.4	322.5	321.2	318.6	318.2
47.5°	349.0	333.6	322.4	316.2	311.1	308.2	304.5	300.7	299.1	297.8	297.7
50°	331.0	316.9	306.4	300.6	295.7	291.4	287.8	285.2	284.2	284.2	284.9
52.5°	312.7	300.7	291.8	284.6	280.0	275.4	272.2	270.5	269.1	270.6	271.8
55°	285.9	273.8	267.3	260.4	255.8	250.6	248.9	248.2	247.3	249.9	251.2
57.5°	257.4	249.0	241.3	234.5	230.4	227.4	225.2	224.8	226.6	227.8	232.1
60°	239.4	229.6	222.7	217.5	212.6	210.6	210.0	209.3	210.6	214.2	219.8
62.5°	219.6	211.5	204.1	200.3	196.7	193.4	193.2	193.6	196.2	200.4	206.0
65°	190.4	183.5	178.6	174.0	171.1	169.1	169.8	171.1	174.0	179.6	185.8
67.5°	160.7	156.0	151.6	147.9	145.1	145.1	145.8	147.7	151.2	157.6	163.2
70°	141.6	136.4	132.8	131.1	128.9	127.6	129.5	132.8	135.7	141.6	146.5
72.5°	122.5	118.0	115.3	114.2	113.1	112.1	112.8	116.3	120.3	126.2	131.9
75°	94.2	92.6	90.6	89.3	88.3	88.9	89.6	92.9	96.2	102.4	108.9
77.5°	68.8	67.1	65.9	65.5	65.0	65.3	67.2	69.6	72.8	77.3	82.3
80°	52.0	51.3	50.7	50.4	50.4	50.7	53.3	54.9	57.9	62.2	66.0
82.5°	37.9	37.5	37.4	37.3	37.5	37.6	39.2	41.3	43.7	47.0	50.4
85°	20.0	19.3	20.3	20.6	20.0	20.9	21.6	22.9	23.8	25.5	27.1
87.5°	7.9	8.8	8.8	9.3	9.6	10.3	10.2	11.5	12.2	12.9	12.8
90°	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7	16.6	17.6	18.3
92.5°	25.1	26.4	28.1	29.7	31.3	33.0	34.3	35.6	36.8	38.1	38.9
95°	57.4	58.5	60.4	62.3	64.3	66.2	67.5	68.9	70.2	71.5	72.4
97.5°	93.4	94.9	97.5	100.1	102.7	105.4	106.7	107.9	109.2	110.5	111.2
100°	120.4	121.6	124.1	126.6	129.1	131.5	133.2	134.9	136.6	138.4	139.5
102.5°	153.0	153.9	155.2	156.5	157.7	159.0	160.9	162.7	164.6	166.5	167.7
105°	199.8	200.9	202.0	203.1	204.3	205.4	206.6	207.8	208.9	210.0	210.9
107.5°	250.7	251.6	252.4	253.4	254.3	255.1	255.7	256.2	256.8	257.4	257.7
110°	285.8	286.5	287.1	287.7	288.3	288.8	289.4	290.0	290.5	291.1	291.3



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	319.7	320.3	321.1	321.8	322.4	323.2	323.5	323.7	324.0	324.3	324.3
115°	373.5	374.1	374.4	374.9	375.2	375.7	375.5	375.2	375.1	374.9	374.7
117.5°	424.8	425.2	425.5	425.9	426.2	426.5	426.7	426.8	427.0	427.1	426.8
120°	460.3	460.8	461.0	461.2	461.4	461.6	461.6	461.6	461.6	461.6	461.2
122.5°	493.6	494.0	494.5	495.0	495.5	495.9	495.8	495.7	495.5	495.3	495.0
125°	545.3	546.0	546.1	546.3	546.5	546.7	546.3	546.0	545.5	545.2	544.8
127.5°	594.9	595.3	595.6	595.7	596.0	596.2	596.0	595.8	595.6	595.5	595.1
130°	627.0	627.7	628.1	628.4	628.8	629.2	629.0	628.8	628.6	628.4	628.2
132.5°	660.4	661.2	661.1	661.0	660.9	660.8	660.6	660.5	660.3	660.0	659.7
135°	707.7	708.4	708.6	708.8	708.9	709.1	709.1	709.1	709.1	709.1	708.8
137.5°	753.6	754.4	754.8	755.3	755.7	756.0	756.3	756.6	756.7	757.0	756.6
140°	782.6	783.3	783.9	784.5	785.1	785.7	786.0	786.4	786.8	787.2	786.9
142.5°	811.6	812.4	813.0	813.8	814.5	815.2	815.5	815.7	815.9	816.1	815.8
145°	854.9	855.6	856.2	856.7	857.3	857.9	857.9	857.9	857.9	857.9	857.6
147.5°	893.7	894.2	894.7	895.1	895.5	896.0	896.5	896.9	897.4	897.9	897.4
150°	918.2	918.4	919.2	920.0	920.7	921.4	921.4	921.4	921.4	921.4	921.3
152.5°	941.9	942.3	942.5	942.9	943.1	943.5	943.9	944.4	944.9	945.3	945.2
155°	974.7	974.8	975.1	975.3	975.4	975.6	976.4	977.1	977.9	978.7	978.6
157.5°	1003.3	1003.2	1003.4	1003.6	1003.8	1004.0	1004.8	1005.5	1006.3	1007.0	1006.8
160°	1020.6	1020.5	1020.6	1020.8	1021.0	1021.1	1021.9	1022.7	1023.5	1024.2	1024.2
162.5°	1037.1	1036.8	1036.9	1036.9	1037.0	1037.0	1037.9	1038.8	1039.7	1040.7	1040.6
165°	1058.3	1058.3	1058.4	1058.6	1058.8	1059.0	1059.8	1060.5	1061.3	1062.0	1061.9
167.5°	1074.7	1074.3	1074.3	1074.3	1074.3	1074.3	1075.5	1076.6	1077.7	1078.9	1078.8
170°	1084.3	1083.9	1083.9	1083.9	1083.9	1083.9	1085.1	1086.2	1087.4	1088.5	1088.4
172.5°	1091.2	1090.8	1090.8	1090.8	1090.8	1090.8	1091.9	1093.1	1094.2	1095.4	1095.4
175°	1098.9	1098.5	1098.5	1098.5	1098.5	1098.5	1099.7	1100.9	1102.0	1103.1	1103.0
177.5°	1103.5	1103.1	1102.9	1102.8	1102.7	1102.5	1103.5	1104.3	1105.3	1106.1	1106.1
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	734.2	736.1	734.5	736.6	734.5	736.1	734.2	735.8	738.1	736.6	740.2
5°	676.7	673.7	675.7	674.4	675.7	673.7	676.7	678.4	682.3	683.5	686.2
7.5°	623.6	620.8	617.6	616.0	617.6	620.8	623.6	624.6	627.9	632.8	636.5
10°	590.4	586.8	586.4	584.2	586.4	586.8	590.4	594.0	596.2	602.4	606.7
12.5°	566.0	562.7	559.0	558.0	559.0	562.7	566.0	569.1	569.8	576.9	579.8
15°	531.5	528.9	526.6	528.6	526.6	528.9	531.5	533.5	537.1	542.0	545.3
17.5°	502.7	500.6	500.2	497.8	500.2	500.6	502.7	503.9	509.8	513.0	518.6
20°	484.7	483.1	483.7	479.5	483.7	483.1	484.7	487.7	493.5	495.2	501.1
22.5°	470.4	467.1	466.7	465.9	466.7	467.1	470.4	473.0	474.2	479.2	483.3
25°	447.8	446.2	444.5	446.2	444.5	446.2	447.8	450.7	452.0	455.6	459.5
27.5°	428.1	426.1	425.7	425.9	425.7	426.1	428.1	427.8	431.4	434.2	437.1
30°	416.0	412.8	413.1	412.8	413.1	412.8	416.0	416.0	418.0	420.6	423.3
32.5°	402.9	400.7	400.3	399.7	400.3	400.7	402.9	402.4	404.9	408.0	411.0
35°	383.7	383.7	382.0	382.0	382.0	383.7	383.7	384.6	387.3	387.3	390.5
37.5°	365.5	365.2	364.2	364.4	364.2	365.2	365.5	366.4	367.2	368.6	370.7
40°	351.9	351.6	350.6	348.6	350.6	351.6	351.9	353.3	353.9	355.5	356.8
42.5°	338.9	337.8	337.3	336.7	337.3	337.8	338.9	339.7	340.0	342.2	344.8
45°	318.2	318.2	317.6	317.3	317.6	318.2	318.2	318.2	318.6	321.2	322.5
47.5°	298.3	298.9	300.1	299.9	300.1	298.9	298.3	297.7	297.8	299.1	300.7
50°	286.2	286.5	287.5	287.8	287.5	286.5	286.2	284.9	284.2	284.2	285.2
52.5°	272.9	274.7	276.0	275.8	276.0	274.7	272.9	271.8	270.6	269.1	270.5
55°	254.2	256.4	258.7	259.1	258.7	256.4	254.2	251.2	249.9	247.3	248.2
57.5°	235.7	238.8	241.3	242.0	241.3	238.8	235.7	232.1	227.8	226.6	224.8
60°	223.1	227.3	230.2	231.6	230.2	227.3	223.1	219.8	214.2	210.6	209.3
62.5°	211.0	215.8	218.8	219.0	218.8	215.8	211.0	206.0	200.4	196.2	193.6
65°	191.3	196.2	198.9	200.8	198.9	196.2	191.3	185.8	179.6	174.0	171.1
67.5°	170.1	175.0	178.0	179.5	178.0	175.0	170.1	163.2	157.6	151.2	147.7
70°	154.7	159.6	163.5	164.9	163.5	159.6	154.7	146.5	141.6	135.7	132.8
72.5°	139.6	143.9	147.1	148.6	147.1	143.9	139.6	131.9	126.2	120.3	116.3
75°	113.1	119.1	122.0	123.6	122.0	119.1	113.1	108.9	102.4	96.2	92.9
77.5°	87.3	92.6	94.4	95.2	94.4	92.6	87.3	82.3	77.3	72.8	69.6
80°	70.0	73.3	75.6	75.9	75.6	73.3	70.0	66.0	62.2	57.9	54.9
82.5°	53.8	56.5	57.3	58.1	57.3	56.5	53.8	50.4	47.0	43.7	41.3
85°	29.4	30.7	31.1	30.7	31.1	30.7	29.4	27.1	25.5	23.8	22.9
87.5°	13.4	13.3	13.4	14.0	13.4	13.3	13.4	12.8	12.9	12.2	11.5
90°	18.9	19.5	20.1	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7
92.5°	39.3	39.7	40.1	40.6	40.1	39.7	39.3	38.9	38.1	36.8	35.6
95°	72.8	73.2	73.5	74.0	73.5	73.2	72.8	72.4	71.5	70.2	68.9
97.5°	111.4	111.7	111.8	112.1	111.8	111.7	111.4	111.2	110.5	109.2	107.9
100°	139.8	140.2	140.6	140.9	140.6	140.2	139.8	139.5	138.4	136.6	134.9
102.5°	168.2	168.8	169.4	169.9	169.4	168.8	168.2	167.7	166.5	164.6	162.7
105°	211.5	212.1	212.6	213.2	212.6	212.1	211.5	210.9	210.0	208.9	207.8
107.5°	257.6	257.6	257.6	257.5	257.6	257.6	257.6	257.7	257.4	256.8	256.2
110°	291.1	290.9	290.8	290.5	290.8	290.9	291.1	291.3	291.1	290.5	290.0



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	323.9	323.6	323.2	322.9	323.2	323.6	323.9	324.3	324.3	324.0	323.7
115°	374.4	374.3	374.1	373.9	374.1	374.3	374.4	374.7	374.9	375.1	375.2
117.5°	426.0	425.3	424.6	423.8	424.6	425.3	426.0	426.8	427.1	427.0	426.8
120°	460.5	459.7	458.9	458.1	458.9	459.7	460.5	461.2	461.6	461.6	461.6
122.5°	494.4	493.8	493.2	492.6	493.2	493.8	494.4	495.0	495.3	495.5	495.7
125°	544.7	544.5	544.3	544.2	544.3	544.5	544.7	544.8	545.2	545.5	546.0
127.5°	594.8	594.3	594.0	593.7	594.0	594.3	594.8	595.1	595.5	595.6	595.8
130°	627.8	627.4	627.0	626.6	627.0	627.4	627.8	628.2	628.4	628.6	628.8
132.5°	659.2	658.7	658.1	657.5	658.1	658.7	659.2	659.7	660.0	660.3	660.5
135°	708.0	707.2	706.5	705.7	706.5	707.2	708.0	708.8	709.1	709.1	709.1
137.5°	755.7	754.8	753.8	752.9	753.8	754.8	755.7	756.6	757.0	756.7	756.6
140°	785.9	785.0	784.0	783.1	784.0	785.0	785.9	786.9	787.2	786.8	786.4
142.5°	814.9	813.9	813.0	811.9	813.0	813.9	814.9	815.8	816.1	815.9	815.7
145°	857.0	856.4	855.8	855.3	855.8	856.4	857.0	857.6	857.9	857.9	857.9
147.5°	896.1	894.8	893.5	892.3	893.5	894.8	896.1	897.4	897.9	897.4	896.9
150°	920.9	920.5	920.2	919.7	920.2	920.5	920.9	921.3	921.4	921.4	921.4
152.5°	944.5	943.8	943.1	942.5	943.1	943.8	944.5	945.2	945.3	944.9	944.4
155°	977.7	976.6	975.7	974.7	975.7	976.6	977.7	978.6	978.7	977.9	977.1
157.5°	1005.6	1004.3	1003.0	1001.8	1003.0	1004.3	1005.6	1006.8	1007.0	1006.3	1005.5
160°	1023.2	1022.3	1021.3	1020.3	1021.3	1022.3	1023.2	1024.2	1024.2	1023.5	1022.7
162.5°	1039.5	1038.4	1037.2	1036.1	1037.2	1038.4	1039.5	1040.6	1040.7	1039.7	1038.8
165°	1060.8	1059.5	1058.4	1057.3	1058.4	1059.5	1060.8	1061.9	1062.0	1061.3	1060.5
167.5°	1077.7	1076.5	1075.3	1074.1	1075.3	1076.5	1077.7	1078.8	1078.9	1077.7	1076.6
170°	1087.1	1085.7	1084.4	1083.1	1084.4	1085.7	1087.1	1088.4	1088.5	1087.4	1086.2
172.5°	1094.2	1093.0	1091.8	1090.6	1091.8	1093.0	1094.2	1095.4	1095.4	1094.2	1093.1
175°	1101.7	1100.4	1099.0	1097.7	1099.0	1100.4	1101.7	1103.0	1103.1	1102.0	1100.9
177.5°	1105.0	1104.0	1102.9	1101.8	1102.9	1104.0	1105.0	1106.1	1106.1	1105.3	1104.3
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	736.8	739.9	743.9	746.7	752.0	754.3	757.2	759.6	763.8	767.7	772.4
5°	687.2	692.8	700.3	708.4	717.9	724.4	733.7	739.2	750.3	760.4	770.3
7.5°	642.1	649.0	659.6	670.1	682.5	693.8	705.2	717.9	732.1	748.9	762.8
10°	611.3	620.4	631.9	645.0	660.0	673.1	688.5	702.2	719.5	739.2	757.5
12.5°	586.7	594.5	607.3	619.8	635.9	651.9	667.8	686.0	706.2	728.0	751.0
15°	552.8	559.3	569.7	587.1	603.5	619.1	643.0	660.0	685.5	709.7	737.5
17.5°	523.7	531.9	540.7	555.6	572.5	592.1	613.5	634.8	659.4	690.1	721.4
20°	506.0	512.6	522.6	534.1	552.1	571.7	592.0	613.5	643.7	675.4	709.1
22.5°	486.6	493.7	505.1	517.6	532.7	551.6	573.9	597.6	629.0	660.2	696.8
25°	463.8	468.7	479.1	490.3	505.3	521.3	544.6	570.8	601.8	637.5	674.8
27.5°	442.3	446.6	456.2	465.8	479.4	498.4	519.2	545.6	574.9	611.1	652.4
30°	426.8	431.4	439.9	450.4	463.5	480.2	501.4	526.2	557.7	593.0	636.2
32.5°	413.5	417.6	424.0	434.5	447.2	463.4	483.1	508.5	539.8	575.8	618.1
35°	392.8	397.4	402.3	410.4	421.6	437.3	458.9	482.8	512.8	547.5	586.4
37.5°	372.3	377.2	381.6	388.9	399.1	412.9	431.6	456.5	483.7	517.1	554.5
40°	359.5	363.3	367.0	374.8	385.0	398.0	415.3	437.6	466.4	497.5	528.6
42.5°	346.6	350.3	353.4	360.2	369.5	382.1	398.6	420.3	447.0	476.0	503.4
45°	326.4	328.7	332.3	338.2	345.7	357.1	373.2	392.5	415.1	442.6	463.1
47.5°	304.5	308.2	311.1	316.2	322.4	333.6	349.0	365.5	386.0	406.4	420.9
50°	287.8	291.4	295.7	300.6	306.4	316.9	331.0	347.7	365.0	380.7	393.1
52.5°	272.2	275.4	280.0	284.6	291.8	300.7	312.7	327.5	344.6	355.9	366.2
55°	248.9	250.6	255.8	260.4	267.3	273.8	285.9	298.9	309.4	317.9	326.4
57.5°	225.2	227.4	230.4	234.5	241.3	249.0	257.4	269.1	275.2	279.6	286.2
60°	210.0	210.6	212.6	217.5	222.7	229.6	239.4	247.6	252.2	255.8	261.3
62.5°	193.2	193.4	196.7	200.3	204.1	211.5	219.6	226.1	230.0	231.7	237.0
65°	169.8	169.1	171.1	174.0	178.6	183.5	190.4	196.2	195.9	197.9	201.1
67.5°	145.8	145.1	145.1	147.9	151.6	156.0	160.7	164.1	164.2	166.8	168.4
70°	129.5	127.6	128.9	131.1	132.8	136.4	141.6	142.9	143.3	144.6	146.2
72.5°	112.8	112.1	113.1	114.2	115.3	118.0	122.5	123.3	123.4	124.2	126.8
75°	89.6	88.9	88.3	89.3	90.6	92.6	94.2	95.5	95.1	95.5	97.5
77.5°	67.2	65.3	65.0	65.5	65.9	67.1	68.8	68.6	69.0	68.9	71.1
80°	53.3	50.7	50.4	50.4	50.7	51.3	52.0	52.7	51.7	52.7	53.3
82.5°	39.2	37.6	37.5	37.3	37.4	37.5	37.9	38.2	38.1	38.5	38.9
85°	21.6	20.9	20.0	20.6	20.3	19.3	20.0	18.9	18.7	18.9	19.3
87.5°	10.2	10.3	9.6	9.3	8.8	8.8	7.9	7.4	6.8	6.7	7.2
90°	14.7	13.8	12.4	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9
92.5°	34.3	33.0	31.3	29.7	28.1	26.4	25.1	24.0	22.9	21.9	20.8
95°	67.5	66.2	64.3	62.3	60.4	58.5	57.4	57.0	56.7	56.2	55.9
97.5°	106.7	105.4	102.7	100.1	97.5	94.9	93.4	93.3	93.2	93.0	92.8
100°	133.2	131.5	129.1	126.6	124.1	121.6	120.4	120.4	120.4	120.4	120.4
102.5°	160.9	159.0	157.7	156.5	155.2	153.9	153.0	152.2	151.4	150.7	149.9
105°	206.6	205.4	204.3	203.1	202.0	200.9	199.8	198.9	197.9	196.9	196.0
107.5°	255.7	255.1	254.3	253.4	252.4	251.6	250.7	249.8	248.7	247.8	246.8
110°	289.4	288.8	288.3	287.7	287.1	286.5	285.8	284.8	283.9	282.9	282.0



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	323.5	323.2	322.4	321.8	321.1	320.3	319.7	319.2	318.7	318.2	317.7
115°	375.5	375.7	375.2	374.9	374.4	374.1	373.5	372.8	372.0	371.3	370.5
117.5°	426.7	426.5	426.2	425.9	425.5	425.2	424.8	424.5	424.1	423.8	423.4
120°	461.6	461.6	461.4	461.2	461.0	460.8	460.3	459.3	458.3	457.4	456.4
122.5°	495.8	495.9	495.5	495.0	494.5	494.0	493.6	493.3	492.9	492.6	492.2
125°	546.3	546.7	546.5	546.3	546.1	546.0	545.3	544.2	542.9	541.8	540.7
127.5°	596.0	596.2	596.0	595.7	595.6	595.3	594.9	594.2	593.6	592.9	592.3
130°	629.0	629.2	628.8	628.4	628.1	627.7	627.0	626.0	625.1	624.1	623.2
132.5°	660.6	660.8	660.9	661.0	661.1	661.2	660.4	658.8	657.3	655.7	654.1
135°	709.1	709.1	708.9	708.8	708.6	708.4	707.7	706.5	705.4	704.3	703.2
137.5°	756.3	756.0	755.7	755.3	754.8	754.4	753.6	752.5	751.4	750.3	749.2
140°	786.0	785.7	785.1	784.5	783.9	783.3	782.6	781.6	780.7	779.7	778.8
142.5°	815.5	815.2	814.5	813.8	813.0	812.4	811.6	810.7	809.9	809.2	808.3
145°	857.9	857.9	857.3	856.7	856.2	855.6	854.9	854.1	853.3	852.6	851.9
147.5°	896.5	896.0	895.5	895.1	894.7	894.2	893.7	893.4	892.9	892.5	892.1
150°	921.4	921.4	920.7	920.0	919.2	918.4	918.2	918.3	918.5	918.7	918.9
152.5°	943.9	943.5	943.1	942.9	942.5	942.3	941.9	941.7	941.4	941.2	940.9
155°	976.4	975.6	975.4	975.3	975.1	974.8	974.7	974.7	974.7	974.7	974.7
157.5°	1004.8	1004.0	1003.8	1003.6	1003.4	1003.2	1003.3	1003.8	1004.2	1004.6	1005.0
160°	1021.9	1021.1	1021.0	1020.8	1020.6	1020.5	1020.6	1021.1	1021.7	1022.4	1022.9
162.5°	1037.9	1037.0	1037.0	1036.9	1036.9	1036.8	1037.1	1037.4	1037.8	1038.3	1038.7
165°	1059.8	1059.0	1058.8	1058.6	1058.4	1058.3	1058.3	1058.7	1059.1	1059.5	1059.9
167.5°	1075.5	1074.3	1074.3	1074.3	1074.3	1074.3	1074.7	1075.5	1076.2	1076.9	1077.7
170°	1085.1	1083.9	1083.9	1083.9	1083.9	1083.9	1084.3	1085.1	1085.8	1086.6	1087.4
172.5°	1091.9	1090.8	1090.8	1090.8	1090.8	1090.8	1091.2	1091.9	1092.7	1093.5	1094.2
175°	1099.7	1098.5	1098.5	1098.5	1098.5	1098.5	1098.9	1099.7	1100.4	1101.2	1102.0
177.5°	1103.5	1102.5	1102.7	1102.8	1102.9	1103.1	1103.5	1104.1	1104.7	1105.4	1106.0
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	774.8	778.4	780.8	785.2	788.9	791.0	792.8	794.4	796.3	797.8	802.3
5°	779.7	788.2	795.5	806.6	816.7	824.6	833.0	840.6	846.8	855.7	862.5
7.5°	777.6	792.7	808.6	825.7	843.3	859.7	874.7	888.8	901.6	917.0	930.5
10°	775.5	796.1	816.4	839.6	863.5	883.7	902.8	922.0	936.1	955.7	972.4
12.5°	774.0	798.2	822.7	850.6	876.8	905.4	930.7	944.8	966.2	981.9	1001.7
15°	767.3	799.4	833.0	864.4	901.7	928.2	950.5	977.9	997.9	1017.9	1039.4
17.5°	755.4	791.8	829.5	870.6	906.4	934.9	963.5	990.0	1013.8	1040.5	1067.5
20°	750.0	786.3	829.5	871.7	906.6	936.4	965.9	995.0	1021.1	1055.5	1086.5
22.5°	738.5	782.4	822.2	863.2	899.3	931.7	965.1	998.1	1032.9	1071.7	1110.6
25°	717.9	762.4	804.6	845.2	881.5	922.0	957.7	1001.9	1046.3	1097.7	1146.1
27.5°	696.6	739.2	777.8	817.0	859.4	905.3	951.5	1001.6	1059.9	1124.6	1193.0
30°	679.3	719.5	757.2	797.4	841.5	893.2	943.9	1003.5	1070.8	1143.8	1224.9
32.5°	659.2	696.3	732.9	775.4	823.5	878.0	937.1	1002.4	1083.4	1166.3	1249.7
35°	624.7	655.8	693.4	738.8	793.2	855.7	924.0	1001.2	1094.1	1189.2	1259.6
37.5°	583.8	612.8	652.4	702.2	759.1	826.2	907.3	998.8	1097.5	1173.4	1196.1
40°	556.4	583.2	624.4	676.1	734.3	805.3	894.2	991.0	1086.5	1135.0	1116.3
42.5°	527.0	555.2	595.4	646.5	709.1	786.4	877.7	974.6	1054.6	1072.9	1008.5
45°	480.8	509.9	549.5	601.2	668.6	752.3	847.5	935.4	981.5	948.5	848.8
47.5°	437.8	465.1	501.8	555.1	624.7	711.3	802.9	873.1	876.8	797.9	691.4
50°	408.5	433.7	470.6	524.0	593.0	680.6	763.4	818.6	793.8	704.6	602.2
52.5°	379.7	404.4	440.8	493.6	561.9	642.1	719.2	757.9	711.1	619.5	532.0
55°	338.2	359.8	395.5	444.2	508.9	583.5	648.9	662.3	601.5	511.2	440.2
57.5°	297.6	317.8	350.3	395.1	454.3	520.4	571.5	568.7	504.4	426.9	370.6
60°	270.2	289.8	318.6	362.4	416.4	473.3	517.1	506.6	442.9	376.2	328.7
62.5°	245.6	263.1	290.3	328.6	377.9	430.6	466.6	451.2	388.7	330.4	292.8
65°	209.3	224.0	247.3	280.0	320.9	364.4	392.2	372.2	318.9	273.5	243.3
67.5°	174.7	186.5	206.0	232.1	267.0	301.9	318.8	298.8	256.1	222.9	200.6
70°	152.7	163.2	178.2	201.5	231.9	261.3	274.1	256.1	219.5	191.0	175.0
72.5°	130.8	139.4	152.7	173.5	197.9	223.4	234.5	217.4	187.3	163.2	148.3
75°	101.1	106.9	116.1	130.5	149.8	170.0	176.3	161.3	142.0	124.0	114.2
77.5°	72.3	77.3	84.3	93.3	107.0	119.9	125.4	116.7	101.7	90.3	82.3
80°	55.6	58.2	64.1	71.6	82.4	90.6	94.2	88.6	78.2	69.7	63.5
82.5°	39.6	42.3	45.8	52.0	58.9	64.4	68.3	64.6	57.0	50.3	46.7
85°	19.3	20.9	22.9	25.5	30.7	34.0	33.7	31.4	28.4	25.8	23.8
87.5°	7.3	7.8	9.0	10.6	11.6	12.9	13.7	13.4	12.7	12.1	11.5
90°	2.4	3.9	5.4	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7
92.5°	21.9	22.9	24.0	25.1	26.4	28.1	29.7	31.3	33.0	34.3	35.6
95°	56.2	56.7	57.0	57.4	58.5	60.4	62.3	64.3	66.2	67.5	68.9
97.5°	93.0	93.2	93.3	93.4	94.9	97.5	100.1	102.7	105.4	106.7	107.9
100°	120.4	120.4	120.4	120.4	121.6	124.1	126.6	129.1	131.5	133.2	134.9
102.5°	150.7	151.4	152.2	153.0	153.9	155.2	156.5	157.7	159.0	160.9	162.7
105°	196.9	197.9	198.9	199.8	200.9	202.0	203.1	204.3	205.4	206.6	207.8
107.5°	247.8	248.7	249.8	250.7	251.6	252.4	253.4	254.3	255.1	255.7	256.2
110°	282.9	283.9	284.8	285.8	286.5	287.1	287.7	288.3	288.8	289.4	290.0



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.2	318.7	319.2	319.7	320.3	321.1	321.8	322.4	323.2	323.5	323.7
115°	371.3	372.0	372.8	373.5	374.1	374.4	374.9	375.2	375.7	375.5	375.2
117.5°	423.8	424.1	424.5	424.8	425.2	425.5	425.9	426.2	426.5	426.7	426.8
120°	457.4	458.3	459.3	460.3	460.8	461.0	461.2	461.4	461.6	461.6	461.6
122.5°	492.6	492.9	493.3	493.6	494.0	494.5	495.0	495.5	495.9	495.8	495.7
125°	541.8	542.9	544.2	545.3	546.0	546.1	546.3	546.5	546.7	546.3	546.0
127.5°	592.9	593.6	594.2	594.9	595.3	595.6	595.7	596.0	596.2	596.0	595.8
130°	624.1	625.1	626.0	627.0	627.7	628.1	628.4	628.8	629.2	629.0	628.8
132.5°	655.7	657.3	658.8	660.4	661.2	661.1	661.0	660.9	660.8	660.6	660.5
135°	704.3	705.4	706.5	707.7	708.4	708.6	708.8	708.9	709.1	709.1	709.1
137.5°	750.3	751.4	752.5	753.6	754.4	754.8	755.3	755.7	756.0	756.3	756.6
140°	779.7	780.7	781.6	782.6	783.3	783.9	784.5	785.1	785.7	786.0	786.4
142.5°	809.2	809.9	810.7	811.6	812.4	813.0	813.8	814.5	815.2	815.5	815.7
145°	852.6	853.3	854.1	854.9	855.6	856.2	856.7	857.3	857.9	857.9	857.9
147.5°	892.5	892.9	893.4	893.7	894.2	894.7	895.1	895.5	896.0	896.5	896.9
150°	918.7	918.5	918.3	918.2	918.4	919.2	920.0	920.7	921.4	921.4	921.4
152.5°	941.2	941.4	941.7	941.9	942.3	942.5	942.9	943.1	943.5	943.9	944.4
155°	974.7	974.7	974.7	974.7	974.8	975.1	975.3	975.4	975.6	976.4	977.1
157.5°	1004.6	1004.2	1003.8	1003.3	1003.2	1003.4	1003.6	1003.8	1004.0	1004.8	1005.5
160°	1022.4	1021.7	1021.1	1020.6	1020.5	1020.6	1020.8	1021.0	1021.1	1021.9	1022.7
162.5°	1038.3	1037.8	1037.4	1037.1	1036.8	1036.9	1036.9	1037.0	1037.0	1037.9	1038.8
165°	1059.5	1059.1	1058.7	1058.3	1058.3	1058.4	1058.6	1058.8	1059.0	1059.8	1060.5
167.5°	1076.9	1076.2	1075.5	1074.7	1074.3	1074.3	1074.3	1074.3	1074.3	1075.5	1076.6
170°	1086.6	1085.8	1085.1	1084.3	1083.9	1083.9	1083.9	1083.9	1083.9	1085.1	1086.2
172.5°	1093.5	1092.7	1091.9	1091.2	1090.8	1090.8	1090.8	1090.8	1090.8	1091.9	1093.1
175°	1101.2	1100.4	1099.7	1098.9	1098.5	1098.5	1098.5	1098.5	1098.5	1099.7	1100.9
177.5°	1105.4	1104.7	1104.1	1103.5	1103.1	1102.9	1102.8	1102.7	1102.5	1103.5	1104.3
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	805.9	808.0	812.4	810.9	813.0	814.0	815.1
5°	871.0	881.5	886.1	885.4	892.3	890.6	889.0
7.5°	944.5	955.5	961.7	969.3	973.8	974.0	977.9
10°	986.1	1000.5	1006.4	1014.6	1019.9	1022.8	1022.4
12.5°	1018.0	1029.3	1042.5	1046.5	1053.6	1057.3	1055.9
15°	1056.4	1074.4	1088.1	1095.0	1103.9	1106.5	1110.1
17.5°	1090.7	1114.8	1130.9	1152.2	1160.3	1165.2	1162.3
20°	1116.6	1148.3	1164.4	1189.9	1203.9	1211.5	1208.8
22.5°	1147.3	1181.6	1211.3	1233.3	1254.7	1264.9	1267.0
25°	1199.7	1246.8	1290.3	1319.4	1345.9	1352.1	1365.9
27.5°	1258.4	1313.9	1360.4	1390.9	1409.5	1416.3	1420.6
30°	1295.2	1350.5	1385.5	1405.1	1411.0	1410.3	1409.7
32.5°	1313.3	1347.9	1354.6	1349.1	1335.7	1324.2	1312.3
35°	1287.7	1261.9	1223.2	1173.5	1137.0	1099.9	1096.3
37.5°	1158.1	1075.5	1011.2	939.5	898.1	872.5	854.8
40°	1036.1	942.3	864.4	803.9	761.7	745.1	728.8
42.5°	903.8	814.1	745.1	694.6	662.9	644.4	631.4
45°	734.3	655.1	601.2	564.6	539.3	525.0	516.8
47.5°	601.7	543.1	497.3	470.9	453.5	442.3	442.3
50°	530.5	474.6	444.2	423.3	408.2	399.3	401.0
52.5°	467.4	425.7	399.7	382.1	371.0	365.6	365.4
55°	390.9	360.8	343.8	331.0	323.5	317.3	318.6
57.5°	334.3	308.9	297.6	287.0	281.7	279.2	275.7
60°	299.3	279.7	269.8	261.3	256.1	254.2	250.6
62.5°	268.1	252.7	243.1	236.2	231.5	230.8	228.0
65°	225.3	213.6	205.1	201.8	196.9	195.6	195.6
67.5°	185.8	177.4	170.7	167.7	165.6	165.9	164.3
70°	160.9	154.0	149.8	146.5	144.9	145.3	143.9
72.5°	140.8	133.1	129.4	127.4	125.3	126.1	125.6
75°	106.6	102.7	100.7	98.8	97.5	96.8	96.2
77.5°	78.3	74.8	73.4	72.2	72.4	70.9	72.1
80°	60.5	57.6	56.6	54.9	54.6	54.6	54.3
82.5°	44.3	42.6	41.9	40.6	40.0	40.5	39.6
85°	22.9	21.6	21.3	21.3	20.6	20.0	21.6
87.5°	11.7	10.8	11.0	10.8	10.9	10.8	10.4
90°	16.6	17.6	18.3	18.9	19.5	20.1	20.7
92.5°	36.8	38.1	38.9	39.3	39.7	40.1	40.6
95°	70.2	71.5	72.4	72.8	73.2	73.5	74.0
97.5°	109.2	110.5	111.2	111.4	111.7	111.8	112.1
100°	136.6	138.4	139.5	139.8	140.2	140.6	140.9
102.5°	164.6	166.5	167.7	168.2	168.8	169.4	169.9
105°	208.9	210.0	210.9	211.5	212.1	212.6	213.2
107.5°	256.8	257.4	257.7	257.6	257.6	257.6	257.5
110°	290.5	291.1	291.3	291.1	290.9	290.8	290.5



TEST NUMBER: P333188-935

CATALOG NUMBER: S125DIP-S610D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	324.0	324.3	324.3	323.9	323.6	323.2	322.9
115°	375.1	374.9	374.7	374.4	374.3	374.1	373.9
117.5°	427.0	427.1	426.8	426.0	425.3	424.6	423.8
120°	461.6	461.6	461.2	460.5	459.7	458.9	458.1
122.5°	495.5	495.3	495.0	494.4	493.8	493.2	492.6
125°	545.5	545.2	544.8	544.7	544.5	544.3	544.2
127.5°	595.6	595.5	595.1	594.8	594.3	594.0	593.7
130°	628.6	628.4	628.2	627.8	627.4	627.0	626.6
132.5°	660.3	660.0	659.7	659.2	658.7	658.1	657.5
135°	709.1	709.1	708.8	708.0	707.2	706.5	705.7
137.5°	756.7	757.0	756.6	755.7	754.8	753.8	752.9
140°	786.8	787.2	786.9	785.9	785.0	784.0	783.1
142.5°	815.9	816.1	815.8	814.9	813.9	813.0	811.9
145°	857.9	857.9	857.6	857.0	856.4	855.8	855.3
147.5°	897.4	897.9	897.4	896.1	894.8	893.5	892.3
150°	921.4	921.4	921.3	920.9	920.5	920.2	919.7
152.5°	944.9	945.3	945.2	944.5	943.8	943.1	942.5
155°	977.9	978.7	978.6	977.7	976.6	975.7	974.7
157.5°	1006.3	1007.0	1006.8	1005.6	1004.3	1003.0	1001.8
160°	1023.5	1024.2	1024.2	1023.2	1022.3	1021.3	1020.3
162.5°	1039.7	1040.7	1040.6	1039.5	1038.4	1037.2	1036.1
165°	1061.3	1062.0	1061.9	1060.8	1059.5	1058.4	1057.3
167.5°	1077.7	1078.9	1078.8	1077.7	1076.5	1075.3	1074.1
170°	1087.4	1088.5	1088.4	1087.1	1085.7	1084.4	1083.1
172.5°	1094.2	1095.4	1095.4	1094.2	1093.0	1091.8	1090.6
175°	1102.0	1103.1	1103.0	1101.7	1100.4	1099.0	1097.7
177.5°	1105.3	1106.1	1106.1	1105.0	1104.0	1102.9	1101.8
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6

(END OF REPORT)