

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333198-935

Luminaire Tested: **S125DIP-S610D1205U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333198-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1205U935-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5898.4 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	38	31
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	23
4	72	62	54	48	65	56	50	45	46	41	37	37	33	30	28	25	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	17	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4977	4977	4977	4977
5°	5763	4994	4372	4994
10°	6705	4968	3831	4968
15°	7422	4931	3534	4931
20°	8308	4874	3296	4874
25°	9733	4809	3180	4809
30°	10513	4744	3078	4744
35°	8643	4623	3012	4623
40°	6144	4457	2939	4457
45°	4720	4230	2898	4230
50°	4029	3950	2892	3950
55°	3587	3675	2917	3675
60°	3237	3375	2992	3375
65°	2989	3073	3069	3073
70°	2717	2761	3114	2761
75°	2400	2433	3084	2433
80°	2020	1982	2823	1982
85°	1601	1430	2275	1430



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	1.3
10°-20°	220.9	3.7
20°-30°	358.6	6.1
30°-40°	437.5	7.4
40°-50°	398.0	6.7
50°-60°	317.0	5.4
60°-70°	220.8	3.7
70°-80°	117.7	2.0
80°-90°	32.5	0.6
90°-100°	359.7	6.1
100°-110°	773.2	13.1
110°-120°	725.6	12.3
120°-130°	588.1	10.0
130°-140°	471.9	8.0
140°-150°	356.1	6.0
150°-160°	250.7	4.3
160°-170°	147.8	2.5
170°-180°	48.1	0.8
0°-30°	653.7	11.1
0°-40°	1091.2	18.5
0°-60°	1806.2	30.6
0°-90°	2177.2	36.9
90°-120°	1858.5	31.5
90°-150°	3274.7	55.5
90°-180°	3721.0	63.1
0°-180°	5898.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	771	771	771	771	771	
5°	889	770	674	770	889	90
15°	1110	738	529	738	1110	318
25°	1366	675	446	675	1366	624
35°	1096	586	382	586	1096	671
45°	517	463	317	463	517	414
55°	319	326	259	326	319	287
65°	196	201	201	201	196	194
75°	96	98	124	98	96	104
85°	22	19	31	19	22	25
90°	23	1	23	1	23	17
95°	235	33	235	33	235	333
105°	1326	113	1326	113	1326	1318
115°	1477	202	1477	202	1477	1443
125°	1164	280	1164	280	1164	1053
135°	966	328	966	328	966	749
145°	762	382	762	382	762	484
155°	639	436	639	436	639	298
165°	560	476	560	476	560	160
175°	503	495	503	495	503	49
180°	496	496	496	496	496	



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	815.1	814.0	813.0	810.9	812.4	808.0	805.9	802.3	797.8	796.3	794.4
5°	889.0	890.6	892.3	885.4	886.1	881.5	871.0	862.5	855.7	846.8	840.6
7.5°	977.9	974.0	973.8	969.3	961.7	955.5	944.5	930.5	917.0	901.6	888.8
10°	1022.4	1022.8	1019.9	1014.6	1006.4	1000.5	986.1	972.4	955.7	936.1	922.0
12.5°	1055.9	1057.3	1053.6	1046.5	1042.5	1029.3	1018.0	1001.7	981.9	966.2	944.8
15°	1110.1	1106.5	1103.9	1095.0	1088.1	1074.4	1056.4	1039.4	1017.9	997.9	977.9
17.5°	1162.3	1165.2	1160.3	1152.2	1130.9	1114.8	1090.7	1067.5	1040.5	1013.8	990.0
20°	1208.8	1211.5	1203.9	1189.9	1164.4	1148.3	1116.6	1086.5	1055.5	1021.1	995.0
22.5°	1267.0	1264.9	1254.7	1233.3	1211.3	1181.6	1147.3	1110.6	1071.7	1032.9	998.1
25°	1365.9	1352.1	1345.9	1319.4	1290.3	1246.8	1199.7	1146.1	1097.7	1046.3	1001.9
27.5°	1420.6	1416.3	1409.5	1390.9	1360.4	1313.9	1258.4	1193.0	1124.6	1059.9	1001.6
30°	1409.7	1410.3	1411.0	1405.1	1385.5	1350.5	1295.2	1224.9	1143.8	1070.8	1003.5
32.5°	1312.3	1324.2	1335.7	1349.1	1354.6	1347.9	1313.3	1249.7	1166.3	1083.4	1002.4
35°	1096.3	1099.9	1137.0	1173.5	1223.2	1261.9	1287.7	1259.6	1189.2	1094.1	1001.2
37.5°	854.8	872.5	898.1	939.5	1011.2	1075.5	1158.1	1196.1	1173.4	1097.5	998.8
40°	728.8	745.1	761.7	803.9	864.4	942.3	1036.1	1116.3	1135.0	1086.5	991.0
42.5°	631.4	644.4	662.9	694.6	745.1	814.1	903.8	1008.5	1072.9	1054.6	974.6
45°	516.8	525.0	539.3	564.6	601.2	655.1	734.3	848.8	948.5	981.5	935.4
47.5°	442.3	442.3	453.5	470.9	497.3	543.1	601.7	691.4	797.9	876.8	873.1
50°	401.0	399.3	408.2	423.3	444.2	474.6	530.5	602.2	704.6	793.8	818.6
52.5°	365.4	365.6	371.0	382.1	399.7	425.7	467.4	532.0	619.5	711.1	757.9
55°	318.6	317.3	323.5	331.0	343.8	360.8	390.9	440.2	511.2	601.5	662.3
57.5°	275.7	279.2	281.7	287.0	297.6	308.9	334.3	370.6	426.9	504.4	568.7
60°	250.6	254.2	256.1	261.3	269.8	279.7	299.3	328.7	376.2	442.9	506.6
62.5°	228.0	230.8	231.5	236.2	243.1	252.7	268.1	292.8	330.4	388.7	451.2
65°	195.6	195.6	196.9	201.8	205.1	213.6	225.3	243.3	273.5	318.9	372.2
67.5°	164.3	165.9	165.6	167.7	170.7	177.4	185.8	200.6	222.9	256.1	298.8
70°	143.9	145.3	144.9	146.5	149.8	154.0	160.9	175.0	191.0	219.5	256.1
72.5°	125.6	126.1	125.3	127.4	129.4	133.1	140.8	148.3	163.2	187.3	217.4
75°	96.2	96.8	97.5	98.8	100.7	102.7	106.6	114.2	124.0	142.0	161.3
77.5°	72.1	70.9	72.4	72.2	73.4	74.8	78.3	82.3	90.3	101.7	116.7
80°	54.3	54.6	54.6	54.9	56.6	57.6	60.5	63.5	69.7	78.2	88.6
82.5°	39.6	40.5	40.0	40.6	41.9	42.6	44.3	46.7	50.3	57.0	64.6
85°	21.6	20.0	20.6	21.3	21.3	21.6	22.9	23.8	25.8	28.4	31.4
87.5°	10.8	11.4	11.5	11.5	11.7	11.4	12.1	12.0	12.6	13.2	13.8
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3	261.1	322.5	327.8
95°	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3	867.4	886.4	723.3
97.5°	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3	1097.5	946.6	645.9
100°	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5	1153.5	903.4	576.3
102.5°	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2	1119.9	827.3	523.4
105°	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6	1012.4	725.3	472.2
107.5°	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7	902.8	655.0	450.6
110°	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4	840.3	622.2	444.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8	793.9	603.0	444.2
115°	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4	743.3	582.3	447.2
117.5°	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1	713.1	572.0	453.8
120°	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4	696.3	567.2	460.2
122.5°	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8	681.9	563.3	465.8
125°	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4	662.3	558.3	475.2
127.5°	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3	644.3	555.9	485.8
130°	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3	632.3	554.2	492.2
132.5°	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3	622.7	554.2	499.4
135°	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3	611.3	554.2	509.2
137.5°	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3	601.1	555.4	518.2
140°	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3	596.2	556.2	522.2
142.5°	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9	592.3	557.1	524.6
145°	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3	586.3	556.2	527.3
147.5°	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5	580.1	553.6	528.2
150°	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3	575.2	551.2	528.2
152.5°	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3	569.6	548.0	527.4
155°	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2	560.3	542.3	525.2
157.5°	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2	551.5	536.2	522.6
160°	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2	544.2	532.3	520.2
162.5°	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5	537.9	527.4	517.8
165°	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2	528.2	520.2	514.2
167.5°	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6	518.8	513.2	508.6
170°	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2	513.2	509.2	506.3
172.5°	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0	507.6	504.5	503.0
175°	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3	500.2	499.2	499.2
177.5°	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8	497.1	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	792.8	791.0	788.9	785.2	780.8	778.4	774.8	772.4	767.7	763.8	759.6
5°	833.0	824.6	816.7	806.6	795.5	788.2	779.7	770.3	760.4	750.3	739.2
7.5°	874.7	859.7	843.3	825.7	808.6	792.7	777.6	762.8	748.9	732.1	717.9
10°	902.8	883.7	863.5	839.6	816.4	796.1	775.5	757.5	739.2	719.5	702.2
12.5°	930.7	905.4	876.8	850.6	822.7	798.2	774.0	751.0	728.0	706.2	686.0
15°	950.5	928.2	901.7	864.4	833.0	799.4	767.3	737.5	709.7	685.5	660.0
17.5°	963.5	934.9	906.4	870.6	829.5	791.8	755.4	721.4	690.1	659.4	634.8
20°	965.9	936.4	906.6	871.7	829.5	786.3	750.0	709.1	675.4	643.7	613.5
22.5°	965.1	931.7	899.3	863.2	822.2	782.4	738.5	696.8	660.2	629.0	597.6
25°	957.7	922.0	881.5	845.2	804.6	762.4	717.9	674.8	637.5	601.8	570.8
27.5°	951.5	905.3	859.4	817.0	777.8	739.2	696.6	652.4	611.1	574.9	545.6
30°	943.9	893.2	841.5	797.4	757.2	719.5	679.3	636.2	593.0	557.7	526.2
32.5°	937.1	878.0	823.5	775.4	732.9	696.3	659.2	618.1	575.8	539.8	508.5
35°	924.0	855.7	793.2	738.8	693.4	655.8	624.7	586.4	547.5	512.8	482.8
37.5°	907.3	826.2	759.1	702.2	652.4	612.8	583.8	554.5	517.1	483.7	456.5
40°	894.2	805.3	734.3	676.1	624.4	583.2	556.4	528.6	497.5	466.4	437.6
42.5°	877.7	786.4	709.1	646.5	595.4	555.2	527.0	503.4	476.0	447.0	420.3
45°	847.5	752.3	668.6	601.2	549.5	509.9	480.8	463.1	442.6	415.1	392.5
47.5°	802.9	711.3	624.7	555.1	501.8	465.1	437.8	420.9	406.4	386.0	365.5
50°	763.4	680.6	593.0	524.0	470.6	433.7	408.5	393.1	380.7	365.0	347.7
52.5°	719.2	642.1	561.9	493.6	440.8	404.4	379.7	366.2	355.9	344.6	327.5
55°	648.9	583.5	508.9	444.2	395.5	359.8	338.2	326.4	317.9	309.4	298.9
57.5°	571.5	520.4	454.3	395.1	350.3	317.8	297.6	286.2	279.6	275.2	269.1
60°	517.1	473.3	416.4	362.4	318.6	289.8	270.2	261.3	255.8	252.2	247.6
62.5°	466.6	430.6	377.9	328.6	290.3	263.1	245.6	237.0	231.7	230.0	226.1
65°	392.2	364.4	320.9	280.0	247.3	224.0	209.3	201.1	197.9	195.9	196.2
67.5°	318.8	301.9	267.0	232.1	206.0	186.5	174.7	168.4	166.8	164.2	164.1
70°	274.1	261.3	231.9	201.5	178.2	163.2	152.7	146.2	144.6	143.3	142.9
72.5°	234.5	223.4	197.9	173.5	152.7	139.4	130.8	126.8	124.2	123.4	123.3
75°	176.3	170.0	149.8	130.5	116.1	106.9	101.1	97.5	95.5	95.1	95.5
77.5°	125.4	119.9	107.0	93.3	84.3	77.3	72.3	71.1	68.9	69.0	68.6
80°	94.2	90.6	82.4	71.6	64.1	58.2	55.6	53.3	52.7	51.7	52.7
82.5°	68.3	64.4	58.9	52.0	45.8	42.3	39.6	38.9	38.5	38.1	38.2
85°	33.7	34.0	30.7	25.5	22.9	20.9	19.3	19.3	18.9	18.7	18.9
87.5°	14.1	13.2	12.0	10.8	9.0	7.8	7.2	7.2	6.7	6.8	7.5
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2	14.8	23.2	35.6
95°	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0	34.0	42.0	53.0
97.5°	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8	56.1	61.6	72.7
100°	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0	72.1	76.0	87.0
102.5°	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9	88.1	91.3	103.1
105°	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0	113.0	118.0	128.0
107.5°	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6	140.7	145.4	153.7
110°	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0	159.1	163.1	172.1



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5	177.5	180.6	189.7
115°	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1	204.1	207.1	216.1
117.5°	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1	229.1	232.3	241.3
120°	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1	245.1	249.1	258.1
122.5°	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9	261.1	264.3	273.3
125°	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1	282.1	287.1	296.1
127.5°	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7	299.7	306.2	317.5
130°	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1	310.1	318.1	331.1
132.5°	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1	318.9	328.6	343.2
135°	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1	332.2	344.1	360.2
137.5°	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6	347.6	358.8	374.8
140°	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1	357.1	369.2	385.2
142.5°	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3	367.6	378.8	394.8
145°	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2	384.2	394.2	408.2
147.5°	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8	401.0	409.6	422.6
150°	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2	412.2	419.2	432.2
152.5°	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4	422.6	428.8	440.2
155°	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2	436.2	442.2	452.2
157.5°	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4	449.2	454.0	462.6
160°	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2	457.2	461.2	468.2
162.5°	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4	464.4	468.4	474.6
165°	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2	474.2	477.3	482.2
167.5°	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5	482.4	484.2	487.0
170°	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2	487.2	488.2	490.3
172.5°	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5	489.7	490.6	492.6
175°	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2	493.2	494.2	495.2
177.5°	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1	495.4	495.4	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	757.2	754.3	752.0	746.7	743.9	739.9	736.8	740.2	736.6	738.1	735.8
5°	733.7	724.4	717.9	708.4	700.3	692.8	687.2	686.2	683.5	682.3	678.4
7.5°	705.2	693.8	682.5	670.1	659.6	649.0	642.1	636.5	632.8	627.9	624.6
10°	688.5	673.1	660.0	645.0	631.9	620.4	611.3	606.7	602.4	596.2	594.0
12.5°	667.8	651.9	635.9	619.8	607.3	594.5	586.7	579.8	576.9	569.8	569.1
15°	643.0	619.1	603.5	587.1	569.7	559.3	552.8	545.3	542.0	537.1	533.5
17.5°	613.5	592.1	572.5	555.6	540.7	531.9	523.7	518.6	513.0	509.8	503.9
20°	592.0	571.7	552.1	534.1	522.6	512.6	506.0	501.1	495.2	493.5	487.7
22.5°	573.9	551.6	532.7	517.6	505.1	493.7	486.6	483.3	479.2	474.2	473.0
25°	544.6	521.3	505.3	490.3	479.1	468.7	463.8	459.5	455.6	452.0	450.7
27.5°	519.2	498.4	479.4	465.8	456.2	446.6	442.3	437.1	434.2	431.4	427.8
30°	501.4	480.2	463.5	450.4	439.9	431.4	426.8	423.3	420.6	418.0	416.0
32.5°	483.1	463.4	447.2	434.5	424.0	417.6	413.5	411.0	408.0	404.9	402.4
35°	458.9	437.3	421.6	410.4	402.3	397.4	392.8	390.5	387.3	387.3	384.6
37.5°	431.6	412.9	399.1	388.9	381.6	377.2	372.3	370.7	368.6	367.2	366.4
40°	415.3	398.0	385.0	374.8	367.0	363.3	359.5	356.8	355.5	353.9	353.3
42.5°	398.6	382.1	369.5	360.2	353.4	350.3	346.6	344.8	342.2	340.0	339.7
45°	373.2	357.1	345.7	338.2	332.3	328.7	326.4	322.5	321.2	318.6	318.2
47.5°	349.0	333.6	322.4	316.2	311.1	308.2	304.5	300.7	299.1	297.8	297.7
50°	331.0	316.9	306.4	300.6	295.7	291.4	287.8	285.2	284.2	284.2	284.9
52.5°	312.7	300.7	291.8	284.6	280.0	275.4	272.2	270.5	269.1	270.6	271.8
55°	285.9	273.8	267.3	260.4	255.8	250.6	248.9	248.2	247.3	249.9	251.2
57.5°	257.4	249.0	241.3	234.5	230.4	227.4	225.2	224.8	226.6	227.8	232.1
60°	239.4	229.6	222.7	217.5	212.6	210.6	210.0	209.3	210.6	214.2	219.8
62.5°	219.6	211.5	204.1	200.3	196.7	193.4	193.2	193.6	196.2	200.4	206.0
65°	190.4	183.5	178.6	174.0	171.1	169.1	169.8	171.1	174.0	179.6	185.8
67.5°	160.7	156.0	151.6	147.9	145.1	145.1	145.8	147.7	151.2	157.6	163.2
70°	141.6	136.4	132.8	131.1	128.9	127.6	129.5	132.8	135.7	141.6	146.5
72.5°	122.5	118.0	115.3	114.2	113.1	112.1	112.8	116.3	120.3	126.2	131.9
75°	94.2	92.6	90.6	89.3	88.3	88.9	89.6	92.9	96.2	102.4	108.9
77.5°	68.8	67.1	65.9	65.5	65.0	65.3	67.2	69.6	72.8	77.3	82.3
80°	52.0	51.3	50.7	50.4	50.4	50.7	53.3	54.9	57.9	62.2	66.0
82.5°	37.9	37.5	37.4	37.3	37.5	37.6	39.2	41.3	43.7	47.0	50.4
85°	20.0	19.3	20.3	20.6	20.0	20.9	21.6	22.9	23.8	25.5	27.1
87.5°	8.2	9.0	9.0	9.6	9.9	10.8	10.8	12.0	12.7	13.4	13.5
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3	128.6	96.9	82.1
95°	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3	567.2	444.2	360.2
97.5°	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3	964.7	844.8	727.9
100°	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5	1181.6	1078.5	974.4
102.5°	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2	1314.4	1265.0	1194.6
105°	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6	1389.7	1433.7	1422.6
107.5°	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7	1322.6	1435.6	1487.9
110°	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4	1246.6	1387.6	1472.7



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8	1171.3	1314.0	1414.2
115°	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4	1063.5	1200.5	1309.6
117.5°	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1	988.9	1106.9	1206.9
120°	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4	946.4	1056.4	1144.5
122.5°	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8	916.0	1014.1	1096.5
125°	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4	875.4	962.4	1034.5
127.5°	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3	836.5	917.8	985.2
130°	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3	809.3	887.4	952.4
132.5°	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3	783.8	854.5	917.2
135°	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3	744.3	808.4	865.4
137.5°	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3	709.1	762.3	810.8
140°	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3	688.3	734.3	776.4
142.5°	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9	670.7	710.3	746.7
145°	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3	648.2	679.3	706.3
147.5°	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5	629.6	653.5	673.9
150°	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3	619.3	638.3	656.3
152.5°	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3	608.9	626.3	640.3
155°	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2	593.2	607.3	618.3
157.5°	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2	578.4	589.3	597.9
160°	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2	567.2	577.2	584.3
162.5°	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5	557.7	566.0	572.2
165°	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2	543.2	549.2	554.2
167.5°	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6	529.3	533.8	537.4
170°	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2	521.2	524.3	526.2
172.5°	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0	514.0	516.3	517.5
175°	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3	503.3	505.2	505.2
177.5°	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8	498.6	498.6	498.6
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	734.2	736.1	734.5	736.6	734.5	736.1	734.2	735.8	738.1	736.6	740.2
5°	676.7	673.7	675.7	674.4	675.7	673.7	676.7	678.4	682.3	683.5	686.2
7.5°	623.6	620.8	617.6	616.0	617.6	620.8	623.6	624.6	627.9	632.8	636.5
10°	590.4	586.8	586.4	584.2	586.4	586.8	590.4	594.0	596.2	602.4	606.7
12.5°	566.0	562.7	559.0	558.0	559.0	562.7	566.0	569.1	569.8	576.9	579.8
15°	531.5	528.9	526.6	528.6	526.6	528.9	531.5	533.5	537.1	542.0	545.3
17.5°	502.7	500.6	500.2	497.8	500.2	500.6	502.7	503.9	509.8	513.0	518.6
20°	484.7	483.1	483.7	479.5	483.7	483.1	484.7	487.7	493.5	495.2	501.1
22.5°	470.4	467.1	466.7	465.9	466.7	467.1	470.4	473.0	474.2	479.2	483.3
25°	447.8	446.2	444.5	446.2	444.5	446.2	447.8	450.7	452.0	455.6	459.5
27.5°	428.1	426.1	425.7	425.9	425.7	426.1	428.1	427.8	431.4	434.2	437.1
30°	416.0	412.8	413.1	412.8	413.1	412.8	416.0	416.0	418.0	420.6	423.3
32.5°	402.9	400.7	400.3	399.7	400.3	400.7	402.9	402.4	404.9	408.0	411.0
35°	383.7	383.7	382.0	382.0	382.0	383.7	383.7	384.6	387.3	387.3	390.5
37.5°	365.5	365.2	364.2	364.4	364.2	365.2	365.5	366.4	367.2	368.6	370.7
40°	351.9	351.6	350.6	348.6	350.6	351.6	351.9	353.3	353.9	355.5	356.8
42.5°	338.9	337.8	337.3	336.7	337.3	337.8	338.9	339.7	340.0	342.2	344.8
45°	318.2	318.2	317.6	317.3	317.6	318.2	318.2	318.2	318.6	321.2	322.5
47.5°	298.3	298.9	300.1	299.9	300.1	298.9	298.3	297.7	297.8	299.1	300.7
50°	286.2	286.5	287.5	287.8	287.5	286.5	286.2	284.9	284.2	284.2	285.2
52.5°	272.9	274.7	276.0	275.8	276.0	274.7	272.9	271.8	270.6	269.1	270.5
55°	254.2	256.4	258.7	259.1	258.7	256.4	254.2	251.2	249.9	247.3	248.2
57.5°	235.7	238.8	241.3	242.0	241.3	238.8	235.7	232.1	227.8	226.6	224.8
60°	223.1	227.3	230.2	231.6	230.2	227.3	223.1	219.8	214.2	210.6	209.3
62.5°	211.0	215.8	218.8	219.0	218.8	215.8	211.0	206.0	200.4	196.2	193.6
65°	191.3	196.2	198.9	200.8	198.9	196.2	191.3	185.8	179.6	174.0	171.1
67.5°	170.1	175.0	178.0	179.5	178.0	175.0	170.1	163.2	157.6	151.2	147.7
70°	154.7	159.6	163.5	164.9	163.5	159.6	154.7	146.5	141.6	135.7	132.8
72.5°	139.6	143.9	147.1	148.6	147.1	143.9	139.6	131.9	126.2	120.3	116.3
75°	113.1	119.1	122.0	123.6	122.0	119.1	113.1	108.9	102.4	96.2	92.9
77.5°	87.3	92.6	94.4	95.2	94.4	92.6	87.3	82.3	77.3	72.8	69.6
80°	70.0	73.3	75.6	75.9	75.6	73.3	70.0	66.0	62.2	57.9	54.9
82.5°	53.8	56.5	57.3	58.1	57.3	56.5	53.8	50.4	47.0	43.7	41.3
85°	29.4	30.7	31.1	30.7	31.1	30.7	29.4	27.1	25.5	23.8	22.9
87.5°	14.1	13.9	14.0	14.6	14.0	13.9	14.1	13.5	13.4	12.7	12.0
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.2	66.8	65.4	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3
95°	289.1	259.1	251.2	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3
97.5°	666.1	610.1	581.1	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3
100°	905.4	833.4	796.3	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5
102.5°	1120.7	1069.4	1029.2	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2
105°	1390.6	1357.6	1337.6	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6
107.5°	1504.1	1503.9	1497.3	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7
110°	1517.7	1536.7	1543.7	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1480.1	1512.7	1530.1	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8
115°	1387.6	1435.6	1463.6	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4
117.5°	1285.0	1334.6	1362.4	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1
120°	1218.6	1266.5	1293.6	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4
122.5°	1162.5	1206.5	1233.6	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8
125°	1090.5	1131.5	1153.5	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4
127.5°	1036.0	1072.3	1093.1	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3
130°	1002.5	1035.4	1055.5	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3
132.5°	967.2	1000.2	1018.6	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3
135°	909.4	942.5	960.4	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3
137.5°	850.2	880.2	896.8	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3
140°	813.4	839.4	854.4	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3
142.5°	778.2	800.1	814.3	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9
145°	730.3	747.3	758.4	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3
147.5°	692.9	706.5	712.9	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5
150°	671.3	683.3	687.3	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3
152.5°	652.9	662.5	666.5	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3
155°	628.3	635.2	638.3	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2
157.5°	605.6	611.5	614.2	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2
160°	591.2	596.2	598.3	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2
162.5°	577.6	581.9	582.3	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5
165°	558.3	560.3	560.3	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2
167.5°	539.4	541.2	540.4	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6
170°	528.2	529.3	529.3	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2
172.5°	517.8	519.6	518.1	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0
175°	505.2	506.3	504.2	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3
177.5°	497.8	498.6	496.2	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	736.8	739.9	743.9	746.7	752.0	754.3	757.2	759.6	763.8	767.7	772.4
5°	687.2	692.8	700.3	708.4	717.9	724.4	733.7	739.2	750.3	760.4	770.3
7.5°	642.1	649.0	659.6	670.1	682.5	693.8	705.2	717.9	732.1	748.9	762.8
10°	611.3	620.4	631.9	645.0	660.0	673.1	688.5	702.2	719.5	739.2	757.5
12.5°	586.7	594.5	607.3	619.8	635.9	651.9	667.8	686.0	706.2	728.0	751.0
15°	552.8	559.3	569.7	587.1	603.5	619.1	643.0	660.0	685.5	709.7	737.5
17.5°	523.7	531.9	540.7	555.6	572.5	592.1	613.5	634.8	659.4	690.1	721.4
20°	506.0	512.6	522.6	534.1	552.1	571.7	592.0	613.5	643.7	675.4	709.1
22.5°	486.6	493.7	505.1	517.6	532.7	551.6	573.9	597.6	629.0	660.2	696.8
25°	463.8	468.7	479.1	490.3	505.3	521.3	544.6	570.8	601.8	637.5	674.8
27.5°	442.3	446.6	456.2	465.8	479.4	498.4	519.2	545.6	574.9	611.1	652.4
30°	426.8	431.4	439.9	450.4	463.5	480.2	501.4	526.2	557.7	593.0	636.2
32.5°	413.5	417.6	424.0	434.5	447.2	463.4	483.1	508.5	539.8	575.8	618.1
35°	392.8	397.4	402.3	410.4	421.6	437.3	458.9	482.8	512.8	547.5	586.4
37.5°	372.3	377.2	381.6	388.9	399.1	412.9	431.6	456.5	483.7	517.1	554.5
40°	359.5	363.3	367.0	374.8	385.0	398.0	415.3	437.6	466.4	497.5	528.6
42.5°	346.6	350.3	353.4	360.2	369.5	382.1	398.6	420.3	447.0	476.0	503.4
45°	326.4	328.7	332.3	338.2	345.7	357.1	373.2	392.5	415.1	442.6	463.1
47.5°	304.5	308.2	311.1	316.2	322.4	333.6	349.0	365.5	386.0	406.4	420.9
50°	287.8	291.4	295.7	300.6	306.4	316.9	331.0	347.7	365.0	380.7	393.1
52.5°	272.2	275.4	280.0	284.6	291.8	300.7	312.7	327.5	344.6	355.9	366.2
55°	248.9	250.6	255.8	260.4	267.3	273.8	285.9	298.9	309.4	317.9	326.4
57.5°	225.2	227.4	230.4	234.5	241.3	249.0	257.4	269.1	275.2	279.6	286.2
60°	210.0	210.6	212.6	217.5	222.7	229.6	239.4	247.6	252.2	255.8	261.3
62.5°	193.2	193.4	196.7	200.3	204.1	211.5	219.6	226.1	230.0	231.7	237.0
65°	169.8	169.1	171.1	174.0	178.6	183.5	190.4	196.2	195.9	197.9	201.1
67.5°	145.8	145.1	145.1	147.9	151.6	156.0	160.7	164.1	164.2	166.8	168.4
70°	129.5	127.6	128.9	131.1	132.8	136.4	141.6	142.9	143.3	144.6	146.2
72.5°	112.8	112.1	113.1	114.2	115.3	118.0	122.5	123.3	123.4	124.2	126.8
75°	89.6	88.9	88.3	89.3	90.6	92.6	94.2	95.5	95.1	95.5	97.5
77.5°	67.2	65.3	65.0	65.5	65.9	67.1	68.8	68.6	69.0	68.9	71.1
80°	53.3	50.7	50.4	50.4	50.7	51.3	52.0	52.7	51.7	52.7	53.3
82.5°	39.2	37.6	37.5	37.3	37.4	37.5	37.9	38.2	38.1	38.5	38.9
85°	21.6	20.9	20.0	20.6	20.3	19.3	20.0	18.9	18.7	18.9	19.3
87.5°	10.8	10.8	9.9	9.6	9.0	9.0	8.2	7.5	6.8	6.7	7.2
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	261.1	322.5	327.8	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2
95°	867.4	886.4	723.3	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0
97.5°	1097.5	946.6	645.9	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8
100°	1153.5	903.4	576.3	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0
102.5°	1119.9	827.3	523.4	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9
105°	1012.4	725.3	472.2	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0
107.5°	902.8	655.0	450.6	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6
110°	840.3	622.2	444.2	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	793.9	603.0	444.2	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5
115°	743.3	582.3	447.2	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1
117.5°	713.1	572.0	453.8	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1
120°	696.3	567.2	460.2	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1
122.5°	681.9	563.3	465.8	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9
125°	662.3	558.3	475.2	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1
127.5°	644.3	555.9	485.8	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7
130°	632.3	554.2	492.2	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1
132.5°	622.7	554.2	499.4	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1
135°	611.3	554.2	509.2	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1
137.5°	601.1	555.4	518.2	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6
140°	596.2	556.2	522.2	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1
142.5°	592.3	557.1	524.6	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3
145°	586.3	556.2	527.3	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2
147.5°	580.1	553.6	528.2	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8
150°	575.2	551.2	528.2	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2
152.5°	569.6	548.0	527.4	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4
155°	560.3	542.3	525.2	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2
157.5°	551.5	536.2	522.6	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4
160°	544.2	532.3	520.2	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2
162.5°	537.9	527.4	517.8	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4
165°	528.2	520.2	514.2	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2
167.5°	518.8	513.2	508.6	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5
170°	513.2	509.2	506.3	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2
172.5°	507.6	504.5	503.0	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5
175°	500.2	499.2	499.2	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2
177.5°	497.1	496.2	496.2	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	774.8	778.4	780.8	785.2	788.9	791.0	792.8	794.4	796.3	797.8	802.3
5°	779.7	788.2	795.5	806.6	816.7	824.6	833.0	840.6	846.8	855.7	862.5
7.5°	777.6	792.7	808.6	825.7	843.3	859.7	874.7	888.8	901.6	917.0	930.5
10°	775.5	796.1	816.4	839.6	863.5	883.7	902.8	922.0	936.1	955.7	972.4
12.5°	774.0	798.2	822.7	850.6	876.8	905.4	930.7	944.8	966.2	981.9	1001.7
15°	767.3	799.4	833.0	864.4	901.7	928.2	950.5	977.9	997.9	1017.9	1039.4
17.5°	755.4	791.8	829.5	870.6	906.4	934.9	963.5	990.0	1013.8	1040.5	1067.5
20°	750.0	786.3	829.5	871.7	906.6	936.4	965.9	995.0	1021.1	1055.5	1086.5
22.5°	738.5	782.4	822.2	863.2	899.3	931.7	965.1	998.1	1032.9	1071.7	1110.6
25°	717.9	762.4	804.6	845.2	881.5	922.0	957.7	1001.9	1046.3	1097.7	1146.1
27.5°	696.6	739.2	777.8	817.0	859.4	905.3	951.5	1001.6	1059.9	1124.6	1193.0
30°	679.3	719.5	757.2	797.4	841.5	893.2	943.9	1003.5	1070.8	1143.8	1224.9
32.5°	659.2	696.3	732.9	775.4	823.5	878.0	937.1	1002.4	1083.4	1166.3	1249.7
35°	624.7	655.8	693.4	738.8	793.2	855.7	924.0	1001.2	1094.1	1189.2	1259.6
37.5°	583.8	612.8	652.4	702.2	759.1	826.2	907.3	998.8	1097.5	1173.4	1196.1
40°	556.4	583.2	624.4	676.1	734.3	805.3	894.2	991.0	1086.5	1135.0	1116.3
42.5°	527.0	555.2	595.4	646.5	709.1	786.4	877.7	974.6	1054.6	1072.9	1008.5
45°	480.8	509.9	549.5	601.2	668.6	752.3	847.5	935.4	981.5	948.5	848.8
47.5°	437.8	465.1	501.8	555.1	624.7	711.3	802.9	873.1	876.8	797.9	691.4
50°	408.5	433.7	470.6	524.0	593.0	680.6	763.4	818.6	793.8	704.6	602.2
52.5°	379.7	404.4	440.8	493.6	561.9	642.1	719.2	757.9	711.1	619.5	532.0
55°	338.2	359.8	395.5	444.2	508.9	583.5	648.9	662.3	601.5	511.2	440.2
57.5°	297.6	317.8	350.3	395.1	454.3	520.4	571.5	568.7	504.4	426.9	370.6
60°	270.2	289.8	318.6	362.4	416.4	473.3	517.1	506.6	442.9	376.2	328.7
62.5°	245.6	263.1	290.3	328.6	377.9	430.6	466.6	451.2	388.7	330.4	292.8
65°	209.3	224.0	247.3	280.0	320.9	364.4	392.2	372.2	318.9	273.5	243.3
67.5°	174.7	186.5	206.0	232.1	267.0	301.9	318.8	298.8	256.1	222.9	200.6
70°	152.7	163.2	178.2	201.5	231.9	261.3	274.1	256.1	219.5	191.0	175.0
72.5°	130.8	139.4	152.7	173.5	197.9	223.4	234.5	217.4	187.3	163.2	148.3
75°	101.1	106.9	116.1	130.5	149.8	170.0	176.3	161.3	142.0	124.0	114.2
77.5°	72.3	77.3	84.3	93.3	107.0	119.9	125.4	116.7	101.7	90.3	82.3
80°	55.6	58.2	64.1	71.6	82.4	90.6	94.2	88.6	78.2	69.7	63.5
82.5°	39.6	42.3	45.8	52.0	58.9	64.4	68.3	64.6	57.0	50.3	46.7
85°	19.3	20.9	22.9	25.5	30.7	34.0	33.7	31.4	28.4	25.8	23.8
87.5°	7.2	7.8	9.0	10.8	12.0	13.2	14.1	13.8	13.2	12.6	12.0
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.6	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3
95°	34.0	42.0	53.0	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3
97.5°	56.1	61.6	72.7	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3
100°	72.1	76.0	87.0	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5
102.5°	88.1	91.3	103.1	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2
105°	113.0	118.0	128.0	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6
107.5°	140.7	145.4	153.7	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7
110°	159.1	163.1	172.1	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.5	180.6	189.7	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8
115°	204.1	207.1	216.1	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4
117.5°	229.1	232.3	241.3	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1
120°	245.1	249.1	258.1	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4
122.5°	261.1	264.3	273.3	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8
125°	282.1	287.1	296.1	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4
127.5°	299.7	306.2	317.5	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3
130°	310.1	318.1	331.1	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3
132.5°	318.9	328.6	343.2	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3
135°	332.2	344.1	360.2	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3
137.5°	347.6	358.8	374.8	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3
140°	357.1	369.2	385.2	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3
142.5°	367.6	378.8	394.8	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9
145°	384.2	394.2	408.2	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3
147.5°	401.0	409.6	422.6	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5
150°	412.2	419.2	432.2	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3
152.5°	422.6	428.8	440.2	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3
155°	436.2	442.2	452.2	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2
157.5°	449.2	454.0	462.6	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2
160°	457.2	461.2	468.2	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2
162.5°	464.4	468.4	474.6	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5
165°	474.2	477.3	482.2	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2
167.5°	482.4	484.2	487.0	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6
170°	487.2	488.2	490.3	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2
172.5°	489.7	490.6	492.6	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0
175°	493.2	494.2	495.2	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3
177.5°	495.4	495.4	496.2	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	805.9	808.0	812.4	810.9	813.0	814.0	815.1
5°	871.0	881.5	886.1	885.4	892.3	890.6	889.0
7.5°	944.5	955.5	961.7	969.3	973.8	974.0	977.9
10°	986.1	1000.5	1006.4	1014.6	1019.9	1022.8	1022.4
12.5°	1018.0	1029.3	1042.5	1046.5	1053.6	1057.3	1055.9
15°	1056.4	1074.4	1088.1	1095.0	1103.9	1106.5	1110.1
17.5°	1090.7	1114.8	1130.9	1152.2	1160.3	1165.2	1162.3
20°	1116.6	1148.3	1164.4	1189.9	1203.9	1211.5	1208.8
22.5°	1147.3	1181.6	1211.3	1233.3	1254.7	1264.9	1267.0
25°	1199.7	1246.8	1290.3	1319.4	1345.9	1352.1	1365.9
27.5°	1258.4	1313.9	1360.4	1390.9	1409.5	1416.3	1420.6
30°	1295.2	1350.5	1385.5	1405.1	1411.0	1410.3	1409.7
32.5°	1313.3	1347.9	1354.6	1349.1	1335.7	1324.2	1312.3
35°	1287.7	1261.9	1223.2	1173.5	1137.0	1099.9	1096.3
37.5°	1158.1	1075.5	1011.2	939.5	898.1	872.5	854.8
40°	1036.1	942.3	864.4	803.9	761.7	745.1	728.8
42.5°	903.8	814.1	745.1	694.6	662.9	644.4	631.4
45°	734.3	655.1	601.2	564.6	539.3	525.0	516.8
47.5°	601.7	543.1	497.3	470.9	453.5	442.3	442.3
50°	530.5	474.6	444.2	423.3	408.2	399.3	401.0
52.5°	467.4	425.7	399.7	382.1	371.0	365.6	365.4
55°	390.9	360.8	343.8	331.0	323.5	317.3	318.6
57.5°	334.3	308.9	297.6	287.0	281.7	279.2	275.7
60°	299.3	279.7	269.8	261.3	256.1	254.2	250.6
62.5°	268.1	252.7	243.1	236.2	231.5	230.8	228.0
65°	225.3	213.6	205.1	201.8	196.9	195.6	195.6
67.5°	185.8	177.4	170.7	167.7	165.6	165.9	164.3
70°	160.9	154.0	149.8	146.5	144.9	145.3	143.9
72.5°	140.8	133.1	129.4	127.4	125.3	126.1	125.6
75°	106.6	102.7	100.7	98.8	97.5	96.8	96.2
77.5°	78.3	74.8	73.4	72.2	72.4	70.9	72.1
80°	60.5	57.6	56.6	54.9	54.6	54.6	54.3
82.5°	44.3	42.6	41.9	40.6	40.0	40.5	39.6
85°	22.9	21.6	21.3	21.3	20.6	20.0	21.6
87.5°	12.1	11.4	11.7	11.5	11.5	11.4	10.8
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.6	96.9	82.1	69.2	66.8	65.4	63.8
95°	567.2	444.2	360.2	289.1	259.1	251.2	235.1
97.5°	964.7	844.8	727.9	666.1	610.1	581.1	568.3
100°	1181.6	1078.5	974.4	905.4	833.4	796.3	780.3
102.5°	1314.4	1265.0	1194.6	1120.7	1069.4	1029.2	1017.3
105°	1389.7	1433.7	1422.6	1390.6	1357.6	1337.6	1325.6
107.5°	1322.6	1435.6	1487.9	1504.1	1503.9	1497.3	1489.3
110°	1246.6	1387.6	1472.7	1517.7	1536.7	1543.7	1543.7



TEST NUMBER: P333198-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1171.3	1314.0	1414.2	1480.1	1512.7	1530.1	1537.3
115°	1063.5	1200.5	1309.6	1387.6	1435.6	1463.6	1476.6
117.5°	988.9	1106.9	1206.9	1285.0	1334.6	1362.4	1370.4
120°	946.4	1056.4	1144.5	1218.6	1266.5	1293.6	1301.6
122.5°	916.0	1014.1	1096.5	1162.5	1206.5	1233.6	1240.8
125°	875.4	962.4	1034.5	1090.5	1131.5	1153.5	1163.6
127.5°	836.5	917.8	985.2	1036.0	1072.3	1093.1	1097.5
130°	809.3	887.4	952.4	1002.5	1035.4	1055.5	1061.4
132.5°	783.8	854.5	917.2	967.2	1000.2	1018.6	1025.5
135°	744.3	808.4	865.4	909.4	942.5	960.4	966.5
137.5°	709.1	762.3	810.8	850.2	880.2	896.8	903.4
140°	688.3	734.3	776.4	813.4	839.4	854.4	859.4
142.5°	670.7	710.3	746.7	778.2	800.1	814.3	818.6
145°	648.2	679.3	706.3	730.3	747.3	758.4	762.3
147.5°	629.6	653.5	673.9	692.9	706.5	712.9	714.7
150°	619.3	638.3	656.3	671.3	683.3	687.3	688.3
152.5°	608.9	626.3	640.3	652.9	662.5	666.5	667.5
155°	593.2	607.3	618.3	628.3	635.2	638.3	639.3
157.5°	578.4	589.3	597.9	605.6	611.5	614.2	614.1
160°	567.2	577.2	584.3	591.2	596.2	598.3	597.3
162.5°	557.7	566.0	572.2	577.6	581.9	582.3	582.0
165°	543.2	549.2	554.2	558.3	560.3	560.3	560.3
167.5°	529.3	533.8	537.4	539.4	541.2	540.4	540.3
170°	521.2	524.3	526.2	528.2	529.3	529.3	528.2
172.5°	514.0	516.3	517.5	517.8	519.6	518.1	517.0
175°	503.3	505.2	505.2	505.2	506.3	504.2	503.3
177.5°	498.6	498.6	498.6	497.8	498.6	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2

(END OF REPORT)