

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331738-927

Luminaire Tested: **SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331738-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3797.4 lumens  
Efficiency: N/A  
Efficacy: 76.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66	63
2	95	88	82	77	90	83	78	74	76	71	68	68	65	62	62	59	57	54
3	87	78	70	65	82	74	68	62	67	62	58	61	57	54	55	52	49	46
4	80	69	61	55	76	66	59	54	60	55	50	55	50	47	50	46	43	40
5	74	62	54	48	70	60	52	47	55	48	44	50	45	41	45	41	38	35
6	68	56	48	42	65	54	47	41	49	43	39	45	40	36	41	37	34	31
7	64	51	43	38	60	49	42	37	45	39	35	42	36	32	38	34	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	28	25
9	55	43	35	30	53	41	34	30	38	32	28	35	30	27	33	28	25	23
10	52	40	32	28	49	38	31	27	35	30	26	33	28	24	30	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.6	3.3
10°-20°	344.8	9.1
20°-30°	484.2	12.8
30°-40°	528.0	13.9
40°-50°	485.4	12.8
50°-60°	381.3	10.0
60°-70°	248.6	6.5
70°-80°	128.2	3.4
80°-90°	34.1	0.9
90°-100°	11.8	0.3
100°-110°	43.3	1.1
110°-120°	115.7	3.0
120°-130°	191.1	5.0
130°-140°	203.2	5.4
140°-150°	188.9	5.0
150°-160°	151.8	4.0
160°-170°	97.8	2.6
170°-180°	33.7	0.9
0°-30°	954.5	25.1
0°-40°	1482.5	39.0
0°-60°	2349.2	61.9
0°-90°	2760.0	72.7
90°-120°	170.8	4.5
90°-150°	754.0	19.9
90°-180°	1037.0	27.3
0°-180°	3797.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	0	3	5	6	7	3
95°	17	9	10	11	11	20
105°	78	81	16	18	20	83
115°	147	152	158	45	21	145
125°	208	212	216	218	219	186
135°	258	262	264	266	266	199
145°	299	299	303	305	304	187
155°	329	327	330	331	329	152
165°	347	345	346	348	346	98
175°	355	353	354	355	353	34
180°	354	354	354	354	354	



TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.6	14.0	12.4	10.8	9.2	8.4	8.6	8.6	8.7	8.8	8.6
90°	0.2	0.9	1.5	2.1	2.8	3.3	3.7	4.2	4.7	5.1	5.4
92.5°	5.1	5.1	5.1	5.0	4.9	5.1	5.2	5.5	5.7	5.9	6.1
95°	16.6	14.7	12.9	11.0	9.1	8.4	8.8	9.2	9.6	10.0	10.3
97.5°	33.0	27.7	22.4	17.2	11.9	9.7	10.6	11.5	12.4	13.4	13.6
100°	45.3	37.5	29.7	21.9	14.2	10.7	11.7	12.7	13.6	14.6	15.1
102.5°	58.9	57.2	55.5	53.9	52.3	47.4	39.3	31.2	23.1	15.0	15.6
105°	77.9	79.5	81.3	83.0	84.7	77.8	62.3	46.7	31.1	15.6	16.2
107.5°	99.5	100.9	102.3	103.7	105.0	96.4	77.8	59.2	40.5	21.9	21.2
110°	113.4	114.6	115.9	117.1	118.3	110.6	94.2	77.7	61.2	44.8	39.1



TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.6	127.6	128.7	129.8	130.8	129.3	125.2	121.2	117.1	113.0	92.3
115°	147.3	148.2	149.2	150.2	151.1	152.3	153.8	155.2	156.6	158.0	131.7
117.5°	165.8	166.8	167.9	169.1	170.1	171.1	172.1	173.1	174.0	175.1	168.7
120°	179.3	180.1	181.0	181.9	182.7	183.6	184.7	185.7	186.7	187.7	188.5
122.5°	190.8	191.7	192.6	193.5	194.4	195.4	196.5	197.6	198.8	199.9	200.3
125°	208.3	209.0	209.7	210.5	211.2	212.1	213.2	214.3	215.3	216.4	216.8
127.5°	224.0	224.9	225.7	226.6	227.4	228.1	228.9	229.8	230.6	231.4	232.0
130°	234.1	235.0	235.9	236.9	237.7	238.5	239.2	239.8	240.4	241.1	241.6
132.5°	244.4	245.1	245.9	246.7	247.5	248.1	248.7	249.4	250.0	250.6	251.2
135°	257.7	258.6	259.5	260.4	261.3	262.1	262.5	263.1	263.6	264.1	264.7
137.5°	271.2	271.8	272.4	273.1	273.7	274.3	274.9	275.4	276.1	276.6	277.2
140°	280.0	280.4	280.8	281.3	281.8	282.3	283.0	283.6	284.2	284.8	285.3
142.5°	287.3	287.7	288.1	288.6	289.0	289.5	290.3	291.0	291.7	292.4	292.9
145°	298.9	298.9	298.8	298.7	298.7	299.1	300.1	301.1	302.1	303.0	303.4
147.5°	309.0	308.8	308.6	308.3	308.2	308.5	309.4	310.5	311.4	312.4	312.6
150°	315.5	315.1	314.7	314.3	313.9	314.3	315.1	316.1	317.0	317.9	318.2
152.5°	321.1	320.7	320.2	319.7	319.3	319.5	320.4	321.2	322.1	323.0	323.3
155°	329.2	328.6	328.1	327.6	327.1	327.2	327.9	328.5	329.2	329.9	330.3
157.5°	335.4	335.0	334.5	334.1	333.7	333.7	334.2	334.7	335.2	335.6	336.0
160°	339.1	338.8	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1	339.5
162.5°	342.4	342.1	341.7	341.4	341.0	341.0	341.3	341.6	341.9	342.2	342.6
165°	346.8	346.5	346.1	345.8	345.5	345.4	345.5	345.7	345.9	346.0	346.4
167.5°	350.1	349.7	349.4	349.0	348.7	348.6	348.8	349.0	349.1	349.3	349.7
170°	352.0	351.6	351.3	350.9	350.5	350.5	350.5	350.7	350.8	350.9	351.3
172.5°	353.2	352.8	352.4	352.1	351.8	351.6	351.8	351.9	352.0	352.1	352.5
175°	354.7	354.3	353.9	353.6	353.2	353.0	353.2	353.2	353.4	353.5	353.9
177.5°	355.0	354.7	354.3	354.0	353.7	353.6	353.6	353.7	353.7	353.8	354.1
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	8.5	8.3	8.2	8.1	8.1	8.2	8.2	8.2
90°	5.7	5.9	6.3	6.5	6.6	6.7	6.8	6.9
92.5°	6.3	6.4	6.5	6.7	6.7	6.8	6.8	6.9
95°	10.5	10.9	11.1	11.2	11.2	11.1	11.1	11.0
97.5°	13.9	14.0	14.3	14.4	14.5	14.6	14.7	14.7
100°	15.5	16.0	16.4	16.7	16.8	17.0	17.0	17.2
102.5°	16.2	16.8	17.3	17.7	17.9	18.1	18.2	18.4
105°	16.9	17.5	18.1	18.5	18.8	19.0	19.3	19.5
107.5°	20.6	20.0	19.3	19.1	19.3	19.6	19.8	20.0
110°	33.4	27.7	22.0	19.3	19.6	19.8	20.0	20.2





TEST NUMBER: P331738-927

CATALOG NUMBER: SA2XXRDIP-C1005D330U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	71.5	50.8	30.0	19.7	19.9	20.0	20.3	20.4
115°	105.4	79.0	52.6	37.4	33.3	29.2	25.1	21.0
117.5°	162.3	155.9	149.6	139.7	126.2	112.7	99.3	85.8
120°	189.1	189.8	190.4	187.0	179.3	171.6	163.9	156.2
122.5°	200.7	201.1	201.5	200.9	199.5	198.0	196.5	195.0
125°	217.2	217.6	218.0	218.3	218.5	218.6	218.8	219.0
127.5°	232.6	233.1	233.7	234.0	234.1	234.1	234.1	234.2
130°	242.2	242.9	243.5	243.8	243.8	243.7	243.7	243.6
132.5°	251.8	252.2	252.8	253.0	252.9	252.9	252.9	252.8
135°	265.2	265.8	266.3	266.6	266.5	266.3	266.3	266.1
137.5°	277.7	278.3	278.8	279.0	278.8	278.7	278.5	278.3
140°	285.8	286.4	286.8	287.0	286.7	286.5	286.1	285.8
142.5°	293.3	293.8	294.3	294.4	294.1	293.8	293.5	293.2
145°	303.8	304.2	304.6	304.7	304.4	304.1	303.8	303.5
147.5°	312.9	313.2	313.5	313.5	313.3	313.1	312.8	312.6
150°	318.5	318.9	319.2	319.2	319.0	318.7	318.4	318.1
152.5°	323.7	324.0	324.3	324.3	323.9	323.6	323.2	322.8
155°	330.6	330.9	331.3	331.2	330.7	330.3	329.9	329.4
157.5°	336.4	336.8	337.2	337.2	336.7	336.3	335.8	335.4
160°	339.8	340.2	340.5	340.5	340.1	339.7	339.3	338.9
162.5°	342.9	343.3	343.7	343.7	343.2	342.7	342.2	341.7
165°	346.8	347.2	347.6	347.6	347.2	346.8	346.4	346.0
167.5°	350.1	350.5	350.9	350.8	350.3	349.7	349.3	348.7
170°	351.7	352.1	352.5	352.4	352.0	351.4	350.9	350.4
172.5°	352.9	353.3	353.7	353.7	353.2	352.7	352.1	351.6
175°	354.3	354.7	355.1	355.0	354.4	353.9	353.2	352.7
177.5°	354.4	354.7	355.1	355.0	354.6	354.2	353.8	353.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9

(END OF REPORT)