

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333167-935

Luminaire Tested: **S125DIP-S610D365U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333167-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D365U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3243.7 lumens  
Efficiency: N/A  
Efficacy: 118.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	69	71	67	63	63	59	56	55	53	50	47
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	2.4
10°-20°	220.2	6.8
20°-30°	325.2	10.0
30°-40°	379.4	11.7
40°-50°	381.1	11.7
50°-60°	334.5	10.3
60°-70°	249.3	7.7
70°-80°	142.5	4.4
80°-90°	42.3	1.3
90°-100°	26.2	0.8
100°-110°	77.3	2.4
110°-120°	131.0	4.0
120°-130°	172.4	5.3
130°-140°	193.2	6.0
140°-150°	189.3	5.8
150°-160°	159.0	4.9
160°-170°	105.7	3.3
170°-180°	37.0	1.1
0°-30°	623.4	19.2
0°-40°	1002.8	30.9
0°-60°	1718.4	53.0
0°-90°	2152.5	66.4
90°-120°	234.5	7.2
90°-150°	789.5	24.3
90°-180°	1091.0	33.6
0°-180°	3243.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	0	3	5	6	7	3
95°	20	21	23	26	26	21
105°	69	71	73	74	76	74
115°	131	132	133	133	132	130
125°	191	193	194	193	193	171
135°	249	251	251	251	250	192
145°	302	303	304	304	303	188
155°	345	345	345	346	345	159
165°	375	375	375	376	374	106
175°	390	389	389	390	389	37
180°	391	391	391	391	391	



TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.2	14.3	14.4	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6
90°	0.3	0.9	1.4	1.9	2.5	3.0	3.4	4.0	4.4	4.9	5.2
92.5°	7.4	7.7	8.1	8.5	8.9	9.4	9.9	10.5	11.1	11.7	12.1
95°	19.8	19.9	20.1	20.1	20.3	20.8	21.4	22.0	22.7	23.4	23.9
97.5°	32.9	32.9	33.0	33.1	33.1	33.6	34.5	35.5	36.3	37.3	37.8
100°	42.6	42.6	42.6	42.6	42.6	43.0	43.9	44.8	45.7	46.6	47.2
102.5°	53.0	53.4	53.6	53.9	54.2	54.5	54.9	55.4	55.9	56.3	57.0
105°	69.4	69.7	70.1	70.4	70.8	71.1	71.5	71.9	72.3	72.8	73.1
107.5°	87.4	87.7	88.1	88.4	88.8	89.1	89.4	89.7	90.0	90.3	90.5
110°	99.8	100.1	100.5	100.8	101.2	101.4	101.6	101.9	102.0	102.3	102.5



TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	112.4	112.6	112.8	113.0	113.1	113.4	113.7	113.9	114.2	114.4	114.5
115°	131.1	131.4	131.7	132.0	132.2	132.4	132.6	132.7	132.9	133.0	132.9
117.5°	149.9	150.0	150.2	150.2	150.4	150.5	150.7	150.8	150.8	151.0	151.0
120°	161.6	162.0	162.3	162.6	162.9	163.2	163.2	163.2	163.3	163.4	163.4
122.5°	174.3	174.4	174.5	174.6	174.7	174.9	175.0	175.2	175.4	175.6	175.6
125°	191.4	191.8	192.3	192.6	193.0	193.3	193.4	193.4	193.5	193.6	193.4
127.5°	209.7	209.9	210.2	210.3	210.6	210.8	210.9	210.9	211.0	211.0	211.0
130°	220.6	220.9	221.3	221.6	222.0	222.2	222.3	222.5	222.7	222.7	222.7
132.5°	231.6	232.1	232.7	233.2	233.8	234.1	234.0	234.0	234.0	233.9	233.8
135°	248.9	249.3	249.8	250.1	250.6	250.8	250.9	250.9	251.0	251.1	251.1
137.5°	265.3	265.6	266.0	266.4	266.8	267.1	267.3	267.3	267.5	267.7	267.8
140°	275.7	276.0	276.4	276.7	277.1	277.3	277.5	277.8	277.9	278.1	278.3
142.5°	286.2	286.5	286.7	287.1	287.3	287.6	287.8	288.1	288.3	288.6	288.7
145°	301.6	301.9	302.1	302.4	302.6	302.9	303.1	303.3	303.5	303.7	303.7
147.5°	315.8	316.0	316.1	316.2	316.4	316.6	316.8	316.9	317.0	317.2	317.4
150°	325.3	325.3	325.2	325.1	325.0	325.1	325.4	325.7	326.0	326.2	326.2
152.5°	333.1	333.2	333.3	333.4	333.5	333.6	333.7	333.8	333.9	334.0	334.2
155°	345.1	345.1	345.1	345.1	345.1	345.1	345.2	345.3	345.3	345.4	345.7
157.5°	355.8	355.7	355.5	355.3	355.2	355.2	355.2	355.3	355.3	355.4	355.7
160°	362.1	362.0	361.7	361.5	361.4	361.3	361.4	361.4	361.4	361.5	361.8
162.5°	367.7	367.6	367.5	367.3	367.1	367.0	367.0	367.1	367.1	367.1	367.5
165°	375.2	375.1	375.0	374.8	374.7	374.6	374.7	374.8	374.9	374.9	375.2
167.5°	381.5	381.3	381.0	380.7	380.5	380.3	380.3	380.3	380.3	380.3	380.7
170°	385.0	384.7	384.4	384.2	383.8	383.7	383.7	383.7	383.7	383.7	384.2
172.5°	387.4	387.1	386.8	386.6	386.3	386.2	386.2	386.2	386.2	386.2	386.6
175°	390.1	389.9	389.6	389.3	389.1	388.9	388.9	388.9	388.9	388.9	389.3
177.5°	391.5	391.3	391.1	390.9	390.6	390.5	390.5	390.5	390.4	390.3	390.6
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	14.7	14.8	14.8	14.8	14.6	14.4	14.2	14.0
90°	5.5	5.9	6.2	6.5	6.7	6.9	7.1	7.3
92.5°	12.6	13.0	13.4	13.8	13.9	14.0	14.2	14.4
95°	24.4	24.9	25.3	25.7	25.7	25.9	26.0	26.2
97.5°	38.2	38.7	39.1	39.3	39.4	39.5	39.6	39.7
100°	47.8	48.4	49.0	49.3	49.5	49.7	49.8	49.9
102.5°	57.6	58.3	59.0	59.4	59.6	59.8	59.9	60.1
105°	73.5	74.0	74.4	74.6	74.8	75.1	75.3	75.5
107.5°	90.7	90.9	91.1	91.3	91.2	91.2	91.2	91.2
110°	102.6	102.9	103.1	103.1	103.1	103.0	102.9	102.9





TEST NUMBER: P333167-935

CATALOG NUMBER: S125DIP-S610D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	114.6	114.7	114.8	114.8	114.7	114.5	114.4	114.3
115°	132.9	132.8	132.7	132.7	132.6	132.5	132.4	132.3
117.5°	151.1	151.2	151.2	151.1	150.8	150.6	150.3	150.0
120°	163.4	163.4	163.4	163.2	163.0	162.7	162.5	162.2
122.5°	175.5	175.4	175.4	175.2	175.0	174.8	174.6	174.4
125°	193.3	193.1	193.0	192.9	192.9	192.8	192.7	192.6
127.5°	210.9	210.9	210.8	210.7	210.6	210.4	210.3	210.2
130°	222.7	222.6	222.5	222.4	222.2	222.1	222.0	221.9
132.5°	233.8	233.8	233.7	233.6	233.3	233.2	233.0	232.8
135°	251.1	251.1	251.1	250.9	250.6	250.4	250.1	249.9
137.5°	267.9	267.9	268.0	267.9	267.5	267.2	266.8	266.5
140°	278.4	278.5	278.7	278.6	278.3	277.9	277.6	277.2
142.5°	288.8	288.9	289.0	288.8	288.4	288.1	287.8	287.5
145°	303.7	303.7	303.7	303.6	303.4	303.2	303.0	302.8
147.5°	317.5	317.7	317.9	317.7	317.3	316.8	316.3	315.9
150°	326.2	326.2	326.2	326.1	326.1	325.9	325.7	325.6
152.5°	334.3	334.5	334.7	334.6	334.4	334.2	333.9	333.6
155°	345.9	346.2	346.5	346.5	346.1	345.8	345.4	345.1
157.5°	355.9	356.3	356.5	356.5	356.0	355.5	355.1	354.6
160°	362.1	362.3	362.6	362.6	362.2	361.9	361.5	361.2
162.5°	367.7	368.1	368.4	368.4	368.0	367.6	367.2	366.8
165°	375.5	375.7	376.0	375.9	375.5	375.1	374.7	374.3
167.5°	381.2	381.5	381.9	381.9	381.5	381.1	380.6	380.3
170°	384.5	385.0	385.4	385.3	384.9	384.4	383.9	383.4
172.5°	387.0	387.4	387.8	387.8	387.4	386.9	386.5	386.1
175°	389.7	390.1	390.5	390.5	390.0	389.5	389.1	388.6
177.5°	391.0	391.3	391.6	391.6	391.2	390.8	390.5	390.0
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1

(END OF REPORT)