

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333177-935

Luminaire Tested: **S125DIP-S610D590U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333177-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3979.9 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50	45
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	2.0
10°-20°	220.2	5.5
20°-30°	325.2	8.2
30°-40°	379.4	9.5
40°-50°	381.1	9.6
50°-60°	334.5	8.4
60°-70°	249.3	6.3
70°-80°	142.5	3.6
80°-90°	42.8	1.1
90°-100°	176.6	4.4
100°-110°	379.6	9.5
110°-120°	356.2	9.0
120°-130°	288.7	7.3
130°-140°	231.7	5.8
140°-150°	174.8	4.4
150°-160°	123.1	3.1
160°-170°	72.5	1.8
170°-180°	23.6	0.6
0°-30°	623.4	15.7
0°-40°	1002.8	25.2
0°-60°	1718.4	43.2
0°-90°	2153.0	54.1
90°-120°	912.4	22.9
90°-150°	1607.6	40.4
90°-180°	1827.0	45.9
0°-180°	3979.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	0	4	8	10	11	3
95°	16	48	435	197	116	17
105°	56	78	356	701	651	59
115°	99	120	286	616	725	98
125°	138	161	274	490	571	122
135°	161	194	272	411	474	125
145°	188	215	273	340	374	118
155°	214	230	266	301	314	99
165°	234	240	255	271	275	66
175°	243	243	245	248	247	23
180°	244	244	244	244	244	



TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.2	14.3	14.6	14.7	14.9	15.1	15.1	15.2	15.1	15.2	15.2
90°	0.5	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4
92.5°	6.0	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2
95°	16.2	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9
97.5°	26.9	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8
100°	34.4	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3
102.5°	42.6	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7
105°	55.5	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1
107.5°	68.1	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2
110°	77.1	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6



TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	86.2	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8
115°	99.2	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9
117.5°	111.0	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1
120°	118.8	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8
122.5°	127.1	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8
125°	137.5	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1
127.5°	145.7	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3
130°	150.8	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4
132.5°	154.7	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7
135°	161.1	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1
137.5°	169.2	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1
140°	173.8	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7
142.5°	179.3	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8
145°	187.6	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8
147.5°	196.2	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7
150°	201.4	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4
152.5°	206.9	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7
155°	214.1	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0
157.5°	220.6	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7
160°	225.0	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2
162.5°	228.5	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1
165°	233.8	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3
167.5°	237.3	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7
170°	239.7	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9
172.5°	241.3	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2
175°	243.1	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6
177.5°	244.0	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	15.4	15.5	15.6	15.7	15.4	15.2	15.1	14.8
90°	8.9	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	87.0	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	353.1	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	525.9	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	604.1	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	630.4	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	614.9	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	559.5	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	518.7	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333177-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	486.5	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	445.9	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	419.8	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	405.7	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	395.1	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	379.6	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	363.9	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	354.1	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	344.3	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	331.5	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	320.7	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	314.8	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	309.7	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	303.1	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	296.8	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	293.2	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	289.3	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	283.4	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	277.5	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	273.5	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	269.2	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	263.2	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	257.5	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	254.4	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	250.9	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.4	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)