

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333186-935

Luminaire Tested: **S125DIP-S610D810U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333186-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4657.6 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	41	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	30	27	24
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.7
10°-20°	220.2	4.7
20°-30°	325.2	7.0
30°-40°	379.4	8.1
40°-50°	381.1	8.2
50°-60°	334.5	7.2
60°-70°	249.3	5.4
70°-80°	142.5	3.1
80°-90°	43.3	0.9
90°-100°	242.0	5.2
100°-110°	520.3	11.2
110°-120°	488.3	10.5
120°-130°	395.7	8.5
130°-140°	317.6	6.8
140°-150°	239.7	5.1
150°-160°	168.7	3.6
160°-170°	99.4	2.1
170°-180°	32.3	0.7
0°-30°	623.4	13.4
0°-40°	1002.8	21.5
0°-60°	1718.4	36.9
0°-90°	2153.5	46.2
90°-120°	1250.6	26.9
90°-150°	2203.6	47.3
90°-180°	2504.0	53.8
0°-180°	4657.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	1	6	11	14	16	3
95°	22	66	596	271	158	24
105°	76	106	488	961	892	80
115°	136	164	392	845	994	134
125°	188	221	376	672	783	167
135°	221	266	373	563	650	171
145°	257	295	374	466	513	161
155°	294	316	365	412	430	135
165°	320	329	350	371	377	90
175°	333	333	336	340	339	32
180°	334	334	334	334	334	



TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.3	14.4	14.6	14.9	15.2	15.4	15.4	15.6	15.6	15.8	15.9
90°	0.7	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5
92.5°	8.2	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7
95°	22.2	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7
97.5°	36.9	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5
100°	47.1	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2
102.5°	58.5	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6
105°	76.1	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3
107.5°	93.3	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5
110°	105.7	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5



TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	118.0	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3
115°	136.0	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2
117.5°	152.1	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8
120°	162.9	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6
122.5°	174.3	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8
125°	188.5	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7
127.5°	199.7	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5
130°	206.6	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5
132.5°	212.1	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0
135°	220.8	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3
137.5°	231.9	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5
140°	238.3	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2
142.5°	245.8	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6
145°	257.2	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5
147.5°	269.0	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3
150°	276.0	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1
152.5°	283.5	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3
155°	293.5	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0
157.5°	302.4	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1
160°	308.3	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3
162.5°	313.1	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9
165°	320.5	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4
167.5°	325.3	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1
170°	328.6	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3
172.5°	330.7	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6
175°	333.2	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6
177.5°	334.4	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	16.0	16.2	16.3	16.4	16.2	16.0	15.9	15.7
90°	12.1	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	119.3	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	484.1	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	720.9	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	828.0	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	864.1	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	842.8	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	766.9	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	710.9	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333186-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	666.8	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	611.3	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	575.5	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	556.0	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	541.6	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	520.4	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	498.9	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	485.3	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	471.9	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	454.4	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	439.6	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	431.5	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	424.6	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	415.3	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	406.7	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	401.9	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	396.5	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	388.5	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	380.4	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	375.0	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	369.0	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	360.8	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	353.0	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	348.7	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	343.9	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.0	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)