

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331746-927

Luminaire Tested: **SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331746-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4396.0 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63				
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	59	54				
2	93	85	80	74	87	80	75	71	71	67	64	62	59	57	54	52	50	46				
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40				
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35				
5	72	61	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31				
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27				
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24				
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22				
9	54	42	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.9
10°-20°	344.8	7.8
20°-30°	484.2	11.0
30°-40°	528.0	12.0
40°-50°	485.4	11.0
50°-60°	381.3	8.7
60°-70°	248.6	5.7
70°-80°	128.2	2.9
80°-90°	35.4	0.8
90°-100°	93.9	2.1
100°-110°	318.8	7.3
110°-120°	338.6	7.7
120°-130°	278.8	6.3
130°-140°	223.9	5.1
140°-150°	169.2	3.8
150°-160°	118.9	2.7
160°-170°	70.0	1.6
170°-180°	22.8	0.5
0°-30°	954.5	21.7
0°-40°	1482.5	33.7
0°-60°	2349.2	53.4
0°-90°	2761.3	62.8
90°-120°	751.3	17.1
90°-150°	1423.1	32.4
90°-180°	1635.0	37.2
0°-180°	4396.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	0	6	15	15	15	3
95°	16	39	177	67	52	17
105°	55	83	335	598	509	59
115°	97	123	280	578	670	96
125°	136	160	269	468	544	120
135°	159	190	266	394	450	123
145°	182	209	265	329	360	114
155°	206	223	257	291	302	95
165°	225	232	246	261	265	63
175°	234	235	237	240	239	22
180°	235	235	235	235	235	



TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.6	14.2	12.8	11.2	9.7	9.1	9.6	10.2	10.8	10.9	10.5
90°	0.5	1.8	3.6	4.5	5.4	6.8	9.0	12.2	14.9	15.4	14.9
92.5°	5.5	7.9	11.2	13.2	16.2	20.5	30.7	45.1	57.9	58.7	49.6
95°	15.8	17.6	22.1	26.2	33.4	44.3	65.0	104.3	156.8	177.1	155.0
97.5°	25.7	28.2	33.0	39.1	47.5	59.7	85.9	140.6	227.7	302.3	317.1
100°	34.8	36.1	40.2	47.5	56.5	69.2	93.1	148.2	245.7	356.9	421.9
102.5°	43.1	44.1	48.2	55.4	64.8	77.4	99.6	148.5	238.9	358.7	461.0
105°	55.1	57.0	60.0	66.9	76.8	89.4	110.7	150.9	225.5	334.8	455.0
107.5°	68.1	69.6	72.6	78.9	88.7	101.5	122.1	157.1	218.7	309.1	415.3
110°	76.8	78.6	81.4	87.2	96.6	109.8	129.7	162.2	217.3	296.8	390.3



TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	86.6	89.6	95.1	104.3	117.7	136.9	167.6	217.7	288.8	373.0
115°	97.1	99.4	102.1	107.5	116.5	128.7	148.2	175.7	219.6	280.1	351.5
117.5°	110.0	111.8	114.5	119.3	127.9	140.6	158.6	184.4	222.8	275.8	337.9
120°	117.9	119.7	122.4	126.5	135.5	148.2	165.8	190.2	225.0	273.3	330.7
122.5°	125.5	127.0	129.7	134.1	143.1	156.1	172.7	195.3	227.5	271.9	324.6
125°	135.5	136.9	139.6	145.0	154.1	166.7	183.0	203.3	231.3	269.3	315.8
127.5°	143.5	145.3	149.1	155.0	163.7	176.7	192.6	210.8	235.2	267.8	307.7
130°	148.2	150.0	154.5	160.8	169.8	182.5	198.4	215.5	238.1	267.0	302.2
132.5°	152.5	154.7	159.5	166.3	175.6	188.3	203.4	220.2	241.0	266.6	297.9
135°	159.0	160.8	166.3	173.0	183.4	196.1	210.6	226.3	244.4	266.1	291.8
137.5°	165.2	167.3	172.8	180.0	190.3	202.0	216.3	231.0	247.5	266.0	287.6
140°	169.8	171.7	177.1	184.3	194.2	206.0	219.6	233.5	248.9	265.6	285.1
142.5°	174.6	176.0	181.1	188.3	197.9	208.9	222.1	235.8	250.0	265.6	282.6
145°	181.6	183.4	187.9	194.7	203.7	213.7	225.9	238.5	251.2	264.7	279.2
147.5°	189.2	190.5	194.9	201.1	208.7	217.5	228.9	240.1	251.5	263.1	275.8
150°	194.2	195.6	199.2	205.1	211.9	220.0	230.4	240.8	251.2	262.1	272.9
152.5°	199.3	199.9	203.6	208.7	215.2	222.5	231.9	241.1	250.5	260.2	270.4
155°	206.4	206.9	209.6	214.6	219.6	226.3	234.0	241.7	249.4	257.1	265.6
157.5°	212.4	212.9	215.1	219.4	223.4	229.0	235.5	241.7	247.3	253.8	261.2
160°	216.4	216.8	218.6	222.3	225.9	230.8	236.3	241.7	246.2	251.7	257.9
162.5°	220.4	220.1	221.9	224.8	228.1	232.0	236.6	241.3	245.1	249.9	255.1
165°	225.0	224.5	225.5	228.1	230.4	233.1	237.2	240.3	243.0	246.2	250.3
167.5°	228.8	228.2	229.0	230.8	232.4	234.1	237.1	239.7	241.0	243.0	245.6
170°	231.3	230.4	230.8	232.2	233.1	234.5	236.7	239.0	239.9	241.2	243.0
172.5°	232.7	232.2	232.0	233.3	233.9	234.8	236.4	237.9	238.4	239.1	240.5
175°	234.5	234.0	233.5	234.5	234.5	234.9	235.8	236.7	236.3	236.7	237.2
177.5°	235.3	234.6	234.2	234.9	234.9	234.9	235.3	236.0	235.3	234.9	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	10.2	9.8	9.8	9.7	9.7	9.7	9.7	9.7
90°	14.4	13.5	14.4	14.9	14.9	14.9	14.9	14.9
92.5°	39.4	33.8	30.0	27.2	26.9	25.4	25.7	25.0
95°	118.4	90.8	71.9	61.9	56.0	52.4	51.0	51.5
97.5°	276.2	226.0	177.1	144.5	122.9	111.8	105.2	101.4
100°	412.5	356.5	294.5	239.9	202.4	183.0	169.8	161.8
102.5°	501.8	489.1	443.9	385.9	345.2	312.0	295.6	284.6
105°	548.9	599.9	605.9	590.9	562.9	534.9	515.5	509.1
107.5°	514.9	591.8	638.8	660.7	664.2	662.7	658.8	650.4
110°	485.7	566.5	624.3	661.4	680.8	689.4	693.5	693.0



TEST NUMBER: P331746-927

CATALOG NUMBER: SA2XXRDIP-C1005D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	458.9	536.5	598.3	640.8	667.8	682.1	689.8	692.3
115°	426.0	495.6	554.8	601.3	633.3	654.2	665.9	669.9
117.5°	401.2	462.3	516.0	559.7	592.4	614.3	626.7	630.1
120°	389.0	445.0	492.9	534.0	565.6	586.8	599.9	604.4
122.5°	379.2	430.6	475.9	513.0	541.4	562.3	573.9	577.7
125°	365.0	411.5	451.3	485.2	511.4	528.5	539.9	543.5
127.5°	351.0	393.2	430.6	461.9	484.7	500.8	510.6	513.5
130°	342.0	380.9	416.5	446.3	468.5	483.9	492.9	496.5
132.5°	333.4	369.3	402.1	430.1	451.9	467.2	475.5	478.8
135°	321.2	351.0	380.9	406.2	425.6	440.5	448.6	450.4
137.5°	311.6	336.5	360.1	382.2	399.9	412.7	419.9	422.6
140°	305.4	327.1	347.8	367.7	382.2	394.0	400.7	403.5
142.5°	300.3	318.8	336.7	353.3	367.0	377.7	383.7	384.3
145°	293.2	308.1	322.1	335.3	346.0	353.7	358.2	359.6
147.5°	287.7	299.4	310.4	320.0	328.9	335.0	338.1	338.9
150°	283.7	293.7	303.2	311.2	318.1	323.4	326.1	326.6
152.5°	279.7	289.0	297.0	304.0	309.3	314.1	316.1	316.2
155°	274.3	281.5	288.2	293.2	298.2	301.3	303.2	302.2
157.5°	267.8	273.9	279.6	283.4	286.9	289.6	290.4	290.4
160°	263.8	268.8	273.8	276.9	280.1	282.3	282.8	282.8
162.5°	259.8	264.1	268.4	270.8	273.9	275.5	275.9	275.6
165°	253.9	257.1	260.2	262.1	263.8	265.6	265.6	265.2
167.5°	248.2	250.6	252.8	254.4	255.2	256.3	256.2	255.6
170°	245.3	246.7	248.5	249.4	249.9	251.2	250.7	249.9
172.5°	242.1	243.0	244.5	245.0	245.5	246.1	245.7	245.1
175°	238.5	239.0	239.5	239.9	239.9	240.3	239.9	239.0
177.5°	236.0	236.0	236.4	236.4	236.4	236.4	236.0	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9

(END OF REPORT)