

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331747-927

Luminaire Tested: **SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331747-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5316.3 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57				
1	100	96	93	89	93	90	87	84	78	75	73	67	65	64	56	55	54	50				
2	92	85	79	74	86	80	75	70	69	65	62	60	57	55	51	49	47	43				
3	85	76	69	63	79	71	65	60	62	57	54	54	50	47	46	43	41	38				
4	78	68	60	54	72	64	57	52	56	51	47	49	45	41	42	39	37	33				
5	72	61	53	47	67	57	50	45	50	45	41	44	40	37	38	35	33	30				
6	67	55	47	42	62	52	45	40	46	40	36	40	36	33	35	32	29	27				
7	62	50	43	37	58	47	41	36	42	37	33	37	33	29	32	29	26	24				
8	58	46	38	33	54	43	37	32	39	33	29	34	30	27	30	27	24	22				
9	54	42	35	30	51	40	33	29	36	30	27	32	27	24	28	25	22	20				
10	51	39	32	27	47	37	31	26	33	28	24	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.6	3.1
10°-20°	461.5	8.7
20°-30°	594.7	11.2
30°-40°	565.1	10.6
40°-50°	484.1	9.1
50°-60°	368.7	6.9
60°-70°	233.1	4.4
70°-80°	116.4	2.2
80°-90°	32.2	0.6
90°-100°	26.1	0.5
100°-110°	95.8	1.8
110°-120°	256.1	4.8
120°-130°	422.7	8.0
130°-140°	449.6	8.5
140°-150°	417.8	7.9
150°-160°	335.9	6.3
160°-170°	216.5	4.1
170°-180°	74.5	1.4
0°-30°	1221.8	23.0
0°-40°	1786.9	33.6
0°-60°	2639.7	49.7
0°-90°	3021.3	56.8
90°-120°	378.0	7.1
90°-150°	1668.1	31.4
90°-180°	2295.0	43.2
0°-180°	5316.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	24
90°	15	1	15	1	15	8
95°	24	37	24	37	24	23
105°	43	172	43	172	43	45
115°	46	326	46	326	46	116
125°	484	461	484	461	484	419
135°	589	570	589	570	589	454
145°	672	661	672	661	672	420
155°	729	728	729	728	729	336
165°	766	767	766	767	766	216
175°	780	785	780	785	780	74
180°	783	783	783	783	783	



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	10.9	11.2	11.2	11.2	11.1	11.0	10.9	11.2	10.6	11.0	10.3
90°	15.3	15.1	14.8	14.6	14.3	13.9	13.2	12.6	12.0	11.3	10.3
92.5°	15.3	15.1	15.0	14.8	14.7	14.4	14.1	13.8	13.5	13.2	12.7
95°	24.4	24.5	24.6	24.7	24.9	24.6	24.0	23.4	22.7	22.1	21.2
97.5°	32.6	32.4	32.2	32.1	31.9	31.6	31.1	30.6	30.1	29.5	27.6
100°	37.9	37.7	37.5	37.2	37.0	36.4	35.3	34.3	33.3	32.3	30.2
102.5°	40.7	40.3	40.0	39.6	39.3	38.4	37.2	35.8	34.5	33.2	31.1
105°	43.1	42.5	42.1	41.6	41.0	40.1	38.7	37.3	36.0	34.5	32.9
107.5°	44.3	43.8	43.3	42.8	42.3	42.8	44.1	45.6	47.0	48.4	49.8
110°	44.8	44.3	43.7	43.3	42.8	48.8	61.4	74.0	86.6	99.2	135.5



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.2	44.8	44.4	44.0	43.6	66.4	112.3	158.3	204.2	250.1	259.1
115°	46.5	55.5	64.6	73.7	82.7	116.5	174.8	233.1	291.4	349.7	346.5
117.5°	189.7	219.5	249.3	279.1	308.9	330.8	344.9	359.1	373.2	387.3	385.1
120°	345.7	362.7	379.7	396.6	413.7	421.4	419.9	418.4	416.8	415.3	413.1
122.5°	431.3	434.7	437.9	441.2	444.6	445.8	444.8	443.9	443.0	442.1	439.7
125°	484.5	484.1	483.8	483.4	483.0	482.4	481.5	480.6	479.7	478.9	476.4
127.5°	518.1	518.0	517.9	517.8	517.8	517.1	515.8	514.5	513.3	511.9	510.2
130°	538.9	539.0	539.2	539.3	539.4	538.8	537.4	536.0	534.6	533.2	531.9
132.5°	559.3	559.4	559.6	559.7	559.8	559.3	558.1	556.9	555.7	554.5	553.2
135°	588.7	589.0	589.3	589.5	589.8	589.3	588.0	586.8	585.5	584.2	583.1
137.5°	615.6	616.1	616.5	617.0	617.3	617.0	615.7	614.5	613.2	612.0	610.7
140°	632.4	633.0	633.7	634.3	634.9	634.7	633.5	632.4	631.3	630.2	628.8
142.5°	648.7	649.4	650.0	650.6	651.3	651.0	650.0	649.0	647.9	646.9	645.3
145°	671.5	672.2	672.8	673.4	674.0	673.9	673.0	672.2	671.3	670.3	668.2
147.5°	691.6	692.1	692.6	693.2	693.7	693.6	693.0	692.3	691.7	691.0	688.9
150°	703.8	704.4	705.0	705.7	706.3	706.2	705.5	704.7	704.0	703.2	701.2
152.5°	714.2	715.1	715.9	716.8	717.6	717.6	716.8	716.1	715.3	714.5	712.6
155°	728.7	729.8	730.8	731.7	732.8	732.9	732.1	731.4	730.6	729.8	728.3
157.5°	742.0	743.0	743.9	745.0	745.9	746.0	745.1	744.3	743.5	742.6	741.5
160°	749.7	750.6	751.5	752.3	753.2	753.3	752.6	751.8	751.1	750.3	749.5
162.5°	756.1	757.2	758.2	759.3	760.4	760.5	759.6	758.8	758.0	757.1	756.5
165°	765.6	766.4	767.3	768.3	769.1	769.1	768.3	767.3	766.4	765.6	765.2
167.5°	771.6	772.7	773.9	775.0	776.1	776.3	775.4	774.5	773.6	772.7	772.4
170°	775.2	776.3	777.4	778.6	779.7	779.9	779.0	778.1	777.2	776.3	776.1
172.5°	777.9	779.0	780.2	781.3	782.4	782.6	781.7	780.9	780.0	779.0	778.8
175°	780.3	781.6	782.8	784.1	785.4	785.5	784.7	783.8	782.9	782.0	781.7
177.5°	781.8	782.7	783.6	784.5	785.4	785.5	784.8	784.1	783.4	782.7	782.6
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	10.1	10.4	10.2	9.5	9.7	9.9	12.0	14.2	12.5	11.3	10.7
90°	9.3	8.3	7.3	6.1	4.8	3.3	2.0	0.6	2.0	3.3	4.8
92.5°	12.1	11.6	11.2	10.9	11.1	11.2	11.3	11.4	11.3	11.2	11.1
95°	20.4	19.5	18.5	20.2	24.4	28.5	32.7	36.8	32.7	28.5	24.4
97.5°	25.5	23.4	21.4	26.2	37.9	49.7	61.4	73.1	61.4	49.7	37.9
100°	28.0	25.9	23.8	31.3	48.6	65.8	83.0	100.3	83.0	65.8	48.6
102.5°	69.0	86.9	104.8	115.6	119.3	122.9	126.6	130.2	126.6	122.9	119.3
105°	103.3	137.7	172.1	187.4	183.6	179.8	176.0	172.3	176.0	179.8	183.6
107.5°	130.9	172.1	213.3	232.4	229.3	226.3	223.2	220.2	223.2	226.3	229.3
110°	172.0	208.3	244.7	261.6	259.0	256.4	253.7	251.0	253.7	256.4	259.0



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	268.1	277.1	286.1	289.4	287.1	284.7	282.4	280.0	282.4	284.7	287.1
115°	343.3	340.2	337.1	334.4	332.2	330.1	328.0	325.8	328.0	330.1	332.2
117.5°	382.9	380.8	378.6	376.3	373.9	371.5	369.2	366.8	369.2	371.5	373.9
120°	410.8	408.6	406.3	404.3	402.3	400.4	398.5	396.6	398.5	400.4	402.3
122.5°	437.2	434.7	432.2	430.0	428.0	426.0	424.1	422.1	424.1	426.0	428.0
125°	474.0	471.7	469.3	467.2	465.6	464.0	462.3	460.7	462.3	464.0	465.6
127.5°	508.3	506.6	504.8	503.0	501.1	499.4	497.6	495.7	497.6	499.4	501.1
130°	530.4	529.1	527.7	526.0	523.9	522.0	520.0	517.9	520.0	522.0	523.9
132.5°	551.8	550.4	549.0	547.5	545.7	544.1	542.3	540.6	542.3	544.1	545.7
135°	581.9	580.8	579.7	578.1	576.2	574.1	572.1	570.1	572.1	574.1	576.2
137.5°	609.4	608.2	606.9	605.5	604.1	602.7	601.3	599.9	601.3	602.7	604.1
140°	627.4	626.0	624.6	623.4	622.4	621.4	620.4	619.4	620.4	621.4	622.4
142.5°	643.7	642.1	640.6	639.3	638.4	637.5	636.6	635.7	636.6	637.5	638.4
145°	666.1	663.9	661.8	660.8	660.9	661.1	661.2	661.3	661.2	661.1	660.9
147.5°	686.7	684.7	682.5	681.8	682.2	682.7	683.2	683.7	683.2	682.7	682.2
150°	699.2	697.2	695.2	694.6	695.5	696.4	697.3	698.2	697.3	696.4	695.5
152.5°	710.7	708.8	706.9	706.5	707.4	708.4	709.4	710.3	709.4	708.4	707.4
155°	726.8	725.3	723.8	723.7	724.8	725.9	727.1	728.2	727.1	725.9	724.8
157.5°	740.5	739.4	738.3	738.3	739.3	740.2	741.2	742.1	741.2	740.2	739.3
160°	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	749.5	748.8	748.0
162.5°	755.7	755.1	754.5	754.5	755.3	756.1	756.8	757.6	756.8	756.1	755.3
165°	764.9	764.5	764.1	764.2	765.0	765.8	766.5	767.3	766.5	765.8	765.0
167.5°	772.0	771.7	771.3	771.5	772.3	773.0	773.8	774.5	773.8	773.0	772.3
170°	775.9	775.6	775.3	775.6	776.3	777.1	777.8	778.6	777.8	777.1	776.3
172.5°	778.6	778.3	778.1	778.3	779.0	779.8	780.5	781.3	780.5	779.8	779.0
175°	781.5	781.3	781.0	781.3	782.2	783.1	783.9	784.8	783.9	783.1	782.2
177.5°	782.5	782.4	782.3	782.6	783.3	784.0	784.7	785.4	784.7	784.0	783.3
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	10.5	10.2	9.4	9.7	9.8	9.6	9.7	9.3	9.4	9.6	9.2
90°	6.1	7.3	8.3	9.3	10.3	11.3	12.0	12.6	13.2	13.9	14.3
92.5°	10.9	11.2	11.6	12.1	12.7	13.2	13.5	13.8	14.1	14.4	14.7
95°	20.2	18.5	19.5	20.4	21.2	22.1	22.7	23.4	24.0	24.6	24.9
97.5°	26.2	21.4	23.4	25.5	27.6	29.5	30.1	30.6	31.1	31.6	31.9
100°	31.3	23.8	25.9	28.0	30.2	32.3	33.3	34.3	35.3	36.4	37.0
102.5°	115.6	104.8	86.9	69.0	51.1	33.2	34.5	35.8	37.2	38.4	39.3
105°	187.4	172.1	137.7	103.3	68.9	34.5	36.0	37.3	38.7	40.1	41.0
107.5°	232.4	213.3	172.1	130.9	89.6	48.4	47.0	45.6	44.1	42.8	42.3
110°	261.6	244.7	208.3	172.0	135.5	99.2	86.6	74.0	61.4	48.8	42.8



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.4	286.1	277.1	268.1	259.1	250.1	204.2	158.3	112.3	66.4	43.6
115°	334.4	337.1	340.2	343.3	346.5	349.7	291.4	233.1	174.8	116.5	82.7
117.5°	376.3	378.6	380.8	382.9	385.1	387.3	373.2	359.1	344.9	330.8	308.9
120°	404.3	406.3	408.6	410.8	413.1	415.3	416.8	418.4	419.9	421.4	413.7
122.5°	430.0	432.2	434.7	437.2	439.7	442.1	443.0	443.9	444.8	445.8	444.6
125°	467.2	469.3	471.7	474.0	476.4	478.9	479.7	480.6	481.5	482.4	483.0
127.5°	503.0	504.8	506.6	508.3	510.2	511.9	513.3	514.5	515.8	517.1	517.8
130°	526.0	527.7	529.1	530.4	531.9	533.2	534.6	536.0	537.4	538.8	539.4
132.5°	547.5	549.0	550.4	551.8	553.2	554.5	555.7	556.9	558.1	559.3	559.8
135°	578.1	579.7	580.8	581.9	583.1	584.2	585.5	586.8	588.0	589.3	589.8
137.5°	605.5	606.9	608.2	609.4	610.7	612.0	613.2	614.5	615.7	617.0	617.3
140°	623.4	624.6	626.0	627.4	628.8	630.2	631.3	632.4	633.5	634.7	634.9
142.5°	639.3	640.6	642.1	643.7	645.3	646.9	647.9	649.0	650.0	651.0	651.3
145°	660.8	661.8	663.9	666.1	668.2	670.3	671.3	672.2	673.0	673.9	674.0
147.5°	681.8	682.5	684.7	686.7	688.9	691.0	691.7	692.3	693.0	693.6	693.7
150°	694.6	695.2	697.2	699.2	701.2	703.2	704.0	704.7	705.5	706.2	706.3
152.5°	706.5	706.9	708.8	710.7	712.6	714.5	715.3	716.1	716.8	717.6	717.6
155°	723.7	723.8	725.3	726.8	728.3	729.8	730.6	731.4	732.1	732.9	732.8
157.5°	738.3	738.3	739.4	740.5	741.5	742.6	743.5	744.3	745.1	746.0	745.9
160°	747.3	747.3	748.0	748.8	749.5	750.3	751.1	751.8	752.6	753.3	753.2
162.5°	754.5	754.5	755.1	755.7	756.5	757.1	758.0	758.8	759.6	760.5	760.4
165°	764.2	764.1	764.5	764.9	765.2	765.6	766.4	767.3	768.3	769.1	769.1
167.5°	771.5	771.3	771.7	772.0	772.4	772.7	773.6	774.5	775.4	776.3	776.1
170°	775.6	775.3	775.6	775.9	776.1	776.3	777.2	778.1	779.0	779.9	779.7
172.5°	778.3	778.1	778.3	778.6	778.8	779.0	780.0	780.9	781.7	782.6	782.4
175°	781.3	781.0	781.3	781.5	781.7	782.0	782.9	783.8	784.7	785.5	785.4
177.5°	782.6	782.3	782.4	782.5	782.6	782.7	783.4	784.1	784.8	785.5	785.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	9.2	8.8	9.3	8.9	9.3	8.8	9.2	9.2	9.6	9.4	9.3
90°	14.6	14.8	15.1	15.3	15.1	14.8	14.6	14.3	13.9	13.2	12.6
92.5°	14.8	15.0	15.1	15.3	15.1	15.0	14.8	14.7	14.4	14.1	13.8
95°	24.7	24.6	24.5	24.4	24.5	24.6	24.7	24.9	24.6	24.0	23.4
97.5°	32.1	32.2	32.4	32.6	32.4	32.2	32.1	31.9	31.6	31.1	30.6
100°	37.2	37.5	37.7	37.9	37.7	37.5	37.2	37.0	36.4	35.3	34.3
102.5°	39.6	40.0	40.3	40.7	40.3	40.0	39.6	39.3	38.4	37.2	35.8
105°	41.6	42.1	42.5	43.1	42.5	42.1	41.6	41.0	40.1	38.7	37.3
107.5°	42.8	43.3	43.8	44.3	43.8	43.3	42.8	42.3	42.8	44.1	45.6
110°	43.3	43.7	44.3	44.8	44.3	43.7	43.3	42.8	48.8	61.4	74.0



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.0	44.4	44.8	45.2	44.8	44.4	44.0	43.6	66.4	112.3	158.3
115°	73.7	64.6	55.5	46.5	55.5	64.6	73.7	82.7	116.5	174.8	233.1
117.5°	279.1	249.3	219.5	189.7	219.5	249.3	279.1	308.9	330.8	344.9	359.1
120°	396.6	379.7	362.7	345.7	362.7	379.7	396.6	413.7	421.4	419.9	418.4
122.5°	441.2	437.9	434.7	431.3	434.7	437.9	441.2	444.6	445.8	444.8	443.9
125°	483.4	483.8	484.1	484.5	484.1	483.8	483.4	483.0	482.4	481.5	480.6
127.5°	517.8	517.9	518.0	518.1	518.0	517.9	517.8	517.8	517.1	515.8	514.5
130°	539.3	539.2	539.0	538.9	539.0	539.2	539.3	539.4	538.8	537.4	536.0
132.5°	559.7	559.6	559.4	559.3	559.4	559.6	559.7	559.8	559.3	558.1	556.9
135°	589.5	589.3	589.0	588.7	589.0	589.3	589.5	589.8	589.3	588.0	586.8
137.5°	617.0	616.5	616.1	615.6	616.1	616.5	617.0	617.3	617.0	615.7	614.5
140°	634.3	633.7	633.0	632.4	633.0	633.7	634.3	634.9	634.7	633.5	632.4
142.5°	650.6	650.0	649.4	648.7	649.4	650.0	650.6	651.3	651.0	650.0	649.0
145°	673.4	672.8	672.2	671.5	672.2	672.8	673.4	674.0	673.9	673.0	672.2
147.5°	693.2	692.6	692.1	691.6	692.1	692.6	693.2	693.7	693.6	693.0	692.3
150°	705.7	705.0	704.4	703.8	704.4	705.0	705.7	706.3	706.2	705.5	704.7
152.5°	716.8	715.9	715.1	714.2	715.1	715.9	716.8	717.6	717.6	716.8	716.1
155°	731.7	730.8	729.8	728.7	729.8	730.8	731.7	732.8	732.9	732.1	731.4
157.5°	745.0	743.9	743.0	742.0	743.0	743.9	745.0	745.9	746.0	745.1	744.3
160°	752.3	751.5	750.6	749.7	750.6	751.5	752.3	753.2	753.3	752.6	751.8
162.5°	759.3	758.2	757.2	756.1	757.2	758.2	759.3	760.4	760.5	759.6	758.8
165°	768.3	767.3	766.4	765.6	766.4	767.3	768.3	769.1	769.1	768.3	767.3
167.5°	775.0	773.9	772.7	771.6	772.7	773.9	775.0	776.1	776.3	775.4	774.5
170°	778.6	777.4	776.3	775.2	776.3	777.4	778.6	779.7	779.9	779.0	778.1
172.5°	781.3	780.2	779.0	777.9	779.0	780.2	781.3	782.4	782.6	781.7	780.9
175°	784.1	782.8	781.6	780.3	781.6	782.8	784.1	785.4	785.5	784.7	783.8
177.5°	784.5	783.6	782.7	781.8	782.7	783.6	784.5	785.4	785.5	784.8	784.1
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	9.7	9.6	9.8	9.7	9.4	10.2	10.5	10.7	11.3	12.5	14.2
90°	12.0	11.3	10.3	9.3	8.3	7.3	6.1	4.8	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.1	11.6	11.2	10.9	11.1	11.2	11.3	11.4
95°	22.7	22.1	21.2	20.4	19.5	18.5	20.2	24.4	28.5	32.7	36.8
97.5°	30.1	29.5	27.6	25.5	23.4	21.4	26.2	37.9	49.7	61.4	73.1
100°	33.3	32.3	30.2	28.0	25.9	23.8	31.3	48.6	65.8	83.0	100.3
102.5°	34.5	33.2	51.1	69.0	86.9	104.8	115.6	119.3	122.9	126.6	130.2
105°	36.0	34.5	68.9	103.3	137.7	172.1	187.4	183.6	179.8	176.0	172.3
107.5°	47.0	48.4	89.6	130.9	172.1	213.3	232.4	229.3	226.3	223.2	220.2
110°	86.6	99.2	135.5	172.0	208.3	244.7	261.6	259.0	256.4	253.7	251.0



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	204.2	250.1	259.1	268.1	277.1	286.1	289.4	287.1	284.7	282.4	280.0
115°	291.4	349.7	346.5	343.3	340.2	337.1	334.4	332.2	330.1	328.0	325.8
117.5°	373.2	387.3	385.1	382.9	380.8	378.6	376.3	373.9	371.5	369.2	366.8
120°	416.8	415.3	413.1	410.8	408.6	406.3	404.3	402.3	400.4	398.5	396.6
122.5°	443.0	442.1	439.7	437.2	434.7	432.2	430.0	428.0	426.0	424.1	422.1
125°	479.7	478.9	476.4	474.0	471.7	469.3	467.2	465.6	464.0	462.3	460.7
127.5°	513.3	511.9	510.2	508.3	506.6	504.8	503.0	501.1	499.4	497.6	495.7
130°	534.6	533.2	531.9	530.4	529.1	527.7	526.0	523.9	522.0	520.0	517.9
132.5°	555.7	554.5	553.2	551.8	550.4	549.0	547.5	545.7	544.1	542.3	540.6
135°	585.5	584.2	583.1	581.9	580.8	579.7	578.1	576.2	574.1	572.1	570.1
137.5°	613.2	612.0	610.7	609.4	608.2	606.9	605.5	604.1	602.7	601.3	599.9
140°	631.3	630.2	628.8	627.4	626.0	624.6	623.4	622.4	621.4	620.4	619.4
142.5°	647.9	646.9	645.3	643.7	642.1	640.6	639.3	638.4	637.5	636.6	635.7
145°	671.3	670.3	668.2	666.1	663.9	661.8	660.8	660.9	661.1	661.2	661.3
147.5°	691.7	691.0	688.9	686.7	684.7	682.5	681.8	682.2	682.7	683.2	683.7
150°	704.0	703.2	701.2	699.2	697.2	695.2	694.6	695.5	696.4	697.3	698.2
152.5°	715.3	714.5	712.6	710.7	708.8	706.9	706.5	707.4	708.4	709.4	710.3
155°	730.6	729.8	728.3	726.8	725.3	723.8	723.7	724.8	725.9	727.1	728.2
157.5°	743.5	742.6	741.5	740.5	739.4	738.3	738.3	739.3	740.2	741.2	742.1
160°	751.1	750.3	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3
162.5°	758.0	757.1	756.5	755.7	755.1	754.5	754.5	755.3	756.1	756.8	757.6
165°	766.4	765.6	765.2	764.9	764.5	764.1	764.2	765.0	765.8	766.5	767.3
167.5°	773.6	772.7	772.4	772.0	771.7	771.3	771.5	772.3	773.0	773.8	774.5
170°	777.2	776.3	776.1	775.9	775.6	775.3	775.6	776.3	777.1	777.8	778.6
172.5°	780.0	779.0	778.8	778.6	778.3	778.1	778.3	779.0	779.8	780.5	781.3
175°	782.9	782.0	781.7	781.5	781.3	781.0	781.3	782.2	783.1	783.9	784.8
177.5°	783.4	782.7	782.6	782.5	782.4	782.3	782.6	783.3	784.0	784.7	785.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.0	9.9	9.7	9.5	10.2	10.4	10.1	10.3	11.0	10.6	11.2
90°	2.0	3.3	4.8	6.1	7.3	8.3	9.3	10.3	11.3	12.0	12.6
92.5°	11.3	11.2	11.1	10.9	11.2	11.6	12.1	12.7	13.2	13.5	13.8
95°	32.7	28.5	24.4	20.2	18.5	19.5	20.4	21.2	22.1	22.7	23.4
97.5°	61.4	49.7	37.9	26.2	21.4	23.4	25.5	27.6	29.5	30.1	30.6
100°	83.0	65.8	48.6	31.3	23.8	25.9	28.0	30.2	32.3	33.3	34.3
102.5°	126.6	122.9	119.3	115.6	104.8	86.9	69.0	51.1	33.2	34.5	35.8
105°	176.0	179.8	183.6	187.4	172.1	137.7	103.3	68.9	34.5	36.0	37.3
107.5°	223.2	226.3	229.3	232.4	213.3	172.1	130.9	89.6	48.4	47.0	45.6
110°	253.7	256.4	259.0	261.6	244.7	208.3	172.0	135.5	99.2	86.6	74.0



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	282.4	284.7	287.1	289.4	286.1	277.1	268.1	259.1	250.1	204.2	158.3
115°	328.0	330.1	332.2	334.4	337.1	340.2	343.3	346.5	349.7	291.4	233.1
117.5°	369.2	371.5	373.9	376.3	378.6	380.8	382.9	385.1	387.3	373.2	359.1
120°	398.5	400.4	402.3	404.3	406.3	408.6	410.8	413.1	415.3	416.8	418.4
122.5°	424.1	426.0	428.0	430.0	432.2	434.7	437.2	439.7	442.1	443.0	443.9
125°	462.3	464.0	465.6	467.2	469.3	471.7	474.0	476.4	478.9	479.7	480.6
127.5°	497.6	499.4	501.1	503.0	504.8	506.6	508.3	510.2	511.9	513.3	514.5
130°	520.0	522.0	523.9	526.0	527.7	529.1	530.4	531.9	533.2	534.6	536.0
132.5°	542.3	544.1	545.7	547.5	549.0	550.4	551.8	553.2	554.5	555.7	556.9
135°	572.1	574.1	576.2	578.1	579.7	580.8	581.9	583.1	584.2	585.5	586.8
137.5°	601.3	602.7	604.1	605.5	606.9	608.2	609.4	610.7	612.0	613.2	614.5
140°	620.4	621.4	622.4	623.4	624.6	626.0	627.4	628.8	630.2	631.3	632.4
142.5°	636.6	637.5	638.4	639.3	640.6	642.1	643.7	645.3	646.9	647.9	649.0
145°	661.2	661.1	660.9	660.8	661.8	663.9	666.1	668.2	670.3	671.3	672.2
147.5°	683.2	682.7	682.2	681.8	682.5	684.7	686.7	688.9	691.0	691.7	692.3
150°	697.3	696.4	695.5	694.6	695.2	697.2	699.2	701.2	703.2	704.0	704.7
152.5°	709.4	708.4	707.4	706.5	706.9	708.8	710.7	712.6	714.5	715.3	716.1
155°	727.1	725.9	724.8	723.7	723.8	725.3	726.8	728.3	729.8	730.6	731.4
157.5°	741.2	740.2	739.3	738.3	738.3	739.4	740.5	741.5	742.6	743.5	744.3
160°	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	751.1	751.8
162.5°	756.8	756.1	755.3	754.5	754.5	755.1	755.7	756.5	757.1	758.0	758.8
165°	766.5	765.8	765.0	764.2	764.1	764.5	764.9	765.2	765.6	766.4	767.3
167.5°	773.8	773.0	772.3	771.5	771.3	771.7	772.0	772.4	772.7	773.6	774.5
170°	777.8	777.1	776.3	775.6	775.3	775.6	775.9	776.1	776.3	777.2	778.1
172.5°	780.5	779.8	779.0	778.3	778.1	778.3	778.6	778.8	779.0	780.0	780.9
175°	783.9	783.1	782.2	781.3	781.0	781.3	781.5	781.7	782.0	782.9	783.8
177.5°	784.7	784.0	783.3	782.6	782.3	782.4	782.5	782.6	782.7	783.4	784.1
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	10.9	11.0	11.1	11.2	11.2	11.2	10.9
90°	13.2	13.9	14.3	14.6	14.8	15.1	15.3
92.5°	14.1	14.4	14.7	14.8	15.0	15.1	15.3
95°	24.0	24.6	24.9	24.7	24.6	24.5	24.4
97.5°	31.1	31.6	31.9	32.1	32.2	32.4	32.6
100°	35.3	36.4	37.0	37.2	37.5	37.7	37.9
102.5°	37.2	38.4	39.3	39.6	40.0	40.3	40.7
105°	38.7	40.1	41.0	41.6	42.1	42.5	43.1
107.5°	44.1	42.8	42.3	42.8	43.3	43.8	44.3
110°	61.4	48.8	42.8	43.3	43.7	44.3	44.8



TEST NUMBER: P331747-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	112.3	66.4	43.6	44.0	44.4	44.8	45.2
115°	174.8	116.5	82.7	73.7	64.6	55.5	46.5
117.5°	344.9	330.8	308.9	279.1	249.3	219.5	189.7
120°	419.9	421.4	413.7	396.6	379.7	362.7	345.7
122.5°	444.8	445.8	444.6	441.2	437.9	434.7	431.3
125°	481.5	482.4	483.0	483.4	483.8	484.1	484.5
127.5°	515.8	517.1	517.8	517.8	517.9	518.0	518.1
130°	537.4	538.8	539.4	539.3	539.2	539.0	538.9
132.5°	558.1	559.3	559.8	559.7	559.6	559.4	559.3
135°	588.0	589.3	589.8	589.5	589.3	589.0	588.7
137.5°	615.7	617.0	617.3	617.0	616.5	616.1	615.6
140°	633.5	634.7	634.9	634.3	633.7	633.0	632.4
142.5°	650.0	651.0	651.3	650.6	650.0	649.4	648.7
145°	673.0	673.9	674.0	673.4	672.8	672.2	671.5
147.5°	693.0	693.6	693.7	693.2	692.6	692.1	691.6
150°	705.5	706.2	706.3	705.7	705.0	704.4	703.8
152.5°	716.8	717.6	717.6	716.8	715.9	715.1	714.2
155°	732.1	732.9	732.8	731.7	730.8	729.8	728.7
157.5°	745.1	746.0	745.9	745.0	743.9	743.0	742.0
160°	752.6	753.3	753.2	752.3	751.5	750.6	749.7
162.5°	759.6	760.5	760.4	759.3	758.2	757.2	756.1
165°	768.3	769.1	769.1	768.3	767.3	766.4	765.6
167.5°	775.4	776.3	776.1	775.0	773.9	772.7	771.6
170°	779.0	779.9	779.7	778.6	777.4	776.3	775.2
172.5°	781.7	782.6	782.4	781.3	780.2	779.0	777.9
175°	784.7	785.5	785.4	784.1	782.8	781.6	780.3
177.5°	784.8	785.5	785.4	784.5	783.6	782.7	781.8
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2

(END OF REPORT)