

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333211-935

Luminaire Tested: **S125DIP-S850D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333211-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D365U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4202.8 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	73	88	81	75	70	73	68	64	65	61	58	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45	42
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30	27
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26	24
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24	22
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	19
10	50	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	2.5
10°-20°	301.0	7.2
20°-30°	444.5	10.6
30°-40°	518.7	12.3
40°-50°	520.9	12.4
50°-60°	457.3	10.9
60°-70°	340.7	8.1
70°-80°	194.8	4.6
80°-90°	57.5	1.4
90°-100°	14.9	0.4
100°-110°	92.0	2.2
110°-120°	166.8	4.0
120°-130°	214.0	5.1
130°-140°	230.2	5.5
140°-150°	216.1	5.1
150°-160°	174.8	4.2
160°-170°	113.0	2.7
170°-180°	39.0	0.9
0°-30°	852.1	20.3
0°-40°	1370.8	32.6
0°-60°	2348.9	55.9
0°-90°	2942.0	70.0
90°-120°	273.7	6.5
90°-150°	934.0	22.2
90°-180°	1261.0	30.0
0°-180°	4202.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	0	3	5	6	7	3
95°	17	16	5	6	6	22
105°	90	91	91	91	90	95
115°	168	169	170	169	167	166
125°	239	241	241	240	239	213
135°	298	300	299	298	297	230
145°	345	346	346	346	344	216
155°	380	379	379	380	378	175
165°	401	400	400	402	399	113
175°	410	409	409	411	409	39
180°	410	410	410	410	410	



TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.4	19.5	19.6	19.7	19.8	19.8	19.8	19.7	19.6	19.5	19.6
90°	0.3	0.9	1.4	1.9	2.5	3.0	3.4	4.0	4.4	4.9	5.2
92.5°	4.6	4.3	4.0	3.5	3.2	3.2	3.6	4.0	4.5	4.9	5.2
95°	17.3	17.1	17.0	16.7	16.5	15.2	12.6	10.0	7.4	4.9	5.2
97.5°	36.2	36.6	36.9	37.3	37.7	35.3	30.2	25.1	20.1	15.0	13.1
100°	50.8	51.1	51.2	51.4	51.7	51.8	52.2	52.4	52.7	53.0	42.9
102.5°	65.7	66.0	66.2	66.5	66.7	66.9	67.1	67.2	67.4	67.6	65.7
105°	89.5	89.7	90.1	90.3	90.6	90.7	90.7	90.7	90.7	90.7	90.7
107.5°	114.2	114.2	114.2	114.2	114.2	114.3	114.4	114.5	114.7	114.8	114.8
110°	130.3	130.3	130.3	130.3	130.3	130.4	130.4	130.6	130.7	130.9	130.7



TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	145.3	145.5	145.7	145.9	146.0	146.1	146.2	146.3	146.4	146.5	146.2
115°	168.0	168.3	168.7	169.0	169.4	169.5	169.6	169.7	169.8	169.8	169.5
117.5°	191.4	191.4	191.4	191.4	191.4	191.5	191.7	192.0	192.3	192.5	192.2
120°	206.0	206.0	206.0	205.9	205.8	205.9	206.0	206.2	206.5	206.6	206.6
122.5°	219.0	219.2	219.5	219.7	220.0	220.2	220.2	220.3	220.4	220.5	220.4
125°	238.9	239.4	239.9	240.3	240.8	241.1	241.1	241.1	241.1	241.1	240.7
127.5°	258.0	258.3	258.6	259.0	259.3	259.5	259.4	259.4	259.3	259.3	259.2
130°	269.7	270.0	270.4	270.7	271.0	271.2	271.3	271.3	271.4	271.5	271.3
132.5°	281.4	281.7	282.1	282.5	282.9	283.0	282.9	282.8	282.6	282.4	282.4
135°	298.0	298.3	298.8	299.2	299.5	299.7	299.5	299.5	299.3	299.2	299.0
137.5°	313.2	313.6	313.9	314.3	314.6	314.8	314.6	314.5	314.4	314.3	314.3
140°	323.2	323.4	323.5	323.6	323.7	323.8	323.7	323.6	323.6	323.6	323.6
142.5°	332.3	332.3	332.4	332.4	332.5	332.6	332.8	332.9	332.9	333.0	333.0
145°	345.4	345.6	345.7	345.9	345.9	346.0	346.0	346.0	346.0	346.0	346.1
147.5°	357.0	357.0	357.0	356.9	356.9	356.9	357.0	357.1	357.1	357.2	357.3
150°	364.3	364.2	364.0	363.9	363.8	363.8	363.9	364.0	364.2	364.3	364.5
152.5°	371.3	371.1	370.7	370.5	370.1	370.1	370.2	370.4	370.5	370.7	370.7
155°	380.5	380.0	379.6	379.2	378.8	378.7	378.8	378.9	379.1	379.2	379.4
157.5°	387.4	387.2	386.9	386.7	386.5	386.3	386.3	386.4	386.4	386.4	386.6
160°	392.3	391.9	391.5	391.1	390.7	390.5	390.5	390.6	390.7	390.8	391.1
162.5°	396.2	395.8	395.4	394.9	394.6	394.4	394.5	394.5	394.6	394.7	395.0
165°	401.4	401.1	400.6	400.2	399.8	399.7	399.7	399.8	399.8	399.9	400.3
167.5°	405.4	404.9	404.5	404.1	403.6	403.5	403.6	403.6	403.7	403.7	404.2
170°	407.5	407.1	406.6	406.1	405.6	405.4	405.5	405.5	405.6	405.7	406.2
172.5°	409.0	408.5	408.0	407.6	407.1	406.9	407.0	407.2	407.3	407.4	407.9
175°	410.5	410.2	409.7	409.3	409.0	408.8	408.8	408.9	409.0	409.1	409.6
177.5°	411.3	411.0	410.6	410.4	410.0	409.8	409.9	410.0	410.0	410.1	410.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	19.7	19.8	19.8	19.7	19.5	19.2	18.9	18.6
90°	5.5	5.9	6.2	6.5	6.7	6.9	7.1	7.3
92.5°	5.5	5.9	6.2	6.5	6.5	6.6	6.7	6.8
95°	5.5	5.9	6.2	6.4	6.4	6.4	6.4	6.4
97.5°	11.2	9.2	7.3	6.4	6.4	6.4	6.4	6.4
100°	32.8	22.7	12.7	7.5	7.2	7.0	6.6	6.4
102.5°	63.7	61.8	59.9	56.7	52.1	47.5	42.9	38.3
105°	90.7	90.7	90.7	90.7	90.6	90.5	90.5	90.4
107.5°	114.9	114.9	114.9	114.8	114.6	114.3	114.2	113.9
110°	130.4	130.3	130.1	130.0	130.1	130.1	130.2	130.3



TEST NUMBER: P333211-935

CATALOG NUMBER: S125DIP-S850D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	145.9	145.7	145.4	145.3	145.2	145.1	145.0	144.9
115°	169.3	169.0	168.8	168.4	168.0	167.6	167.2	166.8
117.5°	191.8	191.5	191.1	190.9	190.7	190.5	190.4	190.2
120°	206.4	206.2	206.1	205.9	205.5	205.2	204.8	204.5
122.5°	220.2	220.2	220.0	219.7	219.3	219.0	218.5	218.2
125°	240.5	240.2	240.0	239.7	239.5	239.4	239.1	238.9
127.5°	259.0	258.8	258.7	258.4	257.9	257.4	256.9	256.4
130°	271.0	270.9	270.7	270.4	270.1	269.8	269.4	269.1
132.5°	282.3	282.3	282.2	282.1	281.7	281.4	281.0	280.8
135°	298.9	298.8	298.6	298.3	298.0	297.6	297.1	296.7
137.5°	314.4	314.4	314.4	314.2	313.8	313.5	313.1	312.8
140°	323.8	323.9	324.1	323.9	323.6	323.1	322.7	322.3
142.5°	333.0	333.1	333.1	332.9	332.5	332.1	331.7	331.3
145°	346.2	346.2	346.3	346.1	345.8	345.3	344.9	344.5
147.5°	357.4	357.5	357.6	357.4	356.9	356.4	355.9	355.4
150°	364.5	364.7	364.8	364.6	364.1	363.6	363.0	362.5
152.5°	370.9	371.0	371.2	371.0	370.5	370.1	369.5	369.0
155°	379.6	379.8	380.0	379.9	379.4	378.8	378.2	377.7
157.5°	386.8	387.0	387.3	387.1	386.6	386.0	385.5	385.0
160°	391.3	391.6	391.8	391.8	391.2	390.6	390.1	389.6
162.5°	395.5	395.8	396.2	396.1	395.5	394.9	394.3	393.7
165°	400.7	401.1	401.6	401.5	401.0	400.4	399.8	399.3
167.5°	404.8	405.2	405.7	405.6	405.0	404.4	403.8	403.2
170°	406.7	407.3	407.9	407.9	407.3	406.7	406.0	405.4
172.5°	408.4	408.9	409.3	409.3	408.7	408.0	407.4	406.8
175°	410.1	410.7	411.2	411.2	410.5	409.9	409.3	408.7
177.5°	410.9	411.2	411.6	411.6	411.1	410.7	410.3	409.8
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)