

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331758-927

Luminaire Tested: **SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331758-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5623.7 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.2
10°-20°	344.8	6.1
20°-30°	484.2	8.6
30°-40°	528.0	9.4
40°-50°	485.4	8.6
50°-60°	381.3	6.8
60°-70°	248.6	4.4
70°-80°	128.2	2.3
80°-90°	37.0	0.7
90°-100°	164.4	2.9
100°-110°	557.8	9.9
110°-120°	592.6	10.5
120°-130°	487.8	8.7
130°-140°	391.8	7.0
140°-150°	296.0	5.3
150°-160°	208.1	3.7
160°-170°	122.5	2.2
170°-180°	39.9	0.7
0°-30°	954.5	17.0
0°-40°	1482.5	26.4
0°-60°	2349.2	41.8
0°-90°	2762.9	49.1
90°-120°	1314.8	23.4
90°-150°	2490.5	44.3
90°-180°	2861.0	50.9
0°-180°	5623.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	1	11	27	26	26	4
95°	28	68	310	117	90	29
105°	96	145	586	1047	891	102
115°	170	215	490	1012	1172	169
125°	237	281	471	819	951	211
135°	278	332	466	689	788	215
145°	318	365	463	575	629	199
155°	361	390	450	509	529	166
165°	394	406	431	457	464	111
175°	410	411	414	420	418	39
180°	411	411	411	411	411	



TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.7	14.4	13.4	12.0	10.5	10.1	10.9	12.0	13.0	13.2	12.8
90°	0.8	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1
92.5°	9.7	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8
95°	27.6	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2
97.5°	45.1	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0
100°	60.8	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5
102.5°	75.4	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8
105°	96.5	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1
107.5°	119.2	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7
110°	134.4	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1



TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.3	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8
115°	170.0	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1
117.5°	192.4	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4
120°	206.4	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8
122.5°	219.7	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0
125°	237.2	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6
127.5°	251.1	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4
130°	259.4	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9
132.5°	266.9	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3
135°	278.3	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7
137.5°	289.1	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3
140°	297.3	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9
142.5°	305.5	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5
145°	317.8	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6
147.5°	331.1	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6
150°	340.0	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5
152.5°	348.8	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1
155°	361.3	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9
157.5°	371.8	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2
160°	378.7	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5
162.5°	385.6	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4
165°	393.7	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0
167.5°	400.4	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8
170°	404.8	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3
172.5°	407.3	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0
175°	410.4	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1
177.5°	411.8	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	12.4	11.9	12.0	12.0	12.0	12.0	12.0	12.0
90°	25.3	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	207.2	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	483.4	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	721.8	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	878.1	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	960.6	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	901.2	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	849.9	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8



TEST NUMBER: P331758-927

CATALOG NUMBER: SA2XXRDIP-C1005D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	803.1	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	745.5	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	702.2	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	680.7	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	663.6	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	638.8	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	614.3	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	598.5	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	583.3	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	562.1	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	545.2	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	534.5	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	525.6	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	513.1	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	503.4	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	496.5	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	489.6	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	479.9	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	468.7	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	461.7	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	454.8	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	444.3	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	434.4	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	429.3	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	423.6	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	417.5	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)