

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333222-935

Luminaire Tested: **S125DIP-S850D590U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333222-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4769.4 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	67	65	59	58	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35	31
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	2.2
10°-20°	301.0	6.3
20°-30°	444.5	9.3
30°-40°	518.7	10.9
40°-50°	520.9	10.9
50°-60°	457.3	9.6
60°-70°	340.7	7.1
70°-80°	194.8	4.1
80°-90°	58.0	1.2
90°-100°	176.6	3.7
100°-110°	379.6	8.0
110°-120°	356.2	7.5
120°-130°	288.7	6.1
130°-140°	231.7	4.9
140°-150°	174.8	3.7
150°-160°	123.1	2.6
160°-170°	72.5	1.5
170°-180°	23.6	0.5
0°-30°	852.1	17.9
0°-40°	1370.8	28.7
0°-60°	2348.9	49.3
0°-90°	2942.5	61.7
90°-120°	912.4	19.1
90°-150°	1607.6	33.7
90°-180°	1827.0	38.3
0°-180°	4769.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	0	4	8	10	11	4
95°	16	48	435	197	116	17
105°	56	78	356	701	651	59
115°	99	120	286	616	725	98
125°	138	161	274	490	571	122
135°	161	194	272	411	474	125
145°	188	215	273	340	374	118
155°	214	230	266	301	314	99
165°	234	240	255	271	275	66
175°	243	243	245	248	247	23
180°	244	244	244	244	244	



TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.4	19.5	19.7	19.9	20.1	20.2	20.1	20.2	20.1	20.1	20.2
90°	0.5	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4
92.5°	6.0	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2
95°	16.2	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9
97.5°	26.9	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8
100°	34.4	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3
102.5°	42.6	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7
105°	55.5	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1
107.5°	68.1	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2
110°	77.1	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6



TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	86.2	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8
115°	99.2	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9
117.5°	111.0	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1
120°	118.8	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8
122.5°	127.1	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8
125°	137.5	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1
127.5°	145.7	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3
130°	150.8	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4
132.5°	154.7	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7
135°	161.1	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1
137.5°	169.2	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1
140°	173.8	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7
142.5°	179.3	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8
145°	187.6	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8
147.5°	196.2	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7
150°	201.4	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4
152.5°	206.9	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7
155°	214.1	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0
157.5°	220.6	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7
160°	225.0	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2
162.5°	228.5	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1
165°	233.8	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3
167.5°	237.3	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7
170°	239.7	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9
172.5°	241.3	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2
175°	243.1	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6
177.5°	244.0	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	20.4	20.5	20.6	20.6	20.3	20.0	19.7	19.5
90°	8.9	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	87.0	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	353.1	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	525.9	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	604.1	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	630.4	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	614.9	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	559.5	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	518.7	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333222-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	486.5	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	445.9	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	419.8	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	405.7	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	395.1	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	379.6	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	363.9	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	354.1	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	344.3	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	331.5	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	320.7	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	314.8	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	309.7	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	303.1	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	296.8	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	293.2	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	289.3	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	283.4	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	277.5	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	273.5	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	269.2	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	263.2	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	257.5	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	254.4	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	250.9	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.4	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)