

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333223-935

Luminaire Tested: **S125DIP-S850D810U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333223-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5763.5 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42	37
3	82	73	65	60	76	67	61	56	58	53	49	49	45	42	40	38	36	32
4	75	64	57	51	69	60	53	48	51	46	42	44	40	36	36	33	31	27
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	29	27	24
6	64	52	43	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6803	6803	6803	6803
5°	7878	6825	5977	6825
10°	9165	6790	5237	6790
15°	10146	6740	4831	6740
20°	11357	6661	4504	6661
25°	13304	6572	4345	6572
30°	14370	6485	4207	6485
35°	11815	6320	4117	6320
40°	8398	6091	4018	6091
45°	6452	5782	3961	5782
50°	5507	5399	3953	5399
55°	4904	5024	3987	5024
60°	4423	4614	4088	4614
65°	4085	4201	4195	4201
70°	3714	3773	4254	3773
75°	3281	3324	4217	3324
80°	2760	2708	3861	2708
85°	2186	1949	3112	1949



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.4	1.8
10°-20°	301.9	5.2
20°-30°	490.2	8.5
30°-40°	598.0	10.4
40°-50°	544.0	9.4
50°-60°	433.3	7.5
60°-70°	301.8	5.2
70°-80°	160.9	2.8
80°-90°	42.5	0.7
90°-100°	33.0	0.6
100°-110°	203.4	3.5
110°-120°	369.0	6.4
120°-130°	473.5	8.2
130°-140°	509.3	8.8
140°-150°	478.1	8.3
150°-160°	386.7	6.7
160°-170°	250.1	4.3
170°-180°	86.3	1.5
0°-30°	893.6	15.5
0°-40°	1491.6	25.9
0°-60°	2468.9	42.8
0°-90°	2974.2	51.6
90°-120°	605.4	10.5
90°-150°	2066.3	35.9
90°-180°	2789.0	48.4
0°-180°	5763.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1215	1053	922	1053	1215	122
15°	1517	1008	722	1008	1517	434
25°	1867	922	610	922	1867	853
35°	1499	802	522	802	1499	917
45°	706	633	434	633	706	565
55°	436	446	354	446	436	392
65°	267	275	274	275	267	265
75°	132	133	169	133	132	142
85°	30	26	42	26	30	34
90°	16	1	16	1	16	8
95°	14	38	14	38	14	12
105°	200	198	200	198	200	181
115°	369	372	369	372	369	366
125°	529	529	529	529	529	470
135°	656	659	656	659	656	507
145°	762	764	762	764	762	476
155°	836	842	836	842	836	385
165°	883	888	883	888	883	249
175°	904	908	904	908	904	86
180°	908	908	908	908	908	



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1114.1	1112.7	1111.3	1108.4	1110.5	1104.5	1101.6	1096.6	1090.5	1088.4	1085.9
5°	1215.1	1217.4	1219.6	1210.2	1211.2	1204.9	1190.6	1179.0	1169.6	1157.5	1149.0
7.5°	1336.8	1331.5	1331.0	1325.0	1314.5	1306.1	1291.1	1272.0	1253.4	1232.3	1214.9
10°	1397.6	1398.0	1394.0	1386.8	1375.7	1367.6	1348.0	1329.1	1306.4	1279.5	1260.3
12.5°	1443.4	1445.2	1440.1	1430.5	1425.0	1407.0	1391.5	1369.2	1342.1	1320.7	1291.4
15°	1517.4	1512.4	1508.9	1496.8	1487.5	1468.7	1444.1	1420.8	1391.3	1364.0	1336.8
17.5°	1588.7	1592.7	1586.0	1574.9	1545.8	1523.9	1490.9	1459.1	1422.4	1385.8	1353.2
20°	1652.4	1656.0	1645.7	1626.5	1591.6	1569.7	1526.3	1485.2	1442.7	1395.8	1360.0
22.5°	1731.8	1729.0	1715.1	1685.8	1655.6	1615.1	1568.1	1518.1	1464.9	1411.9	1364.3
25°	1867.0	1848.2	1839.7	1803.5	1763.8	1704.3	1639.9	1566.6	1500.4	1430.2	1369.4
27.5°	1941.9	1936.0	1926.6	1901.3	1859.5	1796.0	1720.0	1630.6	1537.3	1448.7	1369.2
30°	1926.9	1927.8	1928.7	1920.6	1893.9	1846.0	1770.5	1674.3	1563.4	1463.7	1371.7
32.5°	1793.9	1810.2	1825.7	1844.1	1851.6	1842.5	1795.1	1708.3	1594.2	1480.9	1370.2
35°	1498.6	1503.6	1554.0	1604.1	1672.1	1724.8	1760.1	1721.7	1625.6	1495.5	1368.5
37.5°	1168.5	1192.7	1227.6	1284.2	1382.2	1470.1	1583.0	1635.0	1604.0	1500.2	1365.4
40°	996.1	1018.5	1041.2	1098.9	1181.6	1288.1	1416.3	1525.9	1551.3	1485.2	1354.6
42.5°	863.1	880.7	906.0	949.4	1018.6	1112.8	1235.4	1378.5	1466.6	1441.6	1332.1
45°	706.4	717.6	737.3	771.6	821.7	895.5	1003.7	1160.2	1296.5	1341.7	1278.7
47.5°	604.6	604.5	619.8	643.6	679.8	742.4	822.4	945.0	1090.7	1198.4	1193.4
50°	548.1	545.9	557.9	578.5	607.1	648.7	725.1	823.0	963.0	1085.0	1119.0
52.5°	499.5	499.7	507.1	522.4	546.3	581.9	638.9	727.2	846.8	972.1	1036.0
55°	435.5	433.7	442.1	452.5	469.8	493.1	534.3	601.8	698.8	822.2	905.3
57.5°	376.8	381.7	385.1	392.3	406.7	422.3	457.0	506.5	583.5	689.4	777.3
60°	342.4	347.4	350.1	357.2	368.9	382.3	409.1	449.4	514.1	605.4	692.5
62.5°	311.7	315.6	316.4	322.9	332.3	345.4	366.5	400.3	451.5	531.3	616.7
65°	267.3	267.3	269.1	275.9	280.3	292.0	308.1	332.6	373.8	435.9	508.8
67.5°	224.6	226.8	226.3	229.3	233.4	242.4	253.9	274.2	304.7	350.1	408.4
70°	196.7	198.5	198.0	200.3	204.7	210.6	220.0	239.2	261.1	300.0	350.1
72.5°	171.7	172.4	171.3	174.2	176.8	181.9	192.4	202.7	223.2	256.0	297.1
75°	131.5	132.3	133.2	135.0	137.7	140.3	145.8	156.0	169.4	194.1	220.4
77.5°	98.5	96.9	99.0	98.8	100.2	102.3	107.0	112.4	123.5	139.1	159.5
80°	74.2	74.6	74.6	75.1	77.3	78.7	82.7	86.7	95.2	106.9	121.1
82.5°	54.2	55.4	54.7	55.4	57.3	58.3	60.5	63.8	68.8	77.9	88.3
85°	29.5	27.3	28.2	29.1	29.1	29.5	31.3	32.6	35.3	38.9	42.9
87.5°	11.8	12.5	12.7	12.7	12.9	12.7	14.0	13.9	14.8	15.8	17.0
90°	16.2	15.7	15.2	14.8	14.4	13.8	13.0	12.3	11.5	10.8	9.7
92.5°	15.1	14.9	14.6	14.5	14.2	13.8	13.0	12.3	11.5	10.8	9.8
95°	14.1	14.1	14.1	14.1	14.1	13.8	13.0	12.3	11.5	10.8	16.4
97.5°	14.1	14.1	14.1	14.1	14.1	16.3	20.5	24.7	28.9	33.1	44.3
100°	14.1	14.7	15.3	15.9	16.5	28.0	50.3	72.6	94.9	117.2	116.6
102.5°	84.7	94.9	105.0	115.2	125.4	132.6	136.8	141.0	145.3	149.5	149.1
105°	200.0	200.1	200.3	200.4	200.6	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.1	252.5	253.0	253.5	253.9	254.1	254.1	254.1	254.0	254.0	253.7
110°	288.2	288.0	287.9	287.7	287.6	287.7	288.2	288.6	289.1	289.6	289.2



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	320.6	320.7	320.9	321.2	321.3	321.8	322.3	322.9	323.5	324.0	323.8
115°	369.0	369.9	370.7	371.7	372.6	373.3	373.9	374.5	375.1	375.7	375.6
117.5°	420.7	421.1	421.5	421.9	422.2	422.8	423.6	424.4	425.2	425.9	425.4
120°	452.5	453.2	454.0	454.7	455.5	456.0	456.3	456.6	456.9	457.2	456.8
122.5°	482.7	483.5	484.4	485.3	486.1	486.7	487.0	487.3	487.6	487.9	487.7
125°	528.6	529.0	529.4	529.9	530.4	530.9	531.5	532.1	532.7	533.3	533.3
127.5°	567.2	568.3	569.5	570.6	571.6	572.4	572.7	573.0	573.3	573.7	573.8
130°	595.2	596.0	596.8	597.4	598.2	598.8	599.3	599.7	600.2	600.6	600.5
132.5°	621.1	621.8	622.6	623.4	624.1	624.5	624.6	624.7	624.7	624.8	625.2
135°	656.5	657.4	658.3	659.2	660.1	660.7	661.0	661.3	661.6	661.9	662.2
137.5°	692.1	692.8	693.6	694.4	695.2	695.5	695.4	695.4	695.3	695.3	695.6
140°	713.1	713.9	714.9	715.7	716.7	717.0	716.7	716.4	716.1	715.7	715.9
142.5°	733.0	733.9	734.8	735.7	736.6	737.0	736.9	736.9	736.8	736.8	736.6
145°	762.2	763.1	764.1	764.9	765.8	766.2	766.0	765.9	765.8	765.6	765.6
147.5°	786.4	787.4	788.5	789.5	790.7	791.1	790.9	790.7	790.6	790.4	790.2
150°	801.9	803.1	804.3	805.6	806.8	807.2	806.9	806.6	806.3	806.0	805.7
152.5°	816.5	817.6	818.6	819.8	820.8	821.2	820.9	820.6	820.3	820.0	819.7
155°	835.6	836.8	838.0	839.2	840.4	840.8	840.3	839.9	839.4	839.0	838.7
157.5°	851.6	852.8	854.0	855.2	856.4	856.8	856.4	855.8	855.3	854.9	854.8
160°	861.9	863.1	864.3	865.5	866.7	866.9	866.3	865.7	865.1	864.5	864.4
162.5°	871.1	872.4	873.7	874.9	876.3	876.5	875.7	874.9	874.0	873.2	873.1
165°	883.4	884.6	885.8	887.0	888.2	888.4	887.4	886.6	885.7	884.8	884.6
167.5°	892.1	893.4	894.8	896.0	897.4	897.6	896.5	895.4	894.3	893.3	893.1
170°	896.9	898.2	899.6	901.0	902.2	902.3	901.1	899.9	898.8	897.6	897.4
172.5°	900.1	901.5	902.8	904.1	905.5	905.7	904.6	903.4	902.4	901.3	901.0
175°	904.3	905.7	907.0	908.4	909.6	909.7	908.5	907.3	906.2	905.0	904.8
177.5°	906.7	907.7	908.6	909.6	910.6	910.6	909.7	909.0	908.1	907.2	907.1
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1083.7	1081.2	1078.3	1073.3	1067.3	1064.0	1059.0	1055.8	1049.4	1044.0	1038.3
5°	1138.7	1127.0	1116.4	1102.5	1087.3	1077.5	1065.8	1052.8	1039.5	1025.6	1010.4
7.5°	1195.7	1175.1	1152.7	1128.7	1105.2	1083.6	1062.9	1042.6	1023.6	1000.7	981.4
10°	1233.9	1208.0	1180.3	1147.6	1115.9	1088.2	1060.1	1035.4	1010.4	983.6	959.8
12.5°	1272.2	1237.7	1198.5	1162.7	1124.5	1091.1	1057.9	1026.5	995.1	965.4	937.7
15°	1299.2	1268.8	1232.6	1181.6	1138.7	1092.7	1048.9	1008.1	970.2	937.1	902.2
17.5°	1317.0	1277.8	1239.0	1190.1	1133.8	1082.3	1032.7	986.1	943.2	901.3	867.7
20°	1320.3	1280.0	1239.3	1191.5	1133.8	1074.8	1025.2	969.2	923.3	879.9	838.7
22.5°	1319.1	1273.6	1229.2	1180.0	1123.8	1069.4	1009.4	952.4	902.5	859.8	816.9
25°	1309.1	1260.3	1204.9	1155.3	1099.8	1042.2	981.4	922.3	871.3	822.6	780.2
27.5°	1300.6	1237.4	1174.7	1116.8	1063.2	1010.4	952.2	891.7	835.3	785.8	745.8
30°	1290.3	1221.0	1150.3	1089.9	1035.0	983.6	928.6	869.6	810.5	762.2	719.4
32.5°	1281.0	1200.2	1125.7	1060.0	1001.7	951.7	901.0	844.9	787.0	738.0	695.0
35°	1263.0	1169.6	1084.2	1010.0	947.8	896.4	853.9	801.6	748.4	701.0	659.9
37.5°	1240.2	1129.3	1037.7	959.8	891.7	837.6	798.1	757.9	706.8	661.2	624.0
40°	1222.3	1100.7	1003.7	924.1	853.5	797.1	760.5	722.5	680.0	637.6	598.2
42.5°	1199.8	1075.0	969.4	883.7	813.7	758.9	720.4	688.1	650.7	611.1	574.5
45°	1158.4	1028.3	913.9	821.7	751.1	697.0	657.2	633.1	604.9	567.3	536.5
47.5°	1097.5	972.2	853.9	758.8	685.9	635.8	598.5	575.3	555.4	527.5	499.6
50°	1043.4	930.4	810.5	716.2	643.3	592.8	558.4	537.4	520.4	498.9	475.3
52.5°	983.0	877.8	768.0	674.8	602.6	552.8	519.1	500.6	486.5	471.1	447.7
55°	887.0	797.6	695.7	607.1	540.5	491.8	462.3	446.2	434.5	422.9	408.6
57.5°	781.2	711.3	621.0	540.1	478.7	434.4	406.8	391.2	382.2	376.2	367.7
60°	706.8	647.0	569.1	495.3	435.5	396.1	369.3	357.2	349.7	344.7	338.5
62.5°	637.8	588.7	516.5	449.2	396.8	359.6	335.7	324.0	316.7	314.3	309.1
65°	536.1	498.1	438.6	382.7	338.0	306.3	286.1	274.9	270.4	267.8	268.3
67.5°	435.8	412.7	364.9	317.3	281.5	254.9	238.8	230.2	228.0	224.5	224.4
70°	374.6	357.2	317.0	275.4	243.7	223.1	208.8	199.8	197.6	195.8	195.4
72.5°	320.6	305.4	270.4	237.1	208.6	190.5	178.7	173.4	169.7	168.7	168.6
75°	241.0	232.5	204.7	178.4	158.7	146.2	138.2	133.2	130.5	130.1	130.5
77.5°	171.3	163.9	146.3	127.6	115.2	105.7	98.9	97.2	94.2	94.3	93.8
80°	128.7	123.8	112.7	97.9	87.6	79.6	76.0	72.8	72.0	70.6	72.0
82.5°	93.3	88.1	80.5	71.1	62.6	57.8	54.2	53.2	52.7	52.0	52.3
85°	46.1	46.5	42.0	34.9	31.3	28.6	26.3	26.3	25.9	25.5	25.9
87.5°	17.5	16.5	14.9	13.6	11.6	10.2	9.6	9.8	9.0	8.9	9.5
90°	8.7	7.7	6.5	5.4	4.3	3.1	1.9	0.7	1.9	3.1	4.3
92.5°	9.0	8.0	7.1	7.1	7.8	8.7	9.6	10.3	9.6	8.7	7.8
95°	22.1	27.8	33.5	36.6	37.0	37.5	38.0	38.4	38.0	37.5	37.0
97.5°	55.6	66.9	78.2	83.3	82.6	81.7	80.9	80.2	80.9	81.7	82.6
100°	116.0	115.4	114.8	114.3	113.8	113.3	112.9	112.4	112.9	113.3	113.8
102.5°	148.8	148.4	148.0	147.6	147.0	146.5	145.9	145.3	145.9	146.5	147.0
105°	200.6	200.6	200.6	200.4	199.8	199.1	198.5	197.9	198.5	199.1	199.8
107.5°	253.4	253.0	252.8	252.6	252.6	252.6	252.6	252.6	252.6	252.6	252.6
110°	289.0	288.6	288.3	288.2	288.2	288.2	288.2	288.2	288.2	288.2	288.2



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	323.6	323.5	323.3	323.0	322.7	322.3	321.9	321.6	321.9	322.3	322.7
115°	375.4	375.3	375.1	374.7	373.9	373.2	372.5	371.7	372.5	373.2	373.9
117.5°	424.8	424.2	423.7	423.4	423.4	423.4	423.5	423.5	423.5	423.4	423.4
120°	456.3	455.8	455.4	455.2	455.4	455.6	455.7	455.8	455.7	455.6	455.4
122.5°	487.5	487.2	487.1	486.6	486.1	485.5	485.0	484.4	485.0	485.5	486.1
125°	533.3	533.3	533.3	532.8	531.8	530.6	529.6	528.6	529.6	530.6	531.8
127.5°	573.9	573.9	574.0	573.7	573.0	572.2	571.4	570.8	571.4	572.2	573.0
130°	600.3	600.2	600.0	599.6	598.8	598.1	597.4	596.6	597.4	598.1	598.8
132.5°	625.5	625.9	626.2	625.9	625.0	624.1	623.3	622.4	623.3	624.1	625.0
135°	662.5	662.8	663.1	662.8	661.9	661.0	660.1	659.2	660.1	661.0	661.9
137.5°	695.9	696.1	696.4	696.1	695.3	694.6	693.8	693.0	693.8	694.6	695.3
140°	716.1	716.2	716.4	716.3	716.0	715.7	715.4	715.1	715.4	715.7	716.0
142.5°	736.3	736.2	735.9	735.7	735.6	735.4	735.2	735.0	735.2	735.4	735.6
145°	765.6	765.6	765.6	765.4	765.2	764.8	764.6	764.2	764.6	764.8	765.2
147.5°	790.0	789.8	789.6	789.6	789.6	789.7	789.8	789.8	789.8	789.7	789.6
150°	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	805.7	805.4	805.1
152.5°	819.4	819.1	818.8	819.0	819.7	820.3	821.0	821.7	821.0	820.3	819.7
155°	838.4	838.1	837.8	838.1	839.0	839.9	840.8	841.7	840.8	839.9	839.0
157.5°	854.8	854.8	854.7	855.0	855.6	856.1	856.6	857.1	856.6	856.1	855.6
160°	864.3	864.1	864.0	864.4	865.2	866.2	867.0	868.0	867.0	866.2	865.2
162.5°	872.9	872.7	872.6	873.0	873.8	874.8	875.6	876.6	875.6	874.8	873.8
165°	884.5	884.3	884.2	884.5	885.5	886.3	887.3	888.1	887.3	886.3	885.5
167.5°	892.9	892.8	892.7	893.0	894.0	894.9	895.9	896.7	895.9	894.9	894.0
170°	897.2	897.1	897.0	897.4	898.5	899.5	900.5	901.6	900.5	899.5	898.5
172.5°	900.8	900.5	900.3	900.6	901.7	902.8	903.8	904.8	903.8	902.8	901.7
175°	904.7	904.5	904.4	904.7	905.7	906.5	907.4	908.4	907.4	906.5	905.7
177.5°	907.0	906.9	906.8	907.1	907.8	908.5	909.2	910.0	909.2	908.5	907.8
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1035.1	1031.1	1027.9	1020.8	1016.8	1011.5	1007.2	1011.8	1006.9	1009.0	1005.7
5°	1002.8	990.3	981.4	968.4	957.2	946.9	939.4	938.0	934.4	932.6	927.2
7.5°	964.0	948.3	933.0	916.0	901.6	887.1	877.8	870.1	865.0	858.3	853.8
10°	941.1	920.1	902.2	881.7	863.8	848.1	835.6	829.3	823.5	815.0	811.9
12.5°	912.8	891.1	869.3	847.3	830.2	812.7	801.9	792.5	788.5	778.9	777.9
15°	879.0	846.4	824.8	802.5	778.8	764.5	755.5	745.3	740.8	734.1	729.2
17.5°	838.5	809.4	782.6	759.4	739.1	727.0	715.9	708.9	701.2	696.8	688.8
20°	809.3	781.5	754.7	730.0	714.5	700.6	691.6	684.9	676.9	674.7	666.6
22.5°	784.5	754.0	728.2	707.6	690.4	674.9	665.1	660.6	655.0	648.2	646.5
25°	744.4	712.6	690.8	670.2	655.0	640.7	634.0	628.2	622.8	617.9	616.0
27.5°	709.7	681.3	655.3	636.7	623.5	610.4	604.5	597.4	593.6	589.6	584.8
30°	685.4	656.3	633.5	615.6	601.3	589.7	583.4	578.5	575.0	571.4	568.7
32.5°	660.3	633.4	611.3	593.8	579.5	570.8	565.2	561.7	557.8	553.5	550.1
35°	627.2	597.7	576.3	561.1	549.9	543.2	536.9	533.8	529.3	529.3	525.7
37.5°	590.0	564.5	545.5	531.7	521.7	515.7	508.9	506.7	503.9	502.0	500.8
40°	567.8	544.1	526.2	512.4	501.6	496.7	491.4	487.8	485.9	483.7	482.8
42.5°	544.9	522.3	505.1	492.3	483.0	478.8	473.8	471.3	467.7	464.8	464.3
45°	510.1	488.2	472.6	462.3	454.3	449.4	446.2	440.8	439.0	435.5	435.0
47.5°	477.1	456.1	440.7	432.3	425.2	421.2	416.3	411.0	408.9	407.1	406.9
50°	452.5	433.3	418.9	410.9	404.2	398.4	393.4	389.9	388.5	388.5	389.4
52.5°	427.4	411.0	398.9	389.1	382.7	376.5	372.0	369.8	367.7	369.9	371.5
55°	390.7	374.2	365.2	355.9	349.7	342.4	340.3	339.3	338.0	341.6	343.4
57.5°	352.0	340.4	329.8	320.6	315.0	310.8	307.8	307.2	309.7	311.4	317.3
60°	327.3	313.8	304.4	297.3	290.6	287.9	287.1	286.1	287.9	292.8	300.4
62.5°	300.1	289.2	279.1	273.7	268.8	264.3	264.2	264.7	268.3	273.9	281.5
65°	260.2	250.8	244.1	237.8	233.8	231.2	232.0	233.8	237.8	245.5	253.9
67.5°	219.7	213.3	207.2	202.2	198.3	198.3	199.2	201.9	206.6	215.4	223.2
70°	193.6	186.4	181.5	179.3	176.2	174.4	177.0	181.5	185.5	193.6	200.3
72.5°	167.5	161.4	157.6	156.0	154.7	153.3	154.1	158.9	164.5	172.5	180.3
75°	128.7	126.5	123.8	122.1	120.7	121.6	122.5	127.0	131.5	139.9	148.9
77.5°	93.9	91.6	90.1	89.6	88.9	89.3	91.9	95.1	99.5	105.7	112.4
80°	71.1	70.2	69.3	68.9	68.9	69.3	72.8	75.1	79.1	85.0	90.3
82.5°	51.7	51.2	51.1	51.0	51.3	51.4	53.6	56.5	59.8	64.2	68.9
85°	27.3	26.3	27.7	28.2	27.3	28.6	29.5	31.3	32.6	34.9	37.1
87.5°	10.1	10.9	10.8	11.4	11.6	12.5	12.3	13.9	14.7	15.7	15.4
90°	5.4	6.5	7.7	8.7	9.7	10.8	11.5	12.3	13.0	13.8	14.4
92.5°	7.1	7.1	8.0	9.0	9.8	10.8	11.5	12.3	13.0	13.8	14.2
95°	36.6	33.5	27.8	22.1	16.4	10.8	11.5	12.3	13.0	13.8	14.1
97.5°	83.3	78.2	66.9	55.6	44.3	33.1	28.9	24.7	20.5	16.3	14.1
100°	114.3	114.8	115.4	116.0	116.6	117.2	94.9	72.6	50.3	28.0	16.5
102.5°	147.6	148.0	148.4	148.8	149.1	149.5	145.3	141.0	136.8	132.6	125.4
105°	200.4	200.6	200.6	200.6	200.6	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.8	253.0	253.4	253.7	254.0	254.0	254.1	254.1	254.1	253.9
110°	288.2	288.3	288.6	289.0	289.2	289.6	289.1	288.6	288.2	287.7	287.6



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	323.0	323.3	323.5	323.6	323.8	324.0	323.5	322.9	322.3	321.8	321.3
115°	374.7	375.1	375.3	375.4	375.6	375.7	375.1	374.5	373.9	373.3	372.6
117.5°	423.4	423.7	424.2	424.8	425.4	425.9	425.2	424.4	423.6	422.8	422.2
120°	455.2	455.4	455.8	456.3	456.8	457.2	456.9	456.6	456.3	456.0	455.5
122.5°	486.6	487.1	487.2	487.5	487.7	487.9	487.6	487.3	487.0	486.7	486.1
125°	532.8	533.3	533.3	533.3	533.3	533.3	532.7	532.1	531.5	530.9	530.4
127.5°	573.7	574.0	573.9	573.9	573.8	573.7	573.3	573.0	572.7	572.4	571.6
130°	599.6	600.0	600.2	600.3	600.5	600.6	600.2	599.7	599.3	598.8	598.2
132.5°	625.9	626.2	625.9	625.5	625.2	624.8	624.7	624.7	624.6	624.5	624.1
135°	662.8	663.1	662.8	662.5	662.2	661.9	661.6	661.3	661.0	660.7	660.1
137.5°	696.1	696.4	696.1	695.9	695.6	695.3	695.3	695.4	695.4	695.5	695.2
140°	716.3	716.4	716.2	716.1	715.9	715.7	716.1	716.4	716.7	717.0	716.7
142.5°	735.7	735.9	736.2	736.3	736.6	736.8	736.8	736.9	736.9	737.0	736.6
145°	765.4	765.6	765.6	765.6	765.6	765.6	765.8	765.9	766.0	766.2	765.8
147.5°	789.6	789.6	789.8	790.0	790.2	790.4	790.6	790.7	790.9	791.1	790.7
150°	804.8	804.8	805.1	805.4	805.7	806.0	806.3	806.6	806.9	807.2	806.8
152.5°	819.0	818.8	819.1	819.4	819.7	820.0	820.3	820.6	820.9	821.2	820.8
155°	838.1	837.8	838.1	838.4	838.7	839.0	839.4	839.9	840.3	840.8	840.4
157.5°	855.0	854.7	854.8	854.8	854.8	854.9	855.3	855.8	856.4	856.8	856.4
160°	864.4	864.0	864.1	864.3	864.4	864.5	865.1	865.7	866.3	866.9	866.7
162.5°	873.0	872.6	872.7	872.9	873.1	873.2	874.0	874.9	875.7	876.5	876.3
165°	884.5	884.2	884.3	884.5	884.6	884.8	885.7	886.6	887.4	888.4	888.2
167.5°	893.0	892.7	892.8	892.9	893.1	893.3	894.3	895.4	896.5	897.6	897.4
170°	897.4	897.0	897.1	897.2	897.4	897.6	898.8	899.9	901.1	902.3	902.2
172.5°	900.6	900.3	900.5	900.8	901.0	901.3	902.4	903.4	904.6	905.7	905.5
175°	904.7	904.4	904.5	904.7	904.8	905.0	906.2	907.3	908.5	909.7	909.6
177.5°	907.1	906.8	906.9	907.0	907.1	907.2	908.1	909.0	909.7	910.6	910.6
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1003.6	1006.1	1003.9	1006.9	1003.9	1006.1	1003.6	1005.7	1009.0	1006.9	1011.8
5°	925.0	921.0	923.7	921.9	923.7	921.0	925.0	927.2	932.6	934.4	938.0
7.5°	852.4	848.5	844.2	842.1	844.2	848.5	852.4	853.8	858.3	865.0	870.1
10°	807.0	802.0	801.6	798.5	801.6	802.0	807.0	811.9	815.0	823.5	829.3
12.5°	773.7	769.1	764.1	762.8	764.1	769.1	773.7	777.9	778.9	788.5	792.5
15°	726.5	722.9	719.8	722.5	719.8	722.9	726.5	729.2	734.1	740.8	745.3
17.5°	687.3	684.3	683.7	680.4	683.7	684.3	687.3	688.8	696.8	701.2	708.9
20°	662.5	660.3	661.2	655.4	661.2	660.3	662.5	666.6	674.7	676.9	684.9
22.5°	642.9	638.5	638.0	636.8	638.0	638.5	642.9	646.5	648.2	655.0	660.6
25°	612.1	609.8	607.6	609.8	607.6	609.8	612.1	616.0	617.9	622.8	628.2
27.5°	585.1	582.5	581.9	582.1	581.9	582.5	585.1	584.8	589.6	593.6	597.4
30°	568.7	564.2	564.6	564.2	564.6	564.2	568.7	568.7	571.4	575.0	578.5
32.5°	550.8	547.8	547.2	546.3	547.2	547.8	550.8	550.1	553.5	557.8	561.7
35°	524.4	524.4	522.2	522.2	522.2	524.4	524.4	525.7	529.3	529.3	533.8
37.5°	499.6	499.2	497.8	498.1	497.8	499.2	499.6	500.8	502.0	503.9	506.7
40°	481.0	480.6	479.2	476.6	479.2	480.6	481.0	482.8	483.7	485.9	487.8
42.5°	463.1	461.7	461.1	460.1	461.1	461.7	463.1	464.3	464.8	467.7	471.3
45°	435.0	435.0	434.1	433.7	434.1	435.0	435.0	435.0	435.5	439.0	440.8
47.5°	407.7	408.5	410.2	409.9	410.2	408.5	407.7	406.9	407.1	408.9	411.0
50°	391.2	391.7	393.0	393.4	393.0	391.7	391.2	389.4	388.5	388.5	389.9
52.5°	373.0	375.6	377.2	376.9	377.2	375.6	373.0	371.5	369.9	367.7	369.8
55°	347.4	350.5	353.6	354.1	353.6	350.5	347.4	343.4	341.6	338.0	339.3
57.5°	322.1	326.5	329.8	330.8	329.8	326.5	322.1	317.3	311.4	309.7	307.2
60°	304.9	310.7	314.8	316.5	314.8	310.7	304.9	300.4	292.8	287.9	286.1
62.5°	288.4	295.0	299.0	299.4	299.0	295.0	288.4	281.5	273.9	268.3	264.7
65°	261.6	268.3	271.8	274.5	271.8	268.3	261.6	253.9	245.5	237.8	233.8
67.5°	232.6	239.3	243.2	245.4	243.2	239.3	232.6	223.2	215.4	206.6	201.9
70°	211.5	218.2	223.5	225.3	223.5	218.2	211.5	200.3	193.6	185.5	181.5
72.5°	190.7	196.7	201.0	203.1	201.0	196.7	190.7	180.3	172.5	164.5	158.9
75°	154.7	162.7	166.8	169.0	166.8	162.7	154.7	148.9	139.9	131.5	127.0
77.5°	119.2	126.7	129.1	130.2	129.1	126.7	119.2	112.4	105.7	99.5	95.1
80°	95.7	100.1	103.2	103.8	103.2	100.1	95.7	90.3	85.0	79.1	75.1
82.5°	73.5	77.2	78.3	79.4	78.3	77.2	73.5	68.9	64.2	59.8	56.5
85°	40.2	42.0	42.4	42.0	42.4	42.0	40.2	37.1	34.9	32.6	31.3
87.5°	16.2	15.9	16.0	16.8	16.0	15.9	16.2	15.4	15.7	14.7	13.9
90°	14.8	15.2	15.7	16.2	15.7	15.2	14.8	14.4	13.8	13.0	12.3
92.5°	14.5	14.6	14.9	15.1	14.9	14.6	14.5	14.2	13.8	13.0	12.3
95°	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	13.8	13.0	12.3
97.5°	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	16.3	20.5	24.7
100°	15.9	15.3	14.7	14.1	14.7	15.3	15.9	16.5	28.0	50.3	72.6
102.5°	115.2	105.0	94.9	84.7	94.9	105.0	115.2	125.4	132.6	136.8	141.0
105°	200.4	200.3	200.1	200.0	200.1	200.3	200.4	200.6	200.6	200.6	200.6
107.5°	253.5	253.0	252.5	252.1	252.5	253.0	253.5	253.9	254.1	254.1	254.1
110°	287.7	287.9	288.0	288.2	288.0	287.9	287.7	287.6	287.7	288.2	288.6



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	321.2	320.9	320.7	320.6	320.7	320.9	321.2	321.3	321.8	322.3	322.9
115°	371.7	370.7	369.9	369.0	369.9	370.7	371.7	372.6	373.3	373.9	374.5
117.5°	421.9	421.5	421.1	420.7	421.1	421.5	421.9	422.2	422.8	423.6	424.4
120°	454.7	454.0	453.2	452.5	453.2	454.0	454.7	455.5	456.0	456.3	456.6
122.5°	485.3	484.4	483.5	482.7	483.5	484.4	485.3	486.1	486.7	487.0	487.3
125°	529.9	529.4	529.0	528.6	529.0	529.4	529.9	530.4	530.9	531.5	532.1
127.5°	570.6	569.5	568.3	567.2	568.3	569.5	570.6	571.6	572.4	572.7	573.0
130°	597.4	596.8	596.0	595.2	596.0	596.8	597.4	598.2	598.8	599.3	599.7
132.5°	623.4	622.6	621.8	621.1	621.8	622.6	623.4	624.1	624.5	624.6	624.7
135°	659.2	658.3	657.4	656.5	657.4	658.3	659.2	660.1	660.7	661.0	661.3
137.5°	694.4	693.6	692.8	692.1	692.8	693.6	694.4	695.2	695.5	695.4	695.4
140°	715.7	714.9	713.9	713.1	713.9	714.9	715.7	716.7	717.0	716.7	716.4
142.5°	735.7	734.8	733.9	733.0	733.9	734.8	735.7	736.6	737.0	736.9	736.9
145°	764.9	764.1	763.1	762.2	763.1	764.1	764.9	765.8	766.2	766.0	765.9
147.5°	789.5	788.5	787.4	786.4	787.4	788.5	789.5	790.7	791.1	790.9	790.7
150°	805.6	804.3	803.1	801.9	803.1	804.3	805.6	806.8	807.2	806.9	806.6
152.5°	819.8	818.6	817.6	816.5	817.6	818.6	819.8	820.8	821.2	820.9	820.6
155°	839.2	838.0	836.8	835.6	836.8	838.0	839.2	840.4	840.8	840.3	839.9
157.5°	855.2	854.0	852.8	851.6	852.8	854.0	855.2	856.4	856.8	856.4	855.8
160°	865.5	864.3	863.1	861.9	863.1	864.3	865.5	866.7	866.9	866.3	865.7
162.5°	874.9	873.7	872.4	871.1	872.4	873.7	874.9	876.3	876.5	875.7	874.9
165°	887.0	885.8	884.6	883.4	884.6	885.8	887.0	888.2	888.4	887.4	886.6
167.5°	896.0	894.8	893.4	892.1	893.4	894.8	896.0	897.4	897.6	896.5	895.4
170°	901.0	899.6	898.2	896.9	898.2	899.6	901.0	902.2	902.3	901.1	899.9
172.5°	904.1	902.8	901.5	900.1	901.5	902.8	904.1	905.5	905.7	904.6	903.4
175°	908.4	907.0	905.7	904.3	905.7	907.0	908.4	909.6	909.7	908.5	907.3
177.5°	909.6	908.6	907.7	906.7	907.7	908.6	909.6	910.6	910.6	909.7	909.0
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1007.2	1011.5	1016.8	1020.8	1027.9	1031.1	1035.1	1038.3	1044.0	1049.4	1055.8
5°	939.4	946.9	957.2	968.4	981.4	990.3	1002.8	1010.4	1025.6	1039.5	1052.8
7.5°	877.8	887.1	901.6	916.0	933.0	948.3	964.0	981.4	1000.7	1023.6	1042.6
10°	835.6	848.1	863.8	881.7	902.2	920.1	941.1	959.8	983.6	1010.4	1035.4
12.5°	801.9	812.7	830.2	847.3	869.3	891.1	912.8	937.7	965.4	995.1	1026.5
15°	755.5	764.5	778.8	802.5	824.8	846.4	879.0	902.2	937.1	970.2	1008.1
17.5°	715.9	727.0	739.1	759.4	782.6	809.4	838.5	867.7	901.3	943.2	986.1
20°	691.6	700.6	714.5	730.0	754.7	781.5	809.3	838.7	879.9	923.3	969.2
22.5°	665.1	674.9	690.4	707.6	728.2	754.0	784.5	816.9	859.8	902.5	952.4
25°	634.0	640.7	655.0	670.2	690.8	712.6	744.4	780.2	822.6	871.3	922.3
27.5°	604.5	610.4	623.5	636.7	655.3	681.3	709.7	745.8	785.8	835.3	891.7
30°	583.4	589.7	601.3	615.6	633.5	656.3	685.4	719.4	762.2	810.5	869.6
32.5°	565.2	570.8	579.5	593.8	611.3	633.4	660.3	695.0	738.0	787.0	844.9
35°	536.9	543.2	549.9	561.1	576.3	597.7	627.2	659.9	701.0	748.4	801.6
37.5°	508.9	515.7	521.7	531.7	545.5	564.5	590.0	624.0	661.2	706.8	757.9
40°	491.4	496.7	501.6	512.4	526.2	544.1	567.8	598.2	637.6	680.0	722.5
42.5°	473.8	478.8	483.0	492.3	505.1	522.3	544.9	574.5	611.1	650.7	688.1
45°	446.2	449.4	454.3	462.3	472.6	488.2	510.1	536.5	567.3	604.9	633.1
47.5°	416.3	421.2	425.2	432.3	440.7	456.1	477.1	499.6	527.5	555.4	575.3
50°	393.4	398.4	404.2	410.9	418.9	433.3	452.5	475.3	498.9	520.4	537.4
52.5°	372.0	376.5	382.7	389.1	398.9	411.0	427.4	447.7	471.1	486.5	500.6
55°	340.3	342.4	349.7	355.9	365.2	374.2	390.7	408.6	422.9	434.5	446.2
57.5°	307.8	310.8	315.0	320.6	329.8	340.4	352.0	367.7	376.2	382.2	391.2
60°	287.1	287.9	290.6	297.3	304.4	313.8	327.3	338.5	344.7	349.7	357.2
62.5°	264.2	264.3	268.8	273.7	279.1	289.2	300.1	309.1	314.3	316.7	324.0
65°	232.0	231.2	233.8	237.8	244.1	250.8	260.2	268.3	267.8	270.4	274.9
67.5°	199.2	198.3	198.3	202.2	207.2	213.3	219.7	224.4	224.5	228.0	230.2
70°	177.0	174.4	176.2	179.3	181.5	186.4	193.6	195.4	195.8	197.6	199.8
72.5°	154.1	153.3	154.7	156.0	157.6	161.4	167.5	168.6	168.7	169.7	173.4
75°	122.5	121.6	120.7	122.1	123.8	126.5	128.7	130.5	130.1	130.5	133.2
77.5°	91.9	89.3	88.9	89.6	90.1	91.6	93.9	93.8	94.3	94.2	97.2
80°	72.8	69.3	68.9	68.9	69.3	70.2	71.1	72.0	70.6	72.0	72.8
82.5°	53.6	51.4	51.3	51.0	51.1	51.2	51.7	52.3	52.0	52.7	53.2
85°	29.5	28.6	27.3	28.2	27.7	26.3	27.3	25.9	25.5	25.9	26.3
87.5°	12.3	12.5	11.6	11.4	10.8	10.9	10.1	9.5	8.9	9.0	9.8
90°	11.5	10.8	9.7	8.7	7.7	6.5	5.4	4.3	3.1	1.9	0.7
92.5°	11.5	10.8	9.8	9.0	8.0	7.1	7.1	7.8	8.7	9.6	10.3
95°	11.5	10.8	16.4	22.1	27.8	33.5	36.6	37.0	37.5	38.0	38.4
97.5°	28.9	33.1	44.3	55.6	66.9	78.2	83.3	82.6	81.7	80.9	80.2
100°	94.9	117.2	116.6	116.0	115.4	114.8	114.3	113.8	113.3	112.9	112.4
102.5°	145.3	149.5	149.1	148.8	148.4	148.0	147.6	147.0	146.5	145.9	145.3
105°	200.6	200.6	200.6	200.6	200.6	200.6	200.4	199.8	199.1	198.5	197.9
107.5°	254.0	254.0	253.7	253.4	253.0	252.8	252.6	252.6	252.6	252.6	252.6
110°	289.1	289.6	289.2	289.0	288.6	288.3	288.2	288.2	288.2	288.2	288.2



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	323.5	324.0	323.8	323.6	323.5	323.3	323.0	322.7	322.3	321.9	321.6
115°	375.1	375.7	375.6	375.4	375.3	375.1	374.7	373.9	373.2	372.5	371.7
117.5°	425.2	425.9	425.4	424.8	424.2	423.7	423.4	423.4	423.4	423.5	423.5
120°	456.9	457.2	456.8	456.3	455.8	455.4	455.2	455.4	455.6	455.7	455.8
122.5°	487.6	487.9	487.7	487.5	487.2	487.1	486.6	486.1	485.5	485.0	484.4
125°	532.7	533.3	533.3	533.3	533.3	533.3	532.8	531.8	530.6	529.6	528.6
127.5°	573.3	573.7	573.8	573.9	573.9	574.0	573.7	573.0	572.2	571.4	570.8
130°	600.2	600.6	600.5	600.3	600.2	600.0	599.6	598.8	598.1	597.4	596.6
132.5°	624.7	624.8	625.2	625.5	625.9	626.2	625.9	625.0	624.1	623.3	622.4
135°	661.6	661.9	662.2	662.5	662.8	663.1	662.8	661.9	661.0	660.1	659.2
137.5°	695.3	695.3	695.6	695.9	696.1	696.4	696.1	695.3	694.6	693.8	693.0
140°	716.1	715.7	715.9	716.1	716.2	716.4	716.3	716.0	715.7	715.4	715.1
142.5°	736.8	736.8	736.6	736.3	736.2	735.9	735.7	735.6	735.4	735.2	735.0
145°	765.8	765.6	765.6	765.6	765.6	765.6	765.4	765.2	764.8	764.6	764.2
147.5°	790.6	790.4	790.2	790.0	789.8	789.6	789.6	789.6	789.7	789.8	789.8
150°	806.3	806.0	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0
152.5°	820.3	820.0	819.7	819.4	819.1	818.8	819.0	819.7	820.3	821.0	821.7
155°	839.4	839.0	838.7	838.4	838.1	837.8	838.1	839.0	839.9	840.8	841.7
157.5°	855.3	854.9	854.8	854.8	854.8	854.7	855.0	855.6	856.1	856.6	857.1
160°	865.1	864.5	864.4	864.3	864.1	864.0	864.4	865.2	866.2	867.0	868.0
162.5°	874.0	873.2	873.1	872.9	872.7	872.6	873.0	873.8	874.8	875.6	876.6
165°	885.7	884.8	884.6	884.5	884.3	884.2	884.5	885.5	886.3	887.3	888.1
167.5°	894.3	893.3	893.1	892.9	892.8	892.7	893.0	894.0	894.9	895.9	896.7
170°	898.8	897.6	897.4	897.2	897.1	897.0	897.4	898.5	899.5	900.5	901.6
172.5°	902.4	901.3	901.0	900.8	900.5	900.3	900.6	901.7	902.8	903.8	904.8
175°	906.2	905.0	904.8	904.7	904.5	904.4	904.7	905.7	906.5	907.4	908.4
177.5°	908.1	907.2	907.1	907.0	906.9	906.8	907.1	907.8	908.5	909.2	910.0
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1059.0	1064.0	1067.3	1073.3	1078.3	1081.2	1083.7	1085.9	1088.4	1090.5	1096.6
5°	1065.8	1077.5	1087.3	1102.5	1116.4	1127.0	1138.7	1149.0	1157.5	1169.6	1179.0
7.5°	1062.9	1083.6	1105.2	1128.7	1152.7	1175.1	1195.7	1214.9	1232.3	1253.4	1272.0
10°	1060.1	1088.2	1115.9	1147.6	1180.3	1208.0	1233.9	1260.3	1279.5	1306.4	1329.1
12.5°	1057.9	1091.1	1124.5	1162.7	1198.5	1237.7	1272.2	1291.4	1320.7	1342.1	1369.2
15°	1048.9	1092.7	1138.7	1181.6	1232.6	1268.8	1299.2	1336.8	1364.0	1391.3	1420.8
17.5°	1032.7	1082.3	1133.8	1190.1	1239.0	1277.8	1317.0	1353.2	1385.8	1422.4	1459.1
20°	1025.2	1074.8	1133.8	1191.5	1239.3	1280.0	1320.3	1360.0	1395.8	1442.7	1485.2
22.5°	1009.4	1069.4	1123.8	1180.0	1229.2	1273.6	1319.1	1364.3	1411.9	1464.9	1518.1
25°	981.4	1042.2	1099.8	1155.3	1204.9	1260.3	1309.1	1369.4	1430.2	1500.4	1566.6
27.5°	952.2	1010.4	1063.2	1116.8	1174.7	1237.4	1300.6	1369.2	1448.7	1537.3	1630.6
30°	928.6	983.6	1035.0	1089.9	1150.3	1221.0	1290.3	1371.7	1463.7	1563.4	1674.3
32.5°	901.0	951.7	1001.7	1060.0	1125.7	1200.2	1281.0	1370.2	1480.9	1594.2	1708.3
35°	853.9	896.4	947.8	1010.0	1084.2	1169.6	1263.0	1368.5	1495.5	1625.6	1721.7
37.5°	798.1	837.6	891.7	959.8	1037.7	1129.3	1240.2	1365.4	1500.2	1604.0	1635.0
40°	760.5	797.1	853.5	924.1	1003.7	1100.7	1222.3	1354.6	1485.2	1551.3	1525.9
42.5°	720.4	758.9	813.7	883.7	969.4	1075.0	1199.8	1332.1	1441.6	1466.6	1378.5
45°	657.2	697.0	751.1	821.7	913.9	1028.3	1158.4	1278.7	1341.7	1296.5	1160.2
47.5°	598.5	635.8	685.9	758.8	853.9	972.2	1097.5	1193.4	1198.4	1090.7	945.0
50°	558.4	592.8	643.3	716.2	810.5	930.4	1043.4	1119.0	1085.0	963.0	823.0
52.5°	519.1	552.8	602.6	674.8	768.0	877.8	983.0	1036.0	972.1	846.8	727.2
55°	462.3	491.8	540.5	607.1	695.7	797.6	887.0	905.3	822.2	698.8	601.8
57.5°	406.8	434.4	478.7	540.1	621.0	711.3	781.2	777.3	689.4	583.5	506.5
60°	369.3	396.1	435.5	495.3	569.1	647.0	706.8	692.5	605.4	514.1	449.4
62.5°	335.7	359.6	396.8	449.2	516.5	588.7	637.8	616.7	531.3	451.5	400.3
65°	286.1	306.3	338.0	382.7	438.6	498.1	536.1	508.8	435.9	373.8	332.6
67.5°	238.8	254.9	281.5	317.3	364.9	412.7	435.8	408.4	350.1	304.7	274.2
70°	208.8	223.1	243.7	275.4	317.0	357.2	374.6	350.1	300.0	261.1	239.2
72.5°	178.7	190.5	208.6	237.1	270.4	305.4	320.6	297.1	256.0	223.2	202.7
75°	138.2	146.2	158.7	178.4	204.7	232.5	241.0	220.4	194.1	169.4	156.0
77.5°	98.9	105.7	115.2	127.6	146.3	163.9	171.3	159.5	139.1	123.5	112.4
80°	76.0	79.6	87.6	97.9	112.7	123.8	128.7	121.1	106.9	95.2	86.7
82.5°	54.2	57.8	62.6	71.1	80.5	88.1	93.3	88.3	77.9	68.8	63.8
85°	26.3	28.6	31.3	34.9	42.0	46.5	46.1	42.9	38.9	35.3	32.6
87.5°	9.6	10.2	11.6	13.6	14.9	16.5	17.5	17.0	15.8	14.8	13.9
90°	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5	12.3
92.5°	9.6	8.7	7.8	7.1	7.1	8.0	9.0	9.8	10.8	11.5	12.3
95°	38.0	37.5	37.0	36.6	33.5	27.8	22.1	16.4	10.8	11.5	12.3
97.5°	80.9	81.7	82.6	83.3	78.2	66.9	55.6	44.3	33.1	28.9	24.7
100°	112.9	113.3	113.8	114.3	114.8	115.4	116.0	116.6	117.2	94.9	72.6
102.5°	145.9	146.5	147.0	147.6	148.0	148.4	148.8	149.1	149.5	145.3	141.0
105°	198.5	199.1	199.8	200.4	200.6	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.6	252.6	252.6	252.8	253.0	253.4	253.7	254.0	254.0	254.1
110°	288.2	288.2	288.2	288.2	288.3	288.6	289.0	289.2	289.6	289.1	288.6



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	321.9	322.3	322.7	323.0	323.3	323.5	323.6	323.8	324.0	323.5	322.9
115°	372.5	373.2	373.9	374.7	375.1	375.3	375.4	375.6	375.7	375.1	374.5
117.5°	423.5	423.4	423.4	423.4	423.7	424.2	424.8	425.4	425.9	425.2	424.4
120°	455.7	455.6	455.4	455.2	455.4	455.8	456.3	456.8	457.2	456.9	456.6
122.5°	485.0	485.5	486.1	486.6	487.1	487.2	487.5	487.7	487.9	487.6	487.3
125°	529.6	530.6	531.8	532.8	533.3	533.3	533.3	533.3	533.3	532.7	532.1
127.5°	571.4	572.2	573.0	573.7	574.0	573.9	573.9	573.8	573.7	573.3	573.0
130°	597.4	598.1	598.8	599.6	600.0	600.2	600.3	600.5	600.6	600.2	599.7
132.5°	623.3	624.1	625.0	625.9	626.2	625.9	625.5	625.2	624.8	624.7	624.7
135°	660.1	661.0	661.9	662.8	663.1	662.8	662.5	662.2	661.9	661.6	661.3
137.5°	693.8	694.6	695.3	696.1	696.4	696.1	695.9	695.6	695.3	695.3	695.4
140°	715.4	715.7	716.0	716.3	716.4	716.2	716.1	715.9	715.7	716.1	716.4
142.5°	735.2	735.4	735.6	735.7	735.9	736.2	736.3	736.6	736.8	736.8	736.9
145°	764.6	764.8	765.2	765.4	765.6	765.6	765.6	765.6	765.6	765.8	765.9
147.5°	789.8	789.7	789.6	789.6	789.6	789.8	790.0	790.2	790.4	790.6	790.7
150°	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	806.3	806.6
152.5°	821.0	820.3	819.7	819.0	818.8	819.1	819.4	819.7	820.0	820.3	820.6
155°	840.8	839.9	839.0	838.1	837.8	838.1	838.4	838.7	839.0	839.4	839.9
157.5°	856.6	856.1	855.6	855.0	854.7	854.8	854.8	854.8	854.9	855.3	855.8
160°	867.0	866.2	865.2	864.4	864.0	864.1	864.3	864.4	864.5	865.1	865.7
162.5°	875.6	874.8	873.8	873.0	872.6	872.7	872.9	873.1	873.2	874.0	874.9
165°	887.3	886.3	885.5	884.5	884.2	884.3	884.5	884.6	884.8	885.7	886.6
167.5°	895.9	894.9	894.0	893.0	892.7	892.8	892.9	893.1	893.3	894.3	895.4
170°	900.5	899.5	898.5	897.4	897.0	897.1	897.2	897.4	897.6	898.8	899.9
172.5°	903.8	902.8	901.7	900.6	900.3	900.5	900.8	901.0	901.3	902.4	903.4
175°	907.4	906.5	905.7	904.7	904.4	904.5	904.7	904.8	905.0	906.2	907.3
177.5°	909.2	908.5	907.8	907.1	906.8	906.9	907.0	907.1	907.2	908.1	909.0
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1101.6	1104.5	1110.5	1108.4	1111.3	1112.7	1114.1
5°	1190.6	1204.9	1211.2	1210.2	1219.6	1217.4	1215.1
7.5°	1291.1	1306.1	1314.5	1325.0	1331.0	1331.5	1336.8
10°	1348.0	1367.6	1375.7	1386.8	1394.0	1398.0	1397.6
12.5°	1391.5	1407.0	1425.0	1430.5	1440.1	1445.2	1443.4
15°	1444.1	1468.7	1487.5	1496.8	1508.9	1512.4	1517.4
17.5°	1490.9	1523.9	1545.8	1574.9	1586.0	1592.7	1588.7
20°	1526.3	1569.7	1591.6	1626.5	1645.7	1656.0	1652.4
22.5°	1568.1	1615.1	1655.6	1685.8	1715.1	1729.0	1731.8
25°	1639.9	1704.3	1763.8	1803.5	1839.7	1848.2	1867.0
27.5°	1720.0	1796.0	1859.5	1901.3	1926.6	1936.0	1941.9
30°	1770.5	1846.0	1893.9	1920.6	1928.7	1927.8	1926.9
32.5°	1795.1	1842.5	1851.6	1844.1	1825.7	1810.2	1793.9
35°	1760.1	1724.8	1672.1	1604.1	1554.0	1503.6	1498.6
37.5°	1583.0	1470.1	1382.2	1284.2	1227.6	1192.7	1168.5
40°	1416.3	1288.1	1181.6	1098.9	1041.2	1018.5	996.1
42.5°	1235.4	1112.8	1018.6	949.4	906.0	880.7	863.1
45°	1003.7	895.5	821.7	771.6	737.3	717.6	706.4
47.5°	822.4	742.4	679.8	643.6	619.8	604.5	604.6
50°	725.1	648.7	607.1	578.5	557.9	545.9	548.1
52.5°	638.9	581.9	546.3	522.4	507.1	499.7	499.5
55°	534.3	493.1	469.8	452.5	442.1	433.7	435.5
57.5°	457.0	422.3	406.7	392.3	385.1	381.7	376.8
60°	409.1	382.3	368.9	357.2	350.1	347.4	342.4
62.5°	366.5	345.4	332.3	322.9	316.4	315.6	311.7
65°	308.1	292.0	280.3	275.9	269.1	267.3	267.3
67.5°	253.9	242.4	233.4	229.3	226.3	226.8	224.6
70°	220.0	210.6	204.7	200.3	198.0	198.5	196.7
72.5°	192.4	181.9	176.8	174.2	171.3	172.4	171.7
75°	145.8	140.3	137.7	135.0	133.2	132.3	131.5
77.5°	107.0	102.3	100.2	98.8	99.0	96.9	98.5
80°	82.7	78.7	77.3	75.1	74.6	74.6	74.2
82.5°	60.5	58.3	57.3	55.4	54.7	55.4	54.2
85°	31.3	29.5	29.1	29.1	28.2	27.3	29.5
87.5°	14.0	12.7	12.9	12.7	12.7	12.5	11.8
90°	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	13.0	13.8	14.2	14.5	14.6	14.9	15.1
95°	13.0	13.8	14.1	14.1	14.1	14.1	14.1
97.5°	20.5	16.3	14.1	14.1	14.1	14.1	14.1
100°	50.3	28.0	16.5	15.9	15.3	14.7	14.1
102.5°	136.8	132.6	125.4	115.2	105.0	94.9	84.7
105°	200.6	200.6	200.6	200.4	200.3	200.1	200.0
107.5°	254.1	254.1	253.9	253.5	253.0	252.5	252.1
110°	288.2	287.7	287.6	287.7	287.9	288.0	288.2



TEST NUMBER: P333223-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	322.3	321.8	321.3	321.2	320.9	320.7	320.6
115°	373.9	373.3	372.6	371.7	370.7	369.9	369.0
117.5°	423.6	422.8	422.2	421.9	421.5	421.1	420.7
120°	456.3	456.0	455.5	454.7	454.0	453.2	452.5
122.5°	487.0	486.7	486.1	485.3	484.4	483.5	482.7
125°	531.5	530.9	530.4	529.9	529.4	529.0	528.6
127.5°	572.7	572.4	571.6	570.6	569.5	568.3	567.2
130°	599.3	598.8	598.2	597.4	596.8	596.0	595.2
132.5°	624.6	624.5	624.1	623.4	622.6	621.8	621.1
135°	661.0	660.7	660.1	659.2	658.3	657.4	656.5
137.5°	695.4	695.5	695.2	694.4	693.6	692.8	692.1
140°	716.7	717.0	716.7	715.7	714.9	713.9	713.1
142.5°	736.9	737.0	736.6	735.7	734.8	733.9	733.0
145°	766.0	766.2	765.8	764.9	764.1	763.1	762.2
147.5°	790.9	791.1	790.7	789.5	788.5	787.4	786.4
150°	806.9	807.2	806.8	805.6	804.3	803.1	801.9
152.5°	820.9	821.2	820.8	819.8	818.6	817.6	816.5
155°	840.3	840.8	840.4	839.2	838.0	836.8	835.6
157.5°	856.4	856.8	856.4	855.2	854.0	852.8	851.6
160°	866.3	866.9	866.7	865.5	864.3	863.1	861.9
162.5°	875.7	876.5	876.3	874.9	873.7	872.4	871.1
165°	887.4	888.4	888.2	887.0	885.8	884.6	883.4
167.5°	896.5	897.6	897.4	896.0	894.8	893.4	892.1
170°	901.1	902.3	902.2	901.0	899.6	898.2	896.9
172.5°	904.6	905.7	905.5	904.1	902.8	901.5	900.1
175°	908.5	909.7	909.6	908.4	907.0	905.7	904.3
177.5°	909.7	910.6	910.6	909.6	908.6	907.7	906.7
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4

(END OF REPORT)