

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331620-927

Luminaire Tested: **SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331620-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1832.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331620-927
CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331620-927

CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33	28				
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	28	25				
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22				
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19				
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14				
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331620-927

CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	2.0
10°-20°	102.2	5.6
20°-30°	143.5	7.8
30°-40°	156.5	8.5
40°-50°	143.9	7.9
50°-60°	113.0	6.2
60°-70°	73.7	4.0
70°-80°	38.0	2.1
80°-90°	11.2	0.6
90°-100°	58.2	3.2
100°-110°	197.5	10.8
110°-120°	209.8	11.5
120°-130°	172.7	9.4
130°-140°	138.7	7.6
140°-150°	104.8	5.7
150°-160°	73.7	4.0
160°-170°	43.4	2.4
170°-180°	14.1	0.8
0°-30°	282.9	15.4
0°-40°	439.4	24.0
0°-60°	696.4	38.0
0°-90°	819.2	44.7
90°-120°	465.5	25.4
90°-150°	881.7	48.1
90°-180°	1013.0	55.3
0°-180°	1832.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	0	4	10	9	9	1
95°	10	24	110	41	32	10
105°	34	52	207	371	315	36
115°	60	76	174	358	415	60
125°	84	99	167	290	337	75
135°	98	118	165	244	279	76
145°	112	129	164	204	223	71
155°	128	138	159	180	187	59
165°	139	144	153	162	164	39
175°	145	145	147	148	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331620-927

CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.7	4.4	4.0	3.6	3.2	3.2	3.4	3.8	4.1	4.2	4.1
90°	0.3	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3
92.5°	3.4	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7
95°	9.8	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0
97.5°	15.9	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5
100°	21.5	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4
102.5°	26.7	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6
105°	34.1	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9
107.5°	42.2	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3
110°	47.6	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9



TEST NUMBER: P331620-927

CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.5	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1
115°	60.2	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8
117.5°	68.1	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4
120°	73.0	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9
122.5°	77.8	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1
125°	84.0	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7
127.5°	88.9	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6
130°	91.8	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3
132.5°	94.5	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6
135°	98.5	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8
137.5°	102.3	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2
140°	105.3	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6
142.5°	108.1	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1
145°	112.5	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0
147.5°	117.2	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9
150°	120.3	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1
152.5°	123.5	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5
155°	127.9	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6
157.5°	131.6	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8
160°	134.0	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8
162.5°	136.6	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0
165°	139.4	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0
167.5°	141.7	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2
170°	143.3	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6
172.5°	144.2	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0
175°	145.3	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9
177.5°	145.8	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331620-927

CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	4.0	3.8	3.8	3.9	3.9	3.9	3.9	3.9
90°	9.0	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	24.4	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	73.4	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	171.1	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	255.6	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	310.9	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	340.1	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	319.0	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	300.9	351.0	386.8	409.8	421.8	427.1	429.7	429.4



TEST NUMBER: P331620-927

CATALOG NUMBER: SA2XXRDIP-C290D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	284.3	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	264.0	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	248.6	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	241.0	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	235.0	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	226.2	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	217.5	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	211.9	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	206.5	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	199.0	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	193.1	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	189.2	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	186.1	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	181.6	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	178.2	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	175.8	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	173.3	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	169.9	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	166.0	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	163.4	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	161.0	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	157.3	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	153.8	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.0	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.0	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	147.8	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)