

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333229-935

Luminaire Tested: **S125DIP-S850D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333229-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D810U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5732.4 lumens  
Efficiency: N/A  
Efficacy: 124.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51														
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	43	43	43														
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	36	36	36	36	36	36	36														
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	30	30	30	30	30	30	30														
4	74	64	56	50	68	59	52	47	50	45	41	43	38	35	35	32	30	26	26	26	26	26	26	26														
5	68	57	48	42	63	53	45	40	45	40	35	38	34	30	32	28	26	23	23	23	23	23	23	23														
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	20	20	20														
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18	18	18	18	18	18	18														
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	16	16	16														
9	50	38	30	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14	14	14	14	14	14	14														
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13	13	13	13	13	13	13														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	1.9
10°-20°	301.0	5.3
20°-30°	444.5	7.8
30°-40°	518.7	9.0
40°-50°	520.9	9.1
50°-60°	457.3	8.0
60°-70°	340.7	5.9
70°-80°	194.8	3.4
80°-90°	58.6	1.0
90°-100°	33.0	0.6
100°-110°	203.4	3.5
110°-120°	369.0	6.4
120°-130°	473.5	8.3
130°-140°	509.3	8.9
140°-150°	478.1	8.3
150°-160°	386.7	6.7
160°-170°	250.1	4.4
170°-180°	86.3	1.5
0°-30°	852.1	14.9
0°-40°	1370.8	23.9
0°-60°	2348.9	41.0
0°-90°	2943.0	51.3
90°-120°	605.4	10.6
90°-150°	2066.3	36.0
90°-180°	2789.0	48.7
0°-180°	5732.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	1	6	11	14	16	4
95°	38	35	11	14	14	49
105°	198	200	201	201	200	210
115°	372	375	376	373	369	368
125°	529	533	533	531	529	472
135°	659	663	662	660	656	508
145°	764	766	766	766	762	478
155°	842	838	839	841	836	388
165°	888	884	885	888	883	251
175°	908	905	905	910	904	86
180°	908	908	908	908	908	



TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.5	19.7	19.9	20.1	20.4	20.6	20.6	20.7	20.7	20.8	20.9
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	10.3	9.6	8.7	7.8	7.1	7.1	8.0	9.0	9.8	10.8	11.5
95°	38.4	38.0	37.5	37.0	36.6	33.5	27.8	22.1	16.4	10.8	11.5
97.5°	80.2	80.9	81.7	82.6	83.3	78.2	66.9	55.6	44.3	33.1	28.9
100°	112.4	112.9	113.3	113.8	114.3	114.8	115.4	116.0	116.6	117.2	94.9
102.5°	145.3	145.9	146.5	147.0	147.6	148.0	148.4	148.8	149.1	149.5	145.3
105°	197.9	198.5	199.1	199.8	200.4	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.6	252.6	252.6	252.6	252.8	253.0	253.4	253.7	254.0	254.0
110°	288.2	288.2	288.2	288.2	288.2	288.3	288.6	289.0	289.2	289.6	289.1



TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	321.6	321.9	322.3	322.7	323.0	323.3	323.5	323.6	323.8	324.0	323.5
115°	371.7	372.5	373.2	373.9	374.7	375.1	375.3	375.4	375.6	375.7	375.1
117.5°	423.5	423.5	423.4	423.4	423.4	423.7	424.2	424.8	425.4	425.9	425.2
120°	455.8	455.7	455.6	455.4	455.2	455.4	455.8	456.3	456.8	457.2	456.9
122.5°	484.4	485.0	485.5	486.1	486.6	487.1	487.2	487.5	487.7	487.9	487.6
125°	528.6	529.6	530.6	531.8	532.8	533.3	533.3	533.3	533.3	533.3	532.7
127.5°	570.8	571.4	572.2	573.0	573.7	574.0	573.9	573.9	573.8	573.7	573.3
130°	596.6	597.4	598.1	598.8	599.6	600.0	600.2	600.3	600.5	600.6	600.2
132.5°	622.4	623.3	624.1	625.0	625.9	626.2	625.9	625.5	625.2	624.8	624.7
135°	659.2	660.1	661.0	661.9	662.8	663.1	662.8	662.5	662.2	661.9	661.6
137.5°	693.0	693.8	694.6	695.3	696.1	696.4	696.1	695.9	695.6	695.3	695.3
140°	715.1	715.4	715.7	716.0	716.3	716.4	716.2	716.1	715.9	715.7	716.1
142.5°	735.0	735.2	735.4	735.6	735.7	735.9	736.2	736.3	736.6	736.8	736.8
145°	764.2	764.6	764.8	765.2	765.4	765.6	765.6	765.6	765.6	765.6	765.8
147.5°	789.8	789.8	789.7	789.6	789.6	789.6	789.8	790.0	790.2	790.4	790.6
150°	806.0	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	806.3
152.5°	821.7	821.0	820.3	819.7	819.0	818.8	819.1	819.4	819.7	820.0	820.3
155°	841.7	840.8	839.9	839.0	838.1	837.8	838.1	838.4	838.7	839.0	839.4
157.5°	857.1	856.6	856.1	855.6	855.0	854.7	854.8	854.8	854.8	854.9	855.3
160°	868.0	867.0	866.2	865.2	864.4	864.0	864.1	864.3	864.4	864.5	865.1
162.5°	876.6	875.6	874.8	873.8	873.0	872.6	872.7	872.9	873.1	873.2	874.0
165°	888.1	887.3	886.3	885.5	884.5	884.2	884.3	884.5	884.6	884.8	885.7
167.5°	896.7	895.9	894.9	894.0	893.0	892.7	892.8	892.9	893.1	893.3	894.3
170°	901.6	900.5	899.5	898.5	897.4	897.0	897.1	897.2	897.4	897.6	898.8
172.5°	904.8	903.8	902.8	901.7	900.6	900.3	900.5	900.8	901.0	901.3	902.4
175°	908.4	907.4	906.5	905.7	904.7	904.4	904.5	904.7	904.8	905.0	906.2
177.5°	910.0	909.2	908.5	907.8	907.1	906.8	906.9	907.0	907.1	907.2	908.1
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	21.1	21.2	21.4	21.4	21.1	20.8	20.7	20.4
90°	12.3	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	12.3	13.0	13.8	14.2	14.5	14.6	14.9	15.1
95°	12.3	13.0	13.8	14.1	14.1	14.1	14.1	14.1
97.5°	24.7	20.5	16.3	14.1	14.1	14.1	14.1	14.1
100°	72.6	50.3	28.0	16.5	15.9	15.3	14.7	14.1
102.5°	141.0	136.8	132.6	125.4	115.2	105.0	94.9	84.7
105°	200.6	200.6	200.6	200.6	200.4	200.3	200.1	200.0
107.5°	254.1	254.1	254.1	253.9	253.5	253.0	252.5	252.1
110°	288.6	288.2	287.7	287.6	287.7	287.9	288.0	288.2





TEST NUMBER: P333229-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.9	322.3	321.8	321.3	321.2	320.9	320.7	320.6
115°	374.5	373.9	373.3	372.6	371.7	370.7	369.9	369.0
117.5°	424.4	423.6	422.8	422.2	421.9	421.5	421.1	420.7
120°	456.6	456.3	456.0	455.5	454.7	454.0	453.2	452.5
122.5°	487.3	487.0	486.7	486.1	485.3	484.4	483.5	482.7
125°	532.1	531.5	530.9	530.4	529.9	529.4	529.0	528.6
127.5°	573.0	572.7	572.4	571.6	570.6	569.5	568.3	567.2
130°	599.7	599.3	598.8	598.2	597.4	596.8	596.0	595.2
132.5°	624.7	624.6	624.5	624.1	623.4	622.6	621.8	621.1
135°	661.3	661.0	660.7	660.1	659.2	658.3	657.4	656.5
137.5°	695.4	695.4	695.5	695.2	694.4	693.6	692.8	692.1
140°	716.4	716.7	717.0	716.7	715.7	714.9	713.9	713.1
142.5°	736.9	736.9	737.0	736.6	735.7	734.8	733.9	733.0
145°	765.9	766.0	766.2	765.8	764.9	764.1	763.1	762.2
147.5°	790.7	790.9	791.1	790.7	789.5	788.5	787.4	786.4
150°	806.6	806.9	807.2	806.8	805.6	804.3	803.1	801.9
152.5°	820.6	820.9	821.2	820.8	819.8	818.6	817.6	816.5
155°	839.9	840.3	840.8	840.4	839.2	838.0	836.8	835.6
157.5°	855.8	856.4	856.8	856.4	855.2	854.0	852.8	851.6
160°	865.7	866.3	866.9	866.7	865.5	864.3	863.1	861.9
162.5°	874.9	875.7	876.5	876.3	874.9	873.7	872.4	871.1
165°	886.6	887.4	888.4	888.2	887.0	885.8	884.6	883.4
167.5°	895.4	896.5	897.6	897.4	896.0	894.8	893.4	892.1
170°	899.9	901.1	902.3	902.2	901.0	899.6	898.2	896.9
172.5°	903.4	904.6	905.7	905.5	904.1	902.8	901.5	900.1
175°	907.3	908.5	909.7	909.6	908.4	907.0	905.7	904.3
177.5°	909.0	909.7	910.6	910.6	909.6	908.6	907.7	906.7
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4

(END OF REPORT)