

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333230-935

Luminaire Tested: **S125DIP-S850D810U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333230-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5357.2 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	90	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24
6	64	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	2.0
10°-20°	301.0	5.6
20°-30°	444.5	8.3
30°-40°	518.7	9.7
40°-50°	520.9	9.7
50°-60°	457.3	8.5
60°-70°	340.7	6.4
70°-80°	194.8	3.6
80°-90°	58.6	1.1
90°-100°	57.9	1.1
100°-110°	171.1	3.2
110°-120°	289.8	5.4
120°-130°	381.4	7.1
130°-140°	427.4	8.0
140°-150°	418.9	7.8
150°-160°	351.8	6.6
160°-170°	233.9	4.4
170°-180°	81.8	1.5
0°-30°	852.1	15.9
0°-40°	1370.8	25.6
0°-60°	2348.9	43.8
0°-90°	2943.0	54.9
90°-120°	518.9	9.7
90°-150°	1746.6	32.6
90°-180°	2414.0	45.1
0°-180°	5357.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	1	6	11	14	16	5
95°	44	45	52	56	58	47
105°	154	157	161	165	167	164
115°	290	293	294	294	293	287
125°	423	427	428	427	426	379
135°	551	555	555	555	553	424
145°	667	670	672	672	670	417
155°	763	763	764	766	763	351
165°	830	829	830	832	828	234
175°	863	861	860	864	860	82
180°	865	865	865	865	865	



TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.5	19.7	19.9	20.1	20.4	20.6	20.6	20.7	20.7	20.8	20.9
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	16.3	17.1	18.0	18.8	19.6	20.7	22.0	23.2	24.5	25.8	26.9
95°	43.7	44.1	44.3	44.7	44.9	45.9	47.4	48.8	50.4	51.8	52.9
97.5°	72.8	72.8	72.9	73.1	73.2	74.3	76.4	78.4	80.5	82.6	83.5
100°	94.3	94.3	94.3	94.3	94.3	95.2	97.2	99.1	101.1	103.0	104.4
102.5°	117.4	118.0	118.6	119.2	119.9	120.6	121.6	122.6	123.6	124.6	126.1
105°	153.5	154.3	155.0	155.8	156.5	157.3	158.3	159.1	160.0	160.9	161.8
107.5°	193.4	194.1	194.8	195.6	196.4	197.1	197.8	198.5	199.1	199.8	200.3
110°	220.8	221.6	222.3	223.1	223.9	224.5	224.9	225.3	225.8	226.2	226.7



TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	248.8	249.3	249.6	250.0	250.4	250.9	251.4	252.0	252.6	253.1	253.4
115°	290.2	290.8	291.4	292.0	292.6	293.0	293.3	293.6	293.9	294.2	294.0
117.5°	331.7	331.9	332.2	332.4	332.7	333.0	333.3	333.6	333.8	334.1	334.2
120°	357.5	358.3	359.0	359.7	360.5	360.9	361.1	361.3	361.4	361.5	361.5
122.5°	385.5	385.8	386.1	386.3	386.6	386.9	387.3	387.7	388.1	388.5	388.3
125°	423.4	424.4	425.2	426.2	427.1	427.6	427.7	427.9	428.0	428.2	427.9
127.5°	463.9	464.4	464.9	465.4	465.9	466.2	466.4	466.6	466.8	467.0	466.8
130°	488.1	488.9	489.7	490.3	491.1	491.6	491.9	492.2	492.5	492.8	492.7
132.5°	512.4	513.6	514.8	516.0	517.3	517.8	517.8	517.7	517.6	517.6	517.5
135°	550.7	551.6	552.5	553.5	554.3	554.8	555.0	555.2	555.3	555.4	555.4
137.5°	586.9	587.7	588.6	589.4	590.3	590.9	591.2	591.5	591.9	592.2	592.4
140°	610.0	610.7	611.5	612.3	612.9	613.5	614.0	614.5	614.9	615.4	615.7
142.5°	633.2	633.8	634.4	635.0	635.7	636.3	636.8	637.4	637.9	638.5	638.7
145°	667.2	667.8	668.4	669.0	669.6	670.1	670.5	671.0	671.5	671.9	671.9
147.5°	698.7	699.0	699.4	699.7	700.0	700.3	700.8	701.1	701.5	701.8	702.1
150°	719.7	719.5	719.5	719.3	719.1	719.4	720.0	720.6	721.2	721.8	721.8
152.5°	736.9	737.2	737.4	737.6	737.8	738.0	738.2	738.5	738.7	739.0	739.3
155°	763.4	763.4	763.4	763.4	763.4	763.5	763.7	763.9	764.0	764.1	764.7
157.5°	787.2	786.9	786.5	786.2	785.8	785.7	785.9	786.1	786.2	786.4	787.0
160°	801.2	800.7	800.3	799.9	799.4	799.3	799.4	799.5	799.7	799.9	800.5
162.5°	813.6	813.2	812.9	812.6	812.3	812.1	812.1	812.2	812.2	812.3	813.0
165°	830.2	829.8	829.6	829.2	829.0	828.9	829.0	829.1	829.3	829.5	830.1
167.5°	844.1	843.5	842.9	842.3	841.7	841.5	841.5	841.5	841.5	841.5	842.3
170°	851.7	851.1	850.5	849.9	849.3	848.9	848.9	848.9	848.9	848.9	849.9
172.5°	857.0	856.4	855.8	855.2	854.6	854.4	854.4	854.4	854.4	854.4	855.2
175°	863.2	862.5	861.9	861.3	860.7	860.4	860.4	860.4	860.4	860.4	861.3
177.5°	866.3	865.7	865.3	864.8	864.3	864.0	863.9	863.8	863.7	863.5	864.3
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	21.1	21.2	21.4	21.4	21.1	20.8	20.7	20.4
90°	12.2	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	27.8	28.8	29.8	30.5	30.8	31.1	31.4	31.8
95°	53.9	55.0	56.1	56.7	57.0	57.3	57.6	57.9
97.5°	84.6	85.5	86.5	87.0	87.2	87.4	87.6	87.8
100°	105.7	107.0	108.4	109.3	109.5	109.8	110.1	110.4
102.5°	127.5	129.0	130.4	131.4	131.8	132.2	132.6	133.0
105°	162.7	163.6	164.5	165.1	165.7	166.1	166.5	166.9
107.5°	200.7	201.1	201.6	201.8	201.8	201.7	201.7	201.7
110°	227.1	227.6	228.0	228.2	228.0	227.8	227.7	227.6



TEST NUMBER: P333230-935

CATALOG NUMBER: S125DIP-S850D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	253.6	253.7	254.0	254.0	253.7	253.4	253.1	252.9
115°	293.9	293.8	293.6	293.4	293.3	293.2	293.0	292.9
117.5°	334.3	334.4	334.6	334.3	333.7	333.1	332.5	331.9
120°	361.5	361.5	361.5	361.3	360.7	360.1	359.5	358.9
122.5°	388.2	388.1	388.0	387.7	387.2	386.8	386.2	385.8
125°	427.6	427.3	427.0	426.8	426.6	426.5	426.4	426.2
127.5°	466.7	466.5	466.4	466.1	465.9	465.5	465.3	464.9
130°	492.5	492.4	492.2	492.0	491.7	491.4	491.1	490.8
132.5°	517.3	517.1	517.0	516.7	516.3	515.9	515.5	515.1
135°	555.4	555.4	555.4	555.2	554.6	554.0	553.4	552.8
137.5°	592.5	592.7	592.9	592.6	591.9	591.2	590.4	589.6
140°	616.0	616.2	616.6	616.3	615.6	614.8	614.1	613.4
142.5°	638.9	639.0	639.2	638.9	638.2	637.5	636.7	635.9
145°	671.9	671.9	671.9	671.7	671.2	670.8	670.4	669.9
147.5°	702.5	702.9	703.3	702.9	701.9	700.9	699.9	698.9
150°	721.8	721.8	721.8	721.6	721.3	721.0	720.7	720.4
152.5°	739.7	740.0	740.4	740.3	739.8	739.3	738.7	738.1
155°	765.3	765.9	766.5	766.5	765.7	765.0	764.2	763.4
157.5°	787.6	788.2	788.8	788.6	787.6	786.6	785.6	784.6
160°	801.1	801.6	802.2	802.2	801.4	800.6	799.9	799.2
162.5°	813.6	814.4	815.1	815.0	814.2	813.3	812.4	811.6
165°	830.7	831.3	831.8	831.7	830.8	829.9	829.0	828.1
167.5°	843.3	844.1	845.1	845.0	844.1	843.2	842.2	841.3
170°	850.8	851.7	852.6	852.5	851.4	850.4	849.4	848.3
172.5°	856.2	857.0	858.0	858.0	857.0	856.1	855.1	854.2
175°	862.2	863.2	864.0	863.9	862.9	861.9	860.8	859.8
177.5°	865.0	865.6	866.4	866.3	865.5	864.7	863.8	863.0
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1

(END OF REPORT)