

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331626-927

Luminaire Tested: **SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331626-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2454.7 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331626-927
CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331626-927

CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25				
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21				
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18				
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331626-927

CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	1.5
10°-20°	102.2	4.2
20°-30°	143.5	5.8
30°-40°	156.5	6.4
40°-50°	143.9	5.9
50°-60°	113.0	4.6
60°-70°	73.7	3.0
70°-80°	38.0	1.5
80°-90°	12.0	0.5
90°-100°	93.9	3.8
100°-110°	318.8	13.0
110°-120°	338.6	13.8
120°-130°	278.8	11.4
130°-140°	223.9	9.1
140°-150°	169.2	6.9
150°-160°	118.9	4.8
160°-170°	70.0	2.9
170°-180°	22.8	0.9
0°-30°	282.9	11.5
0°-40°	439.4	17.9
0°-60°	696.4	28.4
0°-90°	820.0	33.4
90°-120°	751.3	30.6
90°-150°	1423.1	58.0
90°-180°	1635.0	66.6
0°-180°	2454.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	0	6	15	15	15	2
95°	16	39	177	67	52	17
105°	55	83	335	598	509	59
115°	97	123	280	578	670	96
125°	136	160	269	468	544	120
135°	159	190	266	394	450	123
145°	182	209	265	329	360	114
155°	206	223	257	291	302	95
165°	225	232	246	261	265	63
175°	234	235	237	240	239	22
180°	235	235	235	235	235	



TEST NUMBER: P331626-927

CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.7	4.4	4.3	4.0	3.6	3.6	4.1	4.8	5.3	5.4	5.2
90°	0.5	1.8	3.6	4.5	5.4	6.8	9.0	12.2	14.9	15.4	14.9
92.5°	5.5	7.9	11.2	13.2	16.2	20.5	30.7	45.1	57.9	58.7	49.6
95°	15.8	17.6	22.1	26.2	33.4	44.3	65.0	104.3	156.8	177.1	155.0
97.5°	25.7	28.2	33.0	39.1	47.5	59.7	85.9	140.6	227.7	302.3	317.1
100°	34.8	36.1	40.2	47.5	56.5	69.2	93.1	148.2	245.7	356.9	421.9
102.5°	43.1	44.1	48.2	55.4	64.8	77.4	99.6	148.5	238.9	358.7	461.0
105°	55.1	57.0	60.0	66.9	76.8	89.4	110.7	150.9	225.5	334.8	455.0
107.5°	68.1	69.6	72.6	78.9	88.7	101.5	122.1	157.1	218.7	309.1	415.3
110°	76.8	78.6	81.4	87.2	96.6	109.8	129.7	162.2	217.3	296.8	390.3



TEST NUMBER: P331626-927

CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	86.6	89.6	95.1	104.3	117.7	136.9	167.6	217.7	288.8	373.0
115°	97.1	99.4	102.1	107.5	116.5	128.7	148.2	175.7	219.6	280.1	351.5
117.5°	110.0	111.8	114.5	119.3	127.9	140.6	158.6	184.4	222.8	275.8	337.9
120°	117.9	119.7	122.4	126.5	135.5	148.2	165.8	190.2	225.0	273.3	330.7
122.5°	125.5	127.0	129.7	134.1	143.1	156.1	172.7	195.3	227.5	271.9	324.6
125°	135.5	136.9	139.6	145.0	154.1	166.7	183.0	203.3	231.3	269.3	315.8
127.5°	143.5	145.3	149.1	155.0	163.7	176.7	192.6	210.8	235.2	267.8	307.7
130°	148.2	150.0	154.5	160.8	169.8	182.5	198.4	215.5	238.1	267.0	302.2
132.5°	152.5	154.7	159.5	166.3	175.6	188.3	203.4	220.2	241.0	266.6	297.9
135°	159.0	160.8	166.3	173.0	183.4	196.1	210.6	226.3	244.4	266.1	291.8
137.5°	165.2	167.3	172.8	180.0	190.3	202.0	216.3	231.0	247.5	266.0	287.6
140°	169.8	171.7	177.1	184.3	194.2	206.0	219.6	233.5	248.9	265.6	285.1
142.5°	174.6	176.0	181.1	188.3	197.9	208.9	222.1	235.8	250.0	265.6	282.6
145°	181.6	183.4	187.9	194.7	203.7	213.7	225.9	238.5	251.2	264.7	279.2
147.5°	189.2	190.5	194.9	201.1	208.7	217.5	228.9	240.1	251.5	263.1	275.8
150°	194.2	195.6	199.2	205.1	211.9	220.0	230.4	240.8	251.2	262.1	272.9
152.5°	199.3	199.9	203.6	208.7	215.2	222.5	231.9	241.1	250.5	260.2	270.4
155°	206.4	206.9	209.6	214.6	219.6	226.3	234.0	241.7	249.4	257.1	265.6
157.5°	212.4	212.9	215.1	219.4	223.4	229.0	235.5	241.7	247.3	253.8	261.2
160°	216.4	216.8	218.6	222.3	225.9	230.8	236.3	241.7	246.2	251.7	257.9
162.5°	220.4	220.1	221.9	224.8	228.1	232.0	236.6	241.3	245.1	249.9	255.1
165°	225.0	224.5	225.5	228.1	230.4	233.1	237.2	240.3	243.0	246.2	250.3
167.5°	228.8	228.2	229.0	230.8	232.4	234.1	237.1	239.7	241.0	243.0	245.6
170°	231.3	230.4	230.8	232.2	233.1	234.5	236.7	239.0	239.9	241.2	243.0
172.5°	232.7	232.2	232.0	233.3	233.9	234.8	236.4	237.9	238.4	239.1	240.5
175°	234.5	234.0	233.5	234.5	234.5	234.9	235.8	236.7	236.3	236.7	237.2
177.5°	235.3	234.6	234.2	234.9	234.9	234.9	235.3	236.0	235.3	234.9	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331626-927

CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	5.1	4.8	4.9	5.0	5.0	5.0	5.0	5.0
90°	14.4	13.5	14.4	14.9	14.9	14.9	14.9	14.9
92.5°	39.4	33.8	30.0	27.2	26.9	25.4	25.7	25.0
95°	118.4	90.8	71.9	61.9	56.0	52.4	51.0	51.5
97.5°	276.2	226.0	177.1	144.5	122.9	111.8	105.2	101.4
100°	412.5	356.5	294.5	239.9	202.4	183.0	169.8	161.8
102.5°	501.8	489.1	443.9	385.9	345.2	312.0	295.6	284.6
105°	548.9	599.9	605.9	590.9	562.9	534.9	515.5	509.1
107.5°	514.9	591.8	638.8	660.7	664.2	662.7	658.8	650.4
110°	485.7	566.5	624.3	661.4	680.8	689.4	693.5	693.0



TEST NUMBER: P331626-927

CATALOG NUMBER: SA2XXRDIP-C290D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	458.9	536.5	598.3	640.8	667.8	682.1	689.8	692.3
115°	426.0	495.6	554.8	601.3	633.3	654.2	665.9	669.9
117.5°	401.2	462.3	516.0	559.7	592.4	614.3	626.7	630.1
120°	389.0	445.0	492.9	534.0	565.6	586.8	599.9	604.4
122.5°	379.2	430.6	475.9	513.0	541.4	562.3	573.9	577.7
125°	365.0	411.5	451.3	485.2	511.4	528.5	539.9	543.5
127.5°	351.0	393.2	430.6	461.9	484.7	500.8	510.6	513.5
130°	342.0	380.9	416.5	446.3	468.5	483.9	492.9	496.5
132.5°	333.4	369.3	402.1	430.1	451.9	467.2	475.5	478.8
135°	321.2	351.0	380.9	406.2	425.6	440.5	448.6	450.4
137.5°	311.6	336.5	360.1	382.2	399.9	412.7	419.9	422.6
140°	305.4	327.1	347.8	367.7	382.2	394.0	400.7	403.5
142.5°	300.3	318.8	336.7	353.3	367.0	377.7	383.7	384.3
145°	293.2	308.1	322.1	335.3	346.0	353.7	358.2	359.6
147.5°	287.7	299.4	310.4	320.0	328.9	335.0	338.1	338.9
150°	283.7	293.7	303.2	311.2	318.1	323.4	326.1	326.6
152.5°	279.7	289.0	297.0	304.0	309.3	314.1	316.1	316.2
155°	274.3	281.5	288.2	293.2	298.2	301.3	303.2	302.2
157.5°	267.8	273.9	279.6	283.4	286.9	289.6	290.4	290.4
160°	263.8	268.8	273.8	276.9	280.1	282.3	282.8	282.8
162.5°	259.8	264.1	268.4	270.8	273.9	275.5	275.9	275.6
165°	253.9	257.1	260.2	262.1	263.8	265.6	265.6	265.2
167.5°	248.2	250.6	252.8	254.4	255.2	256.3	256.2	255.6
170°	245.3	246.7	248.5	249.4	249.9	251.2	250.7	249.9
172.5°	242.1	243.0	244.5	245.0	245.5	246.1	245.7	245.1
175°	238.5	239.0	239.5	239.9	239.9	240.3	239.9	239.0
177.5°	236.0	236.0	236.4	236.4	236.4	236.4	236.0	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9

(END OF REPORT)