

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331631-927

Luminaire Tested: **SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331631-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2872.5 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	42	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.2	1.3
10°-20°	102.2	3.6
20°-30°	143.5	5.0
30°-40°	156.5	5.4
40°-50°	143.9	5.0
50°-60°	113.0	3.9
60°-70°	73.7	2.6
70°-80°	38.0	1.3
80°-90°	12.8	0.4
90°-100°	46.5	1.6
100°-110°	144.4	5.0
110°-120°	246.8	8.6
120°-130°	324.6	11.3
130°-140°	364.3	12.7
140°-150°	357.2	12.4
150°-160°	299.6	10.4
160°-170°	198.7	6.9
170°-180°	69.5	2.4
0°-30°	282.9	9.8
0°-40°	439.4	15.3
0°-60°	696.4	24.2
0°-90°	820.8	28.6
90°-120°	437.7	15.2
90°-150°	1483.9	51.7
90°-180°	2052.0	71.4
0°-180°	2872.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	1	8	22	21	21	2
95°	32	38	40	40	38	37
105°	133	135	136	137	137	141
115°	248	251	250	249	248	245
125°	360	366	364	362	362	322
135°	466	473	474	474	472	360
145°	566	570	574	574	572	353
155°	647	649	651	654	652	298
165°	704	703	703	707	705	198
175°	732	731	729	733	730	70
180°	734	734	734	734	734	



TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.8	4.5	4.4	4.2	4.0	4.2	4.8	5.5	6.0	6.7	6.5
90°	0.6	2.3	4.0	5.5	7.2	9.6	12.6	15.6	18.6	21.7	21.4
92.5°	11.0	12.2	13.5	14.7	15.8	16.8	17.5	18.2	19.0	19.7	19.7
95°	32.2	33.6	34.9	36.4	37.7	38.5	38.8	39.1	39.4	39.6	39.6
97.5°	58.9	60.0	61.2	62.4	63.7	64.6	65.0	65.6	66.1	66.6	66.6
100°	78.7	79.8	80.8	81.9	83.0	83.8	84.2	84.6	85.0	85.5	85.5
102.5°	99.4	100.3	101.2	102.1	103.0	103.7	104.2	104.7	105.2	105.8	105.8
105°	133.2	133.6	134.0	134.4	134.8	135.1	135.4	135.7	135.9	136.3	136.5
107.5°	167.1	167.7	168.3	168.9	169.4	169.8	169.8	169.8	169.8	169.8	169.9
110°	188.9	189.6	190.5	191.3	192.2	192.6	192.6	192.6	192.6	192.6	192.6



TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.6	213.5	214.3	215.1	215.9	216.3	216.2	216.1	215.9	215.9	215.6
115°	247.7	248.5	249.3	250.2	251.0	251.3	251.0	250.7	250.4	250.2	250.0
117.5°	282.6	283.7	284.8	285.9	287.0	287.2	286.4	285.7	284.9	284.1	283.8
120°	305.9	307.0	308.1	309.2	310.3	310.3	309.2	308.1	307.0	305.9	305.9
122.5°	327.2	328.5	329.9	331.1	332.5	332.7	332.0	331.2	330.4	329.6	329.3
125°	360.4	361.6	362.8	364.1	365.4	365.8	365.4	364.9	364.5	364.1	363.7
127.5°	392.7	394.3	395.9	397.4	398.9	399.5	399.0	398.5	398.0	397.5	397.0
130°	413.0	414.8	416.6	418.4	420.2	420.9	420.6	420.3	420.1	419.9	419.5
132.5°	435.8	437.3	438.7	440.1	441.6	442.4	442.4	442.5	442.5	442.6	442.0
135°	466.3	467.8	469.3	470.8	472.3	473.2	473.5	473.7	474.0	474.3	474.2
137.5°	498.4	499.6	500.8	502.1	503.3	504.1	504.5	504.8	505.2	505.5	505.4
140°	517.7	518.9	520.1	521.3	522.6	523.6	524.3	525.0	525.6	526.3	526.3
142.5°	537.5	538.7	540.0	541.2	542.4	543.3	543.8	544.2	544.7	545.2	545.3
145°	565.9	566.9	567.9	568.9	569.8	570.7	571.6	572.4	573.1	574.0	574.2
147.5°	591.4	592.5	593.7	594.8	596.0	596.8	597.4	597.9	598.5	599.0	599.3
150°	608.7	609.5	610.3	611.2	612.0	612.7	613.2	613.8	614.3	614.9	615.3
152.5°	624.0	624.9	625.7	626.5	627.3	628.0	628.8	629.4	630.0	630.7	631.2
155°	647.1	647.5	647.9	648.3	648.7	649.1	649.5	650.0	650.4	650.8	651.5
157.5°	666.8	667.0	667.3	667.6	667.9	668.1	668.4	668.6	668.8	669.1	670.0
160°	678.7	678.9	679.2	679.5	679.8	679.9	680.1	680.2	680.4	680.5	681.4
162.5°	689.5	689.6	689.7	689.7	689.8	689.8	690.0	690.1	690.3	690.4	691.3
165°	704.0	703.9	703.8	703.6	703.5	703.4	703.4	703.4	703.4	703.4	704.4
167.5°	716.1	715.7	715.3	714.9	714.5	714.3	714.3	714.2	714.2	714.2	715.2
170°	722.6	722.2	721.8	721.4	721.0	720.6	720.6	720.4	720.3	720.1	721.1
172.5°	727.1	726.7	726.3	725.8	725.4	725.2	725.0	724.8	724.8	724.6	725.6
175°	732.5	732.1	731.7	731.3	730.9	730.6	730.2	730.0	729.7	729.4	730.4
177.5°	734.7	734.4	734.1	733.7	733.4	733.2	732.9	732.7	732.5	732.3	732.9
180°	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7



TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	6.4	6.3	6.2	6.1	6.2	6.2	6.2	6.3
90°	21.2	20.8	20.6	20.5	20.7	20.8	20.9	21.1
92.5°	19.8	19.9	19.9	20.0	20.0	20.0	20.0	20.0
95°	39.6	39.6	39.6	39.5	39.2	39.0	38.7	38.4
97.5°	66.6	66.6	66.6	66.6	66.6	66.5	66.5	66.5
100°	85.5	85.5	85.5	85.4	85.2	85.1	85.0	84.8
102.5°	106.0	106.1	106.2	106.2	106.1	105.9	105.8	105.6
105°	136.8	137.0	137.4	137.4	137.4	137.4	137.4	137.4
107.5°	170.0	170.1	170.2	170.0	169.4	168.7	168.1	167.5
110°	192.6	192.6	192.6	192.3	191.9	191.5	191.2	190.7





TEST NUMBER: P331631-927

CATALOG NUMBER: SA2XXRDIP-C290D725U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	215.2	214.8	214.5	214.2	213.9	213.6	213.3	213.0
115°	249.9	249.8	249.6	249.3	248.9	248.5	248.1	247.7
117.5°	283.4	283.1	282.7	282.4	282.0	281.5	281.1	280.7
120°	305.9	305.9	305.9	305.7	305.2	304.8	304.4	304.0
122.5°	329.0	328.7	328.4	328.0	327.7	327.4	327.1	326.9
125°	363.3	362.8	362.4	362.2	362.0	361.9	361.8	361.6
127.5°	396.6	396.0	395.5	395.1	394.7	394.2	393.8	393.3
130°	419.3	419.0	418.7	418.3	417.7	417.2	416.7	416.1
132.5°	441.4	440.8	440.2	439.7	439.2	438.8	438.3	437.9
135°	474.0	473.9	473.7	473.5	473.1	472.7	472.2	471.8
137.5°	505.3	505.2	505.1	504.8	504.2	503.7	503.1	502.6
140°	526.3	526.3	526.3	526.0	525.5	525.0	524.4	523.9
142.5°	545.3	545.5	545.6	545.3	544.8	544.2	543.8	543.2
145°	574.3	574.4	574.6	574.3	573.8	573.2	572.7	572.1
147.5°	599.6	599.9	600.2	600.2	599.6	599.0	598.6	598.0
150°	615.7	616.1	616.6	616.6	616.1	615.7	615.3	614.9
152.5°	631.8	632.3	632.8	632.8	632.3	631.8	631.2	630.7
155°	652.1	652.8	653.6	653.7	653.2	652.8	652.4	652.0
157.5°	671.0	671.9	672.9	673.0	672.3	671.7	671.0	670.3
160°	682.1	683.0	683.8	684.0	683.4	682.9	682.3	681.8
162.5°	692.3	693.2	694.2	694.3	693.6	693.0	692.3	691.7
165°	705.4	706.3	707.3	707.4	706.7	706.0	705.4	704.6
167.5°	716.1	717.1	718.0	718.2	717.5	716.8	716.1	715.3
170°	722.1	723.0	724.0	724.1	723.3	722.4	721.6	720.7
172.5°	726.5	727.5	728.4	728.5	727.7	726.8	726.0	725.2
175°	731.3	732.3	733.2	733.3	732.5	731.7	730.9	730.1
177.5°	733.6	734.3	734.9	734.9	734.3	733.6	732.9	732.3
180°	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7

(END OF REPORT)