

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331638-927

Luminaire Tested: **SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331638-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3682.4 lumens  
Efficiency: N/A  
Efficacy: 98.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331638-927  
CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331638-927

CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	59	52	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	19	20	17	15	13	12	10	8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331638-927

CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.2	1.0
10°-20°	102.2	2.8
20°-30°	143.5	3.9
30°-40°	156.5	4.2
40°-50°	143.9	3.9
50°-60°	113.0	3.1
60°-70°	73.7	2.0
70°-80°	38.0	1.0
80°-90°	13.5	0.4
90°-100°	164.4	4.5
100°-110°	557.8	15.1
110°-120°	592.6	16.1
120°-130°	487.8	13.2
130°-140°	391.8	10.6
140°-150°	296.0	8.0
150°-160°	208.1	5.6
160°-170°	122.5	3.3
170°-180°	39.9	1.1
0°-30°	282.9	7.7
0°-40°	439.4	11.9
0°-60°	696.4	18.9
0°-90°	821.6	22.3
90°-120°	1314.8	35.7
90°-150°	2490.5	67.6
90°-180°	2861.0	77.7
0°-180°	3682.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	1	11	27	26	26	2
95°	28	68	310	117	90	29
105°	96	145	586	1047	891	102
115°	170	215	490	1012	1172	169
125°	237	281	471	819	951	211
135°	278	332	466	689	788	215
145°	318	365	463	575	629	199
155°	361	390	450	509	529	166
165°	394	406	431	457	464	111
175°	410	411	414	420	418	39
180°	411	411	411	411	411	



TEST NUMBER: P331638-927

CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.8	4.8	4.8	4.7	4.4	4.7	5.5	6.6	7.5	7.7	7.4
90°	0.8	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1
92.5°	9.7	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8
95°	27.6	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2
97.5°	45.1	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0
100°	60.8	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5
102.5°	75.4	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8
105°	96.5	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1
107.5°	119.2	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7
110°	134.4	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1



TEST NUMBER: P331638-927

CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.3	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8
115°	170.0	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1
117.5°	192.4	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4
120°	206.4	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8
122.5°	219.7	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0
125°	237.2	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6
127.5°	251.1	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4
130°	259.4	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9
132.5°	266.9	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3
135°	278.3	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7
137.5°	289.1	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3
140°	297.3	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9
142.5°	305.5	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5
145°	317.8	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6
147.5°	331.1	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6
150°	340.0	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5
152.5°	348.8	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1
155°	361.3	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9
157.5°	371.8	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2
160°	378.7	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5
162.5°	385.6	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4
165°	393.7	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0
167.5°	400.4	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8
170°	404.8	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3
172.5°	407.3	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0
175°	410.4	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1
177.5°	411.8	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331638-927

CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	7.2	6.9	7.1	7.2	7.2	7.2	7.2	7.2
90°	25.3	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	207.2	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	483.4	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	721.8	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	878.1	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	960.6	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	901.2	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	849.9	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8





TEST NUMBER: P331638-927

CATALOG NUMBER: SA2XXRDIP-C290D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	803.1	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	745.5	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	702.2	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	680.7	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	663.6	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	638.8	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	614.3	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	598.5	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	583.3	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	562.1	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	545.2	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	534.5	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	525.6	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	513.1	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	503.4	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	496.5	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	489.6	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	479.9	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	468.7	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	461.7	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	454.8	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	444.3	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	434.4	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	429.3	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	423.6	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	417.5	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)