

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333500-935

Luminaire Tested: **S125RDIP-S375D590U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333500-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D590U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3007.2 lumens  
Efficiency: N/A  
Efficacy: 117.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35				
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	25				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19				
6	62	50	42	36	56	46	39	34	39	33	29	31	28	25	25	22	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3402	3402	3402
5°	3411	3371	3392
10°	3385	3341	3341
15°	3344	3273	3245
20°	3293	3178	3140
25°	3233	3085	3017
30°	3157	2976	2882
35°	3080	2864	2730
40°	3010	2748	2580
45°	2922	2617	2417
50°	2834	2475	2247
55°	2733	2339	2066
60°	2631	2174	1870
65°	2512	1984	1647
70°	2374	1743	1420
75°	2186	1470	1183
80°	1923	1153	993
85°	1623	941	889



TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.5	1.6
10°-20°	138.4	4.6
20°-30°	200.8	6.7
30°-40°	228.8	7.6
40°-50°	223.0	7.4
50°-60°	187.7	6.2
60°-70°	131.6	4.4
70°-80°	67.6	2.2
80°-90°	18.5	0.6
90°-100°	42.3	1.4
100°-110°	124.8	4.2
110°-120°	211.4	7.0
120°-130°	278.3	9.3
130°-140°	311.8	10.4
140°-150°	305.6	10.2
150°-160°	256.7	8.5
160°-170°	170.6	5.7
170°-180°	59.7	2.0
0°-30°	388.7	12.9
0°-40°	617.6	20.5
0°-60°	1028.3	34.2
0°-90°	1246.0	41.4
90°-120°	378.5	12.6
90°-150°	1274.2	42.4
90°-180°	1761.0	58.6
0°-180°	3007.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	523	50
15°	500	498	490	489	485	141
25°	454	447	433	428	423	209
35°	391	381	363	352	346	245
45°	320	308	286	271	265	247
55°	243	230	208	190	184	217
65°	164	150	130	114	108	163
75°	88	75	59	50	47	93
85°	22	15	13	12	12	25
90°	0	4	8	10	12	3
95°	32	33	38	41	42	34
105°	112	114	117	120	122	120
115°	212	214	215	214	214	209
125°	309	312	312	311	311	277
135°	402	405	405	405	403	310
145°	487	489	490	490	489	304
155°	557	557	558	559	557	256
165°	606	605	605	607	604	171
175°	630	628	628	630	627	60
180°	631	631	631	631	631	



TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	527.8	527.6	527.4	527.2	526.9	526.5	525.8	525.0	524.3	523.7	524.3
5°	526.1	525.7	525.4	525.0	524.6	524.0	523.0	522.0	521.1	520.0	521.0
7.5°	520.9	520.6	520.2	519.9	519.5	518.8	517.6	516.4	515.3	514.1	514.7
10°	516.1	515.8	515.6	515.3	515.1	514.3	513.1	511.8	510.6	509.4	509.6
12.5°	510.7	510.3	510.1	509.7	509.4	508.3	506.7	505.1	503.3	501.7	501.9
15°	500.2	499.6	499.1	498.6	498.1	496.9	495.0	493.2	491.3	489.5	489.4
17.5°	488.4	487.5	486.7	485.9	485.1	483.5	481.1	478.8	476.5	474.2	473.7
20°	479.1	478.2	477.3	476.5	475.5	473.7	470.9	468.0	465.2	462.4	461.9
22.5°	468.9	468.0	467.2	466.2	465.4	463.5	460.5	457.5	454.5	451.6	450.7
25°	453.7	452.3	451.0	449.6	448.3	446.0	442.7	439.5	436.2	432.9	431.8
27.5°	436.1	434.5	432.9	431.3	429.6	427.1	423.6	420.1	416.6	413.1	411.5
30°	423.4	421.7	420.0	418.4	416.6	414.0	410.3	406.6	402.9	399.1	397.1
32.5°	411.0	409.0	407.1	405.1	403.1	400.3	396.5	392.7	388.9	385.1	382.9
35°	390.7	388.7	386.5	384.4	382.3	379.2	375.2	371.3	367.3	363.3	360.8
37.5°	370.9	368.3	365.8	363.2	360.6	357.2	353.2	349.0	345.0	340.9	337.8
40°	357.0	354.3	351.6	349.0	346.3	342.9	338.6	334.4	330.1	325.9	322.5
42.5°	342.2	339.6	336.8	334.2	331.4	327.9	323.5	319.1	314.7	310.3	307.1
45°	319.9	317.4	314.8	312.2	309.7	305.9	301.1	296.3	291.4	286.5	282.9
47.5°	296.8	294.0	291.4	288.6	285.9	282.1	277.2	272.3	267.4	262.5	258.9
50°	282.1	279.2	276.3	273.4	270.4	266.5	261.4	256.4	251.3	246.3	242.6
52.5°	266.2	263.2	260.2	257.3	254.3	250.4	245.6	240.8	236.1	231.4	227.4
55°	242.7	239.9	237.0	234.3	231.4	227.6	222.6	217.6	212.7	207.7	203.7
57.5°	219.0	216.0	212.9	209.9	206.9	203.0	198.2	193.5	188.7	183.9	180.0
60°	203.7	200.6	197.5	194.4	191.3	187.4	182.6	177.9	173.1	168.3	164.5
62.5°	187.5	184.5	181.6	178.7	175.6	171.8	166.9	162.1	157.2	152.4	148.8
65°	164.4	161.4	158.3	155.3	152.3	148.4	143.8	139.1	134.4	129.8	126.2
67.5°	141.4	138.4	135.3	132.3	129.3	125.5	121.1	116.6	112.1	107.6	104.4
70°	125.7	122.8	119.8	116.8	113.7	110.0	105.6	101.2	96.8	92.3	89.5
72.5°	110.5	107.5	104.6	101.7	98.8	95.1	91.0	86.9	82.7	78.6	76.1
75°	87.6	84.9	82.2	79.6	77.0	73.8	70.0	66.3	62.6	58.9	56.9
77.5°	64.7	62.7	60.5	58.4	56.3	53.7	50.8	47.8	44.9	41.8	40.5
80°	51.7	49.6	47.5	45.4	43.2	41.0	38.5	36.0	33.5	31.0	30.2
82.5°	39.0	37.1	35.2	33.2	31.3	29.5	27.9	26.2	24.5	22.7	22.4
85°	21.9	20.3	18.7	17.1	15.5	14.5	14.0	13.6	13.2	12.7	12.7
87.5°	7.4	7.1	6.8	6.5	6.1	6.0	6.1	6.2	6.3	6.4	6.5
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	11.9	12.5	13.1	13.7	14.3	15.1	16.0	17.0	17.9	18.9	19.5
95°	31.9	32.1	32.4	32.5	32.8	33.5	34.5	35.6	36.8	37.8	38.6
97.5°	53.0	53.1	53.2	53.3	53.4	54.2	55.7	57.2	58.7	60.2	61.0
100°	68.8	68.8	68.8	68.8	68.8	69.5	70.9	72.3	73.7	75.2	76.1
102.5°	85.7	86.1	86.5	87.0	87.4	88.0	88.7	89.5	90.1	90.8	92.0
105°	112.0	112.5	113.0	113.7	114.2	114.8	115.5	116.1	116.8	117.4	118.0
107.5°	141.0	141.6	142.2	142.7	143.3	143.8	144.3	144.7	145.3	145.8	146.1
110°	161.1	161.6	162.2	162.7	163.3	163.8	164.0	164.4	164.7	165.1	165.4



TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.5	181.8	182.1	182.4	182.7	183.0	183.5	183.8	184.3	184.7	184.9
115°	211.7	212.2	212.6	213.0	213.4	213.8	214.0	214.2	214.4	214.6	214.6
117.5°	241.9	242.1	242.4	242.5	242.7	243.0	243.1	243.3	243.5	243.7	243.8
120°	260.8	261.4	261.9	262.4	263.0	263.3	263.5	263.6	263.6	263.7	263.7
122.5°	281.3	281.5	281.6	281.8	282.1	282.2	282.6	282.8	283.1	283.4	283.4
125°	308.9	309.6	310.2	310.9	311.6	311.9	312.0	312.2	312.3	312.4	312.2
127.5°	338.5	338.8	339.1	339.5	339.9	340.2	340.3	340.4	340.5	340.7	340.6
130°	356.1	356.6	357.2	357.7	358.3	358.7	358.9	359.1	359.3	359.6	359.5
132.5°	373.8	374.7	375.6	376.4	377.4	377.8	377.7	377.7	377.6	377.6	377.5
135°	401.7	402.4	403.1	403.7	404.4	404.8	404.9	405.0	405.1	405.2	405.2
137.5°	428.1	428.8	429.4	430.0	430.7	431.1	431.4	431.5	431.8	432.0	432.1
140°	445.0	445.6	446.1	446.6	447.2	447.6	448.0	448.3	448.6	448.9	449.2
142.5°	461.9	462.4	462.8	463.3	463.7	464.2	464.6	465.0	465.5	465.8	466.0
145°	486.7	487.2	487.7	488.1	488.5	488.9	489.2	489.6	489.9	490.2	490.2
147.5°	509.7	510.0	510.2	510.5	510.7	510.9	511.2	511.5	511.8	512.0	512.3
150°	525.0	525.0	524.9	524.8	524.6	524.8	525.2	525.6	526.1	526.5	526.5
152.5°	537.6	537.8	538.0	538.1	538.2	538.4	538.6	538.7	538.9	539.2	539.4
155°	557.0	557.0	557.0	557.0	557.0	557.1	557.2	557.2	557.4	557.5	557.9
157.5°	574.3	574.0	573.8	573.6	573.3	573.3	573.3	573.5	573.6	573.7	574.1
160°	584.5	584.2	583.8	583.5	583.2	583.1	583.2	583.3	583.4	583.5	583.9
162.5°	593.6	593.3	593.1	592.8	592.5	592.5	592.5	592.5	592.5	592.5	593.1
165°	605.6	605.4	605.2	604.9	604.8	604.7	604.8	604.9	605.0	605.1	605.5
167.5°	615.9	615.4	614.9	614.5	614.1	613.9	613.9	613.9	613.9	613.9	614.5
170°	621.3	620.9	620.4	620.0	619.6	619.4	619.4	619.4	619.4	619.4	620.0
172.5°	625.3	624.8	624.4	624.0	623.5	623.3	623.3	623.3	623.3	623.3	624.0
175°	629.6	629.2	628.8	628.4	627.9	627.8	627.8	627.8	627.8	627.8	628.4
177.5°	632.0	631.6	631.3	630.9	630.5	630.3	630.3	630.2	630.1	630.0	630.5
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2



TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	525.0	525.8	526.5	526.8	526.8	526.7	526.6	526.5
5°	521.9	522.7	523.6	524.0	523.8	523.6	523.4	523.2
7.5°	515.3	516.0	516.6	516.8	516.6	516.4	516.3	516.0
10°	509.9	510.1	510.4	510.4	510.1	509.9	509.6	509.4
12.5°	502.0	502.3	502.5	502.4	502.0	501.5	501.2	500.8
15°	489.2	489.1	489.0	488.6	487.8	487.1	486.3	485.4
17.5°	473.3	472.9	472.4	471.8	471.2	470.5	469.8	469.2
20°	461.5	461.1	460.6	460.0	459.2	458.4	457.6	456.8
22.5°	449.8	448.9	448.1	447.3	446.7	446.0	445.4	444.7
25°	430.7	429.5	428.3	427.3	426.3	425.3	424.4	423.4
27.5°	409.9	408.3	406.7	405.4	404.5	403.6	402.6	401.7
30°	395.0	393.0	391.0	389.6	388.7	388.0	387.2	386.4
32.5°	380.6	378.4	376.1	374.5	373.5	372.5	371.4	370.5
35°	358.2	355.6	353.0	351.1	349.9	348.7	347.4	346.2
37.5°	334.7	331.7	328.6	326.4	325.2	324.0	322.8	321.6
40°	319.2	315.8	312.5	310.2	309.2	308.2	307.0	306.0
42.5°	303.8	300.7	297.4	295.1	293.5	291.9	290.3	288.8
45°	279.4	275.9	272.3	269.9	268.6	267.3	266.0	264.6
47.5°	255.3	251.6	248.0	245.4	243.9	242.5	241.0	239.5
50°	238.8	235.1	231.4	228.9	227.6	226.3	225.0	223.6
52.5°	223.3	219.4	215.3	212.7	211.4	210.1	208.7	207.4
55°	199.8	195.8	191.8	189.1	187.7	186.2	184.9	183.5
57.5°	176.2	172.3	168.3	165.7	164.5	163.2	162.0	160.7
60°	160.6	156.6	152.7	150.2	148.8	147.5	146.2	144.8
62.5°	145.2	141.5	137.9	135.5	134.1	132.9	131.6	130.2
65°	122.6	119.1	115.5	113.1	111.8	110.5	109.2	107.8
67.5°	101.1	97.9	94.6	92.5	91.4	90.4	89.3	88.3
70°	86.9	84.1	81.4	79.5	78.4	77.3	76.3	75.2
72.5°	73.5	71.0	68.5	66.9	66.2	65.5	64.7	64.1
75°	55.0	53.0	51.1	49.9	49.2	48.6	48.0	47.4
77.5°	39.2	37.8	36.4	35.5	35.0	34.6	34.1	33.7
80°	29.4	28.7	27.9	27.4	27.2	27.0	26.9	26.7
82.5°	22.0	21.6	21.3	21.0	20.9	20.8	20.8	20.6
85°	12.6	12.5	12.4	12.3	12.2	12.1	12.1	12.0
87.5°	6.5	6.7	6.8	6.8	6.8	6.8	6.8	6.8
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	20.3	21.0	21.8	22.2	22.5	22.7	22.9	23.2
95°	39.3	40.1	40.9	41.3	41.6	41.8	42.0	42.3
97.5°	61.6	62.4	63.1	63.5	63.6	63.8	63.9	64.1
100°	77.1	78.1	79.0	79.6	79.9	80.2	80.3	80.6
102.5°	93.0	94.1	95.1	95.8	96.2	96.4	96.8	97.0
105°	118.7	119.3	120.0	120.5	120.8	121.1	121.5	121.8
107.5°	146.5	146.8	147.1	147.2	147.2	147.2	147.1	147.1
110°	165.7	166.0	166.3	166.4	166.3	166.3	166.1	166.0





TEST NUMBER: P333500-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	185.0	185.1	185.3	185.3	185.1	184.9	184.7	184.5
115°	214.4	214.3	214.2	214.1	214.0	213.9	213.8	213.7
117.5°	243.9	244.0	244.1	243.9	243.5	243.1	242.6	242.1
120°	263.7	263.7	263.7	263.6	263.1	262.7	262.3	261.8
122.5°	283.3	283.2	283.1	282.8	282.5	282.1	281.8	281.5
125°	311.9	311.8	311.5	311.3	311.3	311.2	311.0	310.9
127.5°	340.4	340.4	340.3	340.1	339.8	339.7	339.4	339.2
130°	359.3	359.2	359.1	359.0	358.7	358.5	358.3	358.1
132.5°	377.4	377.3	377.2	376.9	376.7	376.3	376.1	375.7
135°	405.2	405.2	405.2	405.0	404.6	404.2	403.7	403.3
137.5°	432.3	432.4	432.6	432.4	431.8	431.3	430.8	430.2
140°	449.4	449.6	449.8	449.6	449.1	448.6	448.0	447.5
142.5°	466.1	466.2	466.3	466.1	465.6	465.0	464.5	464.0
145°	490.2	490.2	490.2	490.0	489.7	489.4	489.0	488.7
147.5°	512.6	512.8	513.1	512.8	512.0	511.3	510.6	509.9
150°	526.5	526.5	526.5	526.4	526.2	526.0	525.8	525.6
152.5°	539.7	539.9	540.2	540.1	539.7	539.3	538.9	538.6
155°	558.4	558.8	559.2	559.2	558.6	558.1	557.5	557.0
157.5°	574.5	575.0	575.4	575.3	574.5	573.9	573.2	572.4
160°	584.4	584.8	585.2	585.2	584.7	584.1	583.6	583.1
162.5°	593.6	594.1	594.7	594.6	594.0	593.3	592.7	592.0
165°	606.0	606.4	606.9	606.7	606.1	605.5	604.8	604.2
167.5°	615.2	615.9	616.5	616.5	615.8	615.1	614.4	613.8
170°	620.7	621.3	622.0	621.9	621.2	620.4	619.7	618.9
172.5°	624.7	625.3	625.9	625.9	625.3	624.6	623.9	623.2
175°	629.0	629.6	630.3	630.3	629.6	628.8	628.0	627.2
177.5°	631.0	631.5	632.1	632.1	631.5	630.9	630.2	629.6
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2

(END OF REPORT)