

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331672-927

Luminaire Tested: **SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331672-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4758.1 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15	12
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	1.3
10°-20°	168.0	3.5
20°-30°	235.9	5.0
30°-40°	257.3	5.4
40°-50°	236.6	5.0
50°-60°	185.8	3.9
60°-70°	121.1	2.5
70°-80°	62.5	1.3
80°-90°	19.1	0.4
90°-100°	38.8	0.8
100°-110°	142.4	3.0
110°-120°	380.6	8.0
120°-130°	628.2	13.2
130°-140°	668.1	14.0
140°-150°	620.9	13.1
150°-160°	499.2	10.5
160°-170°	321.7	6.8
170°-180°	110.7	2.3
0°-30°	465.2	9.8
0°-40°	722.4	15.2
0°-60°	1144.8	24.1
0°-90°	1347.5	28.3
90°-120°	561.7	11.8
90°-150°	2478.9	52.1
90°-180°	3411.0	71.7
0°-180°	4758.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	10	17	21	23	4
95°	55	29	33	37	36	67
105°	256	267	51	60	64	274
115°	484	499	520	148	69	477
125°	685	696	712	717	720	610
135°	847	860	868	876	875	654
145°	983	983	996	1002	998	614
155°	1082	1076	1085	1089	1083	498
165°	1140	1136	1138	1143	1138	322
175°	1166	1161	1162	1167	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.8	7.3	6.9	6.4	6.0	5.9	6.3	6.6	6.9	7.1	7.2
90°	0.9	2.9	5.0	7.1	9.1	10.9	12.4	13.9	15.4	16.9	17.7
92.5°	17.0	16.8	16.6	16.5	16.2	16.6	17.3	18.1	18.8	19.6	20.0
95°	54.7	48.6	42.4	36.2	30.0	27.6	28.9	30.3	31.5	32.9	33.7
97.5°	108.6	91.3	73.8	56.4	39.1	31.8	34.9	37.9	41.0	44.0	44.7
100°	149.1	123.4	97.8	72.2	46.5	35.3	38.4	41.7	44.8	48.0	49.5
102.5°	193.5	188.1	182.7	177.2	171.8	155.8	129.2	102.6	76.0	49.4	51.3
105°	256.0	261.7	267.2	272.8	278.5	255.7	204.6	153.5	102.4	51.3	53.4
107.5°	327.3	331.8	336.3	340.8	345.4	317.0	255.7	194.5	133.2	71.9	69.8
110°	373.0	377.0	381.0	384.8	388.8	363.7	309.6	255.6	201.5	147.3	128.7



TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	416.2	419.7	423.1	426.6	430.1	425.2	411.8	398.5	385.1	371.7	303.5
115°	484.3	487.4	490.6	493.8	496.9	500.9	505.6	510.2	514.9	519.6	432.9
117.5°	545.0	548.6	552.2	555.7	559.3	562.6	565.9	569.1	572.3	575.5	554.5
120°	589.5	592.3	595.1	597.9	600.7	603.8	607.2	610.5	613.9	617.3	619.5
122.5°	627.2	630.2	633.1	636.1	639.1	642.4	646.0	649.7	653.4	657.0	658.4
125°	684.7	687.1	689.5	692.0	694.3	697.4	700.9	704.5	708.1	711.6	712.9
127.5°	736.7	739.4	742.1	744.8	747.5	750.1	752.8	755.4	758.1	760.8	762.7
130°	769.7	772.7	775.7	778.7	781.6	784.2	786.2	788.3	790.4	792.4	794.5
132.5°	803.4	806.0	808.5	811.0	813.6	815.9	817.9	820.0	822.0	824.1	825.9
135°	847.2	850.2	853.2	856.2	859.1	861.5	863.2	864.8	866.6	868.2	870.1
137.5°	891.4	893.6	895.6	897.8	899.8	901.8	903.8	905.7	907.6	909.5	911.3
140°	920.4	921.9	923.4	925.0	926.5	928.2	930.3	932.3	934.4	936.4	938.1
142.5°	944.7	946.0	947.4	948.7	950.1	952.0	954.3	956.6	959.0	961.4	962.9
145°	982.8	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	997.5
147.5°	1016.0	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9
150°	1037.5	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2
152.5°	1055.7	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0
155°	1082.1	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8
157.5°	1102.9	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8
160°	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1
162.5°	1125.8	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3
165°	1140.3	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0
167.5°	1151.0	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6
170°	1157.1	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0
172.5°	1161.1	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0
175°	1166.3	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5
177.5°	1167.2	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	7.3	7.4	7.4	7.5	7.6	7.7	7.8	7.8
90°	18.7	19.6	20.6	21.2	21.6	22.0	22.3	22.7
92.5°	20.5	21.0	21.5	21.9	22.1	22.3	22.5	22.7
95°	34.7	35.6	36.6	37.0	36.8	36.6	36.4	36.2
97.5°	45.5	46.2	47.0	47.5	47.7	47.9	48.1	48.3
100°	51.0	52.5	54.0	54.9	55.3	55.7	56.1	56.4
102.5°	53.2	55.2	57.1	58.4	58.9	59.4	60.0	60.4
105°	55.5	57.5	59.6	61.0	61.8	62.5	63.2	64.0
107.5°	67.7	65.6	63.5	62.9	63.6	64.3	65.1	65.8
110°	110.0	91.3	72.5	63.5	64.2	65.0	65.8	66.5



TEST NUMBER: P331672-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.2	166.9	98.6	64.8	65.4	66.0	66.6	67.2
115°	346.3	259.7	173.0	122.9	109.5	96.0	82.5	69.1
117.5°	533.6	512.6	491.7	459.1	414.8	370.5	326.2	281.9
120°	621.8	624.0	626.3	614.7	589.5	564.2	538.9	513.7
122.5°	659.7	661.1	662.4	660.6	655.8	650.9	645.9	641.0
125°	714.2	715.5	716.8	717.8	718.4	718.9	719.5	720.0
127.5°	764.6	766.5	768.4	769.4	769.5	769.7	769.8	769.8
130°	796.5	798.6	800.7	801.6	801.5	801.2	801.1	800.9
132.5°	827.6	829.4	831.2	831.9	831.7	831.6	831.4	831.2
135°	872.0	873.9	875.7	876.5	876.1	875.7	875.4	875.0
137.5°	913.1	915.0	916.8	917.4	916.8	916.2	915.5	914.9
140°	939.8	941.5	943.2	943.6	942.6	941.7	940.7	939.8
142.5°	964.4	966.0	967.5	967.8	966.9	965.9	965.0	964.1
145°	998.9	1000.1	1001.5	1001.6	1000.8	999.8	998.9	997.9
147.5°	1028.8	1029.8	1030.8	1030.9	1030.1	1029.3	1028.5	1027.7
150°	1047.3	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1064.1	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1086.9	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1106.0	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1117.2	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1127.6	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1151.0	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1156.3	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1160.4	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1164.7	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1165.2	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)