

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331673-927

Luminaire Tested: **SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331673-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4398.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	34	33	26
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	19
4	72	61	54	48	64	56	49	44	44	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	16	15	12
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	27	22	41	31	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	1.4
10°-20°	168.0	3.8
20°-30°	235.9	5.4
30°-40°	257.3	5.9
40°-50°	236.6	5.4
50°-60°	185.8	4.2
60°-70°	121.1	2.8
70°-80°	62.5	1.4
80°-90°	20.6	0.5
90°-100°	69.1	1.6
100°-110°	214.6	4.9
110°-120°	366.8	8.3
120°-130°	482.4	11.0
130°-140°	541.4	12.3
140°-150°	530.9	12.1
150°-160°	445.3	10.1
160°-170°	295.3	6.7
170°-180°	103.2	2.3
0°-30°	465.2	10.6
0°-40°	722.4	16.4
0°-60°	1144.8	26.0
0°-90°	1349.0	30.7
90°-120°	650.5	14.8
90°-150°	2205.2	50.1
90°-180°	3049.0	69.3
0°-180°	4398.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	12	32	31	31	4
95°	48	57	59	59	57	55
105°	198	201	202	204	204	209
115°	368	373	372	371	368	364
125°	536	543	541	538	537	478
135°	693	703	705	704	701	535
145°	841	847	853	854	850	525
155°	962	964	967	971	969	442
165°	1046	1045	1045	1051	1047	295
175°	1089	1086	1084	1090	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.8	7.4	7.1	6.7	6.3	6.7	7.5	8.4	9.3	10.2	10.1
90°	1.0	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8
92.5°	16.4	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3
95°	47.8	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9
97.5°	87.5	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0
100°	116.8	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0
102.5°	147.8	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3
105°	197.8	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9
107.5°	248.3	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5
110°	280.7	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.0	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3
115°	368.0	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5
117.5°	419.9	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7
120°	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6
122.5°	486.2	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4
125°	535.5	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4
127.5°	583.6	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0
130°	613.8	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4
132.5°	647.6	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9
135°	692.9	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6
137.5°	740.5	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1
140°	769.3	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1
142.5°	798.8	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3
145°	841.1	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2
147.5°	878.8	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7
150°	904.5	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3
152.5°	927.3	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1
155°	961.6	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1
157.5°	990.9	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8
160°	1008.5	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5
162.5°	1024.7	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4
165°	1046.2	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8
167.5°	1064.3	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8
170°	1073.9	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6
172.5°	1080.5	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2
175°	1088.6	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4
177.5°	1091.9	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	9.8	9.7	9.5	9.4	9.4	9.5	9.5	9.6
90°	31.4	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.4	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.5	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.3	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.6	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	286.2	285.9	285.3	284.6	284.0	283.4



TEST NUMBER: P331673-927

CATALOG NUMBER: SA2XXRDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.4	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	421.2	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.9	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.9	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	589.3	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	623.1	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.9	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.5	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.9	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.5	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.4	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.1	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	969.2	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	997.1	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1013.8	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1028.8	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1048.2	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1064.2	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1073.0	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1079.7	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1086.9	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)