

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331656-927

Luminaire Tested: **SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331656-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2981.5 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331656-927
CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331656-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331656-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	2.1
10°-20°	168.0	5.6
20°-30°	235.9	7.9
30°-40°	257.3	8.6
40°-50°	236.6	7.9
50°-60°	185.8	6.2
60°-70°	121.1	4.1
70°-80°	62.5	2.1
80°-90°	18.3	0.6
90°-100°	93.9	3.2
100°-110°	318.8	10.7
110°-120°	338.6	11.4
120°-130°	278.8	9.3
130°-140°	223.9	7.5
140°-150°	169.2	5.7
150°-160°	118.9	4.0
160°-170°	70.0	2.3
170°-180°	22.8	0.8
0°-30°	465.2	15.6
0°-40°	722.4	24.2
0°-60°	1144.8	38.4
0°-90°	1346.7	45.2
90°-120°	751.3	25.2
90°-150°	1423.1	47.7
90°-180°	1635.0	54.8
0°-180°	2981.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	0	6	15	15	15	2
95°	16	39	177	67	52	17
105°	55	83	335	598	509	59
115°	97	123	280	578	670	96
125°	136	160	269	468	544	120
135°	159	190	266	394	450	123
145°	182	209	265	329	360	114
155°	206	223	257	291	302	95
165°	225	232	246	261	265	63
175°	234	235	237	240	239	22
180°	235	235	235	235	235	



TEST NUMBER: P331656-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.7	7.1	6.6	5.9	5.3	5.1	5.6	6.3	6.7	6.9	6.7
90°	0.5	1.8	3.6	4.5	5.4	6.8	9.0	12.2	14.9	15.4	14.9
92.5°	5.5	7.9	11.2	13.2	16.2	20.5	30.7	45.1	57.9	58.7	49.6
95°	15.8	17.6	22.1	26.2	33.4	44.3	65.0	104.3	156.8	177.1	155.0
97.5°	25.7	28.2	33.0	39.1	47.5	59.7	85.9	140.6	227.7	302.3	317.1
100°	34.8	36.1	40.2	47.5	56.5	69.2	93.1	148.2	245.7	356.9	421.9
102.5°	43.1	44.1	48.2	55.4	64.8	77.4	99.6	148.5	238.9	358.7	461.0
105°	55.1	57.0	60.0	66.9	76.8	89.4	110.7	150.9	225.5	334.8	455.0
107.5°	68.1	69.6	72.6	78.9	88.7	101.5	122.1	157.1	218.7	309.1	415.3
110°	76.8	78.6	81.4	87.2	96.6	109.8	129.7	162.2	217.3	296.8	390.3



TEST NUMBER: P331656-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	86.6	89.6	95.1	104.3	117.7	136.9	167.6	217.7	288.8	373.0
115°	97.1	99.4	102.1	107.5	116.5	128.7	148.2	175.7	219.6	280.1	351.5
117.5°	110.0	111.8	114.5	119.3	127.9	140.6	158.6	184.4	222.8	275.8	337.9
120°	117.9	119.7	122.4	126.5	135.5	148.2	165.8	190.2	225.0	273.3	330.7
122.5°	125.5	127.0	129.7	134.1	143.1	156.1	172.7	195.3	227.5	271.9	324.6
125°	135.5	136.9	139.6	145.0	154.1	166.7	183.0	203.3	231.3	269.3	315.8
127.5°	143.5	145.3	149.1	155.0	163.7	176.7	192.6	210.8	235.2	267.8	307.7
130°	148.2	150.0	154.5	160.8	169.8	182.5	198.4	215.5	238.1	267.0	302.2
132.5°	152.5	154.7	159.5	166.3	175.6	188.3	203.4	220.2	241.0	266.6	297.9
135°	159.0	160.8	166.3	173.0	183.4	196.1	210.6	226.3	244.4	266.1	291.8
137.5°	165.2	167.3	172.8	180.0	190.3	202.0	216.3	231.0	247.5	266.0	287.6
140°	169.8	171.7	177.1	184.3	194.2	206.0	219.6	233.5	248.9	265.6	285.1
142.5°	174.6	176.0	181.1	188.3	197.9	208.9	222.1	235.8	250.0	265.6	282.6
145°	181.6	183.4	187.9	194.7	203.7	213.7	225.9	238.5	251.2	264.7	279.2
147.5°	189.2	190.5	194.9	201.1	208.7	217.5	228.9	240.1	251.5	263.1	275.8
150°	194.2	195.6	199.2	205.1	211.9	220.0	230.4	240.8	251.2	262.1	272.9
152.5°	199.3	199.9	203.6	208.7	215.2	222.5	231.9	241.1	250.5	260.2	270.4
155°	206.4	206.9	209.6	214.6	219.6	226.3	234.0	241.7	249.4	257.1	265.6
157.5°	212.4	212.9	215.1	219.4	223.4	229.0	235.5	241.7	247.3	253.8	261.2
160°	216.4	216.8	218.6	222.3	225.9	230.8	236.3	241.7	246.2	251.7	257.9
162.5°	220.4	220.1	221.9	224.8	228.1	232.0	236.6	241.3	245.1	249.9	255.1
165°	225.0	224.5	225.5	228.1	230.4	233.1	237.2	240.3	243.0	246.2	250.3
167.5°	228.8	228.2	229.0	230.8	232.4	234.1	237.1	239.7	241.0	243.0	245.6
170°	231.3	230.4	230.8	232.2	233.1	234.5	236.7	239.0	239.9	241.2	243.0
172.5°	232.7	232.2	232.0	233.3	233.9	234.8	236.4	237.9	238.4	239.1	240.5
175°	234.5	234.0	233.5	234.5	234.5	234.9	235.8	236.7	236.3	236.7	237.2
177.5°	235.3	234.6	234.2	234.9	234.9	234.9	235.3	236.0	235.3	234.9	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331656-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	6.5	6.2	6.3	6.3	6.3	6.3	6.3	6.3
90°	14.4	13.5	14.4	14.9	14.9	14.9	14.9	14.9
92.5°	39.4	33.8	30.0	27.2	26.9	25.4	25.7	25.0
95°	118.4	90.8	71.9	61.9	56.0	52.4	51.0	51.5
97.5°	276.2	226.0	177.1	144.5	122.9	111.8	105.2	101.4
100°	412.5	356.5	294.5	239.9	202.4	183.0	169.8	161.8
102.5°	501.8	489.1	443.9	385.9	345.2	312.0	295.6	284.6
105°	548.9	599.9	605.9	590.9	562.9	534.9	515.5	509.1
107.5°	514.9	591.8	638.8	660.7	664.2	662.7	658.8	650.4
110°	485.7	566.5	624.3	661.4	680.8	689.4	693.5	693.0



TEST NUMBER: P331656-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	458.9	536.5	598.3	640.8	667.8	682.1	689.8	692.3
115°	426.0	495.6	554.8	601.3	633.3	654.2	665.9	669.9
117.5°	401.2	462.3	516.0	559.7	592.4	614.3	626.7	630.1
120°	389.0	445.0	492.9	534.0	565.6	586.8	599.9	604.4
122.5°	379.2	430.6	475.9	513.0	541.4	562.3	573.9	577.7
125°	365.0	411.5	451.3	485.2	511.4	528.5	539.9	543.5
127.5°	351.0	393.2	430.6	461.9	484.7	500.8	510.6	513.5
130°	342.0	380.9	416.5	446.3	468.5	483.9	492.9	496.5
132.5°	333.4	369.3	402.1	430.1	451.9	467.2	475.5	478.8
135°	321.2	351.0	380.9	406.2	425.6	440.5	448.6	450.4
137.5°	311.6	336.5	360.1	382.2	399.9	412.7	419.9	422.6
140°	305.4	327.1	347.8	367.7	382.2	394.0	400.7	403.5
142.5°	300.3	318.8	336.7	353.3	367.0	377.7	383.7	384.3
145°	293.2	308.1	322.1	335.3	346.0	353.7	358.2	359.6
147.5°	287.7	299.4	310.4	320.0	328.9	335.0	338.1	338.9
150°	283.7	293.7	303.2	311.2	318.1	323.4	326.1	326.6
152.5°	279.7	289.0	297.0	304.0	309.3	314.1	316.1	316.2
155°	274.3	281.5	288.2	293.2	298.2	301.3	303.2	302.2
157.5°	267.8	273.9	279.6	283.4	286.9	289.6	290.4	290.4
160°	263.8	268.8	273.8	276.9	280.1	282.3	282.8	282.8
162.5°	259.8	264.1	268.4	270.8	273.9	275.5	275.9	275.6
165°	253.9	257.1	260.2	262.1	263.8	265.6	265.6	265.2
167.5°	248.2	250.6	252.8	254.4	255.2	256.3	256.2	255.6
170°	245.3	246.7	248.5	249.4	249.9	251.2	250.7	249.9
172.5°	242.1	243.0	244.5	245.0	245.5	246.1	245.7	245.1
175°	238.5	239.0	239.5	239.9	239.9	240.3	239.9	239.0
177.5°	236.0	236.0	236.4	236.4	236.4	236.4	236.0	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9

(END OF REPORT)