

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333565-935

Luminaire Tested: **S125RDIP-S850D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333565-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5588.2 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	61	56	57	52	48	48	44	42	39	37	35	31
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7647	7647	7647
5°	7664	7577	7623
10°	7606	7506	7506
15°	7515	7353	7294
20°	7399	7142	7056
25°	7264	6933	6780
30°	7095	6689	6475
35°	6923	6437	6133
40°	6762	6175	5798
45°	6566	5881	5431
50°	6370	5561	5050
55°	6141	5255	4641
60°	5913	4885	4204
65°	5644	4455	3703
70°	5336	3916	3191
75°	4908	3301	2655
80°	4322	2592	2228
85°	3646	2119	1993



TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	2.0
10°-20°	311.1	5.6
20°-30°	451.2	8.1
30°-40°	514.2	9.2
40°-50°	501.2	9.0
50°-60°	421.9	7.5
60°-70°	295.7	5.3
70°-80°	152.0	2.7
80°-90°	40.3	0.7
90°-100°	33.0	0.6
100°-110°	203.4	3.6
110°-120°	369.0	6.6
120°-130°	473.5	8.5
130°-140°	509.3	9.1
140°-150°	478.1	8.6
150°-160°	386.7	6.9
160°-170°	250.1	4.5
170°-180°	86.3	1.5
0°-30°	873.6	15.6
0°-40°	1387.8	24.8
0°-60°	2310.8	41.4
0°-90°	2798.8	50.1
90°-120°	605.4	10.8
90°-150°	2066.3	37.0
90°-180°	2789.0	49.9
0°-180°	5588.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1182	1178	1169	1177	1176	112
15°	1124	1118	1100	1099	1091	317
25°	1019	1005	973	961	951	469
35°	878	856	816	791	778	550
45°	719	692	644	609	595	554
55°	545	516	467	428	412	488
65°	369	338	292	257	242	366
75°	197	169	132	113	106	208
85°	49	34	29	28	27	55
90°	1	6	11	14	16	4
95°	38	35	11	14	14	49
105°	198	200	201	201	200	210
115°	372	375	376	373	369	368
125°	529	533	533	531	529	472
135°	659	663	662	660	656	508
145°	764	766	766	766	762	478
155°	842	838	839	841	836	388
165°	888	884	885	888	883	251
175°	908	905	905	910	904	86
180°	908	908	908	908	908	



TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1186.0	1185.6	1185.1	1184.6	1184.1	1183.1	1181.6	1179.9	1178.4	1176.7	1178.4
5°	1182.2	1181.4	1180.5	1179.7	1179.0	1177.5	1175.3	1173.1	1170.9	1168.7	1170.7
7.5°	1170.5	1169.8	1169.0	1168.2	1167.5	1165.8	1163.2	1160.5	1158.0	1155.3	1156.7
10°	1159.8	1159.2	1158.6	1158.0	1157.4	1155.7	1153.0	1150.1	1147.4	1144.6	1145.1
12.5°	1147.6	1146.9	1146.1	1145.4	1144.6	1142.4	1138.6	1134.9	1131.2	1127.4	1127.8
15°	1124.0	1122.8	1121.6	1120.4	1119.2	1116.5	1112.4	1108.2	1104.1	1099.8	1099.7
17.5°	1097.3	1095.5	1093.7	1091.9	1090.0	1086.5	1081.2	1076.0	1070.7	1065.5	1064.5
20°	1076.6	1074.6	1072.6	1070.7	1068.7	1064.5	1058.2	1051.8	1045.4	1039.1	1038.1
22.5°	1053.7	1051.7	1049.7	1047.8	1045.8	1041.5	1034.7	1028.1	1021.4	1014.8	1012.8
25°	1019.4	1016.4	1013.4	1010.5	1007.5	1002.3	995.0	987.6	980.2	972.9	970.3
27.5°	980.1	976.5	972.8	969.2	965.6	959.8	952.0	944.1	936.3	928.3	924.7
30°	951.4	947.6	943.9	940.1	936.3	930.2	922.0	913.6	905.3	896.9	892.3
32.5°	923.5	919.1	914.7	910.3	905.9	899.4	891.0	882.4	873.9	865.4	860.4
35°	878.1	873.3	868.6	863.8	859.0	852.1	843.3	834.3	825.4	816.4	810.6
37.5°	833.5	827.8	822.0	816.1	810.4	802.9	793.7	784.4	775.2	765.9	759.1
40°	802.1	796.2	790.1	784.2	778.3	770.5	761.0	751.4	741.9	732.4	724.8
42.5°	769.2	763.1	757.0	750.8	744.7	736.8	726.9	717.0	707.1	697.3	690.1
45°	718.9	713.2	707.4	701.6	695.9	687.5	676.6	665.7	654.8	643.9	635.8
47.5°	666.9	660.8	654.7	648.7	642.6	634.0	623.0	612.0	601.0	590.0	581.8
50°	634.0	627.4	620.9	614.3	607.8	598.8	587.5	576.2	564.8	553.5	545.2
52.5°	598.2	591.5	584.8	578.1	571.4	562.7	552.0	541.3	530.5	519.9	510.9
55°	545.4	539.1	532.8	526.4	520.0	511.3	500.2	489.0	477.9	466.7	457.8
57.5°	492.1	485.3	478.5	471.7	465.0	456.2	445.5	434.7	424.0	413.3	404.6
60°	457.8	450.9	443.9	437.0	430.0	421.2	410.4	399.7	389.0	378.2	369.5
62.5°	421.4	414.7	408.1	401.4	394.8	386.1	375.1	364.3	353.4	342.5	334.4
65°	369.3	362.6	355.8	349.0	342.2	333.6	323.1	312.5	302.0	291.5	283.5
67.5°	317.6	310.8	304.1	297.4	290.6	282.1	272.1	262.0	251.9	241.8	234.5
70°	282.6	275.8	269.1	262.3	255.5	247.2	237.3	227.3	217.4	207.4	201.3
72.5°	248.2	241.6	235.1	228.4	221.9	213.9	204.6	195.3	186.0	176.7	171.0
75°	196.7	190.8	184.8	178.8	172.9	165.7	157.4	149.0	140.7	132.3	127.9
77.5°	145.6	140.8	136.0	131.3	126.5	120.8	114.1	107.5	100.7	94.1	91.0
80°	116.2	111.5	106.7	101.9	97.2	92.0	86.4	80.8	75.3	69.7	67.9
82.5°	87.6	83.3	79.0	74.7	70.4	66.4	62.6	58.8	54.9	51.1	50.3
85°	49.2	45.6	42.0	38.5	34.9	32.5	31.6	30.6	29.6	28.6	28.4
87.5°	16.6	15.8	14.8	13.9	13.1	12.7	12.7	12.7	12.8	12.9	13.0
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	10.3	9.6	8.7	7.8	7.1	7.1	8.0	9.0	9.8	10.8	11.5
95°	38.4	38.0	37.5	37.0	36.6	33.5	27.8	22.1	16.4	10.8	11.5
97.5°	80.2	80.9	81.7	82.6	83.3	78.2	66.9	55.6	44.3	33.1	28.9
100°	112.4	112.9	113.3	113.8	114.3	114.8	115.4	116.0	116.6	117.2	94.9
102.5°	145.3	145.9	146.5	147.0	147.6	148.0	148.4	148.8	149.1	149.5	145.3
105°	197.9	198.5	199.1	199.8	200.4	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.6	252.6	252.6	252.6	252.8	253.0	253.4	253.7	254.0	254.0
110°	288.2	288.2	288.2	288.2	288.2	288.3	288.6	289.0	289.2	289.6	289.1



TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	321.6	321.9	322.3	322.7	323.0	323.3	323.5	323.6	323.8	324.0	323.5
115°	371.7	372.5	373.2	373.9	374.7	375.1	375.3	375.4	375.6	375.7	375.1
117.5°	423.5	423.5	423.4	423.4	423.4	423.7	424.2	424.8	425.4	425.9	425.2
120°	455.8	455.7	455.6	455.4	455.2	455.4	455.8	456.3	456.8	457.2	456.9
122.5°	484.4	485.0	485.5	486.1	486.6	487.1	487.2	487.5	487.7	487.9	487.6
125°	528.6	529.6	530.6	531.8	532.8	533.3	533.3	533.3	533.3	533.3	532.7
127.5°	570.8	571.4	572.2	573.0	573.7	574.0	573.9	573.9	573.8	573.7	573.3
130°	596.6	597.4	598.1	598.8	599.6	600.0	600.2	600.3	600.5	600.6	600.2
132.5°	622.4	623.3	624.1	625.0	625.9	626.2	625.9	625.5	625.2	624.8	624.7
135°	659.2	660.1	661.0	661.9	662.8	663.1	662.8	662.5	662.2	661.9	661.6
137.5°	693.0	693.8	694.6	695.3	696.1	696.4	696.1	695.9	695.6	695.3	695.3
140°	715.1	715.4	715.7	716.0	716.3	716.4	716.2	716.1	715.9	715.7	716.1
142.5°	735.0	735.2	735.4	735.6	735.7	735.9	736.2	736.3	736.6	736.8	736.8
145°	764.2	764.6	764.8	765.2	765.4	765.6	765.6	765.6	765.6	765.6	765.8
147.5°	789.8	789.8	789.7	789.6	789.6	789.6	789.8	790.0	790.2	790.4	790.6
150°	806.0	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	806.3
152.5°	821.7	821.0	820.3	819.7	819.0	818.8	819.1	819.4	819.7	820.0	820.3
155°	841.7	840.8	839.9	839.0	838.1	837.8	838.1	838.4	838.7	839.0	839.4
157.5°	857.1	856.6	856.1	855.6	855.0	854.7	854.8	854.8	854.8	854.9	855.3
160°	868.0	867.0	866.2	865.2	864.4	864.0	864.1	864.3	864.4	864.5	865.1
162.5°	876.6	875.6	874.8	873.8	873.0	872.6	872.7	872.9	873.1	873.2	874.0
165°	888.1	887.3	886.3	885.5	884.5	884.2	884.3	884.5	884.6	884.8	885.7
167.5°	896.7	895.9	894.9	894.0	893.0	892.7	892.8	892.9	893.1	893.3	894.3
170°	901.6	900.5	899.5	898.5	897.4	897.0	897.1	897.2	897.4	897.6	898.8
172.5°	904.8	903.8	902.8	901.7	900.6	900.3	900.5	900.8	901.0	901.3	902.4
175°	908.4	907.4	906.5	905.7	904.7	904.4	904.5	904.7	904.8	905.0	906.2
177.5°	910.0	909.2	908.5	907.8	907.1	906.8	906.9	907.0	907.1	907.2	908.1
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0	1184.0
2.5°	1179.9	1181.6	1183.1	1183.9	1183.7	1183.5	1183.4	1183.2
5°	1172.7	1174.7	1176.6	1177.5	1177.1	1176.6	1176.3	1175.9
7.5°	1158.1	1159.5	1160.9	1161.3	1160.9	1160.5	1160.0	1159.6
10°	1145.7	1146.3	1146.9	1146.9	1146.3	1145.7	1145.1	1144.6
12.5°	1128.3	1128.7	1129.1	1128.9	1128.0	1127.0	1126.2	1125.2
15°	1099.5	1099.2	1099.1	1098.1	1096.3	1094.5	1092.7	1090.9
17.5°	1063.5	1062.6	1061.5	1060.3	1058.9	1057.4	1055.9	1054.5
20°	1037.1	1036.0	1035.1	1033.7	1031.9	1030.1	1028.3	1026.6
22.5°	1010.8	1008.9	1006.9	1005.2	1003.8	1002.3	1000.8	999.4
25°	967.8	965.2	962.6	960.2	957.9	955.8	953.6	951.4
27.5°	921.1	917.5	913.9	911.0	909.0	906.8	904.7	902.6
30°	887.8	883.2	878.6	875.5	873.7	871.8	870.0	868.2
32.5°	855.3	850.2	845.2	841.5	839.3	837.1	834.7	832.5
35°	804.9	799.1	793.3	789.1	786.3	783.5	780.8	777.9
37.5°	752.2	745.2	738.3	733.5	730.8	728.1	725.4	722.7
40°	717.2	709.7	702.1	697.2	694.8	692.4	690.0	687.7
42.5°	682.9	675.6	668.4	663.0	659.5	656.0	652.5	649.0
45°	627.9	620.0	612.0	606.6	603.6	600.6	597.6	594.6
47.5°	573.6	565.4	557.2	551.5	548.2	544.9	541.6	538.3
50°	536.8	528.5	520.1	514.4	511.5	508.5	505.5	502.6
52.5°	502.0	492.9	484.0	477.9	475.0	472.0	469.1	466.1
55°	448.9	440.0	431.0	424.9	421.8	418.6	415.4	412.2
57.5°	395.8	387.1	378.3	372.6	369.7	366.9	364.1	361.3
60°	360.8	352.0	343.3	337.4	334.4	331.5	328.5	325.5
62.5°	326.2	318.1	310.0	304.5	301.5	298.5	295.6	292.6
65°	275.6	267.7	259.7	254.3	251.2	248.3	245.3	242.3
67.5°	227.2	220.0	212.7	207.8	205.5	203.1	200.7	198.4
70°	195.1	189.0	182.8	178.6	176.2	173.7	171.4	169.0
72.5°	165.3	159.6	153.9	150.3	148.7	147.1	145.6	144.0
75°	123.6	119.2	114.9	112.0	110.6	109.2	107.8	106.4
77.5°	87.9	84.9	81.8	79.8	78.8	77.7	76.7	75.7
80°	66.2	64.4	62.6	61.5	61.1	60.7	60.3	59.9
82.5°	49.5	48.6	47.8	47.3	47.0	46.8	46.6	46.3
85°	28.2	28.0	27.8	27.6	27.4	27.2	27.0	26.9
87.5°	13.2	13.3	13.5	13.5	13.4	13.3	13.3	13.3
90°	12.3	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	12.3	13.0	13.8	14.2	14.5	14.6	14.9	15.1
95°	12.3	13.0	13.8	14.1	14.1	14.1	14.1	14.1
97.5°	24.7	20.5	16.3	14.1	14.1	14.1	14.1	14.1
100°	72.6	50.3	28.0	16.5	15.9	15.3	14.7	14.1
102.5°	141.0	136.8	132.6	125.4	115.2	105.0	94.9	84.7
105°	200.6	200.6	200.6	200.6	200.4	200.3	200.1	200.0
107.5°	254.1	254.1	254.1	253.9	253.5	253.0	252.5	252.1
110°	288.6	288.2	287.7	287.6	287.7	287.9	288.0	288.2



TEST NUMBER: P333565-935

CATALOG NUMBER: S125RDIP-S850D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.9	322.3	321.8	321.3	321.2	320.9	320.7	320.6
115°	374.5	373.9	373.3	372.6	371.7	370.7	369.9	369.0
117.5°	424.4	423.6	422.8	422.2	421.9	421.5	421.1	420.7
120°	456.6	456.3	456.0	455.5	454.7	454.0	453.2	452.5
122.5°	487.3	487.0	486.7	486.1	485.3	484.4	483.5	482.7
125°	532.1	531.5	530.9	530.4	529.9	529.4	529.0	528.6
127.5°	573.0	572.7	572.4	571.6	570.6	569.5	568.3	567.2
130°	599.7	599.3	598.8	598.2	597.4	596.8	596.0	595.2
132.5°	624.7	624.6	624.5	624.1	623.4	622.6	621.8	621.1
135°	661.3	661.0	660.7	660.1	659.2	658.3	657.4	656.5
137.5°	695.4	695.4	695.5	695.2	694.4	693.6	692.8	692.1
140°	716.4	716.7	717.0	716.7	715.7	714.9	713.9	713.1
142.5°	736.9	736.9	737.0	736.6	735.7	734.8	733.9	733.0
145°	765.9	766.0	766.2	765.8	764.9	764.1	763.1	762.2
147.5°	790.7	790.9	791.1	790.7	789.5	788.5	787.4	786.4
150°	806.6	806.9	807.2	806.8	805.6	804.3	803.1	801.9
152.5°	820.6	820.9	821.2	820.8	819.8	818.6	817.6	816.5
155°	839.9	840.3	840.8	840.4	839.2	838.0	836.8	835.6
157.5°	855.8	856.4	856.8	856.4	855.2	854.0	852.8	851.6
160°	865.7	866.3	866.9	866.7	865.5	864.3	863.1	861.9
162.5°	874.9	875.7	876.5	876.3	874.9	873.7	872.4	871.1
165°	886.6	887.4	888.4	888.2	887.0	885.8	884.6	883.4
167.5°	895.4	896.5	897.6	897.4	896.0	894.8	893.4	892.1
170°	899.9	901.1	902.3	902.2	901.0	899.6	898.2	896.9
172.5°	903.4	904.6	905.7	905.5	904.1	902.8	901.5	900.1
175°	907.3	908.5	909.7	909.6	908.4	907.0	905.7	904.3
177.5°	909.0	909.7	910.6	910.6	909.6	908.6	907.7	906.7
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4

(END OF REPORT)