

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331664-927

Luminaire Tested: **SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331664-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4094.6 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	88	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31
2	87	80	75	70	79	73	68	64	59	56	53	47	44	43	35	34	33	27
3	80	71	64	59	72	65	59	54	53	49	45	42	39	37	32	30	28	24
4	73	63	56	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	57	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19
6	62	51	43	38	56	47	40	35	39	34	30	31	28	25	24	22	20	17
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	20	18	15
8	54	42	35	30	49	39	32	28	32	27	24	26	23	20	20	18	16	14
9	50	38	31	27	45	35	29	25	30	25	21	24	21	18	19	17	15	13
10	47	35	28	24	43	33	27	22	27	23	19	22	19	17	18	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13747	13747	13747	13747
5°	15352	13833	12266	13833
10°	17033	13736	10632	13736
15°	17870	13534	8376	13534
20°	15493	13235	7247	13235
25°	10162	12827	6472	12827
30°	6840	12333	5858	12333
35°	5541	11710	5282	11710
40°	4926	11030	4890	11030
45°	4459	10234	4364	10234
50°	4057	9445	4042	9445
55°	3814	8569	3764	8569
60°	3190	7766	3152	7766
65°	2690	7053	3053	7053
70°	2488	6297	2875	6297
75°	2327	5483	2658	5483
80°	2148	4510	2362	4510
85°	1964	3575	2075	3575



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	2.0
10°-20°	224.9	5.5
20°-30°	289.8	7.1
30°-40°	275.4	6.7
40°-50°	235.9	5.8
50°-60°	179.7	4.4
60°-70°	113.6	2.8
70°-80°	56.7	1.4
80°-90°	18.5	0.5
90°-100°	59.4	1.4
100°-110°	184.4	4.5
110°-120°	315.1	7.7
120°-130°	414.4	10.1
130°-140°	465.2	11.4
140°-150°	456.1	11.1
150°-160°	382.5	9.3
160°-170°	253.7	6.2
170°-180°	88.7	2.2
0°-30°	595.4	14.5
0°-40°	870.8	21.3
0°-60°	1286.4	31.4
0°-90°	1475.1	36.0
90°-120°	558.9	13.6
90°-150°	1894.5	46.3
90°-180°	2620.0	64.0
0°-180°	4094.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	851	851	851	851	851	
5°	947	854	757	854	947	93
15°	1069	810	501	810	1069	288
25°	570	720	363	720	570	271
35°	281	594	268	594	281	180
45°	195	448	191	448	195	151
55°	136	304	134	304	136	119
65°	70	185	80	185	70	72
75°	37	88	43	88	37	40
85°	11	19	11	19	11	12
90°	27	1	27	1	27	12
95°	49	41	49	41	49	55
105°	176	170	176	170	176	185
115°	316	316	316	316	316	312
125°	462	460	462	460	462	412
135°	602	595	602	595	602	464
145°	730	722	730	722	730	456
155°	832	826	832	826	832	383
165°	900	899	900	899	900	254
175°	932	935	932	935	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	886.0	886.7	887.4	885.7	885.7	884.3	881.2	878.8	872.2	871.2	871.2
5°	947.2	946.7	947.8	944.0	938.7	937.5	931.8	924.5	916.8	908.2	906.4
7.5°	1008.2	1007.3	1005.0	1004.2	1000.2	991.3	982.2	972.6	959.8	947.3	941.0
10°	1038.9	1048.7	1042.8	1032.5	1034.5	1020.6	1013.2	1000.5	989.8	971.2	967.1
12.5°	1069.2	1073.1	1071.2	1065.3	1062.7	1053.0	1043.1	1032.0	1012.3	995.6	981.0
15°	1069.1	1074.8	1076.3	1074.4	1075.9	1075.3	1070.0	1060.8	1043.7	1025.3	1009.4
17.5°	990.2	994.1	1003.8	1010.3	1018.7	1036.2	1044.8	1048.2	1045.6	1035.1	1023.9
20°	901.7	895.2	922.4	936.3	948.2	977.7	1003.1	1012.9	1028.6	1028.3	1025.3
22.5°	776.3	777.8	803.6	820.1	854.7	884.2	913.2	950.0	980.3	1000.4	1012.1
25°	570.4	581.6	607.4	629.8	668.3	723.3	773.3	831.3	886.0	929.2	970.3
27.5°	428.3	429.2	449.6	470.4	493.2	538.3	601.3	670.5	748.5	812.9	886.9
30°	366.9	365.0	373.7	386.3	405.9	440.8	488.1	556.2	634.0	731.0	817.4
32.5°	323.3	323.4	329.9	339.3	355.5	379.0	411.5	466.7	540.3	635.6	736.9
35°	281.1	280.7	285.5	292.3	299.0	314.2	336.4	365.4	416.0	505.0	608.6
37.5°	250.7	252.1	254.4	258.6	266.1	274.5	287.9	307.3	343.3	396.0	483.0
40°	233.7	234.3	237.6	241.1	245.6	252.1	263.0	278.7	305.0	347.0	410.6
42.5°	218.1	218.6	221.0	224.3	227.8	234.3	243.4	256.9	278.3	311.0	363.5
45°	195.3	195.3	197.3	198.8	202.6	208.6	215.9	227.2	242.0	266.3	301.2
47.5°	173.8	173.9	175.2	177.8	180.2	184.8	192.1	201.3	212.1	230.8	260.6
50°	161.5	161.8	162.7	164.8	166.3	170.4	176.0	184.0	195.3	209.8	234.6
52.5°	151.5	151.4	152.5	153.4	154.4	157.4	161.6	168.7	178.7	191.3	211.9
55°	135.5	134.3	136.1	137.5	138.5	139.7	142.0	146.5	155.0	165.6	181.0
57.5°	115.3	114.9	116.1	117.5	120.3	123.5	125.5	128.3	132.8	140.4	155.7
60°	98.8	98.8	101.5	102.3	105.6	109.7	113.9	116.3	120.7	125.7	137.0
62.5°	84.1	84.4	85.6	86.5	88.3	93.4	99.3	104.4	108.6	113.4	120.9
65°	70.4	71.0	71.0	71.6	72.8	74.0	76.3	80.5	87.9	94.7	100.3
67.5°	59.7	60.0	60.1	60.7	61.0	62.3	63.2	65.1	66.8	73.3	80.2
70°	52.7	53.6	53.2	53.9	54.1	54.7	55.9	56.8	59.5	60.9	65.1
72.5°	46.0	46.7	46.7	47.0	47.8	47.8	48.8	49.7	51.4	52.7	54.9
75°	37.3	37.0	37.3	37.9	38.2	38.4	38.4	39.6	40.6	41.7	43.2
77.5°	28.8	29.1	29.0	29.1	29.1	29.6	29.5	30.1	31.0	31.6	32.3
80°	23.1	23.4	23.1	23.4	23.7	23.9	23.7	23.9	24.9	25.4	25.4
82.5°	17.9	17.9	18.1	18.1	18.2	18.3	18.7	18.8	19.4	19.3	19.5
85°	10.6	10.4	10.4	10.4	10.6	10.9	10.6	10.6	10.9	10.9	10.9
87.5°	9.2	9.3	9.3	9.3	9.3	9.3	9.3	9.7	9.5	9.8	8.8
90°	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9	27.3	27.6	23.8
92.5°	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3	25.2	25.1	24.2
95°	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6	50.6	50.6	50.2
97.5°	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1	85.1	85.1	84.4
100°	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1	109.1	109.1	108.6
102.5°	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3	135.1	135.1	134.4
105°	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6	174.3	173.9	173.6
107.5°	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1	216.9	216.7	216.7
110°	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7	275.2	275.6	275.8
115°	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0	319.2	319.4	319.7
117.5°	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9	362.3	362.7	363.7
120°	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5	390.5	390.5	392.0
122.5°	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0	420.5	420.9	421.9
125°	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8	464.3	464.9	465.4
127.5°	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3	506.9	507.6	508.2
130°	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3	535.7	536.0	536.4
132.5°	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6	564.4	565.1	565.0
135°	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2	605.4	605.5	605.2
137.5°	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2	645.3	645.4	645.0
140°	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0	672.0	672.0	671.1
142.5°	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3	696.2	696.0	695.4
145°	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2	733.0	732.8	731.8
147.5°	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6	765.2	764.8	764.1
150°	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1	784.3
152.5°	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3	804.4
155°	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7	831.8	830.8	830.4
157.5°	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7	855.5	854.3	854.0
160°	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9	869.9	868.8	868.6
162.5°	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8	882.6	881.5	881.3
165°	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6	899.3	898.1	898.1
167.5°	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3	913.1	911.8	911.9
170°	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9	920.7	919.4	919.6
172.5°	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6	926.4	925.1	925.3
175°	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7	932.5	931.3	931.6
177.5°	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9	935.2
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	871.7	869.9	868.2	864.0	861.8	857.1	856.3	856.1	850.0	844.1	842.4
5°	901.7	897.0	889.9	881.5	873.0	864.1	858.2	853.5	841.6	830.4	823.9
7.5°	931.8	921.7	909.4	893.7	880.7	866.0	855.2	845.3	828.5	812.5	801.6
10°	954.3	937.8	921.5	899.9	883.0	866.5	851.1	837.8	818.9	797.6	782.4
12.5°	968.3	950.1	927.6	906.6	884.7	863.6	843.0	825.9	803.7	781.7	763.7
15°	987.2	967.7	940.5	910.3	882.2	854.7	831.0	809.7	780.7	754.4	732.5
17.5°	1002.7	975.7	946.5	911.6	879.1	844.1	813.7	786.4	754.2	722.4	696.6
20°	1007.6	981.0	947.2	912.4	873.9	832.7	799.9	770.3	735.7	701.1	671.5
22.5°	1004.5	983.8	946.3	904.5	865.1	822.1	785.1	750.7	712.3	677.0	642.7
25°	983.7	976.5	941.0	895.5	850.5	800.5	757.6	720.0	676.3	638.4	601.1
27.5°	934.9	950.3	928.3	879.7	829.7	776.1	727.9	685.2	639.7	597.1	559.9
30°	888.1	923.3	913.8	868.9	812.9	760.3	706.2	661.5	613.0	569.2	532.5
32.5°	823.9	882.1	891.4	853.7	795.9	738.0	681.3	636.8	586.2	540.0	504.3
35°	721.8	808.8	848.7	824.7	766.8	704.4	645.8	594.1	543.1	497.6	462.1
37.5°	600.0	718.4	785.1	786.7	733.5	668.6	604.8	553.4	501.3	456.6	418.2
40°	520.9	649.4	736.0	755.3	710.3	640.2	575.7	523.3	472.5	428.6	384.6
42.5°	450.0	577.9	684.4	717.9	682.1	612.5	547.8	493.1	443.5	402.1	357.1
45°	363.8	475.7	593.1	652.9	633.1	568.5	500.3	448.2	401.7	365.9	322.7
47.5°	307.0	385.8	499.4	580.3	579.9	521.0	453.8	403.9	360.8	327.3	292.3
50°	274.5	343.2	439.3	531.0	538.7	489.3	425.4	376.0	335.8	300.6	272.4
52.5°	245.4	302.0	388.4	476.3	498.2	455.4	393.5	347.8	308.8	276.4	252.3
55°	207.4	251.1	316.9	399.1	432.2	402.0	347.0	304.4	272.7	245.6	224.8
57.5°	175.4	208.3	260.9	327.2	365.8	346.7	301.4	266.8	239.7	215.1	198.8
60°	155.3	182.2	226.9	282.3	324.8	311.5	272.7	240.5	217.5	196.1	180.8
62.5°	136.4	159.5	197.8	242.7	281.8	276.2	244.6	217.5	197.3	177.9	164.9
65°	109.7	126.6	156.5	191.7	223.1	225.7	203.0	184.6	166.5	151.1	139.7
67.5°	87.4	98.4	119.5	149.1	172.6	181.0	167.1	153.0	138.7	126.8	116.8
70°	73.7	82.5	97.9	121.9	143.5	152.3	144.3	133.4	121.0	111.2	102.7
72.5°	59.7	68.4	79.7	97.3	115.8	125.4	122.6	114.7	104.6	96.6	88.5
75°	45.0	47.6	55.3	67.2	81.7	89.9	92.0	87.9	79.9	73.7	68.9
77.5°	33.3	34.9	38.5	44.8	54.2	61.6	64.6	64.2	58.6	55.1	50.6
80°	26.6	27.5	29.3	31.9	39.1	46.4	48.5	48.5	44.7	43.2	38.7
82.5°	20.2	20.9	21.9	23.4	26.8	33.2	35.5	36.0	33.5	31.6	28.1
85°	11.6	11.2	11.8	12.8	13.3	15.1	18.6	19.3	18.6	16.2	15.4
87.5°	8.0	7.4	6.7	5.9	5.7	5.5	6.3	7.1	6.5	6.2	6.2
90°	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1	15.6	17.2	18.7
95°	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1	42.9	44.6	46.3
97.5°	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1	76.7	78.2	79.8
100°	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4	101.8	103.2	104.6
102.5°	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0	128.1	129.2	130.3
105°	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0	170.5	171.0	171.6
107.5°	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3	214.0	214.8	215.6
110°	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1	242.2	243.2	244.3



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5	272.5	273.6	274.6
115°	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2	317.3	318.3	319.4
117.5°	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8	362.2	363.6	365.0
120°	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	392.0	393.3	394.7
122.5°	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7	419.4	421.1	422.8
125°	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1	461.7	463.3	464.9
127.5°	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4	503.4	505.4	507.4
130°	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3	529.6	531.9	534.2
132.5°	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4	558.3	560.2	562.0
135°	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3	597.2	599.1	601.1
137.5°	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3	637.8	639.4	641.0
140°	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9	662.5	664.1	665.7
142.5°	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2	687.8	689.4	690.9
145°	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5	723.8	725.0	726.3
147.5°	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9	756.5	758.0	759.4
150°	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1	778.2	779.2	780.3
152.5°	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7	797.8	798.8	799.9
155°	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2	826.6	827.2	827.8
157.5°	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3	851.6	852.0	852.3
160°	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5	866.8	867.1	867.5
162.5°	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4	880.4	880.5	880.6
165°	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9	898.7	898.5	898.3
167.5°	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3	913.9	913.3	912.8
170°	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6	922.0	921.5	921.0
172.5°	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3	927.7	927.2	926.7
175°	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3	934.7	934.1	933.7
177.5°	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1	937.6	937.2	936.8
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	839.3	837.7	834.6	829.9	827.0	822.0	818.7	820.6	821.1	820.6	820.1
5°	816.8	810.6	802.0	793.7	786.0	777.8	773.0	771.0	766.8	764.5	763.3
7.5°	789.5	778.8	766.7	752.3	740.0	727.1	720.6	717.3	708.8	704.3	700.2
10°	769.1	752.3	740.1	721.2	709.7	692.8	681.3	681.6	670.0	663.5	658.8
12.5°	746.7	728.2	708.0	690.9	674.9	661.4	647.5	641.8	629.5	623.3	610.5
15°	709.4	687.8	666.5	643.4	627.2	606.2	586.1	561.5	541.7	524.5	519.8
17.5°	668.7	642.0	620.6	593.5	565.6	530.3	507.0	492.7	480.8	471.7	465.0
20°	640.8	613.5	590.8	549.9	512.4	488.4	471.3	460.3	447.9	438.2	432.8
22.5°	611.4	583.0	552.0	506.4	477.1	457.9	442.6	430.0	421.6	414.0	409.2
25°	569.7	538.7	487.5	456.1	432.5	412.4	401.7	394.0	385.2	374.8	370.1
27.5°	525.8	476.3	439.6	416.3	393.7	380.6	371.1	359.6	351.6	347.0	342.1
30°	492.8	443.5	414.8	389.3	373.4	358.9	347.6	341.1	333.4	325.4	322.2
32.5°	456.1	416.7	389.2	368.0	351.8	339.5	330.6	320.0	314.5	309.6	302.8
35°	410.6	380.7	355.6	338.4	323.1	313.0	302.6	296.4	286.4	282.3	279.6
37.5°	372.0	346.1	327.3	309.3	297.1	286.0	279.6	269.7	265.4	259.6	254.0
40°	350.2	324.8	306.8	292.0	278.4	270.1	262.1	254.1	247.6	244.9	238.1
42.5°	328.0	307.3	289.2	273.1	264.0	255.2	245.1	239.2	232.4	228.1	223.9
45°	297.3	279.0	263.6	250.3	240.2	231.1	224.5	214.8	211.0	202.3	198.8
47.5°	270.3	253.3	238.6	225.9	216.1	210.2	200.7	193.0	186.9	181.6	177.1
50°	251.1	236.9	222.8	211.5	202.6	194.1	184.3	180.5	171.0	168.3	165.6
52.5°	233.6	220.1	207.2	196.1	187.3	179.0	170.3	165.3	158.9	156.2	154.3
55°	209.1	196.1	183.7	174.0	165.1	156.5	151.1	145.0	142.0	139.9	137.5
57.5°	184.5	172.9	163.3	153.4	144.5	137.7	131.5	127.8	124.7	122.0	119.1
60°	168.9	157.6	149.1	139.9	130.8	125.2	120.4	116.0	112.4	108.3	107.1
62.5°	152.3	142.5	134.7	125.7	117.7	112.6	108.1	103.9	99.7	93.6	92.0
65°	129.6	121.9	113.6	106.2	99.1	94.1	87.5	82.9	81.0	80.5	80.2
67.5°	109.0	101.7	94.6	87.1	80.6	75.9	72.6	71.9	70.7	70.3	69.5
70°	95.2	88.5	81.4	74.2	68.0	67.2	66.0	64.8	63.3	62.7	62.1
72.5°	82.9	75.9	68.8	63.1	60.4	59.3	58.1	57.0	56.0	55.4	55.1
75°	63.6	57.1	52.4	50.3	48.8	47.9	46.2	45.2	44.7	43.8	43.5
77.5°	45.8	42.1	39.9	38.7	37.1	36.1	35.2	34.2	33.6	33.4	33.0
80°	34.9	33.1	31.7	29.9	29.3	28.1	27.8	26.9	27.3	26.3	26.3
82.5°	27.1	24.9	23.6	22.8	22.2	21.2	20.9	20.5	20.6	20.0	20.0
85°	13.9	13.3	12.8	12.1	12.1	11.2	11.6	11.2	11.2	10.6	10.4
87.5°	6.3	6.7	7.0	7.8	8.6	9.1	9.0	8.7	8.6	8.6	8.3
90°	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9	26.6	26.3	26.1
92.5°	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3	25.3	25.4	25.5
95°	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6	50.6	50.6	50.4
97.5°	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1	85.1	85.1	85.1
100°	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1	109.1	109.1	109.0
102.5°	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3	135.5	135.6	135.5
105°	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6	175.0	175.3	175.5
107.5°	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1	217.2	217.3	217.0
110°	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.6



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7	274.3	273.9	273.5
115°	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0	318.9	318.7	318.3
117.5°	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9	361.5	361.0	360.5
120°	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5	390.5	390.5	390.3
122.5°	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0	419.6	419.2	418.8
125°	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8	463.3	462.7	462.4
127.5°	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3	505.6	505.0	504.4
130°	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3	535.0	534.6	534.1
132.5°	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6	562.8	562.0	561.3
135°	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2	605.1	604.8	604.5
137.5°	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2	645.0	644.8	644.4
140°	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0	672.0	672.0	671.6
142.5°	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3	696.4	696.6	696.3
145°	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2	733.4	733.6	733.3
147.5°	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6	766.0	766.4	766.2
150°	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1	786.6	787.1	787.1
152.5°	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6	807.2	807.9	807.9
155°	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7	833.5	834.4	834.6
157.5°	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7	857.9	859.0	859.2
160°	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9	872.0	873.1	873.2
162.5°	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8	885.0	886.2	886.5
165°	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6	901.7	903.0	903.2
167.5°	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3	915.5	916.7	916.9
170°	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9	923.1	924.3	924.4
172.5°	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6	928.8	930.0	930.1
175°	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7	934.9	936.2	936.3
177.5°	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6	937.5	938.3	938.3
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	817.5	818.0	817.3	817.8	817.3	818.0	817.5	820.1	820.6	821.1	820.6
5°	761.8	758.2	757.6	756.8	757.6	758.2	761.8	763.3	764.5	766.8	771.0
7.5°	695.1	694.6	693.2	691.0	693.2	694.6	695.1	700.2	704.3	708.8	717.3
10°	652.3	650.9	650.5	648.5	650.5	650.9	652.3	658.8	663.5	670.0	681.6
12.5°	602.1	592.6	591.6	586.5	591.6	592.6	602.1	610.5	623.3	629.5	641.8
15°	512.7	510.9	505.0	501.1	505.0	510.9	512.7	519.8	524.5	541.7	561.5
17.5°	461.5	455.7	453.9	453.1	453.9	455.7	461.5	465.0	471.7	480.8	492.7
20°	428.6	423.3	422.5	421.8	422.5	423.3	428.6	432.8	438.2	447.9	460.3
22.5°	405.9	400.4	398.1	396.3	398.1	400.4	405.9	409.2	414.0	421.6	430.0
25°	367.1	365.0	363.8	363.3	363.8	365.0	367.1	370.1	374.8	385.2	394.0
27.5°	336.8	332.2	331.3	329.8	331.3	332.2	336.8	342.1	347.0	351.6	359.6
30°	319.5	318.0	315.9	314.2	315.9	318.0	319.5	322.2	325.4	333.4	341.1
32.5°	299.1	297.9	296.0	295.2	296.0	297.9	299.1	302.8	309.6	314.5	320.0
35°	276.6	272.4	270.7	268.0	270.7	272.4	276.6	279.6	282.3	286.4	296.4
37.5°	252.8	250.6	248.1	249.0	248.1	250.6	252.8	254.0	259.6	265.4	269.7
40°	234.3	232.8	232.2	232.0	232.2	232.8	234.3	238.1	244.9	247.6	254.1
42.5°	219.6	215.6	214.0	214.0	214.0	215.6	219.6	223.9	228.1	232.4	239.2
45°	197.3	193.5	190.8	191.1	190.8	193.5	197.3	198.8	202.3	211.0	214.8
47.5°	174.5	174.4	172.7	173.3	172.7	174.4	174.5	177.1	181.6	186.9	193.0
50°	163.6	161.8	160.7	160.9	160.7	161.8	163.6	165.6	168.3	171.0	180.5
52.5°	153.2	151.6	150.7	151.9	150.7	151.6	153.2	154.3	156.2	158.9	165.3
55°	136.1	134.3	134.0	133.7	134.0	134.3	136.1	137.5	139.9	142.0	145.0
57.5°	117.0	115.8	114.0	113.3	114.0	115.8	117.0	119.1	122.0	124.7	127.8
60°	103.2	100.8	97.9	97.6	97.9	100.8	103.2	107.1	108.3	112.4	116.0
62.5°	90.7	90.2	89.7	89.6	89.7	90.2	90.7	92.0	93.6	99.7	103.9
65°	79.6	79.3	79.6	79.9	79.6	79.3	79.6	80.2	80.5	81.0	82.9
67.5°	69.3	68.8	68.3	68.5	68.3	68.8	69.3	69.5	70.3	70.7	71.9
70°	61.6	61.2	60.9	60.9	60.9	61.2	61.6	62.1	62.7	63.3	64.8
72.5°	53.9	53.9	53.6	53.4	53.6	53.9	53.9	55.1	55.4	56.0	57.0
75°	43.2	42.6	42.6	42.6	42.6	42.6	43.2	43.5	43.8	44.7	45.2
77.5°	32.9	32.6	32.3	32.1	32.3	32.6	32.9	33.0	33.4	33.6	34.2
80°	26.1	25.7	25.4	25.4	25.4	25.7	26.1	26.3	26.3	27.3	26.9
82.5°	19.9	19.6	19.5	19.3	19.5	19.6	19.9	20.0	20.0	20.6	20.5
85°	10.6	10.9	10.6	11.2	10.6	10.9	10.6	10.4	10.6	11.2	11.2
87.5°	8.3	8.2	8.4	8.2	8.4	8.2	8.3	8.3	8.6	8.6	8.7
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9
92.5°	25.5	25.5	25.6	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3
95°	50.1	49.7	49.4	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6
97.5°	85.0	85.0	84.9	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1
100°	108.8	108.7	108.4	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1
102.5°	135.4	135.2	135.1	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3
105°	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6
107.5°	216.2	215.4	214.6	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1
110°	245.1	244.5	244.0	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.1	272.7	272.4	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7
115°	317.8	317.3	316.7	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0
117.5°	360.0	359.5	358.9	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9
120°	389.8	389.2	388.7	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5
122.5°	418.4	418.0	417.6	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0
125°	462.2	462.0	461.8	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8
127.5°	503.8	503.3	502.7	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3
130°	533.4	532.7	532.0	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3
132.5°	560.8	560.2	559.7	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6
135°	604.0	603.5	602.9	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2
137.5°	643.7	643.0	642.3	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2
140°	670.9	670.2	669.6	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0
142.5°	695.6	694.9	694.2	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3
145°	732.6	731.9	731.2	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2
147.5°	765.6	764.9	764.2	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6
150°	786.6	786.1	785.5	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1
152.5°	807.2	806.6	806.0	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6
155°	834.0	833.5	833.0	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7
157.5°	858.4	857.5	856.7	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7
160°	872.5	871.8	871.1	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9
162.5°	885.6	884.7	883.9	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8
165°	902.3	901.4	900.6	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6
167.5°	916.0	915.0	914.2	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3
170°	923.4	922.3	921.2	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9
172.5°	929.1	928.0	926.9	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6
175°	935.3	934.1	933.1	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7
177.5°	937.5	936.6	935.7	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	818.7	822.0	827.0	829.9	834.6	837.7	839.3	842.4	844.1	850.0	856.1
5°	773.0	777.8	786.0	793.7	802.0	810.6	816.8	823.9	830.4	841.6	853.5
7.5°	720.6	727.1	740.0	752.3	766.7	778.8	789.5	801.6	812.5	828.5	845.3
10°	681.3	692.8	709.7	721.2	740.1	752.3	769.1	782.4	797.6	818.9	837.8
12.5°	647.5	661.4	674.9	690.9	708.0	728.2	746.7	763.7	781.7	803.7	825.9
15°	586.1	606.2	627.2	643.4	666.5	687.8	709.4	732.5	754.4	780.7	809.7
17.5°	507.0	530.3	565.6	593.5	620.6	642.0	668.7	696.6	722.4	754.2	786.4
20°	471.3	488.4	512.4	549.9	590.8	613.5	640.8	671.5	701.1	735.7	770.3
22.5°	442.6	457.9	477.1	506.4	552.0	583.0	611.4	642.7	677.0	712.3	750.7
25°	401.7	412.4	432.5	456.1	487.5	538.7	569.7	601.1	638.4	676.3	720.0
27.5°	371.1	380.6	393.7	416.3	439.6	476.3	525.8	559.9	597.1	639.7	685.2
30°	347.6	358.9	373.4	389.3	414.8	443.5	492.8	532.5	569.2	613.0	661.5
32.5°	330.6	339.5	351.8	368.0	389.2	416.7	456.1	504.3	540.0	586.2	636.8
35°	302.6	313.0	323.1	338.4	355.6	380.7	410.6	462.1	497.6	543.1	594.1
37.5°	279.6	286.0	297.1	309.3	327.3	346.1	372.0	418.2	456.6	501.3	553.4
40°	262.1	270.1	278.4	292.0	306.8	324.8	350.2	384.6	428.6	472.5	523.3
42.5°	245.1	255.2	264.0	273.1	289.2	307.3	328.0	357.1	402.1	443.5	493.1
45°	224.5	231.1	240.2	250.3	263.6	279.0	297.3	322.7	365.9	401.7	448.2
47.5°	200.7	210.2	216.1	225.9	238.6	253.3	270.3	292.3	327.3	360.8	403.9
50°	184.3	194.1	202.6	211.5	222.8	236.9	251.1	272.4	300.6	335.8	376.0
52.5°	170.3	179.0	187.3	196.1	207.2	220.1	233.6	252.3	276.4	308.8	347.8
55°	151.1	156.5	165.1	174.0	183.7	196.1	209.1	224.8	245.6	272.7	304.4
57.5°	131.5	137.7	144.5	153.4	163.3	172.9	184.5	198.8	215.1	239.7	266.8
60°	120.4	125.2	130.8	139.9	149.1	157.6	168.9	180.8	196.1	217.5	240.5
62.5°	108.1	112.6	117.7	125.7	134.7	142.5	152.3	164.9	177.9	197.3	217.5
65°	87.5	94.1	99.1	106.2	113.6	121.9	129.6	139.7	151.1	166.5	184.6
67.5°	72.6	75.9	80.6	87.1	94.6	101.7	109.0	116.8	126.8	138.7	153.0
70°	66.0	67.2	68.0	74.2	81.4	88.5	95.2	102.7	111.2	121.0	133.4
72.5°	58.1	59.3	60.4	63.1	68.8	75.9	82.9	88.5	96.6	104.6	114.7
75°	46.2	47.9	48.8	50.3	52.4	57.1	63.6	68.9	73.7	79.9	87.9
77.5°	35.2	36.1	37.1	38.7	39.9	42.1	45.8	50.6	55.1	58.6	64.2
80°	27.8	28.1	29.3	29.9	31.7	33.1	34.9	38.7	43.2	44.7	48.5
82.5°	20.9	21.2	22.2	22.8	23.6	24.9	27.1	28.1	31.6	33.5	36.0
85°	11.6	11.2	12.1	12.1	12.8	13.3	13.9	15.4	16.2	18.6	19.3
87.5°	9.0	9.1	8.6	7.8	7.0	6.7	6.3	6.2	6.2	6.5	7.1
90°	27.3	27.6	23.8	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.2	25.1	24.2	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1
95°	50.6	50.6	50.2	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1
97.5°	85.1	85.1	84.4	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1
100°	109.1	109.1	108.6	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4
102.5°	135.1	135.1	134.4	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0
105°	174.3	173.9	173.6	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0
107.5°	216.9	216.7	216.7	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3
110°	245.9	245.9	245.9	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.2	275.6	275.8	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5
115°	319.2	319.4	319.7	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2
117.5°	362.3	362.7	363.7	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8
120°	390.5	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5
122.5°	420.5	420.9	421.9	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7
125°	464.3	464.9	465.4	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1
127.5°	506.9	507.6	508.2	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4
130°	535.7	536.0	536.4	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3
132.5°	564.4	565.1	565.0	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4
135°	605.4	605.5	605.2	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3
137.5°	645.3	645.4	645.0	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3
140°	672.0	672.0	671.1	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9
142.5°	696.2	696.0	695.4	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2
145°	733.0	732.8	731.8	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5
147.5°	765.2	764.8	764.1	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9
150°	785.5	785.1	784.3	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1
152.5°	806.0	805.3	804.4	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7
155°	831.8	830.8	830.4	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2
157.5°	855.5	854.3	854.0	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3
160°	869.9	868.8	868.6	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5
162.5°	882.6	881.5	881.3	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4
165°	899.3	898.1	898.1	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9
167.5°	913.1	911.8	911.9	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3
170°	920.7	919.4	919.6	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6
172.5°	926.4	925.1	925.3	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3
175°	932.5	931.3	931.6	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3
177.5°	935.7	934.9	935.2	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	856.3	857.1	861.8	864.0	868.2	869.9	871.7	871.2	871.2	872.2	878.8
5°	858.2	864.1	873.0	881.5	889.9	897.0	901.7	906.4	908.2	916.8	924.5
7.5°	855.2	866.0	880.7	893.7	909.4	921.7	931.8	941.0	947.3	959.8	972.6
10°	851.1	866.5	883.0	899.9	921.5	937.8	954.3	967.1	971.2	989.8	1000.5
12.5°	843.0	863.6	884.7	906.6	927.6	950.1	968.3	981.0	995.6	1012.3	1032.0
15°	831.0	854.7	882.2	910.3	940.5	967.7	987.2	1009.4	1025.3	1043.7	1060.8
17.5°	813.7	844.1	879.1	911.6	946.5	975.7	1002.7	1023.9	1035.1	1045.6	1048.2
20°	799.9	832.7	873.9	912.4	947.2	981.0	1007.6	1025.3	1028.3	1028.6	1012.9
22.5°	785.1	822.1	865.1	904.5	946.3	983.8	1004.5	1012.1	1000.4	980.3	950.0
25°	757.6	800.5	850.5	895.5	941.0	976.5	983.7	970.3	929.2	886.0	831.3
27.5°	727.9	776.1	829.7	879.7	928.3	950.3	934.9	886.9	812.9	748.5	670.5
30°	706.2	760.3	812.9	868.9	913.8	923.3	888.1	817.4	731.0	634.0	556.2
32.5°	681.3	738.0	795.9	853.7	891.4	882.1	823.9	736.9	635.6	540.3	466.7
35°	645.8	704.4	766.8	824.7	848.7	808.8	721.8	608.6	505.0	416.0	365.4
37.5°	604.8	668.6	733.5	786.7	785.1	718.4	600.0	483.0	396.0	343.3	307.3
40°	575.7	640.2	710.3	755.3	736.0	649.4	520.9	410.6	347.0	305.0	278.7
42.5°	547.8	612.5	682.1	717.9	684.4	577.9	450.0	363.5	311.0	278.3	256.9
45°	500.3	568.5	633.1	652.9	593.1	475.7	363.8	301.2	266.3	242.0	227.2
47.5°	453.8	521.0	579.9	580.3	499.4	385.8	307.0	260.6	230.8	212.1	201.3
50°	425.4	489.3	538.7	531.0	439.3	343.2	274.5	234.6	209.8	195.3	184.0
52.5°	393.5	455.4	498.2	476.3	388.4	302.0	245.4	211.9	191.3	178.7	168.7
55°	347.0	402.0	432.2	399.1	316.9	251.1	207.4	181.0	165.6	155.0	146.5
57.5°	301.4	346.7	365.8	327.2	260.9	208.3	175.4	155.7	140.4	132.8	128.3
60°	272.7	311.5	324.8	282.3	226.9	182.2	155.3	137.0	125.7	120.7	116.3
62.5°	244.6	276.2	281.8	242.7	197.8	159.5	136.4	120.9	113.4	108.6	104.4
65°	203.0	225.7	223.1	191.7	156.5	126.6	109.7	100.3	94.7	87.9	80.5
67.5°	167.1	181.0	172.6	149.1	119.5	98.4	87.4	80.2	73.3	66.8	65.1
70°	144.3	152.3	143.5	121.9	97.9	82.5	73.7	65.1	60.9	59.5	56.8
72.5°	122.6	125.4	115.8	97.3	79.7	68.4	59.7	54.9	52.7	51.4	49.7
75°	92.0	89.9	81.7	67.2	55.3	47.6	45.0	43.2	41.7	40.6	39.6
77.5°	64.6	61.6	54.2	44.8	38.5	34.9	33.3	32.3	31.6	31.0	30.1
80°	48.5	46.4	39.1	31.9	29.3	27.5	26.6	25.4	25.4	24.9	23.9
82.5°	35.5	33.2	26.8	23.4	21.9	20.9	20.2	19.5	19.3	19.4	18.8
85°	18.6	15.1	13.3	12.8	11.8	11.2	11.6	10.9	10.9	10.9	10.6
87.5°	6.3	5.5	5.7	5.9	6.7	7.4	8.0	8.8	9.8	9.5	9.7
90°	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9
92.5°	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3
95°	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6
97.5°	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1
100°	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1
102.5°	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3
105°	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6
107.5°	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1
110°	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7
115°	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0
117.5°	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9
120°	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5
122.5°	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0
125°	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8
127.5°	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3
130°	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3
132.5°	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6
135°	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2
137.5°	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2
140°	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0
142.5°	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3
145°	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2
147.5°	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6
150°	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1
152.5°	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6
155°	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7
157.5°	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7
160°	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9
162.5°	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8
165°	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6
167.5°	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3
170°	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9
172.5°	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6
175°	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7
177.5°	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	881.2	884.3	885.7	885.7	887.4	886.7	886.0
5°	931.8	937.5	938.7	944.0	947.8	946.7	947.2
7.5°	982.2	991.3	1000.2	1004.2	1005.0	1007.3	1008.2
10°	1013.2	1020.6	1034.5	1032.5	1042.8	1048.7	1038.9
12.5°	1043.1	1053.0	1062.7	1065.3	1071.2	1073.1	1069.2
15°	1070.0	1075.3	1075.9	1074.4	1076.3	1074.8	1069.1
17.5°	1044.8	1036.2	1018.7	1010.3	1003.8	994.1	990.2
20°	1003.1	977.7	948.2	936.3	922.4	895.2	901.7
22.5°	913.2	884.2	854.7	820.1	803.6	777.8	776.3
25°	773.3	723.3	668.3	629.8	607.4	581.6	570.4
27.5°	601.3	538.3	493.2	470.4	449.6	429.2	428.3
30°	488.1	440.8	405.9	386.3	373.7	365.0	366.9
32.5°	411.5	379.0	355.5	339.3	329.9	323.4	323.3
35°	336.4	314.2	299.0	292.3	285.5	280.7	281.1
37.5°	287.9	274.5	266.1	258.6	254.4	252.1	250.7
40°	263.0	252.1	245.6	241.1	237.6	234.3	233.7
42.5°	243.4	234.3	227.8	224.3	221.0	218.6	218.1
45°	215.9	208.6	202.6	198.8	197.3	195.3	195.3
47.5°	192.1	184.8	180.2	177.8	175.2	173.9	173.8
50°	176.0	170.4	166.3	164.8	162.7	161.8	161.5
52.5°	161.6	157.4	154.4	153.4	152.5	151.4	151.5
55°	142.0	139.7	138.5	137.5	136.1	134.3	135.5
57.5°	125.5	123.5	120.3	117.5	116.1	114.9	115.3
60°	113.9	109.7	105.6	102.3	101.5	98.8	98.8
62.5°	99.3	93.4	88.3	86.5	85.6	84.4	84.1
65°	76.3	74.0	72.8	71.6	71.0	71.0	70.4
67.5°	63.2	62.3	61.0	60.7	60.1	60.0	59.7
70°	55.9	54.7	54.1	53.9	53.2	53.6	52.7
72.5°	48.8	47.8	47.8	47.0	46.7	46.7	46.0
75°	38.4	38.4	38.2	37.9	37.3	37.0	37.3
77.5°	29.5	29.6	29.1	29.1	29.0	29.1	28.8
80°	23.7	23.9	23.7	23.4	23.1	23.4	23.1
82.5°	18.7	18.3	18.2	18.1	18.1	17.9	17.9
85°	10.6	10.9	10.6	10.4	10.4	10.4	10.6
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.2
90°	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.6	245.1	244.5	244.0	243.5



TEST NUMBER: P331664-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)