

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331666-927

Luminaire Tested: **SA2XXRDIP-C485D925U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331666-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4277.2 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31	31	31	31	
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27	27	27	27	
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23	23	23	23	
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20	20	20	20	
4	72	62	54	48	64	56	49	44	45	40	37	35	31	29	25	23	22	17	17	17	17	
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15	15	15	15	
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	19	17	14	14	14	14	
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12	12	12	12	
8	52	40	33	28	47	37	30	26	30	25	22	23	20	18	17	15	14	11	11	11	11	
9	48	37	30	25	44	33	27	23	27	23	19	22	18	16	16	14	12	10	10	10	10	
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9	9	9	9	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.2	1.4
10°-20°	168.0	3.9
20°-30°	235.9	5.5
30°-40°	257.3	6.0
40°-50°	236.6	5.5
50°-60°	185.8	4.3
60°-70°	121.1	2.8
70°-80°	62.5	1.5
80°-90°	18.7	0.4
90°-100°	33.4	0.8
100°-110°	122.3	2.9
110°-120°	326.9	7.6
120°-130°	539.7	12.6
130°-140°	574.0	13.4
140°-150°	533.5	12.5
150°-160°	428.9	10.0
160°-170°	276.4	6.5
170°-180°	95.1	2.2
0°-30°	465.2	10.9
0°-40°	722.4	16.9
0°-60°	1144.8	26.8
0°-90°	1347.1	31.5
90°-120°	482.6	11.3
90°-150°	2129.7	49.8
90°-180°	2930.0	68.5
0°-180°	4277.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	9	14	18	20	3
95°	47	25	28	32	31	58
105°	220	229	44	52	55	235
115°	416	429	446	127	59	409
125°	588	598	611	616	619	524
135°	728	739	746	753	752	562
145°	844	844	856	860	857	528
155°	930	924	932	936	930	428
165°	980	976	978	982	978	277
175°	1002	997	998	1003	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.7	7.2	6.7	6.3	5.8	5.6	5.9	6.2	6.4	6.7	6.7
90°	0.7	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3
92.5°	14.6	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2
95°	47.1	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0
97.5°	93.3	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4
100°	128.1	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5
102.5°	166.3	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0
105°	219.9	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9
107.5°	281.1	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0
110°	320.5	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5



TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.5	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7
115°	416.0	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9
117.5°	468.3	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4
120°	506.4	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3
122.5°	538.8	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6
125°	588.2	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5
127.5°	632.9	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2
130°	661.3	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5
132.5°	690.2	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6
135°	727.9	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5
137.5°	765.9	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9
140°	790.8	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0
142.5°	811.6	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3
145°	844.3	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0
147.5°	872.8	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0
150°	891.4	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8
152.5°	907.0	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3
155°	929.7	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8
157.5°	947.5	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2
160°	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9
162.5°	967.2	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7
165°	979.6	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6
167.5°	988.9	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7
170°	994.1	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3
172.5°	997.5	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8
175°	1002.0	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6
177.5°	1002.7	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	6.8	6.8	6.9	7.0	7.1	7.1	7.1	7.2
90°	16.1	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	17.6	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	29.8	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.1	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	43.8	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	45.7	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	47.7	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	58.1	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	94.4	78.3	62.3	54.6	55.2	55.8	56.5	57.2





TEST NUMBER: P331666-927

CATALOG NUMBER: SA2XXRDIP-C485D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.1	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	297.5	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	458.4	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	534.2	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	566.8	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	613.6	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	656.9	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	684.4	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	711.1	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	749.2	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	784.5	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	807.4	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	828.5	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	858.2	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	883.9	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	899.8	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	914.3	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	933.8	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	950.2	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	959.8	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	968.8	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	988.8	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	993.5	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	996.9	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1000.7	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1001.1	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)