

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331679-927

Luminaire Tested: **SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331679-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2766.6 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331679-927  
CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331679-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66				
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	76	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42				
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37				
5	73	61	53	47	68	58	51	45	52	46	42	47	42	39	42	38	35	32				
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29				
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23				
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21				
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331679-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.6	3.0
10°-20°	229.7	8.3
20°-30°	322.5	11.7
30°-40°	351.7	12.7
40°-50°	323.4	11.7
50°-60°	254.0	9.2
60°-70°	165.6	6.0
70°-80°	85.4	3.1
80°-90°	23.5	0.8
90°-100°	21.0	0.8
100°-110°	65.3	2.4
110°-120°	111.6	4.0
120°-130°	146.7	5.3
130°-140°	164.7	6.0
140°-150°	161.5	5.8
150°-160°	135.4	4.9
160°-170°	89.8	3.2
170°-180°	31.4	1.1
0°-30°	635.8	23.0
0°-40°	987.5	35.7
0°-60°	1564.8	56.6
0°-90°	1839.3	66.5
90°-120°	197.9	7.2
90°-150°	670.7	24.2
90°-180°	927.0	33.5
0°-180°	2766.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	0	4	10	9	10	2
95°	15	17	18	18	17	17
105°	60	61	62	62	62	64
115°	112	114	113	113	112	111
125°	163	165	164	164	163	146
135°	211	214	214	214	213	163
145°	256	258	259	260	259	160
155°	292	293	294	295	295	135
165°	318	318	318	320	318	90
175°	331	330	330	331	330	31
180°	332	332	332	332	332	



TEST NUMBER: P331679-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.4	9.4	8.4	7.4	6.4	6.0	6.3	6.6	6.9	7.1	7.0
90°	0.3	1.0	1.7	2.5	3.2	4.4	5.7	7.1	8.4	9.8	9.7
92.5°	5.0	5.5	6.1	6.7	7.2	7.6	7.9	8.2	8.6	8.9	9.0
95°	14.6	15.2	15.8	16.4	17.0	17.4	17.5	17.7	17.8	17.9	17.9
97.5°	26.6	27.2	27.6	28.2	28.8	29.2	29.4	29.6	29.9	30.1	30.1
100°	35.6	36.0	36.5	37.1	37.5	37.9	38.0	38.3	38.4	38.7	38.7
102.5°	44.9	45.3	45.7	46.1	46.5	46.9	47.1	47.3	47.5	47.8	47.8
105°	60.2	60.4	60.5	60.8	60.9	61.1	61.2	61.3	61.5	61.6	61.7
107.5°	75.5	75.8	76.0	76.4	76.6	76.8	76.8	76.8	76.8	76.8	76.8
110°	85.4	85.7	86.1	86.5	86.8	87.1	87.1	87.1	87.1	87.1	87.1



TEST NUMBER: P331679-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.1	96.5	96.9	97.2	97.6	97.8	97.7	97.7	97.6	97.6	97.4
115°	111.9	112.3	112.7	113.0	113.4	113.6	113.4	113.3	113.2	113.0	113.0
117.5°	127.7	128.3	128.7	129.2	129.8	129.8	129.4	129.1	128.7	128.4	128.3
120°	138.2	138.8	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2	138.2
122.5°	147.9	148.5	149.1	149.6	150.3	150.4	150.0	149.7	149.3	149.0	148.9
125°	162.9	163.4	164.0	164.5	165.1	165.3	165.1	164.9	164.8	164.5	164.4
127.5°	177.5	178.2	179.0	179.6	180.3	180.5	180.4	180.1	179.9	179.7	179.4
130°	186.7	187.5	188.3	189.1	189.9	190.3	190.1	190.0	189.9	189.7	189.6
132.5°	197.0	197.6	198.3	198.9	199.6	199.9	199.9	200.0	200.0	200.0	199.8
135°	210.7	211.4	212.1	212.8	213.5	213.9	214.0	214.1	214.3	214.4	214.3
137.5°	225.2	225.8	226.3	227.0	227.5	227.8	228.0	228.1	228.3	228.5	228.5
140°	234.0	234.6	235.1	235.7	236.2	236.6	236.9	237.3	237.6	237.9	237.9
142.5°	243.0	243.5	244.1	244.6	245.2	245.6	245.7	246.0	246.2	246.4	246.4
145°	255.8	256.3	256.7	257.1	257.5	257.9	258.3	258.7	259.0	259.4	259.5
147.5°	267.3	267.8	268.3	268.9	269.3	269.7	270.0	270.3	270.5	270.8	270.9
150°	275.1	275.5	275.8	276.2	276.6	276.9	277.2	277.4	277.7	277.9	278.1
152.5°	282.1	282.4	282.8	283.2	283.5	283.9	284.2	284.5	284.8	285.1	285.3
155°	292.5	292.6	292.9	293.0	293.2	293.4	293.6	293.7	294.0	294.1	294.5
157.5°	301.3	301.5	301.6	301.7	301.9	302.0	302.1	302.2	302.3	302.5	302.9
160°	306.7	306.9	307.0	307.1	307.2	307.4	307.4	307.4	307.5	307.6	307.9
162.5°	311.6	311.7	311.7	311.7	311.8	311.8	311.9	312.0	312.0	312.0	312.5
165°	318.2	318.1	318.1	318.1	318.0	317.9	317.9	317.9	317.9	317.9	318.4
167.5°	323.7	323.5	323.4	323.1	323.0	322.9	322.8	322.8	322.8	322.8	323.2
170°	326.6	326.5	326.2	326.1	325.9	325.7	325.7	325.6	325.6	325.5	325.9
172.5°	328.6	328.4	328.3	328.0	327.9	327.7	327.7	327.6	327.6	327.5	328.0
175°	331.1	330.9	330.7	330.5	330.3	330.2	330.1	329.9	329.8	329.7	330.1
177.5°	332.1	331.9	331.8	331.7	331.5	331.4	331.3	331.2	331.1	331.0	331.3
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331679-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	6.8	6.7	6.5	6.4	6.4	6.4	6.4	6.4
90°	9.6	9.4	9.3	9.3	9.3	9.4	9.4	9.5
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
95°	17.9	17.9	17.9	17.8	17.7	17.6	17.5	17.3
97.5°	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.0
100°	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3
102.5°	47.9	47.9	48.0	48.0	47.9	47.8	47.8	47.8
105°	61.8	61.9	62.1	62.1	62.1	62.1	62.1	62.1
107.5°	76.8	76.9	76.9	76.8	76.5	76.3	76.0	75.7
110°	87.1	87.1	87.1	87.0	86.7	86.6	86.4	86.2





TEST NUMBER: P331679-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	97.3	97.1	97.0	96.8	96.7	96.6	96.4	96.3
115°	113.0	112.9	112.8	112.7	112.5	112.3	112.2	111.9
117.5°	128.1	127.9	127.8	127.6	127.5	127.3	127.1	126.9
120°	138.2	138.2	138.2	138.2	138.0	137.8	137.6	137.4
122.5°	148.7	148.5	148.4	148.3	148.1	148.0	147.8	147.7
125°	164.2	164.0	163.8	163.7	163.7	163.6	163.5	163.4
127.5°	179.3	179.0	178.8	178.6	178.4	178.2	178.0	177.8
130°	189.5	189.4	189.3	189.1	188.9	188.5	188.3	188.1
132.5°	199.5	199.2	199.0	198.8	198.5	198.4	198.1	198.0
135°	214.3	214.2	214.1	214.0	213.8	213.7	213.5	213.3
137.5°	228.4	228.3	228.3	228.1	227.9	227.7	227.4	227.1
140°	237.9	237.9	237.9	237.7	237.5	237.3	237.0	236.8
142.5°	246.5	246.5	246.6	246.5	246.3	246.0	245.7	245.5
145°	259.6	259.6	259.7	259.6	259.4	259.1	258.9	258.6
147.5°	271.0	271.2	271.3	271.2	271.0	270.8	270.5	270.3
150°	278.3	278.5	278.7	278.7	278.5	278.3	278.1	277.9
152.5°	285.6	285.8	286.1	286.1	285.8	285.6	285.3	285.1
155°	294.8	295.1	295.4	295.5	295.2	295.1	294.9	294.7
157.5°	303.2	303.7	304.1	304.2	303.9	303.6	303.3	303.0
160°	308.3	308.7	309.1	309.1	308.9	308.6	308.4	308.2
162.5°	312.9	313.3	313.8	313.8	313.5	313.2	312.9	312.6
165°	318.8	319.2	319.6	319.7	319.4	319.1	318.8	318.5
167.5°	323.7	324.1	324.6	324.6	324.3	323.9	323.6	323.3
170°	326.4	326.8	327.3	327.3	326.9	326.5	326.1	325.7
172.5°	328.4	328.8	329.2	329.3	328.9	328.5	328.2	327.8
175°	330.6	331.0	331.4	331.4	331.1	330.7	330.3	329.9
177.5°	331.6	331.8	332.2	332.2	331.8	331.6	331.3	331.0
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7

(END OF REPORT)